



RHC121206

by Wiegmann
Catalog ID: RHC121206

N3R Continuous Hinge Wall-Mount 12X12X6 Carbon Steel - Gray

RHC SERIES - 16 GAUGE CARBON STEEL NEMA 3R SMALL HINGE COVER WALL-MOUNT- ENCLOSURE SIZE 12.06 IN X 12.00 IN X 6.13 IN.

- Bodies and doors fabricated from 16 gauge carbon steel. Continuous hinge. Lid is supplied with a padlockable draw latch. Hinge is made of carbon steel with a stainless steel hinge pin. Standard size enclosures are provided with knockouts in bottom. Weldnuts provided for mounting optional back panels. External mounting plates, top and bottom of enclosure. Knockouts on bottom of enclosure. Grounding provisions provided.

Product Details

General

Application	Designed for use as wiring boxes and junction boxes. Provides protection in outdoor installations against rain, sleet, and snow, or indoors against dripping water.
Color	Gray
Construction	Spot Welded
Cover Type	Hinged Cover
Finish Type	Textured
Knockouts	Yes
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	External Mounting Plates
Mounting Type	Wall Mount
Type	Enclosure
UPC	786725406456

Dimensions

Actual Depth	6.13 in
Actual Height	12.060 in
Cubic Capacity	864 cu.in
Depth	6 in

Height	12 in
Weight	12 lb
Width	12 in

Conductor Related

Cable Entry	Knock Outs
-------------	------------

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 3R
UL Listed	Yes