



## RSCG040436G

by Wiegmann  
Catalog ID: RSCG040436G

N3R Gutter 4X4X36 Carbon Steel - Galv

- Trough and cover fabricated from 16 gauge G-90 pre-galvanized steel. Drip shield top and smooth seamless sides, front and back, prevent rain, snow, and sleet from entering the enclosure. Embossed mounting holes are conveniently located on the back. A slip-on removable cover is securely fastened with screws located along the bottom edge. Knockouts are provided on bottom of enclosure.

### Product Details

#### General

Application	Designed to protect wiring in outdoor installations against rain, sleet and snow, or indoors against dripping water.
Construction	Spot and Tack Welded
Finish Type	Galvanized
Knockouts	Yes
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Embossed mounting holes
Type	Gutter
UPC	786725408160

#### Dimensions

Actual Depth	36.13 in
Actual Height	4.060 in
Actual Width	4.060 in
Cubic Capacity	576 cu.in
Depth	36 in
Height	4 in
Weight	13.25 lb
Width	4 in

#### Conductor Related

Cable Entry	Knock Outs
-------------	------------

#### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	3R
UL Listed	Yes