

by Wiegmann Catalog ID: RSCG080818NK

N3R Gutter - No Knockouts 8X8X18 Carbon Steel - Gray

 Trough and cover fabricated from 16 gauge carbon steel. Drip shield top and smooth seamless sides, front and back, prevent rain, snow, and sleet from entering the enclosure. Embossed mounting holes are conveniently located on the back. A slip-on removable cover is securely fastened with screws located along the bottom edge.

Product Details

General

Application	Designed to protect wiring in outdoor installations against rain, sleet and
	snow, or indoors against dripping water.
Color	Gray
Construction	Spot and Tack Welded
Finish Type	Polyester Powder
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Embossed mounting holes
Туре	Gutter
UPC	786725874927

Dimensions

Actual Depth	18.13 in
Actual Height	8.060 in
Actual Width	8.060 in
Cubic Capacity	1152 cu.in
Depth	18 in
Height	8 in
Weight	16 lb
Width	8 in

Certifications and Compliance

Certified Listed	• UL • CSA
Nema Rating	3R
UL Listed	Yes