



RSCG121224NK

by Wiegmann
Catalog ID: RSCG121224NK

N3R Gutter - No Knockouts 12X12X24 Carbon Steel - Gray

- Trough and cover fabricated from 16 gauge carbon steel. Drip shield top and smooth seamless sides, front and back, prevent rain, snow, and sleet from entering the enclosure. Embossed mounting holes are conveniently located on the back. A slip-on removable cover is securely fastened with screws located along the bottom edge.

Product Details

General

| | |
|-----------------|--|
| Application | Designed to protect wiring in outdoor installations against rain, sleet and snow, or indoors against dripping water. |
| Color | Gray |
| Construction | Spot and Tack Welded |
| Finish Type | Polyester Powder |
| Knockouts | No |
| Listings | UL, CSA |
| Material | Carbon Steel |
| Mounting Method | Embossed mounting holes |
| Type | Gutter |
| UPC | 786725875313 |

Dimensions

| | |
|----------------|------------|
| Actual Depth | 24.13 in |
| Actual Height | 12.060 in |
| Cubic Capacity | 3456 cu.in |
| Depth | 24 in |
| Height | 12 in |
| Weight | 24 lb |
| Width | 12 in |

Certifications and Compliance

| | |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none">• UL• CSA |
| Nema Rating | 3R |
| UL Listed | Yes |