



S22120GNK

by Wiegmann
Catalog ID: S22120GNK

N1 Screw-Cover Wireway - No Knockouts 2.5X2.5X120 Carbon Steel - Galvanized

- S Series screw cover design covers held firmly in place with captivated screw fasteners. Straight sections with knockouts are provided on side walls on wireways.

Product Details

General

Application	Designed to protect electrical wiring in applications where dirt, dust, oil and water are not serious problems. All sections are open on one side so wires and cable can be laid in along an entire wireway run.
Construction	Formed
Cover Type	Screw Cover
Finish Type	Galvanized
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Type	Wireway
UPC	786725851584

Dimensions

Actual Height	2.500 in
Actual Length	120.000 in
Actual Width	2.500 in
Depth	120 in
Height	3 in
Weight	90 lb
Width	3 in

Certifications and Compliance

Certified Listed	• UL • CSA
Nema Rating	1
UL Listed	Yes