



## S6612GNK

by Wiegmann  
Catalog ID: S6612GNK

N1 Screw-Cover Wireway - No Knockouts 6X6X12 Carbon Steel - Galvanized

- Bodies and covers are fabricated from 16 gauge pre-galvanized steel. S Series screw cover design covers held firmly in place with captivated screw fasteners.

## Product Details

### General

Application	Designed to protect electrical wiring in applications where dirt, dust, oil, and water are not serious problems. All sections are open on one side so wires and cable can be laid in along an entire wireway run.
Cover Type	Screw Cover
Enclosure Type	Nema 1 Type Enclosure
Finish Type	Galvanized
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Type	Wireway
UPC	786725851744

### Dimensions

Actual Length	12.000 in
Depth	12 in
Height	6 in
Weight	5.5 lb
Width	6 in

### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"> <li>UL</li> <li>CSA</li> </ul>
Nema Rating	1

UL Listed	Yes
-----------	-----