



## SC121206

by Wiegmann  
Catalog ID: SC121206

N1 Screw-Cover 12X12X6 Carbon Steel - Gray

SC SERIES - 16 GAUGE CARBON STEEL NEMA 1 SCREW COVER WALL-MOUNT WITH KNOCKOUTS - ENCLOSURE SIZE 12-1/8 IN X 12-1/8 IN X 6-3/16 IN.

- Fabricated from 16 gauge steel. Flat, removable covers fastened with plated steel screws. Cover design permits easy removal without extracting cover screws. Mounting holes on back of box. Removable concentric knockouts on all four sides.

### Product Details

#### General

Application	Designed for use as a junction box and pull box in commercial and general industrial applications. Flush covers must be ordered separately for flush mount applications.
Color	Gray
Construction	Spot Welded
Cover Type	Screw Cover
Finish Type	Textured
Knockouts	Yes
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Embossed Mounting Holes
Mounting Type	Wall Mount
Type	Enclosure
UPC	786725314003

## Dimensions

Actual Height	12.125 in
Actual Width	12.125 in
Depth	6 in
Height	12 in
Weight	12 lb
Width	12 in

## Conductor Related

Cable Entry	Knock Outs
-------------	------------

## Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	NEMA 1
UL Listed	Yes