



# SSJW410

by Wiegmann  
Catalog ID: SSJW410

N4X Hinged Wireway 4X4X120 304 Stainless Steel

## Product Details

### General

Accessory Type	Wireway
Application	Designed to protect electrical wiring in areas where corrosion problems exist.
Color	Stainless Steel
Cover Type	Hinged Cover
Enclosure Type	Nema 4X & 12 Type Enclosure
Finish Type	Smooth Grained
Knockouts	No
Listings	UL, CSA
Material	304 Stainless Steel
Type	Wireway
UPC	786725481309

### Dimensions

Actual Length	120.000 in
Depth	120 in
Height	4 in
Weight	52 lb

Width	4 in
-------	------

#### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	4X
UL Listed	Yes