

T6618CH

by Wiegmann Catalog ID: T6618CH

N1 Hinged-Cover Wire Trough 6X6X18 Carbon Steel - Gray

- Designed to protect wiring from dirt, dust, oil and water.
- Trough and cover fabricated from 14 gauge steel. Continuously welded seams ground smooth, less knockouts or holes. Oil resistant gasket and adhesive are provided. Trough comes complete with easy to operate external clamps and a continuous hinge. External mounting feet are provided.

## **Product Details**

## General

Accessory Type	Trough
Application	Designed to protect from dirt, dust, oil, and water.
Color	Gray
Cover Type	Hinged Cover
Enclosure Type	Nema 12 Type Enclosure
Finish Type	Polyester Powder
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Туре	Trough
UPC	786725326594

## Dimensions

Actual Length	18.000 in
Depth	18 in
Height	6 in
Weight	12 lb
Width	6 in

Certifications and Compliance

Certified Listed	• UL • CSA
Nema Rating	NEMA 12
UL Listed	Yes