



WA121204GSCG

by Wiegmann

Catalog ID: WA121204GSCG

N4 Gasketed Screw-Cover 12X12X4 Carbon Steel - Galvanized

- Bodies and covers fabricated from 14 gauge G-90 grade galvanized steel. Seams are continuously welded and ground smooth. Cover contains closed cell oil resistant neoprene gasket. Enclosure comes with stainless steel cover screws which thread into sealed wells to prevent liquid, dust, etc from entering into the box through the screw holes. Ground stud located in door. No holes, knockout, or rear mounting holes.

Product Details

General

Application	Designed for use as wiring box, junction box, pull box, and terminal box in many indoor or outdoor applications where dust or moisture is a problem.
Construction	Continuously Welded Seams
Cover Type	Screw Cover
Finish Type	Galvanized
Listings	UL
Material	Carbon Steel
Mounting Method	Mounting Holes
Type	Enclosure
UPC	786725848744

Dimensions

Actual Depth	4.25 in
Actual Height	4.250 in
Actual Width	12.630 in
Cubic Capacity	208 cu.in
Depth	4 in
Height	4 in
Weight	12 lb
Width	13 in

Certifications and Compliance

Certified Listed	UL
Nema Rating	4
UL Listed	Yes