



WA161608GSC

by Wiegmann
Catalog ID: WA161608GSC

N4 Gasketed Screw-Cover 16X16X8 Carbon Steel - Gray

- Bodies and covers fabricated from 14 gauge carbon steel. Seams are continuously welded and ground smooth. Cover contains closed cell oil resistant neoprene gasket. Enclosure comes with stainless steel cover screws which thread into sealed wells to prevent liquid, dust, etc from entering into the box through the screw holes. Ground stud located in door. No holes, knockout, or rear mounting holes.

Product Details

General

Application	Designed for use as wiring box, junction box, pull box, and terminal box in many indoor or outdoor applications where dust or moisture is a problem.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Screw Cover
Finish Type	Smooth
Listings	UL
Material	Carbon Steel
Mounting Method	Mounting Holes
Type	Enclosure
UPC	786725848799

Dimensions

Actual Depth	11.25 in
Actual Height	11.250 in
Actual Width	12.060 in
Cubic Capacity	1452 cu.in
Depth	11 in
Height	11 in
Weight	25 lb
Width	12 in

Certifications and Compliance

Certified Listed	UL
Nema Rating	4
UL Listed	Yes

