



WA242408FM

by Wiegmann
Catalog ID: WA242408FM

N12 Single Door Flush Wall-Mount 24X24X8 Carbon Steel - Gray

Designed to house electrical controls, terminals and instruments. Provide protection from dirt, dust, oil, and water. External frame allows enclosure to recessed in wall. Enclosure is used in applications where external space is limited or in high traffic area.

Product Details

General

Application	Designed to house electrical controls, terminals and instruments. Provides protection from dirt, dust, oil and water. External frame allows enclosure to be recessed in a wall. Enclosure is used in applications where external space is limited or in high traffic areas.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Door
Finish Type	Smooth
Latches Type	Captivated Screws
Listings	UL, CSA
Material	Carbon Steel
Mounting Type	Wall Mount
Number of Doors (Fixed)	1
Type	Enclosure
UPC	786725446209

Dimensions

Depth	8 in
Height	24 in
Weight	63 lb
Width	24 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 12
UL Listed	Yes