



WA72XM6518SSN4

by Wiegmann
Catalog ID: WA72XM6518SSN4

N4X Double Door Right Flanged Disconnect 72X65X18 304 Stainless Steel

Product Details

General

| | |
|-------------------------|---|
| Application | Enclosures having the "WM" preferred cutout are sized for use with up to 200A disconnect switches and up to 400A circuit breakers unless otherwise specified. The "WM" preferred cutout accepts the smaller operating handle whose mounting hole centers are 4. |
| Construction | Continuously Welded Seams |
| Finish Type | Smooth Grained |
| Latches Type | 3-Point Padlocking Handle |
| Listings | UL, CSA |
| Material | 304 Stainless Steel |
| Mounting Type | Freestanding |
| Number of Doors (Fixed) | 2 |
| Type | Enclosure |
| UPC | 786725869824 |

Dimensions

| | |
|---------------|-----------|
| Actual Depth | 18.12 in |
| Actual Height | 72.120 in |
| Actual Width | 65.750 in |

| | |
|----------------|-------------|
| Cubic Capacity | 85536 cu.in |
| Depth | 18 in |
| Height | 72 in |
| Weight | 815 lb |
| Width | 66 in |

Certifications and Compliance

| | |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none">• UL• CSA |
| Nema Rating | 4X |
| UL Listed | Yes |