



WA84XM3924SSN4

by Wiegmann
Catalog ID: WA84XM3924SSN4

N4X Single Door Right Flanged Disconnect 84X39X24 304 Stainless Steel

Product Details

General

Application	Enclosures having the "WM" preferred cutout are sized for use with up to 200A disconnect switches and up to 400A circuit breakers unless otherwise specified. The "WM" preferred cutout accepts the smaller operating handle whose mounting hole centers are 4.
Construction	Continuously Welded Seams
Finish Type	Smooth Grained
Latches Type	3-Point Padlocking Handle
Listings	UL, CSA
Material	304 Stainless Steel
Mounting Type	Freestanding
Number of Doors (Fixed)	1
Type	Enclosure
UPC	786725869770

Dimensions

Actual Depth	24.12 in
Actual Height	84.120 in
Actual Width	39.500 in

Cubic Capacity	80640 cu.in
Depth	24 in
Height	84 in
Weight	660 lb
Width	40 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	4X
UL Listed	Yes