



## WADW150902SS

by Wiegmann

Catalog ID: WADW150902SS

NEMA 4X Deep Hinged Window 14.8X9.5X2.8 304 Stainless Steel

The Wiegmann Universal Deep Hinged Door Kit is styled after Wiegmann's N412 Ultimate Series enclosures. Kits are compatible with any NEMA 3R, 4, 4X, and 12 rated enclosures.

- Quarter-turn style latching for easy access
- Poured in place gasket
- Removable concealed hinge
- Drill template included for ease of mounting and guaranteed alignment
- Polycarbonate window for clear visibility

### Product Details

#### General

Accessory Type	Window/Door Kit
Color	Stainless Steel
Finish Type	Stainless Steel
Latches Type	Quarter Turn Latch
Material	304 Stainless Steel
Type	Accessory
UPC	786725876693

#### Dimensions

Actual Depth	2.75 in
Actual Height	14.75 in
Actual Width	9.5 in
Depth	2 in
Height	15 in
Width	9 in

#### Certifications and Compliance

Certified Listed	UL Recognized 508A
Nema Rating	4X

