



## WADW231702

by Wiegmann  
Catalog ID: WADW231702

NEMA 4 Deep Hinged Window 22.8X17.5X2.8 Carbon Steel-Gray

The Wiegmann Universal Deep Hinged Door Kit is styled after Wiegmann's N412 Ultimate Series enclosures. Kits are compatible with any NEMA 3R, 4, 4X, and 12 rated enclosures.

- Quarter-turn style latching for easy access
- Poured in place gasket
- Removable concealed hinge
- Drill template included for ease of mounting and guaranteed alignment
- Polycarbonate window for clear visibility

### Product Details

#### General

Accessory Type	Window/Door Kit
Color	Gray
Finish Type	Polyester Powder
Latches Type	Quarter Turn Latch
Material	Carbon Steel
Type	Accessory
UPC	786725876747

#### Dimensions

Actual Depth	2.75 in
Actual Height	22.75 in
Actual Width	17.5 in
Depth	2 in
Height	23 in
Width	17 in

#### Certifications and Compliance

Certified Listed	UL Recognized 508A
Nema Rating	4, 12

