

WC10B

by Wiegmann Catalog ID: WC10B

N12 Single Door Console Body 40X24X17 Carbon Steel - Gray

Designed to hold electrical and electronic controls and instruments. Pushbuttons, pilot lights, meters, switches etc., can be mounted on sloping control surfaces. Interior components can be mounted on back panel and terminal straps. Heavy-duty construction provides protection from dirt, dust, oil and water.

- Fabricated from carbon steel
- · Seams are continuously welded and ground smooth
- Removable back panel is provided with the console.
- The large sloping control panel is hinged along the bottom edge.

Fabricated from 14 gauge steel. Seams are continuously welded and ground smooth. 3-point keylocking handle is provided on front, main door. Flush main door. Control panels are hinged along bottom edge. Control panels have captive screws which thread into sealed wells. Door stops provided to hold control panel open. Print pocket is provided. Standard closed cell neoprene gasket is provided. Removable back panel is included with enclosure. Ground provisions provided.

Product Details

General

Designed to hold electrical and electronic controls and instruments. Pushbuttons, pilot lights, meters, switches, etc., can be mounted on sloping control surfaces. Interior components can be mounted on standard back panel and terminal straps. Heavy duty c
Gray
Continuously Welded Seams
Door
Polyester Powder
3-Point Keylocking Handle
UL, CSA

Material	Carbon Steel
Number of Doors (Fixed)	1
Series	WC10
Туре	Console Body
UPC	786725443000
Dimensions	
Actual Height	40.130 in
Actual Width	24.13 in
Depth	17 in
Height	40 in
Weight	129 lb
Width	24 in
Certifications and Compliance	
Certified Listed	• UL • CSA
Nema Rating	NEMA 12
UL Listed	Yes