



WC1436T

by Wiegmann
Catalog ID: WC1436T

Top For WC1436B Carbon Steel - Gray

Designed to hold electrical and electronic controls and instruments. Pushbuttons, pilot lights, meters, switches etc., can be mounted on the instrument panel. Interior components are motorized on stationary sub panels, swing-out sub panels or relay rack angles (panels are optional). Heavy duty construction provides protection from dirt, dust, oil and water. Numerous accessories and variable combinations make these consoles most versatile.

- Fabricated from 14 gauge steel. Top unit is 12.5" deep to accommodate most instruments. Seams are continuously welded and ground smooth, less knockouts or holes. Instrument and access panels have captivated screws which thread into sealed wells. 4 holes are provided in bottom of top for mounting to body. Instrument and access panels are removable. Closed cell neoprene gasket.

Product Details

General

| | |
|-----------------|-------------------------------|
| Application | For use with WC1436B console. |
| Color | Gray |
| Construction | Continuously Welded Seams |
| Cover Type | Screw |
| Finish Type | Polyester Powder |
| Listings | UL, CSA |
| Material | Carbon Steel |
| Mounting Method | Mounting Holes |
| Series | WC14 |
| Type | Console Top |
| UPC | 786725444052 |

Dimensions

| | |
|---------------|-----------|
| Actual Depth | 16.13 in |
| Actual Height | 12.630 in |
| Actual Width | 36.13 in |
| Depth | 16 in |
| Height | 13 in |
| Weight | 62 lb |
| Width | 36 in |

Certifications and Compliance

| | |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none">• UL• CSA |
| Nema Rating | NEMA 12 |
| UL Listed | Yes |