

WC14B

by Wiegmann Catalog ID: WC14B

N12 Single Door Console Body 50X24X23 Carbon Steel - Gray

Designed to hold electrical and electronic controls and instruments. Pushbuttons, pilot lights, meters, switches etc., can be mounted on the instrument panel. Interior components are motorized on stationary sub panels, swing-out sub panels or relay rack angles (panels are optional). Heavy duty construction provides protection from dirt, dust, oil and water. Numerous accessories and variable combinations make these consoles most versatile.

Product Details

General

Application	Designed to hold electrical and electronic controls and instruments. Pushbuttons, pilot lights, meters, switches, etc., can be mounted on the instrument panel. Interior components are motorized on stationary sub panels, swing-out sub panels, or relay rack
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Door
Finish Type	Polyester Powder
Latches Type	3-Point Keylocking Handle
Listings	UL, CSA
Material	Carbon Steel
Number of Doors (Fixed)	1
Series	WC14
Туре	Console Body
UPC	786725443604

Dimensions

Actual Depth	23.13 in
Actual Height	50.130 in
Actual Width	24.13 in
Depth	23 in
Height	50 in
Weight	181 lb
Width	24 in

Certifications and Compliance

Certified Listed	• UL • CSA
Nema Rating	NEMA 12
UL Listed	Yes