TrukTrak® Systems

Ideal for Heavy Vehicle Traffic in Industrial, Commercial or Public Applications

- High density polyurethane construction supports heavy loads and is weather resistant
- Modular interlocking design for easy installation, breakdown and storage
- Safety surface pattern reduces slipping and skidding
- High visibility safety blue and yellow colors



HBLTT5B



HBLTT545LB



HBLTT545RB

TrukTrak® Systems	A	B	C	D	E		
	Trak			Channel			
Description	Length in. (mm)	Width in. (mm)	Height in. (mm)	Width in. (mm)	Height in. (mm)	Weight lbs. (kg)	Catalog Number
5 Channel TrukTrak®, blue and yellow.	36.0" (914)	20" (508)	2.31" (58.7)	1.25" (31.8)	1.25" (31.8)	30.60 (13.9)	**HBLTT5B**
5 Channel TrukTrak® end caps (pair only), yellow.	7.50" (190) 5.25" (133)	20" (508) 20" (508)	2.31" (58.7) 2.31" (58.7)	1.25" (31.8) 1.25" (31.8)	1.25" (31.8) 1.25" (31.8)	8.55 (3.9) 8.55 (3.9)	**HBLTT5ECB** (Female end) (Male end)
5 Channel 45° right turn TrukTrak®, blue and yellow.	25.0" (635)	20" (508)	2.31" (58.7)	1.25" (31.8)	1.25" (31.8)	15.35 (7.0)	**HBLTT545RB**
5 Channel 45° left turn TrukTrak®, blue and yellow.	25.0" (635)	20" (508)	2.31" (58.7)	1.25" (31.8)	1.25" (31.8)	14.45 (6.6)	**HBLTT545LB**
3 Channel TrukTrak®, blue and yellow.	36.0" (914)	20" (508)	3.05" (77.5)	2.25" (57.2)	2.25" (57.2)	30.85 (14.0)	**HBLTT3B**
3 Channel TrukTrak® end caps (pair only), yellow.	8.25" (209) 6.38" (162)	20" (508) 20" (508)	3.05" (77.5) 3.05" (77.5)	2.25" (57.2) 2.25" (57.2)	2.25" (57.2) 2.25" (57.2)	10.25 (4.6) 10.25 (4.6)	**HBLTT3ECB** (Female end) (Male end)
2 Channel TrukTrak®, blue and yellow.	36.0" (914)	22" (559)	4.13" (104.9)	3.25" (82.6)	3.25" (82.6)	41.00 (18.6)	**HBLTT2B**

TrukTrak (Top view)



TrukTrak (Side view)

End Caps



45° Left Turn



45° Right Turn



Specifications

Material	Polyurethane.
Operating Temperature	-40°F to +120°F (-40°C to +49°C).
Hinge Material	Reinforced fiberglass.
Safety Symbols	Per ANSI Z535.3.

Load Capacity

No. of Channels	Test Fixture Footprint Inches (mm)	Tire Load lbs. +/- 20%		Axle Load lbs. +/- 20%	
		70°F (21°C)	120°F (49°C)	70°F (21°C)	120°F (49°C)
5	6.9" x 17.3" (175 X 439)	20,150	9,200	40,300	18,400
3	6.9" x 17.3" (175 X 439)	14,210	4,653	28,420	9,306
2	6.9" x 17.3" (175 X 439)	10,880	2,095	21,760	4,190

Dimensions in Inches (mm)