Wire Basket Tray System

Electroplated Zinc Round Cross-Wire Basket Tray

Features

- T-weld construction prevents snags
- 5mm round wire minimum
- High load rating
- Easy to cut and fabricate fittings in the field
- 2" x 4" mesh opening
- Use factory support hardware or fabricate supports at the job site
- Electroplated zinc galvanized (post plated) made from cabon steel and plated to ASTM B 633, Type III, SC-1

Field Configurable Fittings

90° Sweep Elbow

Use appropriate quantity of splice kits

Tee Fitting

Use one HBTCS corner splice per each

Supports and Hardware



Ordering Information

See page V-12

Wire Diameter



.1969" Dia.
"Round" Wire Design

Dimensions in Inches (mm)

10 Feet per Length 118.3" (3m) 10 pc. min. order qty.	Tray Width	Load (Lb/ft)	Tray Weight per Length (Lb)	Splice Quantity*		Finish
				90° Sweep Elbow	Straight Splice	Electroplated Zinc
2" Deep Tray	4" (102)	45	7	2	2	**HBT0204ZP**
	6" (152) ●	50	9	3	4	**HBT0206ZP**
	8" (203) ●	52	10.5	4	4	**HBT0208ZP**
	12" (305) ●	58	12	6	4	**HBT0212ZP**
	16" (406) ●	70	15	7	4	**HBT0216ZP**
	18" (457) ●	70	23	9	4	**HBT0218ZP**
	20" (508) ●	73	25	9	5	**HBT0220ZP**
	22" (559)	73	27	12	5	**HBT0222ZP**
	24" (610) ●	75	31	12	5	**HBT0224ZP**
	26" (660)	73	33	13	6	**HBT0226ZP**
	28" (711)	73	35	14	6	**HBT0228ZP**
	30" (762)	70	38	15	6	**HBT0230ZP**
	32" (813)	70	39	16	6	**HBT0232ZP**
4" Deep Tray	4" (102)	49	12	2	4	**HBT0404ZP**
	6" (152) ●	49	13	3	5	**HBT0406ZP**
	8" (203) ●	78	15	4	6	**HBT0408ZP**
	12" (305) ●	78	23	6	6	**HBT0412ZP**
	16" (406) ●	108	27	7	7	**HBT0416ZP**
	18" (457) ●	116	29	9	7	**HBT0418ZP**
	20" (508) ●	116	31	9	7	**HBT0420ZP**
	22" (559)	116	33	12	8	**HBT0422ZP**
	24" (610) ●	116	35	12	8	**HBT0424ZP**
	28" (711)	108	39	14	9	**HBT0428ZP**
6" Deep Tray	8" (203) ●	116	23	4	6	**HBT0608ZP**
	12" (305) ●	123	27	6	6	**HBT0612ZP**
	16" (406) ●	123	31	7	7	**HBT0616ZP**
	18" (457) ●	127	33	9	7	**HBT0618ZP**
	20" (508) ●	127	35	9	7	**HBT0620ZP**
	22" (559) ●	127	37	12	8	**HBT0622ZP**
	24" (610) ●	150	39	12	8	**HBT0624ZP**
8" Deep Tray	8" (203) ●	116	27	4	8	**HBT0808ZP**
	12" (305) ●	116	31	6	8	**HBT0812ZP**
	16" (406) ●	116	35	7	9	**HBT0816ZP**
	18" (457) ●	116	37	9	9	**HBT0818ZP**
	20" (508) ●	116	39	9	9	**HBT0820ZP**

Note: ●UL Classified/cUL Classified as equipment ground conductor.
All dimensions are +/- 0.25".
**See page V-13 for details and page V-14 for wire fill and maximum load chart.*