

# RACO SPECIALTY SWITCHES



PULL-CHAIN AND ROCKER SWITCHES



6401, 6354



6402, 6355



6403, 6404



6405



6436



6437

**APPLICATIONS**

- Industrial
- Electronic Instruments
- Automotive/marine equipment
- Power tools
- Home appliances
- Emergency lighting
- Vending machines

**PRODUCT FEATURES:**

**PULL-CHAIN SWITCHES**

- Plastic body and 3/8" nipple - UNS 27 x 5/16" long
- Aluminum knurled nut, brass or nickel finish

**VARIABLE SPD. PULL-CHAIN SWITCHES**

- Plastic body and 3/8" nipple - UNS 27 x 5/16" long
- Brass knurled nut

**ALL ANGLE PULL-CHAIN SWITCHES**

- Plastic body and 15/32" metal nipple - UNS 32
- Steel locknut

**PRODUCT FEATURES:**

**SNAP-IN ROCKER SWITCHES**

- Nylon body and rocker
- Polycarbonate rocker (#6437)
- Contacts - silver-plated copper alloy
- .250 quick connect tabs
- Fits cutout 17/32" x 1-1/8"

CATALOG NUMBER	DESCRIPTION	ELECTRICAL RATINGS	UNIT CTN. QTY.	SHIP CTN. QTY.	UPC BAR CODE
<b>Pull-chain Switches – For Lamps and Ceiling Fixtures</b>					
6401	SPST, ON-OFF 6" Leads, Brass Finish, Carded	6 Amp/125V AC, 3 Amp/250V AC, 6 Amp/125V L	5	—	
6354	SPST, ON-OFF 6" Leads, Brass Finish, Bulk Poly Bag	6 Amp/125V AC, 3 Amp/250V AC, 6 Amp/125V L	25	—	
6402	SPST, ON-OFF 6" Leads, Nickel Finish, Carded	6 Amp/125V AC, 3 Amp/250V AC, 6 Amp/125V L	5	—	
6355	SPST, ON-OFF 6" Leads, Nickel Finish, Bulk Poly Bag	6 Amp/125V AC, 3 Amp/250V AC, 6 Amp/125V L	25	—	
<b>Variable Speed Pull-chain Switches – For Ceiling Fans</b>					
6403	2 Speed, OFF-ON-ON, Stab Connections, Brass Finish, Carded	6 Amp/125V AC, 3 Amp/250V AC, 6 Amp/125V L	5	—	
6404	3 Speed, OFF-ON-ON-ON, Stab Connections, Brass Finish, Carded	6 Amp/125V AC, 3 Amp/250V AC	5	—	
<b>All Angle Pull-chain Switch – For Ceiling Fixtures</b>					
6405	All Angle, ON-OFF, 3" Leads SPST, Carded	6 Amp/125V AC, 3 Amp/250V AC	5	—	
<b>Snap-in Rocker Switches – For Range Hood and Appliances</b>					
6436	Rocker, SPST, ON-OFF, Opening 17/32" x 1-1/8", Carded	16 Amp/250V AC, 1 HP, 250V AC, 1/2 HP, 125V AC	5	—	
6437	Lighted Rocker, SPST, ON-OFF, Opening 17/32" x 1-1/8", Carded	110V Lamp, 16 Amp/250V AC, 15 Amp, 1 HP, 250V AC, 1/2 HP, 125V AC	5	—	

# SWITCHES

## CANOPY SWITCHES



CATALOG NUMBER	DESCRIPTION	ELECTRICAL RATINGS	UNIT CTN. QTY.	SHIP CTN. QTY.	UPC BAR CODE
<b>Rotary Canopy Switches – For Lamps and Appliances</b>					
6445	Rotary, Canopy, SPST, OFF-ON-ON-ON, Plastic Knob, Carded	2 Amp/250V AC, 4 Amp/125V AC, 1 Amp/125V DC	5	—	
6446	Rotary, Canopy, SPST, ON-OFF, 6" Leads, Plastic Knob, Carded	1 Amp/250V AC, 3 Amp/120V AC, 1 Amp/125V ACL	5	—	
6356	Rotary, Canopy, SPST, ON-OFF, 6" Leads, Plastic Knob, Bulk Poly Bag	1 Amp/250V AC, 3 Amp/120V AC, 1 Amp/125V ACL	25	—	
6447	Rotary, Canopy, SPST, ON-OFF, 6" Leads, Brass Knob, Carded	1 Amp/250V AC, 3 Amp/120V AC, 1 Amp/125V ACL	5	—	
6448RAC	Rotary, Canopy, 2-Circuit, OFF-ON-ON-ON, 6" Leads, Brass Knob, Carded	1 Amp/250V AC, 3 Amp/125V ACL	5	—	
6357	Rotary, Canopy, 2-Circuit, OFF-ON-ON-ON, 6" Leads, Brass Knob, Bulk Poly Bag	1 Amp/250V AC, 3 Amp/125V ACL	25	—	
<b>Maintained Contact Push-Button Canopy Switches – For Lamps and Appliances</b>					
6424	Push, Canopy, SPST, ON-OFF, 6" Leads, Brass, Carded	1 Amp/250V AC, 2 Amp/125V ACL, 3 Amp/120V AC	5	—	
6352	Push, Canopy, SPST, ON-OFF, 6" Leads, Brass, Bulk Poly Bag	1 Amp/250V AC, 2 Amp/125V ACL, 3 Amp/120V AC	25	—	
6425	Push, Canopy, SPST, ON-OFF, 6" Leads, Nickel, Carded	1 Amp/250V AC, 2 Amp/125V ACL, 3 Amp/120V AC	5	—	
6353	Push, Canopy, SPST, ON-OFF, 6" Leads, Nickel, Bulk Poly Bag	1 Amp/250V AC, 2 Amp/125V ACL, 3 Amp/120V AC	25	—	

**APPLICATIONS**

- Industrial
- Electronic Instruments
- Automotive/marine equipment
- Power tools
- Home appliances
- Emergency lighting
- Vending machines

SLIDE AND PUSH BUTTON SWITCHES



6431



6426



6428



6427



6358

**PRODUCT FEATURES**

- Plastic Case
- Nickel-plated brass nipple, knurled nut, hex nut
- Nipple 15/32" - 32 x 1/2" long

CATALOG NUMBER	DESCRIPTION	ELECTRICAL RATINGS	UNIT CTN. QTY.	SHIP CTN. QTY.	UPC BAR CODE
<b>Maintained Contact Slide Switch – For Lamps and Appliances</b>					
6431	Slide, SPST, ON-OFF, Opening 9/16" x 7/8", Carded	5 Amp/250V AC, 11 Amp/125V AC	5	—	
<b>Momentary Contact Push Button Switches – For Bells and Buzzers</b>					
6426	Contact, SPST, OFF-ON, Normally OFF, Push ON, Black, Screw Terminals, Carded	3 Amp/240V AC 6 Amp/120V AC	5	—	
6428	Contact, SPST, OFF-ON, Normally ON, Push OFF, Red, Screw Terminals, Carded	1.5 Amp/277V AC 3 Amp/120V AC	5	—	
<b>Push Button Switches – For Lamps and Appliances</b>					
6427	Push Button, SPST, ON-OFF, 6" Leads, Carded	10 Amp/125V AC, 8 Amp/125V AC 4 Amp/250V, 1/3 HP, 125V AC	5	—	
6358	Double Insulated, SPST, ON-OFF, 6" Wire Leads, Bulk Poly Bag	2 Amp/125V ACL, 3 Amp/120V AC, 1 Amp/250V AC	25	—	

# SWITCHES

## TOGGLE SWITCHES



6415



6419



6416



6410RAC



6413



6411



6420



6417



6418



6414

CATALOG NUMBER	DESCRIPTION	ELECTRICAL RATINGS	UNIT CTN. QTY.	SHIP CTN. QTY.	UPC BAR CODE
<b>Extra Heavy-Duty Bat Handle Toggle Switches</b>					
6415	DPST, ON-OFF, Screw Terminals Carded	10 Amp/277V AC, 20 Amp/125V AC, 1-1/2 HP, 125V/250V AC	5	—	
6419	DPDT, ON-ON, Screw Terminals Carded	10 Amp/277V AC, 20 Amp/125V AC, 1-1/2 HP, 125V/250V AC	5	—	
6416	DPDT, ON-OFF-ON, Screw Terminals Carded	20 Amp/125V AC, 1-1/2 HP, 125V/250V AC	5	—	
<b>Extra Heavy-Duty Bat Handle Toggle Switches – Nonmetallic</b>					
6417	SPST, ON-OFF, Screw Terminals Nonmetallic, Carded	20 Amp, 125V//277V AC, 1-1/2 HP, 125V AC, 2 HP, 250V AC	5	—	
6418	DPDT, ON-OFF-ON, Screw Terminals Nonmetallic, Carded	20 Amp, 125V//277V AC, 2 HP, 250V AC, 1-1/2 HP, 125V AC	5	—	
<b>Heavy-Duty Bat Handle Toggle Switches</b>					
6410RAC	SPST, ON-OFF, Screw Terminals, Carded	12 Amp/250V AC, 20 Amp/125V AC, 1 HP, 120V/240V AC	5	—	
6413	SPDT, ON-ON, Screw Terminals, Carded	10 Amp/250V AC, 20 Amp/125V AC, 3/4 HP, 125V/250V AC	5	—	
6411	SPDT, ON-OFF-ON, Screw Terminals	10 Amp/250V AC, 20 Amp/125V AC, 3/4 HP, 125V AC	5	—	
6420	SPST, ON-OFF, Screw Terminals, Carded	10 Amp/250V AC, 20 Amp/125V AC, 3/4 HP, 125V/250V AC	5	—	
<b>Medium-Duty Bat Handle Toggle Switches</b>					
6414	SPST, ON-OFF, Screw Terminals, Carded	15 Amp/120V AC, 10 Amp/240V AC	5	—	

**PRODUCT FEATURES**

- Impact-resistant thermoplastic body
- Silver cadmium oxide contacts
- Knurled nut, hex and strap all nickel-plated
- Keyed brass bushing
- #6-32 screw-type terminals
- Nickel-plated brass toggle
- Suitable for 12V DC use at rated amperage

TOGGLE SWITCHES



6412



6351



6409RAC



6441

**PRODUCT FEATURES**

- Impact resistant thermoplastic body
- Silver cadmium oxide contacts
- Knurled nut, hex and strap all nickel plated
- Keyed brass bushing
- #6-32 screw-type terminals
- Nickel plated brass toggle
- Suitable for 12V DC use at rated amperage

**PRODUCT FEATURES: TOGGLE BOOT**

- Fits standard bat handle toggle switches
- Made of silicone rubber
- Fits nipples with 15/32" - 32 thread
- Packed two per card

CATALOG NUMBER	DESCRIPTION	ELECTRICAL RATINGS	UNIT CTN. QTY.	SHIP CTN. QTY.	UPC BAR CODE
<b>Medium-Duty Bat Handle Toggle Switch – With Wire Leads</b>					
6412	SPST, ON-OFF, 6" Leads, Carded	4 Amp/250V, 8 Amp, 125V 10 Amp/125V AC, 1/3 HP, 125V AC	5	—	
<b>Medium-Duty Ball Handle Toggle Switch – With Wire Leads, Nonmetallic</b>					
6351	SPST, ON-OFF, Ball Handle Toggle for Power Tools & Appliances, 6" Wire Leads Bulk Poly Bag	6 Amp/125V AC 3 Amp/250V AC 3 Amp/125V ACL	25	—	
<b>Medium-Duty Ball Handle Toggle Switch</b>					
6409RAC	SPST, ON-OFF, Screw Terminals, Carded	6 Amp/120V AC 3 Amp/240V AC	5	—	
<b>Toggle Boot</b>					
6441	Rubber Cover & Nut for Toggle Switch, Carded	—	5	—	

# SWITCHES ACCESSORIES



6395

CATALOG NUMBER	DESCRIPTION	UNIT CTN. QTY.	UPC BAR CODE
<b>Display</b>			
6395	Plexiglass Counter Display	1	—

**PRODUCT FEATURES: DISPLAY**

- Counter display board holds 24 switches and features electrical ratings, operation type, and part numbers
- Switches sold separately

CATALOG NUMBER	DESCRIPTION	UNIT CTN. QTY.	SHIP CTN. QTY.	UPC BAR CODE
<b>Specialty Switch Assortment</b>				
6150	Specialty Switch Assortment Includes 5 each of 30 Switches	1	—	

**PRODUCT FEATURES: SWITCH ASSORTMENT**

- All cards are 2-7/8" wide x 5" high
- One carton of five fits on hook
- Hooks and pegboard are not included
- Blisters are 1" deep

INCLUDED PART NUMBERS					
6401	6409RAC	6414	6419	6427	6441
6402	6410RAC	6415	6420	6428	6445
6403	6411	6416	6424	6431	6446
6404	6412	6417	6425	6436	6447
6405	6413	6418	6426	6437	6448RAC

**Blister Card Packaging**

Typical applications for the switch

Reorder number

Basic description and characteristics

Visible packaging lets the customer see the switch details

Electrical Data - Amps, Volts, HP Ratings

Easy to match ratings with the switch

Easy to follow wiring diagram

Clear instructions for safe replacement

UPC Bar Code

**Poly Bagged Packaging**

