



*Commercial, Industrial
and Residential Electrical Products*

NEW! DEEP NONMETALLIC BOXES


Extra room for wiring in wet locations

Application

2-5/8" deep! These extra deep versions of our nonmetallic weatherproof outlet boxes provide extra room for wiring electrical junctions. One and two gang models available in gray or white.

Features

- 2-5/8" deep inside to provide extra room
- Durable high impact PVC construction with integrated lugs
- Threaded hubs for use with 3/4" or 1/2" conduit
- Includes plugs and reducer bushings
- Marine UL Listed
- NEC and NEMA 3R Compliant



NEC & NEMA 3R Compliant

| CAT. # | DESCRIPTION | CUBIC IN. CAPACITY <i>When used with collar</i> | THREADED ENTRIES | STD. PKG. | UPC A BAR CODE |
|--|--|--|------------------|-----------|----------------|
| NEW! 1-Gang Deep Outlet Boxes, Three Threaded Outlets | | | | | |
| PSBD37550GY | Seven 1/2" or 3/4" Holes, 2.625" Deep, Gray | 19.5" | (7) 3/4" or 1/2" | 8 | |
| PSBD37550WH | Seven 1/2" or 3/4" Holes, 2.625" Deep, White | 19.5" | (7) 3/4" or 1/2" | 8 | |
| NEW! 2-Gang Deep Outlet Boxes, Seven Threaded Outlets | | | | | |
| PDBD77550GY | Three 1/2" or 3/4" Holes, 2.625" Deep, Gray | 33.5" | (3) 3/4" or 1/2" | 6 | |
| PDBD77550WH | Three 1/2" or 3/4" Holes, 2.625" Deep, White | 33.5" | (3) 3/4" or 1/2" | 6 | |
| 1-Gang Outlet Boxes, Three Threaded Outlets | | | | | |
| PSB37550GY | Seven 1/2" or 3/4" Holes, 2.0" Deep, Gray | 16.5" | (7) 3/4" or 1/2" | 5 | |
| PSB37550WH | Seven 1/2" or 3/4" Holes, 2.0" Deep, White | 16.5" | (7) 3/4" or 1/2" | 8 | |
| 2-Gang Outlet Boxes, Seven Threaded Outlets | | | | | |
| PDB77550GY | Three 1/2" or 3/4" Holes, 2.0" Deep, Gray | 26.5" | (3) 3/4" or 1/2" | 6 | |
| PDB77550WH | Three 1/2" or 3/4" Holes, 2.0" Deep, White | 26.5" | (3) 3/4" or 1/2" | 6 | |



A Division of Hubbell Incorporated (Delaware)

BELL
Tempe, AZ
800-526-5416
www.hubbell.com/bell/en

