




Life Safety Support Products



For Immediate Identification



COMMERCIAL CONSTRUCTION
A Division of Hubbell Incorporated (Delaware)



RACO[®]

RED BOXES & COVERS

For Identification

Available in the most popular RACO[®] steel boxes and covers for general alarm and security applications. Allows an inspector or building owner to immediately identify alarm/fire or life safety systems.

- **Accommodates local codes for easy identification of products containing cabling relative to life safety systems**
- **Prevents the need for painting or labeling on the job site**
- **For industrial, commercial or residential applications**
- **All products have UL Listed, durable red polyester powder finish**
- **Manufactured from .062 thick steel**
- **Approved for use in 2 hour fire rated walls**

Large 66.7 Cu. In. Capacity Box gives you the RACO[®] advantage. This new design accommodates oversized alarm devices for use in industrial, commercial, or residential applications. **Catalog no. 911-15.**



4-11/16" sq. x 4" sq. adapter ring is raised 5/8" and accepts UFE safety appliances designed to mount to 4" sq. boxes.

Catalog no. 911-16.

4-11/16" sq. x 4" sq. adapter ring is raised 1-1/4" and accepts UFE safety appliances designed to mount to 4" sq. boxes.

Catalog no. 911-17.

RACO® **RETRO-RING®** FOR EXISTING CONSTRUCTION



Application

- RACO RETRO-RING® is used to position any depth, 4" square steel junction box in a sheet rock covered, wall cavity
- RACO 205RAC is used to position life safety devices
- RACO 206RAC is used in old work installations where one or two devices are required - with or without a box*
- RACO **911-19** RETRO-RING® is used to position any depth, 4" square steel junction box in a sheet rock covered, wall cavity - used to position life safety devices - painted red for immediate identification

Features

- Allows 4" square box to be quickly and easily mounted in old work application
- Accommodates any depth, 4" square box
- Works with up to 1-1/2" deep, drywall applications
- Small foot print is easily covered by wall plate (any wall plate or appliance greater than 4-13/32" W x 4-3/4" H)
- Steel old work wings allow for secure mounting of box and devices to wall
- Includes one wall template per carton for easy trace-&-cut-out
- Made from durable, .039" thick galvanized steel
- Can be used to mount low voltage devices without a box*
- Design allows for installation of steel low voltage partition for power/data applications (206RAC only)
- One or two devices mount directly to RETRO-RING® (206RAC only)

RETRO-RING® FOR POWER/DATA DEVICE(S), 4" SQUARE BOX MOUNTING

CAT. NO.	DESCRIPTION	STD. PKG.	I2of5
205RAC	RETRO-RING for Life Safety Appliance Support	20	50050169002051
206RAC	RETRO-RING for One or Two Device Applications	20	50050169002068
706RAC	Box Partition for RETRO-RING & 1-1/2" Deep 4" Sq. Bx.	25	50050169007063
707RAC	Box Partition for RETRO-RING & 2-1/8" Deep 4" Sq. Bx.	25	50050169007070
911-19	RETRO-RING for Life Safety Appliance Support, Red	20	50050169504357

* can be used without a box when in compliance with local building codes.



THE INSIDER[®] CONNECTOR



Unique Design

THE INSIDER[®] allows the installer to run fire alarm cable through the knockout to the desired length before snapping the connector into the knockout. THE INSIDER[®] is a perfect grommet to protect fire alarm cable entering any 1/2" box knockout.

- **Snap-in locking tab design for 1/2" Knockouts**
- **One piece nonmetallic construction**
- **Easy removal**
- **THE INSIDER[®] can be used in old or new work applications**

Also For Power...

Use THE INSIDER[®] in dry locations to connect one or two runs of Nonmetallic Sheathed Cable (NMSC) to a box. THE INSIDER[®] and NMSC can be used with Steel Boxes, Panel Boxes or Plastic Boxes with knockouts.

For use with Nonmetallic Sheathed Cable

SINGLE	
14-2 w/grnd.	14-3 w/grnd.
12-2 w/grnd.	12-3 w/grnd.
10-2 w/grnd.	10-3 w/grnd.

TWO CABLE COMBINATIONS	
(2) 14-2's w/grnd.	
(1) 14-2 w/grnd. & (1) 12-2 w/grnd.	
(1) 14-2 w/grnd. & (1) 10-2 w/grnd.	

SPECIFICATIONS

Cat. No.: 4714

Trade Size: 1/2"

Color: Black

Material: Thermoplastic

Unit Carton Dimensions: 6-1/4" x 4-1/2" x 4-1/4"

Ship Carton Dimensions: 21-3/8" x 9-3/4" x 7-1/2"

I Two of Five Bar Code Unit Carton.: 30050169047140








I Two of Five Bar Code Ship Carton.: 50050169047144

Unit Carton Qty.: 100







Ship Carton Qty.: 100

Wt. Per 100 Pcs.: 0.861

Large Capacity Steel Wall Boxes

Cat. No.	Description	Unpainted Base	Cu. In.	Knockouts		Std Pkg.
				Sides Cond.	Bottom Cond.	
 911-1	3-3/4" Sq., 3-1/2" Deep Box, Welded w/Conduit KO's, Red*	255	45.0	(10) 1/2"- 3/4" Concentric	(4) 1/2"- 3/4" Concentric, (1) 1/2"	10
 911-2	3-3/4" Sq., 3-1/2" Deep Box, w/Conduit KO's, Red* <i>*Accepts Standard 4" Sq. Covers</i>	256	45.0	(12) 1/2"-3/4" Concentric	(4) 1/2"-3/4" Concentric, (1) 1/2"	25
 911-15	4-11/16" Sq., 3-1/4" Deep Box, Welded w/Conduit KO's, Red	260	66.7	(3) 1/2"- 3/4" TKO (2) 1" - 1-1/4" TKO (2) 1" - 2" Conc. KO	(2) 3/4"- 1" TKO (2) 1/2" TKO	10
 260H	4-11/16" Sq., 3-1/4" Deep Box, Welded w/Conduit KO's, H Bracket, UBS		66.7	(3) 1/2"- 3/4" TKO (2) 1" - 1-1/4" TKO (2) 1" - 2" Conc. KO	(2) 3/4"- 1" TKO (2) 1/2" TKO	10
 911-16	4-11/16" Sq., x 4" Sq. x 5/8" Raised Adapter, Red - For Life Safety Appliances	855	8.3	—	—	25
 911-17	4-11/16" Sq., x 4" Sq. x 1-1/4" Raised Adapter, Red - For Life Safety Appliances	859	16.0	—	—	12
 911-19	4" Sq. RETRO-RING® Box Mount Adapter, Red	205RAC	—	—	—	20

Steel Wall Boxes, Extension Rings & Covers

Cat. No.	Description	Unpainted Base	Cu. In.	Knockouts		Std Pkg.
				Sides Cond.	Bottom Cond.	
 911-3	4" Sq., 2-1/8" Deep Box, Welded w/Conduit KO's, Red	232	30.3	(8) 1/2" & (4) TKO	(3) 1/2" & (2) TKO	25
 911-4	4" Sq., 2-1/8" Deep Box, Welded w/Conduit KO's &, Red	237	30.3	(6) 1/2" & (3) TKO	(3) 1/2" & (2) TKO	25
 911-9	4" Sq., 1-1/2" Deep Box, Welded w/Conduit KO's, Red	189	21.0	(8) 1/2" & (4) TKO	(2) 1/2" & (2) TKO	50
 911-6	4" Sq., 1-1/2" Deep, Drawn Extension Ring w/Conduit KO's, Red	203	22.5	(8) 1/2" & (4) 3/4"	—	50
 911-8	4" Sq., Flat Blank Cover, Red	752	—	—	—	50
 911-12	4-11/16" Sq., 2-1/8" Deep Box, Welded w/Conduit KO's, Red	257	42.0	(12) TKO	(1) 1/2" & (3) TKO	25
 911-11	4-11/16" Sq., Flat Blank Cover, Red	832	—	—	—	50

RACO®
RETRO-RING®,
Red Boxes,
Extension Rings
and Covers



RACO®
THE INSIDER®



3902 West Sample St., South Bend, IN 46619

TEL: 574-234-7151

FAX: 574-234-0625

www.hubbell.com/raco/en