

ILLUMINATE THE MOMENTS

PROGRESS LIGHTING™


Featuring Durrell

Lighting helps tell a story, whether it's setting the mood or enjoying a special moment. These occasions are meaningful, expressive, and shared with those we care about most. Let Progress be your guide in illuminating these spaces into special places.

Be Inspired

@ProgressLtg
@ProgressLtg
@ProgressLighting
@ProgressLtg
Progress Lighting
Progress-Lighting




See
Yourself
Here.





Share the moment with those that matter *most.*

At Progress, we care about the time you spend with those who light up your life. This catalog is dedicated to those special moments of shared and meaningful experiences.

Table of Contents

Pictoral Index 6

Collections 45



Pendants 269



Ceiling Fans 321



Light up your life by finding the perfect fixtures that express your personal style, inside and out.

Close-To-Ceiling 409



Outdoor & Landscape 615



Sconces 457



Bath Collections 481



Recessed Downlighting 767



Surface Mount Downlighting 796

Directionals & Track 802



Undercabinet 814



Steplights 820



Egress 822



Lamps 824

Reference 825

Index 832

Collections

ALEXA
Brushed Nickel p.216



ALEXA
Antique Bronze p.217



AMERICANA
Multiple Finishes p.262



ANJOUX
Antique Bronze p.86



ANJOUX
Silver Ridge p.84



APPLAUSE
Brushed Nickel p.235



APPLAUSE
Antique Bronze p.235



APOGEE LED
Brushed Nickel p.266



APOGEE LED
Antique Bronze p.267



ARCHIE
Polished Chrome p.234



ARCHIE
Venetian Bronze p.234



ARDEN
Brushed Nickel p.226



ARDEN
Antique Bronze p.227



AUSTELLE
Antique Bronze p.137



AUSTELLE
Galvanized p.136



BARNES MILL
Antique Bronze p.130



BEDFORD
Brushed Nickel p.257



BONN
Matte Black p.196



BONN
Galvanized p.197



BOWMAN
Matte Black p.114



BOWMAN
Cottage White p.116



BRANDYWINE
Antique Bronze p.64



BRANDYWINE
Silver Ridge p.62



BRAVO
Brushed Nickel p.218



BRAVO
Antique Bronze p.219



BRIARWOOD
Antique Bronze p.140



BRIARWOOD
Graphite p.138



CALHOUN
Brushed Nickel p.164



CALHOUN
Antique Bronze p.162



CARESS
Polished Nickel p.76



CARISA
Brushed Nickel p.200



CARISA
Vintage Gold p.202



CASCADIA
Chrome p.224




CASCADIA
Antique Bronze p.225



CHADWICK
Brushed Nickel p.98



CHADWICK
Matte Black p.100



CHERISH
Brushed Nickel p.187



CHERISH
Antique Bronze p.186



CIRRINE
Antique Bronze p.192



CIRRO
Brushed Nickel p.198



CIRRO
Graphite p.199



CLASSIC
Multiple Finishes p.258



CLIFTON HEIGHTS
Brushed Nickel p.228



CLIFTON HEIGHTS
Antique Bronze p.229



CONESTEE
Galvanized p.145



CONESTEE
Graphite p.142



DOMAIN
Black p.206



DRAPER
Polished Nickel p.74



DRUM SHADE
Brushed Nickel p.260



DRUM SHADE
Antique Bronze p.260



Collections

DRUM SHADE
Black p.260



DURRELL
Brushed Nickel p.166



DURRELL
Matte Black p.168



ECLIPSE
Brushed Nickel p.265




ECLIPSE
Antique Bronze p.265



EQUINOX
Polished Nickel p.88



EQUINOX
Antique Bronze p.90



EQUINOX
Satin Brass p.92



EQUINOX
Matte Black p.92



EQUINOX
Burnished Silver p.93



FIVE-LIGHT
Multiple Finishes p.263



FLEURETTE
Cottage White p.132



FOSTER
Gilded Iron p.176



GATHER
Brushed Nickel p.254



GATHER
Antique Bronze p.255



GATHER
Brushed Nickel p.256



GATHER
Antique Bronze p.256



GREYSON
Black p.120



GULLIVER
Galvanized p.146



GULLIVER
Graphite p.148



GULLIVER
Galvanized p.150



GULLIVER
Graphite p.152




HANSFORD
Antique Bronze p.184



HANSFORD
Polished Nickel p.185



HAVEN
Brushed Nickel p.264



HEART
Brushed Nickel p.252




HEART
Antique Bronze p.253



HEMSWORTH
Textured Black p.122



HEMSWORTH
Galvanized p.124



INSPIRE
Brushed Nickel p.236



INSPIRE
Antique Bronze p.237



INVITE
Brushed Nickel p.242



INVITE
Antique Bronze p.243



JOY
Brushed Nickel p.244



JOY
Antique Bronze p.245



JUDSON
Antique Bronze p.178



JUDSON
Polished Nickel p.180



KEMPSEY
Brushed Nickel p.190



KEMPSEY
Antique Bronze p.188



KENE
Brushed Nickel p.96



KENE
Graphite p.94



LAIRD
Brushed Nickel p.248



LAIRD
Antique Bronze p.249



LANDREE
Black p.58



LANDREE
Silver Ridge p.56



LASSITER
Brushed Nickel p.104



LASSITER
Matte Black p.102



LEAP
Brushed Nickel p.210



LEAP
Antique Bronze p.211



LITCHFIELD
Polished Chrome p.160



Collections

MADISON
Brushed Nickel p.250



MADISON
Antique Bronze p.251



MAST
Brushed Nickel p.127



MAST
Antique Bronze p.126



MINGLE
Brushed Nickel p.195



MINGLE
Antique Bronze p.194



NEALY
Brushed Nickel p.66



ORBITZ
Brushed Nickel p.215



ORBITZ
Antique Bronze p.215



PARKHURST
Brushed Nickel p.290



PARKHURST
Matte Black p.290



PARKHURST
Brushed Bronze p.290



PIEDMONT
Antique Bronze p.108



PIEDMONT
Burnished Silver p.109



RAINEY
Brushed Nickel p.70



RAINEY
Graphite p.72



REPLAY
Polished Nickel p.212



REPLAY
Black p.213



REPLAY
Brushed Nickel p.214



RILEY
Brushed Nickel p.246



RILEY
Matte Black p.247



SALUDA
Brushed Nickel p.170



SALUDA
Antique Bronze p.172



SENECA
Black p.54



SENECA
Polished Nickel p.52



STATUS
Polished Chrome p.68



SWING
Antique Bronze p.182



TALLY
Brushed Nickel p.261



TALLY
Antique Bronze p.261



TILLEY
Brushed Nickel p.158



TILLEY
Antique Bronze p.156



TINSLEY
Brushed Bronze p.80



TINSELY
Polished Chrome p.82



TOBIN
Brushed Nickel p.208



TOBIN
Matte Black p.209



TOPSAIL
Chrome p.220



TOPSAIL
Antique Bronze p.221



TORINO
Brushed Nickel p.230



TORINO
Forged Bronze p.232



TRESTLE
Gilded Iron p.154



TRINITY
Brushed Nickel p.238



TRINITY
Antique Bronze p.240



WHISP
Graphite p.174



WINSLETT
Brushed Nickel p.112



WINSLETT
Matte Black p.110



WISTEN
Brushed Nickel p.222



WISTEN
Antique Bronze p.223



ZAG
Brushed Nickel p.205



ZAG
Vintage Gold p.204



Pendants

ACADEMY
Polished Chrome p.296



ALABASTER GLASS
Brushed Nickel p.316



ALEXA
Brushed Nickel p.216



ALEXA
Antique Bronze p.217



ANJOUX
Antique Bronze p.87



ANJOUX
Silver Ridge p.85



APPLAUSE
Brushed Nickel p.235



APPLAUSE
Antique Bronze p.235



ARCHIE
Polished Chrome p.234



ARCHIE
Venetian Bronze p.234



ARCHIE
Antique Nickel p.234



ARCHIVES
Antique Bronze p.293



ARCHIVES
Antique Bronze p.293



ARCHIVES
Antique Nickel p.293



ARDEN
Brushed Nickel p.226



ARDEN
Antique Bronze p.227



ATWELL
Brushed Nickel p.305



ATWELL
Matte Black p.305



ATWELL
Brushed Bronze p.305



AUSTELLE
Antique Bronze p.137



AUSTELLE
Galvanized p.136



AVALON
Brushed Nickel p.315



AVANT
Brushed Nickel p.310



AVANT
Antique Bronze p.310



BALLINGER
Matte Black p.295



BARNES MILL
Antique Bronze p.130



BASTILLE
White p.289



BASTILLE
Aged Brass p.289



BASTILLE
Coastal Blue p.289



BAY COURT
Brushed Nickel p.288



BAY COURT
Antique Bronze p.288



BEDFORD
Brushed Nickel p.257



BONN
Matte Black p.196



BONN
Galvanized p.197



BOWMAN
Matte Black p.115



BOWMAN
Cottage White p.117



BRANDYWINE
Antique Bronze p.64



BRANDYWINE
Silver Ridge p.62



BRAVO
Brushed Nickel p.218



BRAVO
Antique Bronze p.219



BRIARWOOD
Antique Bronze p.140



BRIARWOOD
Graphite p.138



BROOKSIDE
Brushed Nickel p.294



CAISSON
Graphite p.287



CAISSON
Brushed Nickel p.287



CALHOUN
Brushed Nickel p.164



CALHOUN
Antique Bronze p.162



CARESS
Polished Nickel p.79



CARESS
Polished Nickel p.77



CASCADIA
Polished Chrome p.224



CASCADIA
Antique Bronze p.225



CAYCE
Polished Chrome p.306



CAYCE
Vintage Gold p.306



CHADWICK
Brushed Nickel p.99



CHADWICK
Matte Black p.101



CHAMBERS
Galvanized p.295



CHAMBERS
Matte Black p.295



CIRRINE
Antique Bronze p.192



CIRRO
Brushed Nickel p.198



CIRRO
Graphite p.199



Pendants

CLARION
Brushed Nickel p.308



CLARION
Satin Brass p.308



CLARION
Matte Black p.308



CLARION
Polished Nickel p.308



CLASSIC DOME
Brushed Nickel p.314



CLASSIC DOME
Polished Chrome p.314



CLASSIC DOME
Antique Bronze p.314



CLASSIC DOME
Graphite p.314



CLEAR GLASS
Nickel Polished p.313



CLIFTON HEIGHTS
Brushed Nickel p.228



CLIFTON HEIGHTS
Antique Bronze p.229



CONCOURSE LED
Brushed Nickel p.280



CONESTEE
Galvanized p.145



CONESTEE
Graphite p.142



CUDDLE
Brushed Nickel p.312



DOME LED
Satin Aluminium p.302



DOME LED
Antique Bronze p.302



DOME LED
White p.303



DOUBLE GLASS
Polished Chrome p.312



DOUBLE GLASS
Graphite p.312



DRAPER
Polished Nickel p.75



DURRELL
Brushed Nickel p.166



DURRELL
Matte Black p.168



ETCHED/CLEAR GLASS
Brushed Nickel p.314



ECLIPSE
Brushed Nickel p.265



ECLIPSE
Antique Bronze p.265



EQUINOX
Polished Nickel p.89



EQUINOX
Satin Brass p.92



EQUINOX
Antique Bronze p.91



EQUINOX
Matte Black p.92



EQUINOX
Burnished Silver p.93



FOSTER
Gilded Iron p.176



FRESNEL LENS
Brushed Nickel p.284



FRESNEL LENS
Polished Chrome p.284



FRESNEL LENS
Oil Rubbed Bronze p.284



GAUGE
Graphite p.294



GATHER
Brushed Nickel p.254



GATHER
Antique Bronze p.255



GLOBE LED
Brushed Nickel p.304



GLOBE LED
Polished Chrome p.304



GLOBE LED
Brushed Nickel p.304



GLOBE LED
Matte Black p.304



GULLIVER
Galvanized p.146



GULLIVER
Graphite p.148



HAVEN
Brushed Nickel p.264



HEART
Brushed Nickel p.252



HEART
Antique Bronze p.252



HEMSWORTH
Textured Black p.122



HEMSWORTH
Galvanized p.122



INSPIRE
Brushed Nickel p.236



INSPIRE
Antique Bronze p.237



INVITE
Brushed Nickel p.242



INVITE
Antique Bronze p.243



JOY
Brushed Nickel p.244



JOY
Antique Bronze p.245



JUDSON
Antique Bronze p.178



JUDSON
Polished Nickel p.180



KEMPSEY
Brushed Nickel p.190



KEMPSEY
Antique Bronze p.188



KENE
Brushed Nickel p.97



Pendants

KENE
Graphite p.95



LAIRD
Brushed Nickel p.248



LAIRD
Antique Bronze p.249



LANDREE
Black p.59



LANDREE
Silver Ridge p.57



LASSITER
Matte Black p.103



LASSITER
Brushed Nickel p.105



LATROBE
Brushed Nickel p.297



LATROBE
Matte Black p.297



LEAP
Brushed Nickel p.210



LEAP
Antique Bronze p.211



LITCHFIELD
Polished Chrome p.161



LOFTIN
Matte Black p.282



LOFTIN
Brushed Nickel p.282



MADISON
Brushed Nickel p.250



MADISON
Antique Bronze p.251



MARKOR
Summer Linen p.272



MARKOR
Black Parchment Paper p.272



MARKOR
Beige Silken Fabric p.272



MARKOR
Khaki p.272



MARKOR
Harvest Linen p.272



MAST
Brushed Nickel p.127



MAST
Antique Bronze p.127



MEDAL
Graphite p.282



MEDAL
Brushed Nickel p.282



MEDAL
Coastal Blue p.282



MINGLE
Brushed Nickel p.195



MINGLE
Antique Bronze p.195



MODERN GLASS
Brushed Nickel p.311



NEALY
Brushed Nickel p.67



NEAT LED
Brushed Nickel p.310



NEAT LED
Brushed Nickel p.310



OPAL GLOBES
White p.317



ORBITZ
Brushed Nickel p.215



ORBITZ
Antique Bronze p.215



PARKHURST
Brushed Nickel p.290



PARKHURST
Matte Black p.290



PARKHURST
Brushed Bronze p.290



PASSAGE
Matte Black p.286



PASSAGE
Brushed Nickel p.286



PENDANT LED
Brushed Nickel p.313



PENN
Polished Nickel p.292



PENN
Natural Brass p.292



PIEDMONT
Antique Bronze p.108



PIEDMONT
Burnished Silver p.109



PLANCK LED
Matte Black p.280



PLANCK LED
Brushed Nickel p.280



PLANCK LED
Matte White p.280

PRISMATIC
Brushed Nickel p.307



PRISMATIC GLASS
Brushed Nickel p.316



PURE LED
Brushed Nickel p.313



RANGE
Brushed Nickel p.286



RANGE
Antique Bronze p.286



RANGE
Polished Nickel p.286



RANGE
Graphite p.286



REPLAY
Brushed Nickel p.214



REPLAY
Black p.213



REPLAY
Polished Nickel p.212



RILEY
Brushed Nickel p.246



RILEY
Matte Black p.247



Pendants

SALUDA
Brushed Nickel p.171



SALUDA
Antique Bronze p.173



SATIN OPAL GLASS
Brushed Nickel p.316



SCHOOLHOUSE
Brushed Nickel p.296



SEEDED GLASS
Brushed Nickel p.307



SEEDED GLASS
Antique Bronze p.307



SENECA
Black p.55



SENECA
Polished Nickel p.53



SIMPLE LED
Brushed Nickel p.311



SIMPLE LED
Brushed Nickel p.311



STATUS
Polished Chrome p.69



SWING
Antique Bronze p.183



TALLEY
Brushed Nickel p.261



TALLEY
Antique Bronze p.261



TILLEY
Brushed Nickel p.159



TILLEY
Antique Bronze p.157



TINSLEY
Polished Chrome p.83



TINSLEY
Brushed Bronze p.81



TOBIN
Brushed Nickel p.208



TOBIN
Matte Black p.209



TOPSAIL
Polished Chrome p.220



TOPSAIL
Antique Bronze p.221



TORINO
Brushed Nickel p.231



TORINO
Foged Bronze p.233



TRE
White p.300



TRE
Graphite p.300



TRESTLE
Gilded Iron p.155



TRINITY
Brushed Nickel p.238



TRINITY
Antique Bronze p.240



WAREHOUSE
Brushed Nickel p.315



WAREHOUSE
White p.315



WAREHOUSE
Matte Black p.315



WAREHOUSE
Dark Green p.315



WAREHOUSE
Venetian Bronze p.315



WINSLETT
Brushed Nickel p.113



WINSLETT
Matte Black p.111



WISTEN
Brushed Nickel p.222



WISTEN
Antique Bronze p.223



Ceiling Fans

ALBIN
Satin White p.396



ALBIN
Black p.396



ALBIN
Architectural Bronze p.396



ALFRESCO
Blistered Iron p.385



ALFRESCO
Architectural Bronze p.384



ARLO
Brushed Nickel p.342




ARLO
Black p.343




ARLO
Architectural Bronze p.343



BEDWIN
Antique Nickel p.357




BEDWIN
Galvanized p.357



Ceiling Fans

BEDWIN
Graphite p.357



BILLOWS
Brushed Nickel p.368



BILLOWS
Antique Bronze p.368



BILLOWS
Forged Black p.368



BIXBY
White p.345



BIXBY
Black p.344



BRADEN
Brushed Nickel p.381



BRADEN
Polished Chrome p.381



BRADEN
Architectural Bronze p.381



CALEB
Brushed Nickel p.337



CALEB
Antique Bronze p.336



CHAPIN
Antique Nickel p.356



CHAPIN
Oil Rubbed Bronze p.356



CHAPIN
Graphite p.356



CLIFTON HEIGHTS
Brushed Nickel p.375



CLIFTON HEIGHTS
Antique Bronze p.375



DECORATIVE PATIO FAN
Antique Bronze p.399



DRIFT
Brushed Nickel p.379



DRIFT
White p.379



DRIFT
Architectural Bronze p.379



EDGEFIELD
Brushed Nickel p.375



EDGEFIELD
Antique Bronze p.375



EDGEFIELD
White p.375



EDISTO
Forged Black p.388



EDISTO
Antique Nickel p.389



EDISTO
Architectural Bronze p.389



ELLWOOD
Brushed Nickel p.334



ELLWOOD
Antique Bronze p.335



FARRIS
Brushed Nickel p.327



FARRIS
Oil Rubbed Bronze p.326



FARRIS
Graphite p.327



FRESNO
Brushed Nickel p.365



FRESNO
Antique Bronze p.365



FRESNO
White p.365



GAZE
Brushed Nickel p.346



GAZE
Polished Chrome p.347



GAZE
Antique Bronze p.347



GAZE
Black p.347



GLANDON
Gilded Iron p.354



GLANDON
Antique Nickel p.354



GRACEFUL
Brushed Nickel p.361



GRACEFUL
Polished Chrome p.361



GRACEFUL
Antique Bronze p.361



GREER
Gilded Iron p.355



GREER
Antique Nickel p.355



GULLIVER
Galvanized p.328



GULLIVER
Graphite p.329



GUST
Brushed Nickel p.363



GUST
Antique Bronze p.363



GUST
Graphite p.363



Ceiling Fans

HARRANVALE
Antique Bronze p.360



HARRANVALE
White p.360



HARRANVALE
Graphite p.360



HOLLAND
Brushed Nickel p.350



HOLLAND
Black p.350



HOLLAND
Oil Rubbed Bronze p.350



HUFF
Brushed Nickel p.338



HUFF
Satin White p.339



HUFF
Black p.339



KUDOS
Brushed Nickel p.364



KUDOS
Polished Chrome p.364



KUDOS
Antique Bronze p.364



LAKEHURST
Antique Bronze p.397



LAKEHURST
White p.397



LAKEHURST
Forged Black p.397



LINDALE
Satin White p.380



LINDALE
Antique Nickel p.380



LINDALE
Architectural Bronze p.380



LORING
Matte Black p.330



LORING
Galvanized p.331



MONTAGUE
Antique Bronze p.395



MONTAGUE
White p.395



MONTAGUE
Forged Black p.395



OLSON
Brushed Nickel p.362



OLSON
Graphite p.362



ORIOLE
Brushed Nickel p.351



ORIOLE
Black p.351



ORIOLE
Architectural Bronze p.351



52" PERFORMANCE
Brushed Nickel p.374



52" PERFORMANCE
Antique Bronze p.374



52" PERFORMANCE
White p.374



ROYER
Antique Nickel p.353



ROYER
Forged Black p.353



RUDDER
Satin White p.386



RUDDER
Black p.387



RUDDER
Architectural Bronze p.387



SANFORD
Brushed Nickel p.333



SANFORD
Architectural Bronze p.332



SHAFFER
Satin White p.358



SHAFFER
Forged Black p.358



SHAFFER
Architectural Bronze p.358



SIGNATURE
Brushed Nickel p.369



SIGNATURE
Antique Bronze p.369



SIGNATURE
Forged Bronze p.369



SIGNATURE
Forged Black p.369



SIGNATURE
Antique Nickel p.369



SIGNATURE PLUS
Brushed Nickel p.373



SIGNATURE PLUS
Antique Bronze p.373



SIGNATURE PLUS
White p.373



SIGNATURE PLUS II
Brushed Nickel p.372



Ceiling Fans

SIGNATURE PLUS II
Antique Bronze p.372



SIGNATURE PLUS II
White p.372



SMYRNA
Antique Bronze p.394



SMYRNA
Forged Black p.394



SOAR
Brushed Nickel p.359



SOAR
Antique Bronze p.359



SOAR
White p.359



SPADES
Brushed Nickel p.349



SPADES
Polished Chrome p.348



SPADES
Graphite p.349



SPRINGER
Antique Nickel p.324



SPRINGER
Architectural Bronze p.325



TEASLEY
Architectural Bronze p.352



TEASLEY
Galvanized p.352



TEASLEY
Graphite p.352



TEMPT
Polished Chrome p.366



TEMPT
Antique Bronze p.366



TEMPT
Vintage Brass p.366



TREVINA II 44"
Brushed Nickel p.370



TREVINA II 44"
Satin White p.370



TREVINA II 44"
Black p.370



TREVINA II 52"
Architectural Bronze p.371



TREVINA II 52"
Nickel (Painted) p.371



TREVINA II 52"
Brushed Nickel p.371



TREVINA II 52"
Antique Bronze p.371



TREVINA II 52″
White p.371




VAST
Brushed Nickel p.341



VAST
Antique Bronze p.341



VAST
White p.341



VAST
Black p.340



VERADA
Brushed Nickel p.367



VERADA
Antique Bronze p.367



VOX FAN
Brushed Nickel p.382



VOX FAN
Antique Bronze p.382



VOX FAN
White p.382



WHIRL
Antique Bronze p.391



WHIRL
Forged Black p.391



WHIRL
Antique Nickel p.390



42″ BUILDER FAN
Multiple Finishes p.378



52″ BUILDER FAN
Brushed Nickel p.377



52″ BUILDER FAN
Polished Chrome p.377



52″ BUILDER FAN
Antique Bronze p.377



52″ BUILDER FAN
White p.377




52″ BUILDER FAN
Graphite p.377



42″ HUGGER FAN
Multiple Finishes p.383



52″ HUGGER FAN
Multiple Finishes p.383



52″ PATIO FAN
Multiple Finishes p.398



54″ PATIO FAN
Antique Bronze p.398



Sconces/Wall Brackets

ACE LED
Polished Chrome p.500



ACE LED
Antique Bronze p.501



ADLEY
Brushed Nickel p.518



ADLEY
Satin Brass p.519



ADLEY
Black p.519



ADLEY
Polished Nickel p.519



ADORN
Brushed Nickel p.600



ADORN
Polished Chrome p.600



ADORN
Antique Bronze p.600



ALABASTER GLASS
Brushed Nickel p.608



ALABASTER STONE GLASS SCONCE LED
Brushed Nickel p.474



ALABASTER STONE GLASS SCONCE LED
Black p.474



ALEXA
Brushed Nickel p.586



ALEXA
Antique Bronze p.586



ANJOUX
Antique Bronze p.512



ANJOUX
Silver Ridge p.510



ANSON LED
Arch. Bronze p.479, 742



APPEAL
Brushed Nickel p.576



APPEAL
Polished Chrome p.576



APPEAL
Antique Bronze p.576



APPLAUSE
Brushed Nickel p.582



APPLAUSE
Antique Bronze p.582



APOGEE LED
Brushed Nickel p.477



APOGEE LED
Antique Bronze p.477



ARCHIE
Polished Chrome p.563



ARCHIE
Venetian Bronze p.563



ARCHIE
Antique Nickel p.562



ARCHIE
Vintage Brass` p.563



ARCHIVES
Antique Bronze p.465



ARCHIVES
Antique Nickel p.465



ARCHIVES
Antique Bronze p.465



ARCHIVES
Antique Nickel p.465



ARDEN
Brushed Nickel p.583



ARDEN
Antique Bronze p.583



AVALON
Brushed Nickel p.590



BARNES MILL
Antique Bronze p.467



BEAM LED
Polished Chrome p.476, 491



BEAM LED
Arch. Bronze p.476, 490



BEAM LED
Brushed Nickel p.476, 491



BLANCO LED
Brushed Nickel p.476



BLANCO LED
Satin Brass p.476



BLANCO LED
Matte Black p.476



BLANCO LED
Faux White Marble p.476



BOWMAN
Black p.530



BOWMAN
Cottage White p.531



BRAMLETT
Brushed Nickel p.550



BRAMLETT
Polished Chrome p.551



BRAVO
Brushed Nickel p.587



BRAVO
Antique Bronze p.587



BRIARWOOD
Graphite p.466



BRIARWOOD
Antique Bronze p.466



CAISSON
Brushed Nickel p.462



CAISSON
Graphite p.462



CALHOUN
Brushed Nickel p.540



CALHOUN
Antique Bronze p.541



CARESS
Polished Nickel p.460



CARISSA
Brushed Nickel p.580



CARISSA
Vintage Gold p.580



CASCADIA
Polished Chrome p.578



CASCADIA
Antique Bronze p.578



CHADWICK
Brushed Nickel p.463



CHADWICK
Black p.463



CHERISH
Brushed Nickel p.464



CHERISH
Antique Bronze p.464



CIRCUIT
Brushed Nickel p.558



CIRCUIT
Polished Chrome p.558



CIRRINE
Antique Bronze p.465



CLASSIC
Brushed Nickel p.604



CLASSIC
Black p.605



CLEAR FLUTED GLASS
Brushed Nickel p.610



CLEAR FLUTED GLASS
Polished Chrome p.610



CLEAR FLUTED GLASS
Antique Bronze p.610



Sconces/Wall Brackets

CLIFTON HEIGHTS
Brushed Nickel p.577



CLIFTON HEIGHTS
Antique Bronze p.577



COLLONNADE LED
Brushed Nickel p.488



COLONNADE LED
Polished Chrome p.489



CONCOURSE LED
Brushed Nickel p.487



DART
Graphite p.462



DOMAIN
Black p.526



DRAPER
Polished Nickel p.460



DURRELL
Brushed Nickel p.466



DURRELL
Matte Black p.466



ECLIPSE
Brushed Nickel p.472



ECLIPSE
Antique Bronze p.472



ECLIPSE LED
Brushed Nickel p.477



ECLIPSE LED
Black p.477



ETCHED FLUTED GLASS
Brushed Nickel p.611



ETCHED FLUTED GLASS
Polished Chrome p.611



ETCHED FLUTED GLASS
Antique Bronze p.611



ETCHED GLASS
Antique Bronze p.472

FAWCETT
Brushed Nickel p.536



FAWCETT
Black p.537



FAYETTE
Antique Nickel p.565



FAYETTE
Vintage Brass p.564



FLEET
Brushed Nickel p.575



FLEET
Polished Chrome p.575



FRAME LED
Brushed Nickel p.474



GATHER
Brushed Nickel p.606



GATHER
Polished Chrome p.606



GATHER
Antique Bronze p.606



GAUGE
Graphite p.555



GREYSON
Black p.466



GULLIVER
Graphite p.467



GULLIVER
Galvanized p.467



HARTWICK
Brushed Nickel p.464



HARTWICK
Satin Brass p.464



HARTWICK
Black p.464



HANSFORD
Antique Bronze p.568



HANSFORD
Polished Nickel p.569



HEART
Brushed Nickel p.603



HEART
Polished Chrome p.603



HEART
Antique Bronze p.603



HEMSWORTH
Black p.467



HEMSWORTH
Galvanized p.467



HINTON
Brushed Nickel p.470



HINTON
Black p.470



HINTON
Polished Nickel p.470



HINTON
Vintage Brass p.470



INDEX
Brushed Nickel p.517



INDEX
Black p.517



INSPIRE
Brushed Nickel p.595



INSPIRE
Polished Chrome p.595



INSPIRE
Antique Bronze p.595



INSPIRE LED
Summer Linen p.477



INSPIRE LED
Off White Linen p.477



INVITE
Brushed Nickel p.589



INVITE
Antique Bronze p.589



JACK
Antique Bronze p.469



JACK
Black p.469



JOY
Brushed Nickel p.601



JOY
Antique Bronze p.601



JUDSON
Polished Black p.570



JUDSON
Antique Bronze p.571



KEMPSEY
Brushed Nickel p.468



KEMPSEY
Antique Bronze p.468



KENE
Graphite p.463



KENE
Brushed Nickel p.463



LAIRD
Brushed Nickel p.602



LAIRD
Antique Bronze p.602



LASSITER
Brushed Nickel p.463



LASSITER
Black p.463



LEAP
Brushed Nickel p.584



LEAP
Antique Bronze p.584



ETCHED GLASS SCONCE LED
Brushed Nickel p.479



Sconces/Wall Brackets

ETCHED GLASS SCONCE LED
Black p.479



LINEN GLASS
Brushed Nickel p.473



LINEN GLASS
Black p.473



LITCHFIELD
Polished Chrome p.468



LUCKY
Brushed Nickel p.524



LUCKY
Polished Chrome p.525



LYNZIE
Polished Chrome p.559



MAST
Brushed Nickel p.466



MAST
Antique Bronze p.466



MADISON
Brushed Nickel p.593



MADISON
Polished Chrome p.593



MADISON
Antique Bronze p.593



MILNER
Brushed Nickel p.468



MILNER
Black p.468



MOORE
Satin Brass p.514



MOORE
Polished Nickel p.515



MOORE
Brushed Nickel p.515



MOORE
Black p.515



NEALY
Brushed Nickel p.460



NISSÉ
Polished Nickel p.509



OPAL GLASS
Brushed Nickel p.472



OPAL GLASS
Antique Bronze p.472



ORBITZ
Brushed Nickel p.574



ORBITZ
Antique Bronze p.574



PARALLEL LED
Brushed Nickel p.476



PARALLEL LED
Polished Chrome p.476



PARALLEL LED
Architectural Bronze p.476



PARALLEL LED
Satin Brass p.476



PEEK-A-BOO
Antique Bronze p.469



RAINEY
Brushed Nickel p.461



RAINEY
Graphite p.461



REPLAY
Brushed Nickel p.596



REPLAY
Antique Bronze p.598



REPLAY
Black p.596



REPLAY
Polished Nickel p.598



RILEY
Brushed Nickel p.462



RILEY
Matte Black p.462



RUSHTON
Brushed Nickel p.553



RUSHTON
Graphite p.552



SALUDA
Brushed Nickel p.567



SALUDA
Antique Bronze p.566



SCONCES LED
Brushed Nickel p.478



SCONCES LED
Brushed Nickel p.478



SCONCES LED
Brushed Nickel p.478



SCONCES LED
Brushed Nickel p.478



SCONCES LED
Brushed Nickel p.478



SCONCES LED
Brushed Nickel p.478



SCONCES LED
Architectural Bronze p.478



SHADED SCONCE LED
Brushed Nickel p.475



SHADED SCONCE LED
Black p.475



SHADED SCONCE LED
Brushed Bronze p.475



SIGNAL
Polished Chrome p.556



SIGNAL
Graphite p.557



STATUS
Polished Chrome p.460



STONE GLASS SCONCE LED
Brushed Nickel p.474



STONE GLASS SCONCE LED
Black p.474



SWING
Antique Bronze p.465



TILLEY
Brushed Nickel p.542



TILLEY
Antique Bronze p.542



TINSLEY
Polished Chrome p.460



TINSLEY
Brushed Bronze p.460



TOBIN
Brushed Nickel p.469



TOBIN
Matte Black p.469



TOPSAIL
Polished Chrome p.579



TOPSAIL
Antique Bronze p.579



TORINO
Brushed Nickel p.472



TORINO
Forged Bronze p.472



TORINO
Brushed Nickel p.472



TORINO
Forged Bronze p.472



TRI-BAND LOUVER
White p.473



TRI-BAND LOUVER
Black p.473



TRINITY
Brushed Nickel p.592



Sconces/Wall Brackets

TRINITY
Polished Chrome p.592



TRINITY
Antique Bronze p.592



TRUSS LED
Brushed Nickel p.477



TRUSS LED
Architectural Bronze p.477



VICTORIAN
Brushed Nickel p.591



VICTORIAN
Polished Chrome p.591



VICTORIAN
Venetian Bronze p.591



WHITE GLASS
White p.473



WHITE GLASS
White p.473



WINSLETT
Brushed Nickel p.532



WINSLETT
Black p.533



WISTEN
Brushed Nickel p.588



WISTEN
Antique Bronze p.588



Bath Collections

ACE LED
Polished Chrome p.500



ACE LED
Antique Bronze p.501



ADLEY
Brushed Nickel p.518



ADLEY
Satin Brass p.519



ADLEY
Matte Black p.519



ADLEY
Polished Nickel p.519



ADORN
Brushed Nickel p.600



ADORN
Polished Chrome p.600



ADORN
Antique Bronze p.600



ALABASTER GLASS
Brushed Nickel p.608



ALEXA
Brushed Nickel p.586



ALEXA
Antique Bronze p.586



Bath Collections

ANJOUX
Antique Bronze p.512



ANJOUX
Silver Ridge p.510



APPEAL
Brushed Nickel p.576



APPEAL
Polished Chrome p.576



APPEAL
Antique Bronze p.576



APPLAUSE
Brushed Nickel p.582



APPLAUSE
Antique Bronzel p.582



ARCHIE
Polished Chrome p.563



ARCHIE
Venetian Bronze p.563



ARCHIE
Antique Nickel p.562



ARCHIE
Vintage Brass p.563



ARCHIVES
Antique Bronze p.561



ARCHIVES
Antique Nickel p.561



ARCH LED
Brushed Nickel p.506



ARDEN
Brushed Nickel p.583



ARDEN
Antique Bronze p.583



AVALON
Brushed Nickel p.590



BATH LED
Brushed Nickel p.507



BARNES MILL
Antique Bronze p.543



BEAM LED
Brushed Nickel p.491



BEAM LED
Polished Chrome p.491



BEAM LED
Architectural Bronze p.490



BEDFORD
Brushed Nickel p.609



BLANCO LED
Brushed Nickel p.499



BLANCO LED
Satin Brass p.499



BLANCO LED
Matte Black p.499



BLANCO LED
Faux White Marble p.498

BOWMAN
Black p.530



BOWMAN
Cottage White p.531



BRAMLETT
Brushed Nickel p.550



BRAMLETT
Polished Chrome p.551



BRAVO
Brushed Nickel p.587



BRAVO
Antique Bronze p.587



BRIARWOOD
Graphite p.546



BRIARWOOD
Antique Bronze p.547



CALHOUN
Brushed Nickel p.540



Bath Collections

CALHOUN
Antique Bronze p.541



CAPELLI LED
Polished Chrome p.485



CARESS
Polished Nickel p.513



CARISSA
Brushed Nickel p.580



CARISSA
Vintage Gold p.580



CASCADIA
Polished Chrome p.578



CASCADIA
Antique Bronze p.578



CHANNEL GLASS
White p.609



CIRCUIT
Brushed Nickel p.558



CIRCUIT
Polished Chrome p.558



CLASSIC
Brushed Nickel p.604



CLASSIC
Matte Black p.605



CLEAR FLUTED GLASS
Brushed Nickel p.610



CLEAR FLUTED GLASS
Polished Chrome p.610



CLEAR FLUTED GLASS
Antique Bronze p.610



CLIFTON HEIGHTS
Brushed Nickel p.577



CLIFTON HEIGHTS
Antique Bronze p.577



CLOUD LED
Opal White p.507

COLONNADE LED
Brushed Nickel p.488



COLONNADE LED
Polished Chrome p.489



CONCOURSE LED
Brushed Nickel p.487



DART
Graphite p.522




DELUXE BROADWAY LIGHTS
Polished Chrome p.612



DOMAIN
Matte Black p.526



DRAPER
Polished Nickel p.516



DURRELL
Brushed Nickel p.572



DURRELL
Matte Black p.573



DWYER
Stainless Steel p.538



DWYER
Black p.539



ECONOMY BROADWAY LIGHTS
Polished Chrome p.613



ETCHED FLUTED GLASS
Brushed Nickel p.611



ETCHED FLUTED GLASS
Polished Chrome p.611



ETCHED FLUTED GLASS
Antique Bronze p.611



FAWCETT
Brushed Nickel p.536



FAWCETT
Black p.537



FAYETTE
Antique Nickel p.565



FAYETTE
Vintage Brass p.564



FLEET
Brushed Nickel p.575



FLEET
Polished Chrome p.575



FRAME LED
Brushed Nickel p.494



GATHER
Brushed Nickel p.606



GATHER
Polished Chrome p.606



GATHER
Antique Bronze p.606



GAUGE
Graphite p.555



GULLIVER
Galvanized p.544



GULLIVER
Graphite p.545



HANSFORD
Antique Bronze p.568



HANSFORD
Polished Nickel p.569



HEART
Brushed Nickel p.603



HEART
Polished Chrome p.603



HEART
Antique Bronze p.603



INDEX
Brushed Nickel p.517



INDEX
Black p.517



INSPIRE
Brushed Nickel p.595



INSPIRE
Polished Chrome p.595



INSPIRE
Antique Bronze p.595



INVITE
Brushed Nickel p.589



INVITE
Antique Bronze p.589



JOY
Brushed Nickel p.601



JOY
Antique Bronze p.601



JUDSON
Polished Nickel p.570



JUDSON
Antique Bronze p.571



KENE
Brushed Nickel p.520



KENE
Graphite p.521



LAIRD
Brushed Nickel p.602



LAIRD
Antique Bronze p.602



LASSITER
Brushed NIckel p.528



LASSITER
Black p.529



LEAP
Brushed Nickel p.584



LEAP
Antique Bronze p.584



LITCHFIELD
Polished Chrome p.527



LUCKY
Brushed Nickel p.524



Bath Collections

LUCKY
Polished Chrome p.525



LYNZIE
Polished Chrome p.559



MADISON
Brushed Nickel p.593



MADISON
Polished Chrome p.593



MADISON
Antique Bronze p.593



MARQUEE LIGHTS
Brushed Nickel p.612



MARQUEE LIGHTS
Polished Chrome p.612



MARQUEE LIGHTS
Antique Bronze p.612



MAST
Brushed Nickel p.534



MAST
Brushed Nickel p.535



MITER LED
Brushed Nickel p.486



MOORE
Satin Brass p.514



MOORE
Polished Nickel p.515



MOORE
Brushed Nickel p.515



MOORE
Black p.515



NEALY
Brushed Nickel p.508



NISSÉ
Polished Nickel p.509



ORBITZ
Brushed Nickel p.574



ORBITZ
Antique Bronze p.574



PARALLEL LED
Brushed Nickel p.496



PARALLEL LED
Satin Brass p.497



PARALLEL LED
Polished Chrome p.497



PARALLEL LED
Architectural Bronze p.497



PHASE 1.1 LED
Brushed Nickel p.502



PHASE 1.2 LED
Brushed Nickel p.503



PHASE 2.1 LED
Brushed Nickel p.504



PHASE 2.2 LED
Brushed Nickel p.505



PLANCK LED
Brushed Nickel p.492



PONDER LED
Antique Bronze p.484



PONDER LED
Graphite p.484



REPLAY
Brushed Nickel p.596



REPLAY
Antique Bronze p.598



REPLAY
Black p.596



REPLAY
Polished Nickel p.598



RILEY
Brushed Nickel p.599



RILEY
Matte Black p.599



RUSHTON
Brushed Nickel p.553



RUSHTON
Graphite p.552



SALUDA
Brushed Nickel p.567



SALUDA
Antique Bronze p.556



SIGNAL
Polished Chrome p.556



SIGNAL
Graphite p.557



STATUS
Polished Chrome p.523



TILLEY
Brushed Nickel p.542



TILLEY
Antique Bronze p.542



TOBIN
Brushed Nickel p.585



TOBIN
Matte Black p.585



TOPSAIL
Polished Chrome p.579



TOPSAIL
Antique Bronze p.579



TORINO
Brushed Nickel p.581



TORINO
Forged Bronze p.581



TRINITY
Brushed Nickel p.592



TRINITY
Polished Chrome p.592



TRINITY
Antique Bronze p.592



TRUSS LED
Brushed Nickel p.495



TRUSS LED
Architectural Bronze p.495



VICTORIAN
Brushed Nickel p.591



VICTORIAN
Polished Chrome p.591



VICTORIAN
Venetian Bronze p.591



WINSLETT
Brushed Nickel p.532



WINSLETT
Black p.533



WISTEN
Brushed Nickel p.588



WISTEN
Antique Bronze p.588



Outdoor

ABBOTT
Antique Bronze p.636



ABBOTT
Antique Pewter p.637



ALUM. CYLINDERS
Bronze p.747



ALUM. CYLINDERS
White p.747



ALUM. CYLINDERS
Black p.747



ALUM. CYLINDERS
Metallic Gray p.747



ALUM. CYLINDERS LED
Antique Bronze p.744



ALUM. CYLINDERS LED
White p.744



ALUM. CYLINDERS LED
Graphite p.744



ALUM. CYLINDERS LED
Satin Nickel p.744



ALUMINUM SQUARES
Bronze p.748



ALUMINUM SQUARES
White p.748



ALUMINUM SQUARES
Black p.748



ALUM. SQUARES LED
Bronze p.748



ALUM. SQUARES LED
White p.748



ALUM. SQUARES LED
Black p.748



ALUM. SQUARES LED
Metallic Gray p.748



ANDOVER
Antique Bronze p.656



ANDOVER
Black p.657



ANSON LED
Architectural Bronze p.742



ARRIVE LED
Black p.690



ARTS & CRAFTS
Weathered Bronze p.681



ASHMORE
Antique Bronze p.654



ASHMORE
Textured Black p.654



BARLOWE
Antique Bronze p.633



BARLOWE
Stainless Steel p.632



BARNETT
Antique Bronze p.627



BEAUFORT
Black p.701



BELL
Antique Bronze p.705



BELL
Textured Graphite p.705




BENTON HARBOR
Black p.629



BEVELED GLASS
Brushed Nickel p.728



BEVELED GLASS
Polished Solid Brass p.728



BEVELED GLASS
Antique Bronze p.728



BOTTA
Antique Bronze p.658



BOXWOOD
Antique Bronze p.683



BRASSGUARD LANTERNS
Brushed Nickel p.727



BRASSGUARD LANTERNS
Polished Brass p.726



BRASSGUARD LANTERNS
Black p.726



BRENHAM
Black p.618



BROOKSIDE
Copper p.688



BROOKSIDE
Gilded Iron p.688



BROOKSIDE
Antique Nickel p.688



BROOKSIDE LED
Copper p.689



BROOKSIDE LED
Gilded Iron p.689



BROOKSIDE LED
Antique Nickel p.689



BULKHEADS
White p.735



BULKHEADS
Black p.735



BULKHEADS LED
White p.734



BULKHEADS LED
Black p.734



BURLINGTON
Antique Bronze p.715



CALLAHAN LED
Antique Bronze p.670



CALLAHAN LED
Antique Pewter p.670



CARDIFF
Antique Bronze p.622



CARDIFF
Black p.622



CAST LANTERN
Black p.729



CEDAR SPRING
White p.664



CEDAR SPRING
Black p.664



CEDAR SPRING
Red p.664



CEDAR SPRING
Pistachio p.664



CEDAR SPRING
Metallic Gray p.664



CEDAR SPRING
Navy p.664



CEILING MOUNT
Antique Bronze p.731



CEILING MOUNT
Black p.731



CEILING MOUNT
White p.731



CERAMIC SCONCE
White p.706



COACH LANTERNS
Brushed Nickel p.728



COACH LANTERNS
Antique Bronze p.728



COACH LANTERNS
Black p.728



CONOVER
Antique Bronze p.640



CONOVER
Antique Pewter p.641



CORNICE LED
Antique Bronze p.736



Outdoor

CORNICE LED
Black p.736



CORNICE LED
Metallic Gray p.736



COVENTRY
Textured Black p.710



CRAWFORD
Oil Rubbed Bronze p.650



CRAWFORD
Black p.651



COMPEL
Black p.698



DERBY
Espresso p.674



DERBY LED
Antique Bronze p.675



DIE-CAST LED
Black p.743



DISTRICT
Antique Bronze p.702



DISTRICT
Metalic Gray p.702



DISTRICT LED
Antique Bronze p.703



DISTRICT LED
Metalic Grey p.703



DIVERGE
Architectural Bronze p.707



EAST HAVEN
Antique Bronze p.720



EAST HAVEN
Black p.720



EAST HAVEN LED
Antique Bronze p.721



EAST HAVEN LED
Black p.721



EDITION
Antique Bronze p.711



EDITION
Black p.711



`ENDICOTT
Antique Bronze p.638



ENDICOTT
Black p.639



ENDORSE LED
Black p.628



ENGLEWOOD
Antique Bronze p.668



ENGLEWOOD
Black p.668



ENGLEWOOD
Antique Pewter p.668



ESSENTIAL
Antique Bronze p.708



ESSENTIAL
Black p.708



FAIRVIEW
Black p.699



FELTON
Black p.695



FORMAT
Black p.697



GABLES
Antique Bronze p.625



GALVESTON
Galvanized p.620



GEOMETRIC
Architectural Bronze p.706



GLOBE LANTERN
Black p.708



GRANDBURY
Black p.631



GREENE RIDGE
Black p.700



GREENE RIDGE
Architectural Bronze p.700



GUNTHER
Antique Bronze p.709



HADDON
Antique Bronze p.684



HADDON
Black p.684



HARD-NOX
Black p.733



HASLETT
Black p.660



HASLETT
Antique Pewter p.661



HAWTHORNE
Black p.696



HOLLINGSWORTH
Black p.659



HOLCOMBE
Black p.666



IRONDALE
Black p.694



JACK
Antique Bronze p.705



JACK
Black p.705



LAINE
Architectural Bronze p.667



MAC
Black p.678



MAISON
Black p.648



MAISON
Oil Rubbed Bronze p.648



MANSARD NON-METALLIC
White p.732



MANSARD NON-METALLIC
White p.732



MARQUETTE
Black p.623



MCBEE
Black p.707



MCPHERSON
Black p.646



MEADOWLARK
Oil Rubbed Bronze p.645



MERIDIAN
Black p.653



MERIT
Black p.679



MILLFORD LED
Black p.743



NEW HAVEN
Black p.714



NEWPORT NON-METALLIC
Black p.732



NEWPORT NON-METALLIC
Black p.732



NON-METALLIC LANTERNS
Black p.729



NON-METALLIC LANTERNS
White p.730



NON-METALLIC LANTERNS
Black p.730



NON-METALLIC LANTERNS
White p.730



NON-METALLIC LANTERNS
Black p.730



NOTTINGTON
Forged Bronze p.652



Outdoor

OAKCLIFF
Antique Bronze p.680



ONION LANTERNS
Black p.712



PEDIGREE
Autumn Haze p.687



PEEK-A-BOO
Antique Bronze p.705



PENFIELD
Oil Rubbed Bronze p.691



PIER 33
Black p.704



POLYCARBONATE BULKHEADS
White p.735



POLYCARBONATE BULKHEADS
White p.735



POLYMERIC CYLINDERS
Textured White p.749



POLYMERIC CYLINDERS
Black p.749



PORT ROYAL
Black p.626



PRAIRIE
Brushed Nickel p.686



PRAIRIE
Gilded Iron p.686



PRAIRIE
Brushed Chestnut p.686



PRESTWICK
Oil Rubbed Bronze p.644



REFUGE
Oil Rubbed Bronze p.634



RESIDENCE
Antique Bronze p.676



RESORT
Aged Copper p.647



RIVER PLACE
Antique Bronze p.635



ROMAN COACH
Antique Bronze p.724



ROMAN COACH
Black p.724



ROMAN COACH
Antique Bronze p.725



ROMAN COACH
Black p.725



SEAGROVE
Black p.624



SQUIRE
Antique Bronze p.642



SQUIRE
Black p.643



STRATA LED
White p.736



STRATA LED
Metallic Gray p.736



STRATA LED
Antique Bronze p.736



STRATA LED
Black p.736



TORREY
Antique Bronze p.677



TOWNSHIP
Oil Rubbed Bronze p.621



TRELLIS
Antique Bronze p.682



UTILITY
White p.730



UTILITY
Black p.730



UTILITY
White p.730



UTILITY
Black p.730



VALERA LED
Brushed Nickel p.740



VALERA LED
Architectural Bronze p.740



WELBOURNE
Textured White p.722



WELBOURNE
Textured Black p.722



WELDON
Black p.716



WELDON
Architectural Bronze p.717



WESTPORT
Antique Bronze p.718



WESTPORT
White p.719



WESTPORT
Black p.718



WESTPORT LED
Antique Bronze p.713



WESTPORT LED
Black p.713



WHITE ACRYLIC GLOBES
Black p.733



WISH
Antique Bronze p.673



WISH
Black p.673



WISH LED
Antique Bronze p.672



WISH LED
Black p.672



Z-1010 LED
Black p.738



Z-1010 LED
Architectural Bronze p.738



Z-1020 LED
Black p.739



Z-1020 LED
Architectural Bronze p.739



Z-1030 LED
Antique Bronze p.737



Z-1030 LED
White p.737



Z-1030 LED
Black p.737



Z-1030 LED
Metallic Gray p.737



Z-1050 LED
Black p.739



Z-1060 LED
Black p.742



Z-1070 LED
Black p.741



Z-1070 LED
Metallic Gray p.741



Z-1080 LED
Black p.741



Z-1080 LED
Metallic Gray p.741



Z-1090 LED
Black p.738




Z-1090 LED
Satin White p.738





Z-2010 LED
Oil Rubbed Bronze p.739




Featuring Bonn







Collections

An Expression of *Style*

Scan and see more at
progresslighting.com





Eliza Alkire
Product Designer

Basically Boho

with Eliza

Bohemian style is perfect for non-conformists who shy away from rigid design rules, as they use their unique tastes to create their space. A simpler aesthetic is trending in Bohemian design. Use a minimalist approach when it comes to combining elements and allow patterned décor to add a pop of color. Hanging planters and potted greenery can serve as perfect additions to a Bohemian space, while enhancing character to any room. Add in rugs, pillows and furniture made with soft, lush materials and textures, to create a cozy atmosphere and help family, friends and guests feel at home.

Shop this style at
progresslighting.com/bohemian



"I'm a big fan of mixing metals. If you want to introduce a second finish into a room for plumbing or cabinet hardware, using mixed metal lighting is a great way to coordinate it,"

AMIE FRELING-BROWN
Meme Hill Studio



Featuring Rigsby by Design Series™



Featuring Cumberland by Design Series™

DESIGN+SERIES™





Colleen Visage
Vice President, Product Management

Serenely Simple Transitional

with Colleen

The Transitional home maintains the warmth of Traditional with the brightness of Contemporary trends. Simple silhouettes are ideal for transitional furnishings. Furniture pieces have crisp profiles and straightforward style, cleverly combining curves with straight lines. Tone-on-tone palettes and warm neutrals like beige, ivory and tan are ideal for a luxurious Transitional space.

Minimal use of vivid color creates a serene atmosphere. Textured materials such as leather, burlap, tweed and cotton are incorporated throughout different areas.

Shop this style at
progresslighting.com/transitional



Seneca

FINISHES


- Black - 031
- Polished Nickel - 104

PAIR WITH

Galley
Equinox
Bay Court

P400115-104


Sophisticated simplicity is personified in the Seneca collection. Within its open cage design the candelabra lights seem to float in midair, brought down to earth only by its simple base. Graceful lines radiate downwards for an unexpected, upside-down twist on traditional lighting design, making Seneca ideal for luxurious Transitional settings, while the overall, clean and modern look adds polished flair to Modern Farmhouse interiors.



Seneca


P400115-104


P500121-104


P400175-104


P400187-104


P500122-104

FIVE-LIGHT CHANDELIER
P400115-104 Polished Nickel
25-1/2" dia., 15-7/8" ht.,
Overall ht. w/stem 81-1/2"; wire 15'.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT LINEAR CHANDELIER
P400175-104 Polished Nickel
38-1/4" W., 15-3/8" D., 14-1/8" ht.,
Overall ht. w/stem 80-1/2"; wire 15'.
Six candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER
P400187-104 Polished Nickel
30" dia., 20-7/8" ht.,
Overall ht. w/stem 86-1/2"; wire 15'.
Nine candelabra base lamps,
each 60w max.

FOUR-LIGHT FOYER
P500121-104 Polished Nickel
15" dia., 17-1/4" ht.,
Overall ht. w/stem 83-1/2"; wire 15'.
Four candelabra base lamps,
each 60w max.

EIGHT-LIGHT FOYER
P500122-104 Polished Nickel
19-5/8" dia., 32" ht.,
Overall ht. w/stem 98"; wire 15'.
Eight candelabra base lamps,
each 60w max.

All fixtures shown with EF4T8D927/JA8 LED lamps, not included. See page 824.



Featuring Seneca and Conestee
Image: Schumacher Homes and Design by Trio

Seneca


P400115-031



P500121-031



P400175-031



P400187-031



P500122-031



FIVE-LIGHT CHANDELIER
P400115-031 Black
25-1/2" dia., 15-7/8" ht.,
Overall ht. w/stem 81-1/2"; wire 15'.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT LINEAR CHANDELIER
P400175-031 Black
38-1/4" W., 15-3/8" D., 14-1/8" ht.,
Overall ht. w/stem 80-1/2"; wire 15'.
Six candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER
P400187-031 Black
30" dia., 20-7/8" ht.,
Overall ht. w/stem 86-1/2"; wire 15'.
Nine candelabra base lamps,
each 60w max.

FOUR-LIGHT FOYER
P500121-031 Black
15" dia., 17-1/4" ht.,
Overall ht. w/stem 83-1/2"; wire 15'.
Four candelabra base lamps,
each 60w max.

EIGHT-LIGHT FOYER
P500122-031 Black
19-5/8" dia., 32" ht.,
Overall ht. w/stem 98"; wire 15'.
Eight candelabra base lamps,
each 60w max.

All fixtures shown with EF4T8D927/JA8 LED lamps, not included. See page 824.

Landree

FINISHES
- Black - 031
- Silver Ridge - 134

ALSO IN
Close-to-Ceiling

PAIR WITH
Riley
Rainey

P400178-031

An inner light cluster appears to float inside a geometric outer cage. The frame is designed to dramatically surround each fixture, presenting depth, dimension and beauty. Mini-pendant and flush mount versions feature a white silk shade. The exaggerated scale and elegant accents are suitable for Modern and Luxury design styles. A Black finish is paired with Vintage Gold accents while the Silver Ridge finish features Polished Nickel accents.

Geometric Outer Cage



Elegant Accents

Inner Light Cluster

Landree

P400178-134



P400177-134



P500177-134



P500176-134



THREE-LIGHT CHANDELIER
P400177-134 Silver Ridge
18-1/8″ dia., 12″ ht.,
Overall ht. w/stem 77″; wire 15′.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P400178-134 Silver Ridge
23″ dia., 16″ ht.,
Overall ht. w/stem 81″; wire 15′.
Five candelabra base lamps,
each 60w max.

MINI-PENDANT
P500176-134 Silver Ridge
10″ dia., 11-1/8″ ht.,
Overall ht. w/stem 75-1/2″; wire 10′.
One medium base lamp,
75w max.

EIGHT-LIGHT FOYER
P500177-134 Silver Ridge
23″ dia., 33-1/2″ ht.,
Overall ht. w/stem 102″; wire 15′.
Eight candelabra base lamps,
each 60w max.

P400087-020

Dramatic Beauty



Modern Luxury

Vintage Gold Accents

Landree


P400178-031



P400177-031



P500177-031



P500176-031



THREE-LIGHT CHANDELIER
P400177-031 Black
18-1/8″ dia., 12″ ht.,
Overall ht. w/stem 77″; wire 15′.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P400178-031 Black
23″ dia., 16″ ht.,
Overall ht. w/stem 81″; wire 15′.
Five candelabra base lamps,
each 60w max.

MINI-PENDANT
P500176-031 Black
10″ dia., 11-1/8″ ht.,
Overall ht. w/stem 75-1/2″; wire 10′.
One medium base lamp,
75w max.

EIGHT-LIGHT FOYER
P500177-031 Black
23″ dia., 33-1/2″ ht.,
Overall ht. w/stem 102″; wire 15′.
Eight candelabra base lamps,
each 60w max.

Less is More Impactful





Old becomes new again when a traditional dining room is enhanced with airy details.

1

Provide a youthful balance to traditional furniture by choosing graceful open cage lighting and wall sconces in a fresh mixed metal finish.

2

Use paler hues not only on the walls but on the classically styled dining room set to showcase its curved forms and contribute a modern flair to the setting.

3

Remember that less is more and pare down on accessories to make a bigger impact in a room.


Brandywine

FINISHES
- Antique Bronze - 020
- Silver Ridge - 134

PAIR WITH
Landree
Glimmer

P500069-020

Whimsical and romantic, the Brandywine Collection features an interlocking sphere with carefully crafted decorative details. The elegant frame captures a tasteful, timeless look with hand-painted accents and an airy frame perfect for generating a divine glow in a foyer, dining room, or kitchen.



Brandywine

P500069-134




THREE-LIGHT PENDANT
P500068-134 Silver Ridge
16″ dia., 19-3/4″ ht.,
Overall ht. w/chain 95″; wire 10′.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT PENDANT
P500287-134 Silver Ridge
22″ dia., 26″ ht.,
Overall ht. w/chain 101″, wire 15′.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT PENDANT
P500069-134 Silver Ridge
28″ dia., 31-7/8″ ht.,
Overall ht. w/chain 107″; wire 15′.
Six candelabra base lamps,
each 60w max.

P500287-134



P500068-134



Featuring Brandywine



Brandywine



THREE-LIGHT PENDANT
P500068-020 Antique Bronze
16″ dia., 19-3/4″ ht.,
Overall ht. w/chain 95″; wire 10′.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT PENDANT
P500287-020 Antique Bronze
22″ dia., 26″ ht.,
Overall ht. w/chain 101″, wire 15′.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT PENDANT
P500069-020 Antique Bronze
28″ dia., 31-7/8″ ht.,
Overall ht. w/chain 107″; wire 15′.
Six candelabra base lamps,
each 60w max.





Nealy

FINISH
Brushed Nickel - 009

ALSO IN
Bath

PAIR WITH
Lassiter
Clarion

P400141-009

Nealy offers classic charm with an edge of modern luxury. Curving details and candelabra arms are complemented by luxurious off-white silk shades. Featuring mixed metal influences, the Brushed Nickel frame is accentuated with Graphite detailing and completed with clear and brass-tone accents.



Nealy



P400142-009



P400141-009
shown without shades



P400150-009



P500141-009



P710046-009

FIVE-LIGHT CHANDELIER
P400141-009 Brushed Nickel
28-3/8″ dia., 28-1/4″ ht.,
Overall ht. w/chain 102-1/2″; wire 15′.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER
P400142-009 Brushed Nickel
36″ dia., 37-1/2″ ht.,
Overall ht. w/chain 159-1/2″; wire 15′.
Nine candelabra base lamps,
each 60w max.

THREE-LIGHT CHANDELIER
P400150-009 Brushed Nickel
21-1/2″ dia., 21-3/8″ ht.,
Overall ht. w/chain 96-1/2″; wire 15′.
Three candelabra base lamps,
each 60w max.

MINI-PENDANT
P500141-009 Brushed Nickel
7-1/4″ dia., 16-3/4″ ht.,
Overall ht. w/stem 80″; wire 10′.
One medium base lamp,
100w max.

WALL BRACKET
P710046-009 Brushed Nickel
5-1/2″ dia., 16-5/8″ ht.,
Extends 7″. H/CTR 7-1/2″.
One candelabra base lamp,
60w max.

Status

FINISH
Polished Chrome - 15

ALSO IN
Close-to-Ceiling
Bath

PAIR WITH
Evoke
Celeste
Landree

P4141-15

Status and prestige come naturally to this collection as its shimmering crystal highlights the Polished Chrome frames with shine and brilliance. Sleek, symmetrical arms crowned with classic white shades over an etched glass diffuser extend from the center column, adding a touch of minimalism against the sparkling crystal ornament.



Status


P4142-15

FIVE-LIGHT CHANDELIER
P4141-15 Polished Chrome
28″ dia., 23-1/8″ ht.,
Overall ht. w/chain 97″; wire 15′.
Five medium base lamps,
each 75w max.

NINE-LIGHT CHANDELIER
P4142-15 Polished Chrome
32″ dia., 33-1/8″ ht.,
Overall ht. w/chain 155″; wire 15′.
Nine medium base lamps,
each 75w max.

WALL BRACKET
P2060-15 Polished Chrome
6″ W., 15-1/2″ ht.,
Extends 7-3/8″. H/CTR 8-3/4″.
One medium base lamp,
75w max.

FOUR-LIGHT PENDANT
P3680-15 Polished Chrome
22″ dia., 28-1/2″ ht.,
Overall ht. w/chain 104″; wire 15′.
Four medium base lamps,
each 100w max.

MINI-PENDANT
P5031-15 Polished Chrome
6″ dia., 11-1/8″ ht.,
Overall ht. w/chain 77″; wire 10′.
One medium base lamp,
75w max.


P2060-15


P3680-15


P5031-15

Rainey

FINISHES
- Brushed Nickel - 009
- Graphite - 143

PAIR WITH
Landree
Blakely

P400167-009

Rainey embraces an artful display of asymmetrical design styling. A slender, staggered frame representing organic forms draws the eye upward to admire the fluted ribbed glass shades. The larger scale is suitable for open floor plans, great rooms or anywhere a dramatic focal piece is needed to make a bold statement. Rainey is available in Graphite with Brushed Bronze accents or Brushed Nickel.



Rainey

P400168-009



P350122-009





P350122-009
shown as semi-flush

P400167-009





P710056-009

SEMI-FLUSH CONVERTIBLE
P350122-009 Brushed Nickel
Hanging and ceiling mount hardware included.
18″ dia., 16″ ht.,
Overall ht. w/stem 81-1/2″; wire 10′.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER
P400167-009 Brushed Nickel
24″ dia., 22-1/4″ ht.,
Overall ht. w/stem 88-1/2″; wire 15′.
Five candelabra base lamps, each 60w max.

SIX-LIGHT CHANDELIER
P400168-009 Brushed Nickel
28″ dia., 25-1/4″ ht.,
Overall ht. w/stem 91-1/2″; wire 15′.
Six candelabra base lamps, each 60w max.

WALL BRACKET
P710056-009 Brushed Nickel
11-1/2″ W., 16-1/2″ ht.,
Extends 5-1/8″. H/CTR 5-5/8″.
Two candelabra base lamps, each 60w max.

All fixtures shown with EF4T8D927/JA8 LED lamps, not included. See page 824.

Featuring Rainey and Hide-a-Lite LED undercabinet and Puck lighting



Mix Modern & Natural Styles

Modern and rustic have never looked so good together. Take a cue from the artful placement of the asymmetrically designed Rainey chandelier over the organic shape of a rough-hewn table-top and bench. Use a neutral color palette on the cabinets and walls to lend a sleek look, but be sure to add details such as pairing textured fabric on the otherwise modern style of the dining chairs to keep the look from becoming cold. Finish with undercabinet lighting to cast the perfect amount of light on countertop tasks.

Rainey

P400168-143



P350122-143



SEMI-FLUSH CONVERTIBLE
P350122-143 Graphite
Hanging and ceiling mount hardware included.
18″ dia., 16″ ht.,
Overall ht. w/stem 81-1/2″; wire 10′.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER
P400167-143 Graphite
24″ dia., 22-1/4″ ht.,
Overall ht. w/stem 88-1/2″; wire 15′.
Five candelabra base lamps, each 60w max.

SIX-LIGHT CHANDELIER
P400168-143 Graphite
28″ dia., 25-1/4″ ht.,
Overall ht. w/stem 91-1/2″; wire 15′.
Six candelabra base lamps, each 60w max.

WALL BRACKET
P710056-143 Graphite
11-1/2″ W., 16-1/2″ ht.,
Extends 5-1/8″. H/CTR 5-5/8″.
Two candelabra base lamps, each 60w max.

All fixtures shown with EF4T8D927/JA8 LED lamps, not included. See page 824.

P400167-143





P350122-143
shown as semi-flush




P710056-143

Draper

FINISH	ALSO IN	PAIR WITH
Polished Nickel - 104	Bath	Evoke Glimmer

P4718-104

Inspired by mid-century design, the Draper collection reimagines that era with charm and intrigue. Swooping arms capped with sleek cylinders offer a futuristic shape ideal for use with tubular or globe style lamps to create a truly signature statement for your home.



Draper



P4719-104



P4718-104



P5061-104



P2101-104

WALL BRACKET
P2101-104 Polished Nickel
4-1/2″ W., 8″ ht.,
Extends 4-1/8″. H/CTR 4″.
One candelabra base lamp,
60w max.

FIVE-LIGHT CHANDELIER
P4718-104 Polished Nickel
25″ dia., 15-5/8″ ht.,
Overall ht. w/stem 82″; wire 15′.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER
P4719-104 Polished Nickel
32″ dia., 21-3/4″ ht.,
Overall ht. w/stem 88″; wire 15′.
Nine candelabra base lamps,
each 60w max.

MINI-PENDANT
P5061-104 Polished Nickel
6-1/2″ dia., 12-1/4″ ht.,
Overall ht. w/stem, 78″; wire 10′.
One candelabra base lamp,
60w max.

All fixtures shown with P7826-01 vintage lamps, not included. See page 824.

Caress

FINISH
Polished Nickel - 104

ALSO IN
Close-to-Ceiling
Bath

PAIR WITH
Equinox
Stratham

P4645-104WB

Gently sweeping arms cradle richly textured water glass shades that capture and cast shimmering light against a bright Polished Nickel frame. Etched glass diffusers add to the playful reflections while a unique stem-hung construction carries a clean line to the ceiling.



Caress



P4646-104WB



P4645-104WB



P3946-104



P7046-104WB

ONE-LIGHT FOYER
P3946-104 Polished Nickel
14″ dia., 30″ ht.,
Overall ht. w/stem 96″; wire 15′.
One medium base lamp,
100w max.

FIVE-LIGHT CHANDELIER
P4645-104WB Polished Nickel
27″ dia., 22″ ht.,
Overall ht. w/stem 88″; wire 15′.
Five candelabra base krypton lamps*,
each 60w max., included.

NINE-LIGHT CHANDELIER
P4646-104WB Polished Nickel
36-5/8″ dia., 33-5/8″ ht.,
Overall ht. w/stem 100″; wire 15′.
Nine candelabra base krypton lamps*,
each 60w max., included.

WALL BRACKET
P7046-104WB Polished Nickel
8″ W., 15″ ht.,
Extends 9-1/2″. H/CTR 8-7/8″.
One candelabra base krypton lamp*,
60w max. included.

**Replacement lamp P7807-01.*
See page 824.

Featuring Caress
Image: Sunrise Homes and Masterpiece Design Group



Reflect with Sparkle & Shine

All white is just right when it is coupled with a polished wooden table and floorboards to ground the look. Make the most of a small dining area by using mirrors to reflect light and open up the space. Use a chandelier like Caress as a focal point, whose water glass shades add rich texture and playful reflections from the striking mirrored wall.



Caress

THREE-LIGHT CHANDELIER
P4644-104WB Polished Nickel
22″ dia., 24-1/2″ ht.,
Overall ht. w/stem 91″; wire 15′.
Three candelabra base krypton lamps*, each 60w max., included.

SIXTEEN-LIGHT CHANDELIER
P4685-104WB Polished Nickel
47″ dia., 46′ ht.,
Overall ht. w/stem 181″; wire 15′.
Sixteen candelabra base krypton lamps*, each 60w max., included.
Weight of fixture exceeds NEC limits for outlet box hanging. Consult professional electrician for proper installation.

MINI-PENDANT
P5044-104WB Polished Nickel
6-3/8″ dia., 10-3/4″ ht.,
Overall ht w/chain or stem 77″; wire 15′.
One candelabra base krypton lamp*, 60w max., included.

MINI-PENDANT
P5306-104WB Polished Nickel
8″ dia., 12-1/2″ ht.,
Overall ht. w/stem 78″; wire 15′.
One candelabra base krypton lamp*, 60w max., included.

**Replacement lamp P7807-01.*
See page 824.







Tinsley

FINISHES
- Polished Chrome - 015
- Brushed Bronze - 109

ALSO IN
Close-to-Ceiling

PAIR WITH
Celeste
Landree
Clarion

P400066-109

Featuring soft angles and impressive sculptural curves, Tinsley is a refreshingly updated design for Luxe, Transitional and Traditional interiors. The frame is complemented by classic etched glass shades or open candle designs. Overscale details found in Tinsley are ideal for welcoming guests and visitors in a foyer or entryway, as well as in luxe dining room or classic living room settings.





P400110-109



P400066-109



P710028-109



P400065-109



P400067-109



P350079-109



P500072-109



P500062-109

Tinsley

SEMI-FLUSH CONVERTIBLE
P350079-109 Brushed Bronze
Hanging and ceiling mount hardware included.
16-1/2″ dia., 11-1/2″ ht.,
Overall ht. w/chain 51″, wire 10′.
Two medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER
P400065-109 Brushed Bronze
23-1/2″ dia., 19″ ht.,
Overall ht. w/chain 94″, wire 15′.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER
P400066-109 Brushed Bronze
23″ dia., 24″ ht.,
Overall ht. w/chain 99″, wire 15′.
Five candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER
P400067-109 Brushed Bronze
29-1/4″ dia., 31″ ht.,
Overall ht. w/chain 154″, wire 15′.
Nine candelabra base lamps, each 60w max.

FIFTEEN-LIGHT CHANDELIER
P400110-109 Brushed Bronze
42″ dia., 41-3/4″ ht.,
Overall ht. w/chain 154″, wire 15′.
Fifteen candelabra base lamps, each 60w max.

THREE-LIGHT PENDANT
P500062-109 Brushed Bronze
22-1/2″ dia., 22-1/2″ ht.,
Overall ht. w/chain 97-1/2″, wire 15′.
Three medium base lamps, each 100w max.

MINI-PENDANT
P500072-109 Brushed Bronze
7-1/2″ dia., 12-1/2″ ht.,
Overall ht. w/stem 80-1/2″, wire 10′.
One medium base lamp, 100w max.

WALL BRACKET
P710028-109 Brushed Bronze
4-7/8″ W., 15-1/2″ ht.,
Extends 5-1/2″. H/CTR 8″.
One candelabra base lamp, 60w max.

Featuring Tinsley





P400110-015



P400066-015



P710028-015



P400065-015



P400067-015



P350079-015



P500072-015



P500062-015

Tinsley

SEMI-FLUSH CONVERTIBLE
P350079-015 Polished Chrome
Hanging and ceiling mount hardware included.
16-1/2″ dia., 11-1/2 ht.,
Overall ht. w/chain 51″, wire 10′.
Two medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER
P400065-015 Polished Chrome
23-1/2″ dia., 19″ ht.,
Overall ht. w/chain 94″, wire 15′.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER
P400066-015 Polished Chrome
23″ dia., 24″ ht.,
Overall ht. w/chain 99″, wire 15′.
Five candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER
P400067-015 Polished Chrome
29-1/4″ dia., 31″ ht.,
Overall ht. w/chain 154″, wire 15′.
Nine candelabra base lamps, each 60w max.

FIFTEEN-LIGHT CHANDELIER
P400110-015 Polished Chrome
42″ dia., 41-3/4″ ht.,
Overall ht. w/chain 154″, wire 15′.
Fifteen candelabra base lamps, each 60w max.

THREE-LIGHT PENDANT
P500062-015 Polished Chrome
22-1/2″ dia., 22-1/2″ ht.,
Overall ht. w/chain 97-1/2″, wire 15′.
Three medium base lamps, each 100w max.

MINI-PENDANT
P500072-015 Polished Chrome
7-1/2″ dia., 12-1/2″ ht.,
Overall ht. w/stem 80-1/2″, wire 10′.
One medium base lamp, 100w max.

WALL BRACKET
P710028-015 Polished Chrome
4-7/8″ W., 15-1/2″ ht.,
Extends 5-1/2″. H/CTR 8″.
One candelabra base, 60w max.

Anjoux

FINISHES	ALSO IN	PAIR WITH
Antique Bronze - 020	Bath	Savor
Silver Ridge - 134	Close-to-Ceiling	Stratham

P400087-134

A stunning bell-shaped frame is the hallmark of the Anjoux Collection. Elegant crystal teardrops fall from sparkling strands, gracefully ornamenting the frame's bold curves. Elegant white shades can be added to Anjou fixtures for a distinctively different look. A coordinating wall sconce casts shimmering light through a textured water glass shade.



Anjoux

P500099-134



P400088-134
shown with P860007-000 shade



P500100-134



P400087-134
shown with P860007-000 shade



P350094-134





P300116-134



P860007-000

WALL BRACKET
P300116-134 Silver Ridge
5" W., 8-5/8" ht.,
Extends 6-7/8". H/CTR 4-1/2".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE
P350094-134 Silver Ridge
Hanging and ceiling mount
hardware included.
14-1/2" dia., 17-1/2" ht.,
Overall ht. w/chain 53", wire 10'.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P400087-134 Silver Ridge
24-5/8" dia., 26-1/2" ht.,
Overall ht. w/chain 100-1/2", wire 15'.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER
P400088-134 Silver Ridge
34" dia., 34" ht.,
Overall ht. w/chain 156", wire 15'.
Nine candelabra base lamps,
each 60w max.

FOUR-LIGHT FOYER
P500099-134 Silver Ridge
16" dia., 24" ht.,
Overall ht. w/chain 98", wire 15'.
Four candelabra base lamps,
each 60w max.

SIX-LIGHT FOYER
P500100-134 Silver Ridge
22" dia., 30" ht.,
Overall ht. w/chain 104-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

ACCESSORY SHADE
P860007-000 Ivory Silk
1" uno-style candle fitter
5-3/4" dia., 4-1/2" ht.

P400087-020



Anjoux

P500099-020



P400088-020



P500100-020



P400087-020
shown with P860008-000 shade



P350094-020





P300116-020



P860008-000

WALL BRACKET
P300116-020 Antique Bronze
5" W., 8-5/8" ht.,
Extends 6-7/8". H/CTR 4-1/2".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE
P350094-020 Antique Bronze
Hanging and ceiling mount hardware included.
14-1/2" dia., 17-1/2" ht.,
Overall ht. w/chain 53", wire 10'.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P400087-020 Antique Bronze
24-5/8" dia., 26-1/2" ht.,
Overall ht. w/chain 100-1/2", wire 15'.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER
P400088-020 Antique Bronze
34" dia., 34" ht.,
Overall ht. w/chain 156", wire 15'.
Nine candelabra base lamps,
each 60w max.

FOUR-LIGHT FOYER
P500099-020 Antique Bronze
16" dia., 24" ht.,
Overall ht. w/chain 98", wire 15'.
Four candelabra base lamps,
each 60w max.

SIX-LIGHT FOYER
P500100-020 Antique Bronze
22" dia., 30" ht.,
Overall ht. w/chain 104-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

ACCESSORY SHADE
P860008-000 Vintage Linen
1" uno-style fitter
5-3/4" dia., 4-1/2" ht.

Equinox

FINISHES

- Satin Brass - 12
- Antique Bronze - 20
- Matte Black - 31
- Polished Nickel - 104
- Burnished Silver - 126

PAIR WITH

Litchfield
Seneca
Kene

P3841-104

Interlocking rings form the perfect sphere as they pivot in a variety of adjustable positions around a center stem. Inside the orb, sleek candelabra bases command center stage as they radiate alluring light from every imaginable angle.



Equinox

P3889-104



P3827-104



P3841-104



P7078-104



P7077-104



FOUR-LIGHT PENDANT
P3827-104 Polished Nickel
16″ dia., 18-3/8″ ht.,
Overall ht. w/chain 94″; wire 15′.
Four candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P3841-104 Polished Nickel
22″ dia., 24-3/8″ ht.,
Overall ht. w/chain 99-1/2″; wire 15′.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER
P3889-104 Polished Nickel
27-3/4″ dia., 30″ ht.,
Overall ht. w/chain 105″; wire 15′.
Six candelabra base lamps,
each 60w max.

ONE-LIGHT PENDANT
P7077-104 Polished Nickel
11-3/8″ dia., 12-1/16″ ht.,
Overall ht. w/chain 78″; wire 10′.
One medium base lamp,
100w max.

ONE-LIGHT PENDANT
P7078-104 Polished Nickel
16″ dia., 16-3/4″ ht.,
Overall ht. w/chain 83″; wire 10′.
One medium base lamp,
100w max.

Featuring Equinox and Chronicle by Design Series™
Image: Green Tech Homes, Piper Stromatt and 161 Photography




Warm Wood Adds Comfort & Style

Reclaimed wood takes center stage in an open concept space. Wood acts as a warming element and this rustic kitchen vent hood melds together industrial metals, neutral wall color and a gray-blue undertone of the Shaker-style cabinets into a natural, organic look.

Choose lighting that delivers a punch, but doesn't overwhelm the space. The large Equinox chandelier brings a crisp and clean, yet industrial feel that gives overall balance to the area. A trio of round Chronicle pendants over the island provides contrast to the sea of rectangular shapes furnished by the cabinets, subway tile, paneled kitchen island detail and the oven hood.

Equinox











EIGHT-LIGHT OVAL CHANDELIER
P3791-20 Antique Bronze
39″ L., 14-1/4 W., 26-3/8″ ht.,
Overall ht. w/chain 150″; wire 15′.
Eight candelabra base lamps,
each 60w max.

FOUR-LIGHT PENDANT
P3827-20 Antique Bronze
16″ dia., 18-3/8″ ht.,
Overall ht. w/chain 94″; wire 15′.
Four candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P3841-20 Antique Bronze
22″ dia., 24-3/8″ ht.,
Overall ht. w/chain 99-1/2″; wire 15′.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER
P3889-20 Antique Bronze
27-3/4″ dia., 30″ ht.,
Overall ht. w/chain 105″; wire 15′.
Six candelabra base lamps,
each 60w max.

MINI-PENDANT
P5142-20 Antique Bronze
10-1/8″ dia., 12-1/2″ ht.,
Overall ht. w/chain 87″; wire 15′.
Three candelabra base lamps,
each 60w max.

Equinox

FOUR-LIGHT PENDANT
P3827-12 Satin Brass
P3827-31 Matte Black
16″ dia., 18-3/8″ ht.,
Overall ht. w/chain 94″, wire 15′.
Four candelabra base lamps,
each 60w max.


FIVE-LIGHT CHANDELIER
P3841-12 Satin Brass
P3841-31 Matte Black
22″ dia., 24-3/8″ ht.,
Overall ht. w/chain 99-1/2″, wire 15′.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER
P3889-12 Satin Brass
P3889-31 Matte Black
27-3/4″ dia., 30″ ht.,
Overall ht. w/chain 105″, wire 15′.
Six candelabra base lamps,
each 60w max.

P3841-12



P3841-31



P3889-12



P3889-31




P3827-12



P3827-31



Equinox











EIGHT-LIGHT OVAL CHANDELIER
P3791-126 Burnished Silver
39″ L., 14-1/4 W., 26-3/8″ ht.,
Overall ht. w/chain 150″; wire 15′.
Eight candelabra base lamps,
each 60w max.

FOUR-LIGHT PENDANT
P3827-126 Burnished Silver
16″ dia., 18-3/8″ ht.,
Overall ht. w/chain 94″; wire 15′.
Four candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P3841-126 Burnished Silver
22″ dia., 24-3/8″ ht.,
Overall ht. w/chain 99-1/2″; wire 15′.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER
P3889-126 Burnished Silver
27-3/4″ dia., 30″ ht.,
Overall ht. w/chain 105″; wire 15′.
Six candelabra base lamps,
each 60w max.

MINI-PENDANT
P5142-126 Burnished Silver
10-1/8″ dia., 12-1/2″ ht.,
Overall ht. w/chain 87″; wire 15′.
Three candelabra base lamps,
each 60w max.

Kene


FINISHES
- Brushed Nickel - 009
- Graphite - 143

ALSO IN
Bath

PAIR WITH
Chadwick
Lassiter

P400095-143

With flowing ribbons of metal that hold double glass shades with balance and grace, Kene is inspired by traditional forms yet has a modern edge. Etched glass diffusers offer a patterned texture that shines through clear outer shades providing a luxurious touch. A semi-flush convertible ceiling fixture with a textured fabric shade rounds out the collection beautifully.



Kene



P400096-143



P400095-143



P350098-143



P500103-143

SEMI-FLUSH CONVERTIBLE
P350098-143 Graphite
Hanging and ceiling mount hardware included.
16″ dia., 10-7/8″ ht.,
Overall ht. w/chain 50-1/2″, wire 10′.
Two medium base lamps, each 75w max.

FIVE-LIGHT CHANDELIER
P400095-143 Graphite
27-1/4″ dia., 22-1/2″ ht.,
Overall ht. w/chain 97-1/2″, wire 15′.
Five medium base lamps, each 75w max.

NINE-LIGHT CHANDELIER
P400096-143 Graphite
32-3/4″ dia., 29-7/8″ ht.,
Overall ht. w/chain 152-1/2″, wire 15′.
Nine medium base lamps, each 75w max.

MINI-PENDANT
P500103-143 Graphite
6″ dia., 15-7/8″ ht.,
Overall ht. w/chain 82-1/2″, wire 10′.
One medium base lamp, 75w max.

P400095-009



Kene

P400096-009



P400095-009





P350098-009

P500103-009



SEMI-FLUSH CONVERTIBLE
P350098-009 Brushed Nickel
Hanging and ceiling mount hardware included.
16″ dia., 10-7/8″ ht.,
Overall ht. w/chain 50-1/2″, wire 10′.
Two medium base lamps, each 75w max.

FIVE-LIGHT CHANDELIER
P400095-009 Brushed Nickel
27-1/4″ dia., 22-1/2″ ht.,
Overall ht. w/chain 97-1/2″, wire 15′.
Five medium base lamps, each 75w max.

NINE-LIGHT CHANDELIER
P400096-009 Brushed Nickel
32-3/4″ dia., 29-7/8″ ht.,
Overall ht. w/chain 152-1/2″, wire 15′.
Nine medium base lamps, each 75w max.

MINI-PENDANT
P500103-009 Brushed Nickel
6″ dia., 15-7/8″ ht.,
Overall ht. w/chain 82-1/2″, wire 10′.
One medium base lamp, 75w max.

Chadwick

FINISHES

- Brushed Nickel - 009
- Matte Black - 031

PAIR WITH

Tobin
Haven

P400226-009

Simple geometric forms and clean crisp lines form the Chadwick Collection. Opal glass shades visually calm the sharp edges of the boxy frames. This collection is perfect for minimalist settings in need of a subtle, feminine touch.

Simple Geometric Form




Brushed Nickel

Opal Glass Shades

Chadwick



P400225-009



P400226-009



P500274-009



P710089-009


THREE-LIGHT LINEAR CHANDELIER
P400225-009 Brushed Nickel
40″ W., 12″ D., 8- 3/4″ ht.,
Overall ht. w/stem 59″, wire 15′.
Three medium base lamps,
each 100w max.

FOUR-LIGHT CHANDELIER
P400226-009 Brushed Nickel
21-5/8″ sq., 12-7/8″ ht.,
Overall ht. w/stem 70″, wire 15′.
Four medium base lamps,
each 100w max.

ONE-LIGHT PENDANT
P500274-009 Brushed Nickel
10-1/2″ sq., 14-3/4″ ht.,
Overall ht. w/stem 72″, wire 10′.
One medium base lamp,
100w max.

WALL SCONCE
P710089-009 Brushed Nickel
5-1/2″ W., 18″ ht.,
Extends 5-3/8″. H/CTR 14-1/4″.
One medium base lamp,
100w max.


P400226-031



Chadwick



P400225-031



P400226-031



P500274-031



P710089-031

THREE-LIGHT LINEAR CHANDELIER
P400225-031 Matte Black
40″ W., 12″ D., 8- 3/4″ ht.,
Overall ht. w/stem 59″, wire 15′.
Three medium base lamps,
each 100w max.

FOUR-LIGHT CHANDELIER
P400226-031 Matte Black
21-5/8″ sq., 12-7/8″ ht.,
Overall ht. w/stem 70″, wire 15′.
Four medium base lamps,
each 100w max.

ONE-LIGHT PENDANT
P500274-031 Matte Black
10-1/2″ sq., 14-3/4″ ht.,
Overall ht. w/stem 72″, wire 10′.
One medium base lamp,
100w max.

WALL SCONCE
P710089-031 Matte Black
5-1/2″ W., 18″ ht.,
Extends 5-3/8″. H/CTR 14-1/4″.
One medium base lamp,
100w max.

Lassiter

FINISHES	ALSO IN	PAIR WITH
Matte Black - 031	Bath	Chadwick
Brushed Nickel - 009	Close-to-Ceiling	Kene

P400197-031

Showcase a swoon-worthy lighting experience with the stunning blend of modern and traditional styles in the one-of-a-kind Lassiter Collection. Square tubing with clean, sharp angles demand your attention and appreciation. Vintage light sockets boast their bold, yet simple demeanors as they are encased in sophisticated clear glass shades to complete this statement-making collection.



Lassiter

P400198-031



P500209-031



P400197-031





P350149-031

P500208-031





P710073-031

THREE-LIGHT SEMI-FLUSH
P350149-031 Matte Black
13″ dia., 10-1/2″ ht.,
Three medium base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P400197-031 Matte Black
26″ dia., 26″ ht.,
Overall ht. w/chain 101″, wire 15′.
Five medium base lamps,
each 60w max.

NINE-LIGHT CHANDELIER
P400198-031 Matte Black
32″ dia., 29″ ht.,
Overall ht. w/chain 152″, wire 15′.
Nine medium base lamps,
each 60w max.

MINI-PENDANT
P500208-031 Matte Black
6-3/8″ dia., 12-1/2″ ht.,
Overall ht. w/chain 81″, wire 10′.
One medium base lamp,
60w max.

THREE-LIGHT FOYER
P500209-031 Matte Black
16-5/8″ dia., 26″ ht.,
Overall ht. w/chain 101″, wire 15′.
Three medium base lamps,
each 60w max.

WALL BRACKET
P710073-031 Matte Black
4-7/8″ W., 19-1/4″ ht.,
Extends 6-1/2″. H/CTR 9-3/8″.
One medium base lamp,
60w max.

All fixtures shown with F7ST19DLED927/JA8 LED lamps, not included. See page 824.

P400197-009



Lassiter

P400198-009



P500209-009



P400197-009





P350149-009

P500208-009





P710073-009

THREE-LIGHT SEMI-FLUSH
P350149-009 Brushed Nickel
13″ dia., 10-1/2″ ht.,
Three medium base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P400197-009 Brushed Nickel
26″ dia., 26″ ht.,
Overall ht. w/chain 101″, wire 15′.
Five medium base lamps,
each 60w max.

NINE-LIGHT CHANDELIER
P400198-009 Brushed Nickel
32″ dia., 29″ ht.,
Overall ht. w/chain 152″, wire 15′.
Nine medium base lamps,
each 60w max.

MINI-PENDANT
P500208-009 Brushed Nickel
6-3/8″ dia., 12-1/2″ ht.,
Overall ht. w/chain 81″, wire 10′.
One medium base lamp,
60w max.

THREE-LIGHT FOYER
P500209-009 Brushed Nickel
16-5/8″ dia., 26″ ht.,
Overall ht. w/chain 101″, wire 15′.
Three medium base lamps,
each 60w max.

WALL BRACKET
P710073-009 Brushed Nickel
4-7/8″ W., 19-1/4″ ht.,
Extends 6-1/2″. H/CTR 9-3/8″.
One medium base lamp,
60w max.

All fixtures shown with F7ST19DLED927/JA8 LED lamps, not included. See page 824.

Darker shades of blue are leading the way in color trends.

1

Merge vibrant blues with neutral textures and colors for simple elegance.

2

Place contemporary art on classically crisp white walls.

3

Complement the space with the airy Lassiter pendant for a formal touch that works in perfect harmony with the contemporary furnishings.




Blue Leads the Way
3
2

Piedmont

FINISHES

- Antique Bronze - 20
- Burnished Silver - 126

PAIR WITH

Durrell
Cascadia
Saluda

P3884-20

Refresh your look with the transitional-style Piedmont Collection. This collection features light fixtures with overarching roofs, vertical structures, and clusters of light bases in open, airy designs.



Piedmont


P400033-020


P3884-20

FOUR-LIGHT FOYER
P3884-20 Antique Bronze
P3884-126 Burnished Silver
13-3/8″ sq., 20-3/8″ ht.,
Overall ht. w/chain 95″; wire 15′.
Four candelabra base lamps,
each 60w max.

EIGHT-LIGHT LINEAR CHANDELIER
P400033-020 Antique Bronze
P400033-126 Burnished Silver
30-1/8″ W., 12″ D., 16-1/2″ ht.,
Overall ht. w/chain 83″; wire 15′.
Eight candelabra base lamps,
each 60w max.


P400033-126


P3884-126

Winslett

FINISHES	ALSO IN	PAIR WITH
Brushed Nickel - 009	Bath	Passage
Matte Black - 031	Close-to-Ceiling	Greyson

P400206-031

Immerse yourself in a home atmosphere primed for relaxation and inspired thinking with the beautiful imperfection of the Winslett Collection. Savor this fresh take on a classic light choice as your gaze traces graceful arms and clean crisp lines. Perfectly imperfect lightly seeded glass shades rest in shiny pedestal light bases that adds an unexpected, but welcomed dash of modern personality to this clean, traditional collection.



Winslett

P400207-031



P400208-031



P500240-031



P400206-031



P500239-031



P350153-031





P350153-031
shown as semi-flush

P500238-031



SEMI-FLUSH CONVERTIBLE
P350153-031 Matte Black
Hanging and ceiling mount hardware included
13-3/4″ dia., 11-7/8″ ht.,
Overall ht. w/chain 50-1/2″, wire 10′.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER
P400206-031 Matte Black
27-1/8″ dia., 21-1/8″ ht.,
Overall ht. w/chain 95-1/2″, wire 15′.
Five medium base lamps, each 60w max.

SIX-LIGHT OVAL LINEAR CHANDELIER
P400207-031 Matte Black
34-1/8″ W., 24-3/4″ D., 21-1/4″ ht.,
Overall ht. w/chain 96″, wire 15′.
Six medium base lamps, each 60w max.

NINE-LIGHT CHANDELIER
P400208-031 Matte Black
34-1/8″ dia., 31-5/8″ ht.,
Overall ht. w/chain 155″, wire 15′.
Nine medium base lamps, each 60w max.

MINI-PENDANT
P500238-031 Matte Black
9-1/4″ dia., 15-7/8″ ht.,
Overall ht. w/chain 80″, wire 10′.
One medium base lamp, 60w max.

THREE-LIGHT PENDANT
P500239-031 Matte Black
12-7/8″ dia., 17-1/8″ ht.,
Overall ht. w/chain 91-1/2″, wire 15′.
Three candelabra base lamps, each 60w max.

FOUR-LIGHT FOYER
P500240-031 Matte Black
19-5/8″ sq., 25″ ht.,
Overall ht. w/chain 99-1/2″, wire 15′.
Four candelabra base lamps, each 60w max.

All fixtures shown with F4B10LED927/JA8 or F7ST19DLED927/JA8 LED lamps, not included. See page 824.

Featuring Winslett



In Perfect Balance

Mix it up in a formal dining room by placing two upholstered armchairs at the head and foot of the table, disrupting the scale but still bringing a sense of balance to the room. Beige is anything but boring in a color scheme that incorporates light colors using fun wall art and curvy chairs. The Winslett chandelier adds to the room's charm with its perfectly imperfect seeded glass shades and sweeping arms.

Winslett

P400207-009



P400208-009



P500240-009



P400206-009



P500239-009



P350153-009





P500238-009



P350153-009
shown as semi-flush

SEMI-FLUSH CONVERTIBLE
P350153-009 Brushed Nickel
Hanging and ceiling mount hardware included
13-3/4″ dia., 11-7/8″ ht.,
Overall ht. w/chain 50-1/2″, wire 10′.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER
P400206-009 Brushed Nickel
27-1/8″ dia., 21-1/8″ ht.,
Overall ht. w/chain 95-1/2″, wire 15′.
Five medium base lamps, each 60w max.

SIX-LIGHT OVAL LINEAR CHANDELIER
P400207-009 Brushed Nickel
34-1/8″ W., 24-3/4″ D., 21-1/4″ ht.,
Overall ht. w/chain 96″, wire 15′.
Six medium base lamps, each 60w max.

NINE-LIGHT CHANDELIER
P400208-009 Brushed Nickel
34-1/8″ dia., 31-5/8″ ht.,
Overall ht. w/chain 155″, wire 15′.
Nine medium base lamps, each 60w max.

MINI-PENDANT
P500238-009 Brushed Nickel
9-1/4″ dia., 15-7/8″ ht.,
Overall ht. w/chain 80″, wire 10′.
One medium base lamp, 60w max.

THREE-LIGHT PENDANT
P500239-009 Brushed Nickel
12-7/8″ dia., 17-1/8″ ht.,
Overall ht. w/chain 91-1/2″, wire 15′.
Three candelabra base lamps, each 60w max.

FOUR-LIGHT FOYER
P500240-009 Brushed Nickel
19-5/8″ sq., 25″ ht.,
Overall ht. w/chain 99-1/2″, wire 15′.
Four candelabra base lamps, each 60w max.

All fixtures shown with F4B10LED927/JA8 or F7ST19DLED927/JA8 LED lamps, not included. See page 824.

Bowman

FINISHES	ALSO IN	PAIR WITH
● Matte Black - 031	Bath	Whisp
○ Cottage White - 151	Close-to-Ceiling	Bonn

P400194-031

The Bowman Collection, with its slightly larger scale and gracefully sweeping arms appeal to both classic taste and artistic spirit. Clear chiseled shades adorn elegant light bases topped with traditional candle slips, offering the ultimate refined look.



Bowman

P400196-031



P400195-031



P500207-031



P400194-031



P350148-031



SEMI-FLUSH CONVERTIBLE
P350148-031 Matte Black
Hanging and ceiling mount hardware included.
14-1/4″ dia., 13-3/8″ ht.,
Overall ht. w/chain 52-1/2″, wire 10′.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER
P400194-031 Matte Black
26″ dia., 23-1/4″ ht.,
Overall ht. w/chain 98-1/4″, wire 15′.
Five candelabra base lamps, each 60w max.

SIX-LIGHT CHANDELIER
P400195-031 Matte Black
32″ dia., 28-7/8″ ht.,
Overall ht. w/chain 104″, wire 15′.
Six candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER
P400196-031 Matte Black
37″ dia., 33-1/4″ ht.,
Overall ht. w/chain 156-1/4″, wire 15′.
Nine candelabra base lamps, each 60w max.

FOUR-LIGHT FOYER
P500207-031 Matte Black
14-1/4″ dia., 26-1/4″ ht.,
Overall ht. w/chain 100-1/2″, wire 15′.
Four candelabra base lamps, each 60w max.

All fixtures shown with F4B10LED927/JA8 lamps, not included.
See page 824.

P400194-151



Bowman

P400196-1511



P400195-151



P500207-151



P400194-151



P350148-151



SEMI-FLUSH CONVERTIBLE
P350148-051 Cottage White
Hanging and ceiling mount hardware included.
14-1/4″ dia., 13-3/8″ ht.,
Overall ht. w/chain 52-1/2″, wire 10′.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER
P400194-151 Cottage White
26″ dia., 23-1/4″ ht.,
Overall ht. w/chain 98-1/4″, wire 15′.
Five candelabra base lamps, each 60w max.

SIX-LIGHT CHANDELIER
P400195-151 Cottage White
32″ dia., 28-7/8″ ht.,
Overall ht. w/chain 104″, wire 15′.
Six candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER
P400196-151 Cottage White
37″ dia., 33-1/4″ ht.,
Overall ht. w/chain 156-1/4″, wire 15′.
Nine candelabra base lamps, each 60w max.

FOUR-LIGHT FOYER
P500207-151 Cottage White
14-1/4″ dia., 26-1/4″ ht.,
Overall ht. w/chain 100-1/2″, wire 15′.
Four candelabra base lamps, each 60w max.

All fixtures shown with F4B10LED927/JA8 lamps, not included.
See page 824.

Sleep in Sweet Serenity





Serenity rules when a monochromatic color scheme is layered with tons of texture.

1

Liven a light palette with deep pops of navy blue and introduce texture through decorative items curated in soft shades of gray and blue.

2

Make crisp white bedding truly inviting by layering piles of pillows against a soft upholstered headboard, then toss a throw across the foot for a luxurious welcome.

3

Finish the look with the elegant Bowman chandelier to shed a soft glow from chiseled glass shades atop gently sweeping arms.

Greyson

FINISH
● Black - 31

PAIR WITH
Spicewood
Gresham

P4710-31

Black iron frames with twisted elements and beveled backplates take center stage in the Greyson Collection. Candle-like light bases accent these rustic pieces for a bold, yet casual feel.



Greyson


P4711-31


P4710-31


P3577-31


P4709-31


P7158-31

SIX-LIGHT FOYER
P3577-31 Black
18-1/4" dia., 31-1/4" ht.,
Overall ht. w/chain 106-1/2"; wire 15'.
Six candelabra base lamps,
each 60w max.

THREE-LIGHT CHANDELIER
P4709-31 Black
14-1/4" dia., 15-7/8" ht.,
Overall ht. w/chain 90"; wire 15'.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P4710-31 Black
21-1/2" dia., 20-1/2" ht.,
Overall ht. w/chain 96"; wire 15'.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER
P4711-31 Black
26" dia., 23-1/2" ht.,
Overall ht. w/chain 98-3/4"; wire 15'.
Six candelabra base lamps,
each 60w max.

WALL BRACKET
P7158-31 Black
4" W., 8-1/4 ht.,
Extends 4-3/4. H/CTR 4-1/8".
One candelabra base lamp,
60w max.

Hemsworth

FINISHES
- Textured Black - 031
- Galvanized - 141

ALSO IN
Sconces
Close-to-Ceiling

PAIR WITH
Gulliver
Bonn
Briarwood

P500277-031

A rustic flair is the cornerstone look of this family with both aged and bleached oak faux wood finishes.

Rustic Charm

Barn Inspired Metal Details




Textured Black

Hemsworth



P400229-031



P500277-031



P710093-031



P350172-031



P350172-031
shown as semi-flush

TWO-LIGHT SEMI-FLUSH
P350172-031 Textured Black
Hanging and ceiling mount hardware included.
13-1/2″ sq., 10-1/8″ ht.,
Overall ht. w/chain 51″, wire 10′.
Two medium base lamps, each 60w max.

FOUR-LIGHT LINEAR CHANDELIER
P400229-031 Textured Black
36″ W., 9-14″ D., 7-7/8″ ht.,
Overall ht. w/chain 78-1/2″, wire 15′.
Four medium base lamps, each 60w max.

FOUR-LIGHT PENDANT
P500277-031 Textured Black
18″ sq., 7″ ht.,
Overall ht. w/chain 73″, wire 15′.
Four medium base lamps, each 60w max.

WALL BRACKET
P710093-031 Textured Black
4-3/4″ W., 16-3/4″ ht.,
Extends 3-7/8″. H/CTR 10-3/4″.
One medium base lamp, 60w max.

All fixtures shown with F7ST19DLED927/JA8 LED lamps, not included. See page 824.

Featuring Hemsworth




Bring the Outdoors In

Follow today's trend of forging a deep connection with outdoor life while entertaining in sleek style. Bring the outside in with greenery, wooden accents and terracotta pots placed against a clean black and beige color palette. Add a showstopper chandelier like the clean-lined Hemsworth, whose warm wooden frame and metal hardware bring together the best of rustic and modern design.

Hemsworth



P400229-141



P500277-141



P710093-141



P350172-141



P350172-141
shown as semi-flush

TWO-LIGHT SEMI-FLUSH
P350172-141 Galvanized
Hanging and ceiling mount hardware included.
13-1/2″ sq., 10-1/8″ ht.,
Overall ht. w/chain 51″, wire 10′.
Two medium base lamps, each 60w max.

FOUR-LIGHT LINEAR CHANDELIER
P400229-141 Galvanized
36″ W., 9-14″ D., 7-7/8″ ht.,
Overall ht. w/chain 78-1/2″, wire 15′.
Four medium base lamps, each 60w max.

FOUR-LIGHT PENDANT
P500277-141 Galvanized
18″ sq., 7″ ht.,
Overall ht. w/chain 73″, wire 15′.
Four medium base lamps, each 60w max.

WALL BRACKET
P710093-141 Galvanized
4-3/4″ W., 16-3/4″ ht.,
Extends 3-7/8″. H/CTR 10-3/4″.
One medium base lamp, 60w max.

All fixtures shown with F7ST19DLED927/JA8 LED lamps, not included. See page 824.

Mast


FINISHES
- Brushed Nickel - 009
- Antique Bronze - 020

ALSO IN
Bath
Close-to-Ceiling
Sconces

PAIR WITH
Alexa
Chadwick
Hemsworth

P400190-020

Mast combines a clean, modern design expression with faux wood accents for a modern-meets-farmhouse approach to lighting. The contrast of warm wood paired with sleek metallic lines and double glass shades offers a subtly alluring, Zen look to the linear pendant and mini-pendant. An oversized cylindrical frame banded top and bottom with faux wood accents gives a warm organic feel to the flush mount fixture.



Modern meets Farmhouse

Mast


P400190-009

FOUR-LIGHT LINEAR CHANDELIER
P400190-009 Brushed Nickel
P400190-020 Antique Bronze
38" W., 4-7/8" D., 14-3/4" ht.,
Overall ht. w/stem 80-1/2"; wire 15'.
Four medium base lamps,
each 100w max.

MINI-PENDANT
P500192-009 Brushed Nickel
P500192-020 Antique Bronze
6-1/4" dia., 14" ht.,
Overall ht. w/stem 80"; wire 10'.
One medium base base lamp,
100w max.


P500192-009


P500192-020


P400190-020



Featuring Mast and Gulliver



Barnes Mill

FINISH
Antique Bronze - 020

ALSO IN
Bath
Close-to-Ceiling
Sconces

PAIR WITH
Spicewood
Kempsey

P400055-020

Rustic and vintage décor can transform your home into a nostalgic retreat reminiscent of rural farmhouses. Exposed iron details and a faux-painted wooden plank support artful, clear seeded glass shades. Combine with vintage-style light bulbs to create a romantic focal point for any room.



Barnes Mill



P400055-020



P350059-020



P500056-020



P350059-020
shown flush mounted



P300066-020

WALL BRACKET
P300066-020 Antique Bronze
4 1/2" W., 11 7/8" ht.,
Extends 5 7/8". H/CTR 7-5/8".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE
P350059-020 Antique Bronze
Hanging and ceiling mount
hardware included.
16-1/4" dia., 11-7/8" ht.,
Overall ht. w/chain 52", wire 10'.
Two medium base lamps,
each 75w max.

FIVE-LIGHT LINEAR CHANDELIER
P400055-020 Antique Bronze
38" W., 4" D., 22-5/8" ht.,
Overall ht. w/chain 96-1/2", wire 15'.
Five medium base lamps,
each 100w max.

MINI-PENDANT
P500056-020 Antique Bronze
8-3/4" dia., 14" ht.,
Overall ht. w/chain 89", wire 10'.
One medium base lamp,
100w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

Fleurette

FINISH

○ Cottage White - 151

PAIR WITH

Marche
Austelle

P400151-151

Inspired by the charm of a European countryside, Fleurette is ideal for Farmhouse and Transitional spaces. Its design features a striking juxtaposition of the rustic and the sophisticated. Glass ornaments adorn curved arms that create an elegant interior frame. The chandelier is finished in Cottage White and is embraced by an outer open frame in Gilded Pewter.



Fleurette

P400152-151



SEMI-FLUSH CONVERTIBLE
P350115-151 Cottage White
Hanging and ceiling mount hardware included.
15-7/8″ dia., 19 5/8″ ht.,
Overall ht. w/chain 53-1/2″; wire 10′.
Three candelabra base lamps, each 60w max.

THREE-LIGHT CHANDELIER
P400151-151 Cottage White
22″ dia., 23-1/4″ ht.,
Overall ht. w/stem 89-1/2″; wire 15′.
Three candelabra base lamps, each 60w max.


FIVE-LIGHT CHANDELIER
P400152-151 Cottage White
32″ dia., 33-5/8″ ht.,
Overall ht. w/stem 99-1/2″; wire 15′.
Five candelabra base lamps, each 60w max.

P400151-151



P350115-151





P350115-151
shown as ceiling mount

Featuring Fleurette and Kempsey

Transitional with a Twist





Masculine and feminine touches balance comfortably in Transitional style.

1

Accent an airy color palette with interestingly textured pillows and pops of dark gray to add depth.

2

Place swing arm Kempsey wall sconces over each nightstand not only to free up space but also to provide adjusted, focused light.

3

Complete the room with a classic, yet modern fixture like Fleurette to capture the strong lines yet romantic details of the room.

Austelle

FINISHES
- Antique Bronze - 020
- Galvanized - 141

ALSO IN
Close-to-Ceiling

PAIR WITH
Tilley
Fleurette

P400205-141

Your home will exude comfort and sophistication with the graceful Austelle Collection. Breathtaking mesh shades are the signature design feature of this family that showcases a perfect balance of rustic elegance.



Rustic Elegance

Austelle



P400205-020


P400205-141


P400204-020


P400204-141


P500228-020*


P500228-141*

FOUR-LIGHT CHANDELIER
P400204-020 Antique Bronze
P400204-141 Galvanized
18″ dia., 17-1/8″ ht.,
Overall ht. w/chain 93″, wire 15′.
Four candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P400205-020 Antique Bronze
P400205-141 Galvanized
24″ dia., 20″ ht.,
Overall ht. w/chain 96″, wire 15′.
Five candelabra base lamps,
each 60w max.

MINI-PENDANT
P500228-020 Antique Bronze
P500228-141 Galvanized
8-1/2″ dia., 15-5/8″ ht.,
Overall ht. w/chain 90-1/2″, wire 10′.
One medium base lamp,
60w max.

All fixtures shown with F4B10LED927/JA8 or F7ST19DLED927/JA8 LED lamps, not included. See page 824.


Briarwood

FINISHES	ALSO IN	PAIR WITH
Antique Bronze - 020	Bath	Tilley
Graphite - 143	Close-to-Ceiling	Hemsworth

P400047-143

The Briarwood collection features a classic pattern commonly found on barn or farmhouse doors and gates. The simple geometric form features a faux-painted wood enclosure to frame vintage-style light bulbs. Choose from a coastal-inspired whitewashed finish paired with Graphite details, or a rich oak finish and Antique Bronze combination.

Geometric Form



Faux Painted Wood

Farmhouse Inspiration

Briarwood

P400048-143



FOUR-LIGHT CHANDELIER
P400047-143 Graphite
20″ sq., 12″ ht.,
Overall ht. w/stem 88″, wire 15'.
Four medium base lamps,
each 100w max.

FIVE-LIGHT LINEAR CHANDELIER
P400048-143 Graphite
38″ W., 10″ D., 9″ ht.,
Overall ht. w/stem 75″, wire 15'.
Five medium base lamps,
each 100w max.

MINI-PENDANT
P500041-143 Graphite
10″ sq., 9″ ht.,
Overall ht. w/stem 78″, wire 10'.
One medium base lamp,
100w max.

FOUR-LIGHT FOYER
P500178-143 Graphite
15-1/2″ sq., 20-1/8″ ht.,
Overall ht. w/stem 86-1/2″, wire 15'.
Four medium base lamps,
each 60w max.


WALL SCONCE
P710012-143 Graphite
6-7/8″ W., 12″ ht.,
Extends 6″, H/CTR 4″.
One medium base lamp,
100w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

P500178-143



P400047-143



P500041-143





P710012-143



Featuring Briarwood
Image: Keystone Custom Homes and The Premise Studio

Make it Cozy and Inviting

A rustic kitchen island offers a cozy, warm and inviting contrast to the refined look of classic floor-to-ceiling white cabinets. Make the island a true room divider by building it in a U-shape that follows the flow of the hallway. Compliment the island's weathered barnboard base with geometric pendants like Briarwood, which features a barndoor-inspired, X-brace design and faux wood-painted frame. Pull sleek bar chairs up to the island to add a touch of sophistication while keeping the rustic, comfortable feel.

Briarwood

P400048-020



P500178-020



P400047-020



P500041-020





P710012-020

FOUR-LIGHT CHANDELIER
P400047-020 Antique Bronze
20″ sq., 12″ ht.,
Overall ht. w/stem 88″, wire 15’.
Four medium base lamps,
each 100w max.

FIVE-LIGHT LINEAR CHANDELIER
P400048-020 Antique Bronze
38″ W., 10″ D., 9″ ht.,
Overall ht. w/stem 75″, wire 15’.
Five medium base lamps,
each 100w max.

MINI-PENDANT
P500041-020 Antique Bronze
10″ sq., 9″ ht.,
Overall ht. w/stem 78″, wire 10’.
One medium base lamp,
100w max.

FOUR-LIGHT FOYER
P500178-020 Antique Bronze
15-1/2″ sq., 20-1/8″ ht.,
Overall ht. w/stem 86-1/2″, wire 15’.
Four medium base lamps,
each 60w max.

WALL SCONCE
P710012-020 Antique Bronze
6 7/8″ W., 12″ ht.,
Extends 6″, H/CTR 4″.
One medium base lamp,
100w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

Conestee

FINISHES
- Galvanized - 141
- Graphite - 143

PAIR WITH
Fontayne
Calhoun

P500094-141

Truly eye-catching yet classic, the Conestee collection features graceful orb shapes uniquely finished in complementing dual-tone, hand-painted metalwork. Exposed bulbs are tucked into vintage style light bases offering a look that is ideal for Farmhouse and Industrial settings, while its hand-painted finishes in Galvanized and weathered tones easily complement Coastal and Rustic spaces.

Dual Tone Finish



Spherical Design

Rotating Rings

Conestee


P500094-143

MINI-PENDANT
P500092-143 Graphite
12″ dia., 14″ ht.,
Overall ht. w/chain 89″, wire 10′.
One medium base lamp,
60w max.

THREE-LIGHT PENDANT
P500093-143 Graphite
21-1/4″ dia., 24″ ht.,
Overall ht. w/chain 99″, wire 15′.
Three medium base lamps,
each 60w max.

SIX-LIGHT PENDANT
P500094-143 Graphite
28″ dia., 30-3/4″ ht.,
Overall ht. w/chain 106″, wire 15′.
Six medium base lamps,
each 60w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.


P500093-143


P500092-143

Featuring Conestee



Conestee

P500094-141



MINI-PENDANT
P500092-141 Galvanized
12″ dia., 14″ ht.,
Overall ht. w/chain 89″, wire 10′.
One medium base lamp,
60w max.

THREE-LIGHT PENDANT
P500093-141 Galvanized
21-1/4″ dia., 24″ ht.,
Overall ht. w/chain 99″, wire 15′.
Three medium base lamps,
each 60w max.

SIX-LIGHT PENDANT
P500094-141 Galvanized
28″ dia., 30-3/4″ ht.,
Overall ht. w/chain 106″, wire 15′.
Six medium base lamps,
each 60w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

P500093-141



P500092-141



Gulliver

FINISHES
- Galvanized - 141
- Graphite - 143

ALSO IN
Bath
Ceiling Fans
Close-to-Ceiling
Sconces

PAIR WITH
Briarwood
Conestee

P500090-143

Three circular bands wrap together to create an open design for Gulliver. Dual toned frame color combinations are hand painted Galvanized with antique white accents or Graphite with weathered gray accents. Embossed wood grained texture complements Rustic and Modern Farmhouse home décor, as well as Urban Industrial and Coastal interior settings.



Gulliver

P400097-141



P500090-141





P350049-141
shown as ceiling mount

P500023-141



P500022-141





P710031-141

SEMI-FLUSH CONVERTIBLE
P350049-141 Galvanized
Hanging and ceiling mount hardware included.
17″ dia., 13-1/2″ ht.,
Overall ht. w/chain 52-1/2″, wire 10′.
Three medium base lamps, each 75w max.

FOUR-LIGHT LINEAR CHANDELIER
P400097-141 Galvanized
38-1/2″ W., 10-1/2″ D., 17″ ht.,
Overall ht. w/chain 91-1/2″, wire 15′.
Four medium base lamps, each 75w max.

MINI-PENDANT
P500022-141 Galvanized
8-1/12″ dia., 10″ ht.,
Overall ht. w/chain 85″, wire 10′.
One medium base lamp, 75w max.

FOUR-LIGHT PENDANT
P500023-141 Galvanized
21-5/8″ dia., 18-1/4″ ht.,
Overall ht. w/chain 93-1/2″, wire 10′.
Four medium base lamps, each 75w max.

FIVE-LIGHT PENDANT
P500090-141 Galvanized
27-3/4″ dia., 22-3/4″ ht.,
Overall ht. w/chain 93-1/2″, wire 10′.
Five medium base lamps, each 75w max.

WALL BRACKET
P710031-141 Galvanized
6″ dia., 12″ ht.,
Extends 7″. H/CTR 9-3/8″.
One medium base lamp, 75w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.



Featuring Farris and Gulliver

Go For A Seamless Flow

It's all about flow in an open concept home, and the number one way to achieve that is to use the same flooring throughout. Stick to a cohesive color scheme on the walls to continue the seamless look throughout the space. Next, repeat favorite elements, like the rich wood grain texture of the mantle that is seen again in the circular bands of the Gulliver linear chandelier and eccentric dining chairs which complement the elongated shape of the fixture. Finally, tie the space together by using calm, neutral tones throughout the furnishings in the living area.

Gulliver


P400097-143


P500090-143


P350049-143


P500023-143


P500022-143


P710031-143

SEMI-FLUSH CONVERTIBLE
P350049-143 Graphite
Hanging and ceiling mount hardware included.
17″ dia., 13-1/2″ ht.,
Overall ht. w/chain 52-1/2″; wire 10′.
Three medium base lamps, each 75w max.

FOUR-LIGHT LINEAR CHANDELIER
P400097-143 Graphite
38-1/2″ W., 10-1/2″ D., 17″ ht.,
Overall ht. w/chain 91-1/2″, wire 15′.
Four medium base lamps, each 75w max.

MINI-PENDANT
P500022-143 Graphite
8-1/2″ dia., 10″ ht.,
Overall ht. w/chain 85″; wire 10′.
One medium base lamp, 75w max.

FOUR-LIGHT PENDANT
P500023-143 Graphite
21-5/8″ dia., 18-1/4″ ht.,
Overall ht. w/chain 93-1/2″; wire 10′.
Four medium base lamps, each 75w max.

FIVE-LIGHT PENDANT
P500090-143 Graphite
27-3/4″ dia., 22-3/4″ ht.,
Overall ht. w/chain 93-1/2″, wire 10′.
Five medium base lamps, each 75w max.

WALL BRACKET
P710031-143 Graphite
6″ dia., 12″ ht.,
Extends 7″. H/CTR 9-3/8″.
One medium base lamp, 75w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

P400158-141
shown with P860041-000 shade

Arching and delicate details curve to create an airy design in new Gulliver options. Dual-toned frame color combinations are Galvanized with antique white accents and Graphite with weathered gray accents. The hand painted wood grained texture complements Coastal and Farmhouse home décor. Accessory shades are available in Natural Burlap or Flax Linen options.



Gulliver

P500158-141



P400159-141
shown with P860042-000 shade



P500157-141



P400158-141*



P350117-141*
shown hanging





P350117-141
shown as ceiling mount

SEMI-FLUSH CONVERTIBLE
P350117-141 Galvanized
Hanging and ceiling mount hardware included.
14-7/8″ dia., 12-5/8″ ht.,
Overall ht. w/chain 53″; wire 10′.
Four candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER
P400158-141 Galvanized
26″ dia., 30″ ht.,
Overall ht. w/chain 105-1/2″; wire 12′.
Five candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER
P400159-141 Galvanized
35-1/4″ dia., 40-1/2″ ht.,
Overall ht. w/chain 163-1/2″; wire 12′.
Nine candelabra base lamps, each 60w max.

FOUR-LIGHT FOYER
P500157-141 Galvanized
17″ dia., 26-1/4″ ht.,
Overall ht. w/chain 102-1/2″; wire 12′.
Four candelabra base lamps, each 60w max.

EIGHT-LIGHT FOYER
P500158-141 Galvanized
21″ dia., 33-3/4″ ht.,
Overall ht. w/chain 108-1/2″; wire 12′.
Eight candelabra base lamps, each 60w max.

ACCESSORY SHADE
P860041-000 Natural Burlap
1″ uno-style candle fitter
6″ dia., 5-1/8″ ht.

ACCESSORY SHADE
P860042-000 Flax Linen
1″ uno-style candle fitter
6″ dia., 5-1/8″ ht.

**Fixtures shown with P7826-01 vintage lamps, not included. See page 824.*



P860041-000



P860042-000

Featuring Gulliver
Image: Fridley Homes



Gulliver



P500158-143



P400159-143
shown with P860041-000 shade



P500157-143



P400158-143*



P350117-143*
shown hanging



P350117-143
shown as ceiling mount

SEMI-FLUSH CONVERTIBLE
P350117-143 Graphite
Hanging and ceiling mount hardware included.
14-7/8″ dia., 12-5/8″ ht.,
Overall ht. w/chain 53″; wire 10′.
Four candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER
P400158-143 Graphite
26″ dia., 30″ ht.,
Overall ht. w/chain 105-1/2″; wire 12′.
Five candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER
P400159-143 Graphite
35-1/4″ dia., 40-1/2″ ht.,
Overall ht. w/chain 163-1/2″; wire 12′.
Nine candelabra base lamps, each 60w max.

FOUR-LIGHT FOYER
P500157-143 Graphite
17″ dia., 26-1/4″ ht.,
Overall ht. w/chain 102-1/2″; wire 12′.
Four candelabra base lamps, each 60w max.

EIGHT-LIGHT FOYER
P500158-143 Graphite
21″ dia., 33-3/4″ ht.,
Overall ht. w/chain 108-1/2″; wire 12′.
Eight candelabra base lamps, each 60w max.

ACCESSORY SHADE
P860041-000 Natural Burlap
1″ uno-style candle fitter
6″ dia., 5-1/8″ ht.

ACCESSORY SHADE
P860042-000 Flax Linen
1″ uno-style candle fitter
6″ dia., 5-1/8″ ht.

**Fixtures shown with P7826-01 vintage lamps, not included. See page 824.*



P860041-000



P860042-000

Trestle

FINISH

● Gilded Iron - 71

PAIR WITH

Gulliver
Tilley

P5168-71

Incorporate a handsome look in your industrial or rustic living space with the Trestle Collection. A gilded iron finish is enhanced by hand-painted, golden oak accents.



Trestle









FOUR-LIGHT LINEAR CHANDELIER
P4720-71 Gilded Iron
32-1/2″ W., 15″ D., 20-3/8″ ht.,
Overall ht. w/chain 95″; wire 15′.
Four medium base lamps,
each 60w max.

ONE-LIGHT PENDANT
P5152-71 Gilded Iron
14″ dia., 8-3/4″ ht.,
Overall ht. w/chain 84″; wire 10′.
One medium base lamp,
60w max.

FOUR-LIGHT PENDANT
P5168-71 Gilded Iron
20″ dia., 17″ ht.,
Overall ht. w/stem 92″; wire 15′.
Four medium base lamps,
each 60w max.

MINI-PENDANT
P5315-71 Gilded Iron
7-7/8″ dia., 14-3/4″ ht.,
Overall ht. w/chain 88″, wire 10′.
One medium base lamp,
60w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

Tilley


FINISHES
- Brushed Nickel - 009
- Antique Bronze - 020

ALSO IN
Bath
Close-to-Ceiling

PAIR WITH
Briarwood
Gulliver
Hemsworth

P400074-009

Rustic and vintage décor is a popular trend that can transform a home into a nostalgic retreat. Tilley features warehouse style shades formed from metal mesh that merge with a faux-painted, wooden rim for an artful yet Industrial style.



Tilley

P400074-020



P400073-020



P500078-020



P500079-020



THREE-LIGHT CHANDELIER
P400073-009 Brushed Nickel
20″ dia., 15-1/4″ ht.,
Overall ht. w/chain 90-1/2″, wire 15′.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P400074-009 Brushed Nickel
24″ dia., 16-7/8″ ht.,
Overall ht. w/chain 92″, wire 15′.
Five medium base lamps,
each 100w max.

MINI-PENDANT
P500078-009 Brushed Nickel
8″ dia., 7-1/2″ ht.,
Overall ht. w/stem 73-1/2″, wire 10′.
One medium base lamp,
100w max.

THREE-LIGHT PENDANT
P500079-009 Brushed Nickel
16″ dia., 10-7/8″ ht.,
Overall ht. w/stem 77″, wire 10′.
Three medium base lamps,
each 60w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.



Featuring Tilley
Image: Green Tech Homes, Piper Stromatt and 161 Photography

Focus on Wow

When designing your kitchen, think about which wow factor to focus on.

1

A Modern Farmhouse look is complete when the choice is made to go with bold lighting against a clean, neutral background.

2

The iron mesh shade and painted wood trim of the Tilley pendants join together the kitchen's farmhouse-style.

3

Open shelving and the kitchen vent hood finish the look with symmetry and harmony.

Tilley

P400074-009



P400073-009



P500078-009



P500079-009



THREE-LIGHT CHANDELIER
P400073-020 Antique Bronze
20″ dia., 15-1/4″ ht.,
Overall ht. w/chain 90-1/2″, wire 15′.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P400074-020 Antique Bronze
24″ dia., 16-7/8″ ht.,
Overall ht. w/chain 92″, wire 15′.
Five medium base lamps,
each 100w max.

MINI-PENDANT
P500078-020 Antique Bronze
8″ dia., 7-1/2″ ht.,
Overall ht. w/stem 73-1/2″, wire 10′.
One medium base lamp,
100w max.

THREE-LIGHT PENDANT
P500079-020 Antique Bronze
16″ dia., 10-7/8″ ht.,
Overall ht. w/stem 77″, wire 10′.
Three medium base lamps,
each 60w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

Litchfield

FINISH	ALSO IN	PAIR WITH
Polished Chrome - 015	Bath Sconces	Saluda Equinox

P400103-015

The Litchfield Collection features light fixtures inspired by casual coastal living. A signature clear, hourglass column or shade can be seen on each of the fixtures complemented by a crisp chrome finish.



Hourglass-Inspired Column

Chrome Finish

Casual and Coastal

Litchfield



P710044-015
shown above and below with adjustable arm



P400104-015



P350093-015



P400102-015
shown with P860027-000 shade



P500113-015



P500114-015



SEMI-FLUSH CONVERTIBLE
P350093-015 Polished Chrome
Hanging and ceiling mount hardware included.
18″ dia., 14-3/4″ ht.,
Overall ht. w/chain 52″, wire 10′.
Extends 14-3/4″.
Three medium base lamps, each 60w max.

THREE-LIGHT CHANDELIER
P400102-015 Polished Chrome
19-3/8″ dia., 22-1/8″ ht.,
Overall ht. w/chain 96-1/2″, wire 15′.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER
P400103-015 Polished Chrome
25-7/8″ dia., 21-7/8″ ht.,
Overall ht. w/chain 97″, wire 15′.
Five candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER
P400104-015 Polished Chrome
34″ dia., 32-1/2″ ht.,
Overall ht. w/chain 155-1/2″, wire 15′.
Nine candelabra base lamps, each 60w max.

MINI-PENDANT
P500113-015 Polished Chrome
4-3/4″ dia., 9-3/8″ ht.,
Overall ht. w/stem 75-1/2″, wire 10′.
One medium base lamp, 60w max.

THREE-LIGHT PENDANT
P500114-015 Polished Chrome
13-5/8″ dia., 18″ ht.,
Overall ht. w/stem 84″, wire 15′.
Three candelabra base lamps, each 60w max.

WALL BRACKET
P710044-015 Polished Chrome
5″ W., 13″ ht. Extends 14-1/2″.
Adjustable arm
One medium base lamp, 60w max.

ACCESSORY SHADE
P860027-000 White Sailcloth
1″ uno-style candle fitter
6-3/4″ dia., 5″ ht.

P860027-000

Calhoun

FINISHES
- Brushed Nickel - 009
- Antique Bronze - 020

ALSO IN
Bath

PAIR WITH
Seneca
Mast


P400133-020
spanner with long stem

A trend in home décor is the repurposing of antique pieces. Calhoun playfully follows this trend with an apothecary style clear glass diffuser held in place with a mechanical latch from a spice container. A glass shade showcases a thickened profile to create a vintage-style surface for a classic handmade appearance. The vintage design is a perfect complement to several décor styles including the popular Farmhouse trend.




Calhoun

P400132-020



P400133-020



THREE-LIGHT CHANDELIER
P400132-020 Antique Bronze
22-5/8″ dia., 29-1/8″ ht.,
Overall ht. w/chain 103″, wire 10′.
Three medium base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P400133-020 Antique Bronze
28-5/8″ dia., 29-1/8″ ht.,
Overall ht. w/chain 103″, wire 10′.
Five medium base lamps,
each 60w max.

MINI-PENDANT
P500055-020 Antique Bronze
4-3/4″ dia., 9″ ht.,
Overall ht. w/stem 75″, wire 10′.
One medium base lamp,
100w max.

ONE-LIGHT PENDANT
P500152-020 Antique Bronze
12″ dia., 9-3/8″ ht.,
Overall ht. w/stem 75-1/2″, wire 10′.
One medium base lamp,
60w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

Calhoun is a versatile style that can be displayed in three different ways for both three-light and five-light chandeliers: assemble with the included optional spanner and long or short stems for a unique cord-hung style chandelier, or let the lights hang in a more casual cluster.

P400132-020
spanner with short stem



P400133-020
spanner with short stem



P400132-020
spanner with long stem



P500152-020



P500055-020



Featuring Callahan




Be Ingeniously Industrial


A canvas of exposed brick walls and dark metal-paned windows brings interesting visual and textural elements to the clean Industrial space. Use metal and wood elements throughout to play up the minimal yet rugged vibe. Since utility and function are cornerstones of the warehouse look, place an ultra-functional pendant like Calhoun center stage. With its unique, adjustable design, Calhoun can be installed several ways for three different, personalized custom looks.

Calhoun

P400132-009



P400133-009



P400132-009
spanner with short stem



P400133-009
spanner with short stem



P400132-009
spanner with long stem



P500152-009



P500055-009



THREE-LIGHT CHANDELIER
P400132-009 Brushed Nickel
22-5/8″ dia., 29-1/8″ ht.,
Overall ht. w/chain 103″, wire 10′.
Three medium base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P400133-009 Brushed Nickel
28-5/8″ dia., 29-1/8″ ht.,
Overall ht. w/chain 103″, wire 10′.
Five medium base lamps,
each 60w max.

MINI-PENDANT
P500055-009 Brushed Nickel
4-3/4″ dia., 9″ ht.,
Overall ht. w/stem 75″, wire 10′.
One medium base lamp,
100w max.

ONE-LIGHT PENDANT
P500152-009 Brushed Nickel
12″ dia., 9-3/8″ ht.,
Overall ht. w/stem 75-1/2″, wire 10′.
One medium base lamp,
60w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

Calhoun is a versatile style that can be displayed in three different ways for both three-light and five-light chandeliers: assemble with the included optional spanner and long or short stems for a unique cord-hung style chandelier, or let the lights hang in a more casual cluster.

Durrell


FINISHES
- Brushed Nickel - 009
- Matte Black - 031

ALSO IN
Bath
Close-to-Ceiling

PAIR WITH
Calhoun
Hemsworth

P400199-009

The versatile Durrell Collection will find a home in any coastal, modern farmhouse, or vintage setting in need of gorgeous generous illumination. Featuring a variety of versatile materials including a sailcloth linen shade and wooden accents. Durrell will showcase a lighting experience that is welcoming and sophisticated.



Durrell

P400200-009



P500210-009



P400199-009



P400218-009



P350150-009
shown hanging





P350150-009
shown as ceiling mount



P710074-009

SEMI-FLUSH CONVERTIBLE
P350150-009 Brushed Nickel
Hanging and ceiling mount hardware included
16″ dia., 13-1/2″ ht.,
Overall ht. w/chain 47″, wire 10′.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER
P400199-009 Brushed Nickel
26-1/2″ dia., 22-1/2″ ht.,
Overall ht. w/chain 97-1/2″, wire 15′.
Five candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER
P400200-009 Brushed Nickel
32″ dia., 24-1/2″ ht.,
Overall ht. w/chain 99-1/2″, wire 15′.
Nine candelabra base lamps, each 60w max.

FOUR-LIGHT CHANDELIER
P400218-009 Brushed Nickel
21″ dia., 22-1/2″ ht.,
Overall ht. w/chain 97-1/2″, wire 15′.
Four candelabra base lamps, each 60w max.

FOUR-LIGHT FOYER
P500210-009 Brushed Nickel
18″ dia., 28-1/2″ ht.,
Overall ht. w/chain 103-1/2″, wire 15′.
Four candelabra base lamps, each 60w max.

WALL BRACKET
P710074-009 Brushed Nickel
4-1/2″ W., 12″ ht.,
Extends 5″. H/CTR 6″.
One candelabra base lamp, 60w max.

All fixtures shown with EF4T8D927/JA8 LED lamps, not included. See page 824.

Featuring Durrell



Durrell

P400200-031



P500210-031



P400199-031



P400218-031



P350150-031
shown hanging





P350150-031
shown as ceiling mount



P710074-031

SEMI-FLUSH CONVERTIBLE
P350150-031 Matte Black
Hanging and ceiling mount hardware included
16″ dia., 13-1/2″ ht.,
Overall ht. w/chain 47″, wire 10′.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER
P400199-031 Matte Black
26-1/2″ dia., 22-1/2″ ht.,
Overall ht. w/chain 97-1/2″, wire 15′.
Five candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER
P400200-031 Matte Black
32″ dia., 24-1/2″ ht.,
Overall ht. w/chain 99-1/2″, wire 15′.
Nine candelabra base lamps, each 60w max.

FOUR-LIGHT CHANDELIER
P400218-031 Matte Black
21″ dia., 22-1/2″ ht.,
Overall ht. w/chain 97-1/2″, wire 15′.
Four candelabra base lamps, each 60w max.

FOUR-LIGHT FOYER
P500210-031 Matte Black
18″ dia., 28-1/2″ ht.,
Overall ht. w/chain 103-1/2″, wire 15′.
Four candelabra base lamps, each 60w max.

WALL BRACKET
P710074-031 Matte Black
4-1/2″ W., 12″ ht.,
Extends 5″. H/CTR 6″.
One candelabra base lamp, 60w max.

All fixtures shown with EF4T8D927/JA8 LED lamps, not included. See page 824.

Saluda


FINISHES
- Brushed Nickel - 009
- Antique Bronze - 020

ALSO IN
Bath

PAIR WITH
Litchfield
Range
Piedmont

P400136-009

The Saluda Collection features a gently curving frame paired with clear glass shades. Each shade is accented with a banded ring to carry through the theme of finely crafted metal fittings. The design lends itself to Farmhouse, Coastal and Transitional spaces.



Saluda

P400137-009



P400134-009



P400136-009



P350109-009



P400135-009



P500137-009





P300178-009

WALL BRACKET
P300178-009 Brushed Nickel
5-3/4″ W., 9-1/2″ ht.,
Extends 7-3/4″. H/CTR 4-1/2″.
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE
P350109-009 Brushed Nickel
Hanging and ceiling mount
hardware included.
18″ dia., 12-7/8″ ht.,
Overall ht. w/stem 63″, wire 10′.
Three medium base lamps,
each 60w max.

THREE-LIGHT CHANDELIER
P400134-009 Brushed Nickel
24″ dia., 20-1/8″ ht.,
Overall ht. w/chain 95″, wire 15′.
Three medium base lamps,
each 60w max.

THREE-LIGHT LINEAR CHANDELIER
P400135-009 Brushed Nickel
36″ W., 7-1/4″ D., 22″ ht.,
Overall ht. w/chain 96-1/2″, wire 15′.
Three medium base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P400136-009 Brushed Nickel
28″ dia., 19-3/4″ ht.,
Overall ht. w/chain 94″, wire 15′.
Five medium base lamps,
each 60w max.

NINE-LIGHT CHANDELIER
P400137-009 Brushed Nickel
34″ dia., 25″ ht.,
Overall ht. w/chain 148″, wire 15′.
Nine medium base lamps,
each 60w max.

MINI-PENDANT
P500137-009 Brushed Nickel
7-1/4″ dia., 8″ ht.,
Overall ht. w/stem 74″, wire 10′.
One medium base lamp,
60w max.

All fixtures shown with F8.5A19DLED927/JA8 LED lamps, not included. See page 824.

P400136-020



Saluda



P400137-020



P400134-020



P400136-020



P350109-020
shown as ceiling mount



P400135-020



P500137-020



P300178-020

WALL BRACKET
P300178-020 Antique Bronze
5-3/4″ W., 9-1/2″ ht.,
Extends 7-3/4″. H/CTR 4-1/2″.
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE
P350109-020 Antique Bronze
Hanging and ceiling mount
hardware included.
18″ dia., 12-7/8″ ht.,
Overall ht. w/stem 63″, wire 10′.
Three medium base lamps,
each 60w max.

THREE-LIGHT CHANDELIER
P400134-020 Antique Bronze
24″ dia., 20-1/8″ ht.,
Overall ht. w/chain 95″, wire 15′.
Three medium base lamps,
each 60w max.

THREE-LIGHT LINEAR CHANDELIER
P400135-020 Antique Bronze
36″ W., 7-1/4″ D., 22″ ht.,
Overall ht. w/chain 96-1/2″, wire 15′.
Three medium base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P400136-020 Antique Bronze
28″ dia., 19-3/4″ ht.,
Overall ht. w/chain 94″, wire 15′.
Five medium base lamps,
each 60w max.

NINE-LIGHT CHANDELIER
P400137-020 Antique Bronze
34″ dia., 25″ ht.,
Overall ht. w/chain 148″, wire 15′.
Nine medium base lamps,
each 60w max.

MINI-PENDANT
P500137-020 Antique Bronze
7-1/4″ dia., 8″ ht.,
Overall ht. w/stem 74″, wire 10′.
One medium base lamp,
60w max.

All fixtures shown with F8.5A19DLED927/JA8 LED lamps, not included. See page 824.

Whisp

FINISH

● Graphite - 143

PAIR WITH

Drum Shade
Bowman
Passage

P400029-143

An updated traditional family, Whisp adds distinction to interior spaces. Candles with brushed nickel accents complement a gracefully scrolled frame in a cool Graphite finish.



Whisp



P400030-143

SEMI-FLUSH CONVERTIBLE
P350042-143 Graphite
Hanging and ceiling mount hardware included.
15-1/4″ dia., 15″ ht.,
Overall ht. w/chain 54″; wire 10′.
Three candelabra base lamps, each 60w max.

FOUR-LIGHT CHANDELIER
P400029-143 Graphite
21″ dia., 26-3/4″ ht.,
Overall ht. w/chain 101-1/2″; wire 15′.
Four candelabra base lamps, each 60w max.

SIX-LIGHT CHANDELIER
P400030-143 Graphite
28-1/4″ dia., 30″ ht.,
Overall ht. w/chain 105″; wire 15′.
Six candelabra base lamps, each 60w max.

All fixtures shown with P7826-01 vintage lamps, not included. See page 824.



P400029-143



P350042-143
shown hanging



P350042-143
shown as ceiling mount

Foster

FINISH
● Gilded Iron - 071

ALSO IN
Close-to-Ceiling

PAIR WITH
Remix Range

P400153-071

Clean ironwork inspired by antique trains defines the look of Foster. Substance and form are the watchwords of this family, with a simple design of bent metal arms enclosing exposed bulbs held by an ornamental socket cover. Foster's squared lines and mixed metal elements are ideal for Industrial and Rustic settings.



Featuring Foster

P400154-071



P500155-071



Foster

FIVE-LIGHT CHANDELIER
P400153-071 Gilded Iron
25" dia., 14" ht.,
Overall ht. w/stem 80-1/2"; wire 12'.
Five medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER
P400154-071 Gilded Iron
30" dia., 14" ht.,
Overall ht. w/stem 81"; wire 12'.
Six medium base lamps,
each 60w max.

MINI-PENDANT
P500155-071 Gilded Iron
11-1/4" dia., 10-3/4" ht.,
Overall ht. w/stem 77"; wire 10'.
One medium base lamp,
60w max.

All fixtures shown with F7ST19DLED927/JA8 LED lamps, not included. See page 824.

Judson

FINISHES	ALSO IN	PAIR WITH
Antique Bronze - 020	Bath	Saluda
Polished Nickel - 104	Close-to-Ceiling	Swing

P400058-020

The Judson collection features a timeless clear schoolhouse-style globe. Metal fittings add distinction to complete the vintage look. Available in hanging, wall and ceiling styles, Judson provides the perfect complement to farmhouse or coastal-inspired homes.



Judson

P400058-020



THREE-LIGHT CHANDELIER
P400057-020 Antique Bronze
22″ dia., 18-1/4″ ht.,
Overall ht. w/chain 91-1/2″, wire 15′.
Three medium base lamps,
each 75w max.

FIVE-LIGHT CHANDELIER
P400058-020 Antique Bronze
26″ dia., 19″ ht.,
Overall ht. w/chain 92-1/2″, wire 15′.
Five medium base lamps,
each 75w max.

ONE-LIGHT PENDANT
P500061-020 Antique Bronze
11″ dia., 11-1/4″ ht.,
Overall ht. w/stem 78″, wire 10′.
One medium base lamp,
75w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

P400057-020



P500061-020



Featuring Judson
Image: Tresidio Homes



Judson


P400058-104

THREE-LIGHT CHANDELIER
P400057-104 Polished Nickel
22″ dia., 18-1/4″ ht.,
Overall ht. w/chain 91-1/2″, wire 15′.
Three medium base lamps,
each 75w max.

FIVE-LIGHT CHANDELIER
P400058-104 Polished Nickel
26″ dia., 19″ ht.,
Overall ht. w/chain 92-1/2″, wire 15′.
Five medium base lamps,
each 75w max.

ONE-LIGHT PENDANT
P500061-104 Polished Nickel
11″ dia., 11-1/4″ ht.,
Overall ht. w/stem 78″, wire 10′.
One medium base lamp,
75w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.


P400057-104


P500061-104

Swing

FINISH
Antique Bronze - 20

ALSO IN
Close-to-Ceiling
Sconces

PAIR WITH
Archives
Hansford

P5190-20

A fixture with mechanical nature and unique authenticity is what is pleasing about Swing. Four-light hoop fixture with natural brass accents lends itself to a crafted, warehouse form. The six-light linear frame can revive the look over kitchen islands and bar areas, while adding to a vintage electric feel.



Swing



P5191-20



P5180-20



P5190-20



P7159-20



P4742-20

SIX-LIGHT LINEAR CHANDELIER
P4742-20 Antique Bronze
34-1/2″ W., 10-1/2″ D., 4-1/2″ ht.,
Overall ht. w/stem 70-1/2″; wire 15′.
Six medium base lamps,
each 60w max.

ONE-LIGHT PENDANT
P5180-20 Antique Bronze
14″ dia., 17-1/4″ ht.,
Overall ht. w/chain 92-1/2″; wire 12′.
One medium base lamp,
60w max.

FOUR-LIGHT PENDANT
P5190-20 Antique Bronze
20″ dia., 23-1/4″ ht.,
Overall ht. w/chain 98-1/2″; wire 15′.
Four medium base lamps,
each 60w max.

FOUR-LIGHT PENDANT
P5191-20 Antique Bronze
25″ dia., 28-1/4″ ht.,
Overall ht. w/chain 102″; wire 15′.
Four medium base lamps,
each 60w max.

WALL SCONCE
P7159-20 Antique Bronze
Natural brass backplate.
11-3/4″ W., 11-3/4″ ht.,
Extends 4″. H/CTR 5-7/8″.
One medium base lamp,
60w max.

All fixtures shown with vintage lamps, not included. See page 824.

Hansford

FINISHES
- Antique Bronze - 020
- Polished Nickel - 104

ALSO IN
Bath
Close-to-Ceiling

PAIR WITH
Archives
Saluda
Judson

P400147-020

Hansford features a clear, spherical shade paired with vintage style metal fittings. Choose the antique style bronze and brass combinations, or the elegant nickel finish to bring tranquility to your home with Hansford's classic style. Featuring a clean and precise design with generous scale. Hansford lends itself to Farmhouse, Coastal or Industrial interiors.



Hansford



P400147-104



P400147-020

THREE-LIGHT CHANDELIER
P400146-020 Antique Bronze
P400146-104 Polished Nickel
Hanging and ceiling mount hardware included.
21″ dia., 16-7/8″ ht.,
Overall ht. w/stem 85″, wire 12′.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER
P400147-020 Antique Bronze
P400147-104 Polished Nickel
25″ dia., 19-1/8″ ht.,
Overall ht. w/stem 87″, wire 12′.
Five medium base lamps, each 100w max.

All fixtures shown with F8.5A19DLED927/JA8 LED lamps, not included. See page 824.



P400146-104



P400146-020



P400146-020
shown as ceiling mount

Cherish

FINISHES
- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN
Sconces

PAIR WITH
Joy
Leap

P4618-20

Traditional linear island light and elegant chandelier options are modernized with a summer linen shade. The Antique Bronze fixtures include both bronze and antique brass candle cover options allowing homeowners to complement mixed metal styling within a room.



Cherish



P7172-20
shown with Antique Brass candle covers



P7172-20
shown with Antique Bronze candle covers



P7172-09

P4618-20



P4618-09



SIX-LIGHT CHANDELIER
P4618-09 Brushed Nickel
P4618-20 Antique Bronze
24″ dia., 22-3/8″ ht.,
Overall ht. w/chain 97″; wire 15′.
Six candelabra base lamps,
each 60w max.

TWO-LIGHT WALL SCONCE
P7172-09 Brushed Nickel
P7172-20 Antique Bronze
12″ W., 9″ ht.
Extends 6-1/2″. H/CTR 4-3/4″.
Two candelabra base lamps,
each 60w max.

Kempsey

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

PAIR WITH

Tally
Archie
Alexa

P350110-020

For Farmhouse styling with a twist, look no further than Kempsey, whose inside-out design showcases stylish charm. A structural metal frame on the outside captures the textured linen shade within its arms, so that the structure becomes part of the design. The shade has an inner transparent backing, so its texture is visible from inside out. A wall bracket featuring a multi-directional arm holding the shade completes the collection.



Kempsey



P350110-020
shown hanging



P350110-020
shown as ceiling mount



P500138-020

SEMI-FLUSH CONVERTIBLE
P350110-020 Antique Bronze
Hanging and ceiling mount hardware included
21-3/4" dia., 11" ht.,
Overall ht. w/stem 76"; wire 10'.
Three medium base lamps, each 60w max.

ONE-LIGHT PENDANT
P500138-020 Antique Bronze
11-3/4" dia., 9" ht.,
Overall ht. w/stem 76"; wire 10'.
One medium base lamp, 75w max.

THREE-LIGHT PENDANT
P500139-020 Antique Bronze
17-3/4" dia., 21-3/8" ht.,
Overall ht. w/stem 87-1/2"; wire 10'.
Three medium base lamps, each 60w max.

ONE-LIGHT ADJUSTABLE WALL BRACKET
P710045-020 Antique Bronze
12" dia., 19-3/4" ht.,
Extends 23-5/8".
One medium base lamp, 75w max.
On/off rotary switch on backplate.



P500139-020



P710045-020

P350110-009

Classic Transitional

Stylish Charm



Warm and Inviting

Kempsey



P350110-009
shown hanging



P350110-009
shown as ceiling mount



P500139-009



P500138-009



P710045-009

SEMI-FLUSH CONVERTIBLE
P350110-009 Brushed Nickel
Hanging and ceiling mount hardware included
21-3/4" dia., 11" ht.,
Overall ht. w/stem 76"; wire 10'.
Three medium base lamps, each 60w max.

ONE-LIGHT PENDANT
P500138-009 Brushed Nickel
11-3/4" dia., 9" ht.,
Overall ht. w/stem 76"; wire 10'.
One medium base lamp, 75w max.

THREE-LIGHT PENDANT
P500139-009 Brushed Nickel
17-3/4" dia., 21-3/8" ht.,
Overall ht. w/stem 87-1/2"; wire 10'.
Three medium base lamps, each 60w max.

ONE-LIGHT ADJUSTABLE WALL BRACKET
P710045-009 Brushed Nickel
12" dia., 19-3/4" ht.,
Extends 23-5/8".
One medium base lamp, 75w max.
On/off rotary switch on backplate.

Cirrine

FINISH
Antique Bronze - 20

ALSO IN
Sconces

PAIR WITH
Marque
Swing

P4700-20

Cirrine appeals to the creative spirit within all of us. Hand formed arching elements are highlighted by a painted finish that feathers from a rich bronze tone to a vintage gold accent. Etched white glass complements the artistic frame.



Cirrine


P4700-20


P5082-20


P4699-20


P7149-20

THREE-LIGHT CHANDELIER
P4699-20 Antique Bronze
18″ dia., 13-1/2″ ht.,
Overall ht. w/stem 79-1/2″; wire 15′.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4700-20 Antique Bronze
24″ dia., 14-1/4″ ht.,
Overall ht. w/stem 80-1/2″; wire 15′.
Five medium base lamps,
each 100w max.

MINI-PENDANT
P5082-20 Antique Bronze
6″ dia., 9-3/4″ ht.,
Overall ht. w/stem 76″; wire 10′.
One medium base lamp,
100w max.

WALL SCONCE
P7149-20 Antique Bronze
8″ W., 8″ ht.,
Extends 4″. H/CTR 4″.
One medium base lamp,
75w max.

ADA

Mingle

FINISHES
- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN
Close-to-Ceiling

PAIR WITH
Equinox
Bravo

P5156-20

Mingle with your favorite home décor accents to find a place for this fun, flirty fixture. The Antique Bronze finish features a natural parchment glass to complement the warmer tone. Brushed Nickel finish includes etched parchment glass shades.



Mingle

P5156-09



P5038-09



MINI-PENDANT
P5038-09 Brushed Nickel
P5038-20 Antique Bronze
6″ dia., 6-3/8″ ht.,
Overall ht. w/chain 78-1/2″; wire 10′.
One medium base lamp,
100w max.

FOUR-LIGHT PENDANT
P5156-09 Brushed Nickel
P5156-20 Antique Bronze
21″ dia., 15-1/4″ ht.,
Overall ht. w/chain 81-1/4″; wire 15′.
Four medium base lamps,
each 100w max.

P5156-20



P5038-20



Bonn

FINISHES

- Matte Black - 031
- Galvanized - 141

PAIR WITH

Latrobe
Hemsworth
Austelle

P500225-031

The Bonn Collection personifies a stylishly simplistic industrial vibe sure to create an unforgettable lighting experience. Smooth, thin bars curve and cross to form simple, open-caged structures that harbor light bases within appearing to daintily drip from the top of the light fixtures.

Industrial Style



Architectural Fixture

Black Finish

Bonn

P500223-031



P500223-141



ONE-LIGHT PENDANT
P500223-031 Matte Black
P500223-141 Galvanized
7″ dia., 15-1/8″ ht.,
Overall ht. w/ stem 81″, wire 10′.
One medium base lamp,
60w max.

P500224-031



P500224-141



FOUR-LIGHT PENDANT
P500224-031 Matte Black
P500224-141 Galvanized
14-1/2″ dia., 23″ ht.,
Overall ht. w/ stem 89″, wire 15′.
Four medium base lamps,
each 60w max.

P500225-031



P500225-141



SIX-LIGHT PENDANT
P500225-031 Matte Black
P500225-141 Galvanized
22″ dia., 23-1/8″ ht.,
Overall ht. w/stem 90″, wire 15′.
Six medium base lamps,
each 60w max.

All fixtures shown with F4T10DLED927/JA8 LED lamps, not included. See page 824.

Cirro

FINISHES

- Brushed Nickel - 009
- Graphite - 143


PAIR WITH

Glayse
Carbon

P500140-009

Cirro displays casual elegance that is found in simplicity of form. Nine individual lights suspended from a single point provide the perfect platform for nostalgic oversize globe or vintage light bulbs. The design is a versatile option to provide a dramatic statement to a variety of interior styles ranging from Modern to Casual.

Dramatic and Versatile




Nine Lights


Casual Elegance

Featuring Cirro and Litchfield

P500140-009



P500140-143



Cirro

NINE-LIGHT PENDANT
P500140-009 Brushed Nickel
P500140-143 Graphite
6-1/4" dia., 30-1/4" ht.,
Overall ht. w/stem 91-1/2", wire 10'.
Nine medium base lamps,
each 60w max.

All fixtures shown with G30 Globe lamps, not included.

Diameter/height dimensions without lamps.

Carisa

FINISHES
- Brushed Nickel - 009
- Vintage Gold - 078

ALSO IN
Bath
Close-To-Ceiling

PAIR WITH
Cahill
Draper
Globe LED

P400060-009

Inspired by the revival of Mid-Century fashions, the Carisa collection brings home this classic style. A metallic finish supports glossy white opal glass globes to create a timeless modern design.

Opal Glass Globes

Mid-Century Style



Brushed Nickel

Carisa

P400061-009



WALL BRACKET
P300084-009 Brushed Nickel
6-1/2″ W., 10″ ht.,
Extends 8-1/2″. H/CTR 4-5/8″.
One medium base lamp,
75w max.

THREE-LIGHT CHANDELIER
P400059-009 Brushed Nickel
21/1/2″ dia., 17-1/2″ ht.,
Overall ht. w/stem 83-1/2″, wire 15′.
Three medium base lamps,
each 75w max.

FIVE-LIGHT CHANDELIER
P400060-009 Brushed Nickel
25-1/2″ dia., 20-3/4″ ht.,
Overall ht. w/stem 86-1/2″, wire 15′.
Five medium base lamps,
each 75w max.

NINE-LIGHT CHANDELIER
P400061-009 Brushed Nickel
31-1/2″ dia., 36-1/2″ ht.,
Overall ht. w/stem 102-1/2″, wire 15′.
Nine medium base lamps,
each 75w max.

P400060-009



P400059-009





P300084-009

P400060-078

Opal Glass Globes

Modern Design



Vintage Gold

Carisa



P400061-078

WALL BRACKET
P300084-078 Vintage Gold
6-1/2″ W., 10″ ht.,
Extends 8-1/2″. H/CTR 4-5/8″.
One medium base lamp,
75w max.

THREE-LIGHT CHANDELIER
P400059-078 Vintage Gold
21/1/2″ dia., 17-1/2″ ht.,
Overall ht. w/stem 83-1/2″, wire 15′.
Three medium base lamps,
each 75w max.

FIVE-LIGHT CHANDELIER
P400060-078 Vintage Gold
25-1/2″ dia., 20-3/4″ ht.,
Overall ht. w/stem 86-1/2″, wire 15′.
Five medium base lamps,
each 75w max.

NINE-LIGHT CHANDELIER
P400061-078 Vintage Gold
31-1/2″ dia., 36-1/2″ ht.,
Overall ht. w/stem 102-1/2″, wire 15′.
Nine medium base lamps,
each 75w max.



P400060-078



P400059-078



P300084-078

Zag

FINISHES


- Brushed Nickel - 009
- Vintage Gold - 078

PAIR WITH

Clarion
Atwell
Carisa

P400149-078

Calming organic forms are the focal point in Zag's branching design. Inspired by European styling, these chandelier options are ideal for Modern and Transitional interiors. The streamlined minimalist frame is the perfect showcase for globe or vintage style light bulbs.



Zag



P400149-078



P400148-078

THREE-LIGHT CHANDELIER
P400148-009 Brushed Nickel
P400148-078 Vantage Gold
Hanging and ceiling mount hardware included.
10-1/4" dia., 11" ht.,
Overall ht. w/stem 68", wire 15'.
Three medium base lamps, each 60w max.

FIVE-LIGHT CHANDELIER
P400149-009 Brushed Nickel
P400149-078 Vintage Gold
18" dia., 21-5/8" ht.,
Overall ht. w/stem 78", wire 15'.
Five medium base lamps, each 60w max.

All fixtures shown with G30 Globe lamps, not included.

Diameter/height dimensions are without lamps.



P400149-009



P400148-009
shown hanging



P400148-009
shown as ceiling mount

Domain

FINISH
● Black - 031

ALSO IN
Bath

PAIR WITH
Spatial
Finn

P400035-031

A sensible, yet sophisticated, lighting collection rooted in updated classical modern styling. Suitable for Urban Industrial, Modern and Mid-Century Modern interiors, Domain features a Matte Black finish. A double ring accent and squared off socket holder complement over scale etched glass shades.



Domain

P400036-031



THREE-LIGHT CHANDELIER
P400034-031 Black
22-3/8″ dia., 15-3/8″ ht.,
Overall ht. w/stem 81-1/2″, wire 15′.
Three medium base lamps,
each 100w max.

P400035-031



FOUR-LIGHT CHANDELIER
P400035-031 Black
29″ dia., 19″ ht.,
Overall ht. w/stem 85″, wire 15′.
Four medium base lamps,
each 100w max.

P400034-031



SIX-LIGHT CHANDELIER
P400036-031 Black
32″ dia., 24″ ht.,
Overall ht. w/stem 90″, wire 15′.
Six medium base lamps,
each 100w max.

Tobin

FINISH

Brushed Nickel - 009
Matte Black - 031

ALSO IN

Bath
Sconces

PAIR WITH

Ratio
Haven
Chadwick

WALL BRACKET
P300222-009 Brushed Nickel
5" W., 15-1/2" ht.,
Extends 5-7/8". H/CTR 11".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE
P350137-009 Brushed Nickel
Hanging and ceiling mount
hardware included.
12-1/4" dia., 10-1/8" ht.,
Overall ht. w/chain 48-1/2"; wire 10'.
Two medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P400181-009 Brushed Nickel
22-3/8" dia., 9-7/8" ht.,
Overall ht. w/stem 70"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P400182-009 Brushed Nickel
27-5/8" dia., 9-7/8" ht.,
Overall ht. w/stem 70"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P400183-009 Brushed Nickel
32" dia., 18-5/8" ht.,
Overall ht. w/stem 78-1/2"; wire 15'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT
P500180-009 Brushed Nickel
5-3/4" dia., 21-5/8" ht.,
Overall ht. w/stem 88"; wire 10'.
One medium base lamp,
100w max.



P350137-009
shown hanging



P400183-009



P500180-009



P400182-009



P300222-009



P400181-009

Tobin



P400183-031



P350137-031
shown hanging



P400182-031



P500180-031



P400181-031



P300222-031

WALL BRACKET
P300222-031 Matte Black
5" W., 15-1/2" ht.,
Extends 5-7/8". H/CTR 11".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE
P350137-031 Matte Black
Hanging and ceiling mount
hardware included.
12-1/4" dia., 10-1/8" ht.,
Overall ht. w/chain 48-1/2"; wire 10'.
Two medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P400181-031 Matte Black
22-3/8" dia., 9-7/8" ht.,
Overall ht. w/stem 70"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P400182-031 Matte Black
27-5/8" dia., 9-7/8" ht.,
Overall ht. w/stem 70"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P400183-031 Matte Black
32" dia., 18-5/8" ht.,
Overall ht. w/stem 78-1/2"; wire 15'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT
P500180-031 Matte Black
5-3/4" dia., 21-5/8" ht.,
Overall ht. w/stem 88"; wire 10'.
One medium base lamp,
100w max.

Leap

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ALSO IN

Bath
Close-to-Ceiling

PAIR WITH

Wisten
Joy

SEMI-FLUSH CONVERTIBLE
P350060-009 Brushed Nickel
Hanging and ceiling mount hardware included.
14" W., 8-7/8" ht.,
Overall ht. w/stem 47"; wire 10'.
Two medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER
P400042-009 Brushed Nickel
21" dia., 27-5/8" ht.,
Overall ht. w/chain 102"; wire 15'.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER
P400043-009 Brushed Nickel
25" dia., 30" ht.,
Overall ht. w/chain 105"; wire 15'.
Five medium base lamps, each 100w max.

NINE-LIGHT CHANDELIER
P400044-009 Brushed Nickel
26-3/8" dia., 37" ht.,
Overall ht. w/chain 160"; wire 15'.
Nine medium base lamps, each 100w max.

MINI-PENDANT
P500029-009 Brushed Nickel
5" dia., 6-1/2" ht.,
Overall ht. w/stem 72-1/2"; wire 10'.
One medium base lamp, 100w max.

THREE-LIGHT PENDANT
P500030-009 Brushed Nickel
18" dia., 21" ht.,
Overall ht. w/chain 87"; wire 10'.
Three medium base lamps, each 100w max.


P400043-009


P400044-009


P400042-009


P500030-009


P500029-009


P350060-009
shown hanging

Leap

P400044-020



P400043-020



P500030-020



P400042-020



P350060-020
shown hanging



P500029-020



SEMI-FLUSH CONVERTIBLE
P350060-020 Antique Bronze
Hanging and ceiling mount hardware included.
14″ W., 8-7/8″ ht.,
Overall ht. w/stem 47″; wire 10′.
Two medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER
P400042-020 Antique Bronze
21″ dia., 27-5/8″ ht.,
Overall ht. w/chain 102″; wire 15′.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER
P400043-020 Antique Bronze
25″ dia., 30″ ht.,
Overall ht. w/chain 105″; wire 15′.
Five medium base lamps, each 100w max.

NINE-LIGHT CHANDELIER
P400044-020 Antique Bronze
26-3/8″ dia., 37″ ht.,
Overall ht. w/chain 160″; wire 15′.
Nine medium base lamps, each 100w max.

MINI-PENDANT
P500029-020 Antique Bronze
5″ dia., 6-1/2″ ht.,
Overall ht. w/stem 72-1/2″; wire 10′.
One medium base lamp, 100w max.

THREE-LIGHT PENDANT
P500030-020 Antique Bronze
18″ dia., 21″ ht.,
Overall ht. w/chain 87″; wire 10′.
Three medium base lamps, each 100w max.

Replay

FINISHES

Polished Nickel - 104
Black - 31

ALSO IN

Bath
Close-to-Ceiling

PAIR WITH

Alexa
Tobin
Markor

WALL BRACKET
P2131-104 Polished Nickel
5" W., 9-3/4" ht.,
Extends 5-7/8". H/CTR 7-1/4".
One medium base lamp, 100w max.

SEMI-FLUSH CONVERTIBLE
P3424-104 Polished Nickel
Hanging and ceiling mount
hardware included.
14-3/4" dia., 10" ht.,
Overall ht. w/chain 50"; wire 10'.
Two medium base lamps,
each 100w max.

THREE-LIGHT PENDANT
P3450-104 Polished Nickel
16-5/8" dia., 19" ht.,
Overall ht. w/chain 92-1/2"; wire 15'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P4318-104 Polished Nickel
17" dia., 19-5/8" ht.,
Overall ht. w/chain 95"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4319-104 Polished Nickel
21" dia., 19-5/8" ht.,
Overall ht. w/chain 95"; wire 15'.
Three medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4726-104 Polished Nickel
25-1/2" dia., 28" ht.,
Overall ht. w/chain 104"; wire 15'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT
P5170-104 Polished Nickel
4" dia., 6" ht.,
Overall ht. w/stem 72"; wire 10'.
One medium base lamp, 100w max.

FOUR-LIGHT FOYER
P500206-104 Polished Nickel
18" dia., 31-3/4" ht.,
Overall ht. w/chain 106"; wire 12'.
Four medium base lamps,
each 100w max.

P3450-104



P3424-104
shown hanging



P4319-104
shown with glass facing up



P5170-104





P2131-104

P4726-104



P500206-104



P4318-104
shown with glass facing down



P4726-31



P500206-031



P4318-31
shown with glass facing up



P3450-31



P3424-31
shown hanging



P4319-31
shown with glass facing up



P5170-31





P2131-31

Replay

WALL BRACKET
P2131-31 Black
5″ W., 9-3/4″ ht.,
Extends 5-7/8″. H/CTR 7-1/4″.
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE
P3424-31 Black
Hanging and ceiling mount hardware included.
14-3/4″ dia., 10″ ht.,
Overall ht. w/chain 50″; wire 10′.
Two medium base lamps,
each 100w max.

THREE-LIGHT PENDANT
P3450-31 Black
16-5/8″ dia., 19″ ht.,
Overall ht. w/stem 92-1/2″; wire 15′.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P4318-31 Black
17″ dia., 19-5/8″ ht.,
Overall ht. w/stem 95″; wire 15′.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4319-31 Black
21″ dia., 19-5/8″ ht.,
Overall ht. w/chain 95″; wire 15′.
Three medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4726-31 Black
25-1/2″ dia., 28″ ht.,
Overall ht. w/chain 104″; wire 15′.
Nine medium base lamps,
each 100w max.

MINI-PENDANT
P5170-31 Black
4″ dia., 6″ ht. ,
Overall ht. w/stem 72″; wire 10′.
One medium base lamp,
100w max.

FOUR-LIGHT FOYER
P500206-031 Black
18" dia., 31-3/4" ht.,
Overall ht. w/chain 106"; wire 12′.
Four medium base lamps,
each 100w max.

Replay

FINISH

● Brushed Nickel - 09

WALL BRACKET
P2131-09 Brushed Nickel
5" W., 9-3/4" ht.,
Extends 5-7/8". H/CTR 7-1/4".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE
P3424-09 Brushed Nickel
Hanging and ceiling mount
hardware included.
14-3/4" dia., 10" ht.,
Overall ht. w/chain 49-1/2", wire 10'.
Two medium base lamps,
each 100w max.

THREE-LIGHT PENDANT
P3450-09 Brushed Nickel
16-5/8" dia., 19" ht.,
Overall ht. w/chain 92-1/2", wire 15'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P4318-09 Brushed Nickel
17" dia., 20-1/8" ht.,
Overall ht. w/chain 95", wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4319-09 Brushed Nickel
21" dia., 19-5/8" ht.,
Overall ht. w/chain 95", wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4726-09 Brushed Nickel
25-1/2" dia., 28" ht.,
Overall ht. w/chain 104", wire 15'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT
P5170-09 Brushed Nickel
4" dia., 6" ht.,
Overall Ht. W/Stem 72", wire 10'.
One medium base lamp,
100w max.

FOUR-LIGHT FOYER
P500206-009 Brushed Nickel
18" dia., 31-3/4" ht.,
Overall ht. w/chain 106"; wire 12'.
Four medium base lamps,
each 100w max.

P3450-09





P3424-09
shown as ceiling mount

P4726-09



P500206-009



P4319-09
shown with glass facing up



P5170-09





P2131-09

P4318-09
shown with glass facing down



Orbitz


P4663-09


P5114-09


P3030-09


P4663-20


P5114-20


P3030-20


P3954-09


P4659-20


P3954-20


P4659-20

FINISH

Brushed Nickel - 09
Antique Bronze - 20

ALSO IN

Bath

PAIR WITH

Topsail
Tally
Equinox

WALL BRACKET
P3030-09 Brushed Nickel
P3030-20 Antique Bronze
5-1/2" W., 7-1/4" ht.,
Extends 6". H/CTR 5".
One medium base lamp,
100w max.

THREE-LIGHT CHANDELIER
P3954-09 Brushed Nickel
P3954-20 Antique Bronze
Hanging and ceiling mount
hardware included.
17" dia., 12 1/4" ht.,
Overall ht. w/stem 79"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4659-09 Brushed Nickel
P4659-20 Antique Bronze
23-1/4" dia., 18-1/2" ht.,
Overall ht. w/chain 85"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4663-09 Brushed Nickel
P4663-20 Antique Bronze
27" dia., 23-3/4" ht.,
Overall ht. w/stem 90"; wire 15'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT
P5114-09 Brushed Nickel
P5114-20 Antique Bronze
4" dia., 7-3/4" ht.,
Overall ht. w/chain or stem 78"; wire 10'.
One medium base lamp,
100w max.

Alexa

FINISH

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

Bath
Close-to-Ceiling

PAIR WITH

Haven
Kempsey
Mast

WALL BRACKET
P2959-09 Brushed Nickel
One-light. Mounts up or down.
4-1/2" W., 9-3/8" ht.,
Extends 6-1/8".
One medium base lamp, 100w max.

THREE-LIGHT PENDANT
P3846-09 Brushed Nickel
18" dia., 24-3/8" ht.,
Overall ht. w/chain 99"; wire 15'.
Three medium base lamps,
each 100w max.

FOUR-LIGHT FOYER
P3977-09 Brushed Nickel
18" W., 44-3/8" ht.,
Overall ht. w/chain 119"; wire 15'.
Four medium base lamps,
each 75w max.

THREE-LIGHT CHANDELIER
P4458-09 Brushed Nickel
17" dia., 19-5/8" ht.,
Overall ht. w/chain 95"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4459-09 Brushed Nickel
20" dia., 19-3/4" ht.,
Overall ht. w/chain 95"; wire 15'.
Five medium base lamps,
each 100w max.

FOUR-LIGHT LINEAR CHANDELIER
P4619-09 Brushed Nickel
34" W., 4-1/2" D., 20" ht.,
Overall ht. w/chain 93"; wire 15'.
Four medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4626-09 Brushed Nickel
28" dia., 28-1/2" ht. ,
Overall ht. w/chain 102"; wire 15'.
Nine medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER
P4758-09 Brushed Nickel
25" dia., 19-3/4" ht.,
Overall ht. w/chain 95"; wire 15'.
Six medium base lamps,
each 100w max.

MINI-PENDANT
P5147-09 Brushed Nickel
5-1/8" dia., 7-3/4" ht.,
Overall ht. w/stem 64"; wire 10'.
One medium base lamp, 100w max.

P3977-09



P4626-09



P4458-09



P4758-09



P4459-09



P5147-09



P3846-09



P4619-09





P2959-09

P4626-20



P3977-20



P4758-20



P4458-20



P3846-20



P5147-20



P4459-20



P4619-20



P2959-20



Alexa

WALL BRACKET
P2959-20 Antique Bronze
One-light. Mounts up or down.
4-1/2″ W., 9-3/8″ ht.
Extends 6-1/8″.
One medium base lamp,
100w max.

THREE-LIGHT PENDANT
P3846-20 Antique Bronze
18″ dia., 24-3/8″ ht.,
Overall ht. w/chain 99″; wire 15′.
Three medium base lamps,
each 100w max.

FOUR-LIGHT FOYER
P3977-20 Antique Bronze
18″ W., 44-3/8″ ht.,
Overall ht. w/chain 119″; wire 15′.
Four medium base lamps,
each 75w max.

THREE-LIGHT CHANDELIER
P4458-20 Antique Bronze
17″ dia., 19-5/8″ ht.,
Overall ht. w/chain 95″; wire 15′.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4459-20 Antique Bronze
20″ dia., 19-3/4″ ht.,
Overall ht. w/chain 95″; wire 15′.
Five medium base lamps,
each 100w max.

FOUR-LIGHT LINEAR CHANDELIER
P4619-20 Antique Bronze
34″ W., 4-1/2″ D., 20″ ht.,
Overall ht. w/chain 93″; wire 15′.
Four medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4626-20 Antique Bronze
28″ dia., 28-1/2″ ht.,
Overall ht. w/chain 102″; wire 15′.
Nine medium base lamps,
each 100w max.

SIX-LIGHT CHANDELIER
P4758-20 Antique Bronze
25″ dia., 19-3/4″ ht.,
Overall ht. w/chain 95″; wire 15′.
Six medium base lamps,
each 100w max.

MINI-PENDANT
P5147-20 Antique Bronze
5-1/8″ dia., 7-3/4″ ht.,
Overall ht. w/stem 64″; wire 10′.
One medium base lamp,
100w max.

Bravo

FINISH

- Brushed Nickel - 09
- Antique Bronze - 20W

PAIR WITH

Joy
Mingle

WALL BRACKET
P2004-09 Brushed Nickel
7-1/4" W., 9" ht.,
Extends 8-3/4". H/CTR 4-1/2".
One medium base lamp, 100w max.

THREE-LIGHT FOYER
P3821-09 Brushed Nickel
18" dia., 21-1/2" ht.,
Overall ht. w/chain 96"; wire 12'.
Three candelabra base lamps,
each 60w max.

THREE-LIGHT PENDANT
P3912-09 Brushed Nickel
21" dia., 23-1/2" ht.,
Overall ht. w/chain 98"; wire 12'.
Three medium base lamps,
each 100w max.

THREE-LIGHT FOYER
P3969-09 Brushed Nickel
20" dia., 30-3/8" ht.,
Overall ht. w/chain 105"; wire 12'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P4621-09 Brushed Nickel
23" dia., 20-1/8" ht.,
Overall ht. w/chain 95"; wire 12'.
Three medium base lamps,
each 100w max.

FOUR-LIGHT CHANDELIER
P4622-09 Brushed Nickel
24" dia., 21" ht.,
Overall ht. w/chain 96"; wire 12'.
Four medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4623-09 Brushed Nickel
27" dia., 23" ht.,
Overall ht. w/chain 97"; wire 12'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4625-09 Brushed Nickel
32" dia., 31" ht.,
Overall ht. w/chain 106"; wire 15'.
Nine medium base lamps,
each 100w max.

TWELVE-LIGHT CHANDELIER
P4687-09 Brushed Nickel
38" W., 44" ht.,
Overall ht. w/chain 119"; wire 15'.
Twelve medium base lamps,
each 100w max.

MINI-PENDANT
P5300-09 Brushed Nickel
7-1/4" dia., 6-1/2" ht.,
Overall ht. w/chain or stem 94"; wire 10'.
One medium base lamp, 100w max.

P4622-09



P4687-09



P4623-09



P4621-09



P4625-09



P3821-09



P3912-09



P3969-09



P5300-09



P2004-09




P4687-20W


P4622-20W


P4623-20W


P4625-20W


P4621-20W


P3821-20W


P3969-20W


P3912-20W


P5300-20W


P2004-20W

Bravo

WALL BRACKET
P2004-20W Antique Bronze
7-1/4" W., 9" ht.,
Extends 8-3/4". H/CTR 4-1/2".
One medium base lamp, 100w max.

THREE-LIGHT FOYER
P3821-20W Antique Bronze
18" dia., 21-1/2" ht.,
Overall ht. w/chain 96"; wire 12'.
Three candelabra base lamps,
each 60w max.

THREE-LIGHT PENDANT
P3912-20W Antique Bronze
21" dia., 23-1/2" ht.,
Overall ht. w/chain 98"; wire 12'.
Three medium base lamps,
each 100w max.

THREE-LIGHT FOYER
P3969-20W Antique Bronze
20" dia., 30-3/8" ht.,
Overall ht. w/chain 105-1/2"; wire 12'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P4621-20W Antique Bronze
23" dia., 20-1/8" ht.,
Overall ht. w/chain 95"; wire 12'.
Three medium base lamps,
each 100w max.

FOUR-LIGHT CHANDELIER
P4622-20W Antique Bronze
24" dia., 21" ht.,
Overall ht. w/chain 96"; wire 12'.
Four medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4623-20W Antique Bronze
27" dia., 23" ht.,
Overall ht. w/chain 97"; wire 12'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4625-20W Antique Bronze
32" dia., 31" ht.,
Overall ht. w/chain 106"; wire 15'.
Nine medium base lamps,
each 100w max.

TWELVE-LIGHT CHANDELIER
P4687-20W Antique Bronze
38" dia., 44" ht.,
Overall ht. w/chain 119"; wire 15'.
Twelve medium base lamps,
each 75w max.

MINI-PENDANT
P5300-20W Antique Bronze
7-1/4" dia., 6-1/2" ht.,
Overall ht. w/chain or stem 94"; wire 10'.
One medium base lamp, 100w max.

Topsail

FINISH

Polished Chrome - 015
Antique Bronze - 020

ALSO IN

Bath
Close-to-Ceiling

PAIR WITH

Bay Court
Archie
Medal

WALL BRACKET
P300057-015 Polished Chrome
5-1/4" W., 7" ht.,
Extends 7-1/4". H/CTR 3-1/8".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE
P350063-015 Polished Chrome
Hanging and ceiling mount
hardware included.
12-7/8" dia., 12-3/8" ht.,
Overall ht. w/chain 52-1/2, wire 10'.
Three medium base lamps,
each 75w max.

THREE-LIGHT CHANDELIER
P400052-015 Polished Chrome
21" dia., 19-1/8" ht.,
Overall ht. w/chain 93-1/2", wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P400053-015 Polished Chrome
25" dia., 18-1/4" ht.,
Overall ht. w/chain 93-1/2", wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P400054-015 Polished Chrome
30" dia., 25-3/8" ht.,
Overall ht. w/chain 147", wire 15'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT
P500050-015 Polished Chrome
5-1/4" dia., 13-1/8" ht.,
Overall ht. w/stem 79, wire 10'.
One medium base lamp,
100w max.

THREE-LIGHT PENDANT
P500054-015 Polished Chrome
18-3/4" dia., 21" ht.,
Overall ht. w/chain 96", wire 10'.
Three medium base lamps,
each 100w max.

P500054-015



P400054-015



P400052-015



P400053-015



P350063-015
shown hanging



P500050-015





P300057-015

Topsail

P400054-020



P500054-020



P400053-020



P400052-020



P500050-020





P300057-020



P350063-020
shown as ceiling mount

WALL BRACKET
P300057-020 Antique Bronze
5-1/4" W., 7" ht.,
Extends 7-1/4". H/CTR 3-1/8".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE
P350063-020 Antique Bronze
Hanging and ceiling mount
hardware included.
12-7/8" dia., 12-3/8" ht.,
Overall ht. w/chain 52-1/2, wire 10'.
Three medium base lamps,
each 75w max.

THREE-LIGHT CHANDELIER
P400052-020 Antique Bronze
21" dia., 19-1/8" ht.,
Overall ht. w/chain 93-1/2", wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P400053-020 Antique Bronze
25" dia., 18-1/4" ht.,
Overall ht. w/chain 93-1/2", wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P400054-020 Antique Bronze
30" dia., 25-3/8" ht.,
Overall ht. w/chain 147", wire 15'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT
P500050-020 Antique Bronze
5-1/4" dia., 13-1/8" ht.,
Overall ht. w/stem 79, wire 10'.
One medium base lamp,
100w max.

THREE-LIGHT PENDANT
P500054-020 Antique Bronze
18-3/4" dia., 21" ht.,
Overall ht. w/chain 96", wire 10'.
Three medium base lamps,
each 100w max.

Wisten

FINISH
- Brushed Nickel - 09
- Antique Bronze - 20

PAIR WITH
Leap
Chadwick
Haven

ALSO IN
Bath
Close-to-Ceiling

WALL BRACKET
P2794-09 Brushed Nickel
4-1/2" W., 8-1/4" ht.,
Extends 6-1/4". H/CTR 4".
One medium base lamp, 100w max.

THREE-LIGHT FOYER
P3509-09 Brushed Nickel
12" dia., 25-7/8" ht.,
Overall ht. w/chain 101"; wire 15'.
Three candelabra base lamps,
each 60w max.

THREE-LIGHT PENDANT
P3757-09 Brushed Nickel
18-1/4" dia., 25" ht.,
Overall ht. w/chain 100"; wire 15'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P4434-09 Brushed Nickel
17" dia., 20-1/2" ht.,
Overall ht. w/chain 96"; wire 15'.
Three medium base lamps,
each 100w max.

FOUR-LIGHT LINEAR CHANDELIER
P4435-09 Brushed Nickel
35" W., 12-1/2" D., 29" ht.,
Overall ht. w/stem 79"; wire 15'.
Four candelabra base lamps,
each 60w max

FIVE-LIGHT CHANDELIER
P4436-09 Brushed Nickel
22" dia., 26-3/8" ht.,
Overall ht. w/chain 101"; wire 15'.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER
P4439-09 Brushed Nickel
27" dia., 33-3/8" ht.,
Overall ht. w/chain 156"; wire 15'.
Nine candelabra base lamps,
each 60w max.

MINI-PENDANT
P5108-09 Brushed Nickel
4" dia., 6-3/4" ht.,
Overall ht. w/stem 64"; wire 10'.
One medium base lamp, 100w max.

ONE-LIGHT PENDANT
P5112-09 Brushed Nickel
17" dia., 21-1/8" ht.,
Overall ht. w/chain 97"; wire 15'.
One medium base lamp, 100w max.

MINI-PENDANT
P5167-09 Brushed Nickel
3-3/4" dia., 9-3/4" ht. ,
Overall ht. w/stem 67"; wire 10'.
One medium base lamp, 100w max.


P3509-09


P4439-09


P3757-09


P5167-09


P4436-09


P5112-09


P5108-09


P4435-09


P4434-09


P2794-09


P4439-20


P4436-20


P4435-20


P3509-20


P5167-20


P3757-20


P5108-20


P5112-20


P2794-20


P4434-20

Wisten

WALL BRACKET
P2794-20 Antique Bronze
4-1/2″ W., 8-1/4″ ht.,
Extends 6-1/4″. H/CTR 4″.
One medium base lamp, 100w max.

THREE-LIGHT FOYER
P3509-20 Antique Bronze
12″ dia., 25-7/8″ ht.,
Overall ht. w/chain 101″; wire 15′.
Three candelabra base lamps,
each 60w max.

THREE-LIGHT PENDANT
P3757-20 Antique Bronze
18-1/4″ dia., 25″ ht.,
Overall ht. w/chain 100″; wire 15′.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P4434-20 Antique Bronze
17″ dia., 20-1/2″ ht.,
Overall ht. w/chain 96″; wire 15′.
Three medium base lamps,
each 100w max.

FOUR-LIGHT LINEAR CHANDELIER
P4435-20 Antique Bronze
35″ W., 12-1/2″ D., 29″ ht.,
Overall ht. w/stem 79″; wire 15′.
Four candelabra base lamps,
each 60w max

FIVE-LIGHT CHANDELIER
P4436-20 Antique Bronze
22″ dia., 26-3/8″ ht.,
Overall ht. w/chain 101″; wire 15′.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER
P4439-20 Antique Bronze
27″ dia., 33-3/8″ ht.,
Overall ht. w/chain 156″; wire 15′.
Nine candelabra base lamps,
each 60w max.

MINI-PENDANT
P5108-20 Antique Bronze
4″ dia., 6-3/4″ ht.,
Overall ht. w/stem 64″; wire 10′.
One medium base lamp, 100w max.

ONE-LIGHT PENDANT
P5112-20 Antique Bronze
17″ dia., 21-1/8″ ht.,
Overall ht. w/chain 97″; wire 15′.
One medium base lamp, 100w max.

MINI-PENDANT
P5167-20 Antique Bronze
3-3/4″ dia., 9-3/4″ ht.,
Overall ht. w/stem 67″; wire 10′.
One medium base lamp, 100w max.

Cascadia

FINISH

Polished Chrome - 15
Antique Bronze - 20

ALSO IN

Bath
Close-to-Ceiling

PAIR WITH

Ratio
Tally

WALL BRACKET
P2146-15 Polished Chrome
5-7/8" W., 8" ht.,
Extends 6-1/2". H/CTR 5-1/2".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE
P3644-15 Polished Chrome
Hanging and ceiling mount
hardware included.
14" dia., 10" ht.,
Overall ht. w/chain 49"; wire 10'.
Two medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P4612-15 Polished Chrome
21" dia., 16-3/4" ht.,
Overall ht. w/stem 83"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4613-15 Polished Chrome
26" dia., 10-3/4" ht.,
Overall ht. w/stem 83"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4614-15 Polished Chrome
30" dia., 21-7/8" ht.,
Overall ht. w/chain 88"; wire 15'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT
P5066-15 Polished Chrome
5-7/8" dia., 6-3/4" ht.,
Overall ht. w/stem 73"; wire 10'.
One medium base lamp,
100w max.

P3644-15
shown as hanging





P3644-15
shown as ceiling mount

P4614-15



P5066-15



P4613-15





P2146-15

P4612-15



Cascadia

P4614-20



P3644-20
shown as hanging





P3644-20
shown as ceiling mount

P4613-20



P5066-20



P4612-20





P2146-20

WALL BRACKET
P2146-20 Antique Bronze
5-7/8″ W., 8″ ht.,
Extends 6-1/2″. H/CTR 5-1/2″.
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE
P3644-20 Antique Bronze
Hanging and ceiling mount
hardware included.
14″ dia., 10″ ht.,
Overall ht. w/chain 49″; wire 10′.
Two medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P4612-20 Antique Bronze
21″ dia., 16-3/4″ ht.,
Overall ht. w/stem 83″; wire 15′.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4613-20 Antique Bronze
26″ dia., 10-3/4″ ht.,
Overall ht. w/stem 83″; wire 15′.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4614-20 Antique Bronze
30″ dia., 21-7/8″ ht.,
Overall ht. w/chain 88″; wire 15′.
Nine medium base lamps,
each 100w max.

MINI-PENDANT
P5066-20 Antique Bronze
5-7/8″ dia., 6-3/4″ ht.,
Overall ht. w/stem 73″; wire 10′.
One medium base lamp,
100w max.

Arden

FINISH

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

Bath
Close-to-Ceiling

PAIR WITH

Drum Shade
Piedmont

WALL BRACKET
P2127-09 Brushed Nickel
5-7/8" W., 8" ht.,
Extends 8-1/4". H/CTR 4".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE
P3720-09 Brushed Nickel
Hanging and ceiling mount
hardware included.
14" dia., 11-3/8" ht.,
Overall ht. w/chain 50"; wire 10'.
Two medium base lamps,
each 100w max.

THREE-LIGHT PENDANT
P3905-09 Brushed Nickel
18-1/8" dia., 24-5/8" ht.,
Overall ht. w/stem 99"; wire 10'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P4745-09 Brushed Nickel
22" dia., 18-3/4" ht.,
Overall ht. w/chain 93"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4746-09 Brushed Nickel
24-5/8" dia., 22-1/4" ht.,
Overall ht. w/chain 97"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4747-09 Brushed Nickel
30-1/2" dia., 30" ht.,
Overall ht. w/chain 153"; wire 15'.
Nine medium base lamps,
each 100w max.

TWELVE-LIGHT CHANDELIER
P4748-09 Brushed Nickel
42" dia., 41-1/2" ht.,
Overall ht. w/chain 164"; wire 15'.
Twelve medium base lamps,
each 75w max.

MINI-PENDANT
P5092-09 Brushed Nickel
5-7/8" dia., 9-5/8" ht.,
Overall ht. w/chain 75-1/2"; wire 10'.
One medium base lamp, 100w max.

P4745-09



P4748-09



P3720-09
shown as hanging



P3905-09



P4747-09



P5092-09



P4746-09





P2127-09

Arden


P4748-20


P4745-20


P3720-20
shown as hanging


P4747-20


P3905-20


P4746-20


P5092-20


P2127-20

WALL BRACKET
P2127-20 Antique Bronze
5-7/8″ W., 8″ ht.,
Extends 8-1/4″. H/CTR 4″.
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE
P3720-20 Antique Bronze
Hanging and ceiling mount
hardware included.
14″ dia., 11-3/8″ ht.,
Overall ht. w/chain 50″; wire 10′.
Two medium base lamps,
each 100w max.

THREE-LIGHT PENDANT
P3905-20 Antique Bronze
18-1/8″ dia., 24-5/8″ ht.,
Overall ht. w/stem 99″; wire 10′.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P4745-20 Antique Bronze
22″ dia., 18-3/4″ ht.,
Overall ht. w/chain 93″; wire 15′.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4746-20 Antique Bronze
24-5/8″ dia., 22-1/4″ ht.,
Overall ht. w/chain 97″; wire 15′.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4747-20 Antique Bronze
30-1/2″ dia., 30″ ht.,
Overall ht. w/chain 153″; wire 15′.
Nine medium base lamps,
each 100w max.

TWELVE-LIGHT CHANDELIER
P4748-20 Antique Bronze
42″ dia., 41-1/2″ ht.,
Overall ht. w/chain 164″; wire 15′.
Twelve medium base lamps,
each 75w max.

MINI-PENDANT
P5092-20 Antique Bronze
5-7/8″ dia., 9-5/8″ ht.,
Overall ht. w/chain 75-1/2″; wire 10′.
One medium base lamp,
100w max.

Clifton Heights

FINISH

- Brushed Nickel - 009
- Antique Bronze - 020

ALSO IN

Bath
Close-to-Ceiling
Ceiling Fans

PAIR WITH

Cascadia
Double Glass

WALL BRACKET
P300158-009 Brushed Nickel
5-1/2" W., 8-3/8" ht.,
Extends 7-1/8".
One medium base lamp,
each 100w max.

TWO-LIGHT SEMI-FLUSH
P350107-009 Brushed Nickel
12-3/4" sq., 11" ht.,
Two medium base lamps,
each 100w max.

FOUR-LIGHT CHANDELIER
P400118-009 Brushed Nickel
21" dia., 23-1/2" ht.,
Overall ht. w/chain 97-1/2", wire 15'
Four medium base lamps,
each 100w max.

SIX-LIGHT CHANDELIER
P400119-009 Brushed Nickel
26" dia., 23-1/2" ht.,
Overall ht. w/chain 99-1/2", wire 15'
Six medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P400120-009 Brushed Nickel
30" dia., 30-5/8" ht.,
Overall ht. w/chain 153", wire 15'.
Nine medium base lamps,
each 75w max.

MINI-PENDANT
P500125-009 Brushed Nickel
5-1/2" dia., 7-1/4" ht.,
Overall ht. w/stem 73-1/2", wire 10'.
One medium base lamp,
each 100w max.

TWO-LIGHT PENDANT
P500126-009 Brushed Nickel
16" sq., 24-1/2" ht.,
Overall ht. w/chain 99-1/2", wire 15'.
Two medium base lamps,
each 100w max.

P500126-009



P400120-009



P500125-009



P400119-009



P350107-009



P400118-009





P300158-009

Clifton Heights

P400120-020



P500126-020



P400119-020



P500125-020



P400118-020



P350107-020





P300158-020

WALL BRACKET
P300158-020 Antique Bronze
5-1/2" W., 8-3/8" ht.,
Extends 7-1/8".
One medium base lamp,
each 100w max.

TWO-LIGHT SEMI-FLUSH
P350107-020 Antique Bronze
12-3/4" sq., 11" ht.,
Two medium base lamps,
each 100w max.

FOUR-LIGHT CHANDELIER
P400118-020 Antique Bronze
21" dia., 23-1/2" ht.,
Overall ht. w/chain 97-1/2", wire 15'
Four medium base lamps,
each 100w max.

SIX-LIGHT CHANDELIER
P400119-020 Antique Bronze
26" dia., 23-1/2" ht.,
Overall ht. w/chain 99-1/2", wire 15'
Six medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P400120-020 Antique Bronze
30" dia., 30-5/8" ht.,
Overall ht. w/chain 153", wire 15'.
Nine medium base lamps,
each 75w max.

MINI-PENDANT
P500125-020 Antique Bronze
5-1/2" dia., 7-1/4" ht.,
Overall ht. w/stem 73-1/2", wire 10'.
One medium base lamp,
each 100w max.

TWO-LIGHT PENDANT
P500126-020 Antique Bronze
16" sq., 24-1/2" ht.,
Overall ht. w/chain 99-1/2", wire 15'.
Two medium base lamps,
each 100w max.

Torino

FINISH

Brushed Nickel - 09

ALSO IN

Bath
Close-to-Ceiling
Ceiling Fan

PAIR WITH

Markor

SEMI-FLUSH CONVERTIBLE
P3843-09 Brushed Nickel
Hanging and ceiling mount hardware included.
18″ dia., 18-1/2″ ht.,
Overall ht. w/chain 94″; wire 15′.
Three medium base lamps, each 100w max.

THREE-LIGHT PENDANT
P3847-09 Brushed Nickel
22″ dia., 27″ ht.,
Overall ht. w/chain 102″; wire 15′.
Three medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER
P4405-09 Brushed Nickel
19-1/8″ dia., 19-1/8″ ht.,
Overall ht. w/chain 94″; wire 15′.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER
P4416-09 Brushed Nickel
26-1/8″ dia., 24-3/4″ ht.,
Overall ht. w/chain 100″; wire 15′.
Five medium base lamps, each 100w max.

SIX-LIGHT CHANDELIER WITH THREE-LIGHT BOWL
P4417-09 Brushed Nickel
28-5/8″ dia., 29-7/8″ ht.,
Overall ht. w/chain 105″; wire 15′.
Six medium base lamps, each 100w max. and three medium base lamps, each 75w max.

WALL SCONCE
P7181-09 Brushed Nickel
9-1/2″ W., 6-3/4″ ht.,
Extends 4-3/4″. H/CTR 2-7/8″.
One medium base lamp, 100w max.

P3847-09



P4416-09



P3843-09
shown hanging



P4405-09



P4417-09





P7181-09

Torino

P4419-09



WALL BRACKET
P2881-09 Brushed Nickel
7″ W., 8-1/4″ ht.,
Extends 9-1/8″.
One medium base lamp,
100w max.

NINE-LIGHT CHANDELIER WITH THREE-LIGHT BOWL
P4418-09 Brushed Nickel
32″ dia., 32-5/8″ ht.,
Overall ht. w/chain 155″; wire 15′.
Nine medium base lamps,
each 100w max. and three
medium base lamps,
each 75w max.

TWELVE-LIGHT CHANDELIER
P4419-09 Brushed Nickel
34″ dia., 41-5/8″ ht.,
Overall ht. w/chain 164″; wire 15′.
Twelve medium base lamps,
each 100w max.

MINI-PENDANT
P5153-09 Brushed Nickel
7-1/2″ dia., 11″ ht.,
Overall ht. w/stem 62″; wire 10′.
One medium base lamp,
100w max.

P5153-09





P2881-09

P4418-09



Torino

FINISH

● Forged Bronze - 77

ALSO IN

Bath
Close-to-Ceiling
Ceiling Fan

SEMI-FLUSH CONVERTIBLE
P3843-77 Forged Bronze
Hanging and ceiling mount hardware included.
18" dia., 18-1/2" ht.,
Overall ht. w/chain 94"; wire 15'.
Three medium base lamps, each 100w max.

THREE-LIGHT PENDANT
P3847-77 Forged Bronze
22" dia., 27" ht.,
Overall ht. w/chain 102"; wire 15'.
Three medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER
P4405-77 Forged Bronze
19-1/8" dia., 19-1/8" ht.,
Overall ht. w/chain 94"; wire 15'.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER
P4416-77 Forged Bronze
26-1/8" dia., 24-3/4" ht.,
Overall ht. w/chain 100"; wire 15'.
Five medium base lamps, each 100w max.

SIX-LIGHT CHANDELIER WITH THREE-LIGHT BOWL
P4417-77 Forged Bronze
28-5/8" dia., 29-7/8" ht.,
Overall ht. w/chain 105"; wire 15'.
Six medium base lamps, each 100w max. and three medium base lamps, each 75w max.

WALL SCONCE
P7181-77 Forged Bronze
9-1/2" W., 6-3/4" ht.,
Extends 4-3/4". H/CTR 2-7/8".
One medium base lamp, 100w max.

P3847-77



P4416-77



P3843-77
shown hanging



P4405-77



P4417-77





P7181-77

Torino

P4419-77



WALL BRACKET
P2881-77 Forged Bronze
7″ W., 8-1/4″ ht.
Extends 9-1/8″.
One medium base lamp,
100w max.

NINE-LIGHT CHANDELIER WITH THREE-LIGHT BOWL
P4418-77 Forged Bronze
32″ dia., 32-5/8″ ht.,
Overall ht. w/chain 155″; wire 15′.
Nine medium base lamps, each 100w max. and three medium base lamps, each 75w max.

TWELVE-LIGHT CHANDELIER
P4419-77 Forged Bronze
34″ dia., 41-5/8″ ht.,
Overall ht. w/chain 164″; wire 15′.
Twelve medium base lamps, each 100w max.

MINI-PENDANT
P5153-77 Forged Bronze
7-1/2″ dia., 11″ ht.,
Overall ht. w/stem 62″; wire 10′.
One medium base lamp,
100w max.

P5153-77





P2881-77

P4418-77



Archie

The Archie Collection features finely crafted strap and knob details with clear, double-prismatic glass shades. Smooth stems and backplates support each shade and are coated in a crisp polished chrome, handsome Venetian bronze, or understated antique nickel finish.

FINISH

- Polished Chrome - 15
- Venetian Bronze - 74
- Antique Nickel - 81

ALSO IN

Bath
Close-to-Ceiling

PAIR WITH

Academy
Archives


WALL BRACKET
P2989-15 Polished Chrome
P2989-74 Venetian Bronze
P2989-81 Antique Nickel
5-3/4" W., 8-1/4" ht.,
Extends 7". H/CTR 5-1/4".
One medium base lamp,
100w max.

TWO-LIGHT LINEAR CHANDELIER
P4624-15 Polished Chrome
P4624-74 Venetian Bronze
30" W., 10-5/8" D., 12-3/4" ht.,
Overall ht. w/chain 100"; wire 10'.
Two medium base lamps,
each 100w max.

ONE-LIGHT PENDANT
P5026-15 Polished Chrome
P5026-74 Venetian Bronze
P5026-81 Antique Nickel
10-1/2" W., 9-1/4" ht.,
Overall ht. w/stem 75"; wire 10'.
One medium base lamp,
each 100w max.

MINI PENDANT
P5173-15 Polished Chrome
P5173-74 Venetian Bronze
P5173-81 Antique Nickel
5-3/4" W., 8-3/4" ht.,
Overall ht. w/stem 75"; wire 10'.
One medium base lamp,
each 100w max.

P4624-15



P5026-15



P5173-15





P2989-15

P4624-74



P5026-74



P5173-74





P2989-74

P5026-81



P5173-81





P2989-81

Applause

P4037-09



P5010-09





P2095-09

P4036-09



P4036-20



P4037-20



P5010-20





P2095-20

FINISH

Brushed Nickel - 09
Antique Bronze - 20

ALSO IN

Bath
Close-to-Ceiling

PAIR WITH

Trinity
Classic

WALL BRACKET
P2095-09 Brushed Nickel
P2095-20 Antique Bronze
7" W., 9-1/8" ht.,
Extends 7-7/8". H/CTR 5-3/4".
One medium base lamp,
100w max.

FIVE-LIGHT CHANDELIER
P4036-09 Brushed Nickel
P4036-20 Antique Bronze
24-1/2" dia., 24-5/8" ht.,
Overall ht. w/chain 99"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4037-09 Brushed Nickel
P4037-20 Antique Bronze
29-1/4" dia., 31-3/4" ht.,
Overall ht. w/chain 145-1/2"; wire 15'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT
P5010-09 Brushed Nickel
P5010-20 Antique Bronze
7" dia., 6-1/2" ht.,
Overall ht. w/stem 72-1/2"; wire 10'.
One medium base lamp,
100w max.

Inspire

FINISH

Brushed Nickel - 09
Antique Bronze - 20

ALSO IN

Bath
Close-to-Ceiling

PAIR WITH

Trinity
Drum Shade

ONE-LIGHT FOYER
P3799-09 Brushed Nickel
14-3/4" dia., 20-1/4" ht.,
Overall ht. w/chain 96"; wire 10'.
One medium base lamp,
100w max.

THREE-LIGHT PENDANT
P3931-09 Brushed Nickel
White acrylic diffuser.
19" dia., 21-1/2" ht.,
Overall ht. w/chain 96"; wire 10'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P4632-09 Brushed Nickel
17" dia., 18" ht.,
Overall ht. w/chain 92-1/4"; wire 10'.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P4635-09 Brushed Nickel
23" dia., 20" ht.,
Overall ht. w/chain 94"; wire 10'.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER
P4638-09 Brushed Nickel
29-3/8" dia., 31" ht.,
Overall ht. w/chain 105"; wire 12'.
Nine candelabra base lamps,
each 60w max.

FIFTEEN-LIGHT CHANDELIER
P4650-09 Brushed Nickel
39-1/2" dia., 40-1/4" ht.,
Overall ht. w/chain 163-1/4"; wire 15'.
Fifteen candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER
P4739-09 Brushed Nickel
30" dia., 22" ht.,
Overall ht. w/chain 97"; wire 10'.
Six candelabra base lamps,
each 60w max.

MINI-PENDANT
P5065-09 Brushed Nickel
6-1/2" dia., 6-1/4" ht. ,
Overall ht. w/chain or stem 93"; wire 10'.
One medium base lamp, 100w max.

P4632-09



P4635-09



P3799-09



P3931-09



P5065-09



P4650-09



P4638-09



P4739-09



P4650-20



P4638-20



P4739-20



P4632-20
shown without included shades



P4635-20



P3799-20



P3931-20



P5065-20



Inspire

ONE-LIGHT FOYER
P3799-20 Antique Bronze
14-3/4" dia., 20-1/4" ht.,
Overall ht. w/chain 96"; wire 10'.
One medium base lamp,
100w max.

THREE-LIGHT PENDANT
P3931-20 Antique Bronze
White acrylic diffuser.
19" dia., 21-1/2" ht.,
Overall ht. w/chain 96"; wire 10'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P4632-20 Antique Bronze
17" dia., 18" ht.,
Overall ht. w/chain 92-1/4"; wire 10'.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P4635-20 Antique Bronze
23" dia., 20" ht.,
Overall ht. w/chain 94"; wire 10'.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER
P4638-20 Antique Bronze
29-3/8" dia., 31" ht.,
Overall ht. w/chain 105"; wire 12'.
Nine candelabra base lamps,
each 60w max.

FIFTEEN-LIGHT CHANDELIER
P4650-20 Antique Bronze
39-1/2" dia., 40-1/4" ht.,
Overall ht. w/chain 163-1/4"; wire 15'.
Fifteen candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER
P4739-20 Antique Bronze
30" dia., 22" ht.,
Overall ht. w/chain 97"; wire 10'.
Six candelabra base lamps,
each 60w max.

MINI-PENDANT
P5065-20 Antique Bronze
6-1/2" dia., 6-1/4" ht.,
Overall ht. w/chain or stem 93"; wire 10'.
One medium base lamp,
100w max.

Trinity

FINISH

● Brushed Nickel - 09

ALSO IN

Bath
Close-to-Ceiling

PAIR WITH

Markor
Classic
Applause

SEMI-FLUSH CONVERTIBLE
P3473-09 Brushed Nickel
Hanging and ceiling mount hardware included.
16″ dia., 17-1/2″ ht.,
Overall ht. w/chain 93″; wire 15′.
Two medium base lamps, each 100w max.

THREE-LIGHT PENDANT
P3474-09 Brushed Nickel
18″ dia., 24″ ht.,
Overall ht. w/chain 99″; wire 15′.
Three medium base lamps, each 100w max.

LINEAR CHANDELIER
P4325-09 Brushed Nickel
26-1/2″ W., 6-1/2″ D., 28-1/4″ ht.,
Overall ht. w/chain 103″; wire 15′.
Three medium base lamps, each 100w max.

FOUR-LIGHT CHANDELIER
P4326-09 Brushed Nickel
19″ dia., 20″ ht.,
Overall ht. w/chain 95″; wire 15′.
Four medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER
P4328-09 Brushed Nickel
23″ dia., 24″ ht.,
Overall ht. w/chain 99″; wire 15′.
Five medium base lamps, each 100w max.

ONE-LIGHT PENDANT
P5095-09 Brushed Nickel
18″ dia., 9-1/2″ ht.,
Overall ht. w/chain 85″; wire 15′.
One medium base lamp, 150w max.

MINI-PENDANT
P5096-09 Brushed Nickel
6-1/2″ dia., 7″ ht.,
Overall ht. w/stem 64″; wire 10′.
One medium base lamp, 100w max.

P3474-09



P4328-09



P3473-09
shown hanging



P4326-09



P5095-09



P4325-09



P5096-09



Trinity

P4365-09



P4324-09



P3807-09



P4329-09



P3806-09





P3190-09

WALL BRACKET
P3190-09 Brushed Nickel
6-1/2″ W., 7-1/2″ ht.,
Extends 9″. H/CTR 3-1/2″.
One medium base lamp,
100w max.

TWO-LIGHT FOYER
P3806-09 Brushed Nickel
12″ dia., 18″ ht.,
Overall ht. w/chain 93″; wire 15′.
Two candelabra base lamps,
each 60w max.

THREE-LIGHT FOYER
P3807-09 Brushed Nickel
13-1/2″ dia., 24″ ht.,
Overall ht. w/chain 99″; wire 15′.
Three candelabra base lamps,
each 60w max.

THREE-LIGHT CHANDELIER
P4324-09 Brushed Nickel
19″ dia., 20″ ht.,
Overall ht. w/chain 95″; wire 15′.
Three medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4329-09 Brushed Nickel
30″ dia., 33″ ht.,
Overall ht. w/chain 156″; wire 15′.
Nine medium base lamps,
each 100w max.

FIFTEEN-LIGHT CHANDELIER
P4365-09 Brushed Nickel
43-3/4″ dia., 43-5/8″ ht.,
Overall ht. w/chain 167″; wire 15′.
Fifteen medium base lamps,
each 75w max.

Trinity

FINISH

● Antique Bronze - 20

ALSO IN

Bath
Close-to-Ceiling

SEMI-FLUSH CONVERTIBLE
P3473-20 Antique Bronze
Hanging and ceiling mount hardware included.
16″ dia., 17-1/2″ ht.,
Overall ht. w/chain 93″; wire 15′.
Two medium base lamps, each 100w max.

THREE-LIGHT PENDANT
P3474-20 Antique Bronze
Glass top diffuser.
18″ dia., 24″ ht.,
Overall ht. w/chain 99″; wire 15′.
Three medium base lamps, each 100w max.

LINEAR CHANDELIER
P4325-20 Antique Bronze
26-1/2″ W., 6-1/2″ D., 28-1/4″ ht.,
Overall ht. w/chain 103″; wire 15′.
Three medium base lamps, each 100w max.

FOUR-LIGHT CHANDELIER
P4326-20 Antique Bronze
19″ dia., 20″ ht.,
Overall ht. w/chain 95″; wire 15′.
Four medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER
P4328-20 Antique Bronze
23″ dia., 24″ ht.,
Overall ht. w/chain 99″; wire 15′.
Five medium base lamps, each 100w max.

ONE-LIGHT PENDANT
P5095-20 Antique Bronze
18″ dia., 9-1/2″ ht.,
Overall ht. w/chain 85″; wire 15′.
One medium base lamp, 150w max.

MINI-PENDANT
P5096-20 Antique Bronze
6-1/2″ dia., 7″ ht.,
Overall ht. w/stem 64″; wire 10′.
One medium base lamp, 100w max.

P3474-20



P4328-20



P3473-20
shown hanging



P4326-20



P5095-20



P5096-20



P4325-20



Trinity

P4365-20



P4324-20



P3807-20



P4329-20



P3806-20





P3190-20

WALL BRACKET
P3190-20 Antique Bronze
6-1/2″ W., 7-1/2″ ht.,
Extends 9″. H/CTR 3-1/2″.
One medium base lamp,
100w max.

TWO-LIGHT FOYER
P3806-20 Antique Bronze
12″ dia., 18″ ht.,
Overall ht. w/chain 93″; wire 15′.
Two candelabra base lamps,
each 60w max.

THREE-LIGHT FOYER
P3807-20 Antique Bronze
13-1/2″ dia., 24″ ht.,
Overall ht. w/chain 99″; wire 15′.
Three candelabra base lamps,
each 60w max.

THREE-LIGHT CHANDELIER
P4324-20 Antique Bronze
19″ dia., 20″ ht.,
Overall ht. w/chain 95″; wire 15′.
Three medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4329-20 Antique Bronze
30″ dia., 33″ ht.,
Overall ht. w/chain 156″; wire 15′.
Nine medium base lamps,
each 100w max.

FIFTEEN-LIGHT CHANDELIER
P4365-20 Antique Bronze
43-3/4″ dia., 43-5/8″ ht.,
Overall ht. w/chain 167″; wire 15′.
Fifteen medium base lamps,
each 75w max.

Invite

FINISH

Brushed Nickel - 09
Antique Bronze - 20

ALSO IN

Bath
Close-to-Ceiling

PAIR WITH

Gather
Riley

WALL BRACKET
P2041-09 Brushed Nickel
6-1/2″ W., 11-1/2″ ht.,
Extends 8-1/4″. H/CTR 3-3/4″.
One medium base lamp, 100w max.

SEMI-FLUSH CONVERTIBLE
P3694-09 Brushed Nickel
Hanging and ceiling mount
hardware included.
15″ dia., 5-1/4″ ht.,
Overall ht. w/stem 71″; wire 12′.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P4695-09 Brushed Nickel
22″ dia., 19-3/4″ ht.,
Overall ht. w/stem 86″; wire 12′.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4696-09 Brushed Nickel
25-1/4″ dia., 20-3/4″ ht.,
Overall ht. w/stem 87″; wire 12′.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4697-09 Brushed Nickel
35-5/8″ dia., 26-1/2″ ht.,
Overall ht. w/stem 92″; wire 12′.
Nine medium base lamps,
each 100w max.

TWELVE-LIGHT CHANDELIER
P4725-09 Brushed Nickel
49″ dia., 38″ ht.,
Overall ht. w/chain 161″; wire 15′.
Twelve medium base lamps,
each 75w max.

FOUR-LIGHT PENDANT
P5047-09 Brushed Nickel
20″ dia., 27-3/8″ ht.,
Overall ht. w/stem 93″; wire 12′.
Four medium base lamps,
each 100w max.

MINI-PENDANT
P5110-09 Brushed Nickel
6-1/2″ dia., 7-3/8″ ht.,
Overall ht. w/stem 74″; wire 10′.
One medium base lamp, 100w max.

P4725-09



P4695-09
shown without optional finial



P4696-09



P5047-09



P4697-09



P3694-09
shown as hanging



P5110-09





P2041-09



P4725-20



P4696-20



P4695-20



P4697-20



P5047-20



P2041-20



P5110-20



P3694-20
shown as ceiling mount

Invite

WALL BRACKET
P2041-20 Antique Bronze
6-1/2″ W., 11-1/2″ ht.,
Extends 8-1/4″. H/CTR 3-3/4″.
One medium base lamp, 100w max.

SEMI-FLUSH CONVERTIBLE
P3694-20 Antique Bronze
Hanging and ceiling mount
hardware included.
15″ dia., 5-1/4″ ht.,
Overall ht. w/stem 71″; wire 12′.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P4695-20 Antique Bronze
22″ dia., 19-3/4″ ht.,
Overall ht. w/stem 86″; wire 12′.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4696-20 Antique Bronze
25-1/4″ dia., 20-3/4″ ht.,
Overall ht. w/stem 87″; wire 12′.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4697-20 Antique Bronze
35-5/8″ dia., 26-1/2″ ht.,
Overall ht. w/stem 92″; wire 15′.
Nine medium base lamps,
each 100w max.

TWELVE-LIGHT CHANDELIER
P4725-20 Antique Bronze
49″ dia., 38″ ht.,
Overall ht. w/chain 161″; wire 12′.
Twelve medium base lamps,
each 75w max.

FOUR-LIGHT PENDANT
P5047-20 Antique Bronze
20″ dia., 27-3/8″ ht.,
Overall ht. w/stem 93″; wire 12′.
Four medium base lamps,
each 100w max.

MINI-PENDANT
P5110-20 Antique Bronze
6-1/2″ dia., 7-3/8″ ht.,
Overall ht. w/stem 74″; wire 10′.
One medium base lamp, 100w max.

Joy

FINISH

- Brushed Nickel - 09
- Antique Bronze - 20W

ALSO IN

Bath
Close-to-Ceiling

PAIR WITH

Bravo
Tally
Cherish

WALL BRACKET
P2000-09 Brushed Nickel
6" W., 9-1/2" ht.,
Extends 7". H/CTR 6".
One medium base lamp, 100w max.

THREE-LIGHT FOYER
P3587-09 Brushed Nickel
14-5/8" dia., 17" ht., Overall ht.
w/chain or stem 104"; wire 12'.
Three candelabra base lamps,
each 60w max.

SEMI-FLUSH CONVERTIBLE
P3864-09 Brushed Nickel
Hanging and ceiling mount
hardware included.
16-5/8" dia., 12-1/8" ht.,
Overall ht. w/chain 51", wire 10'.
three medium base lamps,
each 100w max.

THREE-LIGHT PENDANT
P3951-09 Brushed Nickel
19-1/2" dia., 24-3/4" ht.,
Overall ht. w/stem 114"; wire 12'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P4489-09 Brushed Nickel
20" dia., 16-3/8" ht., Overall ht.
w/chain or stem 106"; wire 12'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4490-09 Brushed Nickel
24" dia., 18-7/8" ht., Overall ht.
w/chain or stem 105"; wire 12'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4492-09 Brushed Nickel
28" dia., 27-3/4" ht., Overall ht.
w/chain or stem 115"; wire 15'.
Nine medium base lamps,
each 100w max.

TWELVE-LIGHT CHANDELIER
P4497-09 Brushed Nickel
38" w., 39-5/8" ht.,
Overall ht. w/chain 175"; wire 15'.
Twelve medium base lamps,
each 75w max.

MINI-PENDANT
P5270-09 Brushed Nickel
6" dia., 7" ht. Overall ht.,
w/chain or stem 94"; wire 10'.
One medium base lamp, 100w max.


P3587-09


P4497-09


P4489-09


P3951-09


P4492-09


P3864-09
shown hanging


P2000-09


P5270-09


P4490-09



P4497-20W



P3587-20W



P4489-20W



P4492-20W



P3951-20W



P4490-20W



P5270-20W



P3864-20W
shown hanging



P2000-20W

Joy

WALL BRACKET
P2000-20W Antique Bronze
6″ W., 9-1/2″ ht.,
Extends 7″. H/CTR 6″.
One medium base lamp,
100w max.

THREE-LIGHT FOYER
P3587-20W Antique Bronze
14-5/8″ dia., 17″ ht.,
Overall ht. w/chain 104″; wire 12′.
Three candelabra base lamps,
each 60w max.

SEMI-FLUSH CONVERTIBLE
P3864-20W Antique Bronze
Hanging and ceiling mount
hardware included.
16-5/8″ dia., 12-1/8″ ht.,
Overall ht. w/chain 51″, wire 10′.
three medium base lamps
each, 100w max.

THREE-LIGHT INVERTED PENDANT
P3951-20W Antique Bronze
19-1/2″ dia., 24-3/4″ ht.,
Overall ht. w/chain 114″; wire 12′.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P4489-20W Antique Bronze
20″ dia., 16-3/8″ ht.,
Overall ht. w/chain 103″; wire 12′.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4490-20W Antique Bronze
24″ dia., 18-7/8″ ht.,
Overall ht. w/chain 106″; wire 12′.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4492-20W Antique Bronze
28″ dia., 27-3/4″ ht.,
Overall ht. w/chain 115″; wire 15′.
Nine medium base lamps,
each 100w max.

TWELVE-LIGHT CHANDELIER
P4497-20W Antique Bronze
38″ dia., 39-5/8″ ht.,
Overall ht. w/chain 174-1/2″; wire 15′.
Twelve medium base lamps,
each 75w max.

MINI-PENDANT
P5270-20W Antique Bronze
6″ dia., 7″ ht., Overall ht.
w/chain or stem 94″; wire 10′.
One medium base lamp, 100w max.

Riley

FINISHES

- Brushed Nickel - 009
- Matte Black - 031

ALSO IN

Bath
Sconces

PAIR WITH

Landree
Draper

FIVE-LIGHT CHANDELIER
P400209-009 Brushed Nickel
24" dia., 19-3/4" ht.,
Overall ht. w/chain 85-1/2", wire 15'.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER
P400210-009 Brushed Nickel
30" dia., 25-1/8" ht.,
Overall ht. w/chain 91", wire 15'.
Nine candelabra base lamps,
each 60w max.

THREE-LIGHT PENDANT
P500243-009 Brushed Nickel
21" dia., 11" ht.,
Overall ht. w/chain 77", wire 15'.
Three candelabra base lamps,
each 60w max.

WALL BRACKET
P710082-009 Brushed Nickel
5" W., 14-1/2" ht.,
Extends 4-5/8". H/CTR 7-3/4".
One candelabra base lamp,
60w max.

All fixtures shown with EF4T8D927/JA8 LED lamps, not included. See page 824.

P400210-009



P400209-009



P500243-009





P710082-009

Riley



P400210-031



P400209-031



P500243-031



P710082-031

FIVE-LIGHT CHANDELIER
P400209-031 Matte Black
24″ dia., 19-3/4″ ht.,
Overall ht. w/chain 85-1/2″, wire 15′.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER
P400210-031 Matte Black
30″ dia., 25-1/8″ ht.,
Overall ht. w/chain 91″, wire 15′.
Nine candelabra base lamps,
each 60w max.

THREE-LIGHT PENDANT
P500243-031 Matte Black
21″ dia., 11″ ht.,
Overall ht. w/chain 77″, wire 15′.
Three candelabra base lamps,
each 60w max.

WALL BRACKET
P710082-031 Matte Black
5″ W., 14-1/2″ ht.,
Extends 4-5/8″. H/CTR 7-3/4″.
One candelabra base lamp,
60w max.

All fixtures shown with EF4T8D927/JA8 LED lamps, not included. See page 824.

Laird

FINISH

Brushed Nickel - 009
Antique Bronze - 020

ALSO IN

Bath

PAIR WITH

Heart
Classic

SEMI-FLUSH CONVERTIBLE
P350057-009 Brushed Nickel
Hanging and ceiling mount hardware included.
13" dia., 9-7/8" ht.,
Overall ht. w/chain 55", wire 10'.
Two medium base lamps, each 100w max.

THREE-LIGHT SEMI-FLUSH CONVERTIBLE
P350136-009 Brushed Nickel
Hanging and ceiling mount hardware included.
15-5/8" dia., 11-3/4" ht.
Overall ht. w/chain 55"; wire 120".
Extends 11-3/4".
Three medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER
P400062-009 Brushed Nickel
19-3/4" dia., 16" ht.,
Overall ht. w/chain 60", wire 9.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER
P400063-009 Brushed Nickel
23-3/4" dia., 17-1/2" ht.,
Overall ht. w/chain 61-1/2", wire 9.
Five medium base lamps, each 100w max.

NINE-LIGHT CHANDELIER
P400064-009 Brushed Nickel
27-3/4" dia., 25-1/2" ht.,
Overall ht. w/chain 65", wire 12'.
Nine medium base lamps, each 100w max.

THREE-LIGHT PENDANT
P500071-009 Brushed Nickel
17" dia., 20-3/4" ht.,
Overall ht. w/chain 87-1/2", wire 9.
Three medium base lamps, each 100w max.

P400064-009



P500071-009



P400063-009



P350057-009
shown hanging



P400062-009



P350057-009
shown as ceiling mount



P350136-009
shown hanging



Laird


P400064-020


P400063-020


P500071-020


P400062-020


P350057-020
shown hanging


P350136-020
shown as ceiling mount


P350057-020
shown as ceiling mount

SEMI-FLUSH CONVERTIBLE
P350057-020 Antique Bronze
Hanging and ceiling mount hardware included.
13″ dia., 9-7/8″ ht.,
Overall ht. w/chain 55″, wire 10′.
Two medium base lamps, each 100w max.

THREE-LIGHT SEMI-FLUSH CONVERTIBLE
P350136-020 Antique Bronze
Hanging and ceiling mount hardware included.
15-5/8″ dia., 11-3/4″ ht.
Overall ht. w/chain 55″; wire 120″.
Extends 11-3/4″.
Three medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER
P400062-020 Antique Bronze
19-3/4″ dia., 16″ ht.,
Overall ht. w/chain 60″, wire 9.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER
P400063-020 Antique Bronze
23-3/4″ dia., 17-1/2″ ht.,
Overall ht. w/chain 61-1/2″, wire 9.
Five medium base lamps, each 100w max.

NINE-LIGHT CHANDELIER
P400064-020 Antique Bronze
27-3/4″ dia., 25-1/2″ ht.,
Overall ht. w/chain 65″, wire 12′.
Nine medium base lamps, each 100w max.

THREE-LIGHT PENDANT
P500071-020 Antique Bronze
17″ dia., 20-3/4″ ht.,
Overall ht. w/chain 87-1/2″, wire 9.
Three medium base lamps, each 100w max.

Madison

FINISH

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

Bath
Close-to-Ceiling
Ceiling Fan

PAIR WITH

Hansford
Drum Shade

WALL BRACKET
P3161-09 Brushed Nickel
7-5/8" W., 8" ht.,
Extends 8-1/2". H/CTR 5".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE
P3792-09 Brushed Nickel
Hanging and ceiling mount
hardware included.
9-1/2" dia., 14-5/8" ht.,
Overall ht. w/chain 90"; wire 15'.
One medium base lamp,
75w max.

ONE-LIGHT PENDANT
P3793-09 Brushed Nickel
11" dia., 21-3/8" ht.,
Overall ht. w/chain 96"; wire 15'.
One medium base lamp,
100w max.

THREE-LIGHT CHANDELIER
P4280-09 Brushed Nickel
22" dia., 20" ht.,
Overall ht. w/chain 95"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4281-09 Brushed Nickel
24-5/8" dia., 25" ht.,
Overall ht. w/chain 100"; wire 15'.
Five medium base lamps,
each 100w max.

THREE-LIGHT LINEAR CHANDELIER
P4282-09 Brushed Nickel
31-1/4" W., 7-5/8" D., 24" ht.,
Overall ht. w/chain 99"; wire 15'.
Three medium base lamps,
each 100w max.

MINI-PENDANT
P5078-09 Brushed Nickel
7-1/2" dia., 8" ht.,
Overall ht. w/stem 52"; wire 10'.
One medium base lamp,
100w max.



P4282-09
shown with glass facing down



P3792-09



P3793-09



P5078-09



P4281-09
shown with glass facing up



P4280-09
shown with glass facing down



P3161-09

Madison

P4282-20
shown with glass facing down



P4281-20
shown with glass facing down



P3792-20



P4280-20
shown with glass facing up



P3793-20





P3161-20

P5078-20



WALL BRACKET
P3161-20 Antique Bronze
7-5/8″ W., 8″ ht.,
Extends 8-1/2″. H/CTR 5″.
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE
P3792-20 Antique Bronze
Hanging and ceiling mount
hardware included.
9-1/2″ dia., 14-5/8″ ht.,
Overall ht. w/chain 90″; wire 15′.
One medium base lamp,
75w max.

ONE-LIGHT PENDANT
P3793-20 Antique Bronze
11″ dia., 21-3/8″ ht.,
Overall ht. w/chain 96″; wire 15′.
One medium base lamp,
100w max.

THREE-LIGHT CHANDELIER
P4280-20 Antique Bronze
22″ dia., 20″ ht.,
Overall ht. w/chain 95″; wire 15′.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4281-20 Antique Bronze
24-5/8″ dia., 25″ ht.,
Overall ht. w/chain 100″; wire 15′.
Five medium base lamps,
each 100w max.

THREE-LIGHT LINEAR CHANDELIER
P4282-20 Antique Bronze
31-1/4″ W., 7-5/8″ D., 24″ ht.,
Overall ht. w/chain 99″; wire 15′.
Three medium base lamps,
each 100w max.

MINI-PENDANT
P5078-20 Antique Bronze
7-1/2″ dia., 8″ ht.,
Overall ht. w/stem 52″; wire 10′.
One medium base lamp,
100w max.

Heart

FINISH

Brushed Nickel - 09
Antique Bronze - 20

ALSO IN

Bath

PAIR WITH

Laird
Trinity
Five-Light

WALL BRACKET
P2913-09 Brushed Nickel
6" W., 9-1/16" ht.,
Extends 8". H/CTR 4-1/2".
One medium base lamp,
100w max.

THREE-LIGHT PENDANT
P3955-09 Brushed Nickel
17-3/4" dia., 21-3/4" ht.,
Overall ht. w/chain 66"; wire 8'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P4664-09 Brushed Nickel
22" dia., 18" ht.,
Overall ht. w/chain 63"; wire 8'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4666-09 Brushed Nickel
25-1/2" dia., 19-1/8" ht.,
Overall ht. w/chain 63"; wire 8'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4668-09 Brushed Nickel
30" dia., 27-3/4" ht.,
Overall ht. w/chain 90"; wire 12'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT
P5131-09 Brushed Nickel
6" dia., 6" ht., Overall ht.
w/chain or stem 63"; wire 8'.
One medium base lamp,
100w max.

P3955-09



P4668-09



P4664-09



P4666-09





P2913-09

P5131-09



Heart

P4668-20



P3955-20



WALL BRACKET
P2913-20 Antique Bronze
6″ W., 9-1/16″ ht.,
Extends 8″. H/CTR 4-1/2″.
One medium base lamp,
100w max.

THREE-LIGHT PENDANT
P3955-20 Antique Bronze
17-3/4″ dia., 21-3/4″ ht.,
Overall ht. w/chain 66″; wire 8′.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER
P4664-20 Antique Bronze
22″ dia., 18″ ht.,
Overall ht. w/chain 63″; wire 8′.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4666-20 Antique Bronze
25-1/2″ dia., 19-1/8″ ht.,
Overall ht. w/chain 63″; wire 8′.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER
P4668-20 Antique Bronze
30″ dia., 27-3/4″ ht.,
Overall ht. w/chain 90″; wire 12′.
Nine medium base lamps,
each 100w max.

MINI-PENDANT
P5131-20 Antique Bronze
6″ dia., 6″ ht., Overall ht.
w/chain or stem 63″; wire 8′.
One medium base lamp,
100w max.

P4666-20



P4664-20



P5131-20





P2913-20

Gather

FINISH

Brushed Nickel - 09
Antique Bronze - 20

ALSO IN

Bath
Ceiling Fan

PAIR WITH

5-Light
Drum Shade

SEMI-FLUSH CONVERTIBLE
P3748-09 Brushed Nickel
Hanging and ceiling mount hardware included.
12-1/2" dia., 10-3/8" ht.,
Overall ht. w/chain 24"; wire 6'.
Two medium base lamps, each 100w max.

TWO-LIGHT PENDANT
P3914-09 Brushed Nickel
15" dia., 20-5/8" ht.,
Overall ht. w/chain 66"; wire 8'.
Two medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER
P4440-09 Brushed Nickel
18 1/2" dia., 15" ht.,
Overall ht. w/chain 60"; wire 8'.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER
P4441-09 Brushed Nickel
20-1/2" dia., 15" ht.,
Overall ht. w/chain 60"; wire 8'.
Five medium base lamps, each 100w max.

NINE-LIGHT CHANDELIER
P4627-09 Brushed Nickel
27-3/4" dia., 20-1/2" ht.,
Overall ht. w/chain 84"; wire 10'.
Nine medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER
P4734-09 Brushed Nickel
19-1/2" dia., 16-1/2" ht.,
Overall ht. w/chain 61"; wire 8'.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER
P4735-09 Brushed Nickel
23" dia., 17-1/2" ht.,
Overall ht. w/chain 62"; wire 8'.
Five medium base lamps, each 100w max.

MINI-PENDANT
P5113-09 Brushed Nickel
4" dia., 5-3/4" ht., Overall ht. w/chain or stem 63"; wire 8'.
One medium base lamp, 100w max.

P4440-09



P4627-09



P4734-09



P4735-09



P3914-09



P4441-09



P3748-09
shown hanging



P5113-09





P4627-20



P4440-20

Gather

SEMI-FLUSH CONVERTIBLE
P3748-20 Antique Bronze
Hanging and ceiling mount hardware included.
12-1/2″ dia., 10-3/8″ ht.,
Overall ht. w/chain 24″; wire 6′.
Two medium base lamps, each 100w max.

TWO-LIGHT PENDANT
P3914-20 Antique Bronze
15″ dia., 20-5/8″ ht.,
Overall ht. w/chain 66″; wire 8′.
Two medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER
P4440-20 Antique Bronze
18 1/2″ dia., 15″ ht.,
Overall ht. w/chain 60″; wire 8′.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER
P4441-20 Antique Bronze
20-1/2″ dia., 15″ ht.,
Overall ht. w/chain 60″; wire 8′.
Five medium base lamps, each 100w max.

NINE-LIGHT CHANDELIER
P4627-20 Antique Bronze
27-3/4″ dia., 20-1/2″ ht.,
Overall ht. w/chain 84″; wire 10′.
Nine medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER
P4734-20 Antique Bronze
19-1/2″ dia., 16-1/2″ ht.,
Overall ht. w/chain 61″; wire 8′.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER
P4735-20 Antique Bronze
23″ dia., 17-1/2″ ht.,
Overall ht. w/chain 62″; wire 8′.
Five medium base lamps, each 100w max.

MINI-PENDANT
P5113-20 Antique Bronze
4″ dia., 5-3/4″ ht., Overall ht. w/chain or stem 63″; wire 8′.
One medium base lamp, 100w max.



P4735-20



P4734-20



P4441-20



P3914-20



P5113-20



P3748-20
shown hanging

Gather

FINISH

Brushed Nickel - 09
Antique Bronze - 20

THREE-LIGHT FOYER
P3928-09 Brushed Nickel
P3928-20 Antique Bronze
10″ dia., 16″ ht.,
Overall ht. w/chain 61″; wire 8′.
Three candelabra base lamps,
each 60w max.

SIX-LIGHT FOYER
P3929-09 Brushed Nickel
P3929-20 Antique Bronze
15″ dia., 24″ ht.,
Overall ht. w/chain 87″; wire 10′.
Six candelabra base lamps,
each 60w max.

WALL BRACKET
P2706-09 Brushed Nickel
P2706-20 Antique Bronze
5″ W., 7-1/2″ ht.,
Extends 6-1/2″. H/CTR 2-5/8″.
One medium base lamp,
100w max.



P3929-09
shown with included Brushed Nickel candle sleeves



P3929-20
shown with included White candle sleeves



P3928-09
shown with included White candle sleeves



P3928-20
shown with included Antique Bronze candle sleeves



P2706-09



P2706-20

Bedford


P4391-09


P4390-09


P3788-09


P5090-09

FINISH

Brushed Nickel - 09

PAIR WITH

Americana
Drum Shade

SEMI-FLUSH CONVERTIBLE
P3788-09 Brushed Nickel
Hanging and ceiling mount hardware included.
10-1/2″ dia., 14-1/2″ ht.,
Overall ht. w/chain 54″; wire 15′.
One medium base lamp, 150w max.

THREE-LIGHT CHANDELIER
P4390-09 Brushed Nickel
19-1/2″ dia., 15-5/8″ ht.,
Overall ht. w/chain 54″; wire 15′.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER
P4391-09 Brushed Nickel
22-1/2″ dia., 16″ ht.,
Overall ht. w/chain 91″; wire 15′.
Five medium base lamps, each 100w max.

ONE-LIGHT PENDANT
P5090-09 Brushed Nickel
15-5/8″ dia., 11-1/4″ ht.,
Overall ht. w/chain 50″; wire 15′.
One medium base lamp, 150w max.

Classic

FINISH

- Brushed Nickel - 09
- Antique Bronze - 20
- Polished Chrome - 15

ALSO IN

Bath
Pendants

PAIR WITH

Gather
Drum Shade

THREE-LIGHT CHANDELIER
P4762-09 Brushed Nickel
P4762-15 Polished Chrome
P4762-20 Antique Bronze
18" dia., 17-1/4" ht.,
Overall ht. w/chain 62-1/2", wire 9.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4770-09 Brushed Nickel
P4770-15 Polished Chrome
P4770-20 Antique Bronze
21-7/8" dia., 17-1/4" ht.,
Overall ht. w/chain 62", wire 8'.
Five medium base lamps,
each 100w max.

P4762-09



P4770-09



P4762-15



P4770-15



P4762-20



P4770-20



Classic

P4732-09



P4757-09



THREE-LIGHT CHANDELIER
P4732-09 Brushed Nickel
P4732-15 Polished Chrome
P4732-20 Antique Bronze
20″ dia., 17″ ht.,
Overall ht. w/chain 56″, wire 15′.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P4757-09 Brushed Nickel
P4757-15 Polished Chrome
P4757-20 Antique Bronze
23″ dia., 17-1/4″ ht.,
Overall ht. w/chain 55-1/2″, wire 15′.
Five medium base lamps,
each 100w max.

ONE-LIGHT PENDANT
P500288-009 Brushed Nickel
P500288-015 Polished Chrome
P500288-020 Antique Bronze
5-1/8″ dia., 7″ ht.
Overall ht. w/chain 46″, wire 120″.
One medium base lamp,
each 100w max.

P4732-15



P4757-15



P500288-009



P500288-015



P4732-20



P4757-20



P500288-020



Drum Shade

FINISH

- Black - 031
- Antique Bronze - 20
- Brushed Nickel - 09

PAIR WITH

Inspire
Whisp

FIVE-LIGHT CHANDELIER
P4217-09 Brushed Nickel
P4217-20 Antique Bronze
Linen drum shade.
21-5/8" dia., 21-1/8" ht.,
Overall ht. w/chain 66"; wire 10'.
Five candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P400193-031 Black
21-5/8" dia., 21-1/8" ht.,
Overall ht. w/chain 66"; wire 10'.
Five candelabra base lamps,
each 60w max.

P4217-09



P4217-20



P400193-031



Tally


P3786-20


P3786-09


P3787-20


P3787-09

FINISH

Brushed Nickel - 09
Antique Bronze - 20

PAIR WITH

Laird
Inspire

FOUR-LIGHT FOYER
P3786-09 Brushed Nickel
P3786-20 Antique Bronze
11-7/8″ dia., 19-1/4″ ht.,
Overall ht. w/chain 94″; wire 15′.
Four candelabra base lamps,
each 60w max.

FOUR-LIGHT FOYER
P3787-09 Brushed Nickel
P3787-20 Antique Bronze
16-3/4″ dia., 26-1/2″ ht.,
Overall ht. w/chain 101″; wire 15′.
Four candelabra base lamps,
each 60w max.

Americana

FINISH

- Brushed Nickel - 09
- Polished Brass - 10
- Antique Bronze - 20

PAIR WITH

5-Light Parkhurst

FIVE-LIGHT CHANDELIER
P4346-09 Brushed Nickel
P4346-10 Polished Brass
P4346-20 Antique Bronze
24" dia., 17" ht.,
Overall ht. w/chain 53"; wire 15'.
Five candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P4355-09 Brushed Nickel
P4355-10 Polished Brass
23-1/4" dia., 18-1/4" ht.,
Overall ht. w/chain 58"; wire 15'.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER
P4356-09 Brushed Nickel
P4356-10 Polished Brass
23-1/4" dia., 18" ht.,
Overall ht. w/chain 57"; wire 15'.
Six candelabra base lamps,
each 60w max.

EIGHT-LIGHT CHANDELIER
P4357-09 Brushed Nickel
P4357-10 Polished Brass
26" dia., 18" ht.,
Overall ht. w/chain 54"; wire 15'.
Eight candelabra base lamps,
each 60w max.

ACCESSORY
P8788-10 Polished Brass
Polished Solid Brass
candle-cap accessory.
7/8" dia., 3/4" ht.



P8788-10

P4357-09



P4357-10



P4356-09



P4356-10



P4355-09



P4355-10



P4346-20



P4346-09



P4346-10



5-Light

The gorgeous 5-Light Collection is sure to grab all the attention in the dining or foyer space it calls home. Sweeping arms flow down to hold vintage candlestick-inspired light bases for a timeless, classic design that will tie the whole room together.


P4008-09


P4009-09


P4008-31


P4009-20


P4009-10

FINISH

- Brushed Nickel - 09
- Polished Brass - 10
- Antique Bronze - 20
- Black - 31

PAIR WITH

Piedmont
Drum Shade

FIVE-LIGHT CHANDELIER
P4008-09 Brushed Nickel
P4008-31 Black
21" dia., 16-1/2" ht.,
Overall ht. w/chain 91"; wire 15'.
Five candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER
P4009-09 Brushed Nickel
P4009-10 Polished Brass
P4009-20 Antique Bronze
17-1/2" dia., 15" ht.,
Overall ht. w/chain 91"; wire 15'.
Five candelabra base lamps, each 60w max.

Haven

FINISH

Brushed Nickel - 09


PAIR WITH

Chadwick
Alexa
Tobin

FOUR-LIGHT LINEAR PENDANT
P3898-09 Brushed Nickel
Acrylic bottom diffuser.
34″ W., 8″ D., 8-3/4″ ht.,
Overall ht. w/chain 73″; wire 10′.
Four medium base lamps,
each 100w max.

ONE-LIGHT PENDANT
P3921-09 Brushed Nickel
Acrylic bottom diffuser.
14″ sq., 26-3/4″ ht.,
Overall ht. w/stem 103″; wire 15′.
One medium base lamp,
100w max.

P3898-09



P3921-09



Eclipse


P3487-20


P3575-09


P3486-20


P3573-09

FINISH

Brushed Nickel - 09
Antique Bronze - 20

ALSO IN

Close-to-Ceilling
Sconces

PAIR WITH

Avant
Globe LED

THREE-LIGHT PENDANT
P3486-20 Antique Bronze
19-3/8" dia., 17" ht.,
Overall ht. w/chain 56"; wire 15'.
Three medium base lamps,
each 100w max.

FOUR-LIGHT PENDANT
P3487-20 Antique Bronze
27-3/8" dia., 24-1/8" ht.,
Overall ht. w/chain 63"; wire 15'
Four medium base lamps,
each 100w max.

THREE-LIGHT PENDANT
P3573-09 Brushed Nickel
19-3/8" dia., 17" ht.,
Overall ht. w/chain 56"; wire 15'.
Three medium base lamps,
each 100w max.

FOUR-LIGHT PENDANT
P3575-09 Brushed Nickel
27-3/8" dia., 24" ht.,
Overall ht. w/chain 63"; wire 15'.
Four medium base lamps,
each 100w max.

Apogee LED

FINISH

- Brushed Nickel - 009
- Architectural Bronze - 129

ALSO IN

Close-to-Ceilling

PAIR WITH

Avant
Globe LED

SEMI-FLUSH CONVERTIBLE
P350064-009-30 Brushed Nickel
Hanging and ceiling mount hardware included.
15" dia., 10-3/4" ht.,
Overall ht. w/chain 85-1/4, wire 15'.
30w integrated LED, 3000K, 90CRI, 1855 delivered lumens, 120-277V, 0-10V dimming.

SEMI-FLUSH CONVERTIBLE
P350065-009-30 Brushed Nickel
Hanging and ceiling mount hardware included.
21" dia., 14-1/2" ht.,
Overall ht. w/chain 92", wire 15'.
45w integrated LED, 3000K, 90CRI, 2765 delivered lumens, 120-277V, 0-10V dimming.

SEMI-FLUSH CONVERTIBLE
P350066-009-30 Brushed Nickel
Hanging and ceiling mount hardware included.
27" dia., 20-5/8" ht.,
Overall ht. w/chain 98, wire 15'.
71w integrated LED, 3000K, 90CRI, 4215 delivered lumens, 120-277V, 0-10V dimming.

WALL SCONCE
P710036-009-30 Brushed Nickel
15" W., 7-1/2" ht.,
3-11/16" extends or depth.
20w integrated LED, 3000K, 90CRI, 940 delivered lumens, 120-277V, 0-10V dimming.

All fixtures:

P350066-009-30



P350064-009-30
shown hanging



P350065-009-30





P350064-009-30
shown as ceiling mount



P710036-009-30

Apogee LED



P350066-129-30



P350065-129-30



P350064-129-30
shown hanging



P710036-129-30



P350064-129-30
shown as ceiling mount

SEMI-FLUSH CONVERTIBLE
P350064-129-30 Architectural Bronze
Hanging and ceiling mount hardware included.
15″ dia., 10-3/4″ ht.,
Overall ht. w/chain 85-1/4, wire 15′.
30w integrated LED, 3000K, 90CRI, 1855 delivered lumens, 120-277V, 0-10V dimming.

SEMI-FLUSH CONVERTIBLE
P350065-129-30 Architectural Bronze
Hanging and ceiling mount hardware included.
21″ dia., 14-1/2″ ht.,
Overall ht. w/chain 92″, wire 15′.
45w integrated LED, 3000K, 90CRI, 2765 delivered lumens, 120-277V, 0-10V dimming.


SEMI-FLUSH CONVERTIBLE
P350066-129-30 Architectural Bronze
Hanging and ceiling mount hardware included.
27″ dia., 20-5/8″ ht.,
Overall ht. w/chain 98, wire 15′.
90CRI, 4215 delivered lumens, 120-277V, 0-10V dimming.

WALL SCONCE
P710036-129-30 Architectural Bronze
15″ W., 7-1/2″ ht.,
Extends 3-11/16″.
20w integrated LED, 3000K, 90CRI, 940 delivered lumens, 120-277V, 0-10V dimming.

All fixtures:

Featuring Caisson





Pendants

Versatile *in any* Room

Scan and see more at
progresslighting.com





David Peek
Director, Product Development
Decorative Lighting

The New Farmhouse Fresh

with David

Ideal for the homeowner who loves to combine vintage pieces and weathered furnishings to create interiors that showcase antique charm. Farmhouse style represents the simplicity and common sense functionality of country living, while also incorporating vintage accents. Whites and other soft neutrals work well with this style. Add in weathered wood and distressed décor to tie in the color palette and overall aesthetic. Choose darker elements to create contrast in these soft neutral spaces. Consider dark chairs, bold lighting fixtures and metal or wooden signage.

Shop this style at
progresslighting.com/farmhouse



Markor

The Markor Collection features a versatile series of modular pendant systems. Select your choice of pendant stem kits to help make your installation simple and customized to perfectly fit the personality of your home.

10" DRUM SHADE
Acrylic bottom diffuser.
For use with pendant P5198 only
(See page 273)
10" dia., 8" ht.
P8828-30 Summer Linen

16" DRUM SHADE
Acrylic bottom diffuser.
For use with P5198 or P5199
(See page 273)
16" dia., 10" ht.
P8822-01 Black Parchment Paper
P8823-01 Beige Silken Fabric
P8829-30 Summer Linen
P8829-56 Khaki
P8829-59 Harvest Linen

22" DRUM SHADE
Acrylic bottom diffuser.
For use with P5198 or P5199
(See page 273)
22" dia., 10" ht.
P8824-01 Black Parchment Paper
P8825-01 Beige Silken Fabric
P8830-30 Summer Linen
P8830-56 Khaki
P8830-59 Harvest Linen

All fixtures shown with pendant kit (sold separately).

P8829-56



P8830-56



P8829-59



P8830-59



P8823-01



P8825-01



P8822-01



P8824-01



P8828-30



P8829-30



P8830-30



Markor Pendant System & Ordering

Simple to order. Specify two separate pieces – shade and stem kit of your choice.

Step 1: Choose a fabric


Black parchment paper


Beige silken fabric

Summer Linen


Khaki


Harvest Linen

Step 2: Select a shade size

10" DRUM SHADES
P8828-30 Summer Linen



16" DRUM SHADE
P8822-01 Black Parchment Paper
P8823-01 Beige Silken Fabric
P8829-30 Summer Linen
P8829-56 Khaki
P8829-59 Harvest Linen



22" DRUM SHADES
P8824-01 Black Parchment Paper
P8825-01 Beige Silken Fabric
P8830-30 Summer Linen
P8830-56 Khaki
P8830-59 Harvest Linen



Step 3: Select a stem kit

Shades and pendant kits are sold separately. 9" and 10" shades can be used only with pendant kit P5198. 16" and 22" shades can be used with pendant kit P5198 or P5199.

ONE-LIGHT PENDANT
P5198-09 Brushed Nickel
P5198-20 Antique Bronze
P5198-12 Satin Brass
P5198-31 Black
One-light pendant kit for use with all Markor shades.
1-5/8" dia., 5-5/8" ht. Overall ht. w/stem and lamps 66"; wire 10'.
One medium base lamp, 100w max.

ONE-LIGHT LED PENDANT
P5198-0930K9 Brushed Nickel
One-light pendant kit for use with all Markor shades.
5-3/4" dia., 5-3/8" ht. Overall ht. w/stem and lamps 62"; wire 10'.
One 17w LED module 3000K, 90CRI, 1211 source lumens.

THREE-LIGHT PENDANT
P5199-09 Brushed Nickel
P5199-20 Antique Bronze
P5199-12 Satin Brass
P5199-31 Black
Three-light pendant kit for use with most 16" and 22" shades only.
4-3/4" dia., 6-1/4" ht. Overall ht. w/stem and lamps 64"; wire 10'
Three medium base lamps, each 100w max.


P5198-09


P5198-20


P5198-12


P5198-31


P5198-0930K


P5199-09


P5199-20


P5199-12


P5199-31

Sitting Under a Canopy

Pendants have the power to change the look of a room instantly. Today, they can be seen in bath and vanity areas, kitchens and foyers, in singles or in multiples of two or more. Progress Lighting's canopy accessory offers a convenient way to mount groupings of pendants.



Featuring Markor and Linear Canopy



Round Canopy

The round accessory accommodates 3 fixtures and is available in Brushed Nickel, Antique Bronze and Graphite finishes.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Graphite - 143

THREE-LIGHT ROUND
P8403-09 Brushed Nickel
P8403-20 Antique Bronze
P8403-143 Graphite
Round canopy can be used for three pendants. Refer to website for details.
15-1/2" dia., 1-3/8" ht.



P8403-20



P8403-09



P8403-143

Canopies allow for flexibility and efficiency. Easily transform a simple pendant into a statement piece by clustering them together using a round canopy.

Featuring Kempsey and Round Canopy



Featuring Calhoun and Linear Canopy



Pair multiple pendants or mix and match collections of pendants on a rectangular canopy for a striking focal point that will transform your space.

Linear Canopy

Progress Lighting's canopy accessory offers a convenient way to mount groupings of pendants. The linear option can hold either 2 or 3 pendants. Available in Brushed Nickel, Antique Bronze and Graphite finishes.



P860004-009



P860004-143



P860004-020



P860005-020



P860005-143



P860005-009



P8404-20



P8404-143



P8404-09



P860005-143
shown in use with Staunton pendants Design Series™

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020
- Graphite - 143

THREE-LIGHT LINEAR
P8404-09 Brushed Nickel
P8404-20 Antique Bronze
P8404-143 Graphite
See website for additional details.
4-1/4" W., 23-1/4" L., 11/16" ht.

FIVE-LIGHT LINEAR
P860004-009 Brushed Nickel
P860004-143 Graphite
P860004-020 Antique Bronze
See website for additional details.
4-1/4" W., 59-5/8" L., 1" ht.

SIX-LIGHT LINEAR
P860005-009 Brushed Nickel
P860005-143 Graphite
P860005-020 Antique Bronze
See website for additional details.
8-1/8" W., 39-5/8" L., 1" ht.

Planck LED

Provide a dramatic architectural lighting design to any space with the Plank LED Collection. A smooth, metal beam suspends from the ceiling to add clean, simple visual interest to minimalist residential or commercial settings.

FINISHES

- Brushed Nickel - 009
- Matte White - 028
- Matte Black - 031

LED LINEAR PENDANT
P500276-009-30 Brushed Nickel
P500276-028-30 Matte White
P500276-031-30 Matte Black
47-1/2" W., 1-3/4" D., 1-3/8" ht.
Overall ht. w/cord 113"; wire 9'.
39w integrated LED, 3000K, 90CRI,
2900 delivered lumens.

JA8



P500276-009-30



P500276-028-30



P500276-031-30

Concourse LED

The Concourse LED linear pendant features minimalist design styling and a slim profile that appears to float along the ceiling. Offering energy efficiency and low maintenance benefits, Concourse LED is suitable for both home and commercial applications providing direct, ambient, beautifully diffused light. A Brushed Nickel frame completes the clean seamless look.

FINISH

- Brushed Nickel - 009

LED LINEAR PENDANT
P500002-009-30 Brushed Nickel
40" W., 5-1/4" D., 3" ht.
Overall ht. w/cord 113"; wire 9'.
39w integrated LED, 3000K, 90CRI,
2400 delivered lumens.

JA8



P500002-009-30



Medal

A smoothly curved metal shade ornamented with a star motif medallion holds a headlight-style glass diffuser, reminiscent of a vintage automobile engine.

FINISHES

- Brushed Nickel - 009
- Graphite - 143
- Coastal Blue - 164

ONE-LIGHT PENDANT
P500212-009 Brushed Nickel
P500212-143 Graphite
P500212-164 Coastal Blue
17-3/8" dia., 17-5/8" ht.
Overall ht. w/chain 93"; wire 10'.
One medium base lamp,
100w max.


P500212-009


P500212-143


P500212-164

Loftin

Inspired by vintage automobile headlights, a medal shade suspended from a slim metal bar surrounds a textured glass diffuser.

FINISHES

- Brushed Nickel - 009
- Matte Black - 031

ONE-LIGHT PENDANT
P500170-009 Brushed Nickel
P500170-031 Matte Black
14-3/4" dia., 13-3/8" ht.
Overall ht. w/stem 79-1/2"; wire 10'.
One medium base lamp,
100w max.


P500170-009


P500170-031



Fresnel Lens

Industrial roots in form and function. Antique-inspired Fresnel glass lens in Brushed Nickel, Oil Rubbed Bronze, or Chrome.

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Oil Rubbed Bronze - 108

ONE-LIGHT PENDANT
P5188-09 Brushed Nickel
P5188-108 Oil Rubbed Bronze
12-1/8" dia., 10-1/2" ht.
Overall ht. w/stem 77"; wire 10'.
One medium base lamp,
100w max.

LED PENDANT
P5188-0930K9 Brushed Nickel
P5188-1530K9 Polished Chrome
P5188-10830K9 Oil Rubbed Bronze
12-1/8" dia., 10-1/2" ht.
Overall ht. w/stem 77"; wire 10'.
One 17w LED module, 3000K,
90CRI, 1211 Source Lumens.

ONE-LIGHT PENDANT
P5197-09 Brushed Nickel
P5197-108 Oil Rubbed Bronze
16" dia., 13-1/4" ht.
Overall ht. w/stem 79"; wire 10'.
One medium base lamp,
100w max.

LED PENDANT
P5197-0930K9 Brushed Nickel
P5197-1530K9 Polished Chrome
P5197-10830K9 Oil Rubbed Bronze
16" dia., 13-1/4" ht.
Overall ht. w/stem 79"; wire 10'.
One 17w LED module, 3000K,
90CRI, 1211 source lumens.

P5188-09
P5188-0930K9



P5197-09
P5197-0930K9



P5188-1530K9



P5197-1530K9



P5188-108
P5188-10830K9



P5197-108
P5197-10830K9





Featuring Fresnel Lens
Image: Keystone Custom Homes

P5050-1530K9



P5050-09
P5050-0930K9



P5050-108
P5050-10830K9



MINI-PENDANT
P5050-09 Brushed Nickel
P5050-108 Oil Rubbed Bronze
6-1/8" dia., 6-1/4" ht. Overall ht. w/stem 72-1/4"; wire 10'.
One medium base lamp, 40w max.

LED MINI-PENDANT
P5050-0930K9 Brushed Nickel
P5050-1530K9 Polished Chrome
P5050-10830K9 Oil Rubbed Bronze
6-1/8" dia., 6-1/4" ht.
Overall ht. w/stem 72-1/4"; wire 10'.
One 9w LED module, 3000K, 90CRI, 623 source lumens.

Range

Range features a classic triangular clear seeded glass shade. The simple geometric glass is outlined with a slender frame and finished with a bottom metal accent ring. Simple and stylish, this versatile style is suitable for a variety of designs, such as Modern, Farmhouse and Urban Industrial.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020
- Polished Nickel - 104
- Graphite - 143

PAIR WITH
Debut

ONE-LIGHT PENDANT
P500135-009 Brushed Nickel
P500135-020 Antique Bronze
P500135-104 Polished Nickel
P500135-143 Graphite
13" dia., 13" ht.
Overall ht. w/stem 79"; wire 10'.
One medium base lamp,
60w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

P500135-009



P500135-020



P500135-104



P500135-143



Passage

Smooth, slender metal arms embrace a metal rim topping a simple, clear seeded glass shade and a classic candle cluster.

FINISHES

- Brushed Nickel - 009
- Matte Black - 031

THREE-LIGHT PENDANT
P500237-009 Brushed Nickel
P500237-031 Matte Black
12" dia., 26-3/4" ht.
Overall ht. w/chain 102", wire 15'.
Three candelabra base lamps,
each 60w max.

All fixtures shown with F4B10DLED927/JA8 lamps, not included. See page 824.

P500237-009



P500237-031



Caisson

Infuse your home with a subtle, industrial flair with the Caisson Collection. Inspired by the astounding architecture of suspension bridges, the clean fixtures feature curled, clear glass shades that are suspended from fabric cords. Each shade's rim is rolled inside the diffusers for an extra touch of artisan feel.

FINISHES

- Brushed Nickel - 009
- Graphite - 1430

ALSO IN

Sconces

P500160-009



P500159-009



MINI-PENDANT
P500159-009 Brushed Nickel
P500159-143 Graphite
7-7/8" dia., 10-7/8" ht.
Overall ht. w/stem 119-1/2"; wire 10'.
One medium base lamp,
60w max.

P500160-143



P500159-143



THREE-LIGHT PENDANT
P500160-009 Brushed Nickel
P500160-143 Graphite
30-3/8" dia., 35" ht.
Overall ht. w/stem 90-1/2"; wire 10'.
Three medium base lamps,
each 60w max.



Featuring Baycourt
Image: Toll Brothers


P3701-09


P3701-20

Bay Court

Rediscover antique nautical lanterns. Can be used in traditional and non-traditional fashions. Ideal as single pieces or multiples. Etched interior glass surrounded by etched water glass.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

Close-to-Ceiling

ONE-LIGHT PENDANT
P3701-09 Brushed Nickel
P3701-20 Antique Bronze
11-3/4" dia., 18-1/4" ht.
Overall ht. w/chain 94"; wire 15'.
One medium base lamp,
100w max.


P5589-09


P5589-20

ONE-LIGHT PENDANT
P5589-09 Brushed Nickel
P5589-20 Antique Bronze
8-3/4" dia., 12-3/4" ht.
Overall ht w/chain 87"; wire 10'.
One medium base lamp,
100w max.


P500236-030


P500236-161

Bastille

A basket-inspired dual-toned metal shade suspended by a simple chain encloses a single bulb socket.

FINISHES

- White - 030
- Aged Brass - 161
- Coastal Blue - 164

ONE-LIGHT PENDANT
P500236-030 White
P500236-161 Aged Brass
P500236-164 Coastal Blue
12" dia., 14-1/4" ht.
Overall ht. w/chain 88-1/2"; wire 10'.
One medium base lamp,
60w max.


P500236-164

All fixtures shown with F7ST19DLED927/JA8 LED lamps, not included. See page 824.

Parkhurst

Offer a modern spin on a timeless design with the Parkhurst Collection. Lantern-style metal frames create an airy structure ideal for coastal, farmhouse, and mid-century modern settings. Inside each frame perch smooth, simple light bases ready to offer your home a lovely glow.

FINISHES

- Brushed Nickel - 009
- Matte Black - 031
- Brushed Bronze - 109

THREE-LIGHT FOYER
P500213-009 Brushed Nickel
P500213-031 Matte Black
P500213-109 Brushed Bronze
10-7/8" sq., 19-3/4" ht.
Overall ht. w/chain 94"; wire 10'.
Three candelabra base lamps, each 60w max.

FOUR-LIGHT FOYER
P500214-009 Brushed Nickel
P500214-031 Matte Black
P500214-109 Brushed Bronze
14-3/8" sq., 24-3/8" ht.
Overall ht. w/chain 99-1/2"; wire 10'.
Four candelabra base lamps, each 60w max.

All fixtures shown with EF4T8D927/JA8 LED lamps, not included. See page 824.

P500214-109



P500213-109



P500214-009



P500213-009



P500214-031



P500213-031





Featuring Parkhurst

Perfectly Paired with your Meal

There's nothing quite like a stylish coach lantern to illuminate a kitchen nook or dining table. The Parkhurst lanterns easily accentuate a Transitional style dining space fit for any dinner party.

Penn

Penn offers a modern take on vintage design. Turnkey details clear glass globes are enhanced by a Polished Nickel or Natural Brass finish.

FINISHES

- Polished Nickel - 104
- Natural Brass - 137

PAIR WITH

Elevate
Mod

MINI-PENDANT
P5067-104 Polished Nickel
P5067-137 Natural Brass
6-7/8" dia., 9-1/2" ht.
Overall ht. w/stem 76"; wire 15'.
One medium base lamp,
100w max.

ONE-LIGHT PENDANT
P5070-104 Polished Nickel
P5070-137 Natural Brass
9-3/4" dia., 12-3/4" ht.
Overall ht. w/stem 79"; wire 15'.
One medium base lamp,
100w max.

ONE-LIGHT PENDANT
P5328-104 Polished Nickel
P5328-137 Natural Brass
12" dia., 15" ht.
Overall ht. w/stem 81", wire 10'.
One medium base lamp,
100w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.


P5328-104


P5328-137


P5070-104


P5070-137


P5067-104


P5067-137

Archives


P5161-20


P5161-81


P500034-020

The vintage electric pendants are illuminated with light reflected through a clear piece of glass that is sandblasted on the inside and sits on top of shade. Antique Bronze with Antique Brass accents.

FINISHES

- Antique Bronze - 020
- Antique Nickel - 81

ALSO IN

Bath

MINI-PENDANT

P5161-020 Antique Bronze
P5161-81 Antique Nickel
9″ dia., 5-1/8″ ht.
Overall ht. w/cord 116″; cord 10′.
One medium base lamp, 100w max.

ONE-LIGHT PENDANT

P500034-020 Antique Bronze
14″ dia., 7-1/2″ ht.
Overall ht. w/stem 73-1/2″; wire 10′.
One medium base lamp, 75w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.



Featuring Archives
Image: Green Tech Homes, Piper Stromatt and 161 Photography

Gauge

Inspired by industrial elements, Gauge features an open cage design that's both functional and aesthetically appealing. Multi-pendant is supplied with hoop frame to provide an element of customization. Wire frame is comprised of Graphite with Brushed Nickel accents.

FINISH

● Graphite - 143

ALSO IN

Bath

MINI-PENDANT

P500021-143 Graphite
6-1/8" dia., 9-1/2" ht.
Overall ht. w/cord 130"; wire 10'.
One medium base lamp,
60w max.

Fixture shown with P7825-01 vintage lamp, not included. See page 824.



P500021-143

Brookside

Inspired by vintage light fixtures found in early 20th century train stations. Metal shade and double prismatic glass options.

FINISH

● Brushed Nickel - 09

MINI-PENDANT

P5023-09 Brushed Nickel
8" dia., 7-1/2" ht.
Overall ht. w/stem 64"; wire 10'.
One medium base lamp,
100w max.

PENDANT

P5024-09 Brushed Nickel
12" dia., 9-1/8" ht.
Overall ht. w/stem 65"; wire 10'.
One medium base lamp,
150w max.

LED PENDANT

P5024-0930K9 Brushed Nickel
12" dia., 9-1/8" ht.
Overall ht. w/stem 65"; wire 10'.
One 17w LED, 3000K, 90CRI,
1211 source lumens.



P5023-09



P5024-09
P5024-0930K9



Ballinger

Matte black metal bars in soft geometric shapes surround a single bulb for an open-cage design with an industrial feel.

FINISH

● Matte Black - 031

ONE-LIGHT PENDANT
P500220-031 Black
12-1/2″ sq., 18-1/2″ ht.
Overall ht. w/stem 85-1/2″; wire 10′.
One medium base lamp,
100w max.

Fixture shown with P7825-01 vintage lamp, not included. See page 824.









Chambers

Inspired by a wire egg basket, an airy open-cage shade hangs from a simple metal bar with rustic flair.

FINISHES

● Matte Black - 031
● Galvanized - 141

MINI-PENDANT
P500281-031 Matte Black
P500281-141 Galvanized
10″ dia., 11″ ht.
Overall ht. w/stem 76″; wire 10′.
One medium base lamp,
100w max.

ONE-LIGHT PENDANT
P500282-031 Matte Black
P500282-141 Galvanized
Hanging and ceiling mount hardware included.
16-3/8″ dia., 10-7/8″ ht.
Overall ht. w/stem 76″; wire 15′.
One medium base lamp,
100w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

Academy

Pendants with Classic styling feature clear seeded glass with Polished Chrome.

FINISH

Polished Chrome - 15

MINI-PENDANT
P5137-15 Polished Chrome
8″ dia., 9″ ht.
Overall ht. w/stem 75″; wire 10′.
One medium base lamp,
100w max.

ONE-LIGHT PENDANT
P5138-15 Polished Chrome
12″ dia., 12-3/4″ ht.
Overall ht. w/stem 79″; wire 10′.
One medium base lamp,
100w max.


P5137-15


P5138-15

Schoolhouse

Opal glass gives a hint of nostalgia to any décor.

FINISH

Brushed Nickel - 09

MINI-PENDANT
P5196-09 Brushed Nickel
8″ dia., 9″ ht.
Overall ht. w/stem 75″; wire 10′.
One medium base lamp,
100w max.


P5196-09

Latrobe

Introduce a pop of personality into your home with the Latrobe Collection. A bottle-inspired design adds an unexpected twist to a simple, understated industrial style that brings the collection's vintage charm to the forefront of your home's lighting design.

P500229-009



P500229-031



P500230-009



P500230-031



P500231-009



P500231-031



FINISHES

- Brushed Nickel - 009
- Matte Black - 031

ONE-LIGHT PENDANT
P500229-009 Brushed Nickel
P500229-031 Matte Black
7" dia., 17" ht.
Overall ht. w/cord 139"; wire 10'.
One medium base lamp,
60w max.

ONE-LIGHT PENDANT
P500230-009 Brushed Nickel
P500230-031 Matte Black
9-7/16" dia., 15-1/2" ht.
Overall ht. w/cord 137"; wire 10'.
One medium base lamp,
60w max.

ONE-LIGHT PENDANT
P500231-009 Brushed Nickel
P500231-031 Matte Black
12-1/4" dia., 14" ht.
Overall ht. w/cord 136"; wire 10'.
One medium base lamp,
60w max.

All fixtures shown with F7ST19DLED927/JA8 LED lamps, not included. See page 824.

Featuring Latrobe





A Group Picture Worth Taking

Using canopies are a game-changer when it comes to adding personality to your dining room.

1

Line classic-styled pendants above your dining table for a clean design. Multiple pendants are great solutions for a long table, to extend illumination to all areas of the room.

2

A neutral color palette in furniture and decoration adds refinement to a transitional style dining room while keeping an inviting ambiance.

3

Mix and match fixtures in the same collection, like these Latrobe pendants, for character and interest.

Tre

Tre is a series of classic metal shade pendants with an updated combination of finishes and features. A tri-arm support adds a sense of architectural and industrial detailing, while the open-top shade allows for both downward and upward illumination. Light reflects off the inside of the Vintage Silver shade to provide the metallic reflective effect.

FINISHES

○ White - 030
● Graphite - 143

MINI-PENDANT
P500051-030 White
P500051-143 Graphite
10″ dia., 13-1/4″ ht.
Overall ht. w/cord 134″; wire 10’.
One medium base lamp,
100w max.

ONE-LIGHT PENDANT
P500052-030 White
P500052-143 Graphite
15″ dia., 13-1/2″ ht.
Overall ht. w/cord 134-1/2″; wire 10’.
One medium base lamp,
100w max.

ONE-LIGHT PENDANT
P500053-030 White
P500053-143 Graphite
20″ dia., 14-1/2″ ht.
Overall ht. w/cord 135-1/2″; wire 10’.
One medium base lamp,
100w max.


P500051-030


P500051-143


P500052-030


P500052-143


P500053-030


P500053-143



Featuring Tre

Featuring Dome LED



Dome LED

Inspired to enhance modern home décor, Dome LED pendants come in three intriguing color options and sizes for flexible lighting designs within the home. Satin Aluminum and Gloss White finishes feature a soft silver interior shade while the Antique Bronze dome is complemented with a painted gold interior.

FINISHES

- Satin Aluminum - 16
- Antique Bronze - 20
- White - 30

LED MINI-PENDANT
P5340-1630K9 Satin Aluminum
P5340-2030K9 Antique Bronze
P5340-3030K9 White
10" dia., 5-5/8" ht.
Overall ht. w/cord 125-1/2"; cord 10'.
One 9w LED module 3000K, 90CRI, 623 source lumens.

LED PENDANT
P5341-1630K9 Satin Aluminum
P5341-2030K9 Antique Bronze
P5341-3030K9 White
16" dia., 8-7/8" ht.
Overall ht. w/ cord 129"; cord 10'.
One 17w LED module 3000K, 90CRI, 1211 source lumens.

LED PENDANT
P5342-1630K9 Satin Aluminum
P5342-2030K9 Antique Bronze
P5342-3030K9 White
22" dia., 11-3/4" ht.
Overall ht. w/ cord 131-1/2"; cord 10'.
One 29w LED module 3000K, 90CRI, 2197 source lumens.

All fixtures:

P5342-2030K9



P5340-2030K9



P5341-2030K9



P5342-3030K9



P5340-3030K9



P5341-3030K9



P5342-1630K9



P5340-1630K9



P5341-1630K9



Globe LED

Distinctive, classic globe pendants are accented by striking metal caps as they top beautiful etched glass shades in the Globe LED Collection. These versatility pendants can be displayed as a single fixture or in groups of two or more by mixing and matching finish options and lengths to create custom lighting designs for the home.

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Brushed Bronze - 109
- Matte Black - 031

LED PENDANT
P500147-009-30 Brushed Nickel
P500147-015-30 Polished Chrome
P500147-031-30 Matte Black
P500147-109-30 Brushed Bronze
8" dia., 9-3/4" ht.
Overall ht. w/cord 122"; wire 10'.
One 9w LED module, 3000K, 90CRI, 624 source lumens.

LED PENDANT
P500148-009-30 Brushed Nickel
P500148-015-30 Polished Chrome
P500148-031-30 Matte Black
P500148-109-30 Brushed Bronze
11-5/8" dia., 13-1/2" ht.
Overall ht. w/cord 136-1/2"; wire 10'.
One 17w LED module, 3000K, 90CRI, 1276 source lumens.

All fixtures:

JA8

P500147-009-30



P500148-009-30



P500147-031-30



P500148-031-30



P500147-015-30



P500148-015-30



P500147-109-30



P500148-109-30



Atwell

Extraordinary on the first impression, but always at peace with whatever setting it calls home, the Atwell Collection is an expressive reflection of your mid-century modern taste. An intricate blend of circular and a one-of-a-kind architectural lighting collection that is both remarkable and enduring.

FINISHES

- Brushed Nickel - 009
- Matte Black - 031
- Brushed Bronze - 109

P500283-109



P500284-109



P500283-009



P500284-009



P500283-031



P500284-031



ONE-LIGHT PENDANT
P500283-009 Brushed Nickel
P500283-031 Matte Black
P500283-109 Brushed Bronze
8-1/4" W., 13-1/8" ht.
Overall ht. w/stem 70"; wire 10'.
Extends 8-1/4".
One candelabra base lamp, 60w max.

TWO-LIGHT PENDANT
P500284-009 Brushed Nickel
P500284-031 Matte Black
P500284-109 Brushed Bronze
13-1/2" W., 20-1/2" ht.
Overall ht. w/stem 77"; wire 10'.
Extends 13-1/2".
Two candelabra base lamps, each 60w max.

Cayce

Cayce's capsule silhouette showcases an interior candelabra cluster. An interlocking hexagonal design gracefully adorns the middle of the glass to add visual interest. Available in Chrome and Vintage Gold finishes. Flush with personality, the Cayce pendant provides a unique design style suitable for a variety of interiors, including Modern, Farmhouse, Urban Industrial and Luxe.

FINISHES

- Polished Chrome - 015
- Vintage Gold - 078

THREE-LIGHT PENDANT
P500156-015 Polished Chrome
P500156-078 Vintage Gold
9" dia., 18-1/4" ht.
Overall ht. w/chain 93-1/2"; wire 10'.
Three candelabra base lamps, each 60w max.

P500156-015



P500156-078





Featuring Cayce, Hide-a-Lite LED, Undercabinet and Puck


P3753-09


P3753-20

Seeded Glass

Delicate rope detailing drapes down to a signature, clear seeded glass enclosing a classic candle cluster.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

THREE-LIGHT FOYER
P3753-09 Brushed Nickel
P3753-20 Antique Bronze
9-3/4" dia., 24-1/2" ht.
Overall ht. w/chain 98"; wire 15'.
Three candelabra base lamps, each 60w max.


P5183-09


P5182-09


P5143-0930K9

Prismatic

A bold and striking prismatic glass shade is the focal point in these pendants. Featuring a sleek Brushed Nickel cap and stems highlighting the industrial styling.

FINISH

- Brushed Nickel - 09

PENDANT
P5182-09 Brushed Nickel
12-5/8" dia., 11" ht.
Overall ht. w/stem 53"; wire 10'.
One medium base lamp, 100w max.

PENDANT
P5183-09 Brushed Nickel
16" dia., 13-1/2" ht.
Overall ht. w/stem 56"; wire 10'.
One medium base lamp, 150w max.

LED PENDANT
P5143-0930K9 Brushed Nickel
12-3/4" dia., 10-7/8" ht.
Overall ht. w/stem 77"; wire 10'.
One 9w LED module 3000K, 90CRI
623 source lumens.

Clarion

FINISHES

- Brushed Nickel - 009
- Satin Brass - 012
- Matte Black - 031
- Polished Nickel - 104

MINI-PENDANT
P500241-009 Brushed Nickel
P500241-012 Satin Brass
P500241-031 Matte Black
P500241-104 Polished Nickel
9" dia., 11-3/8" ht.
Overall ht. w/stem 67-1/2"; wire 10'.
One medium base lamp,
60w max.

ONE-LIGHT PENDANT
P500242-009 Brushed Nickel
P500242-012 Satin Brass
P500242-031 Matte Black
P500242-104 Polished Nickel
10-1/2" dia., 15-7/8" ht.
Overall ht. w/stem 72-1/2"; wire 10'.
One medium base lamp,
60w max.

All fixtures shown with F4T10DLED927/JA8 LED lamps, not included. See page 824.

P500241-009



P500242-009



P500241-031



P500242-031



P500241-104



P500242-104



P500241-012



P500242-012





Who says you have to sacrifice form for function?

The versatile Clarion Collection features simple, single clear glass diffuser attached to thin, metal bars for a design that embraces minimalist modernity and functional task lighting.

Neat LED

These timeless and classic LED pendants feature designer oriented details and polished opal glass. Can be displayed singularly or in groupings of two or more in a variety of spaces, such as Modern Farmhouse, Coastal and Mid-Century Modern environments.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ONE-LIGHT PENDANT
P500065-009-30 Brushed Nickel
P500065-020-30 Antique Bronze
4-3/8" dia., 13-1/2" ht.
Overall ht. w/cord 124-1/2"; wire 10'.
One 9w LED module, 3000K, 90CRI, 624 source lumens.

ONE-LIGHT PENDANT
P500066-009-30 Brushed Nickel
P500066-020-30 Antique Bronze
6-5/8" dia., 13-1/2" ht.
Overall ht. w/cord 124-1/2"; wire 10'.
One 9w LED module, 3000K, 90CRI, 624 source lumens.

All fixtures:

JA8

P500065-020-30



P500065-009-30



P500066-020-30



P500066-009-30



Avant LED

A modern LED pendant featuring contrasting textures, including sandblasted glass inside accented by a polished outside surface.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

LED MINI-PENDANT
P5072-0930K9 Brushed Nickel
P5072-2030K9 Antique Bronze
9" dia., 4-3/4" ht.
Overall ht. w/cord 125"; cord 10'.
One 9w LED module 3000K, 90CRI 623 source lumens.

P5072-2030K9



P5072-0930K9




P5176-2030K9


P5176-0930K9

Simple LED

This Simple LED pendant has the LED module tucked inside a frosted acrylic shade. A light commercial pendant ideal for restaurant, bar and hotel applications.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

LED PENDANT
P5176-0930K9 Brushed Nickel
P5176-2030K9 Antique Bronze
5-7/8″ dia., 8-5/8″ ht.
Overall ht. w/cord 130″; cord 10′.
10′. One 9w LED module, 3000K, 90CRI, 624 source lumens.

JA8


P5012-09


P5011-09


P5003-09

Modern Glass

Etched glass diffuser with clear glass accents.

FINISH

- Brushed Nickel - 09

MINI-PENDANT
P5003-09 Brushed Nickel
12-1/4″ dia., 7-1/8″ ht.
Overall ht. w/stem 73″; wire 10′.
One medium base lamp, 100w max.

MINI-PENDANT
P5011-09 Brushed Nickel
12″ dia., 7-1/2″ ht.
Overall ht. w/stem 73″; wire 10′.
One medium base lamp, 100w max.

ONE LIGHT PENDANT
P5012-09 Brushed Nickel
20″ dia., 7-1/2″ ht.
Overall ht. w/stem 73″; wire 10′.
One medium base lamp, 100w max.

Double Glass

Create a focal point with the Double Glass pendant collection's vintage-inspired silhouette. Oversized clear seeded outer glass with an inner etched white glass shade complements linear forms.

FINISHES

- Polished Chrome - 015
- Graphite - 143

MINI-PENDANT
P500018-015 Polished Chrome
P500018-143 Graphite
5-7/8" dia., 10" ht.
Overall ht. w/stem 76"; wire 10'.
One medium base lamp, 100w max.

MINI-PENDANT
P500019-015 Polished Chrome
P500019-143 Graphite
7-3/4" dia., 13-1/2" ht.
Overall ht. w/stem 80"; wire 10'.
One medium base lamp, 100w max.


P500018-015


P500018-143


P500019-015


P500019-143

Cuddle

Organza exterior shade surrounds linen interior shade. Acrylic bottom diffuser.

FINISH

- Brushed Nickel - 09

ONE-LIGHT PENDANT
P5036-09 Brushed Nickel
16" dia., 9-1/4" ht.
Overall ht. w/ one 6" stem 16-1/4";
wire 10'.
One medium base lamp,
100w max.

THREE-LIGHT PENDANT
P5037-09 Brushed Nickel
22" dia., 7-1/4" ht.
Overall ht. w/ one 6" stem 13-3/4";
wire 10'.
Three medium base lamps,
each 100w max.


P5037-09


P5036-09

Pendant LED



P5187-0930K9

This uniquely shaped pendant has a brushed nickel finish with a white linen interior for optimal light output.

FINISH

Brushed Nickel - 09

LED PENDANT
P5187-0930K9 Brushed Nickel
10″ dia., 10-3/4″ ht.
Overall ht. w/stem 77″; wire 10′.
One 17w LED module, 3000K,
90CRI, 1211 source lumens.

Pure LED



P5175-0930K9

Cord hung LED pendants with design oriented details. Brushed Nickel with a gloss white interior.

FINISH

Brushed Nickel - 09

LED PENDANT
P5175-0930K9 Brushed Nickel
6-1/2″ dia., 8-7/8″ ht.
Overall ht. w/cord 130″; wire 10′.
One 9w LED module, 3000K,
90CRI, 623 source lumens.

Clear Glass



P5184-104

Hand blown clear glass shade exposes a hint of Polished Nickel.

FINISH

Polished Nickel - 104

MINI-PENDANT
P5184-104 Polished Nickel
8″ dia., 9-3/4″ ht.
Overall ht. w/stem 52″; wire 10′.
One medium base lamp,
100w max.

Etched and Clear Glass

Clear glass with etched linear pattern and Brushed Nickel finish.

FINISH

Brushed Nickel - 09

MINI-PENDANT
P5158-09 Brushed Nickel
3-7/8" dia., 7-1/4" ht.
Overall ht. w/stem 49"; wire 10'.
One medium base lamp,
100w max.



Classic Dome

The elegantly simple design of the glass dome pendant complements a wide array of home styles. A classic form, the pendant is available in four popular finishes.

FINISHES

Brushed Nickel - 009
Polished Chrome - 015
Antique Bronze - 020
Graphite - 143

ONE-LIGHT PENDANT
P500149-009 Brushed Nickel
P500149-015 Polished Chrome
P500149-020 Antique Bronze
P500149-143 Graphite
15" dia., 8-1/8" ht.
Overall ht. w/chain 46"; wire 10'.
One medium base lamp,
each 100w max.









P5087-09



P5094-09
P5094-0930K9



P5094-30



P5094-31



P5094-45



P5094-74
P5094-7430K9



P5068-09



Warehouse Pendant

Smooth cord hung metal shade with white inner-lining.

FINISHES

- Brushed Nickel - 09
- White - 30
- Matte Black - 31
- Dark Green - 45
- Venetian Bronze - 74

MINI-PENDANT
P5087-09 Brushed Nickel
Cord-hung pendant with white inner-lined metal shade.
10-1/8" dia., 6-1/2" ht.; cord 10'.
One medium base lamp, 100w max.

ONE-LIGHT PENDANT
P5094-09 Brushed Nickel
P5094-30 White
P5094-31 Matte Black
P5094-45 Dark Green
P5094-74 Venetian Bronze
Cord hung. White inner-lined metal shade.
16" dia., 7-1/2" ht.
Overall ht. w/cord 129"; cord 10'.
One medium base lamp, 150w max.

LED PENDANT
P5094-0930K9 Brushed Nickel
P5094-7430K9 Venetian Bronze
Cord hung. White inner-lined metal shade.
16" dia., 7-1/2" ht.
Overall ht. w/cord 129"; cord 10'.
One 17w LED module, 3000K, 90 CRI, 1211 source lumens.

Avalon

Etched alabaster glass.

FINISH

- Brushed Nickel - 09

MINI-PENDANT
P5068-09 Brushed Nickel
7-3/4" dia., 6-1/4" ht.
Overall ht. w/stem 63"; wire 10'.
One medium base lamp, 100w max.

Prismatic Glass

A bold and striking prismatic glass shade held within strip metal detailing offers true industrial styling.

FINISH

Brushed Nickel - 09

MINI-PENDANT
P5080-09 Brushed Nickel
6-3/4″ dia., 7″ ht.
Overall ht. w/chain 42″; wire 10′.
One medium base lamp,
100w max.

ONE-LIGHT PENDANT
P5103-09 Brushed Nickel
15-1/4″ dia., 11″ ht.
Overall ht. w/chain 71″; wire 13′.
One medium base lamp,
150w max.


P5080-09


P5103-09

Alabaster Glass

Scrolling details accentuate soft curves.

FINISH

Brushed Nickel - 09

ONE LIGHT PENDANT
P5091-09 Brushed Nickel
15-3/8″ dia., 16-1/2″ ht.
Overall ht. w/chain 56″; wire 10′.
One medium base lamp, 100w max.


P5091-09

Satin Opal Glass

Satin opal glass with Brushed Nickel trim.

FINISH

Brushed Nickel - 09

ONE LIGHT PENDANT
P5013-09 Brushed Nickel
16-5/8″ dia., 8-7/8″ ht.
Overall ht. w/chain 46″; wire 10′.
One medium base lamp,
100w max.


P5013-09

Opal Globes


P4401-29


P4402-29


P4403-29


P4406-29

Opal glass globes. White cord, canopy and cap.

FINISH

○ White - 29

P4401-29 White
8″ dia., 8″ ht.
Overall ht. w/cord 48″.
One medium base lamp, 60w max.

P4402-29 White
10″ dia., 10″ ht.
Overall ht. w/cord 50″.
One medium base lamp, 100w max.

P4403-29 White
12″ dia., 12″ ht.
Overall ht. w/cord 52″.
One medium base lamp, 150w max.

P4406-29 White
14″ dia., 14″ ht.
Overall ht. w/cord 54″.
One medium base lamp, 150w max.




Featuring Opal Globes
Image: Anice Hoachlander

Pendant and Mini-Pendant Accessories


Socket Collar Tool

The socket collar tool provides extra leverage and eliminates a loose fit when installing glass shades. Working like a wrench, the socket collar tool extends into the shade and tightens the socket ring, securing the shade in place, and can reverse to loosen the ring to remove the shade. This accessory can be used on a variety of fixtures, including chandeliers, mini-pendants, sconces and wall brackets.

P8685-01 Socket Collar Tool
2-5/8″ dia., 7-7/8″ tall.



P8685-01




Stem Kits

Contains (2) 12″ and (2) 15″ sections.

P8601-09 Brushed Nickel
P8601-12 Satin Brass
P8601-15 Chrome
P8601-20 Antique Bronze
P8601-31 Black
P8601-71 Gilded Iron
P8601-74 Venetian Bronze
P8601-77 Forged Bronze
P8601-78 Vintage Gold
P8601-81 Antique Nickel
P8601-104 Polished Nickel
P8601-108 Oil Rubbed Bronze
P8601-109 Brushed Bronze
P8601-134 Silver Ridge
P8601-137 Natural Brass
P8601-141 Galvanized
P8601-143 Graphite
P8601-160 Brushed Brass
P8601-161 Maliblue

Contains (2) 6″ and (1) 12″ stem.

P8602-09 Brushed Nickel
P8602-20 Antique Bronze



Socket/Cord Kit for Higher Ceilings

Provides additional length to cord-hung fixtures (only) for installations on high ceilings and in stairwells. For use with P4401, P4402, P4403, P4406, and P5094.
P8625-30 White
15′ cord with socket for replacement on cord-hung pendants.



P8625-30

Loop and Chain Hang Kit

Converts any stem-hung pendant to sloped ceiling applications.

P8678-09 Brushed Nickel
P8678-20 Antique Bronze
P8678-104 Polished Nickel
7/8″ dia., 9-1/2″ ht.
Kit includes (6) chain links, (2) 1/8″ I.P. loops, (2) 1/8″ I.P. x 9/16″ nipples, (1) hex nut, (1) int. lock washer, and (1) 12″ piece of fiberglass sleeving.



P8678-20

All items on this spread not UL listed.

Shades

The optional shades are available for use with candelabra-based fixtures. Bent tip lamps not recommended for shades with spring clip attachment.

P8704-01 White Fabric
1" candle fitter.
5-1/2" top, 6" bottom, 4-3/4" ht.

P8926-01 Off-White Linen Fabric
Spring clip.
5-1/2" dia., 4-7/8" ht.

P860007-000 Ivory Silk
1" uno-style candle fitter
5-3/4" dia., 4-1/2" ht.

P860008-000 Vintage Linen
1" uno-style candle fitter
5-3/4" dia., 4-1/2" ht.

P860041-000 Natural Burlap
1" uno-style candle fitter
6" dia., 5-1/8" ht.

P860042-000 Flax Linen
1" uno-style candle fitter
6" dia., 5-1/8" ht.

P860027-000 White Sailcloth
1" uno-style candle fitter
6-3/4" dia., 5" ht.


P8704-01


P860007-000


P860041-000


P8926-01


P860008-000


P860042-000

P860027-000

Chain

6-Gauge Chain

P8759-77 Forged Bronze
P8759-104 Polished Nickel
P8759-160 Brushed Brass
P8759-161 Maliblue

- 10 feet of 6 gauge chain permits installation large chain-hung fixtures on high ceilings.
- Maximum fixture weight – 120 lbs.


P8759-104

9-Gauge Chain

P8757-09 Brushed Nickel
P8757-10 Polished Brass
P8757-15 Polished Chrome
P8757-20 Antique Bronze
P8757-31 Textured Black
P8757-71 Gilded Iron
P8757-74 Venetian Bronze
P8757-77 Forged Bronze
P8757-78 Vintage Gold
P8757-81 Antique Nickel
P8757-104 Polished Nickel
P8757-108 Oil Rubbed Bronze
P8757-109 Brushed Bronze
P8757-126 Burnished Silver
P8757-134 Silver Ridge
P8757-137 Natural Brass
P8757-141 Galvanized
P8757-143 Graphite

- 10 feet of 9 gauge chain permits installation of large chain-hung fixtures on high ceilings.
- Maximum fixture weight – 50 lbs.


P8757-78


All items on this spread not UL listed.


Featuring Springer and Briarwood

Ceiling Fans

Flow through Your Home

Scan and see more at
progresslighting.com





Steve Register
Product Manager, Ceiling Fans

Modern + Edgy

with Steve

Quirky and functional, this style's flair comes from its modern, yet retro, juxtaposition. Mid-Century Modern style furniture adds unique shapes and pops of color to a room. Designers look for statement pieces to complete the look. This style is gravitating toward a cleaner, more minimalistic look through the incorporation of a neutral palette and softer accent colors. Mid-Century Modern homes are largely characterized by the use of wood textures to create a sense of connection to nature and the outdoors.

Shop this style at
progresslighting.com/mid-century-modern




Springer

FINISHES
- Antique Nickel - 081
- Architectural Bronze - 129

P250000-081
shown with White Barnwood blades

Springer is a statement-making ceiling fan with a rustic flair. The 12-blade, 60″ ceiling fan was inspired by the form and function of a windmill and is ideal for Farmhouse, Industrial and Transitional interior settings. A full function remote control with batteries is included along with a dual mount canopy that accommodates flat or sloped ceilings.



Springer

P250000-081 Antique Nickel

White Barnwood

P250000-129 Architectural Bronze

Distressed Walnut



P250000-081
shown with White Barnwood blades



P250000-129
shown with Distressed Walnut blades

ENERGY INFORMATION AT HIGH SPEED	
Airflow	6,377 cubic feet per minute
Electricity Use	33 watts (excludes lights)
DOE Weighted CFM/W	206 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-22°)
- DC Motor
- Plywood blades
- Full function remote control with batteries is included

SIZE

60″ dia., 17-3/8″ ht.
80″ lead wires.



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

Farris

FINISHES
- Brushed Nickel - 009
- Oil Rubbed Bronze - 108
- Graphite - 143

P250002-108-30
shown with Walnut blades

Farris features three solid wood carved blades to form a sleek, modern design. The 60″ ceiling fan includes an integrated LED light kit that is removable to provide the option in non-illuminated applications. Available in Brushed Nickel, Oil Rubbed Bronze and Graphite finishes. A full function remote control with batteries is included, and the dual mount canopy accommodates flat or sloped ceilings.



Farris



P250002-009-30
shown with Gray Weathered Wood blades



P250002-108-30
shown with Walnut blades
and light kit removed



P250002-143-30
shown with Driftwood blades

P250002-009-30 Brushed Nickel

Gray Weathered Wood

P250002-108-30 Oil Rubbed Bronze

Walnut

P250002-143-30 Graphite

Driftwood

ENERGY INFORMATION AT HIGH SPEED

Airflow	7,047 cubic feet per minute
Electricity Use	32 watts (excludes lights)
DOE Weighted CFM/W	223 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-13°)
- DC Motor
- Carved wood blades
- Removable light kit
- White opal shatterproof shade
- Full function remote control with batteries is included

SIZE

60″ dia., 15-1/2″ ht.
80″ lead wires.

LAMP

18w LED Module, 3000K, 90 CRI, 1400 lumens, dimmable.

T20 JA8


Gulliver

FINISHES
- Galvanized - 141
- Graphite - 143

P250012-141-22
shown with Antique White Wood

Three circular bands wrap together to create an open design for . Fan blades enclosed within a stylish cage design gives the rustic charm of a pendant combined with the functionality of a ceiling fan. Dual toned frame color combinations of Galvanized with antique white accents or Graphite with weathered gray accents. A hand painted wood grained texture complements Rustic and Modern Farmhouse home decor, as well as Urban Industrial and Coastal interior settings.

Urban Industrial Design



Rustic Charm

Hand-Painted Wood

Gulliver

P250012-141-22 Galvanized

Antique White Wood

P250012-143-22 Galvanized

Gray Wood



P250012-141-22
shown with Antique White Wood



P250012-143-22
shown with Gray Wood

ENERGY INFORMATION AT HIGH SPEED

Airflow	1,297 cubic feet per minute
Electricity Use	39 watts (excludes lights)
Airflow Efficiency	33 cubic feet per minute per watt



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible Motor
- Remote control with batteries is included
- Rust-proof non-metallic blades

SIZE

23″ dia., 18-1/8″ ht.
80″ lead wires.

LAMP

Three LED medium base vintage lamps, 2200K, 80 CRI, 5.5w max each, included, dimmable.

T20

Loring

FINISHES
- Black- 031
- Galvanized - 141

P250006-031
shown with Matte Black blades

Outfitted with stylish mixed metal elements, the Loring Collection shows off an industrial-inspired, open-cage design. Four plywood blades and a handy remote control are ready to help you and your family stay comfortable and relaxed all year round.

Open-Cage Design



Industrial Inspired

Mixed-Metal Elements

Loring

P250006-031 Black

Matte Black

Distressed Ebony

P250006-141 Galvanized

White Barnwood

Driftwood



P250006-031
shown with Gold accent
and Distressed Ebony blades



P250006-141
shown with Matte Black accent
and White Barnwood blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	1,766 cubic feet per minute
Electricity Use	43 watts (excludes lights)
DOE Weighted CFM/W	44 CFM/W



Three Speed Remote Control Included
Three-speed fan operation

FEATURES

- Limited lifetime warranty
- Close-to-ceiling installation
- AC Motor
- Reversible plywood blades
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

33″ dia., 15-1/4″ ht.
80″ lead wires.

Sanford

FINISHES
- Brushed Nickel - 009
- Architectural Bronze - 129

P2594-12930K

Sanford delivers ultra powerful air movement and energy efficient illumination packaged in a modern design. Ideal for both interior and outdoor settings, this "fandelier" adds a contemporary style to porches, foyers, bath and vanity areas providing a wide range of applications. Sanford includes an integrated 23W LED module, offering both form and function with energy and cost-savings benefits. A three-speed remote control is included.

Indoor or Outdoor Use

Contemporary Style



Powerful Air Movement

Sanford

P2594-0930K Brushed Nickel

P2594-12930K Architectural Bronze



P2594-0930K



P2594-12930K

ENERGY INFORMATION AT HIGH SPEED

Airflow	1,008 cubic feet per minute
Electricity Use	37 watts (excludes lights)
DOE Weighted CFM/W	27 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Metal blades
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

22-7/8" dia., 17-3/4" ht.
80" lead wires.

LAMP

23w LED Module, 3000K,
90 CRI, dimmable.

T20


Ellwood

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

P2546-09
shown with Driftwood blades

A picture of modern design, the functional minimalism of the Ellwood 68″ ceiling fan is a product of advanced design. Five long and graceful blades made of carved wood move air with remarkable efficiency. Ellwood features a dual mount system and is compatible with universal light kits. A full function remote control is included.



Ellwood

P2546-09 Brushed Nickel

Driftwood

P2546-20 Antique Bronze

Walnut



P2546-09
shown with Driftwood blades



P2546-20
shown with Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	7,587 cubic feet per minute
Electricity Use	90 watts (excludes lights)
DOE Weighted CFM/W	92 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Patented carved Wood blades
- Compatible with universal light kits
- Remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control

SIZE

68″ dia., 16-3/4″ ht.
80″ lead wires.

T20

Caleb

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

P2560-20
shown with Walnut Blades

Beautiful and expansive in design, the 68″ Caleb ceiling fan is ideal for use in large spaces. Bent Carved Wood blades are paired with either Brushed Nickel or Antique Bronze finishes. Caleb features a dual mount system and is compatible with universal light kits. A full function remote control is included.



Caleb

P2560-09 Brushed Nickel

Medium Cherry

P2560-20 Antique Bronze

Walnut



P2560-09
shown with Medium Cherry blades



P2560-20
shown with Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	7,045 cubic feet per minute
Electricity Use	86 watts (excludes lights)
DOE Weighted CFM/W	91 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Patented bent carved wood blades
- Compatible with universal light kits
- Remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control

SIZE

68″ dia., 18″ ht.
80″ lead wires.


T20

Huff

FINISHES
- Brushed Nickel - 009
- Satin White- 028
- Black- 031

P250030-009
shown with Brushed Nickel blades

The hassles and headaches of the day fade away under the relaxing airflow created by the Huff Collection. Six expansive aluminum blades with decorative winglets stretch out from a dual mount center. Select a brushed nickel, matte white, or matte black finish all with their own complementary highlights to create a perfect design for your modern or transitional space.



Huff



P250030-009
shown with Brushed Nickel blades



P250030-028
shown with Satin White blades



P250030-031
shown with Black blades

P250030-009 Brushed Nickel

Brushed Nickel

P250030-028 Satin White

Satin White

P250030-031 Black

Black

ENERGY INFORMATION AT HIGH SPEED

Airflow	14,482 cubic feet per minute
Electricity Use	49 watts (excludes lights)
DOE Weighted CFM/W	344 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminum blades
- Compatible with universal light kit
- Remote control with batteries is included

SIZE

96″ dia., 15-1/2″ ht.
80″ lead wires.

Vast

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30
- Black - 31

P2550-3130K
shown with Black blades

Beautiful and expansive in design, the 72″ Vast ceiling fan is ideal for use in large areas and outdoor covered areas for maximum cooling. A white opal shade complements a variety of finish options, including Brushed Nickel with Chrome accents, Antique Bronze, White with Chrome accents or Matte Black. Vast features a dual mount system and comes with a full function remote control.



Vast



P2550-0930K
shown with Brushed Nickel blades and Chrome accents



P2550-2030K
shown with Antique Bronze blades



P2550-3030K
shown with White blades and Chrome accents



P2550-3130K
shown with Black blades

P2550-0930K Brushed Nickel

Brushed Nickel

P2550-2030K Antique Bronze

Antique Bronze

P2550-3030K White

White

P2550-3130K Black

Black

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,933 cubic feet per minute
Electricity Use	21 watts (excludes lights)
DOE Weighted CFN/W	322 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminum blades
- White opal glass
- Remote control with batteries is included

SIZE

72″ dia., 16-3/4″ ht
80″ lead wires.

LAMP

18w LED Module, 3000K, 90 CRI, 1400 lumens, dimmable.


T20 JA8

Arlo

FINISHES
- Brushed Nickel - 009
- Black - 031
- Architectural Bronze - 129

P250026-009-30
shown with Brushed Nickel blades

Unwind under the cooling breeze created by the clean, crisp blades of the Arlo Collection's modern ceiling fan. A central LED light provides a perfect way to light a space without flooding the room with harsh light as six metal blades attach to the fan's center. Offered in three different finishes, Arlo is sure to create an intriguing, yet serene retreat in whatever space it calls home.



Arlo



P250026-009-30
shown with Brushed Nickel blades



P250026-031-30
shown with Black blades



P250026-129-30
shown with Architectural Bronze blades

P250026-009-30 Brushed Nickel

Brushed Nickel

P250026-031-30 Black

Black

P250026-129-30 Architectural Bronze

Architectural Bronze

ENERGY INFORMATION AT HIGH SPEED

Airflow	7,558 cubic feet per minute
Electricity Use	29 watts (excludes lights)
DOE Weighted CFM/W	282 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Aluminium blades
- White Opal glass
- Remote control with batteries is included

SIZE

60″ dia., 18-1/2″ ht.
80″ lead wires.

LAMP

24w LED Module, 3000K, 90 CRI, 2000 lumens, dimmable.


JA8

Bixby

FINISHES
○ White - 030
● Black Chrome - 231

P250038-031-30
shown with Black Smoked Transluscent blades

You'll find the time to unwind under the eye-pleasing, urban industrial design of the Bixby collection's ceiling fan. Breathe easy after a warm summer day or a long day at work as Bixby fosters a refreshing current of cool air with three, slightly curved Lucite blades circling a gentle LED light as it provides soothing illumination.



Bixby

P250038-030-30 White

Milk Washed Clear

P250038-231-30 Black Chrome

Black Smoked Translucent



P250038-030-30
shown with Milk Washed Clear blades



P250038-231-30
shown with Black Smoked Translucent blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,846 cubic feet per minute
Electricity Use	32 watts (excludes lights)
DOE Weighted CFM/W	228 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Polycarbonate blades
- White Opal glass
- Remote control with batteries is included

SIZE

60″ dia., 15-1/8″ ht.
80″ lead wires.

LAMP

24w LED Module,
3000K, 90 CRI,
2000 lumens, dimmable.


Gaze

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20
- Black - 31

P2554-0930K
shown with Silver blades

Three-blade 60″ Gaze ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. An opal white shade contains an 18W dimmable, 3000K LED module. Gaze features a dual mount system and includes a three-speed remote control with full range dimming.



Gaze



P2554-0930K
shown with Silver blades



P2554-1530K
shown with White Washed blades



P2554-2030K
shown with Cherry blades



P2554-3130K
shown with Matte Black blades

P2554-0930K Brushed Nickel



Silver

Cherry

P2554-1530K Polished Chrome



White Washed

Cherry

P2554-2030K Antique Bronze



Walnut

Cherry

P2554-3130K Black



Matte Black

Distressed Ebony

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,902 cubic feet per minute
Electricity Use	75 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White shatterproof lens
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

60″ dia., 13-1/8″ ht.
80″ lead wires.

T20 JA8

Spades

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Graphite - 143

P2570-15
shown with Black blades

The 56″ Spades ceiling fan features a sleek contemporary two-blade design that is finished in Brushed Nickel, Polished Chrome or Graphite options. Spades features a dual mount system, an energy saving DC motor and ABS composite blades. A full function remote control is included.



Spades

P2570-09 Brushed Nickel

Silver

P2570-15 Polished Chrome

Black

P2570-143 Graphite

Graphite



P2570-09
shown with Silver blades



P2570-15
shown with Black blades



P2570-143
shown with Graphite blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,746 cubic feet per minute
Electricity Use	32 watts (excludes lights)
DOE Weighted CFM/W	215 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

FEATURES


- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-17°)
- Close-to-ceiling installation
- DC Motor
- Non-reversible ABS blades
- Remote control with batteries is included

SIZE

56″ dia., 18-1/8″ ht
80″ lead wires.

T20

CTC INSTALLATION



Holland

Enjoy nothing but first-rate design inspiration with the gorgeous Holland Collection. Four simple, yet stunning blades blend style with sustainability as they anchor to a sleek, dual mount center. An integrated LED light is ready to offer a gentle glow along with the fan's refreshing breeze. With the versatility to be installed in indoor or outdoor locations, this fan will make a design statement in any modern or transitional setting.

FINISHES
- Brushed Nickel - 009
- Black- 031
- Oil Rubbed Bronze - 108

P250032-009-30 Brushed Nickel

Silver

P250032-031-30 Black

Black

P250032-108-30 Oil Rubbed Bronze

Walnut



P250032-009-30
shown with Silver blades



P250032-031-30
shown with Black blades



P250032-108-30
shown with Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	7,035 cubic feet per minute
Electricity Use	31 watts (excludes lights)
DOE Weighted CFM/W	257 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White Opal glass
- Remote control with batteries is included

SIZE

60" dia., 13-5/8" ht.
80" lead wires.

LAMP

24w LED Module, 3000K, 90 CRI, 2000 lumens, dimmable.

JA8

Oriole



P2592-0930K
shown with Silver blades



P2592-3130K
shown with Black blades
and light kit removed
using blank plate



P2592-12930K
shown with Architectural Bronze blades

This 60″ Oriole ceiling fan is the perfect addition to interior garages, industrial shops or commercial buildings to distribute the right amount of air and keep the space cool and comfortable. Oriole contains an integrated 18W LED module, with an optional finishing cap offering the user the choice to install with or without the light kit. A remote control is included to adjust speed and turn on/off the light or fan. A blank off plate comes standard.

FINISHES

- Brushed Nickel - 09
- Black - 31
- Architectural Bronze - 129

P2592-0930K Brushed Nickel

Silver

P2592-3130K Black

Black

P2592-12930K Architectural Bronze

Architectural Bronze

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,171 cubic feet per minute
Electricity Use	51 watts (excludes lights)
DOE Weighted CFM/W	132 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- ABS blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

68″ dia., 18″ ht.
80″ lead wires.

LAMP

18w LED Module, 3000K, 90 CRI, 1400 lumens, dimmable.

T20 JA8

Teasley

Featuring coastal influences and farmhouse charm, the Teasley 56" 5-blade ceiling fan is suitable for a variety of interior settings. Clear seeded bell-shaped glass shades highlight Architectural Bronze, Graphite or Galvanized finish options. Three vintage LED lamps are included, offering energy efficiency and cost savings benefits for the home, while a dual mount canopy accommodates flat or sloped ceilings.




P250004-129
shown with Brushed Bronze accents and American Walnut blades

FINISHES

- Architectural Bronze - 129
- Galvanized - 141
- Graphite - 143

P250004-129 Architectural Bronze



Distressed Walnut

American Walnut



P250004-141
shown with Brushed Nickel accents and Gray Weathered Wood blades

P250004-141 Galvanized



Driftwood

Gray Weathered Wood

P250004-143 Graphite



American Walnut

Gray Weathered Wood



P250004-143
shown with Brushed Nickel accents and Gray Weathered Wood blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,749 cubic feet per minute
Electricity Use	76 watts (excludes lights)
DOE Weighted CFM/W	88 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible plywood blades
- Clear seeded glass shades
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

56" dia., 22-1/2" ht.
80" lead wires.

LAMP

Three medium base vintage lamps, each 7w max included, dimmable.

Royer

The Royer Collection's ceiling fan offers a charming, rustic look ideal for farmhouse and rustic spaces in need of a fresh breeze. Four plywood blades attach to the fixture's center by finely detailed metal arms. The crafted center is available in three finishes so you can select the perfect piece to complement your home décor.



P250010-080
shown with Distressed Ebony blades



P250010-080
shown with Matte Black blades



P250010-081
shown with Driftwood blades



P250010-081
shown with Chesnut blades

FINISHES
- Antique Nickel - 081
- Forged Black- 080


P250010-080 Forged Black



Matte Black

Distressed Ebony

P250010-081 Antique Nickel



Driftwood

Chesnut

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,255 cubic feet per minute
Electricity Use	67 watts (excludes lights)
DOE Weighted CFM/W	102 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Not compatible with light kit
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

60″ dia., 17-7/8″ ht.
80″ lead wires.


Glandon

Glandon offers a sophisticated design that is ideal for settings requiring a touch of modern flair. Six reversible blades in a Walnut/Driftwood faux wood finish are strapped by a sleek Antique Nickel metal bar for an unexpected industrial detail. The 60″ Glandon ceiling fan features a 17w LED module (3000K color temperature) with a shatterproof white opal shade finish and a dual mount system. Full range dimming and remote control is included.

FINISHES

- Gilded Iron - 71
- Antique Nickel - 81

P2586-7130K Gilded Iron



Driftwood

Toasted Oak

P2586-8130K Antique Nickel



Driftwood

Classic Walnut



P2586-7130K
shown with Toasted Oak blades



P2586-8130K
shown with Classic Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,036 cubic feet per minute
Electricity Use	84 watts (excludes lights)
DOE Weighted CFM/W	96 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal glass
- Remote control with batteries is included

SIZE

60″ dia., 17-1/8″ ht
80″ lead wires.

LAMP

17w LED Module,
3000K, 90 CRI,
1400 lumens, dimmable.

T20 JA8

Greer

This five-blade 54" Greer ceiling fan complements either industrial or farmhouse decor. It comes with a wire meshed shade light kit that uses two vintage LED lamps (included). Remote control is also included. Greer can be hung on a flat or sloped ceiling due to its dual mount system.




P2584-71
shown with Toasted Oak blades

FINISHES

- Gilded Iron - 71
- Antique Nickel - 81

P2584-71 Gilded Iron



Driftwood

Toasted Oak

P2584-81 Antique Nickel



Driftwood

Classic Walnut



P2584-81
shown with Driftwood blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,794 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	82 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-45°)
- AC Motor
- Reversible plywood blades
- Wire basket shade light kit
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 wall control

SIZE

54" dia., 21-5/8" ht
80" lead wires.

LAMP

Two medium base vintage lamps, each 5.5w max included, dimmable.

Fixtures shown with V6.55T19DLED922/JA8 vintage lamps.

Chapin

The Chapin Collection effortlessly unites a spacious room, creating an atmosphere that's both relaxing and reviving. Antique nickel, graphite, or oil rubbed bronze finishes complement each other with four plywood blades and a dual mount canopy for a design destined to provide a truly relaxing experience.



P250022-081
shown with Driftwood blades

FINISHES
- Antique Nickel - 081
- Oil Rubbed Bronze - 108
- Graphite - 143

P250022-081 Antique Nickel




Driftwood

Classic Walnut



P250022-108
shown with Distressed Walnut blades

P250022-108 Oil Rubbed Bronze



Distressed Walnut

American Walnut

P250022-143 Graphite



Graphite

Gray Weathered Wood



P250022-143
shown with Graphite blades

ENERGY INFORMATION AT HIGH SPEED	
Airflow	6,543 cubic feet per minute
Electricity Use	81 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation

FEATURES
- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE


54" dia., 14-1/2" ht.
80" lead wires.

Bedwin


Recall charming, rustic lattice work with the Bedwin Collection's farmhouse-inspired ceiling fan. With three finishes to pick from and four rough hewn plywood blades circling a handsome dual mount canopy, this ceiling fan is sure to help transform any living space into a cool paradise of relaxation.



P250024-081
shown with Driftwood blades



P250024-141
shown with Gray Weathered Wood blades



P250024-143
shown with Graphite blades

FINISHES

- Antique Nickel - 081
- Galvanized - 141
- Graphite - 143


P250024-081 Antique Nickel



Driftwood

Classic Walnut

P250024-141 Galvanized



Driftwood

Gray Weathered Wood

P250024-143 Graphite



Graphite

Gray Weathered Wood

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,044 cubic feet per minute
Electricity Use	34 watts (excludes lights)
DOE Weighted CFM/W	192 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- Reversible plywood blades
- Compatible with universal light kits
- Remote control with batteries is included

SIZE

56″ dia., 15-1/2″ ht.
80″ lead wires.

Shaffer

The 4-blade 56″ Shaffer ceiling fan blends a streamlined design with mixed metal elements and a wire mesh housing, suitable for modern and urban industrial spaces. Available in Satin White with galvanized accents, Forged Black with chrome accents and Architectural Bronze with brushed bronze accents. Shaffer features a dual mount system and includes a remote control with batteries.



P2590-28
shown with Galvanized accents and Silver blades

FINISHES

- ○ Satin White - 28
- ● Forged Black - 80
- ● Architectural Bronze - 129

P2590-28 Satin White

- Silver
- White



P2590-80
shown with Chrome accents and Black blades

P2590-80 Forged Black

- Black
- Silver

P2590-129 Architectural Bronze

- Driftwood
- Natural Cherry



P2590-129
shown with Brushed Bronze accents and Driftwood blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,144 cubic feet per minute
Electricity Use	67 watts (excludes lights)
DOE Weighted CFM/W	99 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible plywood blades
- Not compatible with light kits
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

56″ dia., 16-1/4″ ht.
80″ lead wires.

T20

Soar

With a white opal shade and a 17W dimmable LED module, the 54" Soar ceiling fan offers energy and cost-savings benefits for a variety of living spaces. The four-blade fan comes with a remote control and is available in Brushed Nickel, Antique Bronze and White finishes. LED source features a 3000K-color temperature. Soar features a dual mount system and includes a remote control with batteries.



P2542-0930K
shown with Black blades



P2542-2030K
shown with Walnut blades



P2542-3030K
shown with White blades

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2542-0930K Brushed Nickel

Black

P2542-2030K Antique Bronze

Walnut

P2542-3030K White

White

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,814 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	83 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Non-reversible plywood blades
- White opal shatterproof lens
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 15" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI, 1400 lumens, dimmable.

T20 JA8

Harranvale

The 54" Harranvale features a design that incorporates mixed metal design details that is very popular in today's home decor. Featuring reversible blades and opal glass shade, fans are available in three finish options: Antique Bronze with Brushed Bronze accent; Graphite with Brushed Nickel accent; and White with Brushed Nickel accent. Harranvale features a dual mount system and includes a remote control with batteries.

FINISHES

- Antique Bronze - 20
- White - 30
- Graphite - 143

P2540-2030K Antique Bronze



Classic Walnut


Medium Cherry

P2540-3030K White

White

White

P2540-14330K Graphite



Graphite

American Walnut



P2540-2030K
shown with Brushed Bronze accent and Medium Cherry blades



P2540-3030K
shown with Brushed Nickel accent and White blades



P2540-14330K
shown with Brushed Nickel accent and Graphite blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,121 cubic feet per minute
Electricity Use	66 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 16-3/8" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI, 1400 lumens, dimmable.

T20 JA8

Graceful

Refresh your living space with the crisp, clean style of the 54" Graceful fan. With a white opal glass shade and a 17W dimmable LED module, the five-blade fan comes with a remote control and is available in Brushed Nickel, Polished Chrome and Antique Bronze finishes. LED source offers a 3000K-color temperature, energy savings and maintenance benefits for the home.



P2544-0930K
shown with Medium Cherry blades



P2544-1530K
shown with Silver blades




P2544-2030K
shown with American Walnut blades

FINISHES


- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

P2544-0930K Brushed Nickel



Medium Cherry
Silver

P2544-1530K Polished Chrome



Toasted Oak
Silver

P2544-2030K Antique Bronze



Medium Cherry
American Walnut

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,454 cubic feet per minute
Electricity Use	60 watts (excludes lights)
DOE Weighted CFM/W	83 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 16-3/8" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI, 1400 lumens, dimmable.

T20 JA8

Olson

The 52″ Olson ceiling fan features a generously sized etched watermark glass shade and sweeping blades highlighted with metal accents in a Brushed Nickel or Graphite finish. Two LED lamps are JA8 compliant, offering both form and function with energy and cost-savings benefits. Olson features a dual mount system and a three-speed pull chain fan switch, as well as an on/off pull chain switch to operate the light.

FINISHES

- Brushed Nickel - 09
- Graphite - 143


P2598-09 Brushed Nickel



Medium Cherry

Classic Walnut

P2598-143 Graphite



Gray Weathered Wood

Graphite



P2598-09
shown with Medium Cherry blades



P2598-143
shown with Gray Weathered Wood blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,023 cubic feet per minute
Electricity Use	70 watts (excludes lights)
DOE Weighted CFM/W	83 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- Reversible plywood blades
- Etched watermark glass
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control, P2661-01 or P2662-01 hand-held remote control

SIZE

52″ dia., 21-5/16″ ht.
80″ lead wires.

LAMP

Two Medium base LED lamps, 3000K, 90 CRI, 800 lumens, dimmable.

T20 JA8

Gust

This five-blade 54" Gust ceiling fan features a white opal glass shade that is available in a Brushed Nickel, Graphite or Antique Bronze finish. A remote control is included. Gust has a dual mount system to offer greater flexibility when installing. The 18W dimmable, 3000K LED module provides energy and cost-savings benefits to the homeowner.



P2582-0930K
Shown with Silver blades



P2582-2030K
Shown with Walnut blades



P2582-14330K
Shown with Graphite blades

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Graphite - 143

P2582-0930K Brushed Nickel

Silver

P2582-2030K Antique Bronze

Walnut

P2582-14330K Graphite

Graphite

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,242 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Non-reversible plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 16" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI, 1400 lumens, dimmable.

T20 JA8

Kudos

This five-blade 52" Kudos ceiling fan features a clear Fresnel glass shade. Available in a Brushed Nickel, Polished Chrome or Antique Bronze finish and includes a remote control. The Kudos features a dual mount system to offer greater flexibility when installing. The 18W dimmable, 3000K LED module provides energy and cost-savings benefits to the homeowner.



P2568-0930K
shown with American Walnut blades



P2568-1530K
shown with Black blades




P2568-2030K
shown with Cherry blades

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

P2568-0930K Brushed Nickel



American Walnut

Silver

P2568-1530K Polished Chrome



Medium Cherry

Black

P2568-2030K Antique Bronze



Walnut

Cherry

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,160 cubic feet per minute
Electricity Use	60 watts (excludes lights)
DOE Weighted CFM/W	91 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible plywood Blades
- Clear Fresnel glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

52" dia., 17-5/8" ht.
80" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI, 1400 lumens, dimmable.

T20 JA8

Fresno

Five-blade 60″ Fresno ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. A white opal glass shade features an 18W dimmable, 3000K LED module. A remote control with full range dimming and remote control is included.



P2548-0930K
shown with Silver blades



P2548-2030K
shown with Dark Walnut blades



P2548-3030K
shown with White blades

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2548-0930K Brushed Nickel



Black
Silver

P2548-2030K Antique Bronze



Cherry
Dark Walnut

P2548-3030K White

White
White

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,718 cubic feet per minute
Electricity Use	79 watts (excludes lights)
DOE Weighted CFM/W	80 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-17.5°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries is included, receiver mounted in motor.
- Remote control may be replaced with P2631-30 wall control

SIZE

60″ dia., 17-1/4″ ht.
80″ lead wires.

LAMP

18w LED Module, 3000K, 90 CRI, 1400 lumens, dimmable.

T20 JA8

Tempt

This five-blade 52" Tempt ceiling fan features a clear, double prismatic glass shade that is available in a Polished Chrome, Antique Bronze or Vintage Brass finish. A remote is included. Tempt features a dual mount system to offer greater flexibility when installing. The 17w dimmable, 3000K LED module provides energy and cost-savings benefits to the homeowner.

FINISHES

- Polished Chrome - 15
- Antique Bronze - 20
- Vintage Brass - 163

P2578-2030K Antique Bronze



Medium Cherry

American Walnut


P2578-1530K Polished Chrome



Medium Cherry

Black

P2578-16330K Vintage Brass



Dark Cherry

Chesnut



P2578-1530K
shown with Black blades



P2578-2030K
shown with American Walnut blades



P2578-16330K
shown with Chesnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,314 cubic feet per minute
Electricity Use	63 watts (excludes lights)
DOE Weighted CFM/W	78 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- Clear double prismatic glass shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

52" dia., 16-1/4" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI, 1400 lumens, dimmable.

T20 JA8

Verada

This five-blade 52" Verada ceiling fan combines a linen glass shade with a 17W LED source. Available in a Brushed Nickel or Antique Bronze finish. Verada features a dual mount system and a three-speed pull chain fan switch, as well as an on/off pull chain switch to operate the light. LED light kit features a 3000K color temperature.



P2558-0930K
shown with white linen glass and American Walnut blades



P2558-2030K
shown with tea stained linen glass and Medium Cherry blades

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

P2558-0930K Brushed Nickel



Medium Cherry

American Walnut

P2558-2030K Antique Bronze



Medium Cherry

American Walnut

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,445 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	79 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- Reversible plywood Blades
- Linen Glass shade
- 3 Speed pull chain switches
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

52" dia., 16" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI, 1400 lumens, dimmable.

T20 JA8

Billows

With a sophisticated and traditional design, the Billows offers both form and function with two energy efficient LED lamps, featuring a 3000K color temperature. The 52" Billows ceiling fan features an LED light kit with white opal glass shade and five reversible blades. The fans are available in Brushed Nickel, Antique Bronze and Forged Black finishes.



P2552-09
shown with Silver blades

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Forged Black - 80

P2552-09 Brushed Nickel




White Washed

Silver



P2552-20
shown with American Walnut blades


P2552-20 Antique Bronze



Cherry

American Walnut

P2552-80 Forged Black



Black

Toasted Oak



P2552-80
shown with Toasted Oak blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,682 cubic feet per minute
Electricity Use	59 watts (excludes lights)
DOE Weighted CFM/W	92 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Reversible plywood blades
- White opal glass
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

52" dia., 17-1/2" ht.
80" lead wires.

LAMP

Two medium base, 3000K, LED lamps included. 90 CRI, 800 lumens/lamp, dimmable (with added remote or wall control).

T20 JA8

Signature



P2521-09
shown with White blades



P2521-09CH
Shown with Cherry blades



P2521-20
Shown with P2602-20WB light kit with Classic Walnut blades*

** Light kit sold separately.*



P2521-77
Shown with Classic Walnut blades



P2521-80
Shown with Dark Cherry blades



P2521-81
Shown with Medium Oak blades

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Forged Bronze - 77
- Forged Black - 80
- Antique Nickel - 81

P2521-09 Brushed Nickel



Natural Cherry
White

P2521-09CH Brushed Nickel



Natural Cherry
Cherry

P2521-09WA Brushed Nickel



Dark Walnut
Classic Walnut

P2521-20 Antique Bronze



Classic Walnut
Medium Cherry

P2521-77 Forged Bronze



Classic Walnut
Medium Cherry

P2521-80 Forged Black



Dark Cherry
Dark Walnut

P2521-81 Antique Nickel



Cherry
Medium Oak

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,701 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	84 CFM/W


FEATURES

- 30-year limited warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2614-01 hand-held remote control

SIZE

52″ dia., 14-5/8″ ht. CTC 11-9/16″ ht.
80″ lead wires.

CTC INSTALLATION



Trevina II 44″

The Trevina Collection features fans with a signature three-blade design. Perfect for modern or traditional interiors, each fan includes an LED light source to help extend your day into the evening as you and your family relax in your peaceful retreat.



P2555-0930K
shown with Silver blades

FINISHES

- Brushed Nickel - 09
- Satin White - 28
- Black - 31

P2555-0930K Brushed Nickel

Silver

P2555-2830K Satin White

White

P2555-3130K Black

Black

Distressed Ebony



P2555-2830K
shown with White blades



P2555-3130K
shown with Distressed Ebony blades

BLANK PLATE
P2668-09 Brushed Nickel
P2668-28 Satin White
P2668-31 Black



P2668-09

P2668-28



P2668-31

ENERGY INFORMATION AT HIGH SPEED

Airflow	4306 cubic feet per minute
Electricity Use	42 watts (excludes lights)
DOE Weighted CFM/W	122 CFM/W



Wall Control Included
Four-speed fan operation
Full-range dimming for light
Includes switch plate cover

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible MDF blades
- White Opal glass
- Compatible with remote or hardwired wall controls (P2630, P2661-01, P2662-01, P2663-01, P2665 (sold separately)

SIZE

44″ dia., 15-5/8″ ht.
80″ lead wires.

LAMP

18w LED Module,
3000K, 90 CRI,
1400 lumens, dimmable.

JA8

Trevina II 52″



P2553-129WB
shown with Medium Cherry blades



P2553-152WB
shown with Black blades

FINISHES

- Architectural Bronze - 129
- Painted Nickel - 152

P2553-129WB Architectural Bronze



Medium Cherry
Classic Walnut

P2553-152WB Painted Nickel



Black
Silver

ENERGY INFORMATION AT HIGH SPEED	
Airflow	5,296 cubic feet per minute
Electricity Use	56 watts (excludes lights)
DOE Weighted CFM/W	112 CFM/W

FEATURES

- Limited lifetime warranty (LED model)
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- Close-to-ceiling installation
- White opal glass
- Reversible plywood blades
- Compatible with remote control or hardwired wall controls (P2618-01, P2630, P2662-01 (sold separately)

SIZE


52″ dia., 15-3/4″ ht.
80″ lead wires.

LAMP

Two 9.5w LED lamps, no switch included.

T20

CTC INSTALLATION



Trevina II 52″



P2556-3030K
shown with White blades



P2556-2030K
shown with Medium Cherry blades



P2556-0930K
shown with Silver blades

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White- 030

P2556-3030K White



White
Natural Cherry

P2556-2030K Antique Bronze



Medium Cherry
Classic Walnut

P2556-0930K Brushed Nickel



Silver

ENERGY INFORMATION AT HIGH SPEED	
Airflow	4,916 cubic feet per minute
Electricity Use	62 watts (excludes lights)
DOE Weighted CFM/W	89 CFM/W



Wall Control Included
Four-speed fan operation
Full-range dimming for light
Includes switch plate cover

FEATURES

- Limited lifetime warranty (LED model)
- Dual Mount (flat or sloped ceiling-30°)
- Close-to-ceiling installation
- AC Motor
- White opal glass
- Reversible plywood blades

SIZE


52″ dia., 15-3/4″ ht.
80″ lead wires.

LAMP

17w LED Module, 3000K, 90 CRI, 1400 lumens, dimmable.

T20 JA8

CTC INSTALLATION



Signature Plus II

Five-blade 54" Signature Plus II ceiling fan features an integrated LED light source, offering both form and function with energy and cost-savings benefits. The light kit contains a white opal shatterproof shade and is comprised of a 17W dimmable 3000K LED module.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2539-0930K Brushed Nickel

Driftwood

Silver

P2539-2030K Antique Bronze

Classic Walnut

Medium Cherry

P2539-3030K White

White

White



P2539-0930K
shown with Silver blades



P2539-2030K
shown with Medium Cherry blades



P2539-3030K
shown with White blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,331 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	92 CFM/W



Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- 45° Canopy
- Downrod mount only
- AC Motor
- Reversible MDF blades
- Opal shatterproof shade
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54" dia., 15-1/2" ht.
80" lead wires.

LAMP

17w LED Module, 3000K, 90 CRI, 1400 lumens, dimmable.

T20 JA8

Signature Plus



P2530-30W
shown with White blades



P2530-09
shown with Silver blades



P2530-20
shown with Classic Walnut blades

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2530-09 Brushed Nickel



Natural Cherry

Silver

P2530-20 Antique Bronze



Classic Walnut

Medium Cherry

P2530-30W White

White

White



P2530-20
shown with P2645-01WB light kit and Classic Walnut blades*
** Light kit sold separately.*

ENERGY INFORMATION AT HIGH SPEED	
Airflow	4,716 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	84 CFM/W

FEATURES

- 30-year limited warranty
- 45° Canopy
- Downrod mount only
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

54″ dia., 15″ ht.
80″ lead wires.

T20

52″ Performance

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2503-09 Brushed Nickel



Natural Cherry

Cherry

P2503-20 Antique Bronze



Classic Walnut

Medium Cherry

P2503-30W White

White

White



P2503-20
shown with P2650-20TWB light kit and Medium Cherry blades*

** Light kit sold separately.*



P2503-09
shown with Natural Cherry blades



P2503-30W
shown with White blades



P2503-20
shown with Medium Cherry blades



45° Canopy

- Standard canopy works with sloped ceilings up to 45°. (12:12 ceiling pitch)
- Outlet box mounting plate includes convenient hands-free hanger for wiring.
- Oversize, textured die-cast hanger ball reduces vibrations that can cause noise and wobble.
- Dual-mount for downrod or close-to-ceiling installation (on select fans)



SureConnect® System

- Motor screws pre-installed in blade arms to prevent them from falling out during installation.
- Special guides perfectly align blade arms to motor.
- Preinstalled rubber isolation pads prevent vibration noise.

ENERGY INFORMATION AT HIGH SPEED	
Airflow	5,143 cubic feet per minute
Electricity Use	70 watts (excludes lights)
DOE Weighted CFM/W	85 CFM/W

FEATURES


- Limited lifetime warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

52″ dia., 15-1/4″ ht.
CTC 10-1/2″ ht.
80″ lead wires.

T20

CTC INSTALLATION



Edgefield



P250016-009
shown with American Walnut blades



P250016-030
shown with White blades



P250016-129
shown with Medium Cherry blades

FINISHES

- Brushed Nickel - 009
- White - 030
- Architectural Bronze - 129

P250016-009 Brushed Nickel



American Walnut
Cherry

P250016-030 White

White
White

P250016-129 Antique Bronze



Classic Walnut
Medium Cherry

ENERGY INFORMATION AT HIGH SPEED	
Airflow	5,741 cubic feet per minute
Electricity Use	34 watts (excludes lights)
DOE Weighted CFM/W	179 CFM/W

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- DC motor
- MDF blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Will not accept a wall or remote control

SIZE

52" dia., 14-9/16" ht.
80" lead wires

T20

All fixtures:

Clifton Heights



P2531-09
shown with Natural Cherry blades



P2531-20
shown with Cherry blades

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

P2531-09 Brushed Nickel



Natural Cherry
Cherry

P2531-20 Antique Bronze



Classic Walnut
Cherry

ENERGY INFORMATION AT HIGH SPEED	
Airflow	4,373 cubic feet per minute
Electricity Use	55 watts (excludes lights)
DOE Weighted CFM/W	89 CFM/W

FEATURES


- 30-year limited warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect System
- AC Motor
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

52" dia., 15-3/4" ht.
CTC 11" ht.
80" lead wires.

T20

CTC INSTALLATION



52″ Builder Fan with Light Kit

FINISHES

- Brushed Nickel - 009
- White - 030
- Architectural Bronze - 129

P2599-09 Brushed Nickel



Natural Cherry

Cherry

P2599-30 White

White

White

P2599-129 Antique Bronze



Classic Walnut

Medium Cherry



P2599-09
shown with Cherry blades



P2599-30
shown with White blades



P2599-129
shown with Classic Walnut blades

ENERGY INFORMATION AT HIGH SPEED	
Airflow	4,474 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	82 CFM/W

FEATURES

- 30-year limited warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- MDF/Plywood hybrid blades
- Etched white glass shade
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

52″ dia., 17-5/8″ ht.
80″ lead wires.

T20

52″ Builder Fan



P2501-09
shown with Cherry blades



P2501-30W
shown with White blades



P2501-30
shown with Washed Oak blades



P2501-15
shown with Driftwood blades



P2501-20
shown with Medium Cherry blades



P2501-143
shown with Black blades

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20
- White - 030
- Graphite - 143

P2501-09 Brushed Nickel



Natural Cherry
Cherry

P2501-15 Antique Bronze




Black
Driftwood

P2501-20 White



Medium Cherry
Classic Walnut

P2501-30 White




White
Washed Oak


P2501-30W White

White
White

2501-143 Graphite



Graphite
Black

ENERGY INFORMATION AT HIGH SPEED		FEATURES	SIZE	CTC INSTALLATION
Airflow	4,991 cubic feet per minute	• 30-year limited warranty • 45° Canopy • Close-to-ceiling installation • SureConnect® System • AC Motor • Compatible with universal light kits • Add a P2630 wall control or P2662-01 hand-held remote control	52″ dia., 13-1/2″ ht. CTC 9-3/4″ ht. 80″ lead wires.	
Electricity Use	63 watts (excludes lights)			
DOE Weighted CFM/W	98 CFM/W			

42″ Builder Fan

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30


P2500-09 Brushed Nickel



Cherry

Natural Cherry


P2500-20 Antique Bronze



Classic Walnut

Medium Cherry

P2500-30 White



White

Washed Oak



P2500-09
shown with P2600-09WB light kit and with Cherry blades*

** Light kit sold separately.*




P2500-20
shown with Classic Walnut blades



P2500-09
shown with Cherry blades



P2500-30
shown with White blades

ENERGY INFORMATION AT HIGH SPEED		FEATURES	SIZE	CTC INSTALLATION
Airflow	3,053 cubic feet per minute	• 15-year limited warranty • 23° Canopy • Close-to-ceiling installation • SureConnect® System • AC Motor • Compatible with universal light kits • Three speed pull-chain switch • Add a P2630 wall control or P2662-01 hand-held remote control	42″ dia., 12-3/8″ ht. CTC 8-5/16″ ht. 72″ lead wires. T20	
Electricity Use	46 watts (excludes lights)			
DOE Weighted CFM/W	64 CFM/W			

Drift

Enhance your home with the perfect mix of form and function with the 32" four-blade Drift fan. Ideal for smaller spaces, such as closets, mudrooms and laundry rooms, Drift features a powerful motor and a steep pitch to circulate a lot of air within a smaller space.



P250008-009
shown with Driftwood blades



P250008-030
shown with Driftwood blades




P250008-129
shown with Classic Walnut blades

FINISHES


- Brushed Nickel - 009
- White - 030
- Architectural Bronze - 129

P250008-009 Brushed Nickel



Driftwood
Silver

P250008-030 White



White
Driftwood

P250008-129 Architectural Bronze



Medium Cherry
Classic Walnut

ENERGY INFORMATION AT HIGH SPEED	
Airflow	2,518 cubic feet per minute
Electricity Use	35 watts (excludes lights)
DOE Weighted CFM/W	88 CFM/W

FEATURES


- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-30°)
- Close-to-ceiling installation
- AC Motor
- Reversible MDF blades
- Compatible with universal light kits
- Three speed pull-chain switch
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

32" dia., 14-3/8" ht.
80" lead wires.

T20

CTC INSTALLATION



Lindale

Retreat for a little rest and relaxation under the gentle airflow offered by the Lindale Collection's ceiling fan. A mid-century modern style blends with a flush mount design as four rectangular plywood blades attach to the fan's vase-inspired center. Select your favorite finish from three beautiful options to customize your Lindale fan for a perfect fit in your home décor design.

FINISHES
- Satin White- 028
- Antique Nickel - 081
- Architectural Bronze - 129

P250028-028 Satin White



Matte White

Silver


P250028-081 Antique Nickel



White Barnwood

Driftwood

P250028-129 Architectural Bronze



Distressed Walnut

Classic Walnut



P250028-028
shown with Matte White blades



P250028-081
shown with White Barnwood blades



P250028-129
shown with Distressed Walnut blades and optional P2669-129 Light Kit

LINDALE LIGHT KIT
P2669-028 Satin White
P2669-081 Antique Nickel
P2669-129 Architectural Bronze
24w LED Module, 3000K, 90 CRI, 2000 lumens, dimmable.



P2669-28



P2669-81



P2669-129

ENERGY INFORMATION AT HIGH SPEED	
Airflow	4,642 cubic feet per minute
Electricity Use	60 watts (excludes lights)
DOE Weighted CFM/W	87 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES
- Limited lifetime warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE
52" dia., 11-3/16" ht.
80" lead wires.

Braden

This Braden 56", three-blade, hugger-style ceiling fan features clean lines and a design that complements modern interiors. A shatterproof white opal glass shade contains an integrated 18W LED module, offering both form and function with energy and cost-savings benefits. Featuring a larger motor, Braden moves more air than a traditional hugger ceiling fan.



P2588-0930K
shown with American Walnut blades



P2588-1530K
shown with Black blades




P2588-12930K
shown with Medium Cherry blades

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Architectural Bronze - 129

P2588-0930K Brushed Nickel



American Walnut

Silver

P2588-1530K Polished Chrome



American Walnut

Black

P2588-12930K Architectural Bronze



Medium Cherry

Classic Walnut

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,263 cubic feet per minute
Electricity Use	55 watts (excludes lights)
DOE Weighted CFM/W	85 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited lifetime warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Full function remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control

SIZE

56" dia., 9-7/8" ht.
12" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI, 1400 lumens, dimmable.

T20 JA8

Vox Fan

Five-blade 52" Vox hugger-style ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. A white opal glass shade contains a 17W dimmable, 3000K LED module. A full function remote control is included. The fan mounts close to the ceiling and is available in popular Brushed Nickel, Antique Bronze and White finishes.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 30

P2572-0930K Brushed Nickel

Medium Cherry

P2572-2030K Antique Bronze

American Walnut

P2572-3030K White

White



P2572-0930K
shown with Medium Cherry blades



P2572-2030K
shown with American Walnut blades



P2572-3030K
shown with White blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,276 cubic feet per minute
Electricity Use	62 watts (excludes lights)
DOE Weighted CFM/W	76 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Hugger low profile mounting
- AC Motor
- Non-reversible plywood blades
- White opal glass shade
- Full function remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control

SIZE

52" dia., 11-5/8" ht.
8" lead wires.

LAMP

17w LED Module,
3000K, 90 CRI,
1400 lumens, dimmable.

T20 JA8

52″ Hugger Fan



P2525-30
shown with White blades



P2525-09
shown with Cherry blades

P2525-09 Brushed Nickel

Cherry

Natural Cherry

P2525-20 White

White

White



P2525-09
*shown with P2610-09WB light kit**
and with Cherry blades
** Light kit sold separately.*

ENERGY INFORMATION AT HIGH SPEED	
Airflow	3,229 cubic feet per minute
Electricity Use	56 watts (excludes lights)
DOE Weighted CFM/W	58 CFM/W

FEATURES

- 15-year limited warranty
- Hugger low profile mounting
- AC Motor
- Compatible with universal light kits
- Cannot be used with remote control
- Add a P2630-30 or P2630-95 wall control

SIZE

52″ dia., 8-1/8″ ht.

T20

42″ Hugger Fan



P2524-30
shown with White blades



P2524-09
shown with Natural Cherry blades

P2524-09 Brushed Nickel

Cherry

Natural Cherry

P2524-30 White

White

White



P2524-09
shown with P2602-09WB *light kit**
and with Natural Cherry blades
** Light kit sold separately.*

ENERGY INFORMATION AT HIGH SPEED	
Airflow	2,639 cubic feet per minute
Electricity Use	44 watts (excludes lights)
DOE Weighted CFM/W	72 CFM/W

FEATURES

- 15-year limited warranty
- Hugger low profile mounting
- AC Motor
- Compatible with universal light kits
- Cannot be used with remote control
- Add a P2630-30 or P2630-95 wall control

SIZE

42″ dia., 8-5/16″ ht.

T20

Alfresco

FINISHES
- Architectural Bronze - 129
- Blistered Iron - 171

P250034-129-WB
shown with Dark Bamboo blades

Infuse a warm, nature-inspired style to your outdoor home décor with the one-of-a-kind Alfresco Collection. Five blades decorated in a leaf-like design sprout from a dual mount center that artistically harbors an LED light source. Select from an architectural bronze and blistered iron finish to bring your bohemian dreamland to life.



Alfresco

P250034-129-WB Architectural Bronze

Dark Bamboo

P250034-171-WB Blistered Iron

Pewter



P250034-129-WB
shown with Dark Bamboo blades



P250034-171-WB
shown with Pewter blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,724 cubic feet per minute
Electricity Use	68 watts (excludes lights)
DOE Weighted CFM/W	90 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- ABS blades
- Clear Seeded glass
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54″ dia., 19-1/4″ ht.
80″ lead wires.

LAMP


Two ST19 vintage LED lamps, 3000K, 90 CRI, 800 lumens, dimmable.

Rudder

FINISHES
- ○ Satin White- 028
- ● Black- 031
- ● Architectural Bronze - 129

P250040-028-30
shown with Distressed White blades

Transform any outdoor space into a cozy country abode with the charming rustic character of the Rudder Collection. Four boat oar-inspired blades attach to a smooth center that features an LED light source for friendly illumination as needed. Available in a matte white, matte black, or architectural bronze finish, Rudder is sure to fill your favorite patio or porch with a refreshing breeze wrapped in country character.



Rudder



P250040-028-30
shown with Distressed White blades



P250040-031-30
shown with Distressed Ebony blades



P250040-129-30
shown with Walnut blades

P250040-028-30 Satin White



Distressed White

P250040-031-30 Black



Distressed Ebony

P250040-129-30 Architectural Bronze



Walnut

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,112 cubic feet per minute
Electricity Use	35 watts (excludes lights)
DOE Weighted CFM/W	188 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White Opal glass
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

56″ dia., 16-1/8″ ht.
80″ lead wires.

LAMP

24w LED Module,
3000K, 90 CRI,
2000 lumens, dimmable.

Edisto

FINISHES

- Forged Black - 80
- Antique Nickel - 81
- Architectural Bronze - 129

P2596-8030K
shown with Charcoal Canvas blades

The Edisto 54″ two-blade outdoor ceiling fan combines a sleek, contemporary style with high-quality performance. A wire frame supports canvas wrapped blades that feature UV inhibitors to protect the fabric from fading in the sunlight. Three fan speeds and a reversible switch keep individuals cool in the summer and warm in the winter. A white opal glass shade contains an 18W LED module light kit, offering energy efficient and cost savings benefits.



Edisto



P2596-8030K
shown with Charcoal Canvas blades



P2596-8130K
shown with Oatmeal Canvas blades



P2596-12930K
shown with Mushroom Canvas blades

P2596-8030K Forged Black

Charcoal Canvas

P2596-8130K Antique Nickel

Oatmeal Canvas

P2596-12930K Architectural Bronze

Mushroom Canvas

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,371 cubic feet per minute
Electricity Use	65 watts (excludes lights)
DOE Weighted CFM/W	73 CFM/W



Three-Speed Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- Canvas wrapped blades
- White opal glass shade
- Damp Location Rated
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54″ dia., 14-7/8″ ht.
80″ lead wires.

LAMP

18w LED Module,
3000K, 90 CRI,
1400 lumens, dimmable.

T20 JA8


Whirl

FINISHES

- Antique Bronze - 20
- Forged Black - 80
- Antique Nickel - 81

P2574-8130K
shown with Driftwood blades

Refresh your indoor or covered outdoor living spaces with the crisp, clean style of the 60″ Whirl fan. The stylish design comes in Antique Nickel, Antique Bronze and Forged Black finish options. The five-blade fan features an all weather damp location rating to accommodate a variety of settings throughout the home.



Whirl



P2574-2030K
shown with Walnut blades



P2574-8030K
shown with Toasted Oak blades



P2574-8130K
shown with Driftwood blades

P2574-2030K Antique Bronze



Walnut

P2574-8030K Forged Black



Toasted Oak

P2574-8130K Antique Nickel



Driftwood

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,549 cubic feet per minute
Electricity Use	70 watts (excludes lights)
DOE Weighted CFM/W	106 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- ABS all weather blades
- White Frosted Glass Shade
- Three speed pull-chain switch (fan)
- On/off pull-chain switch (light)
- Damp Location Rated
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

60″ dia., 15-7/8″ ht.
80″ lead wires.

LAMP

18w LED Module,
3000K, 90 CRI,
1400 lumens, dimmable.

T20 JA8



Relax All Year Long



Light-filled sunrooms offer the best of indoor-outdoor living.

1

Add a beautiful ceiling fan to move the air comfortably for ultimate relaxation. The Montague ceiling fan offers dual-action functionality, blowing air down and around to cool in the summer, or upwards in the colder weather for year-round comfort.

2

Accessorize with organic touches of driftwood-gray furniture topped with cozy cushions, greenery and a tranquil neutral color scheme.

3

The Cedar Springs outdoor lantern installed over the inside door completes the serene style.

Smyrna

This 52″ Smyrna ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. The light kit contains a clear hammered glass shade and contains a 17W dimmable 3000K LED module. Includes a wall control switch for fan speed and light operation.

FINISHES

- Antique Bronze - 20
- Forged Black - 80

P2576-2030K Antique Bronze

Walnut

P2576-8030K Forged Black

Toasted Oak



P2576-2030K
shown with Walnut blades



P2576-8030K
shown with Toasted Oak blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,585 cubic feet per minute
Electricity Use	58 watts (excludes lights)
DOE Weighted CFM/W	91 CFM/W



Wall Control Included
Four-speed fan operation
Full-range dimming for light
Includes switch plate cover

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-30°)
- AC Motor
- ABS all weather blades
- Clear Hammered glass shade
- Wet Location Rated

SIZE

52″ dia., 19-1/2″ ht.
80″ lead wires.

LAMP

17w LED Module,
3000K, 90 CRI,
1400 lumens, dimmable.

T20 JA8

Montague



P2564-2030K
shown with Walnut blades



P2564-3030K
shown with White blades



P2564-8030K
shown with Toasted Oak blades

This five-blade 60″ Montague ceiling fan features an all weather wet location rating to accommodate a variety of interior and exterior locations. The white opal glass shade contains a 18W dimmable, 3000K LED module, offering both form and function with energy and cost-savings benefits. A full function remote control is included.

FINISHES

- Antique Bronze - 20
- White - 30
- Forged Black - 80

P2564-2030K Antique Bronze

Walnut

P2564-3030K White

White

P2564-8030K Forged Black

Toasted Oak

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,693 cubic feet per minute
Electricity Use	75 watts (excludes lights)
DOE Weighted CFM/W	96 CFM/W



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- White Opal Glass Shade
- ABS all weather blades
- Wet Location Rated
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

60″ dia., 17-5/8″ ht.
80″ lead wires.

LAMP

18w LED Module,
3000K, 90 CRI,
1400 lumens, dimmable.

T20 JA8

Albin

The Albin Collection offers a modern take on a traditional design that will be perfectly at home in so many outdoor spaces and lifestyles. Five blades finished with a faux wood grain texture extend from a modern-style center available in an architectural bronze, matte white, or matte black finish. An LED light source is encased in a crisp shade to illuminate a patio or porch space that will beg to be lived in an enjoyed.

FINISHES
- ○ Satin White- 028
- ● Black- 031
- ● Architectural Bronze - 129

P250036-028-30 Satin White

Satin White

P250036-031-30 Black

Toasted Oak

P250036-129-30 Architectural Bronze

Distressed Walnut



P250036-028-30
shown with Satin White blades



P250036-031-30
shown with Toasted Oak blades



P250036-129-30
shown with Distressed Walnut blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	5,740 cubic feet per minute
Electricity Use	67 watts (excludes lights)
DOE Weighted CFM/W	95 CFM/W



Three Speed Remote Control Included
Three speed fan operation
Full range dimming with light

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White Opal glass
- Remote control with batteries is included
- Remote control may be replaced with P2630-30 or P2630-95 wall control

SIZE

54″ dia., 15-5/8″ ht.
80″ lead wires.

LAMP

24w LED Module, 3000K,
90 CRI,
2000 lumens, dimmable.

Lakehurst

This five-blade 60″ Lakehurst ceiling fan features an all weather wet location rating (ABS) to accommodate a variety of interior and exterior locations. The Lakehurst fan will accept a universal outdoor rated light kit. Features a dual mount system and a three-speed pull chain fan switch.



P2562-20
shown with Walnut blades



P2562-30
shown with White blades



P2562-80
shown with Toasted Oak blades

FINISHES

- Antique Bronze - 20
- White - 30
- Forged Black - 80

P2562-20 Antique Bronze



Walnut

P2562-20 Antique Bronze

White

P2562-80 Forged Black



Toasted Oak

ENERGY INFORMATION AT HIGH SPEED	
Airflow	6,440 cubic feet per minute
Electricity Use	71 watts (excludes lights)
DOE Weighted CFM/W	105 CFM/W

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC Motor
- ABS all weather blades
- Compatible with universal light kits
- 3 Speed pull chain switch
- Wet Location Rated
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control

SIZE

60″ dia., 15-3/4″ ht.
80″ lead wires.

T20

54″ Patio Fan

FINISH


Antique Bronze - 20

P2533-20 Antique Bronze

Toasted Oak



P2533-20
shown with Toasted Oak blades
** Light kit sold separately.*

ENERGY INFORMATION AT HIGH SPEED		FEATURES	SIZE	CTC INSTALLATION
Airflow	4,986 cubic feet per minute	• 30-year limited warranty • 45° Canopy • SureConnect® System • AC Motor • ABS all-weather blades • Wet location listed • Compatible with universal light kits • Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control	54″ dia., 18-1/4″ ht. CTC 12-3/16 ht. 80″ lead wires. T20	
Electricity Use	65 watts (excludes lights)			
DOE Weighted CFM/W	74 CFM/W			

52″ Patio Fan

P2502-20 Antique Bronze

Oak

P2502-30 White

White

P2502-80 Forged Black

Toasted Oak

P2502-141 Galvanized

Silver



P2502-30
shown with White blades




P2502-80
shown with Toasted Oak blades



P2502-141
shown with Silver blades



P2502-20
shown with Oak blades

ENERGY INFORMATION AT HIGH SPEED		FEATURES	SIZE	CTC INSTALLATION
Airflow	4,991 cubic feet per minute	• 15-year limited warranty • Dual Mount (flat or sloped ceiling-23°) • Close-to-ceiling installation • SureConnect® System • Quick-Install canopy • AC Motor • ABS all-weather blades • Compatible with universal light kits • Three speed pull-chain switch • Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control • Wet location listed	52″ dia., 12-3/4″ ht. CTC 9-11/16 ht. 72″ lead wires. T20	
Electricity Use	64 watts (excludes lights)			
DOE Weighted CFM/W	89 CFM/W			

Decorative Patio Fan



P2526-20
shown with Washed Walnut blades

FINISH

Antique Bronze - 20

P2526-20 Antique Bronze

Washed Walnut



P2526-20
*shown with P2636-20WB light kit**
and Washed Walnut blades
** Light kit sold separately.*

ENERGY INFORMATION AT HIGH SPEED	
Airflow	4,150 cubic feet per minute
Electricity Use	70 watts (excludes lights)
DOE Weighted CFM/W	77 CFM/W

FEATURES


- 15-year limited warranty
- 45° Canopy
- Close-to-ceiling installation
- SureConnect® System
- AC Motor
- ABS all-weather blades
- Compatible with universal light kits
- Add a P2630-30 or P2630-95 wall control or P2662-01 hand-held remote control
- Damp location listed

SIZE

52″ dia., 17-3/8″ ht.
CTC 12-3/16 ht.
80″ lead wires.

T20

CTC INSTALLATION



Indoor/Outdoor

Universal-style with quick-connect wiring.

SCHOOLHOUSE
P2601-20WB Antique Bronze
P2601-30WB White
P2601-80WB Forged Black
P2601-141WB Galvanized
with opal glass.
8-1/2" dia., 7" ht.
One medium base, 3000K,
LED lamp included.
800 lumens/lamp, 90 CRI.
(dimmable)


P2601-20WB


P2601-30WB


P2601-80WB


P2601-141WB

LOW PROFILE
P2611-20WB Antique Bronze
P2611-30WB White
P2611-80WB Forged Black
with opal glass.
10-1/2" dia., 4-1/2" ht.
Two medium base, 3000K,
LED lamp included.
800 lumens/lamp, 90 CRI.
(dimmable)


P2611-20WB


P2611-30WB


P2611-80WB

ASHMORE
P2636-20WB Antique Bronze
with frosted seeded glass.
11" dia., 8-1/4" ht.
Two medium base, 3000K,
LED lamp included.
800 lumens/lamp, 90 CRI.
(dimmable)


P2636-20WB

Torino

Universal-style light kit with quick-connect wiring.

P2645-77WB Forged Bronze
with tea-stained glass.
P2645-01WB
with etched glass.
Included Finials:
-09 Brushed Nickel
-20 Antique Bronze
-80 Forged Black
12" dia., 5-3/4" ht.
Two medium base, 3000K,
LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimmable)



P2645-77WB



P2645-01WB
shown with
-09 finial



P2645-01WB
shown with
-20 finial



P2645-01WB
shown with
-80 finial

Gather, Bravo & Joy

Universal-style light kit with quick-connect wiring.

P2650-20TWB Antique Bronze
with tea-stained glass.
P2650-01WB
with etched glass.
Included Finials:
-09 Brushed Nickel
-20 Antique Bronze
11" dia., 5-1/2" ht.
Two medium base, 3000K,
LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimmable)



P2650-20TWB



P2650-01WB
shown with
-09 finial



P2650-01WB
shown with
-20 finial

Madison

Universal-style with quick-connect wiring.

P2623-09WB Brushed Nickel
P2623-20WB Antique Bronze
with etched glass.
19" dia., 8" ht.
Three medium base, 3000K,
LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimmable)



P2623-09WB



P2623-20WB

Universal Bowl

Universal-style with quick-connect wiring.

P2612-20TWB Antique Bronze
with tea-stained glass.
P2612-01WB
with alabaster glass.
Included Finials:
-09 Brushed Nickel
-20 Antique Bronze
-30 White
-15 Polished Chrome
-143 Graphite
10-3/4" dia., 5-1/2" ht.
Two medium base, 3000K,
LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimmable)


P2612-20TWB


P2612-01WB
shown with
-09 finial


P2612-01WB
shown with
-15 finial


P2612-01WB
shown with
-20 finial


P2612-01WB
shown with
-30 finial


P2612-01WB
shown with
-143 finial

Wisten

Universal-style light kit with quick-connect wiring.

P2649-01WB
with etched glass.
Included Finials:
-09 Brushed Nickel
-20 Antique Bronze
11" dia., 6-1/4" ht.
Two medium base, 3000K,
LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimmable)


P2649-01WB
shown with
-09 finial


P2649-01WB
shown with
-20 finial

Clifton Heights

Universal-style with quick-connect wiring.

P2654-01WB
with etched glass.
Included Finials:
-09 Brushed Nickel
-20 Antique Bronze
12-1/2" sq., 6-1/4" ht.
Two medium base, 3000K,
LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimmable)


P2654-01WB
shown with
-09 finial


P2654-01WB
shown with
-20 finial

LED Light Kits

Universal-style light kits with quick connect wiring.

P2659-09 Brushed Nickel
P2659-20 Antique Bronze
P2659-30 White
with etched white glass.
12-1/4" dia., 4" ht.
One 16w, 3000K
LED module included.
1265 source lumens,
960 delivered lumens,
90 CRI. Indoor use only.
(dimmable)



P2659-09



P2659-20



P2659-30

P2660-01
with etched alabaster glass.
Included Finials:
-09 Brushed Nickel
-20 Antique Bronze
-30 White
11-1/4" dia., 5-3/8" ht.
One 16w, 3000K
LED module included.
1241 source lumens,
1150 delivered lumens,
90 CRI. Indoor use only.
(dimmable)



P2660-01
shown with
-09 finial



P2660-01
shown with
-20 finial



P2660-01
shown with
-30 finial

Trinity

Universal-style with quick-connect wiring.

P2628-01WB
with etched glass.
Included Finials:
-09 Brushed Nickel
-20 Antique Bronze
-30 White
-77 Forged Bronze
13-3/8" dia., 6-3/8" ht.
Two medium base, 3000K,
LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimmable)



P2628-01WB
shown with
-09 finial



P2628-01WB
shown with
-20 finial



P2628-01WB
shown with
-30 finial



P2628-01WB
shown with
-77 finial

Four Light Universal

Universal-style with quick-connect wiring.

P2643-09WB Brushed Nickel
P2643-20WB Antique Bronze
P2643-30WB White
with alabaster glass.
P2643-20TWB Antique Bronze
with tea stained alabaster glass.
13-5/8" dia., 7-3/4" ht.
Four medium base, 3000K,
LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimmable)


P2643-09WB


P2643-20WB


P2643-30WB


P2643-20TWB

Three Light Universal

Universal-style with quick-connect wiring.

P2642-09WB Brushed Nickel
P2642-30WB White
with alabaster glass.
13-5/8" dia., 7-3/4" ht.
Three medium base, 3000K,
LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimmable)


P2642-09WB


P2642-30WB

Low Profile

Universal-style with quick-connect wiring.

P2602-09WB Brushed Nickel
P2602-15WB Polished Chrome
P2602-20WB Antique Bronze
P2602-30WB White
P2602-143WB Graphite
with white opal glass.
10-1/2" dia., 4-1/2" ht.
Two medium base, 3000K,
LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimmable)


P2602-09WB


P2602-15WB


P2602-20WB


P2602-30WB


P2602-143WB

Four Light Alabaster

Spring clip glass attachment. For use with P2500, P2501, P2502, P2524 and P2525.

P2610-09WB Brushed Nickel
P2610-15WB Polished Chrome
P2610-20WB Antique Bronze
P2610-30WB White
P2610-143WB Graphite
with alabaster glass.
14-1/2" dia., 6-1/4" ht.
Four medium base, 3000K,
LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimmable)


P2610-09WB


P2610-15WB


P2610-20WB


P2610-30WB


P2610-143WB

Three Light Alabaster

Spring clip glass attachment. For use with P2500, P2501, P2502, P2524 and P2525.

P2600-09WB Brushed Nickel
P2600-20WB Antique Bronze
P2600-30WB White
with alabaster glass.
15" dia., 6-5/8" ht.
Three medium base, 3000K,
LED lamps included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimmable)


P2600-09WB


P2600-20WB


P2600-30WB

Schoolhouse

Universal-style with quick-connect wiring.

P2644-09WB Brushed Nickel
P2644-30WB White
with white opal glass.
8-1/2" dia., 6-1/2" ht.
One medium base, 3000K,
LED lamp included.
800 lumens/lamp, 90 CRI.
Indoor use only. (dimmable)


P2644-09WB


P2644-30WB

Accessory Downrods


3/4″ diameter; approximately 1″ outside diameter.

CEILING HT. DOWNROD L.	9′-10′ 12″	10′-11′ 18″	11′-12′ 24″	12′-14′ 36″	13′-15′ 48″	14′-16′ 60″	15′-17′ 72″
Brushed Nickel	P2603-09	P2604-09	P2605-09	P2606-09	P2607-09	P2608-09	P2609-09
Polished Chrome	P2603-15	P2604-15	P2605-15	P2606-15	P2607-15	P2608-15	P2609-15
Antique Bronze **Use with 129 finish*	P2603-20	P2604-20	P2605-20	P2606-20	P2607-20	P2608-20	P2609-20
Matte White	P2603-28	P2604-28	P2605-28	P2606-28	P2607-28	P2608-28	P2609-28
White	P2603-30	P2604-30	P2605-30	P2606-30	P2607-30	P2608-30	P2609-30
Matte Black	P2603-31	P2604-31	P2605-31	P2606-31	P2607-31	P2608-31	P2609-31
Gilded Iron	P2603-71	P2604-71	P2605-71	P2606-71	P2607-71	P2608-71	P2609-71
Forged Bronze **Use with 71 finish*	P2603-77	P2604-77	P2605-77	P2606-77	P2607-77	P2608-77	P2609-77
Forged Black	P2603-80	P2604-80	P2605-80	P2606-80	P2607-80	P2608-80	P2609-80
Antique Nickel	P2603-81	P2604-81	P2605-81	P2606-81	P2607-81	P2608-81	P2609-81
Architectural Bronze	P2603-129	P2604-129	P2605-129	P2606-129	P2607-129	P2608-129	P2609-129
Galvanized	P2603-141	P2604-141	P2605-141	P2606-141	P2607-141	-	-
Graphite	P2603-143	P2604-143	P2605-143	P2606-143	P2607-143	P2608-143	P2609-143
Painted Nickel	P2603-152	P2604-152	P2605-152	P2606-152	P2607-152	-	-
Vintage Brass	P2603-163	P2604-163	P2605-163	P2606-163	P2607-163	-	-
Blistered Iron	P2603-171	P2604-171	P2605-171	P2606-171	P2607-171	-	-
Black Chrome	P2603-231	P2604-231	P2605-231	P2606-231	P2607-231	-	-

Downrod Selection Guide

Allow at least 7 feet (84 in.) from the floor to the bottom of the fan, with 8 or 9 feet being the ideal above-floor placement.

**Average length downrod, included with each fan.*



Remotes, Wall Controls & 45° Canopies



P2662-01
Fan/Light Remote

Universal remote operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring four “dip” switches and 16 code options to avoid the chance of interference from other remotes.



P2663-01
Fan/Light Remote

Universal remote with two, four or eight-hour timer option, operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring many code combination options to avoid the chance of interference from other remotes.



P2618-01
Fan/Light Remote

Provides fan speed and light control from convenient hand-held remote. Compatible with non-dimmable compact fluorescent lamps. For single pole applications. Receiver fits in fan canopy.



P2661-01
Universal Fan/Light Remote

Provides fan speed and full range light dimming control from a convenient hand held remote control. For single pole applications. Includes a wall plate for added storage convenience. Receiver fits in the fan canopy.



P2667-031
Wifi Fan/Light Remote

Universal Wifi remote control for AC motor fans. Control your ceiling fan or light kit via Wifi from anywhere. Pairs with Alexa, Google Home, or app on your phone or tablet. Voice control the fan with three speeds and the light with full range dimming. App control the fan with three speeds or four timer selections or full range dimming control of the light. Can be controlled with the hand held remote included with the kit.



P2665-30 White
Universal remote includes a wall mount transmitter, ideal for multi-family applications, that operates three fan speeds and full-range dimming light control. Includes canopy receiver and wall storage bracket. Will work with LED lamps and modules. Featuring four “dip” switches and 16 code options to avoid the chance of interference from other remotes.



P2631-30 White
Full-function wall control transmitter (receiver sold with ceiling fan). Use with, or in place of, hand-held remote included with fans that have a downlight. Includes switch plate cover.



P2630-95 Ivory
Four-speed fan wall control with full-range light dimmer. Fits single-gang wall box; requires two circuits. Includes switch plate cover. Not for use with multiple fans.



P2630-30 White
Four-speed fan wall control with full-range light dimmer. Fits single-gang wall box; requires two circuits. Includes switch plate cover. Not for use with multiple fans.



P2613-95 Ivory
Four-speed fan wall control. Includes switch plate cover. Not for use with multiple fans.



P2613-30 White
Four-speed fan wall control. Includes switch plate cover. Not for use with multiple fans.



P2666-09
Brushed Nickel
45° canopy



P2666-30
White
45° canopy



P2666-129
Architectural Bronze
45° canopy



Featuring Status and Bonita by Design Series™

Close-to-Ceiling

Brighten *Intimate* Spaces

Scan and see more at
progresslighting.com

Anjoux
P350096-134

Carlyn by Design Series™
P300100-104





Kelsey Puls
Product Specialist

A Touch of Glam

with Kelsey

Luxe is a modern take on luxury interior design that incorporates sleek, sophisticated details, gorgeous materials, and statement décor for interiors that exude glamour. It is opulent without being over the top. Rich fabrics, glass and lustrous metallic finishes are balanced throughout the design elements for a refined yet comfortable luxurious look. Classic furniture lines are paired with a sophisticated color palette. Gold, chrome and silver finishes are mixed with crystal in lighting and accessories to offer a light and airy feel, for a space that is ultimately inviting and comfortable.

Shop this style at
progresslighting.com/luxe



Anjoux

Sparkling crystal teardrops accents cascade from a gleaming circular canopy.

FIVE-LIGHT FLUSH MOUNT
P350096-134 Silver Ridge
P350096-020 Antique Bronze
16" dia., 14" ht.
Five candelabra base lamps, each 60w max.

P350096-134



P350096-020



Caress

Shimmering water glass shade surrounds an etched glass diffuser.

TWO-LIGHT SEMI-FLUSH
P3434-104 Polished Nickel
16" dia., 12" ht.
Two medium base lamps, each 100w max.

SEMI-FLUSH CONVERTIBLE
P5044-104WB Polished Nickel
Hanging and ceiling mount hardware included.
6-3/8" dia., 11" ht.,
Overall ht w/chain or stem 76"; wire 15'.
One candelabra base lamp, 60w max. Krypton lamp included.

Replacement lamp P7807-01.
See page 824.



P5044-104WB



P3434-104

Landree

Geometric patterning encloses a soft white silk shade.

THREE-LIGHT FLUSH MOUNT
P350132-031 Black
P350132-134 Silver Ridge
16" dia., 6-5/8" ht.
Three medium base lamps, each 60w max.



P350132-134



P350132-031

Orbitz



P3954-09



P3954-20

A clean-lined, circular frame is topped with etched glass shades.

SEMI-FLUSH CONVERTIBLE
P3954-09 Brushed Nickel
P3954-20 Antique Bronze
Hanging and ceiling mount hardware included.
17″ dia., 12 1/4″ ht.,
Overall ht. w/stem 79″; wire 15′.
Three medium base lamps, each 100w max.

Status



P3495-15



P3402-15

A gleaming glass accent adds a playful punch of status to the shade's simple round silhouette.

TWO-LIGHT FLUSH MOUNT
P3402-15 Polished Chrome
13″ dia., 8″ ht.
Two medium base lamps, each 60w max.

TWO-LIGHT SEMI-FLUSH
P3495-15 Polished Chrome
13″ dia., 13-5/8″ ht.
Two medium base lamps, each 100w max.

Barnes Mill



P350059-020
shown flush mounted

Exposed iron details and a faux-painted wooden plank support artful, clear seeded glass shades. Combine with vintage-style light bulbs to create a romantic focal point for any room.

SEMI-FLUSH CONVERTIBLE
P350059-020 Antique Bronze
Hanging and ceiling mount hardware included.
16-1/4″ dia., 11-7/8″ ht.,
Overall ht. w/chain 52″, wire 10′.
Two medium base lamps, each 75w max.

Fixture shown with P7825-01 vintage lamps, not included. See page 824.

Bay Court

Inspired by antique lanterns, an etched glass diffuser is encircled by a water glass shade.

TWO-LIGHT FLUSH MOUNT
P3942-09 Brushed Nickel
P3942-20 Antique Bronze
15″ dia., 7-3/8″ ht.
Two medium base lamps,
each 60w max.



P3942-20



P3942-09

Lassiter

Clean, sharp-angled arms hold vintage-styled light sockets and clear shades.

THREE-LIGHT SEMI-FLUSH
P350149-009 Brushed Nickel
P350149-031 Black
13″ dia., 10-1/2″ ht.
Three medium base lamps,
each 60w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.



P350149-031



P350149-009

Chadwick

Beautiful opal glass shades offer a simple contrast to the geometric styling of the boxy frames.

TWO-LIGHT FLUSH MOUNT
P350171-009 Brushed Nickel
P350171-031 Black
15-3/8″ sq., 5-1/2″ ht.
Two medium base lamps,
each 60w max.



P350171-009



P350171-031

Kene

Etched glass diffusers surrounded by clear outer shades lend a soft luxurious touch.

SEMI-FLUSH CONVERTIBLE
P350098-009 Brushed Nickel
P350098-143 Graphite
Hanging and ceiling mount
hardware included.
16″ dia., 10-7/8″ ht.,
Overall ht. w/chain 50-1/2″, wire 10′.
Two medium base lamps,
each 75w max.



P350098-143



P350098-009

Leap

Large-scale, tapered etched glass shades perfectly complement contemporary design.

SEMI-FLUSH CONVERTIBLE
P350060-009 Brushed Nickel
P350060-020 Antique Bronze
Hanging and ceiling mount hardware included.
14″ dia., 8-7/8″ ht.,
Overall ht. w/chain 47″; wire 10′.
Two medium base lamps, each 100w max.

TWO-LIGHT FLUSH MOUNT
P350061-009 Brushed Nickel
P350061-020 Antique Bronze
14″ dia., 6-5/8″ ht.
Two medium base lamps, each 60w max.



P350060-009



P350060-020



P350061-009



P350061-020

Hansford

Vintage-style metal fittings capture a clear, spherical shade for a precise design with generous scale.

ONE-LIGHT FLUSH MOUNT
P350046-020 Antique Bronze
P350046-104 Polished Nickel
10″ dia., 12-5/8″ ht.
One medium base lamp, 100w max.



P350046-104



P350046-020

Bowman

Clear, chiseled glass shades surround dainty yet sophisticated curved-arm candle slips.

SEMI-FLUSH CONVERTIBLE
P350148-031 Matte Black
P350148-151 Cottage White
Hanging and ceiling mount hardware included.
14-1/4″ dia., 13-3/8″ ht.,
Overall ht. w/chain 52-1/2″, wire 10′.
Three candelabra base lamps, each 60w max.



P350148-151



P350148-031

Winslett

Perfectly imperfect lightly seeded glass shades rest in shiny pedestal light bases.

SEMI-FLUSH CONVERTIBLE
P350153-009 Brushed Nickel
P350153-031 Black
Hanging and ceiling mount hardware included.
13-3/4" dia., 11-7/8" ht.,
Overall ht. w/chain 50-1/2", wire 10'.
Three candelabra base lamps, each 60w max.



P350153-031



P350153-009

Judson

Vintage-look metal fittings suspend a schoolhouse-style clear glass globe.

ONE-LIGHT FLUSH MOUNT
P350074-020 Antique Bronze
P350074-104 Polished Nickel
11" dia., 12" ht.
One medium base lamp, 75w max.



P350074-020



P350074-104

Swing

Vintage electric undertones abound from a metal mesh shade encasing antique-style fittings.

THREE-LIGHT FLUSH MOUNT
P3452-20 Antique Bronze
15" dia., 8-1/2" ht.
Three medium base lamps, each 60w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.



P3452-20

Mast

Faux wood accents a circular metal frame that secures an etched glass shade.

TWO-LIGHT FLUSH MOUNT
P350144-009 Brushed Nickel
P350144-020 Antique Bronze
13" dia., 5-1/4" ht.
Two medium base lamps, each 60w max.



P350144-020



P350144-009

Archie

A cross-patterned, double-prismatic glass shade is grounded by a metal frame and knob.

SEMI-FLUSH CONVERTIBLE
P2334-15 Polished Chrome
P2334-74 Venetian Bronze
P2334-81 Antique Nickel
P2334-163 Vintage Brass
Hanging and ceiling mount hardware included.
12-3/8" dia., 11-3/8" ht.,
Overall ht. w/chain 48-1/2"; wire 10'.
Two medium base lamps, each 100w max.

TWO-LIGHT FLUSH MOUNT
P3740-15 Polished Chrome
P3740-74 Venetian Bronze
P3740-81 Antique Nickel
P3740-163 Vintage Brass
12-3/8" dia., 6-1/4" ht.
Two medium base lamps, each 75w max.


P2334-81


P2334-74


P2334-15


P2334-163


P3740-81


P3740-74


P3740-15


P3740-163

Dwyer

Clear ribbed glass framed by simple metal banding creates a gaslight glow.

TWO-LIGHT FLUSH MOUNT
P350152-031 Black
P350152-135 Stainless Steel
11" sq., 4" ht.
Two medium base lamps, each 60w max.


P350152-031


P350152-135

Signal

Clear blown glass shade and a clean-lined frame offers a modern attitude.

ONE-LIGHT FLUSH MOUNT
P350145-015 Polished Chrome
P350145-143 Graphite
5-1/8" dia., 7-5/8" ht.
One medium base lamp, 60w max.


P350145-143


P350145-015

Durrell

An open and airy circular metal frame surrounds simple light bases.

TWO-LIGHT FLUSH MOUNT
P350151-009 Brushed Nickel
P350151-031 Matte Black
13" dia., 6-1/2" ht.
Two medium base lamps, each 60w max.


P350151-031


P350151-009

SEMI-FLUSH CONVERTIBLE
P350150-009 Brushed Nickel
P350150-031 Matte Black
Hanging and ceiling mount hardware included.
16" dia., 13-1/2" ht.,
Overall ht. w/chain 47", wire 10'.
Three candelabra base lamps, each 60w max.


P350150-031*


P350150-009*

**Fixtures shown with P7826-01 vintage lamps, not included. See page 824.*

Austelle



P350154-141



P350154-020

Mesh shades are a signature detail, offering rustic elegance.

TWO-LIGHT FLUSH MOUNT
P350154-020 Antique Bronze
P350154-141 Galvanized
14" dia., 6-1/2" ht.
Two medium base lamps, each 60w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

Foster



P350116-071

Iron metal arms hold light bulbs within the frame for an open, yet intimate structure.

TWO-LIGHT FLUSH MOUNT
P350116-071 Gilded Iron
16" dia., 6" ht.
Two medium base lamps, each 60w max.

Fixture shown with P7825-01 vintage lamp, not included. See page 824.

Briarwood



P350022-143



P350022-020

Faux-painted wood encloses a classic geometric form and vintage-style bulbs.

ONE-LIGHT FLUSH MOUNT
P350022-020 Antique Bronze
P350022-143 Graphite
9-1/2" sq., 7-5/8" ht.
One medium base lamp, 60w max.

TWO-LIGHT FLUSH MOUNT
P350039-020 Antique Bronze
P350039-143 Graphite
12" sq., 6" ht.
Two medium base lamps, each 60w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.



P350039-143



P350039-020

Tilley

Warehouse-style mesh shades merge with a faux-painted, wooden rim.

THREE-LIGHT FLUSH MOUNT
P350091-009 Brushed Nickel
P350091-020 Antique Bronze
16″ dia., 9-7/8″ ht.
Three medium base lamps, each 60w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.



P350091-020



P350091-009

Gulliver

Wood-grained textured bands wrap together around vintage-style bulbs.

SEMI-FLUSH CONVERTIBLE
P350049-143 Graphite
P350049-141 Galvanized
Hanging and ceiling mount hardware included.
17″ dia., 13-1/2″ ht.
Overall ht. w/chain 52-1/2″; wire 10′.
Three medium base lamps, each 75w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.



P350049-143



P350049-141

Hemsworth

Barn-inspired metal detailing on either aged or bleached oak fixtures.

SEMI-FLUSH CONVERTIBLE
P350172-031 Black
P350172-141 Galvanized
Hanging and ceiling mount hardware included.
13-1/2″ sq., 10-1/8″ ht.,
Overall ht. w/chain 51″, wire 10′.
Two medium base lamps, each 60w max.



P350172-031



P350172-141

Cedar Springs

A fun take on the traditional warehouse shade, offered in design-forward finishes.

ONE-LIGHT SEMI-FLUSH
P550070-030 White
P550070-031 Black
P550070-039 Red
P550070-079 Pistachio
P550070-082 Metallic Gray
P550070-091 Navy
13-1/4" dia., 9-1/2" ht.
One medium base lamp, 100w max.

Fixtures can be installed outdoors.
See full collection on page 664.
All fixtures shown with P7825-01 vintage lamps, not included. *See page 824.*



P550070-030



P550070-031



P550070-039



P550070-079



P550070-082



P550070-091

Inspire

Traditional forms are freshened with flowing lines.

TWO-LIGHT SEMI-FLUSH
P3712-09 Brushed Nickel
P3712-20 Antique Bronze
13" dia., 10-1/8" ht.
Two medium base lamps, each 75w max.

TWO-LIGHT FLUSH MOUNT
P3713-09 Brushed Nickel
P3713-20 Antique Bronze
13" dia., 5-1/2" ht.
Two medium base lamps, each 60w max.

TWO-LIGHT SEMI-FLUSH
P350129-009 Brushed Nickel
P350129-143 Graphite
13" dia., 10-1/8" ht.
Two medium base lamps, each 75w max.

TWO-LIGHT FLUSH MOUNT
P350130-009 Brushed Nickel
P350130-143 Graphite
13" dia., 5-1/2" ht.
Two medium base lamps, each 60w max.

THREE-LIGHT SEMI-FLUSH
P350167-009 Brushed Nickel
P350167-143 Graphite
18" dia., 11-1/2" ht.
Three medium base lamps, each 60w max.

THREE-LIGHT SEMI-FLUSH
P350168-009 Brushed Nickel
P350168-020 Antique Bronze
18" dia., 11-1/2" ht.
Three medium base lamps, each 60w max.


P350130-009


P350130-143


P350129-009


P350129-143


P350167-009


P350167-143


P3713-09


P3713-20


P3712-09


P3712-20


P350168-009


P350168-020



P3843-77



P3843-09

Torino

Oversized, bell-shaped glass bowl offset squared scrolls or simple banding.

TWO-LIGHT FLUSH MOUNT
P3184-09 Brushed Nickel
P3184-77 Forged Bronze
14-5/8″ dia., 7-1/8″ ht.
Two medium base lamps, each 100w max.

SEMI-FLUSH CONVERTIBLE
P3843-09 Brushed Nickel
P3843-77 Forged Bronze
Hanging and ceiling mount hardware included.
18″ dia., 18-1/2″ ht.,
Overall ht. w/chain 94″; wire 15′.
Three medium base lamps, each 100w max.



P3184-77



P3184-09



P3720-20



P3720-09

Arden

Summer linen shades with etched glass diffuser.

SEMI-FLUSH CONVERTIBLE
P3720-09 Brushed Nickel
P3720-20 Antique Bronze
Hanging and ceiling mount hardware included.
14″ dia., 11-3/8″ ht.,
Overall ht. w/chain 50″; wire 10′.
Two medium base lamps, each 100w max.



P3739-20



P3739-09

TWO-LIGHT FLUSH MOUNT
P3739-09 Brushed Nickel
P3739-20 Antique Bronze
14″ dia., 6-5/8″ ht.
Two medium base lamps, each 60w max.

Applause

Traditional iron forms hold natural parchment-patterned or etched white parchment glass shades.



P3617-20



P3617-09

TWO-LIGHT FLUSH MOUNT
P3617-09 Brushed Nickel
P3617-20 Antique Bronze
14″ dia., 9″ ht.
Two medium base lamps, each 60w max.

Tinsley

Soft angles and impressive curves complement etched glass or open candle designs.

SEMI-FLUSH CONVERTIBLE
P350079-015 Polished Chrome
P350079-109 Brushed Bronze
Hanging and ceiling mount hardware included.
16-1/2" dia., 11-1/2" ht.,
Overall ht. w/chain 51", wire 10'.
Two medium base lamps, each 100w max.

TWO-LIGHT FLUSH MOUNT
P350103-015 Polished Chrome
P350103-109 Brushed Bronze
16-1/2" dia., 5-7/8" ht.
Two medium base lamps, each 60w max.



P350079-015



P350079-109



P350103-015



P350103-109

Trinity

Gracefully exotic soft angles, curving lines and etched glass offer classic sophistication.

SEMI-FLUSH CONVERTIBLE
P3473-09 Brushed Nickel
P3473-20 Antique Bronze
Hanging and ceiling mount hardware included.
16" dia., 14-3/4" ht.
Two medium base lamps, each 100w max.

ONE-LIGHT FLUSH MOUNT
P3475-09 Brushed Nickel
P3475-20 Antique Bronze
12-1/2" dia., 7-3/8" ht.
One medium base lamp, 100w max.

TWO-LIGHT FLUSH MOUNT
P3476-09 Brushed Nickel
P3476-20 Antique Bronze
15" dia., 7-1/4" ht.
Two medium base lamps, each 60w max.



P3473-09



P3473-20



P3475-09



P3475-20



P3476-09



P3476-20



P3633-20



P3633-15



P3644-20



P3644-15

Cascadia

Smooth forms and etched glass produce a beautiful, modern gaslight effect.

TWO-LIGHT FLUSH MOUNT
P3633-15 Polished Chrome
P3633-20 Antique Bronze
14″ dia., 6″ ht.
Two medium base lamps, each 60w max.

SEMI-FLUSH CONVERTIBLE
P3644-15 Polished Chrome
P3644-20 Antique Bronze
Hanging and ceiling mount hardware included.
14″ dia., 10″ ht.,
Overall ht. w/chain 49″; wire 10′.
Two medium base lamps, each 100w max.



P3663-20



P3663-09

Madison

Etched glass and transitional elements offer a simplified vintage style.

ONE-LIGHT FLUSH MOUNT
P3311-09 Brushed Nickel
P3311-20 Antique Bronze
12″ dia., 7-1/2″ ht.
One medium base lamp, 60w max.

TWO-LIGHT FLUSH MOUNT
P3312-09 Brushed Nickel
P3312-20 Antique Bronze
15-3/4″ dia., 8-1/4″ ht.
Two medium base lamps, each 60w max.

THREE-LIGHT SEMI-FLUSH
P3663-09 Brushed Nickel
P3663-20 Antique Bronze
Glass reverses up or down.
20-3/4″ dia., 14″ ht.
Three medium base lamps, each 60w max.



P3312-20



P3312-09



P3311-20



P3311-09

Alexa

Etched linen finished glass is complemented with a crisp, clear edge accent strip.

TWO-LIGHT SEMI-FLUSH
P2851-09 Brushed Nickel
P2851-20 Antique Bronze
12-1/4" dia., 11" ht.
Two medium base lamps,
each 100w max.

TWO-LIGHT FLUSH MOUNT
P3620-09 Brushed Nickel
P3620-20 Antique Bronze
12-1/4" dia., 6-3/8" ht.
Two medium base lamps,
each 60w max.


P2851-09


P2851-20


P3620-09


P3620-20

Invite

Etched glass with translucent mylar drum shade.

TWO-LIGHT FLUSH MOUNT
P3693-09 Brushed Nickel
P3693-20 Antique Bronze
12" dia., 5-3/8" ht.
Two medium base lamps,
each 60w max.

SEMI-FLUSH CONVERTIBLE
P3694-09 Brushed Nickel
P3694-20 Antique Bronze
Hanging and ceiling mount
hardware included.
15" dia., 5-1/4" ht.,
Overall ht. w/stem 71"; wire 12'.
Three medium base lamps,
each 100w max.


P3694-09


P3694-20


P3693-09


P3693-20

Clifton Heights

Clean linear forms with square etched glass shades.

TWO-LIGHT FLUSH MOUNT
P3852-09 Brushed Nickel
P3852-20 Antique Bronze
15" sq., 7-1/8" ht.
Two medium base lamps,
each 100w max.

ONE-LIGHT FLUSH MOUNT
P3854-09 Brushed Nickel
P3854-20 Antique Bronze
12-1/2" sq., 6-1/8" ht.
One medium base lamp,
100w max.


P3852-09


P3852-20


P3854-09


P3854-20



P3424-09



P3424-104



P3424-31



P3423-09



P3423-104



P3423-31

Replay

Etched glass, linear details and a pleasingly elegant frame.

TWO-LIGHT FLUSH MOUNT
P3423-09 Brushed Nickel
P3423-31 Black
P3423-104 Polished Nickel
14" dia., 5-3/4" ht.
Two medium base lamps, each 100w max.

SEMI-FLUSH CONVERTIBLE
P3424-09 Brushed Nickel
P3424-31 Black
P3424-104 Polished Nickel
Hanging and ceiling mount hardware included.
14-3/4" dia., 10" ht.
Overall ht. w/chain 50"; wire 10'.
Two medium base lamps, each 100w max.



P3561-09



P3480-20



P3567-09



P3483-20



P3563-09



P3481-20



P3569-09



P3484-20

Eclipse

Satin white glass enhances the smooth look of the simple banded frame.

TWO-LIGHT FLUSH MOUNT
P3480-20 Antique Bronze
P3561-09 Brushed Nickel
15-1/4" dia., 4-5/8" ht.
Two medium base lamps, each 60w max.

TWO-LIGHT SEMI-FLUSH
P3483-20 Antique Bronze
P3567-09 Brushed Nickel
15-1/4" dia., 10-5/8" ht.
Two medium base lamps, each 100w max.

THREE-LIGHT FLUSH MOUNT
P3481-20 Antique Bronze
P3563-09 Brushed Nickel
19-3/8" dia., 5-1/2" ht.
Three medium base lamps, each 60w max.

THREE-LIGHT SEMI-FLUSH
P3484-20 Antique Bronze
P3569-09 Brushed Nickel
19-3/8" dia., 13-1/4" ht.
Three medium base lamps, each 100w max.

Wisten

Adds minimalist flair with metal clip detailing, clean etched glass and substantial decorative knob.

TWO-LIGHT FLUSH MOUNT
P3290-09 Brushed Nickel
P3290-20 Antique Bronze
14" dia., 7" ht.
Two medium base lamps,
each 100w max.


P3290-20


P3290-09

Lahara

Timeless style with tapered etched glass shades for even illumination.

TWO-LIGHT FLUSH MOUNT
P3836-09 Brushed Nickel
P3836-15 Polished Chrome
13" dia., 6-1/8" ht.
Two medium base lamps,
each 100w max.


P3836-09


P3836-15

Joy/Bravo

Refreshing and fashionable arcing metal forms enhance etched white fluted glass.

TWO-LIGHT SEMI-FLUSH
P3855-09 Brushed Nickel
P3855-20W Antique Bronze
13-3/8" dia., 9-1/8" ht.
Two medium base lamps,
each 100w max.

SEMI-FLUSH CONVERTIBLE
P3864-09 Brushed Nickel
P3864-20W Antique Bronze
Hanging and ceiling mount
hardware included.
16-5/8" dia., 12-1/8" ht.,
Overall ht. w/chain 51"; wire 10'.
Three medium base lamps,
each 100w max.


P3864-20W


P3864-09


P3855-20W


P3855-09

Bedford

Softly diffused alabaster glass shades on a finely crafted metallic frame.

SEMI-FLUSH CONVERTIBLE
P3788-09 Brushed Nickel
Hanging and ceiling mount
hardware included.
10-1/2" dia., 14-1/2" ht.,
Overall ht. w/chain 54"; wire 15'.
One medium base lamp,
150w max.


P3788-09

Appeal

Contemporary design is anchored by square alabaster glass for elevated style.


P3991-09


P3991-15


P3991-20

ONE-LIGHT FLUSH MOUNT
P3991-09 Brushed Nickel
P3991-15 Polished Chrome
P3991-20 Antique Bronze
Etched opal glass.
7-1/2″ sq., 3-1/2″ ht.
One medium base lamp, 75w max.


P3549-09


P3549-15


P3549-20

TWO-LIGHT FLUSH MOUNT
P3549-09 Brushed Nickel
P3549-15 Polished Chrome
P3549-20 Antique Bronze
Etched opal glass.
9″ sq., 3-3/4″ ht.
Two medium base lamps, each 60w max.


P3511-09


P3511-15


P3511-20

TWO-LIGHT FLUSH MOUNT
P3511-09 Brushed Nickel
P3511-15 Polished Chrome
P3511-20 Antique Bronze
Etched opal glass.
11″ sq., 3-3/4″ ht.
Two medium base lamps, each 75w max.


P3992-09


P3992-15


P3992-20

THREE-LIGHT FLUSH MOUNT
P3992-09 Brushed Nickel
P3992-15 Polished Chrome
P3992-20 Antique Bronze
Etched opal glass.
13″ sq., 5″ ht.
Three medium base lamps, each 60w max.


P3490-09


P3490-20

TWO-LIGHT FLUSH MOUNT
P3490-09 Brushed Nickel
P3490-20 Antique Bronze
Alabaster glass.
9″ sq., 3-3/4″ ht.
Two medium base lamps, each 60w max.


P3551-09


P3551-20

TWO-LIGHT FLUSH MOUNT
P3551-09 Brushed Nickel
P3551-20 Antique Bronze
Alabaster glass.
11″ sq., 3-3/4″ ht.
Two medium base lamps, each 75w max.

Glass Domes

Classically styled with an etched glass dome shade, solid trim, and decorative knobs.

ONE-LIGHT FLUSH MOUNT
P350043-009 Brushed Nickel
P350043-143 Graphite
11" dia., 5-3/8" ht.
One medium base lamp, 60w max.

TWO-LIGHT FLUSH MOUNT
P350044-009 Brushed Nickel
P350044-143 Graphite
14" dia., 6-1/2" ht.
Two medium base lamps, each 75w max.

THREE-LIGHT FLUSH MOUNT
P350045-009 Brushed Nickel
P350045-143 Graphite
16-1/2" dia., 6-3/8" ht.
Three medium base lamps, each 60w max.

SEMI-FLUSH CONVERTIBLE
P350133-009 Brushed Nickel
P350133-143 Graphite
Hanging and ceiling mount hardware included.
15" dia., 11" ht.
Three medium base lamps, each 75w max.


P350043-009


P350043-143


P350044-009


P350044-143


P350045-009


P350045-143


P350133-009


P350133-143

Gather

Sleek frame features updated styling and elegant etched glass shades.

SEMI-FLUSH CONVERTIBLE
P3748-09 Brushed Nickel
P3748-20 Antique Bronze
Hanging and ceiling mount hardware included.
13" dia., 10-3/8" ht.
Overall ht. w/chain 24"; wire 6'.
Two medium base lamps, each 100w max.


P3748-09


P3748-20

Laird

Etched glass shade held by scrolled arms add an airy, traditional feel.



P350136-020



P350136-009

SEMI-FLUSH CONVERTIBLE
P350136-009 Brushed Nickel
P350136-020 Antique Bronze
Hanging and ceiling mount hardware included.
15-5/8" dia., 11-3/4" ht.,
Overall ht. w/chain 55"; wire 10'.
Three medium base lamps, each 100w max.



P350057-020



P350057-009

SEMI-FLUSH CONVERTIBLE
P350057-009 Brushed Nickel
P350057-020 Antique Bronze
Hanging and ceiling mount hardware included.
13" dia., 9-7/8" ht.,
Overall ht. w/chain 55", wire 10'.
Extends 9-7/8".
Two medium base lamps, each 100w max.

Semi-Flush

Fanciful scrolled arms hold a swirled alabaster glass bowl.



P3460-20



P3460-09

TWO-LIGHT SEMI-FLUSH
P3460-09 Brushed Nickel
P3460-20 Antique Bronze
13-1/4" dia., 13-3/4" ht.
Alabaster glass
Two medium base lamps, 60w max.



P3460-20ET



P3460-09ET

TWO-LIGHT SEMI-FLUSH
P3460-09ET Brushed Nickel
P3460-20ET Antique Bronze
Etched glass
13-1/4" dia., 13-3/4" ht.
Two medium base lamps, 60w max.

Dome Glass

A true classic, with dome-shaped alabaster glass, solid trim and decorative knobs.

ONE-LIGHT FLUSH MOUNT
P3924-09 Brushed Nickel
P3924-20 Antique Bronze
P3924-30 White
Alabaster glass
11-3/8" dia., 5-1/2" ht.
One medium base lamp,
60w max.

ONE-LIGHT FLUSH MOUNT
P3924-09ET Brushed Nickel
P3924-15ET Polished Chrome
P3924-20ET Antique Bronze
P3924-80 Forged Black
Etched glass
11-3/8" dia., 5-1/2" ht.
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE
P3927-09 Brushed Nickel
P3927-20 Antique Bronze
Etched Glass
Hanging and ceiling mount
hardware included.
13-1/4" dia., 11-3/8" ht.,
Overall ht. w/chain 50".
Two medium base lamps,
each 100w max.

SEMI-FLUSH CONVERTIBLE
P3927-15ET Polished Chrome
Etched Glass
Hanging and ceiling mount
hardware included.
13-1/4" dia., 11-3/8" ht.,
Overall ht. w/chain 50".
Two medium base lamps,
each 100w max.



P3924-09



P3924-20



P3924-30



P3924-80



P3924-09ET



P3924-15ET



P3924-20ET



P3927-09
shown as hanging



P3927-09



P3927-20
shown as hanging



P3927-20



P3927-15ET
shown as hanging



P3927-15ET



P3925-09



P3925-15ET



P3925-20



P3925-20EUL



P3925-30



P3925-80



P3926-09



P3926-15ET



P3926-20



P3926-20ET



P3926-30



P3926-80

Dome Glass

A true classic, with dome-shaped alabaster glass, solid trim and decorative knobs.

TWO-LIGHT FLUSH MOUNT
P3925-09 Brushed Nickel
P3925-20 Antique Bronze
P3925-30 White
Alabaster glass
13-1/4" dia., 5-7/8" ht.
Two medium base lamps, each 75w max.

TWO-LIGHT FLUSH MOUNT
P3925-09ET Brushed Nickel
P3925-15ET Polished Chrome
P3925-20ET Antique Bronze
P3925-80 Forged Black
Etched glass
13-1/4" dia., 5-7/8" ht.
Two medium base lamps, each 75w max.

TWO-LIGHT FLUSH MOUNT
P3925-20EUL Antique Bronze
Etched umber linen glass
13-1/4" dia., 5-7/8" ht.
Two medium base lamps, each 75w max.

THREE-LIGHT FLUSH MOUNT
P3926-09 Brushed Nickel
P3926-20 Antique Bronze
P3926-30 White
Alabaster glass
15-1/4" dia., 6-5/8" ht.
Three medium base lamps, each 60w max.

THREE-LIGHT FLUSH MOUNT
P3926-09ET Brushed Nickel
P3926-15ET Polished Chrome
P3926-20ET Antique Bronze
P3926-80 Forged Black
Etched glass
15-1/4" dia., 6-5/8" ht.
Three medium base lamps, each 60w max.

Ribbed Melon Glass

Etched ribbon melon glass adds simple detailing to classic metal trim and decorative knobs.

ONE-LIGHT FLUSH MOUNT
P3816-09 Brushed Nickel
P3816-20 Antique Bronze
P3816-30 White
11-3/8" dia., 6" ht.
One medium base lamp,
75w max.

TWO-LIGHT FLUSH MOUNT
P3817-09 Brushed Nickel
P3817-20 Antique Bronze
P3817-30 White
13-1/4" dia., 7" ht.
Two medium base lamps,
each 75w max.

THREE-LIGHT FLUSH MOUNT
P3818-09 Brushed Nickel
P3818-20 Antique Bronze
P3818-30 White
15-1/4" dia., 7-1/2" ht.
Three medium base lamps,
each 60w max.

SEMI-FLUSH MOUNT
P3876-09 Brushed Nickel
P3876-20 Antique Bronze
13-1/4" dia., 12-1/2" ht.
Two medium base lamps,
each 100w max.


P3876-09


P3876-20


P3816-09


P3816-20


P3817-09


P3817-20


P3818-09


P3818-20


P3816-30


P3817-30


P3818-30



P350146-009



P350147-009



P350146-031



P350147-031



P350146-012



P350147-012

Etched Glass

The unbeaten simplicity of white etched glass flush bowl paired with clean metal trim.

ONE-LIGHT FLUSH MOUNT
P350146-009 Brushed Nickel
P350146-012 Satin Brass
P350146-031 Black
11-1/2″ dia., 3-3/4″ ht.
One medium base lamp, 60w max.

TWO-LIGHT FLUSH MOUNT
P350147-009 Brushed Nickel
P350147-012 Satin Brass
P350147-031 Black
14″ dia., 4-5/8″ ht.
Two medium base lamps, each 60w max.



P3688-09



P3688-20



P3688-30



P3689-09



P3689-20



P3689-30



P3697-20



P3697-09



P3697-30

Alabaster Glass

Etched alabaster glass is combined with a modern banded metal trim.

ONE-LIGHT FLUSH MOUNT
P3688-09 Brushed Nickel
P3688-20 Antique Bronze
P3688-30 Textured White
11-1/2″ dia., 3-3/4″ ht.
One medium base lamp, 60w max.

TWO-LIGHT FLUSH MOUNT
P3689-09 Brushed Nickel
P3689-20 Antique Bronze
P3689-30 Textured White
14″ dia., 4-3/4″ ht.
Two medium base lamps, each 60w max.

THREE-LIGHT FLUSH MOUNT
P3697-09 Brushed Nickel
P3697-20 Antique Bronze
P3697-30 Textured White
17-1/2″ dia., 5-7/8″ ht.
Three medium base lamps, each 60w max.

6″ Fitter

ONE-LIGHT FLUSH MOUNT
P3408-09 Brushed Nickel
P3408-20 Antique Bronze
P3408-30 White
7-1/2″ dia., 4-3/8″ ht.
One medium base lamp,
60w max.

LED FLUSH MOUNT
P3408-0930K9 Brushed Nickel
P3408-3030K9 White
7-1/2″ dia., 4-3/8″ ht.
One 17w LED module, 3000K,
90 CRI, 1211 source lumens.


P3408-09
P3408-0930K9


P3408-20


P3408-30
P3408-3030K9

8″ Fitter

TWO-LIGHT FLUSH MOUNT
P3410-09 Brushed Nickel
P3410-20 Antique Bronze
P3410-30 White
9-1/2″ dia., 5-1/4″ ht.
Two medium base lamps,
each 60w max.


P3410-09


P3410-20


P3410-30

10″ Fitter

TWO-LIGHT FLUSH MOUNT
P3412-09 Brushed Nickel
P3412-20 Antique Bronze
P3412-30 White
11-3/4″ dia., 5-1/4″ ht.
Two medium base lamps,
each 75w max.


P3412-09


P3412-20


P3412-30

Clear Prismatic Glass

ONE-LIGHT FLUSH MOUNT
P3405-30 White
7-1/2″ dia., 4-3/4″ ht.
One medium base lamp,
60w max.

TWO-LIGHT FLUSH MOUNT
P3406-30 White
9-1/2″ dia., 5-1/4″ ht.
Two medium base lamps,
each 60w max.


P3405-30


P3406-30

Glass Globes

Various styles of glass globes suspended from a banded base, ideal for many interior settings.



P3203-30



P3401-09



P3401-20

ONE-LIGHT FLUSH MOUNT
P3203-30 White
White glass globe
6" dia., 7" ht.
One medium base lamp,
60w max.

ONE-LIGHT FLUSH MOUNT
P3401-09 Brushed Nickel
P3401-20 Antique Bronze
Alabaster glass globe
6" dia., 7-1/4" ht.
One medium base lamp,
60w max.



P3599-30



P3599-09



P3599-20

ONE-LIGHT FLUSH MOUNT
P3599-09 Brushed Nickel
P3599-20 Antique Bronze
P3599-30 White
Clear ribbed glass globe. K.O. for switch.
6" dia., 7-1/4" ht.
One medium base lamp,
60w max.



P3605-30



P3605-30SW



P3750-10

ONE-LIGHT FLUSH MOUNT
P3605-30 White
White glass globe. K.O. for switch.
6" dia., 7-1/4" ht.
One medium base lamp,
60w max.

ONE-LIGHT FLUSH MOUNT
P3605-30SW White
White glass globe with pullchain switch.
6" dia., 7-1/4" ht.
One medium base lamp,
60w max.

ONE-LIGHT FLUSH MOUNT
P3750-10 Polished Brass
Clear patterned acorn glass. K.O. for switch.
5-1/2" dia., 9-1/2" ht.
One medium base lamp,
60w max.

Round Glass

A round white glass shade in a white finish offers a modern edge.



P4609-30



P4610-30

ONE-LIGHT FLUSH MOUNT
P4609-30 White
12" dia., 5-1/2" ht.
Two medium base lamps,
each 60w max.

TWO-LIGHT FLUSH MOUNT
P4610-30 White
14-1/2" dia., 7" ht.
Three medium base lamps,
each 100w max.

Octagonal Beveled Glass

Traditional styling features clear, bound beveled glass in an octagonally shaped frame.

THREE-LIGHT FLUSH MOUNT
P5788-09 Brushed Nickel
P5788-10 Polished Solid Brass
P5788-20 Antique Bronze
9-3/4" dia., 5-7/8" ht.
Three G16.5 candelabra base, each 25w max.

FOUR-LIGHT FLUSH MOUNT
P5789-09 Brushed Nickel
P5789-10 Polished Solid Brass
P5789-20 Antique Bronze
11-1/8" dia., 6-1/4" ht.
Four G16.5 candelabra base, each 25w max.


P5788-09


P5788-10


P5788-20


P5789-09


P5789-10


P5789-20

Beveled Glass

Lantern-style fixture with classic beveled glass in a solid brass frame.

SEMI-FLUSH CONVERTIBLE
P5834-10 Polished Solid Brass
Hanging and ceiling mount hardware included.
7" dia., 10" ht.
One medium base lamp, 100w max.


P5834-10


P5834-10
shown as hanging

Clear Glass

Clear flat glass surrounds white candle sleeves held within a metal frame.

TWO-LIGHT CONVERTIBLE
P3690-09 Brushed Nickel
Hanging and ceiling mount hardware included.
8-3/4" sq., 10-1/2" ht.
Two candelabra base lamps, each 60w max.

THREE-LIGHT CONVERTIBLE
P3645-09 Brushed Nickel
Hanging and ceiling mount hardware included.
8-3/8" dia., 14-1/2" ht.
Three candelabra base lamps, each 60w max.


P3690-09


P3690-09
shown as hanging


P3645-09

Square Glass

Timeless square design is offered with a square patterned or plain white glass shade.



P4961-30



P4962-30

TWO-LIGHT FLUSH MOUNT
P4961-30 White
White glass
12" sq., 5-1/2" ht.
Two medium base lamps,
each 60w max.

TWO-LIGHT FLUSH MOUNT
P4962-30 White
Patterned White Glass
12" sq., 5-1/2" ht.
Two medium base lamps,
each 60w max.

White Glass

Elegant and modern round white glass shade in a white finish.



P3518-30



P3520-30



P3516-30

ONE-LIGHT FLUSH MOUNT
P3516-30 White
6-3/4" dia., 4-3/4" ht.
One medium base lamp,
60w max.

TWO-LIGHT FLUSH MOUNT
P3518-30 White
8-3/4" dia., 5" ht.
Two medium base lamps,
each 60w max.

TWO-LIGHT FLUSH MOUNT
P3520-30 White
10-3/4" dia., 5-3/8" ht.
Two medium base lamps,
each 75w max.

Apogee LED

Tiered metal banded trim holds etched glass shade providing an even, pleasing light effect.

SEMI-FLUSH CONVERTIBLE
P350064-009-30 Brushed Nickel
P350064-129-30 Architectural Bronze
Hanging and ceiling mount hardware included.
15" dia., 10-3/4" ht.,
Overall ht. w/chain 85-1/4, wire 15'.
30w integrated LED, 3000K, 90CRI, 1855 delivered lumens, 120-277V, 0-10V dimming.

SEMI-FLUSH CONVERTIBLE
P350065-009-30 Brushed Nickel
P350065-129-30 Architectural Bronze
Hanging and ceiling mount hardware included.
21" dia., 14-1/2" ht.,
Overall ht. w/chain 92", wire 15'.
45w integrated LED, 3000K, 90CRI, 2765 delivered lumens, 120-277V, 0-10V dimming.

SEMI-FLUSH CONVERTIBLE
P350066-009-30 Brushed Nickel
P350066-129-30 Architectural Bronze
Hanging and ceiling mount hardware included.
27" dia., 20-5/8" ht.,
Overall ht. w/chain 98, wire 15'.
71w integrated LED, 3000K, 90CRI, 4215 delivered lumens, 120-277V, 0-10V dimming.

FLUSH MOUNT
P350070-009-30 Brushed Nickel
P350070-129-30 Architectural Bronze
15" dia., 3-11/16" ht.
30w integrated LED, 3000K, 90CRI, 1660 delivered lumens, 120-277V, 0-10V dimming.

FLUSH MOUNT
P350071-009-30 Brushed Nickel
P350071-129-30 Architectural Bronze
21" dia., 4-1/2" ht.
45w integrated LED, 3000K, 90CRI, 2550 delivered lumens, 120-277V, 0-10V dimming.

FLUSH MOUNT
P350072-009-30 Brushed Nickel
P350072-129-30 Architectural Bronze
27" dia., 5-3/8" ht.
71w integrated LED, 3000K, 90CRI, 3850 delivered lumens, 120-277V, 0-10V dimming.

All fixtures:





P350066-129-30



P350066-009-30



P350065-129-30



P350065-009-30



P350064-129-30



P350064-009-30



P350070-129-30



P350070-129-30



P350071-129-30



P350071-129-30



P350072-129-30



P350072-129-30



P3612-0930K9



P3610-0930K9



P3611-0930K9



P3611-2030K9



P3612-2030K9



P3610-2030K9



P2308-0930K9



P350114-031-30



P350114-009-30

Weaver LED

A linen drum shade with a linen glass diffuser offers a slim and modern profile.

ONE-LIGHT LED FLUSH MOUNT
P3610-0930K9 Brushed Nickel
P3610-2030K9 Antique Bronze
10" dia., 3-1/2" ht.
One 17w LED module, 3000K, 90 CRI, 1211 source lumens.

TWO-LIGHT LED FLUSH MOUNT
P3611-0930K9 Brushed Nickel
P3611-2030K9 Antique Bronze
16" dia., 4" ht.
Two 17w LED modules, 3000K, 90 CRI, 1211 source lumens per module.

THREE-LIGHT LED FLUSH MOUNT
P3612-0930K9 Brushed Nickel
P3612-2030K9 Antique Bronze
22" dia., 4-1/2" ht.
Three 17w LED modules, 3000K, 90 CRI, 1211 source lumens per module.

All fixtures:

Beyond LED

Acrylic diffuser ornamented with metal knobs adds a touch of sophistication.

LED FLUSH MOUNT
P2308-0930K9 Brushed Nickel
Acrylic with white, bronze and brushed nickel knobs included.
12" dia., 2-3/4" ht.
One 17w LED module, 3000K, 90 CRI, 1211 source lumens.

Box LED

Geometric shaping lends elegance to the box frame and square glass.

ONE LIGHT LED FLUSH MOUNT
P350114-009-30 Brushed Nickel
P350114-031-30 Black
10-1/8" sq., 4-1/4" ht., wire 6".
One 17w LED module, 3000K, 90CRI, 1276 source lumens.

Surface Mount LED

Clean modern-lined banded trim holds a white acrylic diffuser.

LED FLUSH MOUNT
P7249-0930K9 Brushed Nickel
P7249-17430K9 Urban Bronze
10-3/8" W., 3-1/2 ht.
21.7w integrated LED, 3000K, 90CRI, 1027 delivered lumens.

LED SURFACE MOUNT
P7250-0930K9 Brushed Nickel
P7250-17430K9 Urban Bronze
17-3/4" W., 4-3/4" ht.
30w integrated LED, 3000K, 90CRI, 1765 delivered lumens.

LED SURFACE MOUNT
P7251-0930K9 Brushed Nickel
P7251-17430K9 Urban Bronze
32-1/2" L., 18"W., 4-3/4" ht.
39w integrated LED, 3000K, 90CRI, 2649 delivered lumens, 120-277V.

LED SURFACE MOUNT
P7253-0930K9 Brushed Nickel
P7253-17430K9 Urban Bronze
14 dia., 3-3/4" ht.
22w integrated LED, 3000K, 90CRI, 1184 delivered lumens.

All fixtures:





P7249-0930K9



P7249-17430K9



P7253-0930K9



P7253-17430K9



P7250-0930K9



P7250-17430K9



P7251-0930K9



P7251-17430K9

Helm LED

Craftsman-inspired architecturally detailed trim encases a square acrylic diffuser.

ONE-LIGHT LED FLUSH MOUNT
P3447-0930K9 Brushed Nickel
P3447-2030K9 Antique Bronze
Ceiling or wall mount.
11" sq., 3-3/4" ht.
One 17w LED module, 3000K,
90 CRI, 1211 source lumens.

TWO-LIGHT LED FLUSH MOUNT
P3448-0930K9 Brushed Nickel
P3448-2030K9 Antique Bronze
Ceiling or wall mount.
14" sq., 3-3/4" ht.
Two 17w LED modules, 3000K,
90 CRI, 1211 source lumens,
per module.

THREE-LIGHT LED FLUSH MOUNT
P3449-0930K9 Brushed Nickel
P3449-2030K9 Antique Bronze
Ceiling or wall mount.
18" sq., 3-3/4" ht.
Three 17w LED modules, 3000K,
90 CRI, 1211 source lumens,
per module.

All fixtures:

ADA



P3447-2030K9



P3447-0930K9



P3448-2030K9



P3448-0930K9



P3449-2030K9



P3449-0930K9

Fresnel LED

Industrial styling with a nautical-inspired Fresnel glass lens offers both form and function.

LED FLUSH MOUNT
P350113-009-30 Brushed Nickel
P350113-015-30 Polished Chrome
P350113-108-30 Oil Rubbed Bronze
12-3/4" dia., 4-1/2" ht.
One 17w LED module, 3000K,
90CRI, 1276 source lumens.

All fixtures:

JA8



P350113-009-30



P350113-108-30



P350113-015-30

Bezel LED

Sleek and slim in appearance with etched white glass shade offering a pleasant glow from the bottom and sides.

LED FLUSH MOUNT
P350085-009-30 Brushed Nickel
P350085-015-30 Polished Chrome
P350085-020-30 Antique Bronze
10-1/2" dia., 3-1/2" ht.
One 17w LED module, 3000K, 90CRI, 1276 source lumens.

LED FLUSH MOUNT
P350086-009-30 Brushed Nickel
P350086-015-30 Polished Chrome
P350086-020-30 Antique Bronze
13" dia., 3-7/8" ht.
One 25w LED module, 3000K, 90CRI, 1770 source lumens.

LED FLUSH MOUNT
P350087-009-30 Brushed Nickel
P350087-015-30 Polished Chrome
P350087-020-30 Antique Bronze
16" dia., 4-3/4" ht.
One 26w LED module, 3000K, 90CRI, 1770 source lumens.

All fixtures:


P350085-009-30


P350085-020-30


P350085-015-30


P350086-020-30


P350086-015-30


P350086-009-30


P350087-009-30


P350087-020-30


P350087-015-30



P350089-143-30



P350089-121-30



P350089-078-30

Finesse LED

The beautifully graphic cage frame closes in a circular pattern around an etched opal glass shade.

ONE-LIGHT LED FLUSH MOUNT
P350089-078-30 Vintage Gold
P350089-121-30 Metallic Silver
P350089-143-30 Graphite
15" dia., 4-1/2" ht.
One 17w LED module, 3000K, 90CRI, 1452 source lumens.

All fixtures:



P2320-2030K9



P2318-2030K9



P2320-0930K9



P2318-0930K9



P2332-0930K9



P2330-0930K9

Mingle LED

Decorative metal frame highlights geometric shapes around a fabric shade and glass diffuser.

FLUSH MOUNT
P2318-0930K9 Brushed Nickel
P2318-2030K9 Antique Bronze
11" dia., 5-7/8" ht.
One 17w LED module, 3000K, 90CRI, 1211 source lumens.

SEMI-FLUSH MOUNT
P2320-0930K9 Brushed Nickel
P2320-2030K9 Antique Bronze
14" dia., 10-1/2" ht.
One 17w LED module, 3000K, 90CRI, 1211 source lumens.

FLUSH MOUNT
P2330-0930K9 Brushed Nickel
11" dia., 5-7/8" ht.
One 17w LED module, 3000K, 90CRI, 1211 source lumens.

SEMI-FLUSH MOUNT
P2332-0930K9 Brushed Nickel
14" dia., 10-1/2" ht.
One 17w LED module, 3000K, 90CRI, 1211 source lumens.

All fixtures:

Inspire LED

Traditional forms are freshened with flowing lines and LED lamping.

LED SEMI-FLUSH MOUNT
P350134-009-30 Brushed Nickel
P350134-143-30 Antique Bronze
13" dia., 10-5/8" ht.
One 17w LED module, 3000K, 90CRI, 1452 source lumens.

LED FLUSH MOUNT
P350135-009-30 Brushed Nickel
P350135-143-30 Antique Bronze
13" dia., 6" ht.
One 17w LED module, 3000K, 90CRI, 1452 source lumens.

LED SEMI-FLUSH MOUNT
P3683-0930K9 Brushed Nickel
P3683-2030K9 Antique Bronze
13" dia., 10-5/8" ht.
One 17w LED module, 3000K, 90CRI, 1452 source lumens.

LED FLUSH MOUNT
P3696-0930K9 Brushed Nickel
P3696-2030K9 Antique Bronze
13" dia., 6" ht.
One 17w LED module, 3000K, 90CRI, 1452 source lumens.

All fixtures:





P350135-143-30



P350135-009-30



P350134-143-30



P350134-009-30



P3696-0930K9



P3696-2030K9



P3683-0930K9



P3683-2030K9

Dome LED

A domed, linen finish glass diffuser is discreetly supported from metal fittings.

LED FLUSH MOUNT
P350055-009-30 Brushed Nickel
12" dia., 4-1/4" ht.
20w integrated LED, 3000K, 90 CRI, 1000 delivered lumens.

LED FLUSH MOUNT
P350056-009-30 Brushed Nickel
16" dia., 4-1/2" ht.
24w integrated LED, 3000K, 90 CRI, 1144 delivered lumens.

All fixtures:





P350055-009-30



P350056-009-30

Portal LED

An ample metal band is adorned with industrial-inspired accents and finished with a white acrylic diffuser.

LED FLUSH MOUNT
P3631-0930K9 Brushed Nickel
P3631-1530K9 Polished Chrome
9″ dia., 2-1/2″ ht.
One 17w LED module, 3000K, 90 CRI, 1211 source lumens.

LED FLUSH MOUNT
P3632-0930K9 Brushed Nickel
P3632-1530K9 Polished Chrome
13″ dia., 2-1/2″ ht.
One 29w LED module, 3000K, 90 CRI, 2197 source lumens.

LED FLUSH MOUNT
P3658-0930K9 Brushed Nickel
P3658-2030K9 Antique Bronze
11″ dia., 3-7/8″ ht.
One 17w LED module, 3000K, 90 CRI, 1211 source lumens.

All fixtures:



P3631-1530K9



P3631-0930K9



P3632-1530K9



P3632-0930K9



P3658-2030K9



P3658-0930K9

Gather LED

Sleek frame features updated styling and elegant etched glass shades.

SEMI-FLUSH CONVERTIBLE
P350088-009-30 Brushed Nickel
P350088-015-30 Polished Chrome
P350088-020-30 Antique Bronze
Hanging and ceiling mount hardware included.
12-7/8″ dia., 10-3/8″ ht.,
Overall ht. w/chain 50″, wire 10′.
One 17w LED module, 3000K, 90CRI, 1276 source lumens.

All fixtures:

P350088-020-30
shown as hanging



P350088-009-30
shown as hanging



P350088-015-30
shown as hanging





P350088-015-30

Flush Mount LED

Etched glass dominates a traditional design with its distinctive and sculptural bowl paired with a metal frame.

LED FLUSH MOUNT
P350051-009-30 Brushed Nickel
P350051-020-30 Antique Bronze
11" dia., 4-3/16" ht.
One 17w LED module, 3000K, 90CRI, 1452 source lumens.

LED FLUSH MOUNT
P350052-009-30 Brushed Nickel
P350052-020-30 Antique Bronze
12-9/16" dia., 4-1/2" ht.
One 25w LED module, 3000K, 90CRI, 2015 source lumens.

LED FLUSH MOUNT
P350053-009-30 Brushed Nickel
P350053-020-30 Antique Bronze
11" dia., 4" ht.
One 17w LED module, 3000K, 90CRI, 1452 source lumens.

LED FLUSH MOUNT
P350054-009-30 Brushed Nickel
P350054-020-30 Antique Bronze
13-1/4" dia., 4-3/4" ht.
One 25w LED module, 3000K, 90CRI, 2015 source lumens.

LED FLUSH MOUNT
P350100-009-30 Brushed Nickel
P350100-015-30 Polished Chrome
P350100-020-30 Antique Bronze
11" dia., 4-1/4" ht.
One 17w LED module, 3000K, 90CRI, 1276 source lumens.

LED FLUSH MOUNT
P350101-009-30 Brushed Nickel
P350101-015-30 Polished Chrome
P350101-020-30 Antique Bronze
13-1/2" dia., 4-1/2": ht.
One 25w LED module, 3000K, 90CRI, 1770 source lumens.

LED FLUSH MOUNT
P350131-009-30 Brushed Nickel
P350131-015-30 Polished Chrome
P350131-020-30 Antique Bronze
15-1/2" dia., 5-1/4" ht.
One 25w LED module, 3000K, 90CRI, 1770 source lumens.

All fixtures:





P350051-009-30



P350051-020-30



P350052-009-30



P350052-020-30



P350053-009-30



P350053-020-30



P350054-009-30



P350054-020-30



P350100-009-30



P350100-015-30



P350100-020-30



P350101-009-30



P350101-015-30



P350101-020-30



P350131-009-30



P350131-015-30



P350131-020-30



P350081-009-30



P350081-020-30



P350082-009-30



P350082-020-30

Opal-Linen LED

Opal glass shade paired with a linen-textured diffuser and architecturally detailed metal trim.

LED FLUSH MOUNT
P350081-009-30 Brushed Nickel
P350081-020-30 Antique Bronze
12" dia., 4-3/4" ht.
One 17w LED module, 3000K, 90CRI, 1452 source lumens.

LED FLUSH MOUNT
P350082-009-30 Brushed Nickel
P350082-020-30 Antique Bronze
15" dia., 5" ht.
One 25w LED module, 3000K, 90CRI, 2015 source lumens.

All fixtures:

JA8



P3665-3130K9



P3673-3130K9

Milford LED

Octagonal aluminum metal frame surrounds white etched glass.

ONE-LIGHT FLUSH MOUNT
P3665-3130K9 Black
8-5/8" dia., 4-1/8" ht.
One 17w LED module, 3000K, 90CRI, 1211 source lumens.

ONE-LIGHT FLUSH MOUNT
P3673-3130K9 Black
10-5/8" dia., 4-7/8" ht.
One 17w LED module, 3000K, 90CRI, 1211 source lumens.

All fixtures:



P7258-0930K9



P7258-17430K9

Surface Mount Linear LED

Thin geometric-styled metal end caps and acrylic shade offer a modern impact.

LED LINEAR FLUSH MOUNT
P7258-0930K9 Brushed Nickel
P7258-17430K9 Urban Bronze
48-1/2" L., 11-13/16" W., 4-1/2" ht.
53w integrated LED, 3000K, 90CRI, 3559 delivered lumens.

All fixtures:

JA8

Alabaster LED

Etched alabaster glass is combined with a modern banded metal trim and LED lamping.

LED FLUSH MOUNT
P350002-009-30 Brushed Nicke
P350002-020-30 Antique Bronze
13" dia., 6-1/2" ht.
21w integrated LED, 3000K,
90CRI, 1231 delivered lumens.

LED FLUSH MOUNT
P350003-009-30 Brushed Nicke
P350003-020-30 Antique Bronze
15" dia., 6-3/4" ht.
28w integrated LED, 3000K,
90CRI, 1416 delivered lumens.

All fixtures:


P350002-009-30


P350002-020-30


P350003-009-30


P350003-020-30

Square Alabaster Glass LED

Classic, square alabaster glass bowl is trimmed with architecturally detailed metal.

LED FLUSH MOUNT
P350019-009-30 Brushed Nickel
P350019-020-30 Antique Bronze
9-1/2" sq., 4-3/8" ht.
One 17w LED module, 3000K,
90CRI, 1452 source lumens.

LED FLUSH MOUNT
P350020-009-30 Brushed Nickel
P350020-020-30 Antique Bronze
11-3/8" sq., 5" ht.
One 25w LED module, 3000K,
90CRI, 2015 source lumens.

All fixtures:


P350019-009-30


P350019-020-30


P350020-009-30


P350020-020-30

Linen LED

White linen glass bowl trimmed with metal banding and punctuated with a metal knob.



P350005-009-30



P350006-009-30



P350007-009-30



P350008-009-30

LED FLUSH MOUNT
P350005-009-30 Brushed Nickel
11" dia., 4-5/8" ht.
21w integrated LED, 3000K,
90CRI, 921 delivered lumens.

LED FLUSH MOUNT
P350006-009-30 Brushed Nickel
13" dia., 5-3/8": ht.
21w integrated LED, 3000K,
90CRI, 1152 delivered lumens.

LED FLUSH MOUNT
P350007-009-30 Brushed Nickel
15" dia., 5-7/8" ht.
28w integrated LED, 3000K,
90CRI, 1389 delivered lumens.

LED FLUSH MOUNT
P350008-009-30 Brushed Nickel
19" dia., 7-1/8" ht.
30w integrated LED, 3000K,
90CRI, 1984 delivered lumens.

All fixtures:

JA8

Square Linen Glass LED

Classic square linen glass bowl is trimmed with architecturally detailed metal.



P350023-009-30



P350023-020-30



P350024-009-30



P350024-020-30

LED FLUSH MOUNT
P350023-009-30 Brushed Nickel
P350023-020-30 Antique Bronze
9-1/2" sq., 4-3/8" ht.
One 17w LED module, 3000K, 90CRI,
1452 source lumens.

LED FLUSH MOUNT
P350024-009-30 Brushed Nickel
P350024-020-30 Antique Bronze
11-1/2" sq., 4-7/8" ht.
One 25w LED module, 3000K, 90CRI,
2015 source lumens.

All fixtures:

JA8

Cloud + Drum LED

Choose either a classic white round diffuser or cloud-like diffuser.

LED DRUM
P730002-030-30 White
13-5/8" W., 4" ht.
22.5w integrated LED, 3000K,
90CRI, 2025 delivered lumens.

LED DRUM
P730003-030-30 White
17" W., 4" ht.
28w integrated LED, 3000K,
90CRI, 2520 delivered lumens.

LED DRUM
P730005-030-30 White
P730005-031-30 Black
11" W., 4" ht.
21w integrated LED, 3000K,
90CRI, 1680 delivered lumens.

LED CLOUD
P730006-030-30 White
13-5/8" W., 4" ht.
22.5w integrated LED, 3000K,
90CRI, 1845 delivered lumens.

LED CLOUD
P730007-030-30 White
17" W., 4" ht.
28w integrated LED, 3000K,
90CRI, 2548 delivered lumens.

LED CLOUD
P730008-030-30 White
11" W., 4" ht.
21w integrated LED, 3000K,
90CRI, 1575 delivered lumens.

LED CLOUD
P810025-030-30 White
11" dia., 3-1/2" ht.
15w integrated LED, 3000,
90CRI, 1152 delivered lumens.

LED CLOUD
P810026-030-30 White
13-3/4" dia., 3-3/4" ht.
20w integrated LED, 3000,
90CRI, 1431 delivered lumens.

All fixtures:

JA8



P730002-030-30



P730003-030-30



P730005-030-30



P730005-031-30



P730006-030-30



P730007-030-30

P730008-030-30

P810026-030-30

P810026-030-30

Maier LED

Simplicity rules with a white opal acrylic diffuser held by double-banded metal trim.



P350076-020-30



P350076-030-30



P350076-009-30



P350077-020-30



P350077-030-30



P350077-009-30



P350078-020-30



P350078-030-30



P350078-009-30

LED SEMI-FLUSH
P350076-009-30 Brushed Nickel
P350076-020-30 Antique Bronze
P350076-030-30 White
9-1/16" dia., 4-5/16" ht.
20.5w integrated LED, 3000K,
90CRI, 1354 delivered lumens.

LED SEMI-FLUSH
P350077-009-30 Brushed Nickel
P350077-020-30 Antique Bronze
P350077-030-30 White
14" dia., 4-3/4" ht.
26w integrated LED, 3000K,
90CRI, 2016 delivered lumens.

LED SEMI-FLUSH
P350078-009-30 Brushed Nickel
P350078-020-30 Antique Bronze
P350078-030-30 White
18" dia., 5-1/4" ht.
28.5w integrated LED, 3000K,
90CRI, 2064 delivered lumens.

All fixtures:

JA8

Z-1060 LED

A minimalist, yet welcoming cylinder-shaped, etched opal glass shade hangs from a handsome black ceiling plate.



P550071-031-30

LED FLUSH MOUNT
P550071-031-30 Black
4-1/2" dia., 4-3/8" ht., wire 6".
9w Module LED, 3000K,
90CRI, 624 source lumens.

Linear Cloud LED

White contoured shallow acrylic cloud lens in LED offers both form and function.

LED LINEAR CLOUD
P7278-3030K9 White
26″ L., 10-1/4″ W., 3-1/4″ ht.
27w integrated LED, 3000K,
90CRI, 1974 delivered lumens.



P7278-3030K9

LED LINEAR CLOUD
P7279-3030K9 White
51″ L., 11-3/4″ W., 4-3/4″ ht.
40w integrated LED, 3000K,
90CRI, 2908 delivered lumens.



P7279-3030K9

All fixtures:

Wrap-Arounds

Clear extruded prismatic acrylic diffuser with squared white end caps and white chassis.

WRAP-AROUNDS
P7183-30EB White
24″ L., 7-3/4″ W., 3″ ht.
120v NPF, 2-F17T8 lamps.



P7183-30EB

WRAP-AROUNDS
P7186-30EB White
48″ L., 7-3/4″ W., 3″ ht.
120v HPF, 2-F32T8 lamps.



P7186-30EB

WRAP-AROUNDS
P7196-30EB White
48″ L., 14-5/8″ W., 3″ ht.
120v HPF, 4-F32T8 lamps.



P7196-30EB

Wrap & Strip LED

White acrylic diffuser, white end caps, white metal chassis. For kitchens, laundry rooms, garage, utility areas, and work spaces.

P730000-030-30

2FT LED STRIP
P730000-030-30 White
23-11/16" L., 2-1/4" W., 2-3/8" ht.
21w integrated LED, 3000K,
90CRI, 1600 lumens.

P730001-030-30

4FT LED STRIP
P730001-030-30 White
47-1/4" W., 2-1/4" W., 2-3/8" ht.
36w LED, 3000, 90CRI,
90CRI, 3200 lumens.

P730011-030-30

2FT LED WRAP
P730011-030-30 White
23-3/4" L., 6-3/16" W., 3" ht.
21w integrated LED, 3000K,
90CRI, 1700 lumens.

P730012-030-30


4FT LED WRAP
P730012-030-30 White
47-3/8" L., 6-3/16" W., 3" ht.
36w integrated LED, 3000K,
90CRI, 3400 lumens.

All fixtures:
Dimmable to 10% with Triac and ELV dimmers

JA8

Featuring Hinton and Benton Harbor





Sconces

Function *Plus* Beauty

Scan and see more at
progresslighting.com





James Thomas
Senior Product Designer

Modernly Minimalism

with James

Modern interiors showcase sleek design through the use of neutrals, a minimalism approach, and the use of glass décor and technology. Take advantage of spaces with wide windows and use glass in other details such as countertops and furniture. This creates a sleek design for interior spaces. Integrate new innovations into a home's décor by adding elements, such as voice activated devices and remote controlled light dimmers. To accentuate a Modern color palette, stick to neutral shades, as well as an overall minimalistic design to create this look.

Shop this style at
progresslighting.com/modern



Status

A gleaming glass accent adds a playful punch of status to the shade's simple round silhouette.

P2060-15 Polished Chrome
6" W., 15-1/2" ht.
Extends 7-3/8". H/CTR 8-3/4".
One medium base lamp,
100w max.

Fixture shown with P7826-01 vintage lamp. See page 824



P2060-15

Draper

Polished architectural detailing and a tubular candelabra offer style, charm and intrigue.

P2101-104 Polished Nickel
4-1/2" W., 8" ht.
Extends 4-1/8". H/CTR 4".
One candelabra base lamp,
60w max.



P2101-104

Nealy

Curved mixed metal, shimmering glass, and silk shade combine for classic charm and modern luxury.

P710046-009 Brushed Nickel
5-1/2" dia., 16-5/8" ht.
Extends 7". H/CTR 7-1/2".
One candelabra base lamp,
60w max.



P710046-009

Caress

A shimmering water glass shade and polished frame add rich textures and playful reflections.

P7046-104WB Polished Nickel
8" W., 15" ht.
Extends 9-1/2". H/CTR 8-7/8".
One candelabra base krypton lamp,
60w max, included.

Replacement lamp P7807-01. See page 824.



P7046-104WB

Tinsley

Soft angles and impressive sculptural curves complement an open candle design.

P710028-109 Brushed Bronze
P710028-015 Polished Chrome
4-7/8" W., 15-1/2" ht.
Extends 5-1/2". H/CTR 8".
One candelabra base lamp,
60w max.



P710028-015



P710028-109

Featuring Draper





P710056-143



P710056-009

Rainey

Asymmetrical styling, mixed metal and clear fluted ribbon glass make a bold statement.

P710056-009 Brushed Nickel
P710056-143 Graphite
11-1/2" W., 16-1/2" ht.
Extends 5-1/8". H/CTR 5-5/8".
Two candelabra base lamps, each 60w max.

Fixture shown with P7826-01 vintage lamp. See page 824

Riley

Smooth metal arms hold simple light bases topped with elegant, elongated clear glass shades.

P710082-009 Brushed Nickel
P710082-031 Black
5" W., 14-1/2" ht.
Extends 4-5/8". H/CTR 7-3/4".
One candelabra base lamp, 60w max.

Fixture shown with P7826-01 vintage lamp. See page 824



P710082-009



P710082-031

Dart

Etched white glass shades balance on a striking arched frame.

P300144-143 Graphite
4-1/2" W., 16-7/8" ht.
Extends 6-7/8". H/CTR 8".
One medium base lamp, 100w max.



P300144-143

Caisson

Industrial styled fixtures feature curled, clear glass shades dangling from fabric cords.

P300215-009 Brushed Nickel
P300215-143 Graphite
7-7/8" W., 14-3/4" ht.
Extends 10". H/CTR 11-1/4".
One medium base lamp, 60w max.



P300215-009



P300215-143



P300120-143



P300120-009

Kene

A soft metal curve supports an etched glass shade offering elegance and charm.

P300120-143 Graphite
P300120-009 Brushed Nickel
4-3/4" W., 12-7/8" ht.
Extends 6-1/2". H/CTR 8-7/8".
One medium base lamp,
75w max.



P710089-031



P710089-009

Chadwick

Overscale geometric forms, clean, crisp lines accented by a soft glass shade are ideal for minimalist settings.

P710089-009 Brushed Nickel
P710089-031 Black
5-1/2" W., 18" ht.
Extends 5-3/8". H/CTR 14-1/4".
One medium base lamp,
100w max.



P710073-031



P710073-009

Lassiter

Clean, sharp-angled arms hold striking, vintage-styled light sockets and clear shades.

P710073-009 Brushed Nickel
P710073-031 Black
4-7/8" W., 19-1/4" ht.
Extends 6-1/2". H/CTR 9-3/8".
One medium base lamp,
60w max.

Fixture shown with P7825-01 vintage lamp. See page 824

Hartwick

Stunning cylinder-shaped diffuser banded with a thin, rounded metal bar tops a sophisticated pedestal.

P710087-009 Brushed Nickel
P710087-012 Satin Brass
P710087-031 Black
4-1/2″ W., 13-1/2″ ht.
Extends 4″. H/CTR 9-1/8″.
One medium base lamp, 60w max.

P710088-009 Brushed Nickel
P710088-012 Satin Brass
P710088-031 Black
5″ W., 18″ ht.
Extends 4″. H/CTR 13-5/8″.
One medium base lamp, 60w max.

All fixtures:

ADA



P710087-009



P710087-012



P710087-031



P710088-009



P710088-012



P710088-031

Cherish

Classic candle covers are refreshed with an elegant summer linen shade.

P7172-09 Brushed Nickel
P7172-20 Antique Bronze
12″ W., 9″ ht.
Extends 6-1/2″. H/CTR 4-3/4″.
Two candelabra base lamps, each 60w max.



P7172-20
shown with Antique Brass candle covers



P7172-20
shown with Antique Bronze candle covers



P7172-09



P7156-81



P7156-20

Archives

Carefully crafted details and distinctive accents achieve a vintage electric feel.

P7156-20 Antique Bronze
P7156-81 Antique Nickel
9″ dia., 7″ ht.
Extends 10″. H/CTR 2-3/8″.
One medium base lamp, 100w max.

P2809-20 Antique Bronze
P2809-81 Antique Nickel
Can be installed vertically or horizontally.
18-1/2″ W., 4-3/4″ ht.
Extends 7″. H/CTR 2-3/8″.
Two medium base lamps, each 100w max.

Fixture shown with P7825-01 vintage lamp. See page 824



P2809-20



P2809-81



P2809-20
shown horizontally



P2809-81
shown horizontally

Swing

A natural brass reflector with bronze accents are a uniquely authentic fit for the vintage electric trend.

P7159-20 Antique Bronze
Natural Brass backplate.
11-3/4″ W., 11-3/4″ ht.
Extends 4″. H/CTR 5-7/8″.
One medium base lamp, 60w max.

Fixture shown with P7825-01 vintage lamp. See page 824



P7159-20

Cirrine

Hand-formed, artistically painted arches and etched glass shade offer an elegant lighting solution.frame.

P7149-20 Antique Bronze
8″ W., 8″ ht.
Extends 4″. H/CTR 4″.
One medium base lamp, 75w max.

ADA



P7149-20

Mast

A faux wood backplate blends with a clean, modern pediment and double glass shade.

P710015-009 Brushed Nickel
P710015-020 Antique Bronze
5" W., 13" ht.
Extends 6-3/8". H/CTR 6-1/2".
One medium base lamp,
100w max.



P710015-009



P710015-020

Greyson

An iron frame ornamented with twist elements supports classic candle slip.

P7158-31 Black
4" W., 8-1/4 ht.
Extends 4-3/4". H/CTR 4-1/8".
One candelabra base lamp,
60w max.



P7158-31

Durrell

Curved arms sweep outwards from a faux wood, oval backplate.

P710074-009 Brushed Nickel
P710074-031 Black
4-1/2" W., 12" ht.
Extends 5". H/CTR 6".
One candelabra base lamp,
60w max.

Fixture shown with P7826-01 vintage lamp. See page 824



P710074-031



P710074-009

Briarwood

Faux-painted wood encloses a classic geometric form and vintage-style bulbs.

P710012-143 Graphite
P710012-020 Antique Bronze
6-7/8" W., 12" ht.
Extends 6", H/CTR 4".
One medium base lamp,
100w max.

Fixture shown with P7825-01 vintage lamp. See page 824



P710012-143



P710012-020

Hemsworth

Barn-inspired metal detailing punctuates either aged or bleached oak backplates.

P710093-031 Black
P710093-141 Galvanized
4-3/4" W., 16-3/4" ht.
Extends 3-7/8". H/CTR 10-3/4".
One medium base lamp,
60w max.

Fixture shown with P7825-01 vintage lamp. See page 824



P710093-141



P710093-031

Gulliver

Wood-grained textured bands wrap together to enclose the bulb.

P710031-143 Graphite
P710031-141 Galvanized
6" dia., 12" ht.
Extends 7". H/CTR 9-3/8".
One medium base lamp,
75w max.

Fixture shown with P7825-01 vintage lamp. See page 824



P710031-141



P710031-143

Barnes Mill

Exposed iron details and a faux-painted wooden plank support clear seeded glass shades.

P300066-020 Antique Bronze
4 1/2" W., 11 7/8" ht.
Extends 5 7/8". H/CTR 7-5/8".
One medium base lamp,
100w max.

Fixture shown with P7825-01 vintage lamp. See page 824



P300066-020

Milner

A crisp, clear glass shade contrasts beautifully with the swing arm and metal backplate.

P710086-009 Brushed Nickel
P710086-031 Black
Adjustable arm.
On/off rotary switch on backplate.
5-5/8″ W., 9″ ht.
Extends 10-3/8″. H/CTR 3-1/4″.
One medium base lamp,
60w max.



P710086-031



P710086-009

Kempsey

A smooth, arced arm holds the small, curved bar that supports an elegant fabric shade.

P710045-009 Brushed Nickel
P710045-020 Antique Bronze
Adjustable arm.
On/off rotary switch on backplate.
12″ dia., 19-3/4″ ht.,
Extends 23-5/8″.
One medium base lamp,
75w max.



P710045-020



P710045-009

Litchfield

An adjustable arm and backplate in a crisp, clean finish hold an hourglass-inspired shade.

P710044-015 Polished Chrome
Adjustable arm.
5″ W., 13″ ht. Extends 14-1/2″.
One medium base lamp,
60w max.



P710044-015
shown above and right with adjustable arm





P5948-20



P5948-31

Jack

A dramatic geometric frame encloses a rectangular etched glass shade.

P5948-20 Antique Bronze
P5948-31 Black
Indoor/Outdoor.
6" W., 13-5/8" ht.
Extends 6-1/4". H/CTR 5-1/4".
One medium base lamp,
100w max.



P300222-009



P300222-031

Tobin

Tubular arms form a gentle curve showcasing an etched glass shade.

P300222-009 Brushed Nickel
P300222-031 Black
5" W., 15-1/2" ht.
Extends 5-7/8". H/CTR 11".
One medium base lamp,
100w max.



P6603-20

Peek-a-Boo

Etched glass shade peeks through an arched frame for a clean, contemporary look.

P6603-20 Antique Bronze
Indoor/Outdoor.
5-1/2" W., 17-1/8" ht.
Extends 3-1/4". H/CTR 10-3/4".
One medium base T10 lamp,
60w max.

ADA

Hinton

Versatile wall bracket with square backplate, swing arm and metal or glass shade.

P710084-009 Brushed Nickel
P710084-031 Black
P710084-104 Polished Nickel
P710084-163 Vintage Brass
Adjustable arm.
On/off rotary switch on backplate.
8" W., 9-5/8" ht.
Extends 12". H/CTR 3-1/4".
One medium base lamp,
60w max.

P710085-009 Brushed Nickel
P710085-031 Black
P710085-104 Polished Nickel
P710085-163 Vintage Brass
Adjustable arm.
On/off rotary switch on backplate.
8-1/4" W., 9-5/8" ht.
Extends 12-1/8". H/CTR 3-1/4".
One medium base lamp,
60w max.



P710084-009



P710084-031



P710084-104



P710084-163



P710085-009



P710085-031



P710085-104



P710085-163

Hinton

Versatile wall bracket with round backplate, adjustable arm and metal or glass shade.

P710094-009 Brushed Nickel
P710094-031 Black
P710094-104 Polished Nickel
P710094-163 Vintage Brass
Adjustable arm.
On/off rotary switch on shade.
8" W., 14-3/8" ht.
Extends 18-1/4". H/CTR 11-1/4".
One medium base lamp,
60w max.

P710095-009 Brushed Nickel
P710095-031 Black
P710095-104 Polished Nickel
P710095-163 Vintage Brass
Adjustable arm.
On/off rotary switch on shade.
8-1/4" W., 14-3/8" ht.
Extends 18-3/8". H/CTR 11-1/4".
One medium base lamp,
60w max.


P710094-009


P710094-031


P710094-104


P710094-163


P710095-009


P710095-031


P710095-104


P710095-163

Torino

Elegantly formed metal frames are completed by rich finishes and bell-shaped glass.

P2881-09 Brushed Nickel
P2881-77 Forged Bronze
7" W., 8-1/4" ht.
Extends 9-1/8".
One medium base lamp,
100w max.


P2881-09


P2881-77

P7181-09 Brushed Nickel
P7181-77 Forged Bronze
9-1/2" W., 6-3/4" ht.
Extends 4-3/4". H/CTR 2-7/8".
One medium base lamp,
100w max.


P7181-09


P7181-77

Etched Glass

Etched bell shape glass is trimmed with a simple narrow metal band.

P7185-20 Antique Bronze
9-1/2" W., 6-3/4" ht.
Extends 4-3/4". H/CTR 2-7/8".
One medium base lamp,
100w max.


P7185-20

Opal Glass

A flared cone-shaped half bowl in etched glass is ornamented with classic knob detailing.

P7153-09W Brushed Nickel
P7153-20W Antique Bronze
15 3/8" W., 7" ht.
Extends 7 1/2". H/CTR 2-1/2".
One medium base lamp,
60w max.


P7153-09W


P7153-20W

Eclipse

Lunar-eclipse inspired half-circle metal frame is accented by satin white glass.

P7170-09 Brushed Nickel
P7175-20 Antique Bronze
15-1/4" W., 7-1/2" ht.
Extends 4". H/CTR 3".
One medium base lamp,
100w max.


P7170-09


P7175-20

ADA

Linen Glass

Squared-off, architectural form is complemented by etched linen glass.

P710072-009 Brushed Nickel
P710072-031 Black
6″ W., 12″ ht.,
Extends 4″.
One medium base lamp,
75w max.

ADA



P710072-009



P710072-031


Tri-Band Louver

Graduated metal tiers add style and illumination from the top, bottom and between louvers.

P7103-30 White
P7103-31 Black
14″ W., 7″ ht. Extends 7″.
H/CTR 2-1/4″.
One medium base lamp,
100w max.



P7103-30



P7103-31

White Glass

Lovely curves and crisp, white glass ensure a seamless blend for any décor.

P7112-30 White
11-1/2″ W., 5″ ht.
Extends 5-3/4″. H/CTR 2-3/8″.
One medium base lamp,
100w max.

P3813-30 White
Rotary switch on socket.
4-3/4″ W., 7-1/2″ ht. Extends 4″.
One medium base lamp,
100w max.

All fixtures:

ADA



P7112-30



P3813-30

Stone Glass Sconce LED

Organically inspired, handmade artisan stone glass is gently clasped by metal arms.

P710080-009-30 Brushed Nickel
P710080-031-30 Black
8" W., 8-1/2" ht., wire 6".
Extends 3-1/4". H/CTR 4".
9.5w Integrated LED, 3000K,
90CRI, 433 delivered lumens.

JA8 ADA



P710080-009-30



P710080-031-30

Alabaster Stone Glass Sconce LED

Handcrafted organic alabaster glass share shade illuminates with a soft, muted glow.

P710081-009-30 Brushed Nickel
P710081-031-30 Black
8" W., 8-1/2" ht., wire 6".
Extends 3-1/4". H/CTR 4".
9.5w Integrated LED, 3000K,
90CRI, 387 delivered lumens.

JA8 ADA



P710081-009-30



P710081-031-30

Frame LED

Modern architectural styling frames an integrated LED source and circular etched opal glass.

P2781-0930K9 Brushed Nickel
4-3/4" W., 12" ht.
Extends 3-1/2". H/CTR 2-3/8".
15w integrated LED, 3000K,
90 CRI, 577 delivered lumens.

ADA



P2781-0930K9

Shaded Sconce LED

Round or square geometric styling is topped with a fabric half-shade.

P710054-009-30 Brushed Nickel
P710054-031-30 Black
P710054-109-30 Brushed Bronze
14" W., 21-1/4" ht., wire 6".
Extends 3-7/8". H/CTR 3-1/4".
One 9w LED module, 3000K,
90CRI, 624 lumens.

P710058-009-30 Brushed Nickel
P710058-031-30 Black
P710058-109-30 Brushed Bronze
14" W., 21-1/4" ht., wire 6".
Extends 3-7/8". H/CTR 3-1/4".
One 9w LED module, 3000K,
90CRI, 624 lumens.

JA8 ADA



P710054-009-30



P710058-009-30



P710054-031-30



P710058-031-30



P710054-109-30



P710058-109-30

Blanco LED

An elegantly modern effect is achieved with a design that minimizes all visible hardware.

P710047-009-30 Brushed Nickel
P710047-012-30 Satin Brass
P710047-031-30 Matte Black
P710047-150-30 Faux White Marble
4-3/4" W., 11-3/4" ht., wire 6".
Extends 3-5/8". H/CTR 8-3/8".
16w Integrated LED, 3000K,
90CRI, 823 delivered lumens.

JA8 ADA


P710047-009-30


P710047-012-30


P710047-031-30


P710047-150-30

Parallel LED

A tubular opal glass diffuser is paired with a simple, modern metal backplate.

P710050-009-30 Brushed Nickel
P710050-012-30 Satin Brass
P710050-015-30 Polished Chrome
P710050-129-30 Architectural Bronze
4-3/4" W., 11" ht., wire 6".
Extends 2-3/4". H/CTR 7-1/2".
16w integrated LED, 3000K,
90CRI, 930 delivered lumens.

JA8 ADA


P710050-009-30


P710050-012-30


P710050-015-30


P710050-129-30

Beam LED

A clean, contemporary metal backplate holds a square tubular opal glass diffuser.

P710049-009-30 Brushed Nickel
P710049-015-30 Polished Chrome
P710049-129-30 Architectural Bronze
4-3/4" W., 10-1/2" ht., wire 6".
Extends 3-1/4". H/CTR 8-3/8".
16w integrated LED, 3000K,
90CRI, 1000 delivered lumens.

JA8 ADA


P710049-009-30


P710049-015-30


P710049-129-30



P2834-0930K9



P2834-12930K9

Truss LED

A unique mesh accent holds an etched glass cylinder against a simple square backplate.

P2834-0930K9 Brushed Nickel
P2834-12930K9 Architectural Bronze
4-3/4" W., 13" ht.
Extends 3-7/8". H/CTR 2-3/8".
20w integrataed LED, 3000K,
90 CRI, 665 delivered lumens.

ADA



P710036-009-30



P710036-129-30

Apogee LED

Tiered metal banded trim holds a half-circle etched glass shade.

P710036-009-30 Brushed Nickel
P710036-129-30 Architectural Bronze
15" W., 7-1/2" ht., Extends 3-11/16"
20w integrated LED, 3000K,
90CRI, 940 delivered lumens,
120-277V, 0-10V dimming.

JA8 ADA



P710090-031-30



P710090-009-30

Eclipse LED

Lunar-eclipse inspired half-circle metal frame accented by satin white glass.

P710090-009-30 Brushed Nickel
P710090-031-30 Black
15-1/2" W., 7-1/2" ht., wire 6".
Extends 4". H/CTR 3".
One 17w LED module, 3000K,
90CRI, 1276 source lumens.

JA8 ADA



P710071-030-30



P710071-159-30

Inspire LED

Gently curving form is accented with a fabric shade.

P710071-030-30 Summer Linen
P710071-159-30 Off White Linen
6-1/4" W., 9" ht.,
Extends 3-1/8".
One 9w LED module, 3000K,
90CRI, 624 source lumens.

JA8 ADA

Sconces LED

Sconces styles to suit any décor offer LED lamping for beauty plus energy efficiency.

P7083-0930K9 Brushed Nickel
White Acrylic
8-7/8" W., 10-5/8" ht.
Extends 4". H/CTR 5-3/8".
One 17w LED module, 3000K,
90 CRI, 1211 source lumens.

P7085-0930K9 Brushed Nickel
White Acrylic
9-1/2" W., 10-5/8" ht.
Extends 3-3/4". H/CTR 10-3/8".
One 17w LED module, 3000K,
90 CRI, 1211 source lumens.

P7088-0930K9 Brushed Nickel
White Acrylic
8" W., 10-5/8" ht.
Extends 3-7/8". H/CTR 5-3/8".
One 17w LED module, 3000K,
90 CRI, 1211 source lumens.

P7092-0930K9 Brushed Nickel
Etched Opal Enclosed
One-piece Glass
8" W., 10-3/4" ht.
Extends 4". H/CTR 5-1/2".
One 17w LED module, 3000K,
90 CRI, 1211 source lumens.

P7093-3030K9 Brushed Nickel
Satin Opal Glass
11-3/8" W., 11-1/8" ht.
Extends 3-3/8". H/CTR 5-5/8".
One 17w LED module, 3000K,
90 CRI, 1211 source lumens.

P7105-0930K9 Brushed Nickel
Ribbed Glass
12-7/8" W., 10" ht.
Extends 3-1/2". H/CTR 6-3/8".
One 17w LED module, 3000K,
90 CRI, 1211 source lumens.

All fixtures:





P7092-0930K9



P7083-0930K9



P7085-0930K9



P7088-0930K9



P7093-3030K9
Shown with Brushed Nickel finial



P7093-3030K9
Shown with Bronze finial



P7105-0930K9

Sconces LED

Sconces styles to suit any décor offer LED lamping for beauty plus energy efficiency.

P710010-009-30 BRUSHED NICKEL
P710010-129-30 ARCHITECTURAL BRONZE
6-3/4" W., 12" ht. Extends 4". H/CTR 6".
One 9w LED module, 3000K
90CRI, 624 source lumens.



P710010-009-30



P710010-129-30

Anson LED

Strong geometric styling surrounds a polycarbonate diffuser.

P560001-129-30 Architectural Bronze
Indoor/Outdoor
10" W., 3" ht.
One 17w LED module, 3000K,
90 CRI, 1211 source lumens.



P560001-129-30

Etched Glass Sconce LED

An elongated cup-shaped etched glass shade is held in place by a beautiful metal frame.

P710079-009-30 Brushed Nickel
P710079-031-30 Black
6" wd., 11" ht., wire 6".
Extends 4". H/CTR 3-1/2".
One 9w LED module, 3000K,
90CRI, 624 source lumens.




P710079-009-30



P710079-031-30


Featuring Durrell



Bath

All-Purpose Illumination

Scan and see more at
progresslighting.com

Bowman
P300255-031





Dan McGinty
Product Designer

Easy, Breezy, Coastal

with David

Bring your home right to the ocean side with beach-inspired accents, organic furnishings and an overall relaxed feel. Designers often create a relaxed and open environment with soft throw blankets, pillows, cozy rugs and cushioned furniture to complete the Coastal look. Focus on an all-white color palette for your coastal inspired home, while incorporating in soft beachy hues to complement the look.

When it comes to selecting materials for flooring, décor and furniture, seek out dark or weathered wood pieces to emulate a seaside environment nestled nicely by the shore.

Shop this style at
progresslighting.com/coastal



Ponder LED

FINISHES

- Antique Bronze - 020
- Graphite - 143

P300091-020-30

Ponder vanity fixtures with prismatic glass shades offer a sleek, industrial-inspired appearance. Etched prismatic glass is framed within a die cast bezel to enhance visual interest in Urban Industrial or Farmhouse-style interiors.



TWO-LIGHT BATH
P300091-020-30 Antique Bronze
P300091-143-30 Graphite
16-1/8 W., 4-5/8" ht.
Extends 3-5/8". H/CTR 2-3/8".
Two 9w LED modules, 3000K,
90CRI, 670 source lumens per module.


P300091-020-30


P300091-143-30

THREE-LIGHT BATH
P300092-020-30 Antique Bronze
P300092-143-30 Graphite
25-3/8" W., 4-5/8" ht.
Extends 3-5/8". H/CTR 2-3/8".
Three 9w LED modules, 3000K,
90CRI, 670 source lumens per module.


P300092-020-30

All fixtures:




P300092-143-30

Capelli LED

FINISH
Polished Chrome - 015

P350054-015-30

Inspired by the beauty of frozen ice forms, Capelli LED sconces feature intriguing glass layers resulting in a sophisticated form. The integrated LED technology runs across the length of the fixture, allowing the illumination to showcase the unique effects of the handmade work of art. The backplate and knob details are finished in Chrome.





P300054-015-30
mounted vertical



P300054-015-30



P710062-015-30



P300055-015-30

24" LINEAR LED BATH
P300054-015-30 Polished Chrome
24" W., 4-3/4" ht.
Extends 3-3/4". H/CTR 2-3/8".
36w integrated LED, 3000K,
90CRI, 2600 delivered lumens.

33" LINEAR LED BATH
P300055-015-30 Polished Chrome
33" W., 4-3/4" ht.
Extends 3-3/4". H/CTR 2-3/8".
53w integrated LED, 3000K,
90CRI, 3850 delivered lumens.

12" LED WALL SCONCE
P710062-015-30 Polished Chrome
4-3/4" W., 12" ht.
Extends 3-3/4". H/CTR 2-3/8".
16w integrated LED, 3000K,
90CRI, 1125 delivered lumens.

All fixtures can be installed horizontally or vertically.

All fixtures:

JA8 ADA


Miter LED

FINISH

Brushed Nickel - 009

P300152-009-30

The Miter LED wall sconce highlights a beautiful layered effect to enhance a variety of interior areas. Each clear beveled glass panel is hand cut and positioned together, creating visual interest that extend to the corners. To complete the form, a backplate and linear accents frame the glass in a Brushed Nickel finish. An integrated LED source provides a variety of energy and cost savings benefits.



24" LINEAR LED BATH
P300152-009-30 Brushed Nickel
24" W., 5" ht.
Extends 3-7/8". H/CTR 2-1/2".
36w integrated LED, 3000K,
90CRI, 1975 delivered lumens.

34" LINEAR LED BATH
P300153-009-30 Brushed Nickel
34-1/8" W., 5" ht.
Extends 3-7/8". H/CTR 2-1/2".
53w integrated LED, 3000K,
90CRI, 2825 delivered lumens.

12" LED WALL BRACKET
P710061-009-30 Brushed Nickel
5" W., 12-1/4" ht.
Extends 3-7/8". H/CTR 6-1/8".
16w integrated LED, 3000K,
90CRI, 825 delivered lumens.

All fixtures can be installed horizontally or vertically.

All fixtures:

JA8 ADA



P710061-009-30



P300152-009-30



P300153-009-30



P300152-009-30
mounted vertical

Concourse LED

FINISH
Brushed Nickel - 009

ALSO IN
Pendants

P300093-009-30

Architectural details and a full size canopy are key elements in Concourse LED vanity fixtures. A dual tone reflector frames the canopy to provide a mirror like effect. Etched opal glass is paired with Brushed Nickel and polished stainless accents in this versatile cylindrical fixture.

Etched Opal Glass

Full-Size Canopy



Architectural Details



P300093-009-30
mounted vertical



P300093-009-30



P300094-009-30

24" LINEAR LED BATH
P300093-009-30 Brushed Nickel
24" W., 4-3/4" ht.
Extends 3-1/2". H/CTR 2-3/8".
One 37w LED module, 3000K, 90CRI, 2191 delivered lumens.

36" LINEAR LED BATH
P300094-009-30 Brushed Nickel
36" W., 4-3/4" ht.
Extends 3-1/2". H/CTR 2-3/8".
One 53w LED module, 3000K, 90CRI, 2969 delivered lumens.

All fixtures can be installed horizontally or vertically.

All fixtures:

JA8 ADA

Colonnade LED


FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015

P300187-009-30

Tubular etched glass shades pop against geometric backplate to create Colonnade, an LED bath collection. Available in one, two, three and four-light options. Modern style and continuous illumination are ideal for a variety of bath settings – including Mid-Century and Luxe.

Tubular Etched Glass



ONE-LIGHT LED BATH
P300185-009-30 Brushed Nickel
4-3/4" W., 7-1/2" ht.
Extends 3-7/8". H/CTR 3-7/8".
9.5w integrated LED, 3000K,
90CRI, 500 delivered lumens.

TWO-LIGHT LED BATH
P300186-009-30 Brushed Nickel
13-1/4" W., 7-1/2" ht.
Extends 3-7/8". H/CTR 3-7/8".
19w integrated LED, 3000K,
90CRI, 1000 delivered lumens.

THREE-LIGHT LED BATH
P300187-009-30 Brushed Nickel
22" W., 7-1/2" ht.
Extends 3-7/8". H/CTR 3-7/8".
28.5w integrated LED, 3000K,
90CRI, 1500 delivered lumens.

FOUR-LIGHT LED BATH
P300188-009-30 Brushed Nickel
31-3/8" W., 7-1/2" ht.
Extends 3-7/8". H/CTR 3-7/8".
38w integrated LED, 3000K,
90CRI, 2000 delivered lumens.

All fixtures:

JA8 ADA




P300185-009-30



P300188-009-30



P300186-009-30



P300187-009-30


Colonnade
LED



P300185-015-30



P300186-015-30



P300187-015-30



P300188-015-30

ONE-LIGHT LED BATH
P300185-015-30 Polished Chrome
4-3/4" W., 7-1/2" ht.
Extends 3-7/8". H/CTR 3-7/8".
9.5w integrated LED, 3000K,
90CRI, 500 delivered lumens.

TWO-LIGHT LED BATH
P300186-015-30 Polished Chrome
13-1/4" W., 7-1/2" ht.
Extends 3-7/8". H/CTR 3-7/8".
19w integrated LED, 3000K,
90CRI, 1000 delivered lumens.

THREE-LIGHT LED BATH
P300187-015-30 Polished Chrome
22" W., 7-1/2" ht.
Extends 3-7/8". H/CTR 3-7/8".
28.5w integrated LED, 3000K,
90CRI, 1500 delivered lumens.

FOUR-LIGHT LED BATH
P300188-015-30 Polished Chrome
31-3/8" W., 7-1/2" ht.
Extends 3-7/8". H/CTR 3-7/8".
38w integrated LED, 3000K,
90CRI, 2000 delivered lumens.

All fixtures:

JA8 ADA


Beam LED

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Architectural Bronze - 129

P300182-129-30

Beam LED vanity and sconces feature a squared, tubular opal glass diffuser paired with a simple, modern metal canopy. An integrated LED source provides a variety of energy and cost savings benefits. Suitable for residential and commercial applications.



22" LINEAR LED BATH
P300182-129-30 Architectural Bronze
Installs horizontal or vertical.
22-1/4" W., 4-3/4" ht.
Extends 3". H/CTR 2-3/8".
36w integrated LED, 3000K,
90CRI, 2200 delivered lumens.

LED WALL BRACKET
P710049-129-30 Architectural Bronze
4-3/4" W., 10-1/2" ht.
Extends 3-1/4". H/CTR 8-3/8".
16w integrated LED, 3000K,
90CRI, 1000 delivered lumens.

All fixtures:

JA8 ADA



P300182-129-30



P710049-129-30



P300182-129-30
mounted vertical



P300182-009-30
mounted vertical



P300182-009-30



P710049-009-30



P300182-015-30
mounted vertical



P300182-015-30



P710049-015-30

22" LINEAR LED BATH
P300182-009-30 Brushed Nickel
P300182-015-30 Polished Chrome
Installs horizontal or vertical.
22-1/4" W., 4-3/4" ht.
Extends 3". H/CTR 2-3/8".
36w integrated LED, 3000K,
90CRI, 2200 delivered lumens.

LED WALL BRACKET
P710049-009-30 Brushed Nickel
P710049-015-30 Polished Chrome
4-3/4" W., 10-1/2" ht.
Extends 3-1/4". H/CTR 8-3/8".
16w integrated LED, 3000K,
90CRI, 1000 delivered lumens.

All fixtures:

JA8 ADA

Planck LED

FINISH
Brushed Nickel - 009

ALSO IN
Pendants

P710052-009-30

Planck LED wall fixtures use indirect illumination to provide a dramatic architectural feature to any space. A brushed metal beam sports a sleek chrome accent to add visual interest to the minimalist form. Suitable for residential or commercial applications.



LED WALL SCONCE
P710051-009-30 Brushed Nickel
4-3/4" W., 16" ht.
Extends 3". H/CTR 12-5/8".
16w integrated LED, 3000K,
90CRI, 600 delivered lumens.

24" LINEAR LED SCONCE
P710052-009-30 Brushed Nickel
Installs horizontal or vertical.
24" W., 4-3/4" ht.
Extends 3". H/CTR 2-3/8".
32w integrated LED, 3000K,
90CRI, 1100 delivered lumens.

All fixtures:

JA8 ADA


P710052-009-30


P710051-009-30


P710052-009-30
mounted vertical


Featuring Planck

Frame LED

FINISH
Brushed Nickel - 09

P2781-0930K9

Modern architectural styling frames an integrated LED source and circular etched opal glass. Frame bath fixtures provide beautiful and even illumination, as well as energy saving benefits.

Etched Opal Glass



Integrated LED

Architectural Frame

12" LINEAR VANITY
P2781-0930K9 Brushed Nickel
12" W., 4-3/4" ht.,
Extends 3-1/2". H/CTR 2-3/8".
15w integrated LED, 3000K,
90 CRI, 738 delivered lumens.

24" LINEAR VANITY
P2782-0930K9 Brushed Nickel
24" W., 4-3/4" ht.,
Extends 3-1/2". H/CTR 2-3/8".
35w integrated LED, 3000K,
90 CRI, 1659 delivered lumens.

All fixtures can be installed horizontally or vertically.



P2782-0930K9



P2781-0930K9



P2781-0930K9
mounted vertical


Truss LED

FINISHES

- Brushed Nickel - 09
- Architectural Bronze - 129

P2834-0930K9

Circular etched opal glass contains an integrated LED source to provide a variety of energy and cost savings benefits for the homeowner. Modern style and even illumination are ideal for a variety of bath settings.





P2839-0930K9



P2834-0930K9



P2839-12930K9
mounted vertical



P2839-12930K9



P2834-12930K9

13" LINEAR VANITY
P2834-0930K9 Brushed Nickel
P2834-12930K9 Architectural Bronze
13" W., 4-3/4" ht.
Extends 3-7/8". H/CTR 2-3/8".
32w integrated LED, 3000K,
90 CRI, 737 delivered lumens.

22" LINEAR VANITY
P2839-0930K9 Brushed Nickel
P2839-12930K9 Architectural Bronze
22-1/2" W., 4-3/4" ht.
Extends 3-7/8". H/CTR 2-3/8".
37w integrated LED, 3000K,
90 CRI, 1222 delivered lumens.

All fixtures can be installed horizontally or vertically.


Parallel LED

FINISHES

- Brushed Nickel - 009
- Satin Brass - 012
- Polished Chrome - 015
- Architectural Bronze - 129

P300183-009-30

The sophisticated, modern style of the Parallel Collection features crisp, tubular, opal glass diffusers, each paired with a simple modern metal backplate for an understated, elegant design.



22" LINEAR LED BATH
P300183-009-30 Brushed Nickel
Installs horizontal or vertical.
22-3/8" W., 4-3/4"ht.
Extends 2-3/4". H/CTR 2-3/8".
36w integrated LED, 3000K,
90CRI, 2166 delivered lumens.

32" LINEAR LED BATH
P300184-009-30 Brushed Nickel
Installs horizontal or vertical.
32" W., 4-3/4" ht.
Extends 2-3/4". H/CTR 2-3/8".
53w integrated LED, 3000K,
90CRI, 2872 delivered lumens.

LED WALL BRACKET
P710050-009-30 Brushed Nickel
4-3/4" W., 11" ht.
Extends 2-3/4". H/CTR 7-1/2".
16w integrated LED, 3000K,
90CRI, 930 delivered lumens.



P710050-009-30



P300183-009-30



P300184-009-30



P300183-009-30
mounted vertical

All fixtures:

JA8 ADA



P300183-012-30



P300184-012-30



P710050-012-30



P300183-015-30



P300184-015-30



P710050-015-30



P300183-129-30
mounted vertical



P300183-129-30



P710050-129-30



P300184-129-30

22″ LINEAR LED BATH
P300183-012-30 Satin Brass
P300183-015-30 Polished Chrome
P300183-129-30 Architectural Bronze
Installs horizontal or vertical.
22-3/8″ W., 4-3/4″ht.
Extends 2-3/4″. H/CTR 2-3/8″.
36w integrated LED, 3000K,
90CRI, 2166 delivered lumens.

32″ LINEAR LED BATH
P300184-012-30 Satin Brass
P300184-015-30 Polished Chrome
P300184-129-30 Architectural Bronze
Installs horizontal or vertical.
32″ W., 4-3/4″ ht.
Extends 2-3/4″. H/CTR 2-3/8″.
53w integrated LED, 3000K,
90CRI, 2872 delivered lumens.

LED WALL BRACKET
P710050-012-30 Satin Brass
P710050-015-30 Polished Chrome
P710050-129-30 Architectural Bronze
4-3/4″ W., 11″ ht.
Extends 2-3/4″. H/CTR 7-1/2″.
16w integrated LED, 3000K,
90CRI, 930 delivered lumens.

All fixtures:

JA8 ADA

Blanco LED

FINISHES

- Brushed Nickel - 009
- Satin Brass - 012
- Matte Black - 031
- Faux White Marble - 150

ALSO IN

Sconces

P300150-150-30

The Blanco Collection highlights classic forms with crisp, contemporary updates. Offered in a variety of metal finishes, each fixture features a thin, horizontal cylinder shade for a clean, linear design. Blanco LED is ideal for modern and transitional settings.



22" LINEAR LED BATH
P300150-150-30 Faux White Marble
Installs horizontal or vertical.
22-1/4" W., 4-3/4" ht.
Extends 3-5/8". H/CTR 2-3/8".
36w integrated LED, 3000K,
90CRI, 1942 delivered lumens.

32" LINEAR LED BATH
P300151-150-30 Faux White Marble
Installs horizontal or vertical.
32-3/8" W., 4-3/4" ht.
Extends 3-3/4". H/CTR 2-3/8".
53w integrated LED, 3000K,
90CRI, 2768 delivered lumens.

LED WALL BRACKET
P710047-150-30 Faux White Marble
4-3/4" W., 11-3/4" ht.
Extends 3-5/8". H/CTR 8-3/8".
16w integrated LED, 3000K,
90CRI, 823 delivered lumens.



P710047-150-30

P300150-150-30

P300151-150-30

P300150-150-30
mounted vertical

All fixtures:

JA8 ADA



P300150-009-30



P300151-009-30



P710047-009-30



P300150-031-30



P300151-031-30



P710047-031-30



P300150-012-30
mounted vertical



P300150-012-30



P710047-012-30



P300151-012-30

22" LED LINEAR BATH
P300150-009-30 Brushed Nickel
P300150-012-30 Satin Brass
P300150-031-30 Matte Black
Installs horizontal or vertical.
22-1/4" W., 4-3/4" ht.
Extends 3-5/8". H/CTR 2-3/8".
36w integrated LED, 3000K,
90CRI, 1942 delivered lumens.

32" LED LINEAR BATH
P300151-009-30 Brushed Nickel
P300151-012-30 Satin Brass
P300151-031-30 Matte Black
Installs horizontal or vertical.
32-3/8" W., 4-3/4" ht.
Extends 3-5/8". H/CTR 2-3/8".
53w integrated LED, 3000K,
90CRI, 2768 delivered lumens.

LED WALL BRACKET
P710047-009-30 Brushed Nickel
P710047-012-30 Satin Brass
P710047-031-30 Matte Black
4-3/4" W., 11-3/4" ht.
Extends 3-5/8". H/CTR 8-3/8".
16w integrated LED, 3000K,
90CRI, 823 delivered lumens.

All fixtures:

JA8 ADA

Ace LED

FINISHES

- Polished Chrome - 15
- Antique Bronze - 20

P2143-1530K9

A simple yet elegant series of modern LED wall fixtures. Geometric frosted glass shades provide evenly diffused illumination for vanity applications.

Simple and Elegant

Evenly Diffused



Geometric Frosted Shades

ONE-LIGHT BATH
P2142-1530K9 Polished Chrome
7" W., 4-3/4" ht.
Extends 4". H/CTR 2-3/4".
One 9w LED module, 3000K,
90CRI, 623 source lumens per module.



P2142-1530K9

TWO-LIGHT BATH
P2143-1530K9 Polished Chrome
15-1/2" W., 4-3/4" ht.
Extends 4". H/CTR 2-3/8".
Two 9w LED modules, 3000K,
90CRI, 623 source lumens per module.



P2143-1530K9

THREE-LIGHT BATH
P2144-1530K9 Polished Chrome
24" W., 4-3/4" ht. Extends 4".
H/CTR 2-3/8".
Three 9w LED modules, 3000K,
90CRI, 623 source lumens per module.



P2144-1530K9

FOUR-LIGHT BATH
P2145-1530K9 Polished Chrome
32-1/2" W., 4-3/4" ht. Extends 4".
Four 9w LED modules, 3000K,
90CRI, 623 source lumens per module.



P2145-1530K9

All fixtures:

ADA

Ace LED



P2143-2030K9



P2142-2030K9



P2144-2030K9



P2145-2030K9

ONE-LIGHT BATH
P2142-2030K9 Antique Bronze
7" W., 4-3/4" ht.
Extends 4". H/CTR 2-3/4".
One 9w LED module, 3000K,
90CRI, 623 source lumens per module.

TWO-LIGHT BATH
P2143-2030K9 Antique Bronze
15-1/2" W., 4-3/4" ht.
Extends 4". H/CTR 2-3/8".
Two 9w LED modules, 3000K,
90CRI, 623 source lumens per module.

THREE-LIGHT BATH
P2144-2030K9 Antique Bronze
24" W., 4-3/4" ht. Extends 4".
H/CTR 2-3/8".
Three 9w LED modules, 3000K,
90CRI, 623 source lumens per module.

FOUR-LIGHT BATH
P2145-2030K9 Antique Bronze
32-1/2" W., 4-3/4" ht. Extends 4".
Four 9w LED modules, 3000K,
90CRI, 623 source lumens per module.


All fixtures:

Phase 1.1 LED

FINISH
Brushed Nickel - 009

P300223-009-30

Featuring a cylindrical acrylic diffuser and a simple rectangular backplate, Phase 1.1 offers a variety of lengths to accommodate residential, light commercial and multi-family applications. An integrated LED source provides uniform illumination, as well as energy and cost savings benefits.



24" LINEAR LED BATH
P300223-009-30 Brushed Nickel
24" W., 4-3/4" ht.
Extends 4". H/CTR 2-3/8".
22w integrated LED, 3000K,
90CRI, 1675 delivered lumens.



P300223-009-30

36" LINEAR LED BATH
P300224-009-30 Brushed Nickel
36" W., 4-3/4" ht.
Extends 4". H/CTR 2-3/8".
33w integrated LED, 3000K,
90CRI, 2600 delivered lumens.



P300224-009-30



P300223-009-30
mounted vertical

48" LINEAR LED BATH
P300225-009-30 Brushed Nickel
48" W., 4-3/4" ht.
Extends 4". H/CTR 2-3/8".
42w integrated LED, 3000K,
90CRI, 3500 delivered lumens.



P300225-009-30

All fixtures can be installed horizontally or vertically.

All fixtures:

JA8 ADA

Phase 1.2 LED

FINISH
Brushed Nickel - 009

P300205-009-30
shown with decorative geometric diffuser

A classic form with contemporary updates, this elongated acrylic shade comes with decorative accents. Both a faux stone option and white geometric decorative diffuser are included to further customize the fixture. An integrated LED source provides uniform illumination, as well as energy and cost savings benefits.





P300223-009-30
mounted vertical



P300205-009-30
shown with faux stone diffuser



P300206-009-30
shown with decorative geometric diffuser



P300207-009-30
shown with faux stone diffuser

24" LINEAR LED BATH
P300205-009-30 Brushed Nickel
24" W., 4-3/4" ht.
Extends 4-1/2". H/CTR 2-3/8".
22w integrated LED, 3000K,
90CRI, 1575 delivered lumens.

36" LINEAR LED BATH
P300206-009-30 Brushed Nickel
36" W., 4-3/4" ht.
Extends 4-1/2". H/CTR 2-3/8".
33w integrated LED, 3000K,
90CRI, 2475 delivered lumens.

48" LINEAR LED BATH
P300207-009-30 Brushed Nickel
48" W., 4-3/4" ht.
Extends 4-1/2". H/CTR 2-3/8".
42w integrated LED, 3000K,
90CRI, 3400 delivered lumens.

All fixtures can be installed horizontally or vertically.

All fixtures:



Detail of faux stone accent



Detail of geometric accent

Phase 2.1 LED

FINISH

Brushed Nickel - 009

P300208-009-30

Phase 2.1 features an acrylic lens that provides even illumination. This specially designed linear fixture delivers ambient light to surfaces free of shadows. Phase 2.1 is a perfect addition to modern applications. An integrated LED source provides energy and cost savings benefits.



24" LINEAR LED BATH
P300208-009-30 Brushed Nickel
24" W., 4-3/4" ht.
Extends 3-1/2". H/CTR 2-3/8".
23w integrated LED, 3000K,
90CRI, 1600 delivered lumens.

36" LINEAR LED BATH
P300209-009-30 Brushed Nickel
36" W., 4-3/4" ht.
Extends 3-1/2". H/CTR 2-3/8".
34w integrated LED, 3000K,
90CRI, 2450 delivered lumens.

48" LINEAR LED BATH
P300210-009-30 Brushed Nickel
48" W., 4-3/4" ht.
Extends 3-1/2". H/CTR 2-3/8".
44w integrated LED, 3000K,
90CRI, 3300 delivered lumens.

All fixtures can be installed horizontally or vertically.

All fixtures:



P300208-009-30



P300209-009-30



P300210-009-30



P300208-009-30
mounted vertical

Phase 2.2 LED

FINISH
Brushed Nickel - 009

P300211-009-30

Phase 2.2 features an acrylic shade framed by architectural accents in Brushed Nickel complete the design to deliver ambient light to surfaces free of shadows. Ideal for residential, commercial and multi-family applications. An integrated LED source provides energy and cost savings benefits.

Architectural Accents

Cost Savings Benefits



Residential and Commercial



P300211-009-30
mounted vertical



P300211-009-30



P300212-009-30



P300213-009-30

24" LINEAR LED BATH
P300211-009-30 Brushed Nickel
24" W., 4-3/4" ht.
Extends 4". H/CTR 2-3/8".
23w integrated LED, 3000K,
90CRI, 1550 delivered lumens.

36" LINEAR LED BATH
P300212-009-30 Brushed Nickel
36" W., 4-3/4" ht.
Extends 4". H/CTR 2-3/8".
34w integrated LED, 3000K,
90CRI, 2400 delivered lumens.

48" LINEAR LED BATH
P300213-009-30 Brushed Nickel
48" W., 4-3/4" ht.
Extends 4". H/CTR 2-3/8".
44w integrated LED, 3000K,
90CRI, 3250 delivered lumens.

All fixtures can be installed horizontally or vertically.

All fixtures:

JA8 ADA

Arch LED

FINISH

Brushed Nickel - 009

P300291-009-30

Discover an innovative series of wall sconces with the Arch LED Collection. Classy, etched glass shades are aligned in a linear fashion, each with a diffuser at its bottom constructed from glass. The sleek, modern look will make your home a perfect environment for a relaxing staycation.

Etched Shades

Modern Look



Bottom Diffuser

TWO LIGHT LED BATH
P300290-009-30 Brushed Nickel
13-1/4" W., 5" ht., wire 6".
Extends 3-7/16". H/CTR 2-1/2".
Two 10w integrated LED, 3000K,
90CRI, 1057 delivered lumens.

THREE LIGHT LED BATH
P300291-009-30 Brushed Nickel
20-1/2" W., 5" ht., wire 6".
Extends 3-7/16". H/CTR 2-1/2".
Three 10w integrated LED, 3000K,
90CRI, 1508 delivered lumens.

FOUR LIGHT LED BATH
P300292-009-30 Brushed Nickel
27-3/4" W., 5" ht., wire 6".
Extends 3-7/16". H/CTR 2-1/2".
Four 10w integrated LED, 3000K,
90CRI, 1988 delivered lumens.

All fixtures:

JA8 ADA



P300291-009-30



P300290-009-30



P300292-009-30

Cloud LED

The Cloud LED Collection features crisp opal white shades. Each shade is shaped into a linear tube design with a seamless aesthetic. The shades are offered in two different sizes to offer you versatility when it comes to fulfilling your design vision.

P300239-060-CS

P300239-060-CS

FINISH

○ Opal White - 060

LED LINEAR CLOUD
P300239-060-CS Opal White
26-3/8" L., 6-1/8" W., ht. 4-5/8".
23w integrated LED, CCT selectable (3000K, 4000K, 5000K), 90CRI, 2124 delivered lumens.

LED LINEAR CLOUD
P300240-060-CS Opal White
38-1/4" L., 6-1/8" W., ht. 4-5/8".
32w integrated LED, CCT selectable (3000K, 4000K, 5000K), 90CRI, 2760 delivered lumens.

Bath LED

The Bath LED Collection offers a taste of subtle sophistication to any design. Beautiful Brushed Nickel bands cap each end of the shades for a clean, modern aesthetic. The shades are offered in two sizes to help meet your unique design needs.



P300243-009-30



P300243-009-30

FINISH

● Brushed Nickel - 009

24IN 20W LED BATH VANITY
P300243-009-30 Brushed Nickel
24" W., 6" ht.
Extends 4-1/4".
23W integrated LED, 3000K, 90CRI, 1798 delivered lumens.

48IN 40W LED BATH VANITY
P300244-009-30 Brushed Nickel
48" W., 6" ht.
Extends 4-1/4".
37W integrated LED, 3000K, 90CRI, 3040 delivered lumens.

Nealy

FINISH
Brushed Nickel - 009

ALSO IN
Collections

P300142-009

Nealy offers classic charm with an edge of modern luxury. Curving details and candelabra arms are complemented by luxurious white glass shades. Featuring mixed metal influences, the Brushed Nickel frame is accentuated with Graphite detailing and completed with clear and brass-tone accents.



White Glass Shades

TWO-LIGHT BATH
P300141-009 Brushed Nickel
13-1/2" W., 9" ht.
Extends 6". H/CTR 6-3/8".
Two medium base lamps, each 100w max.

THREE-LIGHT BATH
P300142-009 Brushed Nickel
23" W., 9" ht.
Extends 6". H/CTR 6-3/8".
Three medium base lamps, each 100w max.

FOUR-LIGHT BATH
P300143-009 Brushed Nickel
30" W., 9" ht.
Extends 6". H/CTR 6-3/8".
Four medium base lamps, each 100w max.

WALL BRACKET
P710046-009 Brushed Nickel
Off-white silk shade.
5-1/2" W., 16-5/8" ht.
Extends 7". H/CTR 7-1/2".
One candelabra base lamp, 60w max.

All fixtures mount up or down, except P710046-009.


P710046-009


P300143-009


P300141-009


P300142-009

Nissé

FINISH
Polished Nickel - 104

ALSO IN
Pendants
Close-to-Ceiling

P2013-104

Elegant oval shaped, etched opal glass shades, accented with clear glass discs on a Polished Nickel finish.




P2015-104


P2012-104


P2014-104


P2013-104

ONE-LIGHT BATH
P2012-104 Polished Nickel
5-1/4" W., 9" ht.
Extends 5-1/4", H/CTR 6-5/8".
One medium base lamp, 100w max.

TWO-LIGHT BATH
P2013-104 Polished Nickel
14-5/8" W., 9" ht.
Extends 5-1/4". H/CTR 6-5/8".
Two medium base lamps, each 100w max.

THREE-LIGHT BATH
P2014-104 Polished Nickel
24" W., 9" ht.
Extends 5-1/4". H/CTR 6-5/8".
Three medium base lamps, each 100w max.

FOUR-LIGHT BATH
P2015-104 Polished Nickel
33-1/2" W., 9" ht.
Extends 5-1/4". H/CTR 6-5/8".
Four medium base lamps, each 100w max.

All fixtures mount up or down.

Anjoux

FINISH
Silver Ridge - 134

ALSO IN
Collections
Close-to-Ceiling

P300118-134

A distinctive collection with casual crystal details. Each fixture in the Anjoux family is highlighted by clear water glass shades.



ONE-LIGHT BATH
P300116-134 Silver Ridge
5" W., 8-5/8" ht.
Extends 6-7/8". H/CTR 4-1/2".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300117-134 Silver Ridge
14" W., 7-1/2" ht.
Extends 6-7/8". H/CTR 5".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300118-134 Silver Ridge
23" W., 7-1/2" ht.
Extends 7". H/CTR 5".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300119-134 Silver Ridge
32" W., 7-1/2" ht.
Extends 7". H/CTR 5".
Four medium base lamps,
each 100w max.


P300116-134


P300117-134


P300119-134

All fixtures mount up or down.

Featuring Anjoux



Anjoux

FINISH
Antique Bronze - 020

ALSO IN
Collections
Close-to-Ceiling

P300118-020



ONE-LIGHT BATH
P300116-020 Antique Bronze
5" W., 8-5/8" ht.
Extends 6-7/8". H/CTR 4-1/2".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300117-020 Antique Bronze
14" W., 7-1/2" ht.
Extends 6-7/8". H/CTR 5".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300118-020 Antique Bronze
23" W., 7-1/2" ht.
Extends 7". H/CTR 5".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300119-020 Antique Bronze
32" W., 7-1/2" ht.
Extends 7". H/CTR 5".
Four medium base lamps,
each 100w max.


P300116-020


P300117-020


P300119-020

All fixtures mount up or down.

Caress

FINISH
Polished Nickel - 104

ALSO IN
Collections
Close-to-Ceiling

P3076-104WB

Chic sophistication with cylindrical glass shades. Etched glass diffuser inside clear water glass floats in a traditional profile.

Etched Glass Diffuser



Traditional Profile

Cylindrical Glass Shades



P3076-104WB



P7046-104WB



P3077-104WB



P3078-104WB

ONE-LIGHT BATH
P7046-104WB Polished Nickel
8" W., 15" ht.
Extends 9-1/2". H/CTR 8-7/8".
One candelabra base krypton lamp, 60w max., included.

TWO-LIGHT BATH
P3076-104WB Polished Nickel
18-1/2" W., 5-5/8" ht. Extends 7".
H/CTR 2-3/4".
Two candelabra base krypton lamps, each 60w max., included.

THREE-LIGHT BATH
P3077-104WB Polished Nickel
26-1/2" W., 5-5/8" ht. Extends 7".
H/CTR 2-3/4".
Three candelabra base krypton lamps, each 60w max., included.

FOUR-LIGHT BATH
P3078-104WB Polished Nickel
34-1/2" W., 5-5/8" ht. Extends 7".
H/CTR 2-3/4".
Four candelabra base krypton lamps, each 60w max., included.

Replacement lamp P7807-01.
See page 824.

Moore

FINISHES

- Satin Brass - 012
- Polished Nickel - 104
- Brushed Nickel - 009
- Black - 031

P300281-012

Your life is busy and hectic, but your home can be an oasis of tranquility and calm under the classic, timeless glow of the Moore Collection. Breathtaking white opal glass shades affix to uncomplicated metal bars and backplates for an enduring light experience. These bath lights are designed for use with G9 LED bulbs.



ONE-LIGHT BATH
P300280-012 Satin Brass
4-3/4" W., 6-3/4" ht.
Extends 5-1/4". H/CTR 4-1/2".
One G9 base lamp,
5w max.

TWO-LIGHT BATH
P300281-012 Satin Brass
12-1/2" W., 6-3/4" ht.
Extends 5-1/4". H/CTR 4-3/8".
Two G9 base lamps,
each 5w max.

THREE-LIGHT BATH
P300282-012 Satin Brass
21-5/8" W., 6-3/4" ht.
Extends 5-1/4". H/CTR 4-3/8".
Three G9 base lamps,
each 5w max.

FOUR-LIGHT BATH
P300283-012 Satin Brass
30-3/4" W., 6-3/4" ht.
Extends 5-1/4". H/CTR 4-3/8".
Four G9 base lamps,
each 5w max.


P300280-012


P300283-012


P300281-012


P300282-012

All fixtures mount up or down.

Moore



P300283-104



P300280-104



P300282-104



P300281-104



P300283-009



P300280-009



P300282-009



P300281-009



P300283-031



P300280-031



P300282-031



P300281-031

ONE-LIGHT BATH
P300280-104 Polished Nickel
P300280-009 Brushed Nickel
P300280-031 Black
4-3/4" W., 6-3/4" ht.
Extends 5-1/4". H/CTR 4-1/2".
One G9 base lamp,
5w max.

TWO-LIGHT BATH
P300281-104 Polished Nickel
P300281-009 Brushed Nickel
P300281-031 Black
12-1/2" W., 6-3/4" ht.
Extends 5-1/4". H/CTR 4-3/8".
Two G9 base lamps,
each 5w max.

THREE-LIGHT BATH
P300282-104 Polished Nickel
P300282-009 Brushed Nickel
P300282-031 Black
21-5/8" W., 6-3/4" ht.
Extends 5-1/4". H/CTR 4-3/8".
Three G9 base lamps,
each 5w max.

FOUR-LIGHT BATH
P300283-104 Polished Nickel
P300283-009 Brushed Nickel
P300283-031 Black
30-3/4" W., 6-3/4" ht.
Extends 5-1/4". H/CTR 4-3/8".
Four G9 base lamps,
each 5w max.

All fixtures mount up or down.



3G9DLED27
See page 824 for details.


Draper

FINISH
Polished Nickel - 104

ALSO IN
Collections

P2102-104

Polished detailing and tubular forms contribute to the simple mid-century design.



ONE-LIGHT BATH
P2101-104 Polished Nickel
4-1/2" W., 8" ht.
Extends 4-1/8". H/CTR 4".
One candelabra base lamp, 60w max.

FOUR-LIGHT BATH
P2102-104 Polished Nickel
24" W., 5-1/8" ht.
Extends 4-1/8". H/CTR 2-1/4".
Four candelabra base lamps, each 60w max.

All fixtures shown with P7827-01 vintage lamps, not included. See page 824.



P2101-104



P2102-104

Index

FINISHES

Brushed Nickel - 009
Black - 031

P300077-009

Etched opal glass shades are nestled in sleek linear bands in the Index collection. Ideal for modern bath areas, Index enhances a spa-like environment.

Etched Opal Glass

Slick Linear Bands



Modern Bath



P300079-009



P300076-009



P300078-009



P300077-009



P300079-031



P300076-031



P300078-031



P300077-031

ONE-LIGHT BATH
P300076-009 Brushed Nickel
P300076-031 Black
4-7/8″ W., 8″ ht.
Extends 6-1/8″. H/CTR 4-1/2″.
One G9 base lamp,
60w max.

TWO-LIGHT BATH
P300077-009 Brushed Nickel
P300077-031 Black
15″ W., 5″ ht.
Extends 6-1/8″. H/CTR 3″.
Two G9 base lamps,
each 60w max.

THREE-LIGHT BATH
P300078-009 Brushed Nickel
P300078-031 Black
23-3/8″ W., 5″ ht.
Extends 6-1/8″. H/CTR 3″.
Three G9 base lamps,
each 60w max.

FOUR-LIGHT BATH
P300079-009 Brushed Nickel
P300079-031 Black
33″ W., 5″ ht.
Extends 6-1/8″. H/CTR 3″.
Four G9 base lamps,
each 60w max.

All fixtures mount up or down.



3G9DLED27
See page 824 for details.

Adley

FINISHES

- Brushed Nickel - 009
- Satin Brass - 012
- Matte Black - 031
- Polished Nickel - 104

P300156-009

Fundamentally modern but with a traditional twist, Adley combines a clear glass shade with a curved rectangular backplate. This sophisticated bath light is offered as a one, two, three or four-light fixture in a choice of four finishes. Adley is a universal choice for New Traditional and Transitional settings.

A Traditional Twist



Clear Glass Shade

Curved Backplate

ONE-LIGHT BATH
P300154-009 Brushed Nickel
4-1/2" W., 7-3/4" ht.,
Extends 6". H/CTR 5-3/8".
One medium base lamp,
60w max.

TWO-LIGHT BATH
P300155-009 Brushed Nickel
13-7/8" W., 7-5/8" ht.,
Extends 6". H/CTR 5-3/8".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH
P300156-009 Brushed Nickel
23" W., 7-5/8" ht.,
Extends 6". H/CTR 5-3/8".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH
P300157-009 Brushed Nickel
32" W., 7-5/8" ht.,
Extends 6". H/CTR 5-3/8".
Four medium base lamps,
each 60w max.



P300154-009



P300157-009



P300155-009



P300156-009

All fixtures mount up or down.

Adley



P300157-012



P300154-012



P300156-012



P300155-012



P300157-031



P300154-031



P300156-031



P300155-031



P300157-104



P300154-104



P300156-104



P300155-104

ONE-LIGHT BATH
P300154-012 Satin Brass
P300154-031 Matte Black
P300154-104 Polished Nickel
4-1/2" W., 7-3/4" ht.,
Extends 6". H/CTR 5-3/8".
One medium base lamp,
60w max.

TWO-LIGHT BATH
P300155-012 Satin Brass
P300155-031 Matte Black
P300155-104 Polished Nickel
13-7/8" W., 7-5/8" ht.,
Extends 6". H/CTR 5-3/8".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH
P300156-012 Satin Brass
P300156-031 Matte Black
P300156-104 Polished Nickel
23" W., 7-5/8" ht.,
Extends 6". H/CTR 5-3/8".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH
P300157-012 Satin Brass
P300157-031 Matte Black
P300157-104 Polished Nickel
32" W., 7-5/8" ht.,
Extends 6". H/CTR 5-3/8".
Four medium base lamps,
each 60w max.

All fixtures mount up or down.

Kene

FINISHES
- Brushed Nickel - 009
- Graphite - 143

ALSO IN
Collections
Close-to-Ceiling

P300121-009

Add a whimsy romance to the heart of your home with the lovely Kene Collection. Quiet, etched glass diffusers surrounded by clear, outer shades mark this collection with a soft luxurious touch. Kene is guaranteed to help make your home a calming, tranquil oasis infused with elegance and charm.



WALL BRACKET
P300120-009 Brushed Nickel
4-3/4" W., 12-7/8" ht.
Extends 6-1/2". H/CTR 8-7/8".
One medium base lamp,
75w max.

TWO-LIGHT BATH
P300121-009 Brushed Nickel
16-1/4" W., 7-3/8" ht.
Extends 7-1/4". H/CTR 4-5/8".
Two medium base lamps,
each 75w max.

THREE-LIGHT BATH
P300122-009 Brushed Nickel
23-3/8" W., 7-3/8" ht.
Extends 7-7/8". H/CTR 4-5/8".
Three medium base lamps,
each 75w max.

FOUR-LIGHT BATH
P300123-009 Brushed Nickel
30-3/4" W., 7-3/8" ht.
Extends 8-1/8". H/CTR 4-5/8".
Four medium base lamps,
each 75w max.


P300120-009


P300123-009


P300121-009


P300122-009

All fixtures mount up or down.

Kene



P300120-143



P300121-143



P300122-143



P300123-143

WALL BRACKET
P300120-143 Graphite
4-3/4″ W., 12-7/8″ ht.
Extends 6-1/2″. H/CTR 8-7/8″.
One medium base lamp,
75w max.

TWO-LIGHT BATH
P300121-143 Graphite
16-1/4″ W., 7-3/8″ ht.
Extends 7-1/4″. H/CTR 4-5/8″.
Two medium base lamps,
each 75w max.

THREE-LIGHT BATH
P300122-143 Graphite
23-3/8″ W., 7-3/8″ ht.
Extends 7-7/8″. H/CTR 4-5/8″.
Three medium base lamps,
each 75w max.

FOUR-LIGHT BATH
P300123-143 Graphite
30-3/4″ W., 7-3/8″ ht.
Extends 8-1/8″. H/CTR 4-5/8″.
Four medium base lamps,
each 75w max.

All fixtures mount up or down.

Dart

FINISH

● Graphite - 143

P300145-143

Dart is a display of modern architectural design styling. Etched white glass shades balance on a striking arched frame. Subtle detailing is enhanced by a Graphite finish with Brushed Nickel accents.

Modern Architectural Design



Etched White Glass

Striking Arched Frame

ONE-LIGHT BATH
P300144-143 Graphite
4-1/2" W., 16-7/8" ht.
Extends 6-7/8". H/CTR 8".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300145-143 Graphite
14-1/4" W., 7-7/8" ht.
Extends 6-7/8". H/CTR 5-5/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300146-143 Graphite
23-5/8" W., 7-7/8" ht.
Extends 6-7/8". H/CTR 5-5/8".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300147-143 Graphite
33" W., 7-7/8" ht.
Extends 6-7/8". H/CTR 5-5/8".
Four medium base lamps,
each 100w max.



P300144-143



P300146-143



P300147-143

All fixtures mount up or down.

Status

FINISH
Polished Chrome - 15

ALSO IN
Collections
Close-to-Ceiling

P2776-15

Status collection's K-9 glass accents offer crystal-like clarity to contrast the softened linen-finish glass shades. A Polished Chrome frame provides the perfect support to this elegant combination.





P2777-15



P2060-15



P2776-15



P2775-15

ONE-LIGHT BATH
P2060-15 Polished Chrome
6" W., 15-1/2 ht.
Extends 7-3/8". H/CTR 8-3/4".
One medium base lamp, 100w max.

TWO-LIGHT BATH
P2775-15 Polished Chrome
13-7/8" W., 10-1/8 ht.
Extends 5-3/4". H/CTR 6-3/4".
Two medium base lamps, each 100w max.

THREE-LIGHT BATH
P2776-15 Polished Chrome
23-3/4" W., 10-1/8" ht.
Extends 5-3/4". H/CTR 6-3/4".
Three medium base lamps, each 100w max.

FOUR-LIGHT BATH
P2777-15 Polished Chrome
33-7/8" W., 10-1/8" ht.
Extends 5-3/4". H/CTR 6-3/4".
Four medium base lamps, each 100w max.

All fixtures mount up or down, except P2060-15.

Lucky

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15

P2117-09

Lucky's distinctive design evokes a vintage flair with finely crafted details. Light is beautifully illuminated through frosted double prismatic glass shades.

Double Prismatic Glass



Vintage Flair

Brushed Nickel

ONE-LIGHT BATH
P2115-09 Brushed Nickel
5" W., 8" ht.
Extends 6-5/8". H/CTR 4".
One medium base lamp,
100w max.



P2115-09

TWO-LIGHT BATH
P2116-09 Brushed Nickel
14-1/2" W., 7-5/8" ht.
Extends 6-5/8". H/CTR 3-7/8".
Two medium base lamps,
each 100w max.



P2116-09

THREE-LIGHT BATH
P2117-09 Brushed Nickel
24" W., 7-5/8" ht.
Extends 6-5/8". H/CTR 3-7/8".
Three medium base lamps,
each 100w max.



P2117-09

FOUR-LIGHT BATH
P2118-09 Brushed Nickel
33-5/8" W., 7-5/8" ht.
Extends 6-5/8". H/CTR 3-7/8".
Four medium base lamps,
each 100w max.



P2118-09

All fixtures mount up or down.

Lucky



P2116-15



P2115-15



P2117-15



P2118-15

ONE-LIGHT BATH
P2115-15 Polished Chrome
5″ W., 8″ ht.
Extends 6-5/8″. H/CTR 4″.
One medium base lamp,
100w max.

TWO-LIGHT BATH
P2116-15 Polished Chrome
14-1/2″ W., 7-5/8″ ht.
Extends 6-5/8″. H/CTR 3-7/8″.
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P2117-15 Polished Chrome
24″ W., 7-5/8″ ht.
Extends 6-5/8″. H/CTR 3-7/8″.
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P2118-15 Polished Chrome
33-5/8″ W., 7-5/8″ ht.
Extends 6-5/8″. H/CTR 3-7/8″.
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

Domain

FINISH
● Matte Black - 031

ALSO IN
Collections

P300033-031

A sensible, yet sophisticated, lighting collection rooted in updated classical modern styling. Suitable for Urban Industrial, Modern and Mid-Century Modern interiors, Domain features a Matte Black finish. A double ring accent and squared off socket holder complement over scale etched glass shades. Bath and chandelier options are available.



ONE-LIGHT BATH
P300032-031 Matte Black
8-3/4" W., 6-5/8" ht.
Extends 9-1/2". H/CTR 4-1/2".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300033-031 Matte Black
20" W., 6-1/2" ht.
Extends 9-1/2". H/CTR 4-1/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300034-031 Matte Black
32" W., 6-1/2" ht.
Extends 9-1/2". H/CTR 4-1/8".
Three medium base lamps,
each 100w max.

All fixtures mount up or down.


P300032-031


P300033-031


P300034-031

Litchfield

FINISH
Polished Chrome - 015

ALSO IN
Collections
Sconces

P300138-015

A casual, coastal-inspired collection. Litchfield features an hourglass-inspired column complemented by a crisp Chrome finish.





P300139-015



P300137-015



P300140-015

ONE-LIGHT BATH
P300137-015 Polished Chrome
5" W., 9-1/4" ht.
Extends 7-3/8". H/CTR 5".
One medium base lamp, 60w max.

TWO-LIGHT BATH
P300138-015 Polished Chrome
15-3/8" W., 9-1/4" ht.
Extends 7-3/8". H/CTR 4-5/8".
Two medium base lamps, each 60w max.

THREE-LIGHT BATH
P300139-015 Polished Chrome
24-3/8" W., 9-1/4" ht.
Extends 7-3/8". H/CTR 4-5/8".
Three medium base lamps, each 60w max.

FOUR-LIGHT BATH
P300140-015 Polished Chrome
33-3/8" W., 9-1/4" ht.
Extends 7-3/8". H/CTR 4-5/8".
Four medium base lamps, each 60w max.

All fixtures mount up or down.

Lassiter

FINISHES
- Brushed Nickel - 009
- Black - 031

ALSO IN
Collections
Close-to-Ceiling
Sconces

P300258-009

Manifest a swoon-worthy lighting experience with the stunning blend of modern and traditional styles in the one-of-a-kind Lassiter Collection. Square tubing with clean, sharp angles demand your attention and appreciation. Striking, vintage light sockets boast their bold, yet simple demeanors as they are encased in sophisticated clear glass shades to complete this statement-making collection.



ONE-LIGHT BATH
P710073-009 Brushed Nickel
4-7/8" W., 19-1/4" ht.,
Extends 6-1/2". H/CTR 9-3/8".
One medium base lamp,
60w max.

TWO-LIGHT BATH
P300257-009 Brushed Nickel
16" W., 8" ht.
Extends 5-1/2". H/CTR 5-1/2".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH
P300258-009 Brushed Nickel
24" W., 8" ht.
Extends 8-1/8". H/CTR 5-5/8".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH
P300259-009 Brushed Nickel
34" W., 8" ht.
Extends 8-1/8". H/CTR 5-5/8".
Four medium base lamps,
each 60w max.

All fixtures mount up or down.



P300257-009



P300258-009



P710073-009



P300259-009

Lassiter



P710073-031



P300257-031



P300258-031



P300259-031

ONE-LIGHT BATH
P710073-031 Black
4-7/8″ W., 19-1/4″ ht.,
Extends 6-1/2″. H/CTR 9-3/8″.
One medium base lamp,
60w max.

TWO-LIGHT BATH
P300257-031 Black
16″ W., 8″ ht.
Extends 5-1/2″. H/CTR 5-1/2″.
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH
P300258-031 Black
24″ W., 8″ ht.
Extends 8-1/8″. H/CTR 5-5/8″.
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH
P300259-031 Black
34″ W., 8″ ht.
Extends 8-1/8″. H/CTR 5-5/8″.
Four medium base lamps,
each 60w max.

All fixtures mount up or down.

Bowman

FINISHES
● Black - 031
○ Cottage White - 151

ALSO IN
Collections
Close-to-Ceiling

P300254-031

Beautiful lighting will appeal to both your classic taste and your artistic spirit with the Bowman Collection. Wandering eyes will focus on clear, chiseled glass shades as they offer an air of refinery. Handsome light bases with dainty, sophisticated curved arms support elegant light bases.



ONE-LIGHT BATH
P300253-031 Black
5" W., 10-3/8" ht.
Extends 7". H/CTR 3-1/2".
One medium base lamp, 60w max.


P300253-031

TWO-LIGHT BATH
P300254-031 Black
16-3/8" W., 7-3/4" ht.
Extends 7-3/8". H/CTR 3-1/4".
Two medium base lamps, each 60w max.


P300254-031

THREE-LIGHT BATH
P300255-031 Black
25" W., 7-3/4" ht.
Extends 7-3/8". H/CTR 3-1/4".
Three medium base lamps, each 60w max.


P300255-031

FOUR-LIGHT BATH
P300256-031 Black
33-5/8" W., 7-3/4" ht.
Extends 7-3/8". H/CTR 3-1/4".
Four medium base lamps, each 60w max.


P300256-031

All fixtures mount up or down.

Bowman



P300254-151



P300253-151



P300255-151



P300256-151

ONE-LIGHT BATH
P300253-151 Cottage White
5" W., 10-3/8" ht.
Extends 7". H/CTR 3-1/2".
One medium base lamp,
60w max.

TWO-LIGHT BATH
P300254-151 Cottage White
16-3/8" W., 7-3/4" ht.
Extends 7-3/8". H/CTR 3-1/4".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH
P300255-151 Cottage White
25" W., 7-3/4" ht.
Extends 7-3/8". H/CTR 3-1/4".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH
P300256-151 Cottage White
33-5/8" W., 7-3/4" ht.
Extends 7-3/8". H/CTR 3-1/4".
Four medium base lamps,
each 60w max.

All fixtures mount up or down.

Winslett

FINISHES
- Brushed Nickel - 009
- Black - 031

ALSO IN
Collections
Close-to-Ceiling

P300273-009

Immerse yourself in a bathroom that is primed for relaxation with the beautiful imperfection of the Winslett Collection. Savor this fresh take on a classic light choice as your gaze traces its clean crisp lines. Perfectly imperfect lightly seeded glass shades rest in shiny pedestal light bases that adds an unexpected, but welcomed dash of modern personality to this clean, traditional collection.



ONE-LIGHT BATH
P300272-009 Brushed Nickel
4-3/4" W., 9-1/2" ht.
Extends 6-3/4". H/CTR 4-3/4".
One medium base lamp,
60w max.

TWO-LIGHT BATH
P300273-009 Brushed Nickel
14-1/4" W., 7-1/4" ht.
Extends 7-3/8". H/CTR 4-1/4".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH
P300274-009 Brushed Nickel
23-3/4" W., 7-1/4" ht.
Extends 7-3/8". H/CTR 4-1/4".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH
P300275-009 Brushed Nickel
33-1/4" W., 7-1/4" ht.
Extends 7-3/8". H/CTR 4-1/4".
Four medium base lamps,
each 60w max.

All fixtures mount up or down.
Shown with P7825-01 vintage lamps, not included. See page 824.


P300272-009


P300273-009


P300274-009


P300275-009

Winslett



P300273-031



P300272-031



P300274-031



P300275-031

ONE-LIGHT BATH
P300272-031 Black
4-3/4" W., 9-1/2" ht.
Extends 6-3/4". H/CTR 4-3/4".
One medium base lamp,
60w max.

TWO-LIGHT BATH
P300273-031 Black
14-1/4" W., 7-1/4" ht.
Extends 7-3/8". H/CTR 4-1/4".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH
P300274-031 Black
23-3/4" W., 7-1/4" ht.
Extends 7-3/8". H/CTR 4-1/4".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH
P300275-031 Black
33-1/4" W., 7-1/4" ht.
Extends 7-3/8". H/CTR 4-1/4".
Four medium base lamps,
each 60w max.

All fixtures mount up or down.
Shown with P7825-01 vintage lamps, not included. See page 824.

Mast

FINISHES
- Brushed Nickel - 009
- Antique Bronze - 020

ALSO IN
Collections
Close-to-Ceiling

P300216-009

Mast combines a clean, modern design expression with faux wood accents for a modern-meets-farmhouse approach to lighting. The contrast of warm wood paired with sleek metallic lines and double glass shades offers a subtly alluring, Zen look to these vanity fixtures. An oversized cylindrical frame banded top and bottom in Brushed Nickel or Antique Bronze and trimmed with faux wood accents gives a warm organic feel to the flush mount fixture.

Modern Meets Farmhouse



Double Glass Shades

Faux Wood Accents

ONE-LIGHT BATH
P710015-009 Brushed Nickel
5" W., 13" ht.,
Extends 6-3/8". H/CTR 6-1/2".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300216-009 Brushed Nickel
13-7/8" W., 7-5/8" ht.,
Extends 6-1/4". H/CTR 5-1/4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300217-009 Brushed Nickel
24" W., 7-3/4" ht.,
Extends 6-1/4". H/CTR 5-1/4".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300218-009 Brushed Nickel
33-7/8" W., 7-3/4" ht.,
Extends 6-1/4". H/CTR 5-1/4".
Four medium base lamps,
each 100w max.



P710015-009



P300218-009



P300216-009



P300217-009

All fixtures mount up or down.

Mast



P710015-020



P300216-020



P300217-020



P300218-020

ONE-LIGHT BATH
P710015-020 Antique Bronze
5" W., 13" ht.,
Extends 6-3/8". H/CTR 6-1/2".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300216-020 Antique Bronze
13-7/8" W., 7-5/8" ht.,
Extends 6-1/4". H/CTR 5-1/4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300217-020 Antique Bronze
24" W., 7-3/4" ht.,
Extends 6-1/4". H/CTR 5-1/4".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300218-020 Antique Bronze
33-7/8" W., 7-3/4" ht.,
Extends 6-1/4". H/CTR 5-1/4".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.


Fawcett

FINISHES

- Brushed Nickel - 009
- Black - 031

P300270-009

Open the door to a world of modern elegance with the clean and crisp Fawcett Collection. Signature, clear grid glass shades provide a calming and relaxing lighting experience. Each shade is held in place by simple, gentle backplates coated in a beautiful brushed nickel or matte black finish.



ONE-LIGHT BATH
P300268-009 Brushed Nickel
4-1/2" W., 7-3/4" ht.
Extends 5-7/8". H/CTR 4-1/2".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300269-009 Brushed Nickel
13-1/8" W., 7-3/4" ht.
Extends 5-7/8". H/CTR 5-1/2".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300270-009 Brushed Nickel
22-1/8" W., 7-3/4" ht.
Extends 5-7/8". H/CTR 5-1/2".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300271-009 Brushed Nickel
31-1/8" W., 7-3/4" ht.
Extends 5-7/8". H/CTR 5-1/2".
Four medium base lamps,
each 100w max.


P300268-009


P300271-009


P300269-009


P300270-009

All fixtures mount up or down.

Fawcett



P300268-031



P300269-031



P300270-031



P300271-031

ONE-LIGHT BATH
P300268-031 Black
4-1/2" W., 7-3/4" ht.
Extends 5-7/8". H/CTR 4-1/2".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300269-031 Black
13-1/8" W., 7-3/4" ht.
Extends 5-7/8". H/CTR 5-1/2".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300270-031 Black
22-1/8" W., 7-3/4" ht.
Extends 5-7/8". H/CTR 5-1/2".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300271-031 Black
31-1/8" W., 7-3/4" ht.
Extends 5-7/8". H/CTR 5-1/2".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

Dwyer

FINISHES
- Black - 031
- Stainless Steel - 135

ALSO IN
Close-to-Ceiling

P300265-135

Incorporate a vintage feel with a dash of industrial personality with the Dwyer Collection. Attention-grabbing, clear, ribbed glass takes center stage in this design, creating a gaslight glow when the fixture is illuminated. Simple metal frames encase the glass panes to emphasize the collection's chic industrial edge.

Industrial Design



Ribbed Glass Panes

Gaslight Glow

TWO-LIGHT BATH
P300265-135 Stainless Steel
14" W., 5" ht.
Extends 4-1/2". H/CTR 2-1/4".
Two G16.5 candelabra base lamps, each 60w max.



P300265-135

THREE-LIGHT BATH
P300266-135 Stainless Steel
22" W., 5" ht.
Extends 4-1/2". H/CTR 2-1/4".
Three G16.5 candelabra base lamps, each 60w max.



P300266-135

FOUR-LIGHT BATH
P300267-135 Stainless Steel
30" W., 5" ht.
Extends 4-1/2". H/CTR 2-1/4".
Four G16.5 candelabra base lamps, each 60w max.



P300267-135



P300265-031



P300266-031



P300267-031

TWO-LIGHT BATH
P300265-031 Black
14″ W., 5″ ht.
Extends 4-1/2″. H/CTR 2-1/4″.
Two G16.5 candelabra base lamps, each 60w max.

THREE-LIGHT BATH
P300266-031 Black
22″ W., 5″ ht.
Extends 4-1/2″. H/CTR 2-1/4″.
Three G16.5 candelabra base lamps, each 60w max.

FOUR-LIGHT BATH
P300267-031 Black
30″ W., 5″ ht.
Extends 4-1/2″. H/CTR 2-1/4″.
Four G16.5 candelabra base lamps, each 60w max.

Calhoun

FINISHES
- Brushed Nickel - 009
- Antique Bronze - 020

ALSO IN
Collections
Close-to-Ceiling
Pendants

P300047-009

A delightful trend in home décor is the repurposing of antique parts into new, functional furniture and accessories. Calhoun playfully follows this lead with an apothecary style and features a clear glass diffuser held in place with a mechanical latch from a spice container. The glass shade showcases a thickened profile to create a vintage-style surface for a classic handmade appearance.



ONE-LIGHT BATH
P300045-009 Brushed Nickel
5" W., 8-5/8" ht.
Extends 6-7/8". H/CTR 5-1/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300046-009 Brushed Nickel
13-1/4" W., 8-5/8" ht.
Extends 6-7/8". H/CTR 6-3/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300047-009 Brushed Nickel
21-5/8"8-5/8" ht.
Extends 6-7/8". H/CTR 6-3/8".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300048-009 Brushed Nickel
30-1/4" W., 8-5/8" ht.
Extends 6-7/8". H/CTR 6-3/8".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.
Shown with P7825-01 vintage lamps, not included. See page 824.


P300045-009


P300048-009


P300046-009


P300047-009

Calhoun



P300046-020



P300045-020



P300047-020



P300048-020

ONE-LIGHT BATH
P300045-020 Antique Bronze
5" W., 8-5/8" ht.
Extends 6-7/8". H/CTR 5-1/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300046-020 Antique Bronze
13-1/4" W., 8-5/8" ht.
Extends 6-7/8". H/CTR 6-3/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300047-020 Antique Bronze
21-5/8"8-5/8" ht.
Extends 6-7/8". H/CTR 6-3/8".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300048-020 Antique Bronze
30-1/4" W., 8-5/8" ht.
Extends 6-7/8". H/CTR 6-3/8".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.
Shown with P7825-01 vintage lamps, not included. See page 824.

Featuring Calhoun
Image: Tresidio Homes



Tilley

FINISHES
- Brushed Nickel - 009
- Antique Bronze - 020

ALSO IN
Collections
Close-to-Ceiling

P300044-020

Rustic and vintage décor is a popular trend that can help transform your home into a nostalgic retreat. Tilley features warehouse style shades formed from metal mesh that merge with a faux-painted, wooden rim for an artful yet industrial style.



ONE-LIGHT BATH
P300042-009 Brushed Nickel
P300042-020 Antique Bronze
6-3/8" W., 8-1/2" ht.
Extends 8-1/4". H/CTR 4-1/4".
One medium base lamp,
100w max.


P300042-020


P300044-020

TWO-LIGHT BATH
P300043-009 Brushed Nickel
P300043-020 Antique Bronze
15" W., 8-3/8" ht.
Extends 8-3/8". H/CTR 4-1/4".
Two medium base lamps,
each 100w max.


P300043-020


P300043-009

THREE-LIGHT BATH
P300044-009 Brushed Nickel
P300044-020 Antique Bronze
23-3/8" W., 8-3/8" ht.
Extends 8-3/8". H/CTR 4-1/4".
Three medium base lamps,
each 100w max.


P300042-009


P300044-009

All fixtures mount up or down. Shown with P7825-01 vintage lamps, not included. See page 824.

Barnes Mill

FINISH
Antique Bronze - 020

ALSO IN
Collections
Close-to-Ceiling

P300068-020

Rustic and vintage décor can transform your home into a nostalgic retreat reminiscent of rural farmhouses. Exposed iron details and a faux-painted wooden plank support artful, clear seeded glass shades. Combine with vintage-style light bulbs to create a romantic focal point for any room. Installs up or down.

Rustic and Vintage



Clear Seeded Glass Shades

Exposed Iron Details



P300067-020



P300066-020



P300068-020



P300069-020

ONE-LIGHT BATH
P300066-020 Antique Bronze
4 1/2" W., 11 7/8" ht.
Extends 5 7/8". H/CTR 7-5/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300067-020 Antique Bronze
13 3/8" W., 8" ht.
Extends 5 7/8". H/CTR 5-3/4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300068-020 Antique Bronze
24" W., 8" ht.
Extends 5 7/8". H/CTR 5-3/4".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300069-020 Antique Bronze
32 1/4" W., 8" ht.
Extends 5 7/8". H/CTR 5-3/4".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.
Shown with P7825-01 vintage lamps, not included. See page 824.

Gulliver

FINISHES
- Galvanized - 141
- Graphite - 143

ALSO IN
Collections
Ceiling Fans

P300124-141

Three circular bands wrap together to create an open design for Gulliver. Dual toned frame color combinations are Galvanized with antique white accents or Graphite with weathered gray accents. A hand painted wood grained texture complements Rustic and Modern Farmhouse home décor, as well as Urban Industrial and Coastal interior settings.

Modern Farmhouse



Hand Painted Wood

Dual Toned Frame

ONE-LIGHT BATH
P710031-141 Galvanized
6" dia., 12" ht.
Extends 7". H/CTR 9-3/8".
One medium base lamp, 75w max.

TWO-LIGHT BATH
P300124-141 Galvanized
15-1/2" W., 8-1/2" ht.
Extends 5". H/CTR 6-1/8".
Two medium base lamps, each 60w max.

THREE-LIGHT BATH
P300125-141 Galvanized
24" W., 8-1/2" ht.
Extends 5". H/CTR 6-1/8".
Three medium base lamps, each 60w max.

FOUR-LIGHT BATH
P300126-141 Galvanized
32-7/8" W., 8-1/2" ht.
Extends 5". H/CTR 6-1/8".
Four medium base lamps, each 60w max.

All fixtures mount up or down.
Shown with P7825-01 vintage lamps, not included. See page 824.



P710031-141



P300126-141



P300124-143



P300125-141

Gulliver



P300124-143



P710031-143



P300125-143



P300126-143

ONE-LIGHT BATH
P710031-143 Graphite
6″ dia., 12″ ht.
Extends 7″. H/CTR 9-3/8″.
One medium base lamp,
75w max.

TWO-LIGHT BATH
P300124-143 Graphite
15-1/2″ W., 8-1/2″ ht.
Extends 5″. H/CTR 6-1/8″.
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH
P300125-143 Graphite
24″ W., 8-1/2″ ht.
Extends 5″. H/CTR 6-1/8″.
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH
P300126-143 Graphite
32-7/8″ W., 8-1/2″ ht.
Extends 5″. H/CTR 6-1/8″.
Four medium base lamps,
each 60w max.

All fixtures mount up or down. Shown with P7825-01 vintage lamps, not included. See page 824.

Briarwood

FINISHES
- Antique Bronze - 020
- Graphite - 143

ALSO IN
Collections
Close-to-Ceiling

P300230-143

The classic, X-brace pattern inspired by farmhouse or barn doors is re-imagined in the Briarwood two, three, and four-light wall sconce offerings. The simple geometric shape, a hallmark of the Briarwood collection, is mounted on the faux-painted wood backplate, with a clear glass shade completing the look.

Barn Doors Reimagined



Faux-Painted Wood Backplate

X-Brace Pattern

ONE-LIGHT BATH
P710012-143 Graphite
6-7/8" W., 12" ht.
Extends 6", H/CTR 4".
One medium base lamp, 100w max.



P710012-143

TWO-LIGHT BATH
P300230-143 Graphite
14-3/4" W., 8-1/4" ht.,
Extends 6-1/2". H/CTR 5-7/8".
Two medium base lamps, each 60w max.



P300232-143

THREE-LIGHT BATH
P300231-143 Graphite
24-3/4" W., 8-1/4" ht.,
Extends 6-1/2". H/CTR 5-7/8".
Three medium base lamps, each 60w max.

FOUR-LIGHT BATH
P300232-143 Graphite
34-3/4" W., 8-1/4" ht.,
Extends 6-1/2". H/CTR 5-7/8".
Four medium base lamps, each 60w max.



P300230-143



P300231-143

All fixtures mount up or down. Shown with P7825-01 vintage lamps, not included. See page 824.

Briarwood



P300230-020



P710012-020



P300231-020



P300232-020

ONE-LIGHT BATH
P710012-020 Antique Bronze
6-7/8" W., 12" ht.
Extends 6", H/CTR 4".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300230-020 Antique Bronze
14-3/4" W., 8-1/4" ht.,
Extends 6-1/2". H/CTR 5-7/8".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH
P300231-020 Antique Bronze
24-3/4" W., 8-1/4" ht.,
Extends 6-1/2". H/CTR 5-7/8".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH
P300232-020 Antique Bronze
34-3/4" W., 8-1/4" ht.,
Extends 6-1/2". H/CTR 5-7/8".
Four medium base lamps,
each 60w max.

All fixtures mount up or down. Shown with P7825-01 vintage lamps, not included. See page 824.

Featuring Briarwood



Featuring Bramlett
Image: Amber Pirillo



Bramlett

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015

P300041-009

Vintage and industrial styling coalesce in the functional, yet elegant frame of the Bramlett fixtures. Metal reflector style shades are complemented by contrasting metallic fittings. Fixtures from this collection pair well with either vintage style or traditional bulbs to create a fun focal point in your home.



ONE-LIGHT BATH
P300039-009 Brushed Nickel
6" W., 8-1/8" ht.
Extends 7-1/8". H/CTR 4-1/2".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300040-009 Brushed Nickel
15-1/8" W., 8-3/8" ht.
Extends 7-1/8". H/CTR 6".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300041-009 Brushed Nickel
24-1/4" W., 8-3/8" ht.
Extends 7-1/8". H/CTR 6".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300203-009 Brushed Nickel
33-3/8" W., 8-3/8" ht.
Extends 7-1/8". H/CTR 6".
Four medium base lamps,
each 100w max.


P300039-009


P300203-009


P300041-009


P300040-009

All fixtures mount up or down.

Bramlett



P300040-015



P300039-015



P300041-015



P300203-015

ONE-LIGHT BATH
P300039-015 Polished Chrome
6" W., 8-1/8" ht.
Extends 7-1/8". H/CTR 4-1/2".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300040-015 Polished Chrome
15-1/8" W., 8-3/8" ht.
Extends 7-1/8". H/CTR 6".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300041-015 Polished Chrome
24-1/4" W., 8-3/8" ht.
Extends 7-1/8". H/CTR 6".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300203-015 Polished Chrome
33-3/8" W., 8-3/8" ht.
Extends 7-1/8". H/CTR 6".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

Rushton

FINISH

Brushed Nickel - 009
Graphite - 143

P300228-143

Celebrate the past with the industrial-styled Rushton vanity. Mechanical details like a pulley wheel complete with a faux cord holding a clear glass shade, an antique style socket, and an exposed bulb (not included) add vintage charm. The mixed metal fixture is offered in either Brushed Nickel accented with a Black tube arm, or Graphite with an Antique Brass tube arm, for a look that preserves a sense of history.

Mechanical Detail

Mixed Metals



Antique Style Socket

ONE-LIGHT BATH
P300226-143 Graphite
5" W., 9-1/2" ht.,
Extends 6". H/CTR 6-1/2".
One medium base lamp,
60w max.



P300226-143

TWO-LIGHT BATH
P300227-143 Graphite
16" W., 9-1/2" ht.,
Extends 6". H/CTR 7".
Two medium base lamps,
each 60w max.



P300229-143

THREE-LIGHT BATH
P300228-143 Graphite
24" W., 9-1/2" ht.,
Extends 6". H/CTR 7".
Three medium base lamps,
each 60w max.



P300227-143

FOUR-LIGHT BATH
P300229-143 Graphite
32" W., 9-1/2" ht.,
Extends 6". H/CTR 7".
Four medium base lamps,
each 60w max.



P300228-143

Rushton



P300229-009



P300226-009



P300228-009



P300227-009

ONE-LIGHT BATH
P300226-009 Brushed Nickel
5" W., 9-1/2" ht.,
Extends 6". H/CTR 6-1/2".
One medium base lamp,
60w max.

TWO-LIGHT BATH
P300227-009 Brushed Nickel
16" W., 9-1/2" ht.,
Extends 6". H/CTR 7".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH
P300228-009 Brushed Nickel
24" W., 9-1/2" ht.,
Extends 6". H/CTR 7".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH
P300229-009 Brushed Nickel
32" W., 9-1/2" ht.,
Extends 6". H/CTR 7".
Four medium base lamps,
each 60w max.

All fixtures shown with P7825-01 vintage lamps, not included.
See page 824.

Featuring Rushton



Featuring Gauge
Image: Landmark Homes



Add Timeless Comfort

Timeless Farmhouse style can take an industrial turn when modern updates are added to the mix. Combine key Farmhouse style icons of comfortable furniture, shiplap walls and a light and fresh color scheme with industrial touches like the pair of Gauge wire-framed wall sconces installed above the stone fireplace. Let sunlight stream through unadorned windows to create a bright and cheerful space.


Gauge

FINISH
● Graphite - 143

ALSO IN
Pendants
Close-to-Ceiling

P300029-143

Inspired by industrial elements, Gauge features an open cage design that's both functional and aesthetically appealing. Frame is comprised of Graphite with Brushed Nickel accents.





P300031-143



P300028-143



P300030-143



P300029-143

ONE-LIGHT BATH
P300028-143 Graphite
6-1/8" W., 10-1/2" ht.
Extends 7-1/4". H/CTR 3".
One medium base lamp, 60w max.

TWO-LIGHT BATH
P300029-143 Graphite
15-5/8" W., 11" ht.
Extends 7-1/4". H/CTR 3".
Two medium base lamps, each 60w max.

THREE-LIGHT BATH
P300030-143 Graphite
25-1/8" W., 11" ht.
Extends 7-1/4". H/CTR 3".
Three medium base lamps, each 60w max.

FOUR-LIGHT BATH
P300031-143 Graphite
34-5/8" W., 11" ht.
Extends 7-1/4". H/CTR 3".
Four medium base lamps, each 60w max.

All fixtures shown with P7825-01 vintage lamps, not included.
See page 824.

Signal

FINISHES
- Polished Chrome - 015
- Graphite - 143

ALSO IN
Close-to-Ceiling

P300175-015

Signal has an industrial origin, yet its clean lines beckon a modern sensibility. Clear blown glass shades deliver a lighter touch, balancing the substantial look of the metal angular arm and round backplate. With its emphasis on simplicity and function, Signal is ideal for many residential settings.



ONE-LIGHT BATH
P300174-015 Polished Chrome
5-1/8" W., 9-1/8" ht.,
Extends 5-3/8". H/CTR 2-5/8".
One medium base lamp,
60w max.

TWO-LIGHT BATH
P300175-015 Polished Chrome
13-1/2" W., 9-1/8" ht.,
Extends 5-3/8". H/CTR 2-5/8".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH
P300176-015 Polished Chrome
23-1/8" W., 9-1/8" ht.,
Extends 5-3/8". H/CTR 2-5/8".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH
P300177-015 Polished Chrome
33-1/2" W., 9-1/8" ht.,
Extends 5-3/8". H/CTR 2-5/8".
Four medium base lamps,
each 60w max.



P300174-015 P300177-015



P300175-015 P300176-015

All fixtures mount up or down.

Signal



P300174-143



P300175-143



P300176-143



P300177-143

ONE-LIGHT BATH
P300174-143 Graphite
5-1/8" W., 9-1/8" ht.,
Extends 5-3/8". H/CTR 2-5/8".
One medium base lamp,
60w max.

TWO-LIGHT BATH
P300175-143 Graphite
13-1/2" W., 9-1/8" ht.,
Extends 5-3/8". H/CTR 2-5/8".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH
P300176-143 Graphite
23-1/8" W., 9-1/8" ht.,
Extends 5-3/8". H/CTR 2-5/8".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH
P300177-143 Graphite
33-1/2" W., 9-1/8" ht.,
Extends 5-3/8". H/CTR 2-5/8".
Four medium base lamps,
each 60w max.

All fixtures mount up or down.

Circuit

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015

P300148-009-WB

Connectivity and electric circuit diagrams inspired the design behind this new bath collection. Circuit fixtures appear to contain a lamp that is a continuous tube for an intriguing appearance. This collection is ideal for residential or light commercial applications, such as restaurants or other Urban Industrial and Vintage Electric design schemes.

Circuit Connectivity Inspired



Urban Industrial

Vintage Electric

ONE-LIGHT BATH
P300148-009-WB Brushed Nickel
P300148-015-WB Polished Chrome
13-1/2" W., 5-1/8" ht.
Extends 3". H/CTR 2-1/2".
One medium base T10 lamp,
40w max included.

TWO-LIGHT BATH
P300149-009-WB Brushed Nickel
P300149-015-WB Polished Chrome
27-1/4" W., 5-1/8" ht.
Extends 3". H/CTR 2-1/2".
Two medium base T10 lamps,
Each 40w max included.


P860028-001 Vintage Amber Lamp
Overall L 8-3/4".
40w T10 medium base.




P860028-001

All fixtures can be installed horizontally or vertically.

All fixtures shown with EF6.5T10DL9927/JA8 lamps, not included. See page 824.



P300148-009-WB



P300149-009-WB



P300148-015-WB



P300149-015-WB



P300148-009-WB
mounted vertical



P300148-015-WB
mounted vertical

Lynzie

FINISH

Polished Chrome - 15

P2803-15

A clean, crisp design serves as the cornerstone for the Lynzie Collection. Elegant, etched white opal glass shades affix to smooth, simple bars. A beautiful oval backplate serves as the foundation for each design. Mount the light fixtures facing up or down, around or over a bathroom mirror to banish shadows from your face while getting ready for the day or for a fun evening out.





P2804-15



P2801-15



P2803-15



P2802-15

ONE-LIGHT BATH
P2801-15 Polished Chrome
5-1/4" W.,10-3/8" ht.
Extends 5-5/8". H/CTR 6-7/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P2802-15 Polished Chrome
14-1/2" W., 11-1/8" ht.
Extends 5-5/8". H/CTR 8-5.8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P2803-15 Polished Chrome
24" W., 11-1/8" ht.
Extends 5-5/8". H/CTR 8-5/8".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P2804-15 Polished Chrome
33-1/4" W., 11-1/8" ht.
Extends 5-5/8". H/CTR 8-5/8".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

Featuring Archives
Image: Green Tech Homes, Piper Stromatt and 161 Photography




Archives

FINISHES
- Antique Bronze - 20
- Antique Nickel - 81

ALSO IN
Pendants

P2809-20

Archives offers a vintage electric feel to the bath. The two-light features clear glass and the mixed metals complement a wide variety of faucets.





P2809-81



P7156-09



P2809-20
mounted vertical



P2809-20



P7156-20

TWO-LIGHT BATH
P2809-20 Antique Bronze with Antique Brass accents
P2809-81 Antique Nickel with Brushed Nickel accents
Installs horizontal or vertical.
18-1/2" W., 4-3/4" ht.
Extends 7". H/CTR 2-3/8".
Two medium base lamps, each 100w max.

WALL BRACKET
P7156-20 Antique Bronze with Antique Brass accents
P7156-81 Antique Nickel with Brushed Nickel accents
9" dia., 7" ht.
Extends 10". H/CTR 2-3/8".
One medium base lamp, 100w max.

All fixtures shown with vintage lamps, not included. See page 824.

Archie

FINISHES

- Polished Chrome - 15
- Antique Nickel - 81
- Venetian Bronze - 74
- Vintage Brass - 163

ALSO IN

Pendants
Close-to-Ceiling

P2992-81

A welcomed blast from the past returning to a design grounded in aesthetic authenticity. Finely crafted strap and knob details with clear double prismatic glass.



ONE-LIGHT BATH
P2989-81 Antique Nickel
5-3/4" W., 8-1/4" ht.
Extends 7". H/CTR 5-1/4".
One medium base lamp,
100w max.


TWO-LIGHT BATH
P2991-81 Antique Nickel
17" W., 8-3/4" ht.
Extends 7". H/CTR 5-1/4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P2992-81 Antique Nickel
26-1/4" W., 8-3/4" ht.
Extends 7". H/CTR 5-1/4".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P2997-81 Antique Nickel
35-1/2" W., 8-3/4" ht.
Extends 7". H/CTR 5-1/4".
Four medium base lamps,
each 100w max.



P2989-81



P2997-81



P2991-81



P2992-81

All fixtures mount up or down.


Archie



P2997-163



P2989-163



P2992-163



P2991-163




P2997-74



P2989-74



P2992-74




P2991-74



P2997-15



P2989-15



P2992-15



P2991-15

ONE-LIGHT BATH
P2989-15 Polished Chrome
P2989-74 Venetian Bronze
P2989-163 Vintage Brass
5-3/4″ W., 8-1/4″ ht.
Extends 7″. H/CTR 5-1/4″.
One medium base lamp,
100w max.

TWO-LIGHT BATH
P2991-15 Polished Chrome
P2991-74 Venetian Bronze
P2991-163 Vintage Brass
17″ W., 8-3/4″ ht.
Extends 7″. H/CTR 5-1/4″.
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P2992-15 Polished Chrome
P2992-74 Venetian Bronze
P2992-163 Vintage Brass
26-1/4″ W., 8-3/4″ ht.
Extends 7″. H/CTR 5-1/4″.
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P2997-15 Polished Chrome
P2997-74 Venetian Bronze
P2997-163 Vintage Brass
35-1/2″ W., 8-3/4″ ht.
Extends 7″. H/CTR 5-1/4″.
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

Fayette

FINISHES

- Antique Nickel - 081
- Vintage Brass - 163

P300287-163

Inspired from early electric lighting, the Fayette Collection will infuse your home with a sense of history. A simple bar attached to a backplate supports three curved arms as they bend to hold blooming, petal-like shades crafted from clear depression glass for a must-have, artistic touch.



ONE-LIGHT BATH
P300286-163 Vintage Brass
7-1/2" W., 7-1/2" ht.
Extends 9-1/2". H/CTR 3-1/2".
One medium base lamp,
60w max.



P300286-163

TWO-LIGHT BATH
P300287-163 Vintage Brass
16-1/2" W., 6-1/2" ht.
Extends 9". H/CTR 4".
Two medium base lamps,
each 60w max.




P300287-163

THREE-LIGHT BATH
P300288-163 Vintage Brass
25-1/2" W., 6-1/2" ht.
Extends 9". H/CTR 4".
Three medium base lamps,
each 60w max.



P300288-163

FOUR-LIGHT BATH
P300289-163 Vintage Brass
34-1/2" W., 6-1/2" ht.
Extends 9". H/CTR 4".
Four medium base lamps,
each 60w max.



P300289-163

Fayette



P300287-081



P300286-081



P300288-081



P300289-081

ONE-LIGHT BATH
P300286-081 Antique Nickel
7-1/2″ W., 7-1/2″ ht.
Extends 9-1/2″. H/CTR 3-1/2″.
One medium base lamp,
60w max.

TWO-LIGHT BATH
P300287-081 Antique Nickel
16-1/2″ W., 6-1/2″ ht.
Extends 9″. H/CTR 4″.
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH
P300288-081 Antique Nickel
25-1/2″ W., 6-1/2″ ht.
Extends 9″. H/CTR 4″.
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH
P300289-081 Antique Nickel
34-1/2″ W., 6-1/2″ ht.
Extends 9″. H/CTR 4″.
Four medium base lamps,
each 60w max.

All fixtures shown with F7ST19DLED927/JA8 LED lamps, not included. *See page 824.*

Saluda

FINISHES
- Brushed Nickel - 009
- Antique Bronze - 020

ALSO IN
Collections
Close-to-Ceiling

P300180-020

The Saluda Collection features a gently curving frame paired with clear glass shades. Each shade is accented with a banded ring to carry through the theme of finely crafted metal fittings. The design lends itself to Farmhouse, Coastal and Transitional spaces.



ONE-LIGHT BATH
P300178-020 Antique Bronze
5-3/4" W., 9-1/2" ht.
Extends 7-3/4". H/CTR 4-1/2".
One medium base lamp, 60w max.


P300178-020

TWO-LIGHT BATH
P300179-020 Antique Bronze
15-1/2" W., 9-1/2" ht.
Extends 7-3/4". H/CTR 5".
Two medium base lamps, each 60w max.


P300181-020

THREE-LIGHT BATH
P300180-020 Antique Bronze
24" W., 9-1/2" ht.
Extends 7-3/4". H/CTR 5".
Three medium base lamps, each 60w max.


P300179-020

FOUR-LIGHT BATH
P300181-020 Antique Bronze
32-1/2" W., 9-1/2" ht.
Extends 7-3/4". H/CTR 5".
Four medium base lamps, each 60w max.


P300180-020

All fixtures mount up or down.

Saluda



P300181-009



P300178-009



P300180-009



P300179-009

ONE-LIGHT BATH
P300178-009 Brushed Nickel
5-3/4" W., 9-1/2" ht.
Extends 7-3/4". H/CTR 4-1/2".
One medium base lamp,
60w max.

TWO-LIGHT BATH
P300179-009 Brushed Nickel
15-1/2" W., 9-1/2" ht.
Extends 7-3/4". H/CTR 5".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH
P300180-009 Brushed Nickel
24" W., 9-1/2" ht.
Extends 7-3/4". H/CTR 5".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH
P300181-009 Brushed Nickel
32-1/2" W., 9-1/2" ht.
Extends 7-3/4". H/CTR 5".
Four medium base lamps,
each 60w max.

All fixtures mount up or down.



Featuring Saluda
Image: Tresidio Homes

Hansford

FINISHES
- Antique Bronze - 020
- Polished Nickel - 104

ALSO IN
Collections
Close-to-Ceiling

P300051-020

Hansford features a clear, spherical shade with vintage style metal fittings. Choose the antique style bronze and brass combinations, or the gleaming nickel finish to bring tranquility to your home with Hansford's classic style.



ONE-LIGHT BATH
P300049-020 Antique Bronze
6-1/2" W., 9-1/2" ht.
Extends 7-1/4". H/CTR 6-7/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300050-020 Antique Bronze
15-1/2" W., 10-7/8" ht.
Extends 7-1/4". H/CTR 8-1/4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300051-020 Antique Bronze
24-1/2" W., 10-7/8" ht.
Extends 7-1/4". H/CTR 8-1/4".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300052-020 Antique Bronze
33-1/2" W., 10-7/8" ht.
Extends 7-1/4". H/CTR 8-1/4".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.
Shown with P7825-01 vintage lamps, not included. See page 824.


P300049-020


P300052-020


P300050-020


P300051-020

Hansford



P300052-104



P300049-104



P300051-104



P300050-104

ONE-LIGHT BATH
P300049-104 Polished Nickel
6-1/2" W., 9-1/2" ht.
Extends 7-1/4". H/CTR 6-7/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300050-104 Polished Nickel
15-1/2" W., 10-7/8" ht.
Extends 7-1/4". H/CTR 8-1/4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300051-104 Polished Nickel
24-1/2" W., 10-7/8" ht.
Extends 7-1/4". H/CTR 8-1/4".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300052-104 Polished Nickel
33-1/2" W., 10-7/8" ht.
Extends 7-1/4". H/CTR 8-1/4".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.



Featuring Hansford
Image: Tresidio Homes

Judson

FINISHES
- Antique Bronze - 020
- Polished Nickel - 104

ALSO IN
Collections
Close-to-Ceiling

P300082-104

The Judson collection features a timeless clear schoolhouse-style globe. Metal fittings add distinction to complete the vintage look. Available in hanging, wall and ceiling styles, Judson provides the perfect compliment to farmhouse or coastal-inspired homes.



ONE-LIGHT BATH
P300080-104 Polished Nickel
6-1/2" W., 11-1/4" ht.
Extends 8-1/2". H/CTR 6-1/4".
One medium base lamp,
75w max.

TWO-LIGHT BATH
P300081-104 Polished Nickel
16-1/4" W., 11-1/4" ht.
Extends 8-1/2". H/CTR 7-1/2".
Two medium base lamps,
each 75w max.

THREE-LIGHT BATH
P300082-104 Polished Nickel
26" W., 11-1/4" ht.
Extends 8-1/2". H/CTR 7-1/2".
Three medium base lamps,
each 75w max.

FOUR-LIGHT BATH
P300083-104 Polished Nickel
35-3/4" W., 11-1/4" ht.
Extends 8-1/2". H/CTR 7-1/2".
Four medium base lamps,
each 75w max.


P300080-104


P300083-104


P300081-104


P300082-104

All fixtures mount up or down.

Judson



P300080-020



P300081-020



P300082-020



P300083-020

ONE-LIGHT BATH
P300080-020 Antique Bronze
6-1/2" W., 11-1/4" ht.
Extends 8-1/2". H/CTR 6-1/4".
One medium base lamp,
75w max.

TWO-LIGHT BATH
P300081-020 Antique Bronze
16-1/4" W., 11-1/4" ht.
Extends 8-1/2". H/CTR 7-1/2".
Two medium base lamps,
each 75w max.

THREE-LIGHT BATH
P300082-020 Antique Bronze
26" W., 11-1/4" ht.
Extends 8-1/2". H/CTR 7-1/2".
Three medium base lamps,
each 75w max.

FOUR-LIGHT BATH
P300083-020 Antique Bronze
35-3/4" W., 11-1/4" ht.
Extends 8-1/2". H/CTR 7-1/2".
Four medium base lamps,
each 75w max.

All fixtures mount up or down.

Durrell

FINISHES
- Brushed Nickel - 009
- Matte Black - 031

ALSO IN
Collections
Close-to-Ceiling

P300263-009

The versatile Durrell Collection will find a home in any coastal, modern farmhouse, or vintage electric setting in need of generous illumination. Curved arms sweep outwards from an oval backplate, clasping clear glass shades for a lighting experience that is welcoming, sophisticated and fun.

Clear Glass Shades



Brushed Nickel *Vintage Look*

ONE-LIGHT BATH
P300261-009 Brushed Nickel
4-5/8" W., 7-7/8" ht.
Extends 6-1/4". H/CTR 4".
One medium base lamp,
60w max.

TWO-LIGHT BATH
P300262-009 Brushed Nickel
13-1/2" W., 7-7/8" ht.
Extends 6-1/4". H/CTR 5-1/4".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH
P300263-009 Brushed Nickel
22-3/8" W., 7-7/8" ht.
Extends 6-1/4". H/CTR 5-1/4".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH
P300264-009 Brushed Nickel
31-1/4" W., 7-7/8" ht.
Extends 6-1/4". H/CTR 5-1/4".
Four medium base lamps,
each 60w max.



P300261-009



P300264-009



P300262-009



P300263-009

All fixtures mount up or down.

Durrell



P300261-031



P300262-031



P300263-031



P300264-031

ONE-LIGHT BATH
P300261-031 Matte Black
4-5/8" W., 7-7/8" ht.
Extends 6-1/4". H/CTR 4".
One medium base lamp,
60w max.

TWO-LIGHT BATH
P300262-031 Matte Black
13-1/2" W., 7-7/8" ht.
Extends 6-1/4". H/CTR 5-1/4".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH
P300263-031 Matte Black
22-3/8" W., 7-7/8" ht.
Extends 6-1/4". H/CTR 5-1/4".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH
P300264-031 Matte Black
31-1/4" W., 7-7/8" ht.
Extends 6-1/4". H/CTR 5-1/4".
Four medium base lamps,
each 60w max.

All fixtures mount up or down. Shown with P7825-01 vintage lamps, not included. See page 824.

Orbitz

Enjoy this classic style when surrounded by the elegant details of the Orbitz family. Opal glass shades float on a circular frame.

FINISHES

Brushed Nickel - 09
Antique Bronze - 20

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH
P3030-09 Brushed Nickel
P3030-20 Antique Bronze
5-1/2" W., 7-1/4" ht.
Extends 6". H/CTR 5".
One medium base lamp, 100w max.

TWO-LIGHT BATH
P3057-09 Brushed Nickel
P3057-20 Antique Bronze
13" W., 7-1/4" ht.
Extends 6". H/CTR 5".
Two medium base lamps, each 100w max.

THREE-LIGHT BATH
P3058-09 Brushed Nickel
P3058-20 Antique Bronze
21-3/4" W., 7-1/4" ht.
Extends 8-1/4". H/CTR 5".
Three medium base lamps, each 100w max.

All fixtures mount up or down.



P3030-09



P3057-09



P3058-09



P3030-20



P3057-20



P3058-20

Fleet

Emulating European faucet designs, Fleet is comprised of a distinct die cast arm and cup, highlighted by etched opal glass, to complete today's spa bath environments.

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15

ONE-LIGHT BATH
P2165-09 Brushed Nickel
P2165-15 Polished Chrome
5-1/4" W., 7-1/4" ht.
Extends 6-1/2". H/CTR 4-3/4".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P2166-09 Brushed Nickel
P2166-15 Polished Chrome
14-1/8" W., 7-1/4" ht.
Extends 6-1/2". H/CTR 5".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P2167-09 Brushed Nickel
P2167-15 Polished Chrome
23" W., 7-1/4" ht.
Extends 6-1/2". H/CTR 5".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P2168-09 Brushed Nickel
P2168-15 Polished Chrome
31-3/4" W., 7-1/4" ht.
Extends 6-1/2". H/CTR 5".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.



P2166-09



P2165-09



P2167-09



P2168-09



P2166-15



P2165-15



P2167-15



P2168-15

Appeal

Distinctive forms highlight soft modern accents. Etched soft square shades balance nicely with the fixture's full backplate and simple square arms. Contributes to a desired spa-like effect.

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

ALSO IN

Close-to-Ceiling

ONE-LIGHT BATH
P2700-09 Brushed Nickel
P2700-15 Polished Chrome
P2700-20 Antique Bronze
5-5/8" W., 6-1/4" ht.
Extends 7-1/4". H/CTR 3-1/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P2701-09 Brushed Nickel
P2701-15 Polished Chrome
P2701-20 Antique Bronze
14-5/8" W., 6-1/4" ht.
Extends 7-1/4". H/CTR 3-1/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P2702-09 Brushed Nickel
P2702-15 Polished Chrome
P2702-20 Antique Bronze
24" W., 6-1/4" ht.
Extends 7-1/4". H/CTR 3-1/8".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P2703-09 Brushed Nickel
P2703-15 Polished Chrome
P2703-20 Antique Bronze
33-1/2" W., 6-1/4" ht.
Extends 7-1/4". H/CTR 3-1/8".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.



P2700-09



P2703-09



P2701-09



P2702-09



P2700-15



P2703-15



P2701-15



P2702-15



P2700-20



P2703-20



P2701-20



P2702-20

Clifton Heights

Distinctive chiseled features and clean lines are key features within the Clifton Heights collection. Inspired by an updated interpretation of handsome Craftsman styling, careful attention to the details and elegant etched glass shades deliver a dramatic accent to any room. The Clifton Heights collection enhances a variety of home styles including Farmhouse, Craftsman and Transitional décor.



P300161-009



P300158-009



P300160-009



P300159-009



P300161-020



P300158-020



P300160-020



P300159-020

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ALSO IN

Collections
Close-to-Ceiling
Ceiling Fans

ONE-LIGHT BATH
P300158-009 Brushed Nickel
P300158-020 Antique Bronze
5-1/2" W., 8-3/8" ht.
Extends 7-1/8". H/CTR 4-5/8".
One medium base lamp,
each 100w max.

TWO-LIGHT BATH
P300159-009 Brushed Nickel
P300159-020 Antique Bronze
14-1/4" W., 8-3/8" ht.
Extends 7-1/8". H/CTR 5-3/4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300160-009 Brushed Nickel
P300160-020 Antique Bronze
23" W., 8-3/8" ht.
Extends 7-1/8". H/CTR 5-3/4".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300161-009 Brushed Nickel
P300161-020 Antique Bronze
31-7/8" W., 8-3/8" ht.
Extends 7-1/8". H/CTR 5-3/4".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

Cascadia

Overscale frames and etched glass shades offer substance in a sleek frame.

FINISHES

- Polished Chrome - 15
- Antique Bronze - 20

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH
P2146-15 Polished Chrome
P2146-20 Antique Bronze
5-7/8" W., 8" ht.
Extends 6-1/2". H/CTR 5-1/2".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P2147-15 Polished Chrome
P2147-20 Antique Bronze
16" W., 8" ht.
Extends 6-1/2". H/CTR 5-5/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P2148-15 Polished Chrome
P2148-20 Antique Bronze
24-1/8" W., 8" ht.
Extends 6-1/2". H/CTR 5-5/8".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P2149-15 Polished Chrome
P2149-20 Antique Bronze
32" W., 8" ht.
Extends 6-1/2". H/CTR 5-5/8".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.



P2146-15



P2147-15



P2148-15



P2149-15



P2146-20



P2147-20



P2148-20



P2149-20

Topsail

Topsail features a graceful curving frame paired with elegant parchment-finish glass shades to create a clean, modern form. Classic metal fittings enhance the crisp appearance of a brilliant Polished Chrome or warm Antique Bronze finish. This collection provides the perfect complement to coastal-inspired or casual décor.



P300058-015



P300057-015



P300059-015



P300060-015



P300058-020



P300057-020



P300059-020



P300060-020

FINISHES

- Polished Chrome - 015
- Antique Bronze - 020

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH
P300057-015 Polished Chrome
P300057-020 Antique Bronze
5-1/4" W., 7" ht.
Extends 7-1/4". H/CTR 3-1/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300058-015 Polished Chrome
P300058-020 Antique Bronze
14" W., 7" ht.
Extends 7-1/4". H/CTR 3-1/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300059-015 Polished Chrome
P300059-020 Antique Bronze
24" W., 7" ht.
Extends 7-1/4". H/CTR 3-1/8".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300060-015 Polished Chrome
P300060-020 Antique Bronze
33-1/2" W., 7" ht.
Extends 7-1/4". H/CTR 3-1/8".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

Carisa

Inspired by the revival of mid-century fashions, the Carisa collection brings home this classic style. A metallic finish supports glossy white glass globes to create a timeless modern design.

FINISHES

- Brushed Nickel - 009
- Vintage Gold - 078

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH
P300084-009 Brushed Nickel
P300084-078 Vintage Gold
6-1/2″ W., 10″ ht.
Extends 8-1/2″. H/CTR 4-5/8″.
One medium base lamp,
75w max.

TWO-LIGHT BATH
P300085-009 Brushed Nickel
P300085-078 Vintage Gold
15-1/4″ W., 10″ ht. , wire 6.
Extends 8″. H/CTR 6″.
Two medium base lamps,
each 75w max.

THREE-LIGHT BATH
P300086-009 Brushed Nickel
P300086-078 Vintage Gold
25″ W., 10″ ht.
Extends 8″. H/CTR 6″.
Three medium base lamps,
each 75w max.

FOUR-LIGHT BATH
P300087-009 Brushed Nickel
P300087-078 Vintage Gold
32-3/4″ W., 10″ ht.
Extends 8″. H/CTR 6″.
Four medium base lamps,
each 75w max.

All fixtures mount up or down.



P300084-009



P300085-009



P300086-009



P300087-009



P300084-078



P300085-078



P300086-078



P300087-078

Torino

Elegant rectangular scrolled arms with casual undertones. Forged Bronze finish with tea stained glass or Brushed Nickel finish with etched glass.



P2882-09



P2881-09



P2883-09



P2884-09



P2882-77



P2881-77



P2883-77



P2884-77

FINISHES

- Brushed Nickel - 09
- Forged Bronze - 77

ALSO IN

Collections
Close-to-Ceiling
Sconces

ONE-LIGHT BATH
P2881-09 Brushed Nickel
P2881-77 Forged Bronze
7" W., 8-1/4" ht.
Extends 9-1/4". H/CTR 4-5/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P2882-09 Brushed Nickel
P2882-77 Forged Bronze
16" W., 7-5/8" ht.
Extends 9-1/4". H/CTR 3-3/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P2883-09 Brushed Nickel
P2883-77 Forged Bronze
25" W., 7-5/8" ht.
Extends 9-1/4". H/CTR 3-3/8".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P2884-09 Brushed Nickel
P2884-77 Forged Bronze
34" W., 7-5/8" ht.
Extends 9-1/4". H/CTR 3-3/8".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

Applause

Applause is comprised of etched natural parchment glass paired with a classic iron form with Antique Bronze finish and etched parchment glass with Brushed Nickel finish.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH
P2095-09 Brushed Nickel
P2095-20 Antique Bronze
7" W., 9-1/8" ht.
Extends 7-7/8". H/CTR 5-3/4".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P2096-09 Brushed Nickel
P2096-20 Antique Bronze
16-1/4" W., 8-1/2" ht.
Extends 9". H/CTR 6".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P2097-09 Brushed Nickel
P2097-20 Antique Bronze
24" W., 8-1/2" ht.
Extends 9". H/CTR 6".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P2105-09 Brushed Nickel
P2105-20 Antique Bronze
34" W., 8-1/2" ht.
Extends 9".H/CTR 6".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.



P2095-09



P2096-09



P2097-09



P2105-09



P2095-20



P2096-20



P2097-20



P2105-20

Arden

Arden features updated farmhouse styling to complement casual home styles.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

Collections
Close-to-Ceiling



P2128-09



P2127-09



P2129-09

ONE-LIGHT BATH
P2127-09 Brushed Nickel
P2127-20 Antique Bronze
5-7/8" W., 8" ht.
Extends 8-1/4". H/CTR 4".
One medium base lamp, 100w max.



P2130-09

TWO-LIGHT BATH
P2128-09 Brushed Nickel
P2128-20 Antique Bronze
16-1/2" W., 7-1/2" ht.
Extends 8-1/8". H/CTR 4-5/8".
Two medium base lamps, each 100w max.



P2128-20



P2127-20

THREE-LIGHT BATH
P2129-09 Brushed Nickel
P2129-20 Antique Bronze
24-1/2" W., 7-1/2" ht.
Extends 8-1/4". H/CTR 4-5/8".
Three medium base lamps, each 100w max.



P2129-20

FOUR-LIGHT BATH
P2130-09 Brushed Nickel
P2130-20 Antique Bronze
34" W., 7-1/2" ht.
Extends 8-1/4". H/CTR 4-5/8".
Four medium base lamps, each 100w max.



P2130-20

All fixtures mount up or down.

Leap

Leap vanity fixtures feature tapered etched glass shades to complement contemporary design trends.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH
P300131-009 Brushed Nickel
P300131-020 Antique Bronze
5" W., 8-1/8" ht.
Extends 6-1/8". H/CTR 4-1/4".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300132-009 Brushed Nickel
P300132-020 Antique Bronze
13-7/8" W., 8-3/8" ht.
Extends 6-1/8". H/CTR 6".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300133-009 Brushed Nickel
P300133-020 Antique Bronze
22-7/8" W., 8-3/8" ht.
Extends 6-1/8". H/CTR 6".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300134-009 Brushed Nickel
P300134-020 Antique Bronze
31-3/4" W., 8-3/8" ht.
Extends 6-1/8". H/CTR 6".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.



P300131-009



P300132-009



P300133-009



P300134-009



P300131-020



P300132-020



P300133-020



P300134-020

Tobin

A modern take on a classic form. Tobin's tubular arms extend outward and are made to form a gentle curve that showcase etched white glass shades. The Tobin collection is ideal for those who appreciate Modern design styles.

FINISHES

- Brushed Nickel - 009
- Matte Black - 031

ALSO IN

Collections
Close-to-Ceiling



P300219-009



P300222-009



P300220-009



P300221-009

ONE-LIGHT BATH
P300222-009 Brushed Nickel
P300222-031 Matte Black
5" W., 15-1/2" ht.
Extends 5-7/8". H/CTR 11".
One medium base lamp, 100w max.

TWO-LIGHT BATH
P300219-009 Brushed Nickel
P300219-031 Matte Black
15-1/4" W., 7-7/8" ht.
Extends 7-5/8". H/CTR 5-5/8".
Two medium base lamps, each 100w max.

THREE-LIGHT BATH
P300220-009 Brushed Nickel
P300220-031 Matte Black
25-1/2" W., 7-7/8" ht.
Extends 7-5/8". H/CTR 5-5/8".
Three medium base lamps, each 100w max.

FOUR-LIGHT BATH
P300221-009 Brushed Nickel
P300221-031 Matte Black
35-3/4" W., 7-7/8" ht.
Extends 7-5/8". H/CTR 5-5/8".
Four medium base lamps, each 100w max.

All fixtures mount up or down.



P300219-031



P300222-031



P300220-031



P300221-031

Alexa

Featuring a transitional design style, this collection offers the best of traditional and modern details. Etched linen and clear glass with Brushed Nickel finish. Umber etched linen and clear glass with Antique Bronze finish.

FINISHES

Brushed Nickel - 09
Antique Bronze - 20

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH
P2959-09 Brushed Nickel
P2959-20 Antique Bronze
4-1/2" W., 9-3/8" ht.
Extends 6-1/8". H/CTR 5-7/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P2977-09 Brushed Nickel
P2977-20 Antique Bronze
13" W., 9-1/2" ht.
Extends 6-1/8". H/CTR 7-1/4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P2978-09 Brushed Nickel
P2978-20 Antique Bronze
22" W., 9-1/2" ht.
Extends 6-1/8". H/CTR 7-1/4".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P2998-09 Brushed Nickel
P2998-20 Antique Bronze
31" W., 9-1/2" ht.
Extends 6-1/8". H/CTR 7-1/4".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.




P2959-09



P2977-09



P2978-09



P2998-09



P2959-20



P2977-20



P2978-20



P2998-20

Bravo

A current, truly transitional style is achieved with Bravo's free flowing arms that are gracefully suspended with fluted shaped glass. The popular Bravo collection comes with etched linen glass.



P2007-09



P2004-09



P2005-09



P2006-09



P2016-09



P2007-20W



P2004-20W



P2005-20W



P2006-20W



P2016-20W

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH
P2004-09 Brushed Nickel
P2004-20W Antique Bronze
7-1/4" W., 9" ht.
Extends 8-3/4". H/CTR 4-1/2".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P2005-09 Brushed Nickel
P2005-20W Antique Bronze
17" W., 8-1/2" ht.
Extends 8-3/4". H/CTR 6".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P2006-09 Brushed Nickel
P2006-20W Antique Bronze
26-3/4" W., 8-3/4" ht.
Extends 8-3/4". H/CTR 6".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P2007-09 Brushed Nickel
P2007-20W Antique Bronze
37-1/4" W., 8-3/4" ht.
Extends 8-3/4". H/CTR 6".
Four medium base lamps,
each 100w max.

FIVE-LIGHT BATH
P2016-09 Brushed Nickel
P2016-20W Antique Bronze
46-1/4" W., 8-7/8" ht.
Extends 8-3/4". H/CTR 6-3/8".
Five medium base lamps,
each 100w max.

All fixtures mount up or down.

Wisten

Simple, modern and elegant, the Wisten family features a sculptured linear look. Etched glass for soft contemporary feel.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH
P2794-09 Brushed Nickel
P2794-20 Antique Bronze
4-1/2" W., 8-1/4" ht.
Extends 6-1/4". H/CTR 3-7/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P2795-09 Brushed Nickel
P2795-20 Antique Bronze
12-1/2" W., 8-1/4" ht.
Extends 6-1/4". H/CTR 5-1/2".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P2796-09 Brushed Nickel
P2796-20 Antique Bronze
21" W., 8-1/4" ht.
Extends 6-1/4". H/CTR 5-1/2".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P2797-09 Brushed Nickel
P2797-20 Antique Bronze
29-1/2" W., 8-1/4" ht.
Extends 6-1/4". H/CTR 6".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.



P2794-09



P2795-09



P2796-09



P2797-09



P2794-20



P2795-20



P2796-20



P2797-20

Invite

Dual-layer etched glass and mylar drum shades on a linear frame offer a modern style.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH
P2041-20 Antique Bronze
P2041-09 Brushed Nickel
6-1/2" W., 11-1/2" ht.
Extends 8-1/4". H/CTR 3-3/4".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P2078-20 Antique Bronze
P2078-09 Brushed Nickel
14-1/2" W., 7-3/8" ht.
Extends 7-1/2". H/CTR 4-7/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P2079-20 Antique Bronze
P2079-09 Brushed Nickel
23-1/2" W., 7-3/8" ht.
Extends 7-1/2". H/CTR 4-7/8".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P2080-20 Antique Bronze
P2080-09 Brushed Nickel
32-1/2" W., 7-3/8" ht.
Extends 7-1/2". H/CTR 4-7/8".
Four medium base lamps,
each 100w max.

FIVE-LIGHT BATH
P2081-20 Antique Bronze
P2081-09 Brushed Nickel
41-1/2" W., 7-3/8" ht.
Extends 7-1/2". H/CTR 4-7/8".
Five medium base lamps,
each 100w max.



P2080-09



P2041-09



P2078-09



P2079-09



P2081-09



P2080-20



P2041-20



P2078-20



P2079-20



P2081-20

Avalon

Soft curves and sophisticated detailing with Alabaster style glass and twisted rope details to complement a variety of bath areas.

FINISH

Brushed Nickel - 09

ALSO IN

Pendants

ONE-LIGHT BATH
P3266-09 Brushed Nickel
7-3/4" W., 12" ht.
Extends 8-3/4".H/CTR 6".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P3267-09 Brushed Nickel
18" W., 7" ht.
Extends 8-3/4". H/CTR 4-3/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P3268-09 Brushed Nickel
24" W., 7" ht.
Extends 8-3/4".H/CTR 4-3/8".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P3269-09 Brushed Nickel
36" W., 7" ht.
Extends 8-3/4".H/CTR 4-3/8".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.



P3266-09



P3267-09



P3268-09



P3269-09

Victorian

White opal glass shades are supported by finely crafted bars attached to refined, oval backplates.

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Venetian Bronze - 74

ONE-LIGHT BATH
P3027-09 Brushed Nickel
P3027-15 Polished Chrome
P3027-74 Venetian Bronze
5-5/8" W., 8-1/2" ht.
Extends 7-1/4". H/CTR 4".
One medium base lamp, 100w max.

TWO-LIGHT BATH
P3028-09 Brushed Nickel
P3028-15 Polished Chrome
P3028-74 Venetian Bronze
16-1/2" W., 8-1/2" ht.
Extends 7-1/4". H/CTR 4".
Two medium base lamps, each 100w max.

THREE-LIGHT BATH
P3029-09 Brushed Nickel
P3029-15 Polished Chrome
P3029-74 Venetian Bronze
24-1/2" W., 8-1/2" ht.
Extends 7-1/4". H/CTR 4".
Three medium base lamps, each 100w max.

FOUR-LIGHT BATH
P3041-09 Brushed Nickel
P3041-15 Polished Chrome
P3041-74 Venetian Bronze
32-1/2" W., 8-1/2" ht.
Extends 7-1/4". H/CTR 4".
Four medium base lamps, each 100w max.

All fixtures mount up or down.



P3041-09



P3027-09



P3028-09



P3029-09



P3041-15



P3027-15



P3028-15



P3029-15



P3041-74



P3027-74



P3028-74



P3029-74

Trinity

Soft angles and curved lines in the Trinity collection are ideal for today's understated interiors. Etched glass shades curve outward.

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH
P3190-09 Brushed Nickel
P3190-15 Polished Chrome
P3190-20 Antique Bronze
6-1/2" W., 7-1/2" ht.
Extends 9". H/CTR 3-1/2".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P3191-09 Brushed Nickel
P3191-15 Polished Chrome
P3191-20 Antique Bronze
17-1/2" W., 8-1/8" ht.
Extends 7-3/8". H/CTR 5-7/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P3192-09 Brushed Nickel
P3192-15 Polished Chrome
P3192-20 Antique Bronze
24" W., 8-1/8" ht.
Extends 7-3/8". H/CTR 5-7/8".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P3193-09 Brushed Nickel
P3193-15 Polished Chrome
P3193-20 Antique Bronze
33-1/4" W., 8-1/8" ht.
Extends 7-3/8". H/CTR 5-7/8".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.



P3190-15



P3193-15



P3191-15



P3192-15



P3190-09



P3193-09



P3191-09



P3192-09



P3190-20



P3193-20



P3191-20



P3192-20

Madison

Authentic and handsome details represent a throwback to a simpler time. Etched glass shade offers classic styling.

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

ALSO IN

Collections
Close-to-Ceiling



P3164-09



P3161-09



P3162-09



P3163-09

ONE-LIGHT BATH
P3161-09 Brushed Nickel
P3161-15 Polished Chrome
P3161-20 Antique Bronze
7-5/8" W., 8" ht.
Extends 9-1/4". H/CTR 5"
One medium base lamp, 100w max.



P3164-20



P3161-20

TWO-LIGHT BATH
P3162-09 Brushed Nickel
P3162-15 Polished Chrome
P3162-20 Antique Bronze
17-1/2" W., 8" ht.
Extends 8-3/4". H/CTR 4-7/8"
Two medium base lamps, each 100w max.



P3162-20



P3163-20

THREE-LIGHT BATH
P3163-09 Brushed Nickel
P3163-15 Polished Chrome
P3163-20 Antique Bronze
27-1/2" W., 8" ht.
Extends 8-3/4". H/CTR 4-7/8"
Three medium base lamps, each 100w max.



P3164-15



P3161-15

FOUR-LIGHT BATH
P3164-09 Brushed Nickel
P3164-15 Polished Chrome
P3164-20 Antique Bronze
37-1/2" W., 8" ht.
Extends 9-3/4". H/CTR 4-7/8"
Four medium base lamps, each 100w max.

All fixtures mount up or down.



P3162-15



P3163-15



Featuring Inspire

Bring the Outdoors In

A bathroom becomes a personal refuge from everyday living when organic touches of wood and stone are incorporated to offset sleek style. Tile the shower floor with pebbled flooring and add an authentic Zen style with a floating wooden vanity. The Inspire vanity light freshens traditional forms with sleek flowing lines.

Inspire

Updated traditional inspiration with gracious, flowing oval arms and etched glass shades.

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH
P2018-09 Brushed Nickel
P2018-15 Polished Chrome
P2018-20 Antique Bronze
4-5/8" W., 7-1/2" ht.
Extends 7-3/8". H/CTR 3-3/4".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P2019-09 Brushed Nickel
P2019-15 Polished Chrome
P2019-20 Antique Bronze
15" W., 8-1/2" ht.
Extends 6-7/8". H/CTR 6-1/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P2020-09 Brushed Nickel
P2020-15 Polished Chrome
P2020-20 Antique Bronze
22-3/8" W., 8-1/4" ht.
Extends 6-7/8". H/CTR 5-1/2".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P2021-09 Brushed Nickel
P2021-15 Polished Chrome
P2021-20 Antique Bronze
31-3/8" W., 8-1/2" ht.
Extends 6-7/8". H/CTR 6-1/8".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.



P2021-09



P2018-09



P2019-09



P2020-09



P2021-15



P2018-15



P2019-15



P2020-15



P2021-20



P2018-20



P2019-20



P2020-20

Replay

Highlighted by simple forms, linear details and etched opal glass. A pleasingly elegant frame enhances a simplified modern look within the Replay collection.

FINISHES

Brushed Nickel - 09
Black - 31

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH
P2131-09 Brushed Nickel
P2131-31 Black
5-1/8" W., 9-3/4" ht.
Extends 5-7/8". H/CTR 7-1/4".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P2158-09 Brushed Nickel
P2158-31 Black
13" W., 7-7/8" ht.
Extends 6". H/CTR 5-1/4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P2159-09 Brushed Nickel
P2159-31 Black
22" W., 7-7/8" ht.
Extends 6". H/CTR 5-1/4".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P2160-09 Brushed Nickel
P2160-31 Black
31-1/8" W., 7-7/8" ht.
Extends 6". H/CTR 5-1/4".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.


P2131-09


P2158-09


P2159-09


P2160-09


P2131-31


P2158-31


P2159-31


P2160-31



Replay

FINISHES

- Antique Bronze - 20
- Polished Nickel - 104

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH
P2131-20 Antique Bronze
P2131-104 Polished Nickel
5-1/8" W., 9-3/4" ht.
Extends 5-7/8". H/CTR 7-1/4".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P2158-20 Antique Bronze
P2158-104 Polished Nickel
13" W., 7-7/8" ht.
Extends 6". H/CTR 5-1/4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P2159-20 Antique Bronze
P2159-104 Polished Nickel
22" W., 7-7/8" ht.
Extends 6". H/CTR 5-1/4".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P2160-20 Antique Bronze
P2160-104 Polished Nickel
31-1/8" W., 7-7/8" ht.
Extends 6". H/CTR 5-1/4".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.



P2131-104



P2158-104



P2159-104



P2160-104



P2131-20



P2158-20



P2159-20



P2160-20

Riley

Smooth metal arms extend from an oval backplate to hold simple light bases topped with elegant, elongated clear glass shades.

FINISHES

- Brushed Nickel - 009
- Black - 031

ALSO IN

Collections

TWO-LIGHT BATH
P300277-009 Brushed Nickel
P300277-031 Black
16-1/8" W., 8-1/4" ht.
Extends 5-1/2". H/CTR 5-3/4".
Two medium base lamps, each 60w max.

THREE-LIGHT BATH
P300278-009 Brushed Nickel
P300278-031 Black
25-1/4" W., 8-1/4" ht.
Extends 5-1/2". H/CTR 5-3/4".
Three medium base lamps, each 60w max.

FOUR-LIGHT BATH
P300279-009 Brushed Nickel
P300279-031 Black
34-3/8" W., 8-1/4" ht.
Extends 5-1/2". H/CTR 5-3/4".
Four medium base lamps, each 60w max.

WALL BRACKET
P710082-009 Brushed Nickel
P710082-031 Black
5" W., 14-1/2" ht.
Extends 4-5/8". H/CTR 7-3/4".
One candelabra base lamp, 60w max.

All fixtures mount up or down, except P710082.

Shown with P7825-01 vintage lamps, not included. See page 824.



P300277-009



P710082-009



P300278-009



P300279-009



P300277-031



P710082-031



P300278-0031



P300279-031

Adorn

Created to easily coordinate with many popular faucet styles, Adorn features fluted etched glass shades on a curving frame.

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

ONE-LIGHT BATH
P2008-09 Brushed Nickel
P2008-15 Polished Chrome
P2008-20W Antique Bronze
5-1/4" W., 6-3/4" ht.
Extends 7". H/CTR 3-3/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P2009-09 Brushed Nickel
P2009-15 Polished Chrome
P2009-20W Antique Bronze
13-1/4" W., 6-5/8" ht.
Extends 6-1/4". H/CTR 4-3/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P2010-09 Brushed Nickel
P2010-15 Polished Chrome
P2010-20W Antique Bronze
21-1/2" W., 6-5/8" ht.
Extends 7-1/2". H/CTR 4-3/8".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P2011-09 Brushed Nickel
P2011-15 Polished Chrome
P2011-20W Antique Bronze
28-1/4" W., 6-5/8" ht.
Extends 7-1/2". H/CTR 4-3/8".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.



P2008-09



P2011-09



P2009-09



P2010-09



P2008-15



P2011-15



P2009-15



P2010-15



P2008-20W



P2011-20W



P2009-20W



P2010-20W

Joy

With sophisticated design styling, Joy features voluminous curves for a soft and stylish profile. Joy is available with etched white glass shades.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20W

ALSO IN

Collections
Close-to-Ceiling



P2001-09



P2000-09



P2002-09



P2003-09

ONE-LIGHT BATH
P2000-09 Brushed Nickel
P2000-20W Antique Bronze
6″ W., 9-1/2″ ht.
Extends 7″. H/CTR 6″.
One medium base lamp, 100w max.

TWO-LIGHT BATH
P2001-09 Brushed Nickel
P2001-20W Antique Bronze
14″ W., 7-5/8″ ht.
Extends 8-1/8″. H/CTR 4-1/8″.
Two medium base lamps, each 100w max.

THREE-LIGHT BATH
P2002-09 Brushed Nickel
P2002-20W Antique Bronze
22″ W., 7-5/8″ ht.
Extends 8-1/8″. H/CTR 4-1/8″.
Three medium base lamps, each 100w max.

FOUR-LIGHT BATH
P2003-09 Brushed Nickel
P2003-20W Antique Bronze
30″ W., 7-5/8″ ht.
Extends 8-1/8″. H/CTR 4-1/8″.
Four medium base lamps, each 100w max.

All fixtures mount up or down.



P2001-20W



P2000-20W



P2002-20W



P2003-20W

Laird

The Laird collection provides a contemporary complement to casual interiors popular in today's homes. Glass shades add distinction and provide pleasing illumination to any room, while scrolling arms create an airy effect.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH
P300095-009 Brushed Nickel
P300095-020 Antique Bronze
5-3/4" W., 9" ht.
Extends 8". H/CTR 3-5/8".
One medium base lamp,
each 100w max.

TWO-LIGHT BATH
P300096-009 Brushed Nickel
P300096-020 Antique Bronze
14-3/4" W., 8" ht.
Extends 7-1/4". H/CTR 5-3/4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300097-009 Brushed Nickel
P300097-020 Antique Bronze
23-3/4" W., 8" ht.
Extends 7-1/4". H/CTR 5-3/4".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300098-009 Brushed Nickel
P300098-020 Antique Bronze
33" W., 8-1/4" ht.
Extends 7-1/4". H/CTR 5-7/8".
Four medium base lamps,
each 100w max.

FIVE-LIGHT BATH
P300099-009 Brushed Nickel
P300099-020 Antique Bronze
41-5/8" W., 8" ht.
Extends 7-1/4". H/CTR 5-3/4".
Five medium base lamps,
each 100w max.

All fixtures mount up or down.



P300095-009



P300098-009



P300096-009



P300097-009



P300099-009



P300095-020



P300098-020



P300096-020



P300097-020



P300099-020

Heart

Heart will bring romance to the vanity, with flowing arms that gently cradle etched glass bowls.

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

ALSO IN

Collections



P2928-09



P2913-09



P2915-09



P2919-09

ONE-LIGHT BATH
P2913-09 Brushed Nickel
P2913-15 Polished Chrome
P2913-20 Antique Bronze
6" W., 9-1/16" ht.
Extends 8". H/CTR 4-1/2".
One medium base lamp, 100w max.



P2928-15



P2913-15

TWO-LIGHT BATH
P2915-09 Brushed Nickel
P2915-15 Polished Chrome
P2915-20 Antique Bronze
14" W., 8-3/8" ht.
Extends 8". H/CTR 2-1/2".
Two medium base lamps, each 100w max.



P2915-15



P2919-15

THREE-LIGHT BATH
P2919-09 Brushed Nickel
P2919-15 Polished Chrome
P2919-20 Antique Bronze
22" W., 8-1/2" ht.
Extends 8". H/CTR 2-1/2".
Three medium base lamps, each 100w max.



P2928-20



P2913-20

FOUR-LIGHT BATH
P2928-09 Brushed Nickel
P2928-15 Polished Chrome
P2928-20 Antique Bronze
29-7/8" W., 8-1/2" ht.
Extends 8". H/CTR 2-1/2".
Four medium base lamps, each 100w max.

All fixtures mount up or down.



P2915-20



P2919-20

Classic

Traditional details and graceful lines add modern elegance to any interior. Classic vanities feature etched glass shades.

FINISHES

- Brushed Nickel - 009
- Matte Black - 031

ALSO IN

Collections

ONE-LIGHT BATH
P300233-009 Brushed Nickel
5" W., 8" ht.,
Extends 7". H/CTR 3".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300234-009 Brushed Nickel
13" W., 7-7/8" ht.,
Extends 7". H/CTR 3".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300235-009 Brushed Nickel
24" W., 7-7/8" ht.,
Extends 7". H/CTR 3".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300236-009 Brushed Nickel
30" W., 7-7/8" ht.,
Extends 7". H/CTR 3".
Four medium base lamps,
each 100w max.

FIVE-LIGHT BATH
P300237-009 Brushed Nickel
36" W., 7-7/8" ht.,
Extends 7". H/CTR 3".
Five medium base lamps,
each 100w max.

SIX-LIGHT BATH
P300238-009 Brushed Nickel
48" W., 7-7/8" ht.,
Extends 7". H/CTR 3".
Six medium base lamps,
each 100w max.

All fixtures mount up or down.



P300233-009



P300234-009



P300235-009



P300236-009



P300237-009



P300238-009

Classic



P300234-031



P300233-031



P300235-031



P300236-031



P300237-031



P300238-031

ONE-LIGHT BATH
P300233-031 Matte Black
5" W., 8" ht.,
Extends 7". H/CTR 3".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P300234-031 Matte Black
13" W., 7-7/8" ht.,
Extends 7". H/CTR 3".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P300235-031 Matte Black
24" W., 7-7/8" ht.,
Extends 7". H/CTR 3".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P300236-031 Matte Black
30" W., 7-7/8" ht.,
Extends 7". H/CTR 3".
Four medium base lamps,
each 100w max.

FIVE-LIGHT BATH
P300237-031 Matte Black
36" W., 7-7/8" ht.,
Extends 7". H/CTR 3".
Five medium base lamps,
each 100w max.

SIX-LIGHT BATH
P300238-031 Matte Black
48" W., 7-7/8" ht.,
Extends 7". H/CTR 3".
Six medium base lamps,
each 100w max.

All fixtures mount up or down.

Gather

Simplified frame with updated styling and elegant etched glass shades.

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

ALSO IN

Collections

ONE-LIGHT BATH
P2706-09 Brushed Nickel
P2706-15 Polished Chrome
P2706-20 Antique Bronze
5" W., 7-1/2" ht.
Extends 6-1/2". H/CTR 2-5/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P2707-09 Brushed Nickel
P2707-15 Polished Chrome
P2707-20 Antique Bronze
12" W., 7-1/2" ht.
Extends 6-1/2". H/CTR 2-1/2".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P2708-09 Brushed Nickel
P2708-15 Polished Chrome
P2708-20 Antique Bronze
24" W., 7-1/2" ht.
Extends 6-1/2". H/CTR 2-1/2".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH
P2709-09 Brushed Nickel
P2709-15 Polished Chrome
P2709-20 Antique Bronze
30" W., 7-1/2" ht.
Extends 6-1/2". H/CTR 2-1/2".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.


P2706-09


P2709-09


P2707-09


P2708-09


P2706-15


P2709-15


P2707-15


P2708-15


P2706-20


P2709-20


P2707-20


P2708-20

Gather



P2713-09



P2714-09



P2713-15



P2714-15



P2713-20



P2714-20

FIVE-LIGHT BATH
P2713-09 Brushed Nickel
P2713-15 Polished Chrome
P2713-20 Antique Bronze
36" W., 7-1/2" ht.
Extends 6-1/2". H/CTR 2-1/2".
Five medium base lamps,
each 100w max.

SIX-LIGHT BATH
P2714-09 Brushed Nickel
P2714-15 Polished Chrome
P2714-20 Antique Bronze
48" W., 7-1/2" ht.
Extends 6-1/2". H/CTR 2-1/2".
Six medium base lamps,
each 100w max.

All fixtures mount up or down.

Alabaster Glass

Etched alabaster glass with soft curves. Brushed Nickel finish complements stepped backplates.

FINISH

Brushed Nickel - 09

ONE-LIGHT BATH
P3051-09 Brushed Nickel
5-1/4" W., 9" ht.
Extends 7-1/4". H/CTR 3".
One medium base lamp, 100w max.

TWO-LIGHT BATH
P3052-09 Brushed Nickel
18" W., 7-1/4" ht.
Extends 7-1/4". H/CTR 3".
Two medium base lamps, each 100w max.

THREE-LIGHT BATH
P3053-09 Brushed Nickel
24" W., 7-1/4" ht.
Extends 7-1/4". H/CTR 3".
Three medium base lamps, each 100w max.

FOUR-LIGHT BATH
P3054-09 Brushed Nickel
30" W., 7-1/4" ht.
Extends 7-1/4". H/CTR 3".
Four medium base lamps, each 100w max.

FIVE-LIGHT BATH
P3055-09 Brushed Nickel
36" W., 7-1/4" ht.
Extends 7-1/4". H/CTR 3".
Five medium base lamps, each 100w max.

SIX-LIGHT BATH
P3056-09 Brushed Nickel
48" W., 7-1/4" ht.
Extends 7-1/4". H/CTR 3".
Six medium base lamps, each 100w max.

All fixtures mount up or down.



P3051-09



P3052-09



P3053-09



P3054-09



P3055-09



P3056-09

Bedford

Brushed Nickel finish highlights curved double arms and etched alabaster glass.

FINISH

Brushed Nickel - 09

ALSO IN

Collections



P3368-09

TWO-LIGHT BATH
P3368-09 Brushed Nickel
14-3/8" W., 8-3/8" ht.
Extends 6-1/4". H/CTR 3-1/8".
Two medium base lamps,
each 100w max.



P3369-09

THREE-LIGHT BATH
P3369-09 Brushed Nickel
16-1/4" W., 8-1/4" ht.
Extends 9-1/2". H/CTR 3-1/8".
Three medium base lamps,
each 100w max.

Channel Glass

White bath glass fixture with curved edges.

FINISH

White - 30



P3813-30

ONE-LIGHT BATH
P3813-30 White Glass
Rotary switch on socket.
4-3/4" W., 7-1/2" ht.
Extends 4".
One medium base lamp,
100w max.



P3111-30

TWO-LIGHT BATH
P3111-30 White Glass
K.O. for switch and G.C.O.
14" W., 4-1/2" ht.
Extends 4-1/2".
Two medium base lamps,
each 75w max.



P3110-30

FOUR-LIGHT BATH
P3110-30 White Glass
K.O. for switch and G.C.O.
24" W., 4-1/4" ht.
Extends 4-3/4".
Four medium base lamps,
each 75w max.

ADA

Clear Fluted Glass

Ribbed detailing offers a subtle texture for the clear fluted glass.

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

ONE-LIGHT BATH
P3287-09 Brushed Nickel
P3287-15 Polished Chrome
P3287-20 Antique Bronze
5-1/4" W., 8-1/4" ht.
Extends 8". H/CTR 3-3/4".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P3288-09 Brushed Nickel
P3288-15 Polished Chrome
P3288-20 Antique Bronze
11-3/4" W., 8-1/4" ht.
Extends 8-1/4". H/CTR 2-3/4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P3289-09 Brushed Nickel
P3289-15 Polished Chrome
P3289-20 Antique Bronze
16" W., 8-1/2" ht.
Extends 8-1/2". H/CTR 2-5/8".
Three medium base lamps,
each 100w max.

All fixtures mount up or down.



P3287-09



P3288-09



P3289-09



P3287-15



P3288-15



P3289-15



P3287-20



P3288-20



P3289-20

Etched Fluted Glass

Fluted glass bath fixture featuring etched glass shades that are nestled in a decorative ring extended by curving arms. Timeless in its classic appeal, this light is stylish for both new and restored homes.

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

ONE-LIGHT BATH
P3287-09ET Brushed Nickel
P3287-15ET Polished Chrome
P3287-20ET Antique Bronze
5-1/4" W., 8-1/4" ht.
Extends 8". H/CTR 3-3/4".
One medium base lamp,
100w max.

TWO-LIGHT BATH
P3288-09ET Brushed Nickel
P3288-15ET Polished Chrome
P3288-20ET Antique Bronze
11-3/4" W., 8-1/4" ht.
Extends 8-1/4". H/CTR 2-3/4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH
P3289-09ET Brushed Nickel
P3289-15ET Polished Chrome
P3289-20ET Antique Bronze
16" W., 8-1/2" ht.
Extends 8-1/2". H/CTR 2-5/8".
Three medium base lamps,
each 100w max.

All fixtures mount up or down.



P3288-09ET



P3287-09ET



P3289-09ET



P3288-15ET



P3287-15ET



P3289-15ET



P3288-20ET



P3287-20ET



P3289-20ET

Deluxe Broadway Lights

Sockets on 6″ centers. Medium base G-lamps recommended. Wall mount only.

FINISH

Polished Chrome - 15

THREE-LIGHT BATH
P3333-15 Polished Chrome
18″ W., 4-1/4″ ht.
Three medium base G-lamps, each 60w max.



P3333-15

FOUR-LIGHT BATH
P3298-15 Polished Chrome
24″ W., 4-1/4″ ht.
Four medium base G-lamps, each 60w max.



P3298-15

FIVE-LIGHT BATH
P3335-15 Polished Chrome
30″ W., 4-1/4″ ht.
Five medium base G-lamps, each 60w max.



P3335-15

SIX-LIGHT BATH
P3299-15 Polished Chrome
36″ W., 4-1/4″ ht.
Six medium base G-lamps, each 60w max.



P3299-15

EIGHT-LIGHT BATH
P3300-15 Polished Chrome
48″ W., 4-1/4″ ht.
Eight medium base G-lamps, each 60w max.



P3300-15

Marquee Lights

G medium base lamps recommended. Wall mount only.

FINISHES

Brushed Nickel - 09
Polished Chrome - 15
Antique Bronze - 20

THREE-LIGHT BATH
P3038-15 Polished Chrome
18″ W., 4-1/2″ ht.
Three medium base G-lamps, each 60w max.



P3038-15

FOUR-LIGHT BATH
P3025-09 Brushed Nickel
P3025-15 Polished Chrome
P3025-20 Antique Bronze
24″ W., 4-3/4″ ht.
Four medium base G-lamps, each 60w max.



P3025-09

SIX-LIGHT BATH
P3026-09 Brushed Nickel
36″ W., 4-3/4″ ht.
Six medium base G-lamps, each 60w max.



P3026-09



P3025-15



P3025-20

Economy Broadway Lights

Sockets on 7-1/2" centers. Medium base G-lamps recommended. Wall mount only.

FINISH

Polished Chrome - 15



P3115-15



P3114-15



P3116-15



P3117-15



P3118-15

THREE-LIGHT BATH
P3114-15 Polished Chrome
24" W., 4-1/4" ht.
Three medium base G-lamps, each 60w max.

FOUR-LIGHT BATH
P3115-15 Polished Chrome
30" W., 4-1/4" ht.
Four medium base G-lamps, each 60w max.


FIVE-LIGHT BATH
P3116-15 Polished Chrome
36" W., 4-1/4" ht.
Five medium base G-lamps, each 60w max.

SIX-LIGHT BATH
P3117-15 Polished Chrome
48" W., 4-1/4" ht.
Six medium base G-lamps, each 60w max.

EIGHT-LIGHT BATH
P3118-15 Polished Chrome
60" W., 4-1/4" ht.
Eight medium base G-lamps, each 60w max.

Featuring Galveston





Outdoor

Dress *Up* the Outdoors

Scan and see more at
progresslighting.com

Port Royal
P560168-031





Kyndra Outlaw
Showroom Merchandiser

A New Take on an Old Classic

with Kyndra

New Traditional spaces are timeless with elegant additions that offer but a little fun and youthfulness to keep the design fresh. Clean, uncluttered spaces make a significant style impact. Add approachable touches, like furniture with sleeker forms, to what used to be formal rooms. Feel free to mix and match different finishes such as light and dark wood stains, paint, mirror, metal and leather. Try lighting that has mixed metal finishes or fixtures that are new takes on classic silhouettes. Light, airy colors accented with a pop of color help make the New Traditional spaces feel open and spacious rather than cramped, as do windows that are uncovered or covered minimally with simpler treatments.

Shop this style at
progresslighting.com/new-traditional



Brenham

FINISH

● Black - 031

P500235-031



The Brenham Collection offers a true farmhouse feel with its mixed elements design. Wood accent rings bookend the top and bottom of each fixture as a black metal frame with simple metal bars and ribbon-like metal arms reach down from a central metal link chain. This collection is perfect for illuminating a covered patio during a warm summer evening.

P500235-031



P500234-03



ONE-LIGHT OUTDOOR PENDANT
P500234-031 Black
10″ dia., 15″ ht.
Overall ht. w/chain 89″, wire 10′.
One medium base lamp,
100w max.

THREE-LIGHT OUTDOOR PENDANT
P500235-031 Black
16″ dia., 20-5/8″ ht.
Overall ht. w/chain 94-1/2″, wire 10′.
Three candelabra base lamps,
each 60w max.

Featuring Brenham



Galveston

FINISH

Galvanized-141

The Galveston collection adds rustic charm with its wash-basin inspired metal shade that offers a comfortable, farmhouse welcome. This collection is perfect for illuminating a covered patio.

P500226-141



Galvanized Finish

P500227-141



P500226-141



ONE-LIGHT OUTDOOR PENDANT
P500226-141 Galvanized
9-1/4" dia., 11-1/8" ht.
Overall ht. w/chain 86-1/2", wire 10'.
One medium base lamp,
100w max.

THREE-LIGHT OUTDOOR PENDANT
P500227-141 Galvanized
17-3/4" dia., 18-7/8" ht.
Overall ht. w/chain 94", wire 10'.
Three candelabra base lamps,
60w max.

Township

FINISH

● Oil Rubbed Bronze - 108

P5504-108



Enjoy the simple elegance of traditional styling. Township's clear beveled glass and Oil Rubbed Bronze finish contains notes of New England-inspired style for this charming outdoor lantern collection.



P5692-108



P5693-108



P5699-108



P5504-108



P5404-108

POST LANTERN
P5404-108 Oil Rubbed Bronze
8" dia., 22-1/2" ht.
Fits 3" post (sold separately).
Three candelabra base lamps, each 60w max.

HANGING LANTERN
P5504-108 Oil Rubbed Bronze
8" dia., 19-3/8" ht.
Overall ht. w/chain 94"; wire 10'.
Three candelabra base lamps, each 60w max.

SMALL WALL LANTERN
P5692-108 Oil Rubbed Bronze
5-1/2" W., 14-3/4" ht.
Extends 8". H/CTR 3-3/4 ".
One medium base lamp, 60w max.

MEDIUM WALL LANTERN
P5693-108 Oil Rubbed Bronze
6-1/2" W., 17-1/2" ht.
Extends 8-3/8". H/CTR 3-3/4".
Two candelabra base lamps, each 60w max.

LARGE WALL LANTERN
P5699-108 Oil Rubbed Bronze
8" W., 22" ht.
Extends 10-1/2 ". H/CTR 4-1/4".
Three candelabra base lamps, each 60w max.

Cardiff

FINISHES

- Antique Bronze - 020
- Black - 031

P560167-020

Beckon family and friends home with the coastal glow of the Cardiff Collection. Clear seeded glass panes that evoke memories of salty sea spray rest in timeless, traditional, non-metallic black and antique bronze frames that are corrosion resistant for excellent longevity. Made with DURASHIELD, a durable material specially designed and tested to resist harsh environmental conditions.





P560166-020



P560166-031



P560167-020



P560167-031

POST LANTERN
P540039-020 Antique Bronze
P540039-031 Black
Fits 3" post (sold separately)
3" sq., 20" ht.
One medium base lamp,
75w max.

SMALL WALL LANTERN
P560166-020 Antique Bronze
P560166-031 Black
7" W., 12-1/2" ht.
Extends 7-7/8". H/CTR 3-11/16".
One medium base lamp,
60w max.

MEDIUM WALL LANTERN
P560167-020 Antique Bronze
P560167-031 Black
8-15/16" W., 16-1/2" ht.
Extends 10-5/16". H/CTR 4-15/16".
One medium base lamp,
75w max.



P540039-020



P540039-031

Marquette

FINISH

● Black - 031

P550062-031



The Marquette Collection is a go-to choice when incorporating classic silhouettes with a farmhouse flair into your home décor vision. Traditional lantern frames constructed with non-metallic, corrosion-resistant housing with a classic black finish holds a beautiful water glass shade to add charming character to the timeless design. Made with DURASHIELD, a durable material specially designed and tested to resist harsh environmental conditions.



P560171-031



P560172-031



P560173-031

P550062-031





P540062-031

POST LANTERN
P540062-031 Black
8-5/8″ sq., 18-5/8″ ht.
Fits 3″ post (sold separately)
One medium base lamp,
75w max.

HANGING LANTERN
P550062-031 Black
8-5/8″ sq., 15-1/8″ ht.
Overall ht. w/chain 90-1/2″,
wire 10′.
One medium base lamp,
75w max.

SMALL WALL LANTERN
P560171-031 Black
7-1/8″ W., 13″ ht.
Extends 8-5/8″. H/CTR 5-1/2″.
One medium base lamp,
60w max.

MEDIUM WALL LANTERN
P560172-031 Black
8-5/8″ W., 16″ ht.
Extends 10-3/8″. H/CTR 6-5/8″.
One medium base lamp,
75w max.

LARGE WALL LANTERN
P560173-031 Black
10-1/8″ W., 18-5/8″ ht.
Extends 12-1/2″. H/CTR 7-5/8″.
One medium base lamp,
100w max.

Seagrove

FINISH

● Black - 031

P560164-031

Capture the raw strength and captivating honesty of salty seashores with the coastal-inspired Seagrove Collection. Clear seeded glass panes rest in a non-metallic, corrosion resistant frame with a rich black finish. On each side of the frames, an x-brace design adds an extra pinch of rustic character. Made with DURASHIELD, a durable material specially designed and tested to resist harsh environmental conditions.

Coastal



Rustic Character

X-brace Design



P560163-031



P560164-031

SMALL WALL LANTERN
P560163-031 Black
5-1/2" W., 10-1/2" ht.
Extends 7-1/2". H/CTR 3-1/4".
One medium base lamp,
40w max.

MEDIUM WALL LANTERN
P560164-031 Black
7-1/2" W., 12-1/2" ht.
Extends 8-1/2". H/CTR 3-1/4".
One medium base lamp,
60w max.

Gables

FINISH

Antique Bronze - 020

P560088-020

Engineered polymers are used to create the distinctive Gables lanterns. Developed to withstand a broad range of environmental conditions, the corrosion-resistant housing delivers beautiful lighting and reliability. A clear glass globe enhances the classic design. Made with DURASHIELD, a durable material specially designed and tested to resist harsh environmental conditions.





P560087-020



P560088-020

SMALL WALL LANTERN
P560087-020 Antique Bronze
5-7/8" W., 11-3/8" ht.
Extends 6-7/8". H/CTR 7-5/8".
One medium base lamp,
60w max.

MEDIUM WALL LANTERN
P560088-020 Antique Bronze
7-1/2" W., 14-1/8" ht.
Extends 8-1/2".
H/CTR 10-9/16".
One medium base lamp,
100w max.

Port Royal

FINISH
● Black - 031

The Port Royal Collection distills both industrial and artisan influences with its textured black frame constructed from durable corrosion resistant non-metallic materials. An elongated, clear glass shade rests inside the frame, adding to the modern flair of this collection. Made with DURASHIELD, a durable material specially designed and tested to resist harsh environmental conditions.

P550061-031





P550061-031



P560168-031

HANGING LANTERN
P550061-031 Black
6-1/4" dia., 14" ht.
Overall ht. w/chain 86-1/2", wire 10'.
One medium base lamp,
60w max.

SMALL WALL LANTERN
P560168-031 Black
6-1/4" W., 12-1/2" ht.
Extends 7-1/2". H/CTR 2-1/2".
One medium base lamp,
60w max.

Benton Harbor

FINISH
● Black - 031

P550065-031



The Benton Harbor Collection is expertly crafted with that casual, coastal style you love. Classic black frames constructed with a non-metallic, corrosion-resistant housing features thin bars holding clear glass shades for that seaside-living vibe. Made with DURASHIELD, a durable material specially designed and tested to resist harsh environmental conditions.



P560177-031



P560178-031



P560185-031



P550065-031



P540065-031

POST LANTERN
P540065-031 Black
9-1/8" dia., 16-3/8" ht.
Fits 3" post (sold separately)
One medium base lamp,
75w max.

HANGING LANTERN
P550065-031 Black
8-3/4" dia., 13-1/4" ht.
Overall ht. w/chain 93-1/2",
wire 10'.
One medium base lamp,
75w max.

SMALL WALL LANTERN
P560177-031 Black
6-1/4" W., 9-3/4" ht.
Extends 9". H/CTR 2-5/8".
One medium base lamp,
60w max.

MEDIUM WALL LANTERN
P560178-031 Black
7-1/2" W., 11" ht.
Extends 8-5/8". H/CTR 2-5/8".
One medium base lamp,
75w max.

LARGE WALL LANTERN
P560185-031 Black
8-3/4" W., 13" ht.
Extends 9-5/8". H/CTR 2-5/8".
One medium base lamp,
100w max.

Endorse LED

FINISH

● Black - 31

P6057-3130K9

Endorse celebrates the traditional form of a gas-powered coach light with illumination from a modern LED source. A die-cast aluminum, powder coated frame creates an intriguing visual effect with clear beveled glass.

Traditional Form



Powdered Coated Frame



P6056-3130K9



P6058-3130K9



P6057-3130K9



P6426-3130K9

SMALL WALL LANTERN
P6056-3130K9 Black
6-3/4" W., 12" ht.
Extends 7-5/8". H/CTR 3-1/4".
One 9w LED module, 3000K, 90CRI, 623 source lumens.

MEDIUM WALL LANTERN
P6057-3130K9 Black
8-3/4" W., 14-3/4" ht.
Extends 9-3/4". H/CTR 4".
One 9w LED module, 3000K, 90CRI, 623 source lumens.

LARGE WALL LANTERN
P6058-3130K9 Black
10-3/4" W., 17-3/4" ht.
Extends 11-3/4". H/CTR 4".
One 9w LED module, 3000K, 90CRI, 623 source lumens.

POST LANTERN
P6426-3130K9 Black
Fits 3" post (sold separately)
3" W., 21" ht.
One 9w LED module, 3000K, 90CRI, 623 source lumens.

All fixtures:

Barnett

FINISH

● Antique Bronze - 020

Barnett lanterns deliver timeless appeal with a decidedly modern flair. Large clear panes of glass frame your choice of traditional or vintage style bulbs. A graphic-inspired over-scale loop features a contrasting brass-tone finish.

P560028-020





P560077-020



P560078-020



P560079-020

P550028-020





P540028-020

POST LANTERN
P540028-020 Antique Bronze
11-1/4" W., 9" L., 27" ht.
Fits 3" post (sold separately).
Two medium base lamps,
each 60w max.

HANGING LANTERN
P550028-020 Antique Bronze
11-1/4" W., 9" L., 26-7/8" ht.
Overall ht. w/chain 102", wire 10'.
Two medium base lamps,
each 60w max.

SMALL WALL LANTERN
P560077-020 Antique Bronze
6-1/2" W., 15-1/8" ht.
Extends 6-7/8". H/CTR 7-1/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560078-020 Antique Bronze
9" W., 18-7/8" ht.
Extends 8-1/8". H/CTR 9".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P560079-020 Antique Bronze
11-1/4" W., 23-5/8" ht.
Extends 10". H/CTR 10".
Two medium base lamps,
each 60w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

Featuring Grandbury



Grandbury

FINISH

● Black - 031

P550064-031



The Grandbury Collection partners timeless elegance with a pinch of coastal vibe. Beautiful black, square frames crafted from corrosion proof material feature a half loop on top of each structure as they hold clear glass panes in place. This collection is sure to complement other farmhouse and coastal features for an overall beautiful, welcoming look. Made with DURASHIELD, a durable material specially designed and tested to resist harsh environmental conditions.



P560174-031



P560175-031



P560176-031

P550064-031





P540064-031

POST LANTERN
P540064-031 Black
7" sq., 15-5/8" ht.
Fits 3" post (sold separately)
One medium base lamp, 75w max.

HANGING LANTERN
P550064-031 Black
7" sq., 15-3/8" ht.
Overall ht. w/chain 90-1/2", wire 10'.
One medium base lamp, 75w max.

SMALL WALL LANTERN
P560174-031 Black
5-1/2" W., 11-7/8" ht.
Extends 6-1/2". H/CTR 3-1/8".
One medium base lamp, 60w max.

MEDIUM WALL LANTERN
P560175-031 Black
7-1/8" W., 13-5/8" ht.
Extends 8". H/CTR 3-1/8".
One medium base lamp, 75w max.

LARGE WALL LANTERN
P560176-031 Black
9" W., 17" ht.
Extends 10". H/CTR 3-3/4".
Two medium base lamps, each 60w max.

All fixtures shown with F7ST19DLED927/JA8 vintage lamps, not included. See page 824.

Barlowe

FINISHES

- Antique Bronze - 020
- Stainless Steel - 135

P550068-135



Transform your home into a warm and cozy dream with the farmhouse-style of the Barlowe collection. A rustic X-brace design decorates each side of the charming lantern silhouettes. Metal finishes with antique copper or white accents provide added warmth and character.



P560156-135



P550068-135



P560157-135



P540068-135



P560158-135

POST LANTERN
P540068-135 Stainless Steel
Fits 3" post (sold separately)
9" sq., 20" ht.
One medium base lamp,
100w max.

HANGING LANTERN
P550068-135 Stainless Steel
9" sq., 21" ht.
Overall ht. w/chain 96", wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P560156-135 Stainless Steel
6-1/2" W., 13" ht.
Extends 7-1/2". H/CTR 2-3/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560157-135 Stainless Steel
7-1/2" W., 16" ht.
Extends 8-1/2". H/CTR 3-1/2".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P560158-135 Stainless Steel
9-1/8" W., 19" ht.
Extends 10". H/CTR 3-1/2".
One medium base lamp,
100w max.

Barlowe



P550068-020



P560156-020



P560157-020



P540068-020



P560158-020

POST LANTERN
P540068-020 Antique Bronze
Fits 3″ post (sold separately)
9″ sq., 20″ ht.
One medium base lamp,
100w max.

HANGING LANTERN
P550068-020 Antique Bronze
9″ sq., 21″ ht.
Overall ht. w/chain 96″, wire 10′.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P560156-020 Antique Bronze
6-1/2″ W., 13″ ht.
Extends 7-1/2″. H/CTR 2-3/8″.
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560157-020 Antique Bronze
7-1/2″ W., 16″ ht.
Extends 8-1/2″. H/CTR 3-1/2″.
One medium base lamp,
100w max.

LARGE WALL LANTERN
P560158-020 Antique Bronze
9-1/8″ W., 19″ ht.
Extends 10″. H/CTR 3-1/2″.
One medium base lamp,
100w max.

All fixtures shown with F7ST19DLED927/JA8 vintage lamps, not included. See page 824.

Refuge

FINISH

● Oil Rubbed Bronze - 108

P6531-108



A Cape Cod-inspired frame pays homage to a classic nautical style. Light output and geometric forms offer visual interest to outdoor exteriors. Clear glass windows are paired with a unique umber glass reflector panel on wall lanterns.



P6030-108



P6031-108



P6032-108



P6531-108



P6431-108

SMALL WALL LANTERN
P6030-108 Oil Rubbed Bronze
6-1/2″ W., 13-1/4″ ht.
Extends 6-7/8″. H/CTR 4-1/4″.
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P6031-108 Oil Rubbed Bronze
8″ W., 16″ ht.
Extends 8-1/8″. H/CTR 5-3/4″.
One medium base lamp,
100w max.

LARGE WALL LANTERN
P6032-108 Oil Rubbed Bronze
10-1/2″ W., 21″ ht.
Extends 10″. H/CTR 7-1/2″.
One medium base lamp,
100w max.

POST LANTERN
P6431-108 Oil Rubbed Bronze
8″ W., 18-5/8″ ht.
Fits 3″ post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN
P6531-108 Oil Rubbed Bronze
8″ W., 16″ ht.
Overall ht. w/chain 91″; wire 10′.
One medium base lamp,
100w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

River Place

FINISH

● Antique Bronze - 020

P550034-020



River Place lanterns showcase an inviting design to create instant curb appeal for the home. The clear seeded glass is topped with a flared roof, resembling the features of a pineapple, the symbol of hospitality. An Antique Bronze finish completes the lanterns with a graceful touch of tradition.



P560101-020



P560102-020



P560103-020

P550034-020





P540034-020

POST LANTERN
P540034-020 Antique Bronze
9-1/4" W., 21-1/4" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN
P550034-020 Antique Bronze
9-1/4" W., 19-3/4" ht.,
Overall ht. w/chain 95"; wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P560101-020 Antique Bronze
6-1/2" W., 17" ht.
Extends 7". H/CTR 8-7/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560102-020 Antique Bronze
7-3/4" W., 20-1/2" ht.
Extends 8-3/8". H/CTR 10-3/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P560103-020 Antique Bronze
9-1/4" W., 24-1/8" ht.
Extends 9-5/8". H/CTR 12".
One medium base lamp,
100w max.

Abbott

FINISHES

- Antique Bronze - 020
- Antique Pewter - 103

P550040-020



Distinctive forms with ancient roots are featured in Abbott lanterns. Transparency, depth and dimension are all on display to highlight the clear seeded glass and sweeping details within the frame.



P560113-020



P560114-020



P560115-020



P550040-020



P540011-020

POST LANTERN
P540011-020 Antique Bronze
8-1/4" W., 18-1/2" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN
P550040-020 Antique Bronze
8-1/4" W., 15-1/4" ht.
Overall ht. w/chain 90-1/2"; wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P560113-020 Antique Bronze
6-1/4" W., 12-1/4" ht.
Extends 8-1/4". H/CTR 9-3/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560114-020 Antique Bronze
8-1/4" W., 16-1/4" ht.
Extends 10-3/4". H/CTR 12-1/2".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P560115-020 Antique Bronze
10-3/8" W., 20-1/4" ht.
Extends 13-1/2". H/CTR 15-1/4".
One medium base lamp,
100w max.

Abbott



P550040-103



P560113-103



P560114-103



P540011-103



P560115-103

POST LANTERN
P540011-103 Antique Pewter
8-1/4" W., 18-1/2" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN
P550040-103 Antique Pewter
8-1/4" W., 15-1/4" ht.
Overall ht. w/chain 90-1/2"; wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P560113-103 Antique Pewter
6-1/4" W., 12-1/4" ht.
Extends 8-1/4". H/CTR 9-3/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560114-103 Antique Pewter
8-1/4" W., 16-1/4" ht.
Extends 10-3/4". H/CTR 12-1/2".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P560115-103 Antique Pewter
10-3/8" W., 20-1/4" ht.
Extends 13-1/2". H/CTR 15-1/4".
One medium base lamp,
100w max.

Endicott

FINISHES

- Antique Bronze - 20
- Black - 31

P5500-20



With a Craftsman-inspired silhouette, Endicott offers visual interest. The elongated frame is finished in Antique Bronze with umber linen glass or Black with clear seeded glass.



P5605-20



P5500-20



P5610-20



P5611-20



P5613-20



P5400-20

POST LANTERN
P5400-20 Antique Bronze
7-3/8" dia., 17-3/4" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN
P5500-20 Antique Bronze
7-3/8" dia., 15-1/4" ht.
Overall ht. w/chain 91"; wire 12'.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P5605-20 Antique Bronze
7-1/4" W., 10-1/2" ht.
Extends 9-1/2". H/CTR 2-3/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P5610-20 Antique Bronze
7-1/4" W., 14-1/4" ht.
Extends 9-1/2". H/CTR 3-5/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P5611-20 Antique Bronze
8-7/8" W., 12-1/2" ht.
Extends 11". H/CTR 3-5/8".
One medium base lamp,
100w max.

EXTRA LARGE WALL LANTERN
P5613-20 Antique Bronze
8-7/8" W., 18" ht.
Extends 11". H/CTR 4-1/2".
One medium base lamp,
100w max.

Endicott


P5500-31


P5605-31


P5611-31


P5610-31


P5400-31


P5613-31

POST LANTERN
P5400-31 Black
7-3/8" dia., 17-3/4" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN
P5500-31 Black
7-3/8" dia., 15-1/4" ht.
Overall ht. w/chain 91"; wire 12'.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P5605-31 Black
7-1/4" W., 10-1/2" ht.
Extends 9-1/2". H/CTR 2-3/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P5610-31 Black
7-1/4" W., 14-1/4" ht.
Extends 9-1/2". H/CTR 3-5/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P5611-31 Black
8-7/8" W., 12-1/2" ht.
Extends 11". H/CTR 3-5/8".
One medium base lamp,
100w max.

EXTRA LARGE WALL LANTERN
P5613-31 Black
8-7/8" W., 18" ht.
Extends 11". H/CTR 4-1/2".
One medium base lamp,
100w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

Conover

FINISHES

- Antique Bronze - 020
- Antique Pewter - 103

P550030-020



Conover is an outdoor lantern collection featuring nautical influences. A protective die cast ring surrounds beautiful clear seeded glass. Vintage metallic finishes are available for this collection that is sure to enhance curb appeal for a variety of exteriors.



P560083-020



P560084-020



P560085-020



P550030-020



P540030-020

POST LANTERN
P540030-020 Antique Bronze
10-7/8" dia., 19" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN
P550030-020 Antique Bronze
10-7/8" dia., 15-1/2" ht.
Overall ht. w/chain 90-1/2", wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P560083-020 Antique Bronze
7" W., 14-1/4" ht.
Extends 9". H/CTR 7-1/2".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560084-020 Antique Bronze
8-5/8" W., 16" ht.
Extends 10-1/4". H/CTR 7-5/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P560085-020 Antique Bronze
10-7/8" W., 21" ht.
Extends 13-1/8". H/CTR 9-3/8".
One medium base lamp,
100w max.

Conover



P550030-103



P540030-103



P560083-103



P560084-103



P560085-103

POST LANTERN
P540030-103 Antique Pewter
10-7/8″ dia., 19″ ht.
Fits 3″ post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN
P550030-103 Antique Pewter
10-7/8″ dia., 15-1/2″ ht.
Overall ht. w/chain 90-1/2″, wire 10′.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P560083-103 Antique Pewter
7″ W., 14-1/4″ ht.
Extends 9″. H/CTR 7-1/2″.
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560084-103 Antique Pewter
8-5/8″ W., 16″ ht.
Extends 10-1/4″. H/CTR 7-5/8″.
One medium base lamp,
100w max.

LARGE WALL LANTERN
P560085-103 Antique Pewter
10-7/8″ W., 21″ ht.
Extends 13-1/8″. H/CTR 9-3/8″.
One medium base lamp,
100w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

Squire

FINISHES

- Antique Bronze - 020
- Black - 031

P550012-020



Squire lanterns feature a classic traditional profile with clean, modern metal fittings. Accented with contrasting metallic elements, the cylindrical frame is comprised of a clear glass diffuser.



P550011-020



P550012-020



P560037-020



P560036-020



P560038-020



P540012-020

POST LANTERN
P540012-020 Antique Bronze
9-7/8" dia., 22-5/8" ht.
Fits 3" post (sold separately).
Three candelabra base lamps, each 60w max.

SEMI-FLUSH CONVERTIBLE
P550011-020 Antique Bronze
Hanging and ceiling mount hardware included.
9-7/8" dia., 11" ht.
Overall ht. w/chain 50", wire 9'.
Three candelabra base lamps, each 60w max.

HANGING LANTERN
P550012-020 Antique Bronze
9-7/8" dia., 20-1/4" ht.
Overall ht. w/chain 65", wire 9'.
Three candelabra base lamps, each 60w max.

SMALL WALL LANTERN
P560036-020 Antique Bronze
6" W., 14-3/4" ht.
Extends 7-3/8". H/CTR 6-3/8".
One medium base lamp, 100w max.

MEDIUM WALL LANTERN
P560037-020 Antique Bronze
8" W., 19-1/4" ht.
Extends 8-3/4". H/CTR 6-3/4".
Two candelabra base lamps, each 60w max.

LARGE WALL LANTERN
P560038-020 Antique Bronze
9-7/8" W., 22-3/4" ht.
Extends 10-5/8". H/CTR 8".
Three candelabra base lamps, each 60w max.

Squire



P550012-031



P550011-031



P560036-031



P560037-031



P540012-031



P560038-031

POST LANTERN
P540012-031 Black
9-7/8" dia., 22-5/8" ht.
Fits 3" post (sold separately).
Three candelabra base lamps, each 60w max.

SEMI-FLUSH CONVERTIBLE
P550011-031 Black
Hanging and ceiling mount hardware included.
9-7/8" dia., 11" ht.
Overall ht. w/chain 50", wire 9'.
Three candelabra base lamps, each 60w max.

HANGING LANTERN
P550012-031 Black
9-7/8" dia., 20-1/4" ht.
Overall ht. w/chain 65", wire 9'.
Three candelabra base lamps, each 60w max.

SMALL WALL LANTERN
P560036-031 Black
6" W., 14-3/4" ht.
Extends 7-3/8". H/CTR 6-3/8".
One medium base lamp, 100w max.

MEDIUM WALL LANTERN
P560037-031 Black
8" W., 19-1/4" ht.
Extends 8-3/4". H/CTR 6-3/4".
Two candelabra base lamps, each 60w max.

LARGE WALL LANTERN
P560038-031 Black
9-7/8" W., 22-3/4" ht.
Extends 10-5/8". H/CTR 8".
Three candelabra base lamps, each 60w max.

All fixtures shown with P7826-01 vintage lamps, not included. See page 824.

Prestwick

FINISH

● Oil Rubbed Bronze - 108

Classic rooflines and unique cast yoke straps in Oil Rubbed Bronze finish. Water glass urn shade.

P5584-108





P5920-108



P5921-108



P5923-108



P5584-108



P5484-108

POST LANTERN
P5484-108 Oil Rubbed Bronze
10-3/4″ dia., 18-3/4″ ht.
Fits 3″ post (sold separately).
Three candelabra base lamps, each 60w max.

HANGING LANTERN
P5584-108 Oil Rubbed Bronze
10-3/4″ dia., 17-3/4″ ht.
Overall ht. w/chain 93″, wire 15′.
Three candelabra base lamps, each 40w max.

SMALL WALL LANTERN
P5920-108 Oil Rubbed Bronze
6-7/8″ W., 11″ ht.
Extends 8″. H/CTR 5-1/4″.
One medium base lamp, 100w max.

MEDIUM WALL LANTERN
P5921-108 Oil Rubbed Bronze
8-3/4″ W., 13-7/8″ ht.
Extends 10″. H/CTR 6-3/4″.
Two candelabra base lamps, each 60w max.

LARGE WALL LANTERN
P5923-108 Oil Rubbed Bronze
10-3/4″ W., 16-3/4″ ht.
Extends 12″. H/CTR 7-7/8″.
Three candelabra base lamps, each 60w max.

Meadowlark

FINISH

● Oil Rubbed Bronze - 108

P5716-108



Arched roof, ribbon scrolled loops and arching arms with water seeded glass. Cast aluminum construction with powder coat finish in Oil Rubbed Bronze.



P5715-108



P5716-108



P5717-108



P5468-108

POST LANTERN
P5468-108 Oil Rubbed Bronze
6-7/8" L., 8-1/2" W., 17-7/8" ht.
Fits 3" post (sold separately).
Three candelabra base lamps, each 60w max.

SMALL WALL LANTERN
P5715-108 Oil Rubbed Bronze
6-3/8" W., 12" ht.
Extends 6-7/8". H/CTR 7-5/8".
One medium base lamp, 100w max.

MEDIUM WALL LANTERN
P5716-108 Oil Rubbed Bronze
7-1/4" W., 14-1/2" ht.
Extends 8-1/4". H/CTR 7-3/4".
Two candelabra base lamps, each 60w max.

LARGE WALL LANTERN
P5717-108 Oil Rubbed Bronze
8-1/2" W., 17-1/8" ht.
Extends 9-5/8". H/CTR 9".
Three candelabra base lamps, each 60w max.

McPherson

FINISH
● Black - 031

P550023-031



McPherson outdoor lanterns are sure to make a statement. A clever clover-shaped handle accentuates elegantly fluted clear glass. Wall, hanging and post lanterns are finished in Black and complement Rustic and Modern Farmhouse exteriors, as well as Traditional and Transitional homes.


P560062-031


P560063-031


P560064-031


P550023-031


P540023-031

POST LANTERN
P540023-031 Black
9-1/2" dia., 19" ht.
Fits 3" post (sold separately).
Three candelabra base lamps, each 60w max.

HANGING LANTERN
P550023-031 Black
9-1/2" W., 19" ht.
Overall ht. w/chain 93", wire 10'.
Three candelabra base lamps, each 60w max.

SMALL WALL LANTERN
P560062-031 Black
7-1/2" W., 13-1/2" ht.
Extends 7-1/8". H/CTR 9-1/2".
One medium base lamp, 100w max.

MEDIUM WALL LANTERN
P560063-031 Black
9-1/2" W., 17-1/2" ht.
Extends 9-1/4". H/CTR 12-1/4".
Two candelabra base lamps, each 60w max.

LARGE WALL LANTERN
P560064-031 Black
10-5/8" W., 20" ht.
Extends 10-1/2". H/CTR 13-3/4".
Three candelabra base lamps, each 60w max.

Resort

FINISH

● Aged Copper - 122

P6504-122



Tudor styling meets Prairie design. Gradual ombré umber tint on glass shades. A woven cast pattern encases a casual profile. Large-scale cast aluminum lanterns feature powder coat finish in a warm Aged Copper finish.



P5987-122



P5988-122



P5989-122

P6504-122





P6404-122

SMALL WALL LANTERN
P5987-122 Aged Copper
6-1/2″ W., 10-7/8″ ht.
Extends 7-1/2″. H/CTR 3-1/2″.
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P5988-122 Aged Copper
8-1/2″ W., 15-7/8″ ht.
Extends 11-1/4″. H/CTR 4-3/4″.
One medium base lamp,
100w max.

LARGE WALL LANTERN
P5989-122 Aged Copper
10-1/2″ W., 19-3/4″ ht.
Extends 14″. H/CTR 5-7/8″.
One medium base lamp,
100w max.

POST LANTERN
P6404-122 Aged Copper
Decorative bottom grill included.
8-1/2″ dia., 17-3/8″ ht.
Fits 3″ post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN
P6504-122 Aged Copper
Decorative bottom grill included.
8-1/2″ dia., 14-1/8″ ht.
Overall ht. w/chain 88″; wire 15′.
One medium base lamp,
100w max.

Maison

FINISHES

- Black - 31
- Oil Rubbed Bronze - 108

P6532-108



Die-Cast Aluminum

Clear Water Glass

The Maison Collection offers traditional French country styling for a variety of home settings. The etched glass pillar diffuser inside the clear water seeded glass gives off a soft glow of light. This collection is ideal for illuminating farmhouse and coastal settings.



P6532-31



P6532-108

French Country Styling



P6432-31



P6432-108

POST LANTERN
P6432-31 Black
P6432-108 Oil Rubbed Bronze
7-1/4" dia., 20-5/8" ht.
Fits 3" post (sold separately).
Two candelabra base lamps, each 60w max.

HANGING LANTERN
P6532-31 Black
P6532-108 Oil Rubbed Bronze
7-1/4" dia., 17-7/8" ht.
Overall ht. w/chain 93"; wire 10'.
Two candelabra base lamps, each 60w max.

Maison



P5753-108



P5753-31



P5754-108



P5754-31



P5755-108



P5755-31

SMALL WALL LANTERN
P5753-31 Black
P5753-108 Oil Rubbed Bronze
5-3/4" W., 16-1/4" ht.
Extends 8-5/8". H/CTR 9".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P5754-31 Black
P5754-108 Oil Rubbed Bronze
7-1/4" W., 20" ht.
Extends 10-1/2". H/CTR 10-5/8".
Two candelabra base lamps,
each 60w max.

LARGE WALL LANTERN
P5755-31 Black
P5755-108 Oil Rubbed Bronze
8-1/2" W., 23-3/4" ht.
Extends 12". H/CTR 13-1/2".
Three candelabra base lamps,
each 60w max.

Crawford

FINISHES
- Black - 31
- Oil Rubbed Bronze - 108

P5574-108



The Crawford Collection offers updated traditional styling with scroll arms. Clear beveled or etched glass panes give off a soft glow of light while a hinged door makes maintenance easy and stress-free. This collection is ideal for illuminating new traditional and transitional settings.


P5671-108


P5574-108


P5672-108


P5670-108


P5673-108


P5474-108

POST LANTERN*
P5474-108 Oil Rubbed Bronze
12" dia., 28-1/2" ht.
Fits 3" post (sold separately).
Four candelabra base lamps, each 60w max.

HANGING LANTERN*
P5574-108 Oil Rubbed Bronze
12" dia., 29-3/8" ht.
Overall ht. w/ chain 68"; wire 15'.
Four candelabra base lamps, each 60w max.

SMALL WALL LANTERN
P5670-108 Oil Rubbed Bronze
6-1/2" W., 12-1/2" ht.
Extends 8-3/4". H/CTR 8".
One medium base lamp, 100w max.

MEDIUM WALL LANTERN*
P5671-108 Oil Rubbed Bronze
8-1/2" W., 16-3/4" ht.
Extends 11-1/8" H/CTR 9-5/8".
Two candelabra base lamps, each 60w max.

LARGE WALL LANTERN*
P5672-108 Oil Rubbed Bronze
10" W., 29" ht.
Extends 12-1/2". H/CTR 11-5/8".
Three candelabra base lamps, each 60w max.

EXTRA LARGE WALL LANTERN*
P5673-108 Oil Rubbed Bronze
12" W., 32-3/4" ht.
Extends 14-3/4". H/CTR 14-3/4".
Four candelabra base lamps, each 60w max.

**Hinged door for easy relamping.*

Crawford



P5686-108MD



P5686-31MD



P6630-31MD



P6631-31MD



P6632-31MD



P6633-31MD

MEDIUM WALL LANTERN
P5686-31MD Black
P5686-108MD Oil Rubbed Bronze
8-1/2" W., 16-3/4" ht.
Extends 11". H/CTR 9-5/8".
One medium base lamp,
100w max.

SMALL WALL LANTERN
P6630-31MD Black
6-1/2" W., 12-1/2" ht.
Extends 8-3/4". H/CTR 8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN *
P6631-31MD Black
8-1/2" W., 20-1/2" ht.
Extends 11". H/CTR 8-3/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN*
P6632-31MD Black
9-7/8" W., 28-7/8" ht.
Extends 12-5/8". H/CTR 11-5/8".
One medium base lamp,
100w max.

EXTRA LARGE WALL LANTERN*
P6633-31MD Black
12" W., 32-7/8" ht.
Extends 14-3/4". H/CTR 14-7/8".
One medium base lamp,
100w max.

**Hinged door for easy relamping.*

Nottington

FINISH

● Forged Bronze - 77

Scrolling cast arms, fluted bodies and acorn accents. Clear seeded glass with Forged Bronze powder coat finish. Cast aluminum construction.

P5837-77





P5836-77



P5837-77



P5835-77



P5438-77

POST LANTERN
P5438-77 Forged Bronze
10" dia., 22-1/2" ht.
Fits 3" post (sold separately).
Three candelabra base lamps, each 60w max.

MEDIUM WALL LANTERN
P5835-77 Forged Bronze
8" W., 19-5/8" ht.
Extends 10-5/8". H/CTR 10-5/8".
Two candelabra base lamps, each 60w max.

MEDIUM WALL LANTERN
P5836-77 Forged Bronze
8" W., 19-5/8" ht.
Extends 10-5/8". H/CTR 8".
Two candelabra base lamps, each 60w max.

LARGE WALL LANTERN
P5837-77 Forged Bronze
10" W., 26" ht.
Extends 13". H/CTR 9-1/2".
Three candelabra base lamps, each 60w max.

Meridian

FINISH

● Black - 31

Decorative shepherd hooks and acanthus leaf cast arms. Clear seeded glass urns in a die-cast aluminum Black frame.

P5520-31



POST LANTERN
P5420-31 Black
12″ dia., 26″ ht.
Fits 3″ post (sold separately).
Three candelabra base lamps, each 60w max.

HANGING LANTERN
P5520-31 Black
12″ dia., 24-1/4″ ht.
Overall ht. w/chain 99″; wire 15′
Three candelabra base lamps, each 60w max.

SMALL WALL LANTERN
P5820-31 Black
6-3/4″ W., 15″ ht.
Extends 9-5/8″. H/CTR 5-1/2″.
One medium base lamp, 100w max.

MEDIUM WALL LANTERN
P5822-31 Black
9″ W., 20-1/4″ ht.
Extends 12-1/2″. H/CTR 7-1/2″.
Two candelabra base lamps, each 60w max.

MEDIUM WALL LANTERN
P5823-31 Black
9″ W., 19-3/4″ ht.
Extends 12-1/2″. H/CTR 10″.
Two candelabra base lamps, each 60w max.



P5820-31



P5822-31



P5823-31



P5520-31



P5420-31

Ashmore

FINISHES

- Antique Bronze - 20
- Textured Black - 31

P5550-20



The Ashmore Collection features quill scrolled arms and decorative finials with etched water glass shades in a die-cast aluminum construction. This collection is ideal for illuminating new traditional and rustic settings.


P5550-20


P5550-31


P5562-20


P5562-31


P5450-20


P5450-31

POST LANTERN
P5450-20 Antique Bronze
P5450-31 Textured Black
9-5/8" dia., 23-3/4" ht.
Fits 3" post (sold separately).
Three candelabra base lamps, each 60w max.

HANGING LANTERN
P5550-20 Antique Bronze
P5550-31 Textured Black
9-5/8" dia., 17-3/4" ht.
Overall ht. w/ chain 92"; wire 10'.
Three candelabra base lamps, each 60w max.

FLUSH MOUNT
P5562-20 Antique Bronze
P5562-31 Textured Black
10-1/2" dia., 9-3/4" ht.
Two candelabra base lamps, each 60w max.

SMALL WALL LANTERN
P5649-20 Antique Bronze
P5649-31 Textured Black
6-5/8" dia., 14-7/8" ht.
Extends 9-3/8". H/CTR 4-1/2".
Two candelabra base lamps, each 60w max.

MEDIUM WALL LANTERN
P5650-20 Antique Bronze
P5650-31 Textured Black
8-5/8" dia., 16-1/2" ht.
Extends 10-3/8". H/CTR 4-1/2".
Three candelabra base lamps, each 60w max.

LARGE WALL LANTERN
P5651-20 Antique Bronze
P5651-31 Textured Black
9-5/8" dia., 20-1/2" ht.
Extends 12-3/4". H/CTR 7".
Three candelabra base lamps, each 60w max.

LARGE WALL LANTERN
P5652-20 Antique Bronze
P5652-31 Textured Black
8-5/8" dia., 26-1/2" ht.
Extends 12-3/8". H/CTR 19-1/8".
Three candelabra base lamps, each 60w max.

ONE-LIGHT WALL LANTERN
P5875-20MD Antique Bronze
8-3/8" W., 16-5/8" ht.
Extends 10-1/2". H/CTR 4-1/2".
One medium base lamp, each 100w max.

Ashmore


P5650-20


P5650-31


P5649-20


P5651-20


P5651-31


P5649-31


P5652-20


P5652-31


P5875-20MD

Andover

FINISHES

- Antique Bronze - 20
- Black - 31

The Andover Collection offers a mixture of styles to complement a variety of spaces. The Black finish features an etched glass pillar diffuser inside the clear water seeded glass gives off a soft glow of light. This Andover collection is ideal for illuminating farmhouse and coastal settings.



P5587-20





P5688-20



P5487-20

POST LANTERN*
P5487-20 Antique Bronze
9-1/2" sq., 21-1/2" ht.
Fits 3" post (sold separately).
Three candelabra base lamps, each 60w max.

HANGING LANTERN*
P5587-20 Antique Bronze
9-1/2" sq., 20" ht.
Overall ht. w/chain 94"; wire 10'.
Three candelabra base lamps, each 60w max.

MEDIUM WALL LANTERN*
P5688-20 Antique Bronze
7-1/2" W., 21-1/4" ht.
Extends 8-1/4". H/CTR 7-1/2".
Two candelabra base lamps, each 60w max.

**Hinged door for easy relamping.*

Andover



P5687-20



P6619-31CD



P5689-20



P6620-31MD



P5627-20



P6621-31MD

SMALL WALL LANTERN
P5687-20 Antique Bronze
5-1/2" W., 12-3/4" ht.
Extends 6-1/4". H/CTR 6-1/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN*
P5689-20 Antique Bronze
9-1/2" W., 26-1/4" ht.
Extends 10-1/4". H/CTR 9".
Three candelabra base lamps,
each 60w max.

EXTRA LARGE WALL LANTERN*
P5627-20 Antique Bronze
12-1/2" W., 34-1/2" ht.
Extends 13-1/2". H/CTR 11-3/4".
Four candelabra base lamps,
each 60w max.

SMALL WALL LANTERN
P6619-31CD Black
5-5/8" W., 13-3/8" ht.
Extends 6-3/8". H/CTR 6-3/8".
One candelabra base lamp,
60w max.

MEDIUM WALL LANTERN
P6620-31MD Black
7-1/2" W., 18-3/8" ht.
Extends 8-3/8". H/CTR 10-1/2".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P6621-31MD Black
9-1/2" W., 26-1/8" ht.
Extends 10-1/4". H/CTR 12-3/4".
One medium base lamp,
100w max.

**Hinged door for easy relamping.*

Botta

FINISH

● Antique Bronze - 20

P5560-20



Provide a casual, rustic feel to interior and exterior spaces with a vintage flair with the Botta Collection. Finely crafted metal accents create a light-house inspired design with a clear seeded glass shade for extra visual character.



P6043-20



P5560-20



P6050-20



P5561-20



P6436-20

SMALL HANGING LANTERN
P5560-20 Antique Bronze
6-1/4" dia., 9-3/4" ht.
Overall ht. w/chain 76"; wire 15'.
One medium base lamp,
100w max.

MEDIUM HANGING LANTERN
P5561-20 Antique Bronze
7-3/4" dia., 12" ht.
Overall ht. w/chain 78"; wire 15'.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P6043-20 Antique Bronze
6-1/4" W., 11-5/8" ht.
Extends 6-1/2". H/CTR 8-7/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P6050-20 Antique Bronze
7-3/4" W., 13-7/8" ht.
Extends 8-3/8". H/CTR 11".
One medium base lamp,
100w max.

POST LANTERN
P6436-20 Antique Bronze
Fits 3" post (sold separately)
7-3/4" dia., 16" ht.
One medium base lamp,
each 100w max.

Hollingsworth

FINISH
● Black - 031

P550029-031



Hollingsworth lanterns feature a crisscross design that surrounds clear seeded glass, emulating popular Farmhouse décor. Ideal for a variety of transitional exteriors when paired with either vintage or traditional bulbs. Includes wall, hanging and post options.



P560080-031



P560081-031



P560082-031

P550029-031





P540029-031

SMALL WALL LANTERN
P560080-031 Black
6″ W., 14-1/2″ ht.
Extends 8-1/8″. H/CTR 7″.
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560081-031 Black
8″ W., 19″ ht.
Extends 10-5/8″. H/CTR 8-5/8″.
One medium base lamp,
100w max.

LARGE WALL LANTERN
P560082-031 Black
10″ W., 24″ ht.
Extends 13-1/8″. H/CTR 11-1/8″.
One medium base lamp,
100w max.

HANGING LANTERN
P550029-031 Black
10″ dia., 20-1/4″ ht.
Overall ht. w/chain 94″, wire 10′.
One medium base lamp,
100w max.

POST LANTERN
P540029-031 Black
10″ dia., 23″ ht.
Fits 3″ post (sold separately).
One medium base lamp,
100w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

Haslett

FINISHES

- Black - 031
- Antique Pewter - 103

P550031-031



Haslett lanterns feature a design with intersecting linear details that surrounds clear seeded glass. Coastal-inspired frame is suitable to complement architecture with Farmhouse flair. Includes wall, hanging and post options.



P560094-031



P560095-031



P560096-031

P550031-031





P540031-031

POST LANTERN
P540031-031 Black
7-1/2" dia., 18" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN
P550031-031 Black
7-1/2" dia., 16-1/4" ht.
Overall ht. w/chain 9"; wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P560094-031 Black
6-1/2" W., 14" ht.
Extends 8-1/4". H/CTR 7-1/2".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560095-031 Black
7-1/2" W., 18-1/8" ht.
Extends 10". H/CTR 8-3/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P560096-031 Black
9-3/8" W., 22-1/8" ht.
Extends 12". H/CTR 9-7/8".
One medium base lamp,
100w max.

Haslett



P550031-103



P540031-103



P560094-103



P560095-103



P560096-103

POST LANTERN
P540031-103 Antique Pewter
7-1/2" dia., 18" ht.
One medium base lamp,
100w max.
Fits 3" post (sold separately).

HANGING LANTERN
P550031-103 Antique Pewter
7-1/2" dia., 16-1/4" ht.
Overall ht. w/chain 9"; wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P560094-103 Antique Pewter
6-1/2" W., 14" ht.
Extends 8-1/4". H/CTR 7-1/2".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560095-103 Antique Pewter
7-1/2" W., 18-1/8" ht.
Extends 10". H/CTR 8-3/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P560096-103 Antique Pewter
9-3/8" W., 22-1/8" ht.
Extends 12". H/CTR 9-7/8".
One medium base lamp,
100w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

Featuring Haslett
Image: Stephen Aexander Homes

Take Farmhouse Up A Notch

Contemporary Craftsman meets Farmhouse style when a home's exterior features wood cladding, a covered front porch, and gabled rooflines.

1

Add exposed rafter detailing along the porch and dormer eaves for an authentic Craftsman touch.

2

Bright blue doors and pottery make entryways a welcoming focal point.

3

The Haslett hanging lantern and wall lantern at the doors are beacons of simple and classic style.




1
3

Cedar Springs

P550070-030

FINISHES

- White - 030
- Black - 031
- Red - 039
- Pistachio - 079
- Metallic Gray - 082
- Navy - 091

A fun take on the traditional warehouse shade, the Cedar Springs Collection features a signature gooseneck arm and a smooth, simple, metal shade. This modern collection provides excellent task lighting for reading a book in your bedroom or illuminating a doorway in your home. Dark Sky Compliant.

Traditional Warehouse



Smooth Design

Simple Metal Shade



P550070-030



P550070-031



P550070-039



P550070-079



P550070-082



P550070-091

ONE-LIGHT SEMI-FLUSH
P550070-030 White
P550070-031 Black
P550070-039 Red
P550070-079 Pistachio
P550070-082 Metallic Gray
P550070-091 Navy
13-1/4" dia., 9-1/2" ht.
One medium base lamp,
100w max.

All fixtures shown with F7ST19DLED927/JA8 vintage lamps, not included. See page 824.

LARGE WALL LANTERN
P560091-030 White
P560091-031 Black
P560091-039 Red
P560091-079 Pistachio
P560091-082 Metallic Gray
P560091-091 Navy
13-1/4" W., 11-1/4" ht.
Extends 21-5/8". H/CTR 7-1/4".
One medium base lamp,
100w max.



P560091-030



P560091-031



P560091-039



P560091-079



P560091-082



P560091-091

Holcombe

FINISH

● Black - 031

A nautical-inspired collection ideal for a variety of exteriors, including Coastal, Transitional and Urban Industrial settings. Black lanterns with clear seeded glass feature a hint of brushed nickel on the interior. Geometric details offer a finishing touch for wall, hanging and post lantern options.

P550025-031





P560065-031



P560066-031



P560067-031



P550025-031



P540025-031

POST LANTERN
P540025-031 Black
10-1/2" dia., 18-1/4" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN
P550025-031 Black
10-1/2" dia., 16-5/8" ht.
Overall ht. w/chain 91-1/2", wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P560065-031 Black
6-3/8" W., 10-5/8" ht.
Extends 8". H/CTR 3-7/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560066-031 Black
8-1/4" W., 13-5/8" ht.
Extends 9-3/8". H/CTR 3-5/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P560067-031 Black
10-1/2" W., 16" ht.
Extends 12-1/4". H/CTR 3-5/8".
One medium base lamp,
100w max.

Laine

FINISH

● Architectural Bronze - 129

P550022-129



Laine features a cylindrical frame accented with clear glass and metallic elements. Traditional Architectural Bronze profile is paired with vintage gold accents. Wall lantern option features an arm that resembles a pipe fitting, offering an industrial-inspired appeal. Available in wall, hanging and post lantern options.



P560059-129



P560060-129



P560061-129

P550022-129





P540022-129

POST LANTERN
P540022-129 Architectural Bronze
9-3/4" dia., 18-3/4" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN
P550022-129 Architectural Bronze
9-3/4" dia., 15-7/8" ht.
Overall ht. w/chain 91", wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P560059-129 Architectural Bronze
6-1/2" W., 12-1/2" ht.
Extends 7-1/4". H/CTR 3".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560060-129 Architectural Bronze
8" W., 15" ht.
Extends 8-7/8". H/CTR 2-3/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P560061-129 Architectural Bronze
9-3/4" W., 16-1/2" ht.
Extends 10-5/8". H/CTR 3-1/8".
One medium base lamp,
100w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

Englewood

FINISHES

- Antique Bronze - 020
- Black - 031
- Antique Pewter - 103

P540032-020

Inspired by the warmth and beauty of hammered copper home accents, Englewood's design displays elements of rustic craftsmanship. Available in Antique Bronze, Black or Antique Pewter, the inside of the shade features a metallic finish, offering higher illumination reflection. Antique Bronze and Black finishes feature a copper inside shade, while the Antique Pewter finish is paired with a metallic silver inner shade. The post top fixture adds the finishing touch to outdoor settings, giving eye-catching appeal to Farmhouse and cottage Rustic homes and is Dark Sky compliant.

Rustic Craftsmanship



Dark Sky Compliant



P540032-020



P540032-031



P540032-103

ONE-LIGHT POST LANTERN
P540032-020 Antique Bronze
P540032-031 Black
P540032-103 Antique Pewter
16" W., 13-1/2" ht. Extends 12".
Fits 3" post (sold separately).
One medium base lamp,
100w max.

SMALL WALL LANTERN
P560097-020 Antique Bronze
P560097-031 Black
P560097-103 Antique Pewter
8" W., 9-3/4" ht.
Extends 10". H/CTR 7-1/2".
One medium base lamp,
100w max.

HANGING LANTERN
P550032-020 Antique Bronze
P550032-031 Black
P550032-103 Antique Pewter
12" W., 8" ht.
Overall ht. w/cord 122"; wire 10'.
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560098-020 Antique Bronze
P560098-031 Black
P560098-103 Antique Pewter
12" W., 10-3/8" ht.
Extends 13-3/4". H/CTR 8".
One medium base lamp,
100w max.

All fixtures:



P550032-020



P550032-031



P550032-103



P560097-020



P560097-031



P560097-103



P560098-020



P560098-031



P560098-103

Callahan LED

FINISHES

- Antique Bronze - 020
- Antique Pewter - 103

P560052-020-30

Callahan draws inspiration from farmhouse decor. Hidden within this vintage frame is a modern LED light source that delivers energy-efficient performance. The inner surface of the shade is accented with a contrasting finish to complete the nostalgic look. Additionally, the full reflector provides illumination that is compliant with Dark Sky requirements for full cutoff lighting.

Modern LED Light



Farmhouse Décor



P560052-020-30



P560052-103-30

Interior Contrasting Finish



P560053-020-30



P560053-103-30

SMALL WALL LANTERN
P560052-020-30 Antique Bronze
P560052-103-30 Antique Pewter
8-1/2" W., 10" ht.
Extends 8-7/8". H/CTR 3-3/4".
One 9w LED module , 3000K,
90CRI, 624 source lumens.

MEDIUM WALL LANTERN
P560053-020-30 Antique Bronze
P560053-103-30 Antique Pewter
11" W., 11-1/2" ht.
Extends 11-1/2". H/CTR 4-1/4".
One 17w LED module, 3000K,
90CRI, 1273 source lumens.

All fixtures:

JA8



Featuring Callahan and Whisp

Homage to Days Past

Rustic Farmhouse style is a nod to days gone by. To achieve this look, use an earthy color palette accessorized with furnishings handcrafted from sturdy materials like distressed wood and vintage iron. Add lighting that hints of times past, like the Whisp chandelier with its sweeping metal arms and candelabra lights. A pair of Callahan wall sconces has the feel of an age-worn lantern to complete the lived-in rustic look.

Wish LED

FINISHES

- Antique Bronze - 20
- Black - 31

P6085-3130K9

Wish maximizes aesthetics in outdoor areas for those who desire to preserve the exterior environment. Included dark sky shield provides full cut off illumination or remove for a traditional lighting effect. Antique Bronze finish has etched umber linen glass. Black finish has etched white linen glass.





P6084-3130K9



P6084-2030K9



P6085-3130K9



P6085-2030K9

SMALL WALL LANTERN
P6084-2030K9 Antique Bronze
P6084-3130K9 Black
7" W., 10-3/8" ht.
Extends 8-5/8". H/CTR 3-1/8".
One 9w LED module, 3000K, 90CRI, 623 source lumens.

MEDIUM WALL LANTERN
P6085-2030K9 Antique Bronze
P6085-3130K9 Black
9" W., 12-1/2" ht.
Extends 10-1/2". H/CTR 3-1/8".
One 17w LED module, 3000K, 90CRI, 1211 source lumens.

POST LANTERN*
P6424-2030K9 Antique Bronze
P6424-3130K9 Black
Dark Sky shield not included.
9" dia., 15-1/4" ht.
Fits 3" post (sold separately).
One 9w LED module, 3000K, 90CRI, 623 source lumens.



Dark sky cylinder included, except the post lantern.

All fixtures:

**Post lantern is not Dark Sky Compliant.*



P6424-3130K9*



P6424-2030K9*

Wish

FINISHES

- Antique Bronze - 20
- Black - 31

P6524-20



P6524-31



P6524-20





P6084-31



P6084-20



P6085-31



P6085-20

SMALL WALL LANTERN
P6084-20 Antique Bronze
P6084-31 Black
7″ W., 10-3/8″ ht.
Extends 8-5/8″. H/CTR 3-1/8″.
One medium base lamp,
75w max.

MEDIUM WALL LANTERN
P6085-20 Antique Bronze
P6085-31 Black
9″ W., 12-1/2″ ht.
Extends 10-1/2″. H/CTR 3-1/8″.
One medium base lamp,
100w max.

POST LANTERN*
P6424-20 Antique Bronze
P6424-31 Black
Dark Sky shield not included.
9″ dia., 15-1/4″ ht.
Fits 3″ post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN
P6524-20 Antique Bronze
P6524-31 Black
9″ dia., 12-1/2″ ht.
Overall ht. w/chain 87-1/2″; wire 15′.
One medium base lamp,
100w max.



Dark sky cylinder included, except the post lantern.

**All fixtures except post lantern:*





P6424-31*



P6424-20*

Derby

FINISH

● Espresso - 84

Derby boasts an Espresso powder coat finish. Features a blown, clear seeded glass diffuser encased in a cast aluminum black frame. Espresso finish on roof and back plate.

P5579-84





P5749-84



P5579-84



P5750-84



P6017-84

POST LANTERN
P5479-84 Espresso
8-1/2" dia., 13-3/8" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN
P5579-84 Espresso
8-1/2" dia., 12-3/8" ht.,
Overall ht. w/chain 86"; wire 15'.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P5749-84 Espresso
6-1/2" W., 8-3/8" ht.
Extends 7-5/8". H/CTR 3".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P5750-84 Espresso
8-1/2" W., 11" ht.
Extends 9-5/8". H/CTR 4-1/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P5751-84 Espresso
10-5/8" W., 15" ht.
Extends 14-1/8". H/CTR 3-3/8".
One medium base lamp,
100w max.

FLUSH MOUNT
P6017-84 Espresso
10" sq., 5-1/2" ht.
Two medium base lamps,
each 60w max.



P5751-84



P5479-84

Derby LED

FINISH

Antique Bronze - 20

P5750-2030K9

Craftsman styling marries traditional and rustic details. Derby boasts an artistic glass diffuser with a die-cast aluminum, powder coated Antique Bronze frame.

Rustic Details



Craftsman Style

Artistic Glass



P5749-2030K9



P5750-2030K9



P5751-2030K9

SMALL WALL LANTERN
P5749-2030K9 Antique Bronze
6-1/2" W., 8-3/8" ht.
Extends 7-3/8". H/CTR 3".
One 9w LED module, 3000K,
90CRI, 623 source lumens.

MEDIUM WALL LANTERN
P5750-2030K9 Antique Bronze
8-1/2" W., 11-1/4" ht.
Extends 9-3/8". H/CTR 4-1/4".
One 9w LED module, 3000K,
90CRI, 623 source lumens.

LARGE WALL LANTERN
P5751-2030K9 Antique Bronze
10-5/8" W., 15-1/2" ht.
Extends 11-5/8". H/CTR 3-3/8".
One 9w LED module, 3000K,
90CRI, 623 source lumens.

All fixtures:

Residence

FINISH

● Antique Bronze - 20

P6552-20



A rich earthy palette, geometric details and textured art glass characterize residence – a truely craftsman style with a die-cast aluminum, powder coated frame.



P6052-20



P6552-20



P6053-20



P6055-20

SMALL WALL LANTERN
P6052-20 Antique Bronze
6″ W., 9-1/4″ ht.
Extends 6-7/8″. H/CTR 3-1/2″.
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P6053-20 Antique Bronze
8″ W., 12-3/8″ ht.
Extends 9″. H/CTR 5″.
One medium base lamp,
100w max.

LARGE WALL LANTERN
P6054-20 Antique Bronze
10″ W., 15-3/8″ ht.
Extends 11-1/8″. H/CTR 5-5/8″.
One medium base lamp,
100w max.

FLUSH MOUNT
P6055-20 Antique Bronze
12″ W., 5″ ht.
Two medium base lamps,
each 75w max.

POST LANTERN
P6452-20 Antique Bronze
8″ W., 15-3/4″ ht.
Fits 3″ post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN
P6552-20 Antique Bronze
8″ sq., 12-5/8″ ht.
Overall ht. w/ chain 86-1/4″; wire 10′.
One medium base lamp,
100w max.



P6054-20



P6452-20

Torrey

FINISH

Antique Bronze - 020

P550060-020



Step outside and smell the fresh air without ever venturing far from your home with the Torrey Collection. Gorgeous, etched seeded glass panes are held in place by handsome antique bronze frames adorned with intricate, forest-inspired designs that captures the beautiful essence of the wild outdoors.



P560161-020



P550060-020



P560162-020



P550059-020

POST LANTERN
P540060-020 Antique Bronze
Fits 3" post (sold separately)
7" sq., 15" ht.
One medium base lamp,
100w max.

FLUSH MOUNT
P550059-020 Antique Bronze
11-3/4" sq., 5-1/2" ht.
Two medium base lamps,
each 60w max.

HANGING LANTERN
P550060-020 Antique Bronze
7" sq., 12-5/8" ht.
Overall ht. w/chain 87-1/2", wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P560161-020 Antique Bronze
5-1/2" W., 10-5/8" ht.
Extends 6-3/4". H/CTR 6".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560162-020 Antique Bronze
7" W., 13-1/2" ht.
Extends 8-3/8". H/CTR 8-3/4".
One medium base lamp,
100w max.



P540060-020

Mac

FINISH
● Black - 31

P5559-31



Classic Arts and Crafts inspired profile. Cast aluminum construction. clear water glass and decorative bottom detail. Textured Black powder coated finish.


P5906-31


P5559-31


P5907-31


P6023-31


P5999-31


P5459-31

POST LANTERN
P5459-31 Black
9-1/2" sq., 16-1/2" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN
P5559-31 Black
8-1/2" sq., 14-7/8" ht.,
Overall ht. w/chain 87"; wire 15'.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P5906-31 Black
6" sq., 8-1/2" ht.
Extends 7-1/8". H/CTR 5".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P5907-31 Black
8-1/2" sq., 12" ht.
Extends 10". H/CTR 6-3/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P5999-31 Black
11" sq., 16-3/4" ht.
H/CTR 7-3/4".
One medium base lamp,
100w max.

FLUSH MOUNT
P6023-31 Black
11" sq., 7" ht.
Two medium base lamps,
each 100w max.

Merit

FINISH

● Black - 31

P6500-31



Square etched glass shade within rectilinear frame. Cast aluminum construction. Frame showcases pierced grid pattern with Black powder coat finish.



P6000-31



P6001-31



P6002-31



P6500-31



P6400-31

SMALL WALL LANTERN
P6000-31 Black
5-1/4″ sq., 8″ ht.
Extends 6-1/4″. H/CTR 2-1/2″.
One medium base lamp,
60w max.

MEDIUM WALL LANTERN
P6001-31 Black
7-3/4″ sq., 12-1/4″ ht.
Extends 9″. H/CTR 3″.
One medium base lamp,
100w max.

LARGE WALL LANTERN
P6002-31 Black
10″ sq., 15-3/4″ ht.
Extends 11-3/8″. H/CTR 4″.
One medium base lamp,
100w max.

POST LANTERN
P6400-31 Black
10″ sq., 18-3/4″ ht.
Fits 3″ post (sold separately).
One medium base lamp,
100w max.


HANGING LANTERN
P6500-31 Black
10″ sq., 17″ ht.
Overall ht. w/chain 91″; wire 10′.
One medium base lamp,
100w max.

Oakcliff

FINISH

● Antique Bronze - 020

P550055-020



The Oakcliff Collection is a fine illustration of how rustic style can be comfortable and contemporary. Each fixture displays a cabin-inspired design with the ability to produce a gentle, modern mountain glow ideal for your favorite lodge escape.

P550055-020





P560151-020



P560152-020

HANGING LANTERN
P550055-020 Antique Bronze
12-7/8″ sq., 11-1/8″ ht.
Overall ht. w/chain 86″, wire 10′.
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560151-020 Antique Bronze
9-5/8″ sq., 8-1/8″ ht.
Extends 10-3/8″. H/CTR 2-1/4″.
One medium base lamp,
100w max.

LARGE WALL LANTERN
P560152-020 Antique Bronze
12-7/8″ sq., 10-3/8″ ht.
Extends 13-5/8″. H/CTR 2-1/4″.
One medium base lamp,
100w max.

Arts & Crafts

FINISH
● Weathered Bronze - 46

P5628-46

Reminisce under lighting inspired by the bungalows of the 1900's. Charming highlights include hipped-pitch roof and frame. Honey art glass with Weathered Bronze finish. Die-cast aluminum construction.




P5628-46


P5629-46


P5428-46

POST LANTERN
P5428-46 Weathered Bronze
10" W., 18-1/8" ht.
Fits 3" post (sold separately).
One medium base lamp,
150w max.

MEDIUM WALL LANTERN
P5628-46 Weathered Bronze
6-5/8" W., 10-1/2" ht.
Extends 7-1/2". H/CTR 2-1/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P5629-46 Weathered Bronze
10" W., 15-1/4" ht.
Extends 10-3/4". H/CTR 10".
One medium base lamp,
150w max.

Trellis

FINISH

● Antique Bronze - 020

P550058-02



Create a home that is undeniably beautiful with the intricate craftsmanship of the Trellis Collection. Beautiful white, art glass panels are housed in antique bronze frames decorated with nature-inspired designs that will capture the gazes and hearts of both family members and guests.



P560159-020



P550058-020



P560160-020



P550057-020



P540058-020

POST LANTERN
P540058-020 Antique Bronze
Fits 3" post (sold separately)
7-1/2" sq., 15-3/8" ht.
One medium base lamp,
100w max.

FLUSH MOUNT
P550057-020 Antique Bronze
11-3/4" sq., 5-1/2" ht.
Two medium base lamps,
each 60w max.

SMALL WALL LANTERN
P560159-020 Antique Bronze
6-1/2" W., 10" ht.
Extends 5-1/2". H/CTR 4-3/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560160-020 Antique Bronze
7-1/2" W., 12-1/2" ht.
Extends 7". H/CTR 6".
One medium base lamp,
100w max.

HANGING LANTERN
P550058-020 Antique Bronze
7-1/2" sq., 13-1/2" ht.
Overall ht. w/chain 88-1/2", wire 10'.
One medium base lamp,
100w max.

Boxwood

FINISH

● Antique Bronze - 020

Geometric details in Boxwood's design enhance Craftsman-inspired architecture. The construction features clear seeded glass while traditional or vintage lamping completes the authentic style finished in Antique Bronze.

P550039-020



Architectural

Craftsman Inspired

Clear Seeded Glass



P560110-020



P550039-020



P560111-020



P550038-020



P560112-020



P540010-020

POST LANTERN
P540010-020 Antique Bronze
9" W., 18-1/4" ht.
Fits 3" post (sold separately).
One medium base lamp, 60w max.

FLUSH MOUNT
P550038-020 Antique Bronze
11-3/8" W., 4-1/2" ht.
Two medium base lamps, each 60w max.

HANGING LANTERN
P550039-020 Antique Bronze
8-7/8" W., 17-1/2" ht.
Overall ht. w/chain 92-1/2"; wire 10'.
One medium base lamp, 60w max.

SMALL WALL LANTERN
P560110-020 Antique Bronze
6-1/4" W., 11-3/4" ht.
Extends 6-1/4". H/CTR 9-5/8".
One medium base lamp, 60w max.

MEDIUM WALL LANTERN
P560111-020 Antique Bronze
7-5/8" W., 14-1/8" ht.
Extends 7-1/4". H/CTR 12".
One medium base lamp, 60w max.

LARGE WALL LANTERN
P560112-020 Antique Bronze
9" W., 16-1/2" ht.
Extends 8-1/2". H/CTR 14-1/4".
One medium base lamp, 60w max.

Haddon

FINISHES

- Antique Bronze - 020
- Black - 031

P550015-020



A classic New England coach light, the Haddon lanterns feature either a clear seeded shade paired with an Antique Bronze frame or an etched opal diffuser paired with classic Black. The wire surround is a classic industrial-inspired detail that provides nostalgic charm.

P550014-031



P550015-020





P550016-031



P550017-020



P560042-031



P560043-020



P540014-031



P540015-020

POST LANTERN
P540014-031 Black
P540015-020 Antique Bronze
10" dia., 16-1/8" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN
P550014-031 Black
P550015-020 Antique Bronze
10" dia., 12-3/4" ht.
Overall ht. w/chain 88", wire 10'.
One medium base lamp,
100w max.

FLUSH MOUNT
P550016-031 Black
P550017-020 Antique Bronze
10" dia., 10" ht.
One medium base lamp,
75w max.

MEDIUM WALL LANTERN
P560042-031 Black
P560043-020 Antique Bronze
10" W., 17" ht.
Extends 10-5/8".
H/CTR 9-1/4".
One medium base lamp,
100w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.



Featuring Haddon
Image: Green Tech Homes, Piper Stromatt and 161 Photography

Seamless Inside-Outside Style

When the entryway of a home features a sitting area, you can connect with nature and spend quality time with loved ones. Sometimes simplicity is key. Choose lighting that shares its glimmer inside while adding to the beauty and functionality of the outside porch that is nestled just off the front door. Rather than mounting a traditional outdoor wall sconce, hang a pendant like the Haddon hanging lantern to illuminate with nostalgic charm.

Prairie

FINISHES
- Brushed Nickel - 09
- Gilded Iron - 71
- Burnished Chestnut - 86

P5763-09

Unique cantilevered arms, distinctive roof and clear seeded glass. Aluminum and brass construction in Brushed Nickel, Gilded Iron or Burnished Chestnut finishes.





P5764-09



P5763-09



P5764-71



P5763-71



P5764-86



P5763-86

SMALL WALL LANTERN
P5763-09 Brushed Nickel*
P5763-71 Gilded Iron
P5763-86 Burnished Chestnut
6-3/8" W., 9-1/8" ht.
Extends 8-1/2". H/CTR 5-1/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P5764-09 Brushed Nickel*
P5764-71 Gilded Iron
P5764-86 Burnished Chestnut
10" W., 13-1/2" ht.
Extends 12-1/2". H/CTR 7-1/2".
One medium base lamp,
100w max.

**Brass construction*

Pedigree

FINISH

● Autumn Haze - 97

P5981-97MD

The Pedigree Collection features cast pyramidal black and Autumn haze uprights. Etched seeded glass is housed in an energy efficient, die-cast aluminum housing. This collection is ideal for transitional and new traditional settings.





P5980-97MD



P5981-97MD

SMALL WALL LANTERN
P5980-97MD Autumn Haze
7″ W., 10″ ht.
Extends 8-1/2″. H/CTR 2-5/8″.
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P5981-97MD Autumn Haze
9″ W., 13-3/8″ ht.
Extends 10-1/2″. H/CTR 5-3/8″.
One medium base lamp,
100w max.

LARGE WALL LANTERN
P5982-97MD Autumn Haze
11-1/2″ W., 16-1/2″ ht.
Extends 13-1/2″. H/CTR 5-3/4″.
One medium base lamp,
100w max.



P5982-97MD

Brookside

FINISHES
- Copper - 14
- Gilded Iron - 71
- Antique Nickel - 81

P5721-81

Get inspired from vintage undertones and train station styling with this outdoor lantern collection. Available in aluminum with Gilded Iron finish or solid brass Antique Nickel or solid Copper that ages to a patina finish. Dark Sky compliant.




P5721-81


P5721-14


P5721-71

SMALL WALL LANTERN
P5721-14 Copper
P5721-71 Gilded Iron
P5721-81 Antique Nickel
8" W., 9-3/4" ht.
Extends 9-3/4". H/CTR 5-3/4".
One medium base lamp,
60w max.


P5722-81


P5722-71


P5722-14

MEDIUM WALL LANTERN
P5722-14 Copper
P5722-71 Gilded Iron
P5722-81 Antique Nickel
10" W., 10-3/4" ht.
Extends 11-3/4". H/CTR 6-1/2".
One medium base lamp,
75w max.


P5723-81


P5723-71


P5723-14

LARGE WALL LANTERN
P5723-14 Copper
P5723-71 Gilded Iron
P5723-81 Antique Nickel
12" W., 12-3/8" ht.
Extends 13-1/8". H/CTR 6-7/8".
One medium base lamp,
100w max.

All fixtures:

Brookside LED

FINISHES
- Copper - 14
- Gilded Iron - 71
- Antique Nickel - 81

P5723-7130K9



Farmhouse Appeal

Modern Tech

Raw Metal Styles

LARGE WALL LANTERN
P5723-1430K9 Copper
P5723-7130K9 Gilded Iron
P5723-8130K9 Antique Nickel
12" W., 12-1/4" ht.
Extends 13-1/4". H/CTR 6-7/8".
One 17w LED module, 3000K, 90CRI, 1211 source lumens.



P5723-1430K9



P5723-8130K9



P5723-7130K9

Featuring Brookside
Image: Schumacher Homes and Possibilities for Design



Arrive LED

FINISH

● Black - 31

P6527-3130K9



Arrive LED lanterns feature a die-cast aluminum powder coated frame and heavily textured glass to create a unique visual effect.



P6067-3130K9



P6527-3130K9



P6068-3130K9



P6069-3130K9

SMALL WALL LANTERN
P6067-3130K9 Black
6" W., 8-3/4" ht.
Extends 7-3/8". H/CTR 4".
One 9w LED module, 3000K, 90CRI, 623 source lumens.

MEDIUM WALL LANTERN
P6068-3130K9 Black
7-1/2" W., 11-1/8" ht.
Extends 8-3/4". H/CTR 5-1/4".
One 9w LED module, 3000K, 90CRI, 623 source lumens.

LARGE WALL LANTERN
P6069-3130K9 Black
9" W., 13" ht.
Extends 10-1/4". H/CTR 5-3/4".
One 17w LED module, 3000K, 90CRI, 1211 source lumens.

EXTRA LARGE WALL LANTERN
P6076-3130K9 Black
11" W., 16" ht.
Extends 12-1/4". H/CTR 8-5/8".
One 17w LED module, 3000K, 90CRI, 1211 source lumens.

POST LANTERN
P6427-3130K9 Black
9" sq., 15-7/8" ht.
Fits 3" post (order separately).
One 17w LED module, 3000K, 90CRI, 1211 source lumens.

HANGING LANTERN
P6527-3130K9 Black
9" sq., 15-1/8" ht. Overall ht. w/chain 88-1/4"; wire 15'.
One 17w LED module, 3000K, 90CRI, 1211 source lumens.



P6076-3130K9



P6427-3130K9

All fixtures:

Penfield

FINISH
● Oil Rubbed Bronze - 108

P5896-108

Reinvent exterior areas with smooth curves. Highlighted by clear glass exterior surrounding an opal glass interior diffuser. Aluminum and brass construction.

Smooth Curves



Opal Glass Interior



P5895-108



P5896-108



P5899-108

SMALL WALL LANTERN
P5895-108 Oil Rubbed Bronze
6-1/2″ W., 9-3/4″ ht.
Extends 8-1/2″. H/CTR 5″.
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P5896-108 Oil Rubbed Bronze
8″ W., 11-3/4″ ht.
Extends 10-1/4″. H/CTR 6″.
One medium base lamp,
100w max.

LARGE WALL LANTERN
P5899-108 Oil Rubbed Bronze
8″ W., 24″ ht.
Extends 10-3/8″. H/CTR 12-1/4″.
Two medium base lamps,
each 75w max.





Irondale

FINISH

● Matte Black - 031

P550054-031



Incorporate memorable, modern lighting with the Irondale collection. A matte black frame holds a clear glass shade that harbors an etched glass diffuser inside ready to provide a main door or foyer with a lovely, timeless ambiance.



P560148-031



P560149-031



P560150-031

P550054-031





P540054-031

POST LANTERN
P540054-031 Matte Black
9-1/2" dia., 20-1/2" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN
P550054-031 Matte Black
9-1/2" dia., 18-1/2" ht.
Overall ht. w/chain 93", wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P560148-031 Matte Black
6-1/2" W., 12" ht.
Extends 7-3/8". H/CTR 9-1/2".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560149-031 Matte Black
7-7/8" W., 15-1/2" ht.
Extends 8-1/2". H/CTR 13".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P560150-031 Matte Black
9" W., 18-1/2" ht.
Extends 10-1/2". H/CTR 16".
One medium base lamp,
100w max.

Felton

FINISH

● Matte Black - 031

P550047-031



Achieve a stylish and peaceful home environment you've been waiting for with the Felton Collection. A matte black frame holds elongated, rippled glass panes in a simple, intelligent design just right for gently illuminating a doorway or modern-style bedroom.



P560129-031



P550047-031



P560131-031



P540024-031



P560130-031

POST LANTERN
P540024-031 Matte Black
7-1/4" sq., 18-3/4" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN
P550047-031 Matte Black
7" sq., 17-5/8" ht.
Overall ht. w/chain 83", wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P560129-031 Matte Black
4-1/2" W., 12-3/4" ht.
Extends 6-1/2". H/CTR 2-3/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560130-031 Matte Black
5-5/8" W., 15-3/8" ht.
Extends 7-3/4". H/CTR 3-3/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P560131-031 Matte Black
7" W., 18-1/4" ht.
Extends 9-1/4". H/CTR 3-3/8".
One medium base lamp,
100w max.

Hawthorne

FINISH
● Black - 31

This outdoor lantern collection takes a modern approach to the popular Prairie design style. Black with etched seeded glass.

P5523-31





P5624-31



P5523-31



P5625-31



P5513-31



P5665-31



P5413-31

POST LANTERN
P5413-31 Black
7-1/2″ dia., 17-1/4″ ht.
Fits 3″ post (order separately).
Two candelabra base lamps, each 60w max.

SMALL HANGING LANTERN
P5513-31 Black
5″ dia., 9-1/8″ ht.
Overall ht. w/stem 74″, wire 10′.
One medium base lamp, 100w max.

LARGE HANGING LANTERN
P5523-31 Black
7-1/2″ dia., 14-7/8″ ht.
Overall ht. w/stem 88″, wire 10′.
One medium base lamp, 100w max.

SMALL WALL LANTERN
P5624-31 Black
5″ W., 9-5/8″ ht.
Extends 6-1/2″. H/CTR 2-3/4″.
One medium base lamp, 100w max.

MEDIUM WALL LANTERN
P5625-31 Black
6″ W., 12-5/8″ ht.
Extends 8-3/8″. H/CTR 3-3/8″.
One medium base lamp, 100w max.

LARGE WALL LANTERN
P5665-31 Black
7-1/2″ W., 16″ ht.
Extends 10-3/4″. H/CTR 4-1/8″.
One medium base lamp, 100w max.

Format

FINISH

● Black - 31

P6063-31



The Format collection is comprised of an oval form factor with grid overlay. Etched glass shades. Cast aluminum with a powder coat finish.



P6063-31



P6064-31



P6062-31



P6428-31

SMALL WALL LANTERN
P6062-31 Black
5-7/8" W., 7-5/8" ht.
Extends 4-7/8". H/CTR 2-3/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P6063-31 Black
7-3/8" W., 11-5/8" ht.
Extends 6". H/CTR 3-1/2".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P6064-31 Black
9-1/2" W., 16-1/8" ht.
Extends 7-1/2". H/CTR 4-5/8".
One medium base lamp,
100w max.

POST LANTERN
P6428-31 Black
9-1/2" W., 17-1/8" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

Compel

FINISH

● Black - 31

P6520-31



Modern forms and layered glass. Etched opal glass within seeded glass shade, offers design flexibility for exterior settings and in unexpected interior applications. Steel construction with a powder coat finish.



P6038-31



P6520-31



P6039-31



P6420-31

SMALL WALL LANTERN
P6038-31 Black
5-3/4" W., 9-7/8" ht.
Extends 7-1/4". H/CTR 5-1/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P6039-31 Black
7-7/8" W., 13-1/2" ht.
Extends 9-3/8". H/CTR 7-1/2".
One medium base lamp,
100w max.

POST LANTERN
P6420-31 Black
7-7/8" W., 21-5/8" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN
P6520-31 Black
7-7/8" dia., 15-3/8" ht.
Overall ht. w/chain 90"; wire 15'.
One medium base lamp,
100w max.

Fairview

FINISH
● Black - 31

P5775-31

Explore the great outdoors with classic details. Softly etched glass and a powder coat textured finish on aluminum frame.

Classic Details



Powder Coat Finish

Etched Glass



P5778-31



P5775-31



P5780-31



P5402-31

POST LANTERN
P5402-31 Textured Black
10-1/2" dia., 18-1/4" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

SMALL WALL LANTERN
P5775-31 Textured Black
6-1/2" W., 11-3/4" ht.
Extends 8-1/2". H/CTR 3-3/4".
One medium base lamp,
75w max.

MEDIUM WALL LANTERN
P5778-31 Textured Black
8-3/8" W., 14-1/2" ht.
Extends 11-1/4". H/CTR 10".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P5780-31 Textured Black
10-1/2" W., 17" ht.
Extends 12-1/4". H/CTR 12-1/2".
One medium base lamp,
100w max.

Greene Ridge

FINISHES

- Black - 031
- Architectural Bronze - 129

P550033-031



With its uncomplicated lines and tailored look, Greene Ridge unites simplicity and artistry in a tribute to its Craftsman-style inspiration. A strong, boxy shape tops a clear seeded glass shade in keeping with the utilitarian design and lack of curves that define the Arts and Crafts look.

P550033-031



P550033-129





P560099-031



P560099-129



P560100-031



P560100-129

HANGING LANTERN
P550033-031 Black
P550033-129 Architectural Bronze
6-3/4" sq., 14" ht.,
Overall ht. w/chain 88-1/2"; wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN
P560099-031 Black
P560099-129 Architectural Bronze
5-1/4" W., 11-5/8" ht.,
Extends 6-3/4". H/CTR 8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560100-031 Black
P560100-129 Architectural Bronze
6-3/4" W., 14-1/4" ht.,
Extends 8-1/4". H/CTR 10-3/4".
One medium base lamp,
100w max.

All fixtures shown with F7ST19DLED927/JA8 vintage lamps, not included. See page 824.

Beaufort

FINISH
● Black - 031

Beaufort is an understated lantern that draws its design from both industrial and nautical influences. A clear seeded glass diffuser works well with either traditional or vintage style lights.

P550019-031






P560049-031


P560050-031

HANGING LANTERN
P550019-031 Black
10" dia., 12 5/8" ht.
Overall Ht. w/stem 78-1/2", wire 10'.
One medium base lamp,
60w max.

SMALL WALL LANTERN
P560049-031 Black
8-5/8" W., 11-1/2" ht.
Extends 10-1/4". H/CTR 4-5/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560050-031 Black
10" W., 14-3/8" ht.
Extends 12-1/8". H/CTR 5-3/4".
One medium base lamp,
100w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

District

District's metal shade offers an industrial-inspired design. Available in both incandescent and LED versions, the versatile vintage form can be used in indoor and outdoor applications. Dark sky compliant.

FINISHES

- Antique Bronze - 20
- Metallic Gray -82

MEDIUM HANGING LANTERN
P5535-20 Antique Bronze
P5535-82 Metallic Gray
8" dia., 6-1/4" ht.
Overall ht. w/cord 130"; wire 12'.
One medium base lamp,
100w max.

LARGE HANGING LANTERN
P5551-20 Antique Bronze
P5551-82 Metallic Gray
12" dia., 8-1/4" ht.
Overall ht. w/cord 130"; wire 12'.
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P5622-20 Antique Bronze
P5622-82 Metallic Gray
8" W., 8-1/4" ht.
Extends 10-1/4". H/CTR 4-1/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P5623-20 Antique Bronze
P5623-82 Metallic Gray
12" W., 10-1/2" ht.
Extends 13-1/4". H/CTR 5".
One medium base lamp,
100w max.

All fixtures:


P5551-20


P5551-82


P5535-20


P5535-82


P5622-20


P5622-82


P5623-20


P5623-82

District LED



P5622-2030K9



P5622-8230K9



P5623-2030K9



P5623-8230K9

FINISHES

- Antique Bronze - 20
- Metallic Gray -82

MEDIUM WALL LANTERN
P5622-2030K9 Antique Bronze
P5622-8230K9 Metallic Gray
8" W., 8-1/4" ht.
Extends 10-1/4". H/CTR 4-1/8".
One 9w LED module, 3000K,
90CRI, 623 source lumens.

LARGE WALL LANTERN
P5623-2030K9 Antique Bronze
P5623-8230K9 Metallic Gray
12" W., 10-1/2" ht.
Extends 13-1/4". H/CTR 5".
One 9w LED module, 3000K,
90CRI, 623 source lumens.

All fixtures:



Pier 33

Outdoor hanging and wall lanterns from the Pier 33 collection feature coastal undertones and a design reminiscent of industrial spaces. LED and incandescent options are comprised of a die-cast frame. Clear seeded glass complements a Black finish.

FINISH

● Black - 031

MEDIUM WALL LANTERN
P560024-031 Black
8-1/8" W., 13" ht.
Extends 9". H/CTR 3-1/4".
One medium base lamp, 100w max.

MEDIUM LED WALL LANTERN
P560034-031-30 Black
8-1/8" dia., 13" ht.
Extends 9". H/CTR 3-1/4".
One 9w LED module, 3000K, 90CRI, 624 source lumens.

JA8

SMALL LED WALL LANTERN
P560071-031-30 Black
8-1/8" W., 8" ht.
Extends 9". H/CTR 3-1/8".
One 9w LED module, 3000K, 90CRI, 624 source lumens.

JA8

SMALL WALL LANTERN
P560089-031 Black
8-1/8" W., 8" ht.
Extends 9". H/CTR 3-1/8".
One medium base lamp, 100w max.

**Fixture shown with P7825-01 vintage lamps, not included. See page 824.*



P560024-031*



P560034-031-30



P560071-031-30



P560089-031*

Jack

Rectilinear design. Antique Bronze finish with etched umber flax glass. Black finish with etched white glass.

FINISHES

- Antique Bronze - 20
- Black - 31

SMALL WALL LANTERN
P5948-20 Antique Bronze
P5948-31 Black
6" W., 13-5/8" ht.
Extends 6-1/4". H/CTR 5-1/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P5949-20 Antique Bronze
P5949-31 Black
8" W., 15-1/4" ht.
Extends 6-1/4". H/CTR 5-7/8".
One medium base lamp,
100w max.



P5948-20



P5949-20



P5948-31



P5949-31

Bell

Featuring nautical undertones, the Bell outdoor collection offers cage lights reminiscent of industrial architecture. Ideal for use in both interior and exterior settings, this LED fixture is available in a wall mount option.

FINISHES

- Antique Bronze - 20
- Textured Graphite -136

WALL LANTERN
P5676-2030K9 Antique Bronze
P5676-13630K9 Textured Graphite
5-1/2" W., 10-5/8" ht.
Extends 7-3/8". H/CTR 3".
One 9w LED module, 3000K,
90CRI, 623 source lumens.



P5676-13630K9



P5676-2030K9

Peek-A-Boo

Etched glass shade "peeks through" arched frame. Clean, contemporary wall lantern in steel construction with antique bronze powder coat finish.

FINISH

- Antique Bronze - 20

LARGE WALL LANTERN
P6603-20 Antique Bronze
5-1/2" W., 17-1/8" ht.
Extends 3-1/4". H/CTR 10-3/4".
One medium base T10 lamp,
60w max.



P6603-20

Geometric

Geometric lanterns feature an artfully crafted glass enclosure with a pleasing arrangement of contrasting seeded and water glass panels. ADA compliant.

FINISHES

● Architectural Bronze - 129

SMALL WALL LANTERN
P560047-129 Architectural Bronze
6" W., 8" ht.
Extends 4". H/CTR 4".
One medium base lamp,
60w max.

MEDIUM WALL LANTERN
P560048-129 Architectural Bronze
6" W., 16" ht.
Extends 4". H/CTR 4-1/4".
Two medium base lamps,
each 60w max.

All fixtures:



P560047-129



P560048-129

Ceramic Sconce

A white ceramic outdoor sconce can be painted to easily blend with your home's exterior. Dark Sky compliant.

FINISH

○ White - 030

MEDIUM WALL LANTERN
P560044-030 White
8-1/4" W., 10" ht.
Extends 5-3/4". H/CTR 4-1/8".
One medium base lamp,
100w max.



P560044-030

Diverge

Diverge is a low-profile, modern style exterior sconce that complements urban and commercial structures. Its medium base lamping is compatible with incandescent, LED or compact fluorescent sources. ADA compliant.

FINISH

● Architectural Bronze - 129

SMALL WALL LANTERN
P560045-129 Architectural Bronze
6" W., 10-7/8" ht.
Extends 4". H/CTR 5-3/4".
One medium base lamp,
60w max.

MEDIUM WALL LANTERN
P560046-129 Architectural Bronze
6" W., 17-3/4" ht.
Extends 4". H/CTR 9-3/8".
Two medium base lamps,
each 60w max.

All fixtures:





P560046-129



P560045-129

McBee

A truly distinctive style, the McBee lantern delivers sophisticated styling that has a classic vintage appearance suitable for residential or urban exteriors. The clear cylindrical glass shade is held in place with a working mechanical cover that provides easy access for maintenance.

FINISH

● Black - 031

MEDIUM WALL LANTERN
P560035-031 Black
4-1/2" W., 20-3/4" ht.
Extends 8". H/CTR 11-3/4".
One medium base lamp,
60w max.

Fixture shown with P7827-01 vintage lamps, not included. See page 824.



P560035-031

Globe Lantern

Classic in both form and function, the Globe lanterns provide a stylish update for the home. A clear glass diffuser is the perfect way to showcase vintage or globe style light bulbs.

FINISH

● Black - 031

POST LANTERN
P540007-031 Black
9-7/8" dia., 13-1/4" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560092-031 Black
9-7/8" W., 11-5/8" ht.
Extends 11". H/CTR 9".
One medium base lamp,
100w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.



P540007-031



P560092-031

Essential

White linen glass is completed with a powder coated aluminum frame and Black finish, while an umber linen glass shade complements the warm Antique Bronze finish.

FINISHES

● Antique Bronze - 20
● Black - 31

SMALL WALL LANTERN
P6059-20 Antique Bronze
P6059-31 Black
5-7/8" W., 8-3/4" ht.
Extends 6-3/4". H/CTR 2-1/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P6060-20 Antique Bronze
P6060-31 Black
8" W., 11-1/8" ht.
Extends 8-7/8". H/CTR 2-1/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P6086-20 Antique Bronze
P6086-31 Black
10" W., 13-7/8" ht.
Extends 11-1/8". H/CTR 2-3/8".
One medium base lamp,
100w max.



P6059-20



P6060-20



P6086-20



P6059-31



P6060-31



P6086-31

Gunther

Gunther lanterns provide an affordable and stylish option to update a home's curb appeal. Inspired by the popular farmhouse design trend, these cylindrical lights provide the perfect showcase for vintage style light bulbs.



P550020-020



P560057-020



P560058-020



P540020-020



P550021-020

FINISH

● Antique Bronze - 020

FLUSH MOUNT
P550021-020 Antique Bronze
12-5/8" dia., 5-3/4" ht.
Two medium base lamps,
each 75w max.

SMALL WALL LANTERN
P560057-020 Antique Bronze
6-1/2" W., 9-1/2" ht.
Extends 7-3/4". H/CTR 2-3/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560058-020 Antique Bronze
8" W., 11-1/2" ht.
Extends 9-1/4". H/CTR 3-3/8".
One medium base lamp,
100w max.

POST LANTERN
P540020-020 Antique Bronze
8" dia., 13-1/2" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN
P550020-020 Antique Bronze
8" dia., 12" ht.
Overall ht. w/chain 87", wire 10'.
One medium base lamp,
100w max.

All fixtures shown with P7825-01 vintage lamps, not included. See page 824.

Coventry

Capture the romance with optic hammered glass, stylized cap and shepherd's crook support arm. Die-cast aluminum construction.

FINISH

● Textured Black - 31

PAIR WITH

Path Light

POST LANTERN
P5429-31 Textured Black
9-3/4" dia. 19-5/8" ht.
Fits 3" post (sold separately).
Two candelabra base lamps,
each 60w max.

HANGING LANTERN
P5529-31 Textured Black
9-3/4" dia., 19-1/4" ht.
Overall ht. w/chain 94"; wire 10'.
Two candelabra base lamps,
each 60w max.

MEDIUM WALL LANTERN
P5828-31 Textured Black
8" W., 17-1/4" ht.
Extends 10". H/CTR 10".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P5829-31 Textured Black
9-3/4" W., 20-1/2" ht.
Extends 12-1/2". H/CTR 12".
Two candelabra base lamps,
each 60w max.



P5529-31



P5828-31



P5429-31



P5829-31

Edition

Edition features clear water glass elements and a die-cast aluminum, powder coated frame. The distinct octagonal shape offers a classical style to consider for updating a home's curb appeal.

FINISHES

- Antique Bronze - 20
- Black - 31

SMALL WALL LANTERN
P6070-20 Antique Bronze
P6070-31 Black
5-1/2" W., 9-1/8" ht.
Extends 6-1/2". H/CTR 2-3/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P6071-20 Antique Bronze
P6071-31 Black
7-1/8" W., 12-1/2" ht.
Extends 8-1/8". H/CTR 3-1/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P6072-20 Antique Bronze
P6072-31 Black
9" W., 15-7/8" ht.
Extends 10". H/CTR 4-1/16".
One medium base lamp,
100w max.

POST LANTERN
P6429-20 Antique Bronze
P6429-31 Black
9" W., 21-7/8" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN
P6529-20 Antique Bronze
P6529-31 Black
7-1/8" W., 13" ht.
Overall ht. w/chain 88"; wire 180".
One medium base lamp,
100w max.


P6429-31


P6429-20


P6529-31


P6529-20


P6070-31


P6070-20


P6071-31


P6071-20


P6072-31


P6072-20

Onion Lanterns

Detailed finials, end caps and scrollwork in powder coat Black finish, featuring clear beveled glass and cast aluminum frames.

FINISH

● Black - 31

POST LANTERN
P5401-31 Black
11-1/8" dia., 27-3/4" ht.
Fits 3" post (sold separately).
Four candelabra base lamps, each 60w max.

HANGING LANTERN
P5501-31 Black
11-1/8" dia., 28" ht.
Overall ht. w/chain 102"; wire 15'.
Four candelabra base lamps, each 60w max.

MEDIUM WALL LANTERN
P5700-31 Black
7-3/4" W., 23-1/4" ht.
Extends 10-3/4".
Three candelabra base lamps, each 60w max.

LARGE WALL LANTERN
P5701-31 Black
Four-light wall lantern.
11-1/8" W., 31" ht.
Extends 16".
Four candelabra base lamps, each 60w max.

SMALL WALL LANTERN
P5878-31 Black
6-1/2" W., 21-1/4" ht.
Extends 10". H/CTR 13-1/8".
One medium base lamp, 100w max.



P5878-31



P5700-31



P5701-31



P5501-31



P5401-31



P5862-2030K9



P5862-3130K9



P5863-2030K9



P5863-3130K9



P5864-2030K9



P5864-3130K9



P5445-2030K9



P5445-3130K9

Westport LED

Westport LED offers traditional styling to complement a variety of home décor options. A durable, die-cast aluminum frame cradles a softly diffused, seeded glass shade.

FINISHES

- Antique Bronze - 20
- Black - 31

POST LANTERN
P5445-2030K9 Antique Bronze
P5445-3130K9 Black
9" dia., 16-3/8" ht.
Fits 3" post (order separately).
One 9w LED module, 3000K, 90CRI, 623 source lumens.

SMALL WALL LANTERN
P5862-2030K9 Antique Bronze
P5862-3130K9 Black
6-7/8" W., 10-1/4" ht.
Extends 8-3/8". H/CTR 3-1/8".
One 9w LED module, 3000K, 90CRI, 623 source lumens.

MEDIUM WALL LANTERN
P5863-2030K9 Antique Bronze
P5863-3130K9 Black
9" W., 12-7/8" ht.
Extends 10-3/8". H/CTR 3-3/4".
One 9w LED module, 3000K, 90CRI, 623 source lumens.

LARGE WALL LANTERN
P5864-2030K9 Antique Bronze
P5864-3130K9 Black
11" W., 15-3/8" ht.
Extends 12-7/8". H/CTR 4".
One 17w LED module, 3000K, 90CRI, 1211 source lumens.

All fixtures:

New Haven

A Black finish complements clear beveled glass in the New Haven outdoor lantern collection.

FINISH

● Black - 31

POST LANTERN
P6433-31 Black
11″ dia., 23″ ht.
Fits 3″ post (sold separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN
P6533-31 Black
11″ dia., 19-3/4″ ht.
Overall ht. w/chain 95″; wire 10′.
Three candelabra base lamps,
each 60w max.

FLUSH MOUNT
P550036-031 Black
11″ dia., 6″ ht.
Two medium base lamps,
each 60w max.

SMALL WALL LANTERN
P6610-31 Black
7-5/8″ W., 14-7/8″ ht.
Extends 7-3/8″. H/CTR 5-1/2″.
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P6611-31 Black
9″ W., 18-1/8″ ht.
Extends 8-5/8″. H/CTR 8-1/2″.
One candelabra base lamp,
100w max.

LARGE WALL LANTERN
P6612-31 Black
11″ W., 21-7/8″ ht.
Extends 10-3/8″. H/CTR 8-5/8″.
Three candelabra base lamps,
each 60w max.

P6533-31





P6610-31



P550036-031



P6611-31



P6433-31



P6612-31

Burlington

The Burlington collection features all aluminum construction, weather-resistant performance with clear beveled glass panels.

FINISH

Antique Bronze - 20

POST LANTERN
P6437-20 Antique Bronze
9" sq., 18-3/8" ht.
Fits 3" post (sold separately).
Two candelabra base lamps, each 60w max.

HANGING LANTERN
P6537-20 Antique Bronze
9" sq., 15-3/4" ht.
Overall ht. w/chain 91"; wire 10'.
Two candelabra base lamps, each 60w max.

FLUSH MOUNT
P550035-020 Antique Bronze
7" sq., 7" ht.
One medium base lamp, each 60w max.

SMALL WALL LANTERN
P6615-20 Antique Bronze
7" W., 12-7/8" ht.
Extends 7-3/4". H/CTR 4-1/8".
One medium base lamp, 100w max.

MEDIUM WALL LANTERN
P6616-20 Antique Bronze
9" W., 18-3/4" ht.
Extends 9-3/4". H/CTR 7-5/8".
Two candelabra base lamps, each 60w max.

LARGE WALL LANTERN
P6617-20 Antique Bronze
11" W., 21-7/8" ht.
Extends 11-3/4". H/CTR 8-5/8".
Three candelabra base lamps, each 60w max.


P6537-20


P550035-020


P6437-20


P6615-20


P6616-20


P6617-20

Weldon

Featuring nautical influences, Weldon delivers a full collection of outdoor lantern styles ideal for Farmhouse or Transitional architecture designs. Curved clear seeded glass is topped with an ample roof in Architecture Bronze or Black.

FINISHES

- Black - 031
- Architectural Bronze - 129

POST LANTERN
P540019-031 Black
10" W., 15-5/8" ht.
Fits 3" post (sold separately).
Extends 12-1/8".
One medium base lamp,
60w max.

FLUSH MOUNT
P550042-031 Black
10-3/4" dia., 4-1/2" ht.
Two medium base lamps,
each 60w max.

HANGING LANTERN
P550043-031 Black
10" dia., 13-7/8" ht.
Overall ht. w/chain 87"; wire 10'.
One medium base lamp,
60w max.

SMALL WALL LANTERN
P560119-031 Black
6" W., 9" ht.
Extends 6-3/4". H/CTR 3-1/2".
One medium base lamp,
60w max.

MEDIUM WALL LANTERN
P560120-031 Black
8" W., 11-7/8" ht.
Extends 8-3/4". H/CTR 4-3/8".
One medium base lamp,
60w max.

LARGE WALL LANTERN
P560121-031 Black
10" W., 14-7/8" ht.
Extends 10-3/4". H/CTR 5-5/8".
One medium base lamp,
60w max.

P550043-031





P560119-031



P550042-031



P560120-031



P540019-031



P560121-031

Weldon



P560119-129



P560120-129



P560121-129



P550043-129



P550042-129



P540019-129

POST LANTERN
P540019-129 Architectural Bronze
10" W., 15-5/8" ht.
Fits 3" post (sold separately).
Extends 12-1/8".
One medium base lamp,
60w max.

FLUSH MOUNT
P550042-129 Architectural Bronze
10-3/4" dia., 4-1/2" ht.
Two medium base lamps,
each 60w max.

HANGING LANTERN
P550043-129 Architectural Bronze
10" dia., 13-7/8" ht.
Overall ht. w/chain 87"; wire 10'.
One medium base lamp,
60w max.

SMALL WALL LANTERN
P560119-129 Architectural Bronze
6" W., 9" ht.
Extends 6-3/4". H/CTR 3-1/2".
One medium base lamp,
60w max.

MEDIUM WALL LANTERN
P560120-129 Architectural Bronze
8" W., 11-7/8" ht.
Extends 8-3/4". H/CTR 4-3/8".
One medium base lamp,
60w max.

LARGE WALL LANTERN
P560121-129 Architectural Bronze
10" W., 14-7/8" ht.
Extends 10-3/4". H/CTR 5-5/8".
One medium base lamp,
60w max.

Westport

Classic styling with detailed touches. Clear seeded glass with die-cast aluminum frames and durable powder coat finish.

FINISHES

- Antique Bronze - 20
- White - 30
- Black - 31

FLUSH MOUNT
P3883-20 Antique Bronze
P3883-31 Black
9" dia., 10-1/4" ht.
One medium base lamp, 100w max.

LARGE WALL LANTERN
P5864-20 Antique Bronze
P5864-31 Black
11" W., 19-1/2" ht;
Extends 12-7/8". H/CTR 4-5/8".
Two candelabra base lamps, each 60w max.

HANGING LANTERN
P5530-20 Antique Bronze
P5530-31 Black
9" dia., 14-5/8" ht.
Overall ht. w/chain 90", wire 15'.
One medium base lamp, 100w max.

POST LANTERN
P5458-20 Antique Bronze
P5458-31 Black
11" dia., 19" ht.
Fits 3" post (sold separately).
One medium base lamp, 100w max.



P3883-20



P3883-31

P5530-20



P5530-31





P5864-20



P5864-31



P5458-20



P5458-31

Westport



P5862-30



P5862-20



P5862-31

SMALL WALL LANTERN
P5862-20 Antique Bronze
P5862-30 White
P5862-31 Black
6-7/8" W., 12-5/8" ht.
Extends 8-3/8". H/CTR 3-1/8".
One medium base lamp,
60w max.



P5863-30



P5863-20



P5863-31

MEDIUM WALL LANTERN
P5863-20 Antique Bronze
P5863-30 White
P5863-31 Black
9" W., 15-7/8" ht.
Extends 10-3/8". H/CTR 3-1/4".
One medium base lamp,
100w max.

POST LANTERN
P5445-20 Antique Bronze
P5445-30 White
P5445-31 Black
9" dia., 16-3/8" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.



P5445-30



P5445-20



P5445-31

East Haven

East Haven offers contemporary styling to complement a variety of home styles. A Black or Antique Bronze die-cast aluminum frame cradles a seeded glass shade.

FINISHES

- Antique Bronze - 20
- Black - 31

SMALL WALL LANTERN
P6073-20 Antique Bronze
P6073-31 Black
5-3/4" W., 10-3/8" ht.
Extends 7". H/CTR 5-3/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P6074-20 Antique Bronze
P6074-31 Black
7-1/2" W., 12-3/4" ht.
Extends 9-1/2". H/CTR 7-1/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN
P6075-20 Antique Bronze
P6075-31 Black
9-1/2" W., 15-1/8" ht.
Extends 11-1/2". H/CTR 9-3/4".
One medium base lamp,
100w max.

POST LANTERN
P6425-20 Antique Bronze
P6425-31 Black
7-1/2" dia., 15" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN
P6525-20 Antique Bronze
P6525-31 Black
7-1/2" dia., 13-3/8" ht.
Overall ht. w/chain 90"; wire 15'.
One medium base lamp,
100w max.


P6525-20


P6525-31


P6073-20


P6073-31


P6074-20


P6074-31


P6425-20


P6425-31


P6075-20


P6075-31

East Haven LED

East Haven offers contemporary styling to complement today's home styles. A Black or Antique Bronze frame cradles a seeded glass shade.

FINISHES

- Antique Bronze - 20
- Black - 31



P6077-2030K9



P6077-3130K9



P6078-2030K9



P6078-3130K9



P6079-2030K9



P6079-3130K9



P6430-2030K9



P6430-3130K9

SMALL WALL LANTERN
P6077-2030K9 Antique Bronze
P6077-3130K9 Black
5-3/4" W., 7-7/8" ht.
Extends 7-1/2". H/CTR 4-3/4".
One 9w LED module, 3000K, 90CRI, 623 source lumens.

LARGE WALL LANTERN
P6079-2030K9 Antique Bronze
P6079-3130K9 Black
9-1/2" W., 12" ht.
Extends 11-1/8". H/CTR 4-3/4".
One 17w LED module, 3000K, 90CRI, 1211 source lumens.

MEDIUM WALL LANTERN
P6078-2030K9 Antique Bronze
P6078-3130K9 Black
7-1/2" W., 9-3/4" ht.
Extends 9-1/8". H/CTR 4-3/4".
One 9w LED module, 3000K, 90CRI, 623 source lumens.

POST LANTERN
P6430-2030K9 Antique Bronze
P6430-3130K9 Black
7-1/2" dia., 15" ht.
Fits 3" post (order separately).
One 9w LED module, 3000K, 90CRI, 623 source lumens.

All fixtures:

Welbourne

Hexagonal cast aluminum framework with vine-inspired scrolls. Beveled clear glass panels in Textured Black or Textured White finishes.

FINISHES

○ Textured White - 30
● Textured Black - 31

POST LANTERN
P5482-30 Textured White
P5482-31 Textured Black
9-1/2" dia., 21-1/4" ht.
Fits 3" post (sold separately).
One medium base lamp, 100w max.

LARGE POST LANTERN
P5483-31 Textured Black
13" dia., 26" ht.
Fits 3" post (sold separately).
Three candelabra base lamps, 60w max.

HANGING LANTERN
P5582-30 Textured White
P5582-31 Textured Black
9-1/2" dia., 15" ht.
Overall ht. w/ chain 51"; wire 10'
One medium base lamp, 100w max.


P5682-30


P5681-30


P5582-30


P5582-31


P5482-30


P5482-31


P5483-30


P5483-31

Welbourne



P5682-31



P5681-31



P5683-31



P5684-31
shown without tail



P5690-31



P5684-31
shown with tail

SMALL WALL LANTERN
P5681-30 Textured White
P5681-31 Textured Black
6-1/2" W., 16-7/8" ht.
Extends 9-1/4". H/CTR 13-1/4".
One medium base lamp,
100w max.

SMALL WALL LANTERN
P5682-30 Textured White
P5682-31 Textured Black
6-1/2" W., 13-1/4" ht.
Extends 9". H/CTR 3-1/2".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P5684-31 Textured Black
Use with or without tail.
9-1/2" W., 30-3/4" ht.
with tail. 23-1/4" ht. without tail.
Extends 11-3/8". H/CTR 18-3/8"
One medium base lamp,
100w max.

LARGE WALL LANTERN
P5690-31 Textured Black
13" W., 22-1/4" ht.
Extends 14". H/CTR 5".
Three candelabra base lamps,
each 60w max.

MEDIUM WALL LANTERN
P5683-31 Textured Black
9-1/2" W., 18" ht.
Extends 9-3/4" H/CTR 8-1/2".
One medium base lamp,
100w max.

Roman Coach

The Roman Coach Collection features elegant lanterns with low maintenance for years of enjoyment. This collection is ideal for illuminating transitional, new traditional, and mid-century modern settings.

FINISHES

- Antique Bronze - 20
- Black - 31

WALL LANTERN
P5770-20MD Antique Bronze
7" W., 15-3/8" ht.
Extends 7-1/4". H/CTR 6-7/8"
One medium base lamp,
100w max.

HANGING LANTERN
P5565-20 Antique Bronze
P5565-31 Black
Chain and ceiling mounts included.
7" dia., 13" ht.
Overall ht. w/chain 36"; wire 10'
Ceiling mount ht. 12-3/4
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P5777-20 Antique Bronze
7" W., 12-1/2 ht.
Extends 7-1/4". H/CTR 4".
One medium base lamp,
100w max.

SMALL WALL LANTERN
P5773-20 Antique Bronze
Can be used with or without tail.
5-3/4" W., 18-1/4" ht. w/tail.
13-1/2" ht. w/o tail.
Extends 5-3/4". H/CTR 7-1/4".
One medium base lamp,
100w max.

SMALL WALL LANTERN
P5985-20MD Antique Bronze
P5985-31MD Black
4-5/8" W., 10" ht.
Extends 6-1/8". H/CTR 2-3/4".
One medium base lamp,
100w max.

SMALL WALL LANTERN
P5986-20MD Antique Bronze
P5986-31MD Black
4-5/8" W., 8-1/2" ht.
Extends 6-1/8". H/CTR 2-3/4".
One medium base lamp,
100w max.



P5770-20MD



P5565-20
shown as ceiling mount



P5565-20



P5565-31



P5777-20



P5773-20
shown without tail



P5773-20
shown with tail



P5985-31MD



P5985-20MD



P5986-31MD



P5986-20MD



P5475-20

Roman Coach



P6019-20



P6019-31



P5767-20
shown without tail



P5762-20



P5762-31



P5767-20
shown with tail



P5765-20



P5765-31



P6417-20



P6417-31



P5767-31
shown with tail

FLUSH MOUNT
P6019-20 Antique Bronze
P6019-31 Black
11" W., 6-3/8 ht.
Two medium base lamps,
each 60w max.

MEDIUM WALL LANTERN
P5765-20 Antique Bronze
P5765-31 Black
7" W., 15-1/4" ht.
Extends 7-1/4". H/CTR 6-7/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P5767-20 Antique Bronze
P5767-31 Black
Can be used with or without tail.
7" W., 26-3/8" ht. w/tail.
19-1/4" ht. w/o tail.
Extends 7". H/CTR 16-1/4".
One medium base lamp,
100w max.

SMALL WALL LANTERN
P5762-20 Antique Bronze
P5762-31 Black
6" W., 9-3/4" ht.
Extends 6-1/2". H/CTR 3-1/2".
One medium base lamp,
100w max.

POST LANTERN
P6417-20 Antique Bronze
P6417-31 Black
9-1/2" W., 22-1/2" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

POST LANTERN
P5475-20 Antique Bronze
7" W., 15-3/4" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

Brassguard® Lanterns

Unique, clear lacquer applied for long-lasting finish. All-brass construction includes protective gasket to reduce staining on siding. Black fixtures utilize aluminum construction with clear lacquer coating.

FINISHES

- Brushed Nickel - 09
- Polished Brass - 10
- Black - 31

MEDIUM HANGING LANTERN
P5834-10 Polished Solid Brass
Chain and ceiling mounts included.
7″ dia., 10″ ht.
Overall ht. w/chain 39-1/2″; wire 10′.
1 medium base lamp,
100w max.

LARGE POST LANTERN
P5432-10 Polished Solid Brass
P5432-31 Black
9-1/2″ dia., 21″ ht.
Fits 3″ post (sold separately).
Three candelabra base lamps,
each 60w max.

LARGE WALL LANTERN
P5730-10 Polished Solid Brass
9-1/2″ W., 26″ ht.
Extends 9-1/2″. H/CTR 20-1/4″.
Three candelabra base lamps,
each 60w max.

MEDIUM WALL LANTERN
P5832-10 Polished Solid Brass
7″ W., 14-1/4″ ht.
Extends 7″. H/CTR 5-3/8″.
One medium base lamp,
100w max.

MEDIUM POST LANTERN
P5430-10 Polished Solid Brass
7″ dia., 17″ ht.
Fits 3″ post (sold separately).
One medium base base lamp,
100w max.


P5834-10


P5834-10
shown as semi-flush


P5730-10


P5832-10


P5430-10


P5432-10


P5432-31

Brassguard® Lanterns



P5756-10



P5756-09



P5846-31



P5756-31



P5731-31



P5831-31



P5758-31

SMALL WALL LANTERN
P5756-09 Brushed Nickel
P5756-10 Polished Solid Brass
P5756-31 Black
Open bottom.
5-1/2" W., 10-1/4" ht.
Extends 5-3/4". H/CTR 3-3/4".
One medium base lamp,
100w max.

SMALL WALL LANTERN
P5758-31 Black
5-1/2" W., 18-3/4" ht.
Extends 5-5/8". H/CTR 7-1/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P5831-31 Black
7" W., 29" ht.
Extends 6-3/4". H/CTR 15-3/8".
One medium base lamp,
100w max.

SMALL WALL LANTERN
P5846-31 Black
5-1/4" W., 14-3/4" ht.
Extends 6". H/CTR 8-3/8".
One medium base lamp,
60w max.

LARGE WALL LANTERN
P5731-31 Black
9-1/2" W., 35" ht.
Extends 9-1/2". H/CTR 20-1/4".
Three candelabra base lamps,
each 60w max.

Coach Lanterns

Square fixture with clear flat glass.

WALL LANTERN
P5607-09 Brushed Nickel
P5607-20 Antique Bronze
P5607-31 Black
4-1/2" W., 8-5/8" ht.
Extends 6-1/8". H/CTR 2-3/4".
One medium base lamp,
100w max.


P5607-09


P5607-20


P5607-31

Beveled Glass

Octagonal close-to-ceiling fixtures. Clear, bound beveled glass. Damp location listed.

THREE LIGHT
P5788-09 Brushed Nickel
P5788-10 Polished Solid Brass
P5788-20 Antique Bronze
9-3/4" dia., 5-7/8" ht.
Three candelabra base lamp,
each 25w max.*

FOUR LIGHT
P5789-09 Brushed Nickel
P5789-10 Polished Solid Brass
P5789-20 Antique Bronze
11-1/8" dia., 6-1/4" ht.
Four candelabra base lamp,
each 25w max.*

**G16.5 lamp recommended*


P5788-10


P5789-10


P5788-09


P5789-09


P5788-20


P5789-20

Cast Lantern



P5826-31

Cast aluminum with Shatter resistant clear acrylic diffuser.

FINISH

● Black - 31

WALL LANTERN
P5826-31 Black
8″ W., 14-1/8″ ht.
Extends 10-1/4″. H/CTR 10-1/4″.
One medium base lamp,
75w max.

Non-Metallic Lanterns



P5456-31



P5656-31



P5738-31

Non-metallic incandescent lanterns available in classic White or Black finishes. Classic outdoor lantern lines. Clear beveled acrylic panels.

POST LANTERN
P5456-31 Black
8″ sq., 18″ ht.
Fits 3″post (sold separately).
One medium base lamp,
100w max.

WALL LANTERN
P5656-31 Black
8″ W., 20″ ht.
Extends 9″, H/CTR 15″.
One medium base lamp,
100w max.

WALL LANTERN
P5738-31 Black
8″ W., 21″ ht.
Extends 8-1/2″, H/CTR 13″.
One medium base lamp,
60w max.

Utility

Dress up essential lighting with finesse to match any décor, Globe or cylindrical marine glass for clean, minimalist look.

WALL LANTERN
P5602-30 White
P5602-31 Black
With clear marine glass.
4-1/2" W., 7-1/4" ht.
Extends 5-1/2". H/CTR 2-1/4".
One medium base lamp,
75w max.


P5602-31


P5604-31


P5604-30

FLUSH MOUNT
P5603-30 White
P5603-31 Black
With clear marine glass.
4-7/8" dia., 6-1/4" ht.
One medium base lamp,
60w max.


P5602-30


P5603-31


P5603-30

WALL LANTERN
P5604-30 White
P5604-31 Black
With white 5-3/4" glass globe.
5-3/4" W., 8-3/8" ht.
Extends 6-1/2". H/CTR 2-1/4".
One medium base lamp,
100w max.

Non-Metallic Lanterns

Durable construction polycarbonate lanterns.

POLYCARBONATE
WALL LANTERN
P5612-30 White
P5612-31 Black
With clear Lexan diffuser.
4-3/4" W., 7-1/4" ht.
Extends 5-3/4". H/CTR 2-1/2".
One medium base lamp,
60w max.


P5612-30


P5612-31

POLYCARBONATE
WALL LANTERN
P5813-30 White
P5813-31 Black
With with 6" acrylic globe.
6" W., 7-3/4" ht.
Extends 6-1/2". H/CTR 2-1/2".
One medium base lamp,
60w max.

POLYPROPYLENE LANTERN
WALL LANTERN
P5844-30 White
P5844-31 Black
With white acrylic diffuser.
6" W., 8-3/4" ht.
Extends 7-1/4". H/CTR 3".
One medium base lamp,
60w max.


P5817-31


P5813-31

POLYPROPYLENE
WALL LANTERN
P5817-31 Black
With white acrylic diffuser.
4-3/8" W., 7" ht.
Extends 5-3/4". H/CTR 3-1/4"
One medium base lamp,
60w max.


P5844-30


P5844-31

Ceiling Mount

Antique Bronze, White or Black finish, textured glass or white acrylic panels.



P5727-31



P5727-20



P5729-31



P5729-31



P5744-31



P5744-30



P5745-31



P5745-30

Metal

ONE-LIGHT
FLUSH MOUNT
P5727-20 Antique Bronze
P5727-31 Black
Textured glass.
7-1/2″ sq., 5″ ht.
One medium base lamp,
60w max.

TWO-LIGHT
FLUSH MOUNT
P5729-20 Antique Bronze
P5729-31 Black
Textured glass.
9-1/4″ sq., 5″ ht.
Two medium base lamps,
each 60w max.

Polycarbonate

ONE LIGHT
FLUSH MOUNT
P5744-30 White
P5744-31 Black
With white acrylic panels.
8-1/4″sq., 4-3/4″ ht.
One medium base lamp,
60w max.

TWO LIGHT
FLUSH MOUNT
P5745-30 White
P5745-31 Black
With white acrylic panels.
10-1/4″ sq., 5-1/2″ ht.
Two medium base lamps,
each 60w max.

Newport Non-Metallic Lanterns

Tiered pagoda outdoor light fixtures. Clear prismatic polycarbonate diffusers. UV stabilized to prevent fading. Polypropylene lanterns will not rust.

POST LANTERN
P5444-31 Black
10″ dia., 10″ ht.
Fits 3″ post (sold separately).
One medium base lamp,
60w max.

WALL LANTERN
P5645-30 White
P5645-31 Black
10″ W., 10″ ht.
Extends 11″. H/CTR 5-1/2″.
One medium base lamp,
60w max.

POST LANTERN
P5493-31 Black
28-3/4″ W., 13″ ht.
Fits 3″ post (sold separately).
Two medium base lamps,
each 60w max.


P5645-30


P5493-31


P5645-31


P5444-31

Mansard Non-Metallic Lanterns

Four-sided gambrel-style hip roof non-metallic outdoor lanterns in classic White or Black finishes.

POST LANTERN
P5414-30 White
P5414-31 Black
8″ sq., 12″ ht.
Fits 3″ post (sold separately).
One medium base lamp,
60w max.

WALL LANTERN
P5814-30 White
P5814-31 Black
8″ W., 12-3/4″ ht.
Extends 8-1/4″. H/CTR 10-5/8″.
One medium base lamp,
60w max.

WALL LANTERN
P5815-30 White
P5815-31 Black
8″ W., 17″ ht.
Extends 8-1/4″. H/CTR 10-5/8″.
One medium base lamp,
60w max.


P5814-30


P5815-30


P5814-31


P5414-30


P5414-31

Hard-Nox®

Ideal for wide range of outdoor areas. Wet location listed. For indoor or outdoor use.



P5710-31



P5711-31

Polycarbonate/ Acrylic Diffuser

WALL OR CEILING
P5710-31 Black
8-3/4" dia., 5-1/4" ht.
One medium base lamp,
75w max.

WALL OR CEILING
P5711-31 Black
8-3/4" dia., 5-1/4" ht.
Two medium base lamps,
each 75w max.

White Acrylic Globes

Shatter-resistant globe ideal for range of outdoor areas. Cast aluminum wall mounts in White or Black finish.



P5626-60



P5436-60

P5426-60

P5478-60

POST LANTERN
P5426-60 White
With white fitter.
12" dia., 11-7/8" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

POST LANTERN
P5436-60 White
With white fitter.
14" dia., 14" ht.
Fits 3" post (sold separately).
One medium base lamp,
150w max.

POST LANTERN
P5478-60 Black
With black polycarbonate fitter. Twist-lock globe.
10" dia., 13-1/8" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

WALL LANTERN
P5626-60 White
One-light cast aluminum
8" W., 15" ht.
Extends 10". H/CTR 8".
One medium base lamp,
100w max.

Bulkheads LED

Robust and energy efficient, LED bulkheads are a general-purpose luminaire. Comprised of a die-cast aluminum frame and polycarbonate diffuser. Fixtures are impact resistant and offer various mounting options and can be widely adopted for indoor and outdoor applications.

OVAL WALL OR CEILING
P3647-3030K9 White
P3647-3130K9 Black
6-1/2" W., 10-1/2" ht.
Extends 4-3/8". H/CTR 5-1/4".
One 9w LED module, 3000K,
90CRI, 623 source lumens.

ROUND WALL OR CEILING
P3648-3030K9 White
P3648-3130K9 Black
9-1/2" dia., 4-3/8" ht.
H/CTR 4-3/4".
One 17w LED module, 3000K,
90CRI, 623 source lumens.

OVAL WALL OR CEILING
P3649-3030K9 White
P3649-3130K9 Black
6-1/2" W., 10-1/2" ht.
Extends 4-1/2". H/CTR 5-1/4".
One 9w LED module, 3000K,
90CRI, 623 source lumens.

ROUND WALL OR CEILING
P3650-3030K9 White
P3650-3130K9 Black
9-1/2" dia., 4-1/2" ht.
H/CTR 4-3/4".
One 9w LED module, 3000K,
90CRI, 623 source lumens.

All fixtures:



P3647-3030K9
shown wall-mounted



P3647-3130K9
shown ceiling-mounted



P3649-3130K9
shown wall-mounted



P3649-3030K9
shown ceiling-mounted



P3648-3130K9
shown wall-mounted



P3648-3030K9
shown ceiling-mounted



P3650-3130K9
shown wall-mounted



P3650-3030K9
shown ceiling-mounted

Polycarbonate Bulkheads

Virtually maintenance free fixtures. Install on ceilings or walls. Classic white details and trim, Corrosion, impact and shatter resistant, UV stabilized.



P5706-30



P5704-30



P5705-30



P5702-30



P5703-30

ROUND WALL OR CEILING
P5702-30 White
10" dia.,
Extends 4-3/4".
One medium base lamp,
75w max.

ROUND WALL OR CEILING
P5703-30 White
With grill.
10-3/8" dia.,
Extends 5-7/8".
One medium base lamp,
75w max.

OVAL WALL
P5704-30 White
10-1/2" L., 5-5/8" W.
Extends 3-3/4".
One medium base lamp,
60w max.

ADA

OVAL WALL
P5705-30 White
With grill.
10-1/2" L., 5-7/8" W.
Extends 4".
One medium base lamp,
60w max.

ADA

OVAL WALL
P5706-30 White
Hooded.
10-1/2" L., 5-7/8" W.
Extends 4-1/8".
One medium base lamp,
60w max.

Bulkheads

Die-cast aluminum with clear glass lens.



P3706-31
shown ceiling-mounted



P3709-30
shown wall-mounted



P3709-31
shown ceiling-mounted



P3706-30
shown wall-mounted

OVAL WALL OR CEILING
P3706-30 White
P3706-31 Black
6-3/8" W., 11" ht.
Extends 5". H/CTR 5-1/2".
One medium base lamp,
100w max.

ROUND WALL OR CEILING
P3709-30 White
P3709-31 Black
7-7/8" dia., 4-1/2" ht.
H/CTR 4".
One medium base lamp,
60w max.

Strata LED

The Strata features a modern, low profile design ideal for residential and multifamily applications. Energy efficient and functional, wall mounted, can be installed indoor and outdoor.

FINISHES

- White - 030
- Metallic Gray - 82
- Antique Bronze - 020
- Black - 031

WALL LANTERN
P560090-020-30K Antique Bronze
P560090-030-30K White
P560090-031-30K Black
P560090-082-30K Metallic Gray
6-5/8" W., 5-1/2" ht.
12w integrated LED, 3000K, 90CRI,
825 delivered lumens.

All fixtures:


P560090-030-30K


P560090-082-30K


P560090-020-30K


P560090-031-30K

Cornice LED

Modern geometric outdoor LED sconces are designed to complement a range of residential and commercial architectural styles. ADA compliant. Available in Black, Antique Bronze and Metallic Gray finishes.

FINISHES

- AntiqueBronze - 20
- Black - 31
- Metallic Gray - 82

OUTDOOR WALL SCONCE
P5634-2030K9 Antique Bronze
P5634-3130K9 Black
P5634-8230K9 Metallic Gray
5-1/4" W., 4-3/4" ht.
Extends 4". H/CTR 2-3/8".
One 9w LED module, 3000K,
623 source lumens.

OUTDOOR WALL SCONCE
P5635-2030K9 Antique Bronze
P5635-3130K9 Black
P5635-8230K9 Metallic Gray
6-1/8" W., 5" ht.
Extends 4". H/CTR 2-3/8".
One 9w LED module, 3000K,
623 source lumens.

All fixtures:


P5634-3130K9


P5635-3130K9


P5634-8230K9


P5635-8230K9


P5634-2030K9


P5635-2030K9

Z-1030 LED

A modern outdoor LED sconce with an architectural-inspired open linear frame and clear glass diffuser. Finished in Black, White, Metallic Gray or Antique Bronze.


P560051-020-30


P560051-030-30


P560051-031-30


P560051-082-30


P560056-020-30


P560056-030-30


P560056-031-30


P560056-082-30

FINISHES

- Antique Bronze - 020
- White - 030
- Black - 031
- Metallic Gray -082

SMALL WALL LANTERN
P560051-020-30 Antique Bronze
P560051-030-30 White
P560051-031-30 Black
P560051-082-30 Metallic Gray
5-1/8" W., 12" ht.
Extends 5-3/4". H/CTR 2-1/4".
One 9w LED module, 3000K, 90CRI, 624 source lumens.

MEDIUM WALL LANTERN
P560056-020-30 Antique Bronze
P560056-030-30 White
P560056-031-30 Black
P560056-082-30 Metallic Gray
5-1/8" W., 20" ht.
Extends 5-3/4". H/CTR 2-1/4".
One 9w LED module, 3000K, 90CRI, 624 source lumens.

All fixtures:

Z-1090 LED

An elongated frame and clean, crisp lines are the hallmarks of the Z-1090 Collection. A modern take on an open-cage design is manifested by a rectangular silhouette with an open bottom through which a stunning glow shines.

FINISHES

● Black - 031
○ Satin White - 030

WALL LANTERN
P560137-028-30 Satin White
P560137-031-30 Black
4-1/2" W., 16" ht., wire 6".
Extends 4-3/8". H/CTR 2-1/2".
9w Module LED, 3000K,
90CRI, 624 source lumens.



P560137-031-031



P560137-028-30

Z-1010 LED

A modern outdoor sconce with an open linear frame and seeded glass diffuser. Finished in Black and Architectural Bronze.

FINISHES

● Black - 031
● Architectural Bronze - 129

WALL LANTERN
P560029-031-30 Black
P560029-129-30 Architectural Bronze
7-1/2" W., 16" ht.
Extends 4". H/CTR 4-1/4".
One 9w LED module. 3000K
90CRI, 624 source lumens.



P560029-031-30



P560029-129-30

Z-1020 LED

A modern outdoor sconce with white glass shade is suspended in a curved frame that serves as a reflector when illuminated. Finished in Black or Architectural Bronze.

FINISHES

- Black - 031
- Architectural Bronze - 129

WALL LANTERN
P560030-031-30 Black
P560030-129-30 Architectural Bronze
7-1/2" W., 13-1/2" ht.
Extends 4-3/4". H/CTR 11-1/8".
One 9w LED module. 3000K
90CRI, 670 source lumens.



P560030-031-30



P560030-129-30

Z-2010 LED

Experience lighting inspired by other worlds with the Z-2010 Collection, featuring a circle within a circle structure that mimics the design of planets.

OUTDOOR WALL SCONCE
P560132-108-30 Oil Rubbed Bronze
Fixture can be installed facing left, right, up or down
12" dia. Extends 2-3/16". H/CTR 6".
9w Module LED, 3000K,
90CRI, 670 source lumens.



P560132-108-30

Z-1050 LED

Featuring a modern design, the Z-1050 LED sconce is suitable for a variety of exterior or interior architecture settings. Wall sconce is wet location listed with a replaceable LED module protected within a glass enclosure.

OUTDOOR WALL SCONCE
P560093-031-30 Black
12" dia. Extends 3". H/CTR 6".
One 9w LED module, 3000K,
90CRI, 670 source lumens.



P560093-031-30

Valera LED

Transform outdoor settings with a bold, straightforward style. Double linear details finished in Brushed Nickel or Antique Bronze over a white acrylic diffuser. Die-cast aluminum construction.

FINISHES

- Brushed Nickel - 09
- Architectural Bronze - 129

LED WALL LANTERN
P5800-0930K9 Brushed Nickel
P5800-12930K9 Architectural Bronze
5-5/8" W., 8" ht.
Extends 4". H/CTR 4".
One 9w LED module, 3000K,
90CRI, 623 source lumens.

LED WALL LANTERN
P5801-0930K9 Brushed Nickel
P5801-12930K9 Architectural Bronze
8-5/8" W., 11" ht.
Extends 4". H/CTR 5-1/2".
One 17w LED module, 3000K,
90CRI, 1211 source lumens.

LED WALL LANTERN
P5806-0930K9 Brushed Nickel
P5806-12930K9 Architectural Bronze
5-5/8" W., 16" ht.
Extends 4". H/CTR 8".
Two 9w LED modules, 3000K,
90CRI, 623 source lumens per module.

All fixtures:


P5800-0930K9


P5800-12930K9


P5801-0930K9


P5801-12930K9


P5806-0930K9


P5806-12930K9

Z-1070 LED


P560208-031-30


P560208-082-30


P560209-031-30


P560209-082-30

Tranquility is yours with the Z-10170 Collection, whose sleek rectangular back plate hold a curved etched glass shade trimmed top and bottom with minimalist metal caps.

FINISHES

- Black - 031
- Metallic Gray - 082

SMALL WALL LANTERN
P560208-031-30 Black
P560208-082-30 Metallic Gray
6" W., 12-9/16" ht.
Extends 3-3/4". H/CTR 6-1/4".
11w integrated LED, 3000K,
90CRI, 528 delivered lumens.

LARGE WALL LANTERN
P560209-031-30 Black
P560209-082-30 Metallic Gray
6" W., 23-1/8" ht., wire 6".
Extends 3-3/4". H/CTR 11-9/16".
22w integrated LED, 3000K,
90CRI, 1019 delivered lumens.

Z-1080 LED


P560210-031-30


P560210-082-30


P560211-031-30


P560211-082-30

Smooth, elongated frames hold a simple shade banded top and bottom, exuding thea modern attitude that is a hallmark of the Z-1080 collection.

FINISHES

- Black - 031
- Metallic Gray - 082

SMALL WALL LANTERN
P560210-031-30 Black
P560210-082-30 Metallic Gray
5" W., 13" ht.
Extends 3". H/CTR 6-1/2".
11w integrated LED, 3000K,
90CRI, 415 delivered lumens.

LARGE WALL LANTERN
P560211-031-30 Black
P560211-082-30 Metallic Gray
5" W., 23-1/2" ht.
Extends 3". H/CTR 11-3/4".
22w integrated LED, 3000K, 90CRI,
847 delivered lumens.

All fixtures:

Anson LED

One-light ADA wall lantern with polycarbonate diffuser and stainless steel frame. 3000 K, 90+CRI, 1452 lumens.

WALL LANTERN
P560001-129-30 Architectural Bronze
10" W., 3" ht.
One 17w LED module, 3000K,
90CRI, 1452 source lumens.



P560001-129-30

Z-1060 LED

Get even more of the home décor compliments you love with the classic Z-1060 Collection. A minimalist, yet welcoming cylinder-shaped, etched opal glass shade hangs from a handsome black ceiling plate. This collection is perfect for casting a welcoming glow near an entryway or for guiding guests and family down a hallway.

LED FLUSH MOUNT
P550071-031-30 Black
4-1/2" dia., 4-3/8" ht., wire 6".
9w Module LED, 3000K,
90CRI, 624 source lumens.

SMALL WALL LANTERN
P560072-031-30 Black
4-1/2" W., 4-1/2" ht.
Extends 4-3/4". H/CTR 2-1/4".
One 9w LED module, 3000K,
90CRI, 624 source lumens.

SMALL WALL LANTERN
P560073-031-30 Black
Shown with glass
4-1/2" W., 4-1/2" ht.
Extends 4-3/4". H/CTR 2-1/4".
One 9w LED module, 3000K,
90CRI, 624 source lumens.

All fixtures:



P560072-031-30



P560073-031-30



P550071-031-30

Die-Cast LED



P560136-031-30

This energy efficient LED wall lantern features a Black finish on a die-cast aluminum frame. This fixture includes integrated LED technology with no bulbs to replace. The frosted glass panels have a warm quality that adds to the lantern's traditional design.

LED WALL LANTERN
P560136-031-30 Black
5-5/8" dia., 8-7/8" ht.
Extends 6-5/8". H/CTR 6-5/8".
11w integrated LED, 3000K,
80CRI, 560 delivered lumens.

Milford LED



P3665-3130K9



P3673-3130K9

Etched glass surrounded by a die-cast aluminum frame, ideal for indoor and outdoor application.

ONE-LIGHT FLUSH MOUNT
P3665-3130K9 Black
8-5/8" dia., 4-1/8" ht.
One 17w LED module, 3000K,
90CRI, 1211 source lumens.

ONE-LIGHT FLUSH MOUNT
P3673-3130K9 Black
10-5/8" dia., 4-7/8" ht.
One 17w LED module, 3000K,
90CRI, 1211 source lumens.

All fixtures:

Aluminum Cylinders LED

Sleek, cylindrical forms in elegant finish selections. Die-cast aluminum wall brackets and heavy-duty aluminum framing. Fade and chip-resistant. Listed for wet locations.

3″ Aluminum Cylinders LED

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P563000-020-30K **P563000-030-30K** **P563000-143-30K** **P563000-147-30K**	Antique Bronze White Graphite Satin Nickel	One-light down For wet locations	5-1/2″ W., 5-5/8″ ht.	1 12w integrated LED, 3000K, 90CRI, 900 delivered lumens
P563001-020-30K **P563001-030-30K** **P563001-143-30K** **P563001-147-30K**	Antique Bronze White Graphite Satin Nickel	Two-light up/down For wet locations	5-1/2″ W., 8-1/4″ ht.	2 24w integrated LED, 3000K, 90CRI, 1800 delivered lumens

All fixtures:



P563000-020-30K



P563000-030-30K



P563000-143-30K



P563000-147-30K



P563001-020-30K



P563001-030-30K



P563001-143-30K



P563001-147-30K

Aluminum Cylinders LED

5″ Aluminum Cylinders LED

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5674-20/30K **P5674-30/30K** **P5674-31/30K** **P5674-82/30K**	Bronze White Black Metallic Gray	One-light down.	5″ W., 7-1/4″ ht. Extends 8″. H/CTR 2-1/2″.	1 17w integrated LED 3000K, 90CRI, 531 delivered lumens
P5675-20/30K **P5675-30/30K** **P5675-31/30K** **P5675-82/30K**	Bronze White Black Metallic Gray	Two-light up/down For wet locations requires top cover lens, P860045.	5″ W., 14″ ht. Extends 8″. H/CTR 7″.	2 17w integrated LED, 3000K, 90CRI, 1025 delivered lumens
P5774-20/30K **P5774-30/30K** **P5774-31/30K** **P5774-82/30K**	Bronze White Black Metallic Gray	One-light. Mounts flush to ceiling.	5″ dia., 6-1/2″ ht.	1 17w integrated LED, 3000K, 90CRI, 764 delivered lumens

All fixtures:



P5674-20/30K



P5674-30/30K



P5674-31/30K



P5674-82/30K



P5675-20/30K



P5675-30/30K



P5675-31/30K



P5675-82/30K



P5774-20/30K



P5774-30/30K



P5774-31/30K



P5774-82/30K

Aluminum Cylinders LED

6″ Aluminum Cylinders LED

All fixtures:

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5641-20/30K **P5641-30/30K** **P5641-31/30K** **P5641-82/30K**	Bronze White Black Metallic Gray	One-light down	6″ W., 12″ ht. Extends 8-7/8″. H/CTR 4-1/2″.	1 29w integrated LED, 3000K, 90CRI, 1800 delivered lumens
P5642-20/30K **P5642-30/30K** **P5642-31/30K** **P5642-82/30K**	Bronze White Black Metallic Gray	Two-light up/down For wet location requires top cover lens, P860046	6″ W., 18″ ht. Extends 8-7/8″. H/CTR 8″.	2 29w integrated LED, 3000K, 90CRI, 2566 delivered lumens
P5741-20/30K **P5741-30/30K** **P5741-31/30K** **P5741-82/30K**	Bronze White Black Metallic Gray	One-light cylinder. Mounts flush to ceiling or hangs with pendant accessory kit, page 318.	6″ W., 12″ ht.	1 29w integrated LED, 3000K, 90CRI, 1800 delivered lumens


P5641-20/30K


P5641-30/30K


P5641-31/30K


P5641-82/30K


P5642-20/30K


P5642-30/30K


P5642-31/30K


P5642-82/30K


P5741-20/30K


P5741-30/30K


P5741-31/30K


P5741-82/30K

Aluminum Cylinders

Sleek, cylindrical forms in elegant finish selections. Die-cast aluminum wall brackets and heavy-duty aluminum framing. Fade and chip-resistant. UL listed for wet locations when used with lens cover. Dark Sky compliant for down light only.

5″ Aluminum Cylinders

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5674-20 **P5674-30** **P5674-31** **P5674-82**	Bronze White Black Metallic Gray	One-light down	5″ W., 7-1/4″ ht. Extends 8″. H/CTR 2-1/2″.	1 75w PAR-30 or 75w BR-30
P5675-20 **P5675-30** **P5675-31** **P5675-82**	Bronze White Black Metallic Gray	Two-light up/down For wet locations requires top cover lens, P860045	5″ W., 14″ ht. Extends 8″. H/CTR 7″.	2 75w PAR-30
P5774-20 **P5774-30** **P5774-31**	Bronze White Black	One-light. Mounts flush to ceiling	5″ dia., 6-3/4″ ht.	1 75w PAR-30 or 75w BR-30


P5675-20


P5675-82


P5774-20


P5774-30


P5774-31


P5674-31


P5674-20


P5674-82

6″ Aluminum Cylinders

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5641-20 **P5641-30** **P5641-31** **P5641-82**	Bronze White Black Metallic Gray	One-light down	6″ W., 12″ ht. Extends 8-7/8″. H/CTR 4-1/2″.	1 250w PAR-38 or 150w BR-40
P5642-20 **P5642-30** **P5642-31** **P5642-82**	Bronze White Black Metallic Gray	Two-light up/down. For wet location requires top cover lens, P860046	6″ W., 18″ ht. Extends 8-7/8″. H/CTR 8″.	2 250w PAR-38 or 150w BR-40
P5741-20 **P5741-30** **P5741-31**	Bronze White Black	One-light cylinder. Mounts flush to ceiling or hangs with pendant accessory kit, page 318.	6″ dia., 12″ ht.	1 250w PAR-38 or 150w BR-40


P5741-30


P5741-31


P5641-31


P5641-82


P5642-20

Aluminum Squares

Heavy-duty aluminum construction, die-cast aluminum wall bracket. Listed for wet locations. Powder coat for chipping and fading resistance. Dark Sky compliant for down light only.

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5643-20 **P5643-30** **P5643-31**	Bronze White Black	One-light 6" square	6" W., 12" ht. Extends 8-7/8". H/CTR 4-1/2".	1 250w PAR-38 or 150w BR-40
P5644-20 **P5644-30** **P5644-31**	Bronze White Black	Two-light 6" up/down square*	6" W., 18" ht. Extends 8-7/8". H/CTR 8".	2 250w PAR-38 or 150w BR-40

**For use in wet locations, requires top cover lens, P860047.*


P5643-20


P5643-30


P5643-31


P5644-20


P5644-30


P5644-31

Aluminum Squares LED

Heavy-duty aluminum construction, die-cast aluminum wall bracket. UL listed for wet locations. Powder coat for chipping and fading resistance. Dark Sky compliant for down light only. 3000K, 90+ CRI.


P5644-2030K


P5644-3030K

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5643-2030K **P5643-3030K** **P5643-3130K** **P5643-8230K**	Bronze White Black Metallic Gray	One-light 6" square LED	6" W., 12" ht. Extends 8-7/8". H/CTR 4-1/2".	1 29w integrated LED 3000K, 90CRI, 1800 delivered lumens
P5644-2030K **P5644-3030K** **P5644-3130K** **P5644-8230K**	Bronze White Black Metallic Gray	Two-light 6" LED up/down square*	6" W., 18" ht. Extends 8-7/8". H/CTR 8".	2 29w integrated LED 3000K, 90CRI, 1800 delivered lumens

**For use in wet locations, requires top cover lens, P860047.*


P5643-2030K


P5643-3030K


P5643-3130K


P5643-8230K


P5644-3130K


P5644-8230K

Polymeric Cylinders

Sleek, cylindrical forms ideal for coastal locations. Up or down configuration. Non-corrosive components withstand salt, wind, sand, water and sun. Down version shields par lamp and bug lights to minimize glare onto beach for turtle law compliance. Wet location listed. Dark Sky compliant Down Light Only.

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5712-30 **P5712-31**	Textured White Black	One-light polymeric cylinder	5″ W., 7-1/4″ ht. Extends 7-3/4″.	1 75w PAR-30 or 65w BR-30
P5713-30 **P5713-31**	Textured White Black	Two-light polymeric cylinder*	5″ W., 14″ ht. Extends 7-3/4″.	2 75w PAR-30 or 65w BR-30
P8712-30 **P8712-31**	Textured White Black	Turtle-friendly accessory	5″ dia., 4″ ht.	n/a

Downlight only:

**Wet location listed with P860045 top cover.*


P8712-30


P8712-31


P5712-30


P5712-31


P5713-30*


P5713-31*

Accessories for Squares & Cylinders

DEEP GROOVE STEP BAFFLES
Black anodized aluminum to minimize glare

PRODUCT NO.	FINISH	DESCRIPTION	SIZE
P8710-31	Black	Deep groove step baffle for P5641, P5642 and P5741 6″ cylinders.	6″ dia., 4″ ht.


P8710-31

TOP COVER LENS
Adapts up/down fixtures for wet location use.
Heat & shatter-resistant clear tempered lens w/metal trim.

PRODUCT NO.	FINISH	DESCRIPTION	SIZE
P860045-031 **P860045-030**	Black White	Round cylinder cover Water proof version	5″ dia., 5/6″ ht.
P860046-031 **P860046-030**	Black White	Round cylinder cover Water proof version	6″ dia., 4/5″ ht.
P860047-031 **P860047-030**	Black White	Square cylinder cover Water proof version	6″ wd., 7/9″ ht. Extends 6″ dp.



P860045-031


P860046-031

P860045-030


P860046-030


P860047-030


P860047-031

PENDANT KIT
Pendant kit adapts P5741 ceiling fixture to 6″, 12″ or 18″ stem mounting. Includes canopy, hang-straight swivel, 6″ and 12″ sections with coupling.

PRODUCT NO.	FINISH	DESCRIPTION
P8741-20	Bronze	Pendant kit for P5741
P8741-30	White	
P8741-31	Black	


P8741-30





Featuring Aluminum Squares LED and Recessed

Pedestal Mount for Lanterns

Aluminum construction offers virtually maintenance-free benefits and sturdy operation that will last over time. Works with 3″ filter lanterns. Cannot mount to poles.

P8726-20 Antique Bronze
P8726-31 Black
Cast aluminum pedestal mount.
For mounting post lanterns
with 3″ fitters on pedestals
or on top of walls.
7″ dia., 3-1/4″ ht.


P8726-20


P8726-31

Night Saver® Shield

Shield fits over A-19 medium base bulb to provide Dark Sky friendly illumination.

P8709-20 Antique Bronze
P8709-31 Black
Nightsaver® lamp shade.
3″ bottom., 2-1/2″W top.

P8400-31 Black
Small dark sky shield.
4″ dia., 5-7/8″ ht.


P8709-20


P8709-31


P8400-31

All fixtures:

Dark Sky Compatibility List for P8400

Collection Name
ESSENTIAL (page 708)
P6059
P6060
P6086
P6512
RESORT (page 647)
P5987
P5988
P5989
P6504
P6606

Non-Metallic Par Lampholders

Ideal for environmental conditions where metallic fixtures are undesirable. UV stabilized non-metallic materials and non-corrosive hardware.



P5202-31

P5202-20 Bronze
P5202-31 Black
Single painted adjustable swivel floodlight. Aluminum construction.
Locking adjustment.
5-7/8″ dia., 9″ ht.
One PAR38, 150w max.



P5203-31

P5203-20 Bronze
P5203-30 White
P5203-31 Black
Two painted adjustable swivel floodlights with lamp shroud.
Aluminum construction.
6-1/4″ dia., 9″ ht.
Two PAR38, each 150w max.

P5207-30 White
Two painted adjustable swivel floodlights. Aluminum construction.
Locking adjustment.
4-7/8″ dia., 6-3/4″ ht.
Two PAR20, PAR30 or PAR38, each 150w max.

P5212-20 Bronze
P5212-30 White
Double non-metallic PAR lampholder.
11″ W., 4-5/8″ ht.
Extends 5″.
One PAR 38, 120w max.

P5214-30 White
PAR lampholder shroud for P5212.
6-5/8″ dia., 5-1/8″ ht.



P5207-30



P5212-30



P5202-20



P5212-20



P5214-30



P5203-20

Address Lights

Long lamp life (50,000 hours) and weather resistant. Housing constructed from high-grade polypropylene. Stainless steel mounting hardware and lamps included. Complies with municipal codes that require illuminated house numbers. Order 16V transformer separately.

Address Light Housing

Numbers, letters and blanks must be ordered separately from address light fixture.

P5968-31WB Black
Two-light address
light housing 12V.
12-1/2" W., 6-3/4" ht.
Extends 2-1/4".
2 T-3/1/4 5w xenon
wedge base, lamps included.

P5969-01
Transformer
16V 10w for P5968
2" W., 1-3/4" L.



P5968-31WB


P5969-01

Address Numbers

Numbers, letters and blanks must be ordered separately from address light fixture, P5968. Ten numbers per pack.

PRODUCT NO.	DESCRIPTION	SIZE
P5970-000	0	2-1/4" W., 5" ht.
P5970-001	1	
P5970-002	2	
P5970-003	3	
P5970-004	4	
P5970-005	5	
P5970-006	6 or 9	
P5970-007	7	
P5970-008	8	
P5970-HLF	1/2	
P5970-FBK	Full Blank	
P5970-HBK	Half Blank	1-1/8" W., 5" ht.


P5970-000


P5970-001


P5970-002


P5970-003


P5970-004


P5970-005


P5970-006


P5970-007


P5970-008

P5970-FBK

P5970-HBK



P5970-HLF

Door Chime

Includes transformer, chime assembly and lighted push button.

PC001-30 Textured White
One-chime kit with
10va transformer
4" W., 7-3/16" ht., Depth 2".


PC001-30

Photo Control

Remote mount photo control installs into standard, rain-tight junction box and includes faceplate and gasket. Max load 2000 watts. Operating range 40 + 140F. Consumes less than 1 watt.

PHOTOCONTROL
PTORK3010 Unfinished
3" W., 5" ht.


PTORK3010

Posts

Surround your home with decorative posts to add style and elegance for years to come. Aluminum construction and popular finish choices add to functionality of outdoor lighting.



P5390-20



P5390-31
P5394-31



P5391-20PC



P5391-31PC



P540005-031



P8748-31

P5390-20 Antique Bronze
Aluminum post.
P5390-31 Black
3″ dia., 7′ ht. (Can be cut to desired length).

P5390-31PC Black
Aluminum post with photocell which automatically turns on at dusk, off at dawn.
3″ dia., 7′ ht. (Can be cut to desired length).

P540005-031 Black
Fluted aluminum post.
3″ dia., 84″ ht.

P5391-31 Black
Aluminum post with ladder rest.
3″ dia., 7′ ht. (Can be cut to desired length).

P5391-20PC Antique Bronze
P5391-31PC Black
Aluminum post with ladder rest and photocell which automatically turns lantern on at dusk and off at dawn.
3″ dia., 7′ ht. (Can be cut to desired length).

P5392-31PC Black
Black aluminum post with ladder rest, photocell which automatically turns on at dusk off at down and weather proof GCO.
3″ dia., 7′ ht. (Can be cut to desired length).

P5394-31 Black
Commercial grade black aluminum post, .125 wall thickness.
3″ dia., 12′ ht. (Can be cut to desired length).

P8748-31 Black
Surface Mount Post Adapter
Flanged cast aluminum base for surface mounting round posts. Anchor bolts and allen set screws included.
8″ dia., 5″ ht.
3″ bottom O.D.

Pole Base Cover

Our decorative Pole Base Cover offers both form and function. A die-cast aluminum material is crafted into a handsome design and coated in a classic, powder-coated black finish. The base offers exceptional versatility with its ability to support three-inch smooth or fluted poles.



P860006-031

P860006-031 Black
11″ dia., 24″ ht.
Cast aluminum.
Fits 3″ smooth and fluted posts (sold separately).



Uplighting

Highlight or accent distinct plants, trees or accessories in your yard by positioning in-ground lights close to your focal point.

Shadowing

Add an elegant, but mysterious, touch to your outdoor design with this effect. Shadow lighting is typically achieved with uplighting placed out of sight to create silhouette images of trees, plants, and accessories.

Silhouetting

Produce an awe-inspiring effect by placing light fixtures directly behind your subject. Lights mounted near the bottom of a tree or shrub will cast the plant's shadow against the sky for an intriguing twilight display.

Grazing

Grazing light is an effect that illuminates the outline of a particular tree, shrub or architectural feature to enhance its shape and texture.



Design Tips

Security Lighting

Decorative outdoor lighting designs can also add security features for your home. The majority of residential crimes take place after dark when thieves feel they cannot be seen.

Path Lighting

Lighting along paths and driveways enhances the overall theme of your outdoor space while preventing accidents in the dark.

Landscape

Set the Scene.

Scan and see more at
progresslighting.com

Integrated LED Low Voltage

Several LED landscape lighting options are available for popular exterior applications. Low voltage LED landscape, bollard and path lights enhance outdoor settings, while adding safety, security and curb appeal to areas around the home. 3000K color temperature.

PATH LIGHT
P5245-20 Antique Bronze*
P5245-31 Black*
Die cast aluminum construction.
Includes stake and deck mount,
6-1/2" dia., 20-3/4" ht.
Extends 9-1/2".
One 1.5w LED module included.

LINEAR PATH LIGHT
P5246-31 Black*
Linear path light with ground stake.
Die cast aluminum construction
with louvered glass.
5-3/8 " W., 2-3/8" ht.
Extends 4-3/8".
One 1.5w LED module included.

BOLLARD
P5247-09 Brushed Nickel*
P5247-31 Black*
Slim bollard with cast aluminum construction. Frosted internal diffuser surrounded by clear plastic.
2-5/8" dia., 24" ht.
One 1.5w LED module included.

WELL LIGHT
P5295-31 Black
Die cast aluminum, glass cover.
Includes 4' cable and connector.
Cannot mount in concrete.
5" dia., 4" ht.
One 3w LED module included.
Use with P8270-31 transformer.

BALL LIGHT
P5296-31 Black
Die cast aluminum with black powder-coat finish. Polycarbonate diffuser. 12v AC input.
Use with LED transformer P8270-31.
4-1/8" dia., extends 2-1/4"
Three 1.5w LED modules included.

SPREAD LIGHT
P5297-31 Black*
Die cast aluminum construction.
Includes stake and deck mount,
4' cable and connector.
7" dia., 16-1/2" ht.
One 1.5w LED module included.

PATH LIGHT
P5298-31 Black*
Die cast aluminum construction.
Includes stake and deck mount,
4' cable and connector.
5-1/8" dia., 17-1/2" ht.
One 1.5w LED module included.

FLOOD LIGHT
P5299-31 Black
Adjustable knuckle for aiming.
Die cast aluminum.
Stake and deck mount,
4' cable and connector included.
4-1/2" dia., 6-5/8" ht.
One 3w LED module included.
Use with P8270-31 transformer.

*See page 762 for available 12V low voltage transformers.

All low voltage LED fixtures require connection to a 12V low voltage transformer.


P5245-20


P5245-31


P5247-09


P5247-31


P5298-31


P5297-31


P5296-31


P5295-31


P5246-31


P5299-31

Line Voltage



P5204-38



P5204-31



P5235-31



P5205-31



P5313-31



P5205-31

shown with P5313-31 pole

PAGODA
P5204-38 Green
P5204-31 Black
Die-cast aluminum. Clear glass liner.
½ NPS threaded fitting for permanent or P5233 for portable installation.
Cannot be used with P5312-31.
6″ dia., 7-1/8″ ht.
One medium base lamp, 100w max.

BOLLARD
P5205-31 Black
Etched glass.
½ NPS threaded fitting for permanent or P5233 installation.
For Bollard mount order with P5313-31 pole or P8562-31 page 761.
5″ dia., 6-1/4″ ht.
One medium base lamp, 60w max.

FLOOD LIGHT
P5235-31 Black*
Black powder-coat painted aluminum resists chipping and fading. Clear lens. Locking vertical adjustment.
5-1/4″ dia., 8-1/4″ long.
One PAR 38, 150w max.

BOLLARD AND POLE
P5313-31 Black
Bollard Pole for P5205-31. (order each separately).
4-3/4″ dia., 28-3/8″ ht.
Accepts P5205-31 only.

BOLLARD POLE MOUNT
Mount P5205-31 on top of bollard to spread wider circles of light and to coordinate ground lights with bollards. Aluminum construction with pedestal and “J” bolts for surface mounting on paved areas or atop walls. For complete unit order bollard accessory and light.

**See page 761 for flood light accent accessories.*

Low Voltage

CAST ALUMINUM SHADE
P5253-20 Antique Bronze
With wire guard and etched glass enclosure. Solid brass stem.
6" W., 26" ht.
Extends 6-7/8".
One 12V T5 wedge base, 18w max. included.

TIFFANY ART GLASS
P5271-20 Antique Bronze
Green art glass shade suspended from detailed arm.
Solid brass construction.
6-7/8" dia., 23" ht.
Extends 9-1/4".
One 12V T5 wedge base, 18w max. included.

CRANBROOK
P5276-71 Gilded Iron
Tiffany art glass
5-1/8" dia., 25" ht.
Extends 6-1/4".
One 12V T5 wedge base, 18w max. included.

PAGODA
P5219-31 Black
Die-cast aluminum. Clear glass liner.
½ NPS threaded fitting.
6" dia., 7 1/8" ht.
One 12V T5 wedge base, 18W max, lamp included.

ARTS & CRAFTS
P5272-46 Weathered Bronze
Light honey art glass panels.
Solid brass construction.
5-1/2" W., 28-3/4" ht.
Extends 6-5/8".
One 12V T5 wedge base, 18w max. included.

MISSION
P5261-46 Weathered Bronze
Light honey art glass.
Solid brass construction.
6-1/2" sq., 19-3/8" ht.
Extends 5-1/4".
One 12V T5 wedge base, 18w max. included.

COVENTRY
P5275-31 Black
Water seeded glass.
5-3/4" dia., 25" ht.
Extends 5-3/4".
One 12V T5 wedge base, 18w max. included.

All low voltage incandescent fixtures require connection to a 12V low voltage transformer. See page 762-763 for available 12V low voltage transformers. Except where noted, all 12V low voltage fixtures include: ½ NPS threaded adaptor connector (P8651), mounting stake (P8618-31), and lamp. 12V T5 LED wedge base lamps (supplied by others) may be used in place of supplied 12V T5 Xenon wedge base bulbs.

Lighting walkways, paths, steps and driveways will welcome your guests and help prevent unwanted accidents.The first impression of a home or business is the entryway, and it is important that care be taken to light it properly.


P5253-20


P5272-46


P5271-20


P5261-46


P5276-71


P5275-31


P5219-31

Low Voltage

Post Mount



P5262-46

Linear Mount



P5200-20

Flood Light



P5230-31



P8671-31

MISSION
P5262-46 Weathered Bronze
Rail mount or post lantern.
Fits 4" x 4" post or flush mount.
6-1/2" W., 7-1/2" ht.
One T5 wedge base,
18w max. included.

LINEAR PATH LIGHT
P5200-20 Antique Bronze
Cast solid bronze.
Furnished with stake.
7" W., 1-7/8" ht.
One 12-volt T5 wedge base,
18w max. included.

FLOOD LIGHT
P5230-31 Black
Miniature low voltage spot light.
Black powder coat
painted aluminum.
Locking vertical adjustment.
Mounting stake included.
3" dia., 5" long.
One 12V MR16, 50w max.
Lamp not included.

FLOOD MOUNT ACCESSORY
P8671-31 Black
Polycarbonate canopy for
surface mount. ½ NPS thread.
Low voltage only.
4-1/4" dia. Extends 1-3/16".

Must be connected to a 12V transformer, page 762-763.

Landscape Installation Accessories

Installation accessories work with all fixture styles (where applicable).

P8651-01 Black
Low voltage Quick-connector.
Allows #10 or #12 gauge outdoor
low voltage cable to connect to
an 18 gauge wire from fixture.
1-5/8" W., 1-1/4" L., 5/8" ht.



P8672-31 Black
Miniature pedestal mount. Powder-
coat painted cast metal. Flanged base
for surface mounting. ½ NPS thread.
Low voltage only.
1-1/2" dia., 1" ht.



P8708-01 Silicone filled
underground direct burial wire
connector. #20-#10 gauge.
10 per pack (1 standard pack =
10 pieces).
1-5/8" L., 5/8" dia.



P8618-31 Black
Ground stake, 8-3/4" ABS movable stake
for direct mounting of 12v landscape lights.
½ NPS thread.



P8562-31 Black
Quick-mount landscape post for 120v or 12v PVC.
3" dia., 20" length with stabilizing grid and post,
½ NPS threaded hole. Wet location listed.



Mounting Stems ½ NPS threads

16" stem	**P8666-31**	Black
	P8666-38	Green
8" stem	**P8667-31**	Black
	P8667-38	Green



P7801-01 Lamp
18w T5 wedge base lamp.
Replacement for standard
low voltage fixtures.



Outdoor Transformers

LED Low Voltage Transformer

P8270-31 Non metallic case protects timer controls and 120v to 12v transformer. Surge protected with grounded cord/plug set and easy 12V cable attachment. Photocontrol triggers "time on", eliminating seasonal adjustment. 56w max. Non-dimmable. Recommend using 14 gauge cable.



P8270-31

PRODUCT	WATT	DESCRIPTION	SIZE (W X H X D)
P8270-31	56	45w LED	4" x 5-5/8" x 3-1/2"

The above electronic 12V LED low voltage transformer is designed to operate 12V low voltage LED fixtures only, It cannot operate low voltage incandescent or halogen fixtures.

Electronic Low Voltage

P8517-31 supplied with integral photo-cell. Non-metallic housing to prevent corrosion. Three foot 18-gauge cord with grounding plug. Suitable for outdoor installation only. 20w minimum.

P8518-31 supplied with remote mount photo-cell with auto setting and 2 hr., 6 hr., and 8 hr. shut off settings. Suitable for outdoor installation only. 20w minimum.



P8517-31



P8518-31

PRODUCT	WATT	DESCRIPTION	SIZE (W X H X D)
P8517-31	150	150w electronic	3-5/8" x 6-1/2" x 2-3/8"
P8518-31	300	300w electronic	5-1/8" x 7-1/4" x 2-3/4"

All fixtures:
The above electronic low voltage transformers are suitable for providing 12V power to both 12V low voltage incandescent fixtures and 12V low voltage LED fixtures.

Outdoor Transformers

Magnetic Low Voltage — Plug-In Compatible

- Multiple secondary taps of 12, 13 and 15 volts allow maximum light output and lamp life for long or short runs and loading variations (300, 600 and 900 watt units only).
- Three foot 12 gauge cord with grounding plug.
- Thermal protection in the primary circuit to avoid overheating.
- Resettable circuit breakers in secondary circuits for electrical safety and convenience.
- Weatherproof construction, powder-coat painted (P8522-31 and P8523-31).
- Stainless steel construction (P8519-01, P8520-01 and P8521-01).
- Easy open enclosure with KO's for hardwiring and photocell installation.
- Easy wire terminal board for secondary connections.
- For outdoor use.
- Plug in timer and photocell compatible, see below.


P8519-01


P8520-01


P8522-31


P8523-31

PRODUCT	WATT	DESCRIPTION	SIZE (W X H X D)
P8519-01	300	300w stainless steel	5-3/8" x 17" x 5-3/8"
P8520-01	600	(2) 300w circuits, stainless steel	6-5/8" x 17" x 5-5/8"
P8521-01	900	(3) 300w circuits, stainless steel	6-5/8" x 19" x 5-1/2"
P8522-31	300	300w	5-1/4" x 17" x 5-5/8"
P8523-31	600	(2) 300w circuits	6-1/2" x 17" x 5-5/8"


P8521-01
shown with access cover removed


P8521-01
shown with photocell (P8525-31)


P8521-01
shown with timer (P8524-01)


P8521-01
shown with photocell and timer (P8525-31 & P8524-01)

All fixtures:
The above magnetic low voltage transformers are suitable for providing 12V power to both 12V low voltage incandescent fixtures and 12V low voltage LED fixtures.

Magnetic Transformer Accessories

P8524-01 Two-prong plug-in timer
2-3/4" W., 3-1/8" ht.
Allows multiple settings.



P8531-01 Digital timer
3"w, 4-1/8" ht, extends 1-5/8"
Allows multiple settings.



P8525-31 Direct mount photo-cell.
1-5/8" dia., 4-7/8" length.
Turns transformer on at dusk and off when ambient light appears.



P8526-31 Remote mount photo-cell.
1-3/8" dia., 5-1/4" length
Turns on transformer at dusk and off when ambient light appears.
Includes 10 ft. of cord.



Step Lights LED

5w 3000K color temperature with 84+ CRI and a 120° beam spread. LED step/wall lights are available in a vertical or horizontal configuration for mounting into a single-gang wallbox.

FEATURES
- Integral power supply module in a compact package.
- Consumes less than 5w of power per fixture.
- Beam spread: 120 degrees.
- cCSAus listed for wet locations.
- Warm white 3000K LED's included.
- 84+ CRI.

P6827-0930K Brushed Nickel
P6827-2030K Antique Bronze
P6827-3030K White
P6827-3130K Black
Louvered horizontal step/wall light.
Wet location listed.
5-1/4" W. , 3-1/2" ht.
5w LED module included.


P6828-0930K


P6828-2030K

P6828-0930K Brushed Nickel
P6828-2030K Antique Bronze
P6828-3030K White
P6828-3130K Black
Louvered veritcal step/wall light.
Wet location listed.
3-1/2" W. , 5-1/4" ht.
5w LED module included.


P6828-3030K


P6828-3130K

P6829-0930K Brushed Nickel
P6829-2030K Antique Bronze
P6829-3030K White
P6829-3130K Black
Vertical step/wall light.
Wet location listed.
2-7/8" W., 4-1/2" ht.
5w LED module included.


P6829-2030K


P6829-0930K

P6832-0930K Brushed Nickel
P6832-2030K Antique Bronze
P6832-3030K White
P6832-3130K Black
Horizontal step/wall light.
Wet location listed.
2-7/8" ht., 4-1/2" W.
5w LED module included.


P6832-0930K


P6827-0930K


P6832-3130K



P6827-3030K



Featuring Aluminum Square LED and LED Step Lights



Featuring 6" LED Recessed



Recessed Downlighting

Useful *and* Practical Light

Scan and see more at
progresslighting.com

6″ Recessed
P8071-20-30K





Linkoln Dixon
Product Manager, Commercial Lighting

Light Bright & Now

with Linkoln

Mountain Modern style is all about clean lines and an uncluttered interior. With open layouts and tall ceilings, sweeping views command attention. Homes are big, bright and have a fresh aesthetic due in part to a more neutral color palette of whites, grays and blues. The design emphasis is placed on the building materials for texture like smooth glass, rough stone, chunky woodwork and textured concrete. Rather than covering up the details of the home, neutral colors allow the textures of all the elements to shine as the building materials become part of the decor. Lighting can be oversized, with airy, open designs that are meant to cast light without obstructing views from the plentiful windows in the space.

Shop this style at
progresslighting.com/modern-mountain



Edgelit Recessed LED

The LED edgelit recessed downlight combines a slim, low profile design with innovative technology, aesthetics, functionality and affordability. A separate recessed housing or junction box is not required for installation. The wet location listing allows for the product to be used in many applications, including showers. The low profile downlight is ideal for many residential, multi-family, commercial and hospitality applications. The detachable driver box can be removed from the fixture and mounted remotely when installing into shallow ceiling applications. The energy efficient design provides up to a 75% energy savings and up to 50,000 hours of LED life. The edgelit recessed luminaire can be dimmed down to 10%, flicker free, and is compatible with many forward phase (TRIAC) and electronic low voltage (ELV) dimmers.

TRIM FEATURES

- Features a detachable driver box, which can be mounted remotely for shallow ceiling installations.
- White polycarbonate lens controls direct glare from LEDs.
- No housing or J-box required for installation.
- Wet location listed.
- 120V input voltage.
- Dimmable to 10% with many Triac or ELV dimmers.
- IC rated and Air-Tight.
- Energy efficient design provides up to a 75% energy savings and up to 54,000 hours of LED life.
- Energy Star and Title 24 JA8-2016 listed.

5" LED EDGELIT
P800004-009-30 Brushed Nickel
P800004-020-30 Antique Bronze
P800004-028-30 White
P800004-031-30 Black
5" W., 3" ht.
9.5w integrated LED, 3000K, 90CRI, 550 lumens.

7" LED EDGELIT
P800005-009-30 Brushed Nickel
P800005-020-30 Antique Bronze
P800005-028-30 White
P800005-031-30 Black
7" W., 3" ht.
13w integrated LED, 3000K, 90CRI, 800 lumens.

All fixtures:


P800004-009-30


P800004-020-30


P800004-028-30


P800004-031-30



P800005-009-30


P800005-020-30


P800005-028-30


P800005-031-30


P800005-028-30
back view shown with junction box attached


P800004-028-30
back view shown with junction box attached


Edgelit Recessed Accessories

Progress lighting has released two new accessories for the Edgelit Recessed fixtures. P860040-028 - 18" extender cable allows for the junction box to be remote and mounted further away from the fixture. P860044 - rough in accessory allows for Edge Lit recessed fixtures to be used in new construction installations. This accessory ensures a mounting location after the dry wall is installed and can be used when building codes require that the luminaire is supported from the building structure

18" CABLE WITH TERMINALS
P860040-028 Satin White
18" L., 1/2" dia.




P860040-028



EDGELIT RECESSED ROUGH-IN ACCESSORY
P860044-001 Unfinished
20" W., 9" ht.



P860044-001



Emblem Round Recessed Trims LED

The Emblem Round LED recessed trim is ideal for use in both new construction as well as remodel/retrofit installations. Great for general ambient lighting applications. Offered in 4", 5" and 6" sizes and 4 finishes to match interior décor. The deep trim offers maximum glare control and the flat lens and bezel detail add a minimal and low profile look.

TRIM FEATURES

- The trim is equipped with both Edison base adapter and quick link connector allowing easy installation in many standard medium based socket recessed housings and Progress LED recessed housings.
- A polycarbonate diffused lens reduces glare and pixilation from LEDs.
- Trim uses friction springs for easy installation into recessed housings.
- cCSAus Listed for Wet Locations, Energy Star.
- Flicker free dimming down to 10% with many Triac or ELV dimmers.
- Suitable for use in IC and Non IC applications.
- LEDs are 3000K, CRI 90+ and rated for 50,000 hours.

4" Round Trim

P8080-09-30K Brushed Nickel
P8080-20-30K Antique Bronze
P8080-28-30K White
P8080-31-30K Black
Integrated LED, 630 lumens,
66 lumens per watt, equivalent
to 50W R20 incandescent lamp.


P8080-09-30K


P8080-20-30K


P8080-28-30K


P8080-31-30K

COMPATIBLE RECESSED HOUSINGS
P830-LED
P831-LED
P832-LED
P830-TG
P831-AT
P832-TG

5" Round Trim

P8061-09-30K Brushed Nickel
P8061-20-30K Antique Bronze
P8061-28-30K White
P8061-31-30K Black
Integrated LED, 700 lumens,
66 lumens per watt, equivalent
to 65W BR30 incandescent lamp.


P8061-09-30K


P8061-20-30K


P8061-28-30K


P8061-31-30K

COMPATIBLE RECESSED HOUSINGS
P84-LED
P851-ICAT
P1841-LED
P1851-ICAT
P1841-ICAT

6" Round Trim

P8071-09-30K Brushed Nickel
P8071-20-30K Antique Bronze
P8071-28-30K White
P8071-31-30K Black
Integrated LED, 725 lumens,
69 lumens per watt, equivalent
to 65W BR30 incandescent lamp.


P8071-20-30K


P8071-28-30K


P8071-31-30K


P8071-09-30K

COMPATIBLE RECESSED HOUSINGS
P87-AT
P87-ATQC
P87-LED
P187-TG

All fixtures:

Emblem Eyeball Recessed Trims LED

The Emblem Eyeball LED recessed trim is ideal for use in both new construction as well as remodel/retrofit installations. Adjustable light source is great for directing the light at walls and items you want to accent. Offered in 4", 5" and 6" sizes and 4 finishes to match interior décor. The deep trim offers 360° positioning and 30° tilt to adjust the beam direction.

TRIM FEATURES

- The trim is equipped with both Edison base adapter and quick link connector allowing easy installation in many standard medium based socket recessed housings and Progress LED recessed housings.
- A polycarbonate diffused lens reduces glare and pixilation from LEDs.
- Trim uses friction springs for easy installation into recessed housings.
- cCSAus Listed for Damp Locations, Energy Star.
- Flicker free dimming down to 10% with many Triac or ELV dimmers.
- Suitable for use in IC and Non IC applications.
- LEDs are 3000K, CRI 90+ and rated for 50,000 hours.

4" Eyeball Trim

P8046-09-30K Brushed Nickel
P8046-20-30K Antique Bronze
P8046-28-30K White
P8046-31-30K Black
Integrated LED, 630 lumens,
66 lumens per watt, equivalent to 50W
R20 incandescent lamp.


P8046-09-30K


P8046-20-30K


P8046-28-30K


P8046-31-30K

COMPATIBLE RECESSED HOUSINGS
P830-LED
P831-LED
P832-LED
P830-TG
P831-AT
P832-TG

5" Eyeball Trim

P8176-09-30K Brushed Nickel
P8176-20-30K Antique Bronze
P8176-28-30K White
P8176-31-30K Black
Integrated LED, 670 lumens,
63 lumens per watt, equivalent
to 65W BR30 incandescent lamp.


P8176-09-30K


P8176-20-30K


P8176-28-30K


P8176-31-30K

COMPATIBLE RECESSED HOUSINGS
P84-LED
P851-ICAT
P1841-LED
P1851-ICAT
P1841-ICAT

6" Eyeball Trim

P8076-09-30K Brushed Nickel
P8076-20-30K Antique Bronze
P8076-28-30K White
P8076-31-30K Black
Integrated LED, 700 lumens,
66 lumens per watt, equivalent
to 65W BR30 incandescent lamp.


P8076-09-30K


P8076-20-30K


P8076-28-30K


P8076-31-30K

COMPATIBLE RECESSED HOUSINGS
P87-AT
P87-ATQC
P87-LED
P187-TG

All fixtures:

4″ Recessed LED

LED Housings

For complete fixture, order housing with trim.



New Construction Non-IC
with LED Quick Connect

P830-LED
Ceiling opening: 4-1/2″
Plaster frame: 7-7/8″ x 10-3/4″
Recessed depth: 5-1/2″
Pryouts: 1/2″ and 3/4″

P830-LED HOUSING FEATURES
- Integral quick link connector mates with P8080 and P8046 series LED trims.



New Construction Air-Tight IC
with LED Quick Connect

P831-LED
Ceiling opening: 4-1/2″
Plaster frame: 8-3/8″ x 13″
Recessed depth: 7-1/2″

P831-LED HOUSING FEATURES
- Integral quick link connector mates with P8080 and P8046 series LED trims.



Remodel Non-IC
with LED Quick Connect

P832-LED
Ceiling opening: 4-1/4″
Recessed depth: 5-1/2″
Pryouts: 1/2″

P832-LED HOUSING FEATURES
- Retrofit version of P830-LED for use in existing ceilings.

4″ LED Round Trim

Flicker free dimming down to 10% with many Triac or forward phase dimmers. Flicker rate less than 30%.

P8080-09-30K Brushed Nickel
P8080-20-30K Antique Bronze
P8080-28-30K White
P8080-31-30K Black
9.5w integrated LED, 3000K, 90CRI, 630 lumens.



P8080-09-30K



P8080-20-30K



P8080-28-30K



P8080-31-30K

P8080 & P8046 TRIM FEATURES
- Frosted polycarbonate lens controls direct glare from LEDs.
- cULus listed for wet locations.
- Lumen output and distribution comparable to 50w R20 incandescent lamp.
- CRI is 90+.
- Suitable for use in IC or NON-IC applications.
- 50,000 hours life based on 70% lumen maintenance (TM-21).

4″ LED Eyeball Trim

Flicker free dimming down to 10% with many Triac or forward phase dimmers. Flicker rate less than 30%.

P8046-09-30K Brushed Nickel
P8046-20-30K Antique Bronze
P8046-28-30K White
P8046-31-30K Black
9.5w integrated LED, 3000K, 90CRI, 630 lumens.



P8046-09-30K



P8046-20-30K



P8046-28-30K



P8046-31-30K

5″ Recessed LED

LED Housings

For complete fixture, order housing with trim.



New Construction Air-Tight IC
with LED Quick Connect

P84-LED
Ceiling opening: 5-1/4″
Plaster frame: 7-7/8″ x 10-3/4″
Recessed depth: 5-1/2″
Pryouts: 1/2″ and 3/4″

P84-LED HOUSING FEATURES
- Integral quick connectors mate with P8061 and P8176 series.



Remodel Air-Tight IC
with LED Quick Connect

P1841-LED
Ceiling opening: 5-1/2″
Recessed depth: 5-3/8″
Pryouts: 1/2″

P1841-LED HOUSING FEATURES
- Rated for direct contact with insulated ceiling.
- Adjustable housing to accommodate ceiling thickness 1/2″ to 1-1/2″ .
- Meets ASTM-E283 air flow requirements.

5″ LED Round Trim

Flicker free dimming down to 10% with many Triac or forward phase dimmers. Flicker rate less than 30%.

P8061-09-30K Brushed Nickel
P8061-20-30K Antique Bronze
P8061-28-30K White
P8061-31-30K Black
10.5w integrated LED, 3000K, 90CRI, 700 lumens.



P8061-09-30K



P8061-20-30K



P8061-28-30K



P8061-31-30K

P8061 & P8176 TRIM FEATURES
- Frosted polycarbonate lens controls direct glare from LEDs.
- cULus listed for wet locations.
- Lumen output and distribution comparable to 65w BR30 incandescent lamp.
- CRI is 90+ rivaling CFL.
- Suitable for use in IC or NON-IC applications.
- 50,000 hours life based on 70% lumen maintenance (TM-21).

5″ LED Eyeball Trim

Flicker free dimming down to 10% with many Triac or forward phase dimmers. Flicker rate less than 30%.

P8176-09-30K Brushed Nickel
P8176-20-30K Antique Bronze
P8176-28-30K White
P8176-31-30K Black
10.5w integrated LED, 3000K, 90CRI, 670 lumens.



P8176-09-30K



P8176-20-30K



P8176-28-30K



P8176-31-30K

6″ Recessed LED

LED Housing - New Construction

For complete fixture, order housing with trim.



New Construction Air-Tight IC & Non-IC with LED Quick Connect

P87-LED
Ceiling opening: 6-7/8″ dia.
Plaster frame: 7-7/8″ x 10-3/4″
Recessed depth: 7-1/2″
Pryouts: 1/2″ & 3/4″

P87-LED HOUSING FEATURES
- Integral quick connect mates with P8071 and P8076 series LED trims.

6″ LED Trim 1000 Lumens

Flicker free dimming down to 10% with many Triac or forward phase dimmers. Flicker rate less than 30%.

P8071-2830K-L10-STR2 White
12w integrated LED, 3000K,
80 CRI, 1000 lumens.

P8071-2835K-L10-STR2 White
12w integrated LED, 3500K,
80 CRI, 1000 lumens.

All fixtures:



P8071-2830K-L10-STR2



P8071-2835K-L10-STR2



Includes Edison base socket and Quick-Link connector

P8071 & P8076 TRIM FEATURES
- Frosted polycarbonate lens controls direct glare from the LEDs.
- cULus listed for wet locations.
- 12-watt input power.
- Lumen output 1037 lumens.
- Lumen output and distribution comparable to a 75w PAR30 incandescent lamp.
- CRI is 80+.
- Suitable for use in IC or NON-IC applications.
- 60,000 hours life based on 70% lumen maintenance (TM-21).

6″ LED Round Trim

Flicker free dimming with Triac or forward phase dimmers. Flicker rate less than 30%.

P8071-09-30K Brushed Nickel
P8071-20-30K Antique Bronze
P8071-28-30K White
P8071-31-30K Black
10.5w integrated LED, 3000K,
90CRI, 725 lumens.



P8071-09-30K



P8071-20-30K



P8071-28-30K



P8071-31-30K

6″ LED Eyeball Trim

Flicker free dimming down to 10% with many Triac or forward phase dimmers. Flicker rate less than 30%.

P8076-09-30K Brushed Nickel
P8076-20-30K Antique Bronze
P8076-28-30K White
P8076-31-30K Black
10.5w integrated LED, 3000K,
90CRI, 700 lumens.



P8076-09-30K



P8076-20-30K



P8076-28-30K



P8076-31-30K

Featuring 6" LED Recessed Trim and Penn by Design Series™
Image: Richmond American Homes



4″ Low Voltage MR 16

Low Voltage Housings

For complete fixture, order housing with trim.



New Construction Air-Tight IC
with G8 socket

P817-AT
Ceiling opening: 4-1/2″
Plaster frame: 15-3/4″ x 9-3/4″
Recessed depth: 7-1/2″
Pryouts: 1/2″ and 3/4″

P817-AT HOUSING FEATURES
- UL and CUL Listed for damp locations and through wiring.
- Meets Washington State Energy Code requirements.
- Can be installed in ceilings from 1/2″ to 2-1/2″ thick.
- Electronic transformer.
- Rated for 8 #12 90° conductors (4 in/4 out).



New Construction Non-IC
with G8 socket

P816-TG
Ceiling opening: 4-1/2″
Plaster frame: 7-7/8″ x 10-3/4″
Recessed depth: 5-1/2″
Pryouts: 1/2″ and 3/4″

P816-TG HOUSING FEATURES
- UL and CUL Listed for damp locations and through wiring.
- Can be installed in ceilings from 1/2″ to 2-1/2″ thick.
- Magnetic transformer.
- Rated for 8 #12 90° conductors (4 in/4 out).



Remodel Non-IC
with G8 socket

P818-TG
Ceiling opening: 4-1/4″
Recessed depth: 5-1/2″
Pryouts: 1/2″

P818-TG HOUSING FEATURES
- Integral flange on housing and exclusive locking bars permit quick mounting on ceilings from 1/2″ to 1″ thick.
- UL & CUL Listed for damp locations.
- Magnetic transformer.
- Rated for 60° supply wires in end-of-run applications.
- Rated for 4 #12 90° conductors (2 in/2 out).

IC Trims & Non-IC Trims

5″ outside diameter. All trims have 360° positioning. Lamps tilt 30°.



STEP BAFFLE
P8037-28 White Baffle
IC & Non-IC:
12V 50w MR16



STEP BAFFLE
P8037-31 Black Baffle
IC & Non-IC:
12V 50w MR16



STEP BAFFLE
P8037-09 Brushed Nickel
IC & Non-IC:
12V 50w MR16



SLOTTED
P8039-28 White
IC: 12V 35w MR16
Non-IC: 12V 50w MR16



PINHOLE
P8036-28 White
IC: 12V 35w MR16
Non-IC: 12V 50w MR16



WALL WASHER
P8045-31 White w/Black Baffle
IC: 12V 35w MR16
Non-IC: 12V 50w MR16



EYEBALL
P8057-28 White
IC/Non-IC:
12V 50w MR16



EYEBALL
P8057-20 Antique Bronze
IC & Non-IC:
12V 50w MR16

Lamp wattages shown are maximum.
For accessories see page 795 for details.

4″ Recessed

Housings

For complete fixture, order housing with trim.



New Construction Air-Tight IC
with E26 socket

P831-AT
Ceiling opening: 4-1/2″
Plaster frame: 8-3/8″ x 13″
Recessed depth: 7-1/2″

P831-AT HOUSING FEATURES

- UL and CUL listed for damp locations and feed through wiring.
- Meets WSEC code requirements.
- Adjustable from 1/2″ to 2-1/2″ ceiling thickness.
- Notched plaster frame for easy alignment.
- Locking feature to secure housing.
- Integral T-bar clamps.
- Nail grip bar hangers accommodate up to 24″ on center ceiling joists.
- Rated for 8 #12 90° conductors (4 in/4 out).
- Integral Romex clamp.
- Trim mounted socket snaps into trim for consistent lamp positioning.
- Shipped in air-tight configuration.



New Construction Non-IC
with E26 socket

P830-TG
Ceiling opening: 4-1/2″
Plaster frame: 7-7/8″ x 10-3/4″
Recessed depth: 5-1/2″
Pryouts: 1/2″ and 3/4″

P830-AT HOUSING FEATURES

- UL and CUL listed for damp locations and feed through wiring.
- Adjustable from 1/2″ to 2-1/2″ ceiling thickness.
- Notched plaster frame for easy alignment.
- Locking feature to secure housing.
- Integral T-bar clamps.
- Nail grip bar hangers accommodate up to 24″ on center ceiling joists.
- Rated for 8 #12 90° conductors (4 in/4 out).
- Integral Romex clamp.
- Trim mounted socket snaps into trim for consistent lamp positioning.



Remodel Non-IC
with E26 socket

P832-TG
Ceiling opening: 4-1/4″
Recessed depth: 5-1/2″
Pryouts: 1/2″

P832-AT HOUSING FEATURES

- Retrofit version of P830-TG for use in existing ceilings.
- UL and CUL listed for damp locations and through wiring.
- Integral flange on housing and exclusive locking bars permits quick mounting in ceilings from 1/2″ to 1″ thick.
- Attached junction box with removable sides.

IC Trims & Non-IC Trims

5″ outside diameter. Lamps tilt 20°.



OPEN
P8041-28 White
IC & Non-IC:
50w PAR20, R20



OPEN SHOWER TRIM
P8041WL-28 White
Wet location listed.
IC & Non-IC:
50w PAR20*
**WL trims require use with outdoor rated PAR lamps.*



PINHOLE
P8042-28 White
IC & Non-IC:
40w PAR16, 30w R20



STEP BAFFLE
P8044-31 Black Baffle
P8044-09 Brushed Nickel
P8044-20 Antique Bronze
P8044-28 White Baffle
IC & Non-IC:
55w PAR16, 50w PAR20, R20



WALL WASHER
P8047-31 White w/Black Baffle
IC & Non-IC:
40w PAR16, 35w R 20



EYEBALL
P8046-28 White
P8046-09 Brushed Nickel
P8046-20 Antique Bronze
IC & Non-IC:
40w PAR16, 30w R 20

LED IC Trims

LED EYEBALL
P8046-09-30K Brushed Nickel
P8046-20-30K Antique Bronze
P8046-28-30K White
P8046-31-30K Black
9.5w integrated LED, 3000K,
90CRI, 630 lumens.




LED ROUND
P8080-09-30K Brushed Nickel
P8080-20-30K Antique Bronze
P8080-28-30K White
P8080-31-30K Black
9.5w integrated LED, 3000K,
90CRI, 630 lumens.

5″ Recessed

Housings

For complete fixture, order housing with trim.



New Construction Air-Tight IC with E26 socket

P851-ICAT
Ceiling opening: 5-1/2″
Recessed depth: 5-3/8″
Pryouts: 1/2″ and 3/4″

P851-ICAT HOUSING FEATURES
- Rated for direct contact with insulated ceiling.
- Meets ASTM-E283 air flow requirements.
- Adjustable housing to accommodate ceiling thickness.
- Bar hangers with integral nail, can be installed up to 24″ joists.
- Use with compatible items only.



Remodel Air-Tight IC with E26 socket

P1851-ICAT
Ceiling opening: 5-1/2″
Recessed depth: 7-3/16″
Pryouts: 1/2″

P1851-ICAT HOUSING FEATURES
- Rated for direct contact with insulated ceiling.
- Meets ASTM-E283 air flow requirements.
- Adjustable housing to accommodate ceiling thickness 1/2″ to 1-1/2″.

IC Trims & Non-IC Trims

6-1/2″ outside diameter.



STEP BAFFLE
P868-31 Black
Damp location listed.
50w max. PAR30/R30



STEP BAFFLE
P868-28 White
50w PAR30/R30



EYEBALL
P876-28 White
75w PAR30



OPEN
P8268-21 Clear Alzak
With gasket.
Damp location listed.
50w max. PAR30/R30

OPEN
P8268-28 Satin White
With gasket.
Damp location listed.
50w max. PAR30/R30



SHOWER TRIM
P867WL-28 White
Wet location listed when used with an outdoor rated PAR30 lamp. 50w PAR30*

**WL trims require use with outdoor rated PAR lamps*

LED IC Trims

LED ROUND
P8061-09-30K Brushed Nickel
P8061-20-30K Antique Bronze
P8061-28-30K White
P8061-31-30K Black
10.5w integrated LED, 3000K, 90CRI, 725 lumens.



P8061-09-30K



P8061-20-30K



P8061-28-30K



P8061-31-30K

LED EYEBALL
P8176-09-30K Brushed Nickel
P8176-20-30K Antique Bronze
P8176-28-30K White
P8176-31-30K Black
10.5w integrated LED, 3000K, 90CRI, 700 lumens.



P8176-09-30K



P8176-31-30K



P8176-20-30K



P8176-28-30K

All fixtures:



Featuring 5" Recessed and Gust
Image: Schumacher Homes

5″ Recessed

Shallow Housing

For complete fixture, order housing with trim.



New Construction Air-Tight IC and Non-IC with E26 socket

P84-AT
Ceiling opening: 5-1/4″
Plaster frame: 7-7/8″ x 10-3/4″
Recessed depth: 5-1/4″
Pryouts: 1/2″ and 3/4″

P84-AT HOUSING FEATURES
- Shallow profile (5-1/2″) for 2x6 construction.
- UL & CUL listed for damp locations & through wiring.
- Meets Washington State Energy Code requirements.
- Can be installed in ceilings from 1/2″ to 1-1/2″ thick.
- Notched mounting frame for easy alignment.
- Locking feature to secure housing.
- Integral T-bar clamps.
- Nail grip bar hangers accommodate up to 24″ on center ceiling joists.
- Slotted interlocking bar hangers provide solid mounting on 24″ centers.
- Rated for 8 #12 90 degree conductors (4 in/4 out).
- Integral Romex clamps.
- Trims are easy-in & push-lock into place.
- Adjustable lamp position.

IC Trims & Non-IC Trims

For insulated or non-insulated ceilings. 6-1/8″ outside diameter, except where indicated.



SHALLOW BAFFLE
P8375-28 White
P8375-31 Black
65w BR-30, 50w PAR-30



OPEN
P8368-28 White
65w BR-30, 50w PAR-30



EYEBALL
P8176-28 White
6-3/8″ dia.
75w PAR-30 Short Neck



DROP OPAL SHOWER
P8109-28 White
Wet location listed.
Metal flange.
30w R-20



OPEN SHOWER TRIM
P8367-WL28 White
Wet location listed.
50w PAR30*

** WL trims require use with outdoor rated PAR lamps*

LED IC Trims

All fixtures:



LED ROUND
P8061-09-30K Brushed Nickel
10.5w integrated LED, 3000K, 90CRI, 700 lumens.



LED ROUND
P8061-20-30K Antique Bronze
10.5w integrated LED, 3000K, 90CRI, 700 lumens.



LED ROUND
P8061-28-30K White
10.5w integrated LED, 3000K, 90CRI, 700 lumens.



LED ROUND
P8061-31-30K Black
10.5w integrated LED, 3000K, 90CRI, 700 lumens.



LED EYEBALL
P8176-09-30K Brushed Nickel
10.5w integrated LED, 3000K, 90CRI, 670 lumens.



LED EYEBALL
P8176-20-30K Antique Bronze
10.5w integrated LED, 3000K, 90CRI, 670 lumens.



LED EYEBALL
P8176-28-30K White
10.5w integrated LED, 3000K, 90CRI, 670 lumens.



LED EYEBALL
P8176-31-30K Black
10.5w integrated LED, 3000K, 90CRI, 670 lumens.

5″ Recessed

Shallow Remodel Housing

For complete fixture, order housing with trim.



Remodel Air-Tight IC
with E26 Socket

P1841-ICAT
Ceiling opening: 5-1/2″
Recessed depth: 5-3/8″
Pryouts: 1/2″

P1841-ICAT HOUSING FEATURES
- Rated for direct contact with insulated ceiling.
- Meets ASTM-E283 air flow requirements.
- Adjustable housing to accommodate ceiling thickness 1/2″ to 1-1/2″.
- Use with compatible items only.

c UL us LISTED

IC Trim

6-1/2″ outside diameter. Can also be used with P851-ICAT.



SHALLOW STEP BAFFLE
P8475-28 Satin White
Damp location listed.
Lamp: PAR30/R30, 50w max.
Compatible with **P851-ICAT and P1841-ICAT.**



SHOWER TRIM
P867WL-28 White
Wet location listed when used with an outdoor rated PAR30 lamp. 50w PAR30*
**WL trims require use with outdoor rated PAR lamps*



EYEBALL
P876-28 White
75w PAR30

LED IC Trims

All fixtures:



LED ROUND
P8061-09-30K Brushed Nickel
10.5w integrated LED, 3000K, 90CRI, 700 lumens.



LED ROUND
P8061-20-30K Antique Bronze
10.5w integrated LED, 3000K, 90CRI, 700 lumens.



LED ROUND
P8061-28-30K White
10.5w integrated LED, 3000K, 90CRI, 700 lumens.



LED ROUND
P8061-31-30K Black
10.5w integrated LED, 3000K, 90CRI, 700 lumens.



LED EYEBALL
P8176-09-30K Brushed Nickel
10.5w integrated LED, 3000K, 90CRI, 670 lumens.



LED EYEBALL
P8176-20-30K Antique Bronze
10.5w integrated LED, 3000K, 90CRI, 670 lumens.



LED EYEBALL
P8176-28-30K White
10.5w integrated LED, 3000K, 90CRI, 670 lumens.



LED EYEBALL
P8176-31-30K Black
10.5w integrated LED, 3000K, 90CRI, 670 lumens.

6″ Recessed

Housings

For complete fixture, order housing with trim.



New Construction Air-Tight IC & Non-IC with E26 socket

P87-AT
Ceiling opening: 6-7/8″ dia.
Plaster frame: 7-7/8″ x 10-3/4″
Recessed depth: 7-1/4″
Pryouts: 1/2″ & 3/4″

P87-AT HOUSING FEATURES
- UL & CUL listed for damp locations and through wiring.
- Meets Washington State Energy Code requirements.
- Can be installed in ceilings from 1/2″ to 2-1/2″ thick.
- Tool-less can adjustment for varying ceiling thickness.
- Slotted, interlocking bar hangers securely span 24″ T-bar spacing.
- Integral Romex clamp.
- Full reflector design eliminates light leaks.
- Rated for 8 #12 90° conductors (4 in/4 out).
- US Patent #5758959, 5857766, 6004011.



New Construction Air-Tight IC & Non-IC with E26 socket

P87-ATQC
Ceiling opening: 6-7/8″ dia.
Plaster frame: 7-7/8″ x 10-3/4″
Recessed depth: 7-1/4″
Pryouts: 1/2″ & 3/4″

P87-ATQC HOUSING FEATURES
- UL & CUL listed for damp locations and through wiring.
- Meets Washington State Energy Code requirements.
- Can be installed in ceilings from 1/2″ to 2-1/2″ thick.
- Tool-less can adjustment for varying ceiling thickness.
- Slotted, interlocking bar hangers securely span 24″ T-bar spacing.
- Quick-connects allow simple installation of 12-20 AWG wire, without the need for wire nuts.
- Integral Romex clamp.
- Full reflector design eliminates light leaks.
- Rated for 8 #12 90° conductors (4 in/4 out).
- US Patent #5758959, 5857766, 6004011.



Remodel IC and Non-IC with E26 socket

P187-TG
Ceiling opening: 6-5/8″ dia.
Recessed depth: 7-1/2″
Pryouts: 1/2″

P187-TG HOUSING FEATURES
- Retrofit version of the P87-AT.
- UL and CUL listed for damp locations and through wiring.
- IC/Non-IC peel away label for field conversion.
- Can be installed in ceilings from 1/2″ to 1-1/2″ thick.
- Exclusive mounting slide bars permit quick and solid mounting in ceilings.
- Rated for 4 #12 90° conductors (2 in/2 out).
- Rated for 60° supply wires in end-of-run applications.
- US Patent #5758959.
- P187-TG can be converted to Air Tight in the field with P8593-01 Gasket Kit. See page 795.

LED IC Trims

All fixtures:



LED ROUND
P8071-09-30K Brushed Nickel
10.5w integrated LED, 3000K, 90CRI, 725 lumens.



LED ROUND
P8071-20-30K Antique Bronze
10.5w integrated LED, 3000K, 90CRI, 725 lumens.



LED ROUND
P8071-28-30K White
10.5w integrated LED, 3000K, 90CRI, 725 lumens.



LED ROUND
P8071-31-30K Black
10.5w integrated LED, 3000K, 90CRI, 725 lumens.



LED EYEBALL
P8076-09-30K Brushed Nickel
10.5w integrated LED, 3000K, 90CRI, 700 lumens.



LED EYEBALL
P8076-20-30K Antique Bronze
10.5w integrated LED, 3000K, 90CRI, 700 lumens.



LED EYEBALL
P8076-28-30K White
10.5w integrated LED, 3000K, 90CRI, 700 lumens.



LED EYEBALL
P8076-31-30K Black
10.5w integrated LED, 3000K, 90CRI, 700 lumens.

6″ Recessed

IC Trims & Non-IC Trims

For insulated or non-insulated ceilings. 7-3/4″ outside diameter, except where indicated.



STEP BAFFLE
P8066-28 White
IC: 75w PAR30, 65w BR30
Non-IC: 150w PAR38, 120w BR40, 40w A19



STEP BAFFLE
P8066-20 Antique Bronze
Unpainted flange.
IC: 75w PAR30, 65w BR30
Non-IC: 150w PAR38, 120w BR40, 40w A19



STEP BAFFLE
P8066-31 Black
White flange.
IC: 75w PAR30, 65w BR30
Non-IC: 150w PAR38, 120w BR40, 40w A19



STEP BAFFLE
P8082-31 Black
P8082-28 White
8-3/4″ dia.
IC: 90w PAR38, BR40
Non-IC: 150w PAR38, 150w BR40



LONG NECK BAFFLE
P8075-28 White
P8075-31 Black
IC: 65w BR30 75w PAR30 Long Neck
Non-IC: 100w A19, 75w PAR30 Long Neck, 85w BR30



EYEBALL
P8076-20 Antique Bronze
Rotates 358°, tilts 30° max.
IC & Non-IC:
75w PAR30, 65w BR30



EYEBALL
P8076-09 Brushed Nickel
P8076-28 White
Rotates 358°, tilts 30° max.
IC & Non-IC:
75w PAR30, 65w BR30



BAFFLED MINI EYEBALL
P8077-28 White Baffle
Rotates 358°, tilts 30° max.
IC & Non-IC:
75w R20, PAR20



REGRESSED BAFFLED EYEBALL
P8079-28 White Baffle
Rotates 358°, tilts 30° max.
IC: 65w BR30, 50w PAR30
Non-IC: 75w PAR30, 85w BR30



REGRESSED BAFFLED EYEBALL
P8079-31 Black Baffle
Rotates 358°, tilts 30° max.
IC: 65w BR30, 50w PAR30
Non-IC: 75w PAR30, 85w BR30



OPEN
P8074-28 White
8-3/4″ dia.
IC: 90w BR40/PAR38
Non-IC: 150w PAR38, 120w BR40



OPEN SPLAY
P8072-28 White
IC: 75w PAR30 Long Neck, 65w BR30
Non-IC: 75w PAR30 Long Neck, 100w A19, 85w BR30



CONES
P8068-21A Clear Alzak®
White flange.
IC: 75w PAR30, 65w BR30
Non-IC: 150w PAR38, 120w BR40, 40w A19



CONES
P8068-28 White
White flange.
IC: 75w PAR30, 65w BR30
Non-IC: 150w PAR38, 120w BR40, 40w A19



DROP OPAL SHOWER
P8007-60 White
Wet location listed.
Metal flange.
8-1/4″ dia.
IC: 60w A19, 50w PAR30
Non-IC: 100w A19, 75w PAR30



DROP OPAL SHOWER
P8009-60 White Glass
Wet location listed.
Non-metallic flange.
IC: 40w A19, 50w PAR30
Non-IC: 75w A19, 75w PAR30



DOME SHOWER
P8025-60 White Polycarbonate
Wet location listed.
8-3/4″ dia.
IC: 40w A 19
Non-IC: 75w A19



OPEN SHOWER
P8072WL-28* White
Wet location listed.
Metal flange.
IC & Non-IC:
50w PAR30* Long Neck
** WL trims require use with outdoor rated PAR lamps*



OPEN SHOWER
P8074WL-28 White
Wet location listed.
Metal flange.
7-3/4″ dia.
IC & Non-IC:
75w PAR38*
** WL trims require use with outdoor rated PAR lamps*



FRESNEL SHOWER
P8011-60 White
Wet location listed Non-metallic flange
IC: 50w PAR30 SN
Non-IC: 75w PAR30 Short Neck



PIN HOLE
P8065-28 White w/ Black Baffle
Non-IC: 75w PAR16, 40w R16, 50w R20/ PAR20/PAR30, 40w A19



WALL WASHER
P8052-28 White Baffle
Non-IC: 60w A19



FRESNEL
P8062-28 White
Wet location listed.
Metal flange.
Non-IC: 60w A19, 75w PAR30 Short Neck



ALBALITE GLASS
P8060-28 White
Wet location listed.
Metal flange.
Non-IC: 60w A19, 75w PAR30 Short Neck



ALBALITE GLASS
P8008-60 White
Wet location listed.
Non-metallic flange.
Non-IC: 60w A19, 75w PAR30 Short Neck




Featuring 6" Recessed
Image: Schumacher Homes

6″ Recessed

Shallow Housings

For complete fixture, order housing with trim.



New Construction IC and Non-IC with E26 socket

P86-TG
Ceiling opening: 6-7/8″ dia.
Plaster frame: 7-7/8″ x 10-3/4″
Recessed depth: 5-1/2″
Pryouts 1/2″ and 3/4″

P86-TG HOUSING FEATURES

- Designed for shallow plenums and 2″x 6″ construction.
- UL and CUL listed for damp locations and through wiring.
- Can be installed in ceilings from 1/2″ to 1-1/2″ thick.
- Integral nailer and T-bar mounting clamp.
- Integral bar hanger.
- Integral Romex clamp.
- Rated for 8 #12 90° conductors (4 in/4 out).

**P86-TG and P186-TG can be converted to Air-Tight in the field with P8593-01 Gasket Kit.*
See page 795.



Remodel IC and Non-IC with E26 socket

P186-TG
Ceiling opening: 6-5/8″ dia.
Recessed depth: 5-1/2″
Pryouts 1/2″

P186-TG HOUSING FEATURES

- Retrofit version of P86-TG.
- UL and CUL listed for damp locations and through wiring.
- Exclusive locking bars permit quick mounting in ceilings 1/2″ to 1″ thick.
- Integral flange on housing.
- For use in existing ceilings.
- Rated for 4 #12 90° conductors (2 in/2 out).
- Rated for 60° supply wires in end-of-run applications.

Non-IC Trims

Insulation must be 3″ from housing.
7-3/4″ outside diameter.



P8020-28 White
Wet location listed.
Metal flange.
60w A19

IC Trims

For insulated ceilings. 7-3/4″ outside diameter.
IC trims may be used as non-IC trims with same wattages.

STEP BAFFLE
P8063-28 White
P8063-31 Black
75w PAR30, 65w BR30



OPEN TRIM
P8073-28 White
75w PAR30 Long Neck, 65w BR30



EYEBALL
P6676-29 White
Rotates 358°, tilts 30° max.
75w PAR30, 65w BR30



OPEN SHOWER TRIM
P8073WL-28 White
Wet location listed.
Metal flange.
50w PAR30*

LED IC Trims

LED ROUND
P8071-09-30K Brushed Nickel
P8071-20-30K Antique Bronze
P8071-28-30K White
P8071-31-30K Black
10.5w integrated LED, 3000K, 90CRI, 725 lumens.



P8071-09-30K



P8071-20-30K



P8071-28-30K



P8071-31-30K

LED EYEBALL
P8076-09-30K Brushed Nickel
P8076-20-30K Antique Bronze
P8076-28-30K White
P8076-31-30K Black
10.5w integrated LED, 3000K, 90CRI, 700 lumens.



P8076-09-30K



P8076-20-30K



P8076-28-30K




P8076-31-30K

All fixtures:

4″ Recessed

Fire Rated Housing

For complete fixture, order housing with trim.



New Construction Fire Rated Ceilings with E26 socket

P831-FB
Ceiling Opening: 4-1/2″
Recessed Depth: 9-1/8″
Plaster Frame: 9-9/16″ x 13-1/4″
Pryouts: 1/2″ and 3/4″

P831-FB HOUSING FEATURES

- UL Classified to maintain fire ratings of 1 hour or less for L500 and G531 series roof/ceiling designs.
- UL Classified to maintain fire ratings of 2 hours or less for UL D200, D500, G200, G500, L200 and L500 series floor/ceiling designs.
- UL-CUL listed for damp location and feed through wiring.
- Non-IC rated*.
- Fits Into 2″ x 10″ construction.

U.S. Patent #: 5758959, 6004011, 6357891, 6254527

Trims - Non-IC

5″ outside diameter. All trims have 360° positioning. Lamps tilt 20°.



OPEN
P8041-28 White
55w PAR16,
50w PAR20, R20



STEP BAFFLE
P8044-09 Brushed Nickel
P8044-31 Black
P8044-28 White
55w PAR16,
50w PAR20, R20



STEP BAFFLE
P8044-20 Antique Bronze
55w PAR16,
50w PAR20, R20



OPEN SHOWER
P8041WL-28 White
Wet location listed.
50w PAR20
Wet Location trims require use with outdoor rated PAR lamps



EYEBALL
P8046-09 Brushed Nickel
P8046-20 Antique Bronze
P8046-28 White
40w PAR16, 30w R20



WALL WASHER
P8047-31 Black Baffle
40w PAR16, 35w R20



PINHOLE SPOT
P8042-28 White
40w PAR16, 30w R20

5″ Recessed

Fire Rated Housing

For complete fixture, order housing with trim.



New Construction Fire Rated Ceilings with E26 socket

P85-FB
Ceiling Opening: 5-1/4″
Recessed Depth: 9-1/16″
Plaster Frame: 9-9/16″ x 13-1/4″
Pryouts: 1/2″ and 3/4″

See page 795 for P8555-01 IC Box to allow use in IC rated applications.

P85-FB HOUSING FEATURES

- UL Classified to maintain fire rating of 1 hour or less for UL P500 series roof/ceiling designs.
- UL Classified to maintain fire ratings of 2 hours or less for UL D200, D500, G200, G500, L200 and L500 series floor/ceiling designs.
- Non-IC rated*.
- Fits into 2″ x 10″ construction.

U.S. Patent #: 5758959, 6004011, 6357891, 6254527

Trims - Non-IC

6-1/8″ outside diameter, except where indicated*.



EYEBALL
P8176-28 White
*6-3/8″ dia.
75w PAR-30,
short neck.



STEP BAFFLE
P8175-20 Antique Bronze
P8175-31 Black
65w BR30, 50w PAR30



STEP BAFFLE
P8175-28 White
65w BR30, 50w PAR30



OPEN
P8168-28 White
65w BR30,
50w PAR30 LN



OPEN SHOWER
P8367WL-28 White
Wet Location listed.
50w PAR30
Wet Location trims require use with outdoor rated PAR lamps



SHOWER LIGHT
P8109-60 White Glass
Wet Location listed.
Metal flange.
40w A19, 50w PAR30
Short Neck



ALZAK®
P8172-21A Clear Alzak®
85w BR30, 50w PAR30
Short Neck

6″ Recessed

Fire Rated Housings

For complete fixture, order housing with trim.



New Construction Fire Rated Ceilings
with E26 socket

P821-FB
Ceiling Opening: 6-7/8″
Recessed Depth: 8-13/16″
Plaster Frame: 12-3/8″ x 9-9/16″
Pryouts: 1/2″ and 3/4″

P821-FB HOUSING FEATURES

- UL Classified to maintain fire ratings of 1 hour or less for UL P200 and P500 series roof/ceiling designs.
- UL Classified to maintain fire ratings of 2 hours or less for UL D200, D500, G200, G500, L200 and L500 series floor/ceiling designs.
- UL-CUL listed for damp location and through branch wiring.
- Non-IC rated*.
- Acoustically tested to maintain STC Ratings of L500 floor/ceiling assemblies.
- Fits into 2 x 10 construction.

U.S. Patent #: 5758959, 6004011, 6357891, 6254527



New Construction Fire Rated Ceilings
with E26 socket

P821-FBFC
Ceiling Opening: 6-7/8″
Recessed Depth: 8-13/16″
Plaster Frame: 12-3/8″ x 9-9/16″
Pryouts: 1/2″ and 3/4″

P821-FBFC HOUSING FEATURES

- UL Classified to maintain fire ratings of 1 hour or less for all UL P500 series fire rated ceiling/floor assemblies.
- UL Classified to maintain fire ratings of 2 hours or less in all UL D200, G200, L200, D500, G500 and L500 series fire rated ceiling assemblies.
- UL-CUL listed for damp location and feed through wiring.
- Non-IC rated; insulation must be kept at least 3″ away from housing*.
- Acoustically tested to maintain STC Ratings of L500 floor/ceiling assemblies.
- Fits into 2 x 10 construction.
- Air-Tight.
- Shipped with hardware to install bar hangers to furring channels.

U.S. Patent #: 5758959, 6004011, 6357891, 6254527

6″ Recessed

Fire Rated Trims

7-3/4″ outside diameter, except where indicated.



ALBALITE GLASS
P8060-28 White
Wet location listed.
Metal flange.
60w A19

STEP BAFFLE
P8066-28 White
120w BR40, 150w PAR38,
40w A19



STEP BAFFLE
P8066-20 Antique Bronze
P8066-31 Black Baffle
120w BR40, 150w PAR38,
40w A19



STEP BAFFLE SPLAY
P8082-28 White Baffle
P8082-31 Black Baffle
8-3/4″ dia.
150w BR40, 150w PAR38,
40w A19



LONG NECK BAFFLE
P8075-28 White Baffle
P8075-31 Black Baffle
85w BR30, 75w PAR30



PIN HOLE
P8065-28 White w/
Black Baffle
75w PAR16, 40w R16,
50w R20/PAR20/ PAR30



OPEN
P8074-28 White
8-3/4″ dia.
120w BR40, 150w PAR38



OPEN SPLAY
P8072-28 White
85w BR30, 75w PAR30,
60w A19



CONE
P8053-31 Black Alzak®
120w BR40, 150w PAR38



CONE
P8068-21A Clear Alzak®
P8068-28 White
120w BR40, 150w PAR38



EYEBALL
P8076-09 Brushed Nickel
P8076-20 Antique Bronze
P8076-28 White
Rotates 358°, tilts 30° max.
65w BR30, 75w PAR30



BAFFLED MINI EYEBALL
P8077-28 White Baffle
Rotates 358°, tilts 30° max.
75w R20, PAR16,
50w PAR20



REGRESSED EYEBALL
P8079-28 White Baffle
P8079-31 Black Baffle
Rotates 358°, tilts 30° max.
65w BR30, 75w PAR30



FRESNEL
P8011-60 White
Wet location listed.
Non-metallic flange.
50w PAR30



FRESNEL GLASS
P8062-28 White
Wet location listed.
Metal flange.
60w A19



DROP OPAL SHOWER
P8007-60 White Glass
Wet location listed.
Metal flange.
8-1/4″ dia.
75w A19, 75w PAR30



DROP OPAL SHOWER
P8009-60 White Glass
Wet location listed.
Non-metallic flange.
50w PAR30, 60w A19



DOME SHOWER
P8025-60 White
Polycarbonate
Wet location listed.
8-3/4″ dia.
40w A19



OPEN SHOWER
P8072WL-28 White
Wet location listed.
Metal flange.
50w PAR30*

** WL trims require use with outdoor rated PAR lamps*



OPEN SHOWER TRIM
P8074WL-28 White
Wet location listed.
Metal flange.
8-3/4″ dia.
75w PAR38*

** WL trims require use with outdoor rated PAR lamps*



WALL WASHER
P8052-28 White Baffle
60w A19

Lamp wattages shown are maximum.
For accessories see page 795.

6″ Recessed

Sloped Ceiling Housings

For complete fixture, order housing with trim.



New Construction IC
with E26 socket

P645-TG
Ceiling opening: 6-7/8″
Plaster frame: 8-3/8″ x 13″
Recessed depth: 7-5/8″
Pryouts: 1/2″ and 3/4″

P645-TG HOUSING FEATURES
- Maintains lamp in a vertical position from a 0° to a 45° slope (0/12 to 12/12 pitch).
- UL and CUL listed for damp locations and through wiring.
- Can be installed in ceiling from 1/2″ to 1-1/2″.
- Locking screw to secure housing in place.
- Integral nailer and T-bar clamps.
- Bar hangers, with nail grip feature, span to position housing anywhere within 24″ joist spacing.
- Rated for 8 #12 90° conductors (4 in/4 out).
- Integral Romex clamps.
- Easy spring installation of trims.



New Construction Air-Tight & IC
with E26 socket

P645-AT
Ceiling opening: 6-7/8″
Plaster frame: 8-3/8″ x 13″
Recessed depth: 7-5/8″
Pryouts: 1/2″ and 3/4″

P645-AT HOUSING FEATURES
- Maintains lamp in a vertical position from a 0° to a 45° slope (0/12 to 12/12 pitch).
- UL and CUL listed for damp locations and through wiring.
- Meets Washington State Energy Code requirements.
- Can be installed in ceiling from 1/2″ to 1-1/2″.
- Locking screw to secure housing in place.
- Integral nailer and T-bar clamps.
- Bar hangers, with nail grip feature, span to position housing anywhere within 24″ joist spacing.
- Rated for 8 #12 90° conductors (4 in/4 out).
- Integral Romex clamps.



Remodel IC with E26 socket

P745-IC
Ceiling opening: 7-3/8″
Recessed depth: 7-1/4″
Pryouts: 1/2″

P745-IC HOUSING FEATURES
- Maintains lamp in a vertical position from a 0° to a 45° slope (0/12 to 12/12 pitch).
- UL and CUL listed for damp locations and through wiring.
- Can be installed in ceiling from 1/2″ to 1-1/4″.
- Easy spring installation of trims.
- Slide bars stay in place, and have locking screw to secure housing in place.
- Integral nailer and T-bar clamps.
- Bar hangers, with nail grip feature, span to position housing anywhere within 24″ joist spacing.
- Rated for 4 #12 90° conductors (2 in/2 out).
- Integral Romex clamps.

Trims

8-1/4″ outside diameter.



BAFFLE
P8004-20 Antique Bronze
P645-TG 75w BR30, 75w BR30/PAR30LN
P645-AT 75w BR30, 75w PAR30LN



BAFFLE
P8004-28 White
P645-TG 75w BR30, 75w BR30/PAR30LN
P645-AT 75w BR30, 75w PAR30LN
P745-IC 65w BR30, 75w PAR30LN



BAFFLE
P8004-31 Black
P645-TG 75w BR30, 75w BR30/PAR30LN
P645-AT 75w BR30, 75w PAR30LN
P745-IC 65w BR30, 75w PAR30LN

Lamp wattages shown are maximum.
For accessories see page 795.

8″ Recessed

Sloped Ceiling Housings

For complete fixture, order housing with trim.



New Construction Air-Tight & IC with E26 socket

P45-AT
Ceiling opening: 8-3/4″
Plaster frame: 15-3/4″ x 9-3/4″
Recessed depth: 7-1/2″
Pryouts: 1/2″ and 3/4″

P45-AT HOUSING FEATURES
- Maintains lamp in a vertical position in 9° to 45° ceilings (2/12 to 12/12 pitch).
- UL & CUL listed for damp locations and through wiring.
- Meets Washington State Energy Code requirements.
- Can be installed in ceilings from 1/2″ to 1-1/2″ thick.
- Integral nailer and T-bar mounting clamp.
- Single spring installation of trims.



Remodel IC with E26 socket

P245-TG
Ceiling opening: 8″
Recessed depth: 7-13/16″
Pryouts: 1/2″

P245-TG HOUSING FEATURES
- Cast trim flange is integral part of housing.
- UL and CUL listed for damp locations and through wiring.
- Can be installed in ceilings from 1/2″ to 1-1/2″ thickness.
- Lamp is adjustable to vertical position in 9° to 45° ceilings (2/12 to 12/12 pitch).
- Exclusive mounting bars permit quick and solid mounting.
- Rated for 4 #12 90° conductors (2 in/2 out).
- Rated for 60° supply wires in end of run applications.
- Single spring installation of trims.

Trims

9-3/4″ outside diameter.



BAFFLE
P8000-28 White
P45-AT 120w PAR38, BR40
P245-TG 75w PAR38, BR40



BAFFLE
P8000-31 Black
P45-AT 120w PAR38, BR40
P245-TG 75w PAR38, BR40



ALZAK® CONES
P8001-21 Clear Alzak®
P45-AT 120w PAR38, BR40
P245-TG 75w PAR38, BR40

Lamp wattages shown are maximum.
For accessories see page 795.

Specialty Recessed



P6917-TG

COMPLETE ROUND
Unwired unit: White trim, housing, plaster frame, clips and 4-1/2 feet of wire. All are UL listed for damp locations. Therma-Gard™ automatic resetting thermal protection.


Cat. No.	**P6917-TG**
Desc.	Open trim, unwired
Finish	White
Plaster Frame	6-5/8" sq.
Recess Depth	5-3/4"
Ceiling Opening	4-1/2"
Trim O.D.	5-7/8"
Lamp	45w BR30, 50w PAR30



P6952-16TG

BATH HEATER LIGHT
Complete with housing, trim and 26" adjustable bar hangers. Therma-Gard™ automatic resetting thermal protection. Junction box has riveted ground, 9 K.O.'s. UL listed for damp locations. Thru-branch wiring, 4 in, 4 out.

Cat. No.	**P6952-16TG**
Desc.	Heater light
Finish	Satin aluminum
Plaster Frame	8-3/8" x 13"
Recess Depth	7-3/4"
Ceiling Opening	6-7/8"
Trim O.D.	7-3/4"
Lamp	250w R 40




P6414-30TG , P6416-30TG

COMPLETE SQUARE
Complete with housing and trim. Flat white glass. Torsion springs for easy relamping. UL listed for damp locations. Therma-Gard™ automatic resetting thermal protection.

Cat. No.	**P6414-30TG**	**P6416-30TG**
Desc.	Pre-wired	White
Finish	Pre-wired	White
Recess Depth	4-1/4"	4-1/4"
Ceiling Opening	8-1/8"	10-1/8"
Trim (Sq.)	9-1/2"	11-1/2"
Lamp	100w	150w

Installation Hardware for P6917, P6414 and P6416

P8700-01 Four clips for finished or suspended ceiling installation.



P8700-01


P8716-01 Accessory bar hangers for new construction. For use with complete squares (P6914, P6416) and complete rounds (P6917).



P8716-01

Recessed Accessories

P8511-01
Furring channel mounting clip for bar hangers.


P8511-01


P8585-01 Goof Ring
8-7/8" OD, 7-1/2" ID.
For use with any recessed trim with a 7-3/4" OD.


P8585-01


P8588-01 4" ceiling gasket
P8584-01 5" ceiling gasket
P8587-01 6" ceiling gasket
P8589-01 8" ceiling gasket
Ceiling gasket seals housing to drywall opening for Washington State Energy Code compliance.


P8584-01
P8588-01
P8587-01
P8589-01


P8593-01
Airtight Gasket Kit to convert the P86-TG, P186-TG, P187-TG to an air tight unit. When not using caulk at the ceiling line, P8587-01 may also be required.


P8593-01

P8607-01 Remodel Clips
Three plaster frame clips for use in new construction frames in finished ceilings.


P8607-01

P8700-01
Four plaster frame clips and screws for complete squares and rounds.


P8700-01

P8716-01 Adjustable hangers
Two 26" adjustable hangers for step lights, complete rounds and squares.


P8716-01

P8773-01
Four mounting clips and screws for T-Bar ceilings for any new construction recessed product using bar hangers.


P8773-01

Bar Hangers

P8725-01
Bar hangers for T-bar. For use with separate recessed housings and trims.


P8739-01
Bar hangers for joist. For use with separate recessed housings and trims.

Recessed Enclosure for Non-IC Housings in IC applications



P8555-01 IC Barrier
24-1/2"W. x 35"ht.
Creates a barrier to prevent insulation from making contact with recessed fixtures. For use only with Firebox, P60-FB, P821-FB, P821-FBFC, P85-FB, P831-FB, P830-TG, P86-TG, P816-TG. For use with any other Progress fixture consult factory.

Note: The P8555-01 does not make recessed housings IC-rated.



P8555-01 IC Box flat

FEATURES
- Material is Coroplast™, which is made from polypropylene co-polymer resin.
- Deflection temperature F(@66psi) = 194 (90°C).
- Melting point = 162°C, 324°F.
- Normal termperature performance range = -17°F to 160°F.
- MSDS available upon request.

APPLICATION
- Use to create a barrier to keep insulation from making contact with the following type Non-IC rated recessed housings: P60-FB, P821-FB, P821-FBFC, P85-FB, P831-FB, P830-TG, P86-TG, P816-TG.
- Requires no insulation on top.

U.S. Patent #: 6,872,885



Featuring Emblem Surface Mount and Era by Design Series™

Surface Mount Downlighting

Bright, Even Light.

Everlume™ Square Surface Mount LED

Edgelit technology creates a large glare free and evenly illuminated surface for a variety of applications for both residential and commercial applications. Offering a low profile design, LED Everlume™ Square Surface Mount is available in three sizes: 7", 11", and 14", in a White finish. The integrated driver does not recess into junction box, allowing for easy installation into 4" octagonal, 4" round PVC and 4" x 1/2" ceiling pan junction boxes. Wet location listed and offers a 50,000-hour LED life.

LED FEATURES
- Wet location listed.
- 120v input voltage.
- Flicker-free dimming with many Triac and ELV dimmers.
- 50,000 hour life.

7" SQUARE
P810019-030-30 White
7" sq., 1-1/8" ht.
15w integrated LED,
3000, 90CRI, 1100 lumens.

11" SQUARE
P810020-030-30 White
11" sq., 1-1/8" ht.
17w integrated LED,
3000, 90CRI, 1400 lumens.

14" SQUARE
P810021-030-30 White
14" sq., 1-1/8" ht.
20w integrated LED,
3000, 90CRI, 1600 lumens.

P810019-030-30

P810020-030-30

P810021-030-30

Everlume™ Square Trim Accessories

Design the perfect lighting aesthetic for any residential or commercial setting with our Everlume™ Square Trim Accessories collection. We offer a variety of finishes and square trim sizes to best fit your unique design. Each square trim is easy to install and can make an excellent addition to a variety of style settings

7" SQUARE TRIM RING
P860053-009 Brushed Nickel
P860053-020 Antique Bronze
P860053-031 Black
7" sq., 1-1/8" ht.


P860053-009


P860053-020


P860053-031

11" SQUARE TRIM RING
P860054-009 Brushed Nickel
P860054-020 Antique Bronze
P860054-031 Black
11" sq., 1-1/8" ht.


P860054-009


P860054-020


P860054-031

14" SQUARE TRIM RING
P860055-009 Brushed Nickel
P860055-020 Antique Bronze
P860055-031 Black
14" sq., 1-1/8" ht.


P860055-009


P860055-020


P860055-031

Everlume™ Round Surface Mount LED

Edgelit technology creates a large glare free and evenly illuminated surface for a variety of applications for both residential and commercial applications. Offering a low profile design, LED Everlume™ Round Surface Mount is available in a White finish. The integrated driver does not recess into junction box, allowing for easy installation into 4″ octagonal, 4″ round PVC and 4-1/2″ ceiling pan junction boxes. Wet location listed and offers a 50,000-hour LED life.

LED FEATURES
- Wet location listed.
- Flicker-free dimming with many Triac and ELV dimmers.
- 120v input voltage.
- 50,000 hour life.

5″ ROUND
P810024-030-30 White
5″ dia., 1-1/8″ ht.
12w integrated LED
3000K, 90CRI, 800 lumens.

P810024-030-30

7″ ROUND
P810015-030-30 White
7″ dia., 1-1/8″ ht.
15w integrated LED
3000K, 90CRI, 1000 lumens.

P810015-030-30

11″ ROUND
P810016-030-30 White
11″ dia., 1-1/8″ ht.
17w integrated LED
3000K, 90CRI, 1300 lumens.

14″ ROUND
P810017-030-30 White
14″ dia., 1-1/8″ ht.
19.5w integrated LED
3000K, 90CRI, 1700 lumens.

P810016-030-30

18″ ROUND
P810018-030-30 White
18″ dia., 1-1/8″ ht.
23w integrated LED
3000K, 90CRI, 2100 lumens.

All fixtures:

P810017-030-30

P810018-030-30

Everlume™ Round Trim Accessories

You'll never have to sacrifice function for style with our Everlume™ Round Trim Accessories. This collection offers a variety of finishes and trim ring sizes to best fit your unique design needs. Each trim ring is easy to install in both residential and commercial settings.

5" ROUND TRIM RING
P860048-009 Brushed Nickel
P860048-020 Antique Bronze
P860048-031 Black
5" dia., 1-1/8" ht.


P860048-009


P860048-020


P860048-031

7" ROUND TRIM RING
P860049-009 Brushed Nickel
P860049-020 Antique Bronze
P860049-031 Black
7" dia., 1-1/8" ht.


P860049-009


P860049-020


P860049-031

11" ROUND TRIM RING
P860050-009 Brushed Nickel
P860050-020 Antique Bronze
P860050-031 Black
11" dia., 1-1/8" ht.


P860050-009


P860050-020


P860050-031

14" ROUND TRIM RING
P860051-009 Brushed Nickel
P860051-020 Antique Bronze
P860051-031 Black
14" dia., 1-1/8" ht.


P860051-009


P860051-020


P860051-031

18" ROUND TRIM RING
P860052-009 Brushed Nickel
P860052-020 Antique Bronze
P860052-031 Black
18" dia., 1-1/8" ht.


P860052-009


P860052-020


P860052-031

Emblem Surface Mount LED

Easy installation and a sleek, modern lighting aesthetic are offered by our Emblem Surface Mount LED Collection. An excellent choice for general ambient lighting, each polished design features a smooth, slightly tapered trim ring surrounding a single, integrated LED light source. Enjoy the unmatched level of glare control offered by the fixture's diffused polycarbonate lens that also hides any unwanted LED pixelation. Each light fixture is home to an integrated AC LED light engine that seamlessly installs to a variety of ceiling pan junction boxes to give you added flexibility when it comes to creating your design vision. The surface mount provides unparalleled longevity with its, 50,000-hour LED life span and 80% energy savings.

LED FEATURES
- Wet location listed.
- 120v input voltage.
- 60 Lumens per watt.
- Flicker-free dimming with many Triac and ELV dimmers.
50,000 hour life.

P810014-020-30 Antique Bronze
P810014-028-30 Satin White
7-1/4" dia., 1-3/8" ht.
15.5w integrated LED,
3000K, 90CRI, 1080 lumens.

P810014-028-30



P810014-020-30K

P810027-020-30 Antique Bronze
P810027-028-30 Satin White
5-1/2" dia., 1-7/8" ht.
12.5w integrated LED,
3000K, 90CRI, 750 lumens.



P810027-028-30



P810027-020-30K



Shown installed into 1/2" ceiling pan J-box

All fixtures:

Intrinsic Surface Mount LED

Elevate your design vision with just the flip of a switch with our Intrinsic Surface Mount LED Collection. The simple, classic design of these light fixtures can easily be installed into a variety of style applications in both residential and commercial settings. We offer two different sizes of surface mounts, both coated in a crisp white finish, to meet your unique design needs. Each smooth trim ring surrounds an integrated LED light fixture ready to emit general ambient lighting wherever it calls home in your design plan.

LED FEATURES
- Wet location listed.
- 120v input voltage.
- 60 Lumens per watt.
- Flicker-free dimming with many Triac and ELV dimmers.
50,000 hour life.

P810012-028-30 White
5-1/2" dia., 1" ht.
12w integrated LED,
3000K, 90CRI, 600 lumens.



P810012-028-30

P810013-028-30 White
7-1/2" dia., 1-3/16" ht.
15.5w integrated LED,
3000K, 90CRI, 1000 lumens.

P810013-028-30K

All fixtures:

Decorative Surface Mount

Get the perfect lighting for any situation or task with our Decorative Surface Mount Triac Dimming Collection. This collection offers a flicker-free dimming lighting solution that allows the fixture to dim down to 10% with many Triac or forward phase dimmers. Choose from two different sizes of round surface mounts, each in a beautiful brushed nickel finish and trimmed with etched glass for an added level of aesthetic appeal. Wet location listed.

P8147-09-30K Brushed Nickel
Round trim with etched glass
7-1/4" dia., 2-3/4" ht.
10.5w integrated LED, 3000K, 90CRI,
690 lumens, 66 lumens per watt.

P8247-09-30K Brushed Nickel
Round with etched glass
5-1/2" dia., 1-1/2" ht.
10.5w integrated LED, 3000K, 90CRI,
690 lumens, 66 lumens per watt.

All fixtures:



P8147-09-30K
Triac/ELV dimming



P8247-09-30K
Triac/ELV dimming

Round Surface Mount LED

P8222-28/30K White
7-1/4" round flush mount
7-1/4" dia., 1-1/4" ht.
17w LED integrated,
3000K, 90CRI, 1170 lumens.

P8222-28/30K
Triac/ELV dimming

Retrofit Recessed Accessories

The P8147 and P8247 surface mounts require an accessory mounting option for recessed housings.

P8595-01
Recessed mounting accessory
for P8147 and P8222 series.
Allows for installation in 6" housings.
Edison base adapter included.

P8596-01
Recessed mounting accessory
for P8247 series. Allows for
installation in 4" housings.
Edison base adapter included.



P8595-01



P8596-01


Directionals & Track

Ideal Adjustable Light.

Round Back Directionals

THREE-LIGHT
P6160-09 Brushed Nickel
P6160-30 White
P6160-174 Urban Bronze
Wall or ceiling mount round back.
27" W., 5-1/4" ht.
Extends 6-5/8". H/CTR 2-3/8".
Three PAR20 lamps,
each 50w max.

FOUR-LIGHT
P6162-09 Brushed Nickel
P6162-174 Urban Bronze
Wall or ceiling mount round back.
36" W., 5-1/8" ht.
Extends 6-5/8".
Four PAR20 lamps,
each 50w max.


P6160-09


P6160-30


P6160-174


P6162-09


P6162-174

On-Off Switch Round Back Directionals

ONE-LIGHT
P6155-09 Brushed Nickel
P6155-30 White
Wall mount round back.
On/off switch.
3-3/4" dia., 5" ht.
Extends 6-7/8".
One PAR20 medium base lamp, 50w max.


P6155-30


P6155-09

Round Back Directionals

ONE-LIGHT
P6147-09 Brushed Nickel
P6147-30 White
P6147-174 Urban Bronze
Ceiling mount round back.
5" dia., 3-3/4" ht.
Extends 6-1/2".
One PAR20 medium base lamp, 50w max.


P6147-09


P6149-09

TWO-LIGHT
P6149-09 Brushed Nickel
P6149-30 White
P6149-174 Urban Bronze
Wall or ceiling mount round back.
9" dia., 3-3/4" ht.
Extends 6-1/2".
Two PAR20 medium base lamps, each 50w max.


P6147-30


P6149-30

ONE-LIGHT
P6144-30 White
P6144-174 Urban Bronze
Wall or ceiling mount round back.
5" dia., 5-1/2" ht.
Extends 7".
One PAR30 medium base lamp, 75w max.


P6144-30


P6147-174


P6149-174


P6144-174

Heat Lamp Flat Back Directionals

ONE LIGHT
P6397-30 White
Adjustable wall or ceiling heat lamp with black baffle.
5-3/4" dia., 8-1/8" ht.
Extends 11".
One BR-40 medium base lamp, 250w max.


P6397-30

Ridgecrest

Infuse an abundance of sophistication, versatility, and light to any commercial or residential setting with our Ridgecrest collection. Multi-directional lamp heads provide design flexibility and illuminate typically hard-to-reach areas. Select a brushed nickel, satin white, or black finish to best fit your design aesthetic. Each lamp head features a crisp frosted glass shade for soft, general ambient light.

1 HEAD TRACK W/ FROSTED GLASS
P900011-009 Brushed Nickel
P900011-028 Satin White
P900011-031 Black
5" wd., 6-7/16" ht.
Extends 7-9/16" dp.
One medium base lamp,
each 60w max.



P900011-009



P900011-028



P900011-031

4 HEAD TRACK W/ FROSTED GLASS
P900012-009 Brushed Nickel
P900012-028 Satin White
P900012-031 Black
5" wd., 7-3/16" ht.
Extends 26-1/8" dp.
Four medium base lamps,
each 60w max.



P900012-009



P900012-028



P900012-031

Kitson

Incorporate a hint of stylish industrial light to any commercial or residential setting with our Kitson collection. Multi-directional lamp heads provide design flexibility and illuminate typically hard-to-reach areas, such as highlighting images in a lobby or gallery. Select a brushed nickel, satin white, or black finish to best fit your design aesthetic. Each lamp head features an industrial-styled shade with an outer ribbed design. Use with GU10 lamps to create different beam shapes as desired.


1 HEAD TRACK METAL
P900013-009 Brushed Nickel
P900013-028 Satin White
P900013-031 Black
5" wd., 5-15/16" ht.
Extends 5" dp.
One GU10 lamp,
each 50w max.


P900013-009


P900013-028


P900013-031

4 HEAD TRACK METAL
P900014-009 Brushed Nickel
P900014-028 Satin White
P900014-031 Black
5" wd., 6-7/16" ht.
Extends 26-1/8" dp.
Four GU10 lamps,
each 50w max.


P900014-009


P900014-028


P900014-031

ALPHA TRAK®

Line Voltage Adjustable Track Heads

Track mounting hardware and fixture accessories appear on pages 810-813.

Brushed Nickel

Track heads in a brushed nickel finish add a level of aesthetic appeal to both residential and retail spaces.

P6112-09 Brushed Nickel
2-9/16" dia., 5-1/4" ht.
One MR16 lamp, 50w max., included. GU10 twist lock base.

P6115-09WB Brushed Nickel
Die-cast gimbal track head
2-7/8" dia., 5-1/4" ht.
One 120V MR16 lamp, 50w max., included. GU10 twist lock base.

P6117-09 Brushed Nickel
Die-cast gimbal track head
4-5/8" dia., 8-1/4" ht.
One PAR30, 75w max.


P6115-09WB


P6112-09


P6117-09

High Tech

Excellent for residential and retail applications. Lampholder rotates 360° horizontal, 90° up from vertical.

P6325-28 Bright White
P6325-31 Black
2-3/4" dia., 5-1/4" ht.
One 75w PAR16.

P6326-28 Bright White
P6326-31 Black
2-3/4" dia., 5-1/2" ht.
One 50w PAR20.

P6327-28 Bright White
P6327-31 Black
4" dia., 6-1/8" ht.
One 75w PAR30 short neck.

P6369-28 Bright White
5" dia., 8" ht.
One 250w PAR38.


P6325-31


P6326-31



P6327-31


P6325-28


P6326-28


P6327-28


P6369-28


Note: Height is to bottom of track.

See pages 810-813 for accessories and track.

Flair

White Flair Alpha Trak track head with 360° horizontal rotation and 90° vertical rotation and black baffle. Heads can be easily repositioned on the track to provide lighting in different areas of the room. Excellent for both residential
and retail locations

P9200-28 Bright White
P9200-31 Black
Complete with black baffle.
3-1/2" dia., 7-5/8" ht.
One 50w PAR20, one 50w
R 20, or one 75w PAR16.

P9201-28 Bright White
P9201-31 Black
Complete with black baffle.
4-3/8" dia., 8-3/4" ht.
One 75w PAR30 long neck
or one 65w BR30.


P9200-28


P9200-31


P9201-28


P9201-31

Free Form

Clean design to accommodate the exposed portion of the PAR lamps. For retail and accent locations. Lampholder rotates 360° horizontal, 90° vertical.

P6328-28 Bright White
3-1/4" dia., 4-1/8" ht.
One 50w PAR20
or 75w PAR16.

P6329-28 Bright White
4-5/8" dia., 7-7/8" ht.
One 75w PAR30 short neck.


P6328-28


P6329-28

ALPHA TRAK®

Line Voltage Adjustable Track Heads

Track mounting hardware and fixture accessories appear on pages 810-813.

Universal

Simple design provides minimal obtrusion into the visual space. Lampholder rotates 360° horizontal, 90° vertical.

P6280-28 Bright White
P6280-31 Black
2" dia., 5-7/8" ht.
Any medium base PAR or R lamp except PAR30 short neck up to 300w max.


P6280-28


P6280-31

Flatback

Flat Back Alpha Trak track head with 360° horizontal rotation and 90° vertical rotation and black baffle. Heads can be easily repositioned on the track to provide lighting in different areas of the room. Excellent for both residential and retail locations.

P9205-28 Bright White
P9205-31 Black
Complete with black baffle.
3-1/2" dia., 7-1/4" ht.
One 50w PAR20, one 50w R 20, or one 75w PAR16.


P9205-28


P9205-31

P9206-28 Bright White
P9206-31 Black
Complete with black baffle.
4-3/8" dia., 9" ht.
One 75w PAR30 long neck or one 65w BR30.



P9206-28


P9206-31

P9207-28 Bright White
P9207-31 Black
Complete with black baffle.
6" dia., 10-7/8" ht.
One 250w PAR38, one 300w R 40, or one 250w BR40.


P9207-28


P9207-31


Note: Height is to bottom of track.

See pages 810-813 for accessories and track.

Roundback

Round Back Alpha Trak track head with 360° horizontal rotation and 90° vertical rotation and black baffle. Excellent for both residential and retail locations.

P9203-28 Bright White
P9203-31 Black
Complete with black baffle.
3-1/2" dia., 7-1/4" ht.
One 50w PAR20, one 50w R 20, or one 75w PAR16.


P9203-31

P9204-28 Bright White
P9204-31 Black
Complete with black baffle.
4-3/8" dia., 8" ht.
One 75w PAR30 long neck or one 65w BR30.


P9204-28

Shallow Profile

Non-metallic, architecturally-designed molded fitter. Designed for PAR20 and PAR30 lamps. Lampholder rotates 360° horizontally, 90° vertically.

P9219-28 Bright White
P9219-31 Black
3-1/2" dia., 5-3/4" ht.
One 50w PAR20.


P9219-31


P9219-28

P9220-28 Bright White
P9220-31 Black
4-3/4" dia., 6" ht.
One 75w PAR30.


P9220-31


P9220-28

Alpha Trak® Kits

All Alpha Trak® Kits come with three track heads, 4′ track, canopy, dead end, feed and mounting hardware.

P9215-28 Bright White
Track heads complete with black baffle.
4-3/8" dia., 9" ht.
Three 75w PAR30 long neck or three 65w BR30.


P9215-28
Flair

P9216-28 Bright White
Track heads complete with black baffle.
4-3/8" dia., 8-3/4" ht.
Three 75w PAR30 or three 65w BR30.


P9216-28
Flat Back

ALPHA TRAK® Accessories

Alpha Trak® Sections

Alpha Trak single-circuit track sections are extruded aluminum with flat copper conductors for positive contact and can be field cut to required lengths. All have easy-guide polarity notch. Designed for 120-volt supply with 20 amp capacity (2,400 watts). Order power feeds and system hardware separately as required. All track sections include two dead ends and mounting hardware.

P9103-09 Brushed Nickel
P9103-28 Bright White
P9103-31 Black
2′ L., 1-1/8″ W., 7/8″ ht.



Brushed Nickel

P9104-09 Brushed Nickel
P9104-28 Bright White
P9104-31 Black
4′ L., 1-1/8″ W., 7/8″ ht.



Bright White

P9105-09 Brushed Nickel
P9105-28 Bright White
P9105-31 Black
8′ L., 1-1/8″ W., 7/8″ ht.

P9106-09 Brushed Nickel
P9106-28 Bright White
P9106-31 Black
12′ L., 1-1/8″ W., 7/8″ ht.



Black



Cross section of track

Alpha Trak® Power Feeds

FLOATING CANOPY
P9123-09 Brushed Nickel
P9123-28 Bright White
P9123-31 Black
Floating canopy mounts anywhere on track, includes power feed and covers. Fits over standard outlet box. Includes one P8717 and P9122-28 dead end.



P9123-28

“ANYWHERE” POWER FEED
P8730-09 Brushed Nickel
P8730-31 Black
P9108-28 Bright White
“Anywhere” power feed snaps into place at any point along the track. Canopy kit required P8753, P91007. Has 8″ leads. Includes one P8717 dead end.*



P8730-09

T-BAR END FEED
P8760-09 Brushed Nickel
P8760-31 Black
P9109-28 Bright White
T-bar end feed with canopy cover for suspended ceilings. (Use P8770-01 slotted outlet box.)



P8760-09

“ANYWHERE” POWER FEED
P8742-31 Black
P9121-28 Bright White
“Anywhere” power feed with 3/8″ Greenfield connector. Has 72″ of wire. Includes one P8717 dead end.*



P8742-31
P9121-28

END FEED
P8745-09 Brushed Nickel
P8745-28 Bright White
P8745-31 Black
4 -1/2″ sq.
End feed with flush canopy.



P8745-31

TOP OR END FEED
P8746-09 Brushed Nickel
P8746-31 Black
P9110-28 Bright White
Top or end feed for Romex, 3/8″ Greenfield or 1/2″ EMT.



P9110-28

**Not UL listed*

Alpha Trak® System Hardware

CANOPY KIT – FLUSH MOUNT
P8753-09 Brushed Nickel
P8753-31 Black
P9107-28 Bright White
Canopy Kit – Flush Mount. Mounting plate can be used anywhere along track. Slips between ceiling and track. Use with P8730, P9108 power feed.


P9107-28

SLOTTED OUTLET BOX
P8770-01
4" slotted outlet box for suspended ceilings. For use with P8760 and P9109 T-bar end feed. Mounts into T-bar grid cross section.*


P8770-01

DEAD END
P8717-09 Brushed Nickel
P8717-31 Black
P9122-28 Bright White
Dead end closes open end of track. Two dead ends already supplied with track sections.


P8717-28

SUSPENDED CEILING CLIPS
P8771-30 White
Suspended ceiling clips. Use two for 2' or 4' track sections. Three for 8' track. Five for 12' track. For mounting track sections onto T-bar grid.


P8771-30

Alpha Trak® Connectors

For joining two or more track sections in straight runs, "L", "T", cross, square and "any angle" patterns. The connectors plug into track sections only one way to ensure positive polarization.

STRAIGHT CONNECTOR
P8720-09 Brushed Nickel
P8720-31 Black
P9115-28 Bright White


P8720-09


P9115-28

"L" CONNECTOR
A. Inside polarity
P8721-9109 Brushed Nickel
P8721-9131 Black
P9116-9128 Bright White

B. Outside polarity
P8721-8909 Brushed Nickel
P9116-8928 Bright White

"L" connector. Inside polarity type connector generally used. To identify polarity, orient connector to "L" shape and polarity grooves will intersect where indicated.

A


P8721-9109

A


P8721-9131

B


P8721-8909

B


P9116-8928

CROSS CONNECTOR
P8723-09 Brushed Nickel
P8723-28 Bright White
P8723-31 Black


P8723-31

"T" CONNECTOR
A. Inside-right polarity
P8722-9109 Brushed Nickel
P8722-9128 Bright White
P8722-9131 Black

B. Inside-left polarity
P8722-8909 Brushed Nickel
P8722-8928 Bright White
P8722-8931 Black

"T" connector. Inside-right polarity type connector generally used. To identify polarity, orient connector to "T" shape and polarity grooves will intersect where indicated.

A


P8722-9131

B


P8722-8928

FLEX CONNECTOR
P8736-09 Brushed Nickel,
P8736-31 Black
P9117-28 Bright White
Flex connector permits a variety of track layouts at almost any angle and variation of planes including wall-to-ceiling or on cathedral ceilings. Can flex to 90°.


P8736-09


P9117-28

ALPHA TRAK® Accessories

Alpha Trak® Mounting Options

FIXTURE ADAPTER
P8727-09 Brushed Nickel
P8727-28 Bright White
P8727-31 Black
Fixture adapts cord-hung (max. wt. 10 lbs.) or chain-hung (max. wt. 25 lbs.) fixtures to Trak-1® or AlphaTrack®.


P8727-09

ADAPTERS
P8728-09 Brushed Nickel
P8728-28 White
P8728-31 Black
Alpha-Trak® stem-hung mini-pendant adapter.
1-1/4" dia., 3-7/8" ht.
Max. weight 11 lbs.


P8728-09


P8728-28


P8728-31

MONOPOINT
P8734-09 Brushed Nickel
P8734-31 Black
P9113-28 Bright White
Monopoint mounts any lampholder, not requiring an external transformer, to junction box on ceiling or wall.
5" dia., 1" ht.


P8734-31


P9113-28


P9103-09
Track

+


P8728-09
Adapter

+


P5161-81
Pendant

Alpha Trak® Pendant Kits

Used for suspending track from higher and sloped ceilings. Maximum spacing between pendants is 4 feet. Stem will suspend track 6", 12" and 18" from ceiling. 6" and 12" stem and connectors provided. Will hang straight from ceiling up to 45°.

P8715-09 Brushed Nickel
P8715-28 Bright White
P8715-31 Black
Pendant kit (less power feed) with outlet box cover, 6" and 12" stem lengths and all necessary mounting hardware.*

P8718-09 Brushed Nickel
P8718-28 Bright White
P8718-31 Black
Pendant kit (with power feed) and 24" wire includes outlet box cover, 6" and 12" stem lengths and all necessary mounting hardware.

**Not UL listed*


P8715-28
Pendant Kit Less Power Feed


P8718-09
Pendant Kit with Power Feed and 24" Wire


P8715-28

+


P9104-28
Track

+


P9206-28
Alpha Trak® Head

LED TRACK

Ideal for residential and light commercial applications, this LED Track Kit is provided with all components required for installation. Track Kits include 42″ of linear track, a floating power feed, three AC LED Track Heads and installation hardware. Track Heads feature a frosted glass lens to reduce glare.

LED FEATURES

- 120v input voltage.
- 2700K color temperature; 90+ CRI.
- Flicker free dimming down to 10% with many Triac forward or reverse ELV phase dimmers.
- 50,000 hr. life.

Track Kits

P900002-028-27 Satin White
P900002-031-27 Black
42″ L., 2-7/8″ W., 6-1/2″ ht.,
Extends 2-3/4″.
Three 9.5W LED,
2700K, 1575 lumens.

P900003-028-27 Satin White
P900003-031-27 Black
42″ L., 3-1/4″ W., 7-1/2″ ht.,
Extends 3-1/4″.
Three 14.5W LED,
2700K, 2350 lumens.

All fixtures:

JA8

P900002-028-27



P900002-031-27



P900003-028-27



P900003-031-27



AC LED Track Heads

P900000 and P900001 Track Heads are compatible with P900002 and P900003 Track Kits. These AC LED Track Heads can be added to a track kit to provide more light when needed.

P900000-028-27 Satin White
P900000-031-27 Black
2-7/8″ W., 6-1/2″ ht.,
Extends 2-3/4″.
One 9.5W LED,
2700K, 533 lumens.

P900001-028-27 Satin White
P900001-031-27 Black
3-1/4″ W., 7-1/2″ ht.,
Extends 3-1/4″.
One 14.5W LED,
2700K, 797 lumens.

All fixtures:

JA8

P900000-028-27



P900000-031-27



P900001-028-27



P900001-031-27



Undercabinet

Shining *Useful* Light.

Which Hide-A-Lite™ Fits?

There are three primary types of HIDE-a-LITE™ lighting: puck, linear undercabinet, and tape. Puck lighting is spot lighting that focuses light to accent items and brings decorative character to a room. Linear undercabinet lighting evenly illuminates under the entire cabinet length. Tape lighting is flexible and can be used where space is limited, or where longer lengths of light are needed.

Quick Tip

Most rooms will need a combination of some or all of these types of task and ambient lighting. Begin by assessing the size of the space.





Linear Underabinet

Pick linear undercabinet lighting where even illumination and high light levels are desired. It comes complete with 120V direct wire application, eliminating the need for remote power supplies or conversion boxes, and an on-off switch for easy access task lighting.




Puck Lights

Puck lighting is used to create focused lighting effects that highlight decorative elements. Puck can be used inside and underneath cabinets when a spot or targeted light distribution is desired.



Tape Lights

Available in various lengths, tape lights can be cut to fit a specific size. Its length, low profile, flexibility for navigating curves, and adhesive backing that sticks to many surfaces makes it ideal for use in hard-to-light areas.


Above cabinets
2
Inside Cabinet Niche
1 Under wall-mount upper cabinets
Quick Tip
Often, puck, linear undercabinet, and tape lighting can be used in the same space to provide the overall effect.
3 Along base cabinets

Linear Undercabinet LED

The HIDE-a-LITE™ Linear undercabinet series provides the ideal solution for residential and light commercial applications. The luminaire is constructed from an aluminum housing and features a lens designed to optimize light distribution, ensuring for proper illumination of the work space below. The HIDE-A-LITE linear undercabinet utilizes a through hole mounting method to allow for an easy installation. The luminaire can be direct wired, removing the need for separate cords. Two armored cable fittings are included with the product for applications requiring the use of armored cable. An on/off switch is located on the front of the luminaire, allowing for easy access when used as a task light. The energy efficient LEDs can be dimmed down to 10% with many forward phase (TRIAC) and electronic low voltage (ELV) dimmers.

HIDE a LITE™

9" LED UNDERCABINET
P700000-020-30 Antique Bronze
P700000-028-30 White
9" L., 3-1/4" W., 1-1/8" ht.
One 4.5w integrated LED, 3000K, 90CRI, 300 delivered lumens.


P700000-028-30


P700000-020-30

12" LED UNDERCABINET
P700001-020-30 Antique Bronze
P700001-028-30 White
11-1/2" L., 3-1/4" W., 1-1/8" ht.
One 7.5w integraged LED, 3000K, 90CRI, 500 delivered lumens.


P700001-028-30


P700001-020-30

18" LED UNDERCABINET
P700002-020-30 Antique Bronze
P700002-028-30 White
17-1/2" L., 3-1/4" W., 1-1/8" ht.
One 12.5w integrated LED, 3000K, 90CRI, 815 delivered lumens.


P700002-028-30


P700002-020-30

24" LED UNDERCABINET
P700003-020-30 Antique Bronze
P700003-028-30 White
23-1/2" L., 3-1/4" W., 1-1/8" ht.
One 15.5w integrated LED, 3000K, 90CRI, 980 delivered lumens.


P700003-028-30


P700003-020-30

36" LED UNDERCABINET
P700004-020-30 Antique Bronze
P700004-028-30 White
35-1/2" L., 3-1/4" W., 1-1/8" ht.
One 20w integrated LED, 3000K, 90CRI, 1500 delivered lumens.


P700004-028-30


P700004-020-30

All fixtures:

Puck LED

The HIDE-a-LITE™ Puck LED provides an ideal solution for many applications. The low profile design provides versatility to allow installations inside a cabinet, under a cabinet and above a cabinet to provide up light. The HIDE-a-LITE™ Puck LED offers a quick and simple mounting installation and SPT-2 wire can be used for direct wiring. Energy Star Listed and meets CA T24 JA8-2016 requirements. The HIDE-a-LITE™ Pucks LED can be dimmed down to 10% with many Forward Phase (Triac) and Electronic Low Voltage (ELV) dimmers.

HIDE a LITE™







Featuring Puck LED Undercabinet
Image: Beazer Homes

LED PUCK
P700005-020-30 Antique Bronze
P700005-028-30 Satin White
3" dia., 1" ht.
3w integrated LED 3000K, 90CRI
120V LED, 140 delivered lumens
Damp location listed.



P700005-020-30



P700005-028-30

3FT DIRECT WIRE CABLE
P860031-020 Antique Bronze
P860031-028 Satin White
36" Direct Wire Cable
(when used with P8740)



P860031-020



P860031-028

HAL3 JUNCTION BOX
P8740-20 Antique Bronze
P8740-30 White
3-1/2" L., 3-1/4" W., 1" ht.



P8740-20



P8740-30

50FT CABLE
P860029-020 Antique Bronze
P860029-028 Satin White
50' 18 AWG SPT-2 Cable


100FT CABLE
P860030-020 Antique Bronze
P860030-028 Satin White
100' 18 AWG SPT-2 Cable



P860029-020
P860030-020



P860029-028
P860030-028



Easy to install and daisy chain with SPT-2 cable

Tape Undercabinet System LED

LED Tape provides lighting to enhance aesthetics, while also aiding in tasks around the home. Common applications for LED Tape include; undercabinet lighting in kitchens to add illumination to work surfaces, highlighting back splashes in kitchens or bathroom areas and adding toe kick lighting at the bases of cabinets for dramatic and functional lighting.

HIDE a LITE™

Follow Five Simple Steps:


1. Choose Tape Length



12", 60" and 240" lengths to meet different sized projects and features an adhesive backing for easy application to desired surfaces.



Flexible tape can be cut every 4 inches (cut ends can be reconnected, allowing for full use of LED tape).



Tape is fully enclosed in silicone to allow for use in damp location. 24 VDC tape pairs with 24 VDC power supplies.

P700008-000-27
12" L., 3/8" W., 1/8" ht.
2700K

P700008-000-30
12" L., 3/8" W., 1/8" ht.
3000K

P700009-000-27
60" L., 3/8" W., 1/8" ht.
2700K

P700009-000-30
60" L., 3/8" W., 1/8" ht.
3000K

P700010-000-27
240" L., 3/8" W., 1/8" ht.
2700K

P700010-000-30
240" L., 3/8" W., 1/8" ht.
3000K



P700008-000-27



P700009-000-27
P700010-000-27

LED FEATURES
- Field cuttable at every 4" to end of run.
- cETLus listed damp location.
- 300 lumens per foot and consumes 4.2 watts per foot (71 lumens/w).
- 90CRI, 50,000 hr. life.
- 5 year warranty.

All fixtures:

JA8

2. Select Transformer

Progress Lighting offers multiple power supplies to meet various project sizes. Power supplies can be dimmed, flicker-free, on Forward Phase (TRIAC) and Reverse Phase (ELV) dimmers down to 10% output.

P700020-031 Black
Max length of tape 60"
8-3/16" L., 2" W., 1-3/4" ht.
25w

P700021-031 Black
Max length of tape 120"
8-3/16" L., 2" W., 1-3/4" ht.
40w

P700023-031 Black
Max length of tape 240"
9-3/16" L., 3-3/8" W., 1-15/16" ht.
80w



P700020-000
P700021-000
P700023-000

PRODUCT FEATURES
- Maximum operating temperature -20° C to +40° C.
- Enclosure provided.
- Wire nuts and additional hardware included.

3. Additional System Connectors

Various connectors allow for customized layouts. Use linking connectors to join runs of tape. Use the L Connector for 90° bends and use the Y Connector to split one run of tape into two.



Connectors feature piercing conductors for secure connection.



Y, L and multi-linking connectors allow for flexibility in design.





Connectors provided with snap-fit covers for intuitive installation.

2″ CONNECTOR CORD
P700011-000 Black
Connect tape sections (P700008, P700009, P700010)
2″ L., 5/8″ W., 1/4″ ht.



P700011-000

12″ CONNECTOR CORD
P700012-000 Black
Connect tape sections (P700008, P700009, P700010)
12″ L., 5/8″ W., 1/4″ ht.



P700012-000

18″ CONNECTOR CORD
P700013-000 Black
Connect tape sections (P700008, P700009, P700010)
18″ L., 5/8″ W., 1/4″ ht.



P700013-000

36″ CONNECTOR CORD
P700014-000 Black
Connect tape sections (P700008, P700009, P700010)
36″ L., 5/8″ W., 1/4″ ht.



P700014-000

72″ CONNECTOR CORD
P700015-000 Black
Connect tape sections (P700008, P700009, P700010)
72″ L., 5/8″ W., 1/4″ ht.



P700015-000

L CONNECTOR
P700016-000 Black
90° connector for connecting sections of tape (P700008, P700009, P700010) on corners.
2-1/16″ L., 2-1/16″ W., 1/6″ ht.



P700016-000

Y CONNECTOR
P700017-000 Black
Three-way Y connector for connecting sections of tape (P700008, P700009, P700010)
3-3/16″ L., 3-3/16″ W., 1/4″ ht.



P700017-000

OUTPUT POWER CONNECTOR
P700022-000 Black
60″ L., 5/8″ W., 1/4″ ht.




P700022-000

4. Mounting Clips/End Clips

Select end caps or add mounting clips to finish the installation.

P700018-000
Pack of 10 clips/screws for straight runs for added support (2 clips per foot recommended)
1-1/8″ L., 1/4″ W., 1/8″ ht.



P700018-000

P700019-000
End caps to terminate run of LED tape. For use when tape has been cut at end of run. Sold in sets of 10.
1/2″ L., 1/2″ W., 1/4″ ht.



P700019-000

5. Additional Accessories

Splicer for LED Tape Undercabinet System with connection between Romex wire and low voltage cable. Includes mounting screws.

P7024-31 Black
1″ L., 2″ W., 5/8″ ht.



P7024-31

Steps, Corridors & Wall Lights

Safe Light At Night.

Indoor Step, Outdoor Step & Wall Lights LED

5w 3000K color temperature with 84+ CRI and a 120° beam spread. LED step/wall lights are available in a vertical or horizontal configuration for mounting into a single-gang wallbox.

FEATURES

- Integral power supply module in a compact package.
- Consumes less than 5w of power per fixture.
- Beam spread: 120 degrees.
- cCSAus listed for wet locations.
- Warm white 3000K LED's included.
- 84+ CRI.

P6827-0930K Brushed Nickel
P6827-2030K Antique Bronze
P6827-3030K White
P6827-31-30K Black
Louvered horizontal
5-1/4" W., 3-1/2" ht.
5w LED module included.


P6827-0930K


P6827-2030K


P6827-3030K


P6827-3130K

P6828-0930K Brushed Nickel
P6828-2030K Antique Bronze
P6828-3030K White
P6828-31-30K Black
Louvered vertical
3-1/2" W., 5-1/4" ht.
5w LED module included.


P6828-0930K


P6828-2030K


P6828-3030K


P6828-3130K

P6832-0930K Brushed Nickel
P6832-2030K Antique Bronze
P6832-3030K White
P6832-31-30K Black
Horizontal step/wall light
4-1/2" W., 2-7/8" ht.
5w LED module included.


P6832-0930K


P6832-2030K


P6832-3030K


P6832-3130K

P6829-0930K Brushed Nickel
P6829-2030K Antique Bronze
P6829-3030K White
P6829-31-30K Black
Vertical step/wall light
2-7/8" W., 4-1/2" ht.
5w LED module included.


P6829-0930K


P6829-2030K


P6829-3030K


P6829-3130K

U.S. Patent #. 6357891, 5379199

Indoor & Protected Outdoor

Spring-held white louver faceplate. Metal housing has 1/2" I.P. conduit entry. For indoor and protected outdoor use. UL listed for damp locations. Sheet rock or dry wall installations.

P6820-30TG* White
P6820-31TG* Black
Non-IC
Therma-Gard protection.
Porcelain socket.
One medium base lamp, 60w max.


** Requires accessory bar hanger kit, P8716-01 for installation to wood studs.*



P6820-30TG



P6820-31TG



P6820-30 & P6826-30

Indoor Steplights LED

The mini-steplights are ideal for indoor residential applications. Energy efficient steplights include both vertical and horizontal louvers and are available in four finishes.

LED STEP LIGHT
P660003-009-30K Brushed Nickel
P660003-020-30K Antique Bronze
P660003-028-30K White
P660003-031-30K Black
2-3/4" W., 4-1/2" ht.
1w LED, 3000K, 90CRI, 12 lumens.



P660003-009-30K



P660003-020-30K



P660003-028-30K



P660003-031-30K

Egress

Showing The Way.

Combo Exit/Emergency Sign LED

The PECUE Series offers quality and value with a compact and attractive LED based combination emergency exit. The white housing and lamp-heads are made of high impact UL flame rated thermoplastic. Snap together canopy, housing, removable chevrons for quick and easy installation. Universal single or double-face.

PECUE-UG-30 White/Green
PECUE-UR-30 White/Red
18" W., 7-1/4" ht.,
Extends 2".
Universal face.
101 lumens.



PECUE-UG-30



PECUE-UR-30

Exit Sign LED

The PETPE Series offers quality and value with a compact and attractive LED based emergency exit. The white housing is made of high impact UL flame rated thermoplastic. Snap together canopy, housing, removable chevrons for quick and easy installation. Universal single or double-face.

PETPE-UG-30 White/Green
PETPE-UR-30 White/Red
11-1/2" W., 7-1/4" ht.,
Extends 2".
Universal face.
101 lumens.



PETPE-UG-30



PETPE-UR-30

Emergency Light LED

The PE2EU Series offers quality and value with a compact and attractive LED based emergency light. The white housing and lamp-heads are fully adjustable and glare-free. Snap together design for quick and easy installation with option for Wall or Ceiling mount.

PE2EU-30 White
9" W., 4-5/8" ht.,
Extends 2-3/4".
Input 120V or 277V, AC Input
101 lumens.



PE2EU-30

Normally On/Off Emergency Light LED

The PEOEU Series offers LED performance in "normally on" AC and emergency lighting modes. The unit has a prismatic polycarbonate refractor with a durable die-cast aluminum housing available with durable powder coated finish in Bronze. The housing is fully sealed and gasketed. It is designed for wall mounting with a universal K/O pattern in the back-plate for installation to most standard size junction boxes. Illumination is provided by 2 high power LEDs driven at 3 watts each. LED color at 5500K.

PEOEU-EM-20 Bronze
6-1/8" W., 10-1/2" ht.,
Extends 3-5/8".
Input 120V or 277V, AC Input.
AC Mode-223 lumens.
DC Mode-261 lumens.
(Running on Emergency Battery)



PEOEU-EM-20

Lamps

Vintage Lamps



P7825-01
Overall L. 5-7/16" maximum.
40w ST64 Edison E26 medium base. Vintage Amber bulb.



P7827-01
Overall L. 5-7/16" maximum.
40w T9 E26 medium base.
Vintage Amber bulb.



P7826-01
Overall L. 3-1/2" maximum.
40w T8 E12 candelabra base.
Vintage Amber bulb.

LED Lamps



LED LAMP
F8.5A19DLED927/JA8
8.5W A19 LED medium base filament lamp.
2700K, 600 lumens,
1500 hours, dimmable.
JA8



LED LAMP
F4B10DLED927/JA8
4W B10 LED candelabra base filament lamp.
2700K, 300 lumens,
1500 hours, dimmable.
JA8



LED LAMP
F4T10DLED927/JA8
4w T10 LED medium base filament lamp
2700K, 300 lumens,
15,000 hours, dimmable.
JA8



VINTAGE LED LAMP
V6.5ST19DLED922/JA8
6.5w ST19 LED medium base amber filament lamp
2200K, 450 lumens,
15,000 hours, dimmable.
JA8



LED LAMP
3G9DLED27
3w LED G9 base lamp
2700K, 270 lumens,
25,000 hours, dimmable.



LED LAMP
EF4T8D927/JA8
4w T8 LED candelabra base filament lamp
2700K, 300 lumens,
15,000 hours, dimmable.
JA8



EF6.5T10DL9927/JA8
6.5w T10 LED medium base filament lamp
2700K, 600 lumens,
15,000 hours, dimmable.
JA8



F7ST19DLED927/JA8
7w ST19 LED medium base filament lamp
27000K, 600 lumens
15,000 hours, dimmable.
JA8

Landscape Lamps



P7801-01
18w T5 wedge base clear lamp, 12v.

Halogen Lamps



P7812-01
35w G9 halogen frosted lamp, 120v.



P7818-01
6-pack of 60w G9 halogen frosted lamps, 120v.

Krypton Lamps



P7807-01
E12 (candelabra) frosted lamp, 120v.

Lamp Reference Chart

Medium Base - E26



A19 — A19 LED

A Series



R20 — R30 — R40

R Series



PAR20 — PAR30L — PAR30S — PAR38

PAR Series



BR30 — BR40

BR Series



G25 — G30 — G40

G Series



Spiral CFL

CFL



ST64 — T9

Vintage

Candelabra Base - E12



B10 — B11 LED

B Series



T8 — T4

T Series



G16.5

G Series

Spiral CFL

CFL



T8

Vintage

PIN Base



MR16 LED

MR Series



GU4 Halogen — GU5.3 Halogen — GU10 Halogen — GU24 CFL

GU Series



G4 Halogen — G9 Halogen

G Series



T4 CFL 2-Pin — T4 CFL 4-Pin — T5 — T8 — T5 Krypton

T Series

Equivalent Light Output

The following wattages are now available for medium base A lamps. It is at our customers discretion to install CFL or LED bulbs. Pay careful attention to the bulb manufacturer's caution statements regarding use in enclosed fixtures or dimmer compatibility.

LEGACY BULBS WATTS (W)	EISA COMPLIANT INCANDESCENT BULBS (W)	TYPICAL LIGHT OUTPUT (LUMENS)	COMMON CFL LIGHT BULBS WATTS (W)	TYPICAL LED LIGHT BULBS WATTS (W)
40	29	450	9-13	5
60	43	800	13-15	9
75	53	1,100	18-25	13
100	72	1,600	23-30	17
150	N/A	2,600	30-52	22

Foyer Sizing Guides

Foyers

The rule of thumb is to accommodate 2.5 - 3 inches of chandelier height for each foot of ceiling height.

9′ - 10′ Ceiling

Hang a fixture using a guideline 7-to-7.5 feet should proceed sufficient results.

11′ + Ceiling


Divide the vertical space into thirds, positioning the fixture(s) two-thirds of the distance from the floor, so that the ceiling height does not overwhelm the space. If the foyer is large and has a high ceiling, it's recommended to choose a slightly larger fixture than formulas suggest.

**Note confirm that light doesn't interfere with door swing. If it does, place it further back.*

Foyer Sizing Recommendations

ROOM WIDTH (smallest rm. dimension)	Fixture Width		
	Max.	Target	Min.
5′	21″	16.8″	9″
6′	25.2″	20.2″	10.8″
7′	29.4″	23.5″	12.6″
8′	33.6″	26.9″	14.4″
9′	37.8″	30.2″	16.2″
10′	42″	33.6″	18″
11′	46.2″	37″	19.8″
12′	50.4″	40.3″	21.6″
13′	54.6″	43.7″	23.4″
14′	58.8″	47″	25.2″
15′	63″	50.4″	27″
16′	63″	53.8″	28.8″
17′	71.4″	57.1″	30.6″
18′	75.6″	60.5″	32.4″

ROOM HEIGHT	Fixture Height	
	Max.	Min.
8′	12″	-
9′	24″	-
10′	30″	18″
11′	33″	19.8″
12′	36″	21.6″
13′	39″	23.4″
14′	42″	25.2″
15′	45″	27″
16′	48″	28.8″
17′	51″	30.6″
18′	54″	32.4″
19′	57″	34.2″
20′	60″	36″
21′	63″	37.8″
22′	66″	39.6″
23′	69″	41.4″
24′	72″	43.2″




Dining Sizing Guides

Dining

The table under the fixture should serve as a guide for selecting the right fixture for your space. To calculate the correct width, start with the width of your table and subtract 12". (For example, if your table is 42" wide, your chandelier should not be more than 30" wide.)

Based on an 8' ceiling, your fixture should hang between 30"-36" above the table.



Dining Sizing Recommendations

ROOM WIDTH (smallest rm. dimension)	Fixture Width		ROOM HEIGHT	Fixture Height
	Max.	Min.		Max.
10'	30"	See Notes Below	8'	24"
11'	33"		9'	27"
12'	36"		10'	30"
13'	39"		11'	33"
14'	42"		12'	36"
15'	45"		13'	39"
16'	48"		14'	42"
17'	51"		15'	45"
18'	54"		16'	48"
20'	57"		17'	51"
21'	63"		18'	54"

Minimum Width Recommendations:
Add width of room + length and use this number as inches

Note: For 10'-0" ceiling heights or below, fixture should not exceed width of table less than 12".

Dining Mounting Recommendations

Ceiling Height	Distance from bottom of fixture to table surface
8'	30"
9'	33"
10'	36"
11'	39"
12'	42"
Above 12'	Fixture should be mounted more in relation to the room than to the table

Kitchen Sizing Guides

Kitchen Pendants


Start the row 12″-15″ in from either end of the island and then space the pendants evenly within that span.

Space pendants around 24″- 30″ apart from one another (depending on style & quantity).

Pendants should be at least 10″ smaller in diameter than the width of the countertops. Consider the rule of odd numbers (unless using oversized fixtures).

Keep 30″-36″ of space between the countertop and fixtures.

- 8′ island = 96″
- 96″ - 24″ (12″ from ends of island) = 72″
- 72″ - 24″ - 24″ = 24″/3 = 8″ diameter max. (spaced 24″ apart from each other)
- 72″ - 30″ - 30″ =30″/3 = 4″ diameter min. (spaced 30″ apart from each other)



Bath Sizing Guides

Single Bowl Vanities


Position fixtures on both sides of the mirror to provide shadow-free lighting for your face. Ideal width is at least 28″ apart and centered 66″ above the floor, depending on mirror size and ceiling height.

Task Lighting

Center recessed downlights 24″ to 36″ between where the face and the mirror are at the vanity to eliminate shadows.

Vanities With Two Sinks

Consider mounting two separate fixtures, one above each sink. They should be approximately 75″-80″ above the floor.




Outdoor Sizing Guides

Front Door – Wall Lanterns

For a front door with two lanterns, the lantern height should be approximately 1/4 the height of the door. Front doors with one lantern should be approximately 1/3 the height of the door. Mount lanterns approximately 66” above floor for accurate lighting effects.

For a door that is 96” in height, multiply the height by .25 to get 24” for the suggested height of each fixture.




96″ Door x .25″ = 24″
24″ height for each fixture

Front Door – Hanging Lanterns

For a front door with a hanging lantern, the lantern height should be approximately 1/5 the height of the door.

Hanging lanterns are hung using chain or stems connections, so be sure to consider the additional length of the chain or stem. The hanging lantern should not hang below 7’ from the ground, including the fixture, chain and stem.

Allow 6” minimum clearance from the bottom of the lantern to the top of the door to allow the door to open and close. If there is not enough clearance, consider using a flush mount outdoor fixture. the height of the door.




96″ Door x .2 = 19″ ht. fixture

Garage – Wall Lanterns

If you are installing two or more wall lanterns on the exterior of your garage, the lantern height should be approximately 1/4 the height of the door. For installing a single wall lantern, the height of the fixture should be approximately 1/3 the height of the door.

For a garage door that is 16’ in height, multiply the height by .25 to get 4’. Divide 4’ by 2 to get 24”, which is the suggested height of each fixture.



16′ Door x .25″ = 4′
4’/2 = 24” height for each fixture

Icon Guide

Products referencing this logo meet the energy efficiency requirements for light fixtures set forth in ENERGY STAR® product specifications. Please refer to www.energystar.gov for specific product qualifications and list of certified products.

Please note indoor only (dry location) fans should only be used indoors. Even if an outdoor area or screened-in porch is covered, the motor and the blades can be affected when exposed to humidity. You can, however, "bring the outdoors inside" – as using outdoor ceiling fans are perfectly acceptable to use in interior spaces.

If you are selecting a ceiling fan for a space that is outdoors and under a roof, i.e. any covered porches; you should select either a damp rated or wet listed fan. Damp location fans may also be used indoors.

If the fan comes directly into contact with water, you'll need to ensure that the ceiling fan has a "wet" listing. Ceiling fans designed for damp or wet locations feature elements, such as moisture-resistant motors and all weather blades. Wet location fans may also be used indoors.

JA8

This marking indicates fixtures that have an integrated LED or replaceable LED module that has been tested and listed in the California Appliance Database. Check for certified lamps, fixtures or LED light engines by searching the MAEDBS database. Go to cacertappliances.enegy.ca.gov

T24

Table 150.0A defines products that do not have to meet JA8 and can be used to comply with 2016 Title 24. The most common types include:

- Pin-based linear or compact fluorescent light sources using electronic ballasts
- GU-24 sockets containing light sources other than LEDs
- Inseparable SSL luminaires that are installed outdoors

T20

Products comply with the California Appliance Efficiency Regulations. Certified products are listed on the appliance efficiency database found at www.appliances.energy.ca.gov.

Products with this icon are Dark-Sky Friendly: they are certified by the International Dark-Sky Association to minimize glare while reducing light trespass and skyglow (they don't pollute the night sky.)

Fixtures that support compliance when used in outdoor lighting applications

The products with this logo have passed the cUL requirements and are available for sale in Canada. These products include the additional safety features needed to comply with the regulations in Canada. Items with the icon are listed with NRCan.

ADA

Complies with "American with Disabilities Act"

Warranty

For more details regarding product warranty coverage, please consult a qualified Progress Lighting distributor or visit:

progresslighting.com/warranty

Where to buy

To purchase Progress Lighting products from one of our authorized dealers visit:

progresslighting.com/where-to-buy

Product Index

P1000

P1841 . . . . . 775, 783
P1851 780
P186 787
P187 784

P2000

P2000 . . . . . 244, 245, 601
P2001 601
P2002 601
P2003 601
P2004 . . . . . 218, 219, 587
P2005 587
P2006 587
P2007 587
P2008 600
P2009 600
P2010 600
P2011 600
P2012 509
P2013 509
P2014 509
P2015 509
P2016 587
P2018 595
P2019 595
P2020 595
P2021 595
P2041 . . . . . 242, 243, 589
P2060 . . . . . 69, 460, 523
P2078 589
P2079 589
P2080 589
P2081 589
P2095 . . . . . 235, 582
P2096 582
P2097 582

P2101 . . . . . 75, 460, 516
P2102 516
P2105 582
P2115 . . . . . 524, 525
P2116 . . . . . 524, 525
P2117 . . . . . 524, 525
P2118 . . . . . 524, 525
P2127 . . . . . 226, 227, 583
P2128 583
P2129 583
P2130 583
P2131 . . 212, 213, 214, 596, 598
P2142 . . . . . 500, 501
P2143 . . . . . 500, 501
P2144 . . . . . 500, 501
P2145 . . . . . 500, 501
P2146 . . . . . 224, 225, 578
P2147 578
P2148 578
P2149 578
P2158 . . . . . 596, 598
P2159 . . . . . 596, 598
P2160 . . . . . 596, 598
P2165 575
P2166 575
P2167 575
P2168 575

P2308 441
P2318 445
P2320 445
P2330 445
P2332 445
P2334 417

P245 793

P2500 378
P250000 325
P250002 327
P250004 352
P250006 331
P250008 379
P250010 353
P250012 329
P250016 375
P250022 356
P250024 357
P250026 343
P250028 380
P250030 339
P250032 350
P250034 385
P250036 396
P250038 345
P250040 387
P2501 377
P2502 398
P2503 374
P2521 369
P2524 383
P2525 383
P2526 399
P2530 373
P2531 375
P2539 372
P2540 360
P2542 359
P2544 361
P2546 335
P2548 365
P2550 341
P2552 368
P2553 371
P2554 347
P2555 370
P2556 371
P2558 367
P2560 337
P2562 397
P2564 395
P2568 364
P2570 349
P2572 382
P2574 391
P2576 394
P2578 366
P2582 363
P2584 355
P2586 354
P2588 381
P2590 358
P2592 351
P2594 333
P2596 389
P2598 362
P2599 376

P2600 405
P2601 400
P2602 404
P2603 406
P2604 406
P2605 406
P2606 406
P2607 406
P2608 406
P2609 406
P2610 405
P2611 400
P2612 402
P2613 407
P2618 407
P2623 401
P2628 403
P2630 407
P2631 407
P2636 400
P2642 404
P2643 404
P2644 405
P2645 401
P2649 402
P2650 401
P2654 402
P2659 403
P2660 403
P2661 407
P2662 407
P2663 407
P2665 407
P2666 407
P2667 407

P2700 576
P2701 576
P2702 576
P2703 576
P2706 . . . . . 256, 606
P2707 606
P2708 606
P2709 606
P2713 607
P2714 607
P2775 523
P2776 523
P2777 523
P2781 . . . . . 474, 494
P2782 494
P2794 . . . . . 222, 223, 588
P2795 588
P2796 588
P2797 588

P2801 559
P2802 559
P2803 559
P2804 559
P2809 . . . . . 465, 561
P2834 . . . . . 477, 495
P2839 495
P2851 426
P2881 . . . . . 231, 233, 472, 581
P2882 581
P2883 581
P2884 581

P2913 . . . . . 252, 253, 603
P2915 603
P2919 603
P2928 603
P2959 . . . . . 216, 217, 586
P2977 586
P2978 586
P2989 . . . . . 234, 562, 563
P2991 . . . . . 562, 563
P2992 . . . . . 562, 563
P2997 . . . . . 562, 563
P2998 586

P3000

P300028 555
P300029 555
P300030 555
P300031 555
P300032 526
P300033 526
P300034 526
P300039 . . . . . .550, 551
P300040 . . . . . .550, 551
P300041 . . . . . .550, 551
P300042 542
P300043 542
P300044 542
P300045 . . . . . 540, 541
P300046 . . . . . 540, 541
P300047 . . . . . 540, 541
P300048 . . . . . 540, 541
P300049 . . . . . 568, 569
P300050 . . . . . 568, 569
P300051 . . . . . 568, 569
P300052 . . . . . 568, 569
P300054 485
P300055 485
P300057 . . . . . .220, 221, 579
P300058 579
P300059 579
P300060 579
P300066 . . . . . 131, 467, 543
P300067 543
P300068 543
P300069 543
P300076 517
P300077 517
P300078 517
P300079 517
P300080 . . . . . .570, 571
P300081 . . . . . .570, 571
P300082 . . . . . .570, 571
P300083 . . . . . .570, 571
P300084 . . . . . 201, 203, 580
P300085 580
P300086 580
P300087 580
P300091 484
P300092 484
P300093 487
P300094 487
P300095 602
P300096 602
P300097 602
P300098 602
P300099 602
P300116 . . . . . 85, 87, 510, 512
P300117 . . . . . 510, 512
P300118 . . . . . 510, 512

P300119 . . . . . 510, 512
P300120 . . . . . 463, 520, 521
P300121 . . . . . .520, 521
P300122 . . . . . .520, 521
P300123 . . . . . .520, 521
P300124 . . . . . 544, 545
P300125 . . . . . 544, 545
P300126 . . . . . 544, 545
P300131 584
P300132 584
P300133 584
P300134 584
P300137 527
P300138 527
P300139 527
P300140 527
P300141 508
P300142 508
P300143 508
P300144 . . . . . 462, 522
P300145 522
P300146 522
P300147 522
P300148 558
P300149 558
P300150 . . . . . 498, 499
P300151 . . . . . 498, 499
P300152 486
P300153 486
P300154 . . . . . 518, 519
P300155 . . . . . 518, 519
P300156 . . . . . 518, 519
P300157 . . . . . 518, 519
P300158 . . . . . 228, 229, 577
P300159 577
P300160 577
P300161 577
P300174 . . . . . 556, 557
P300175 . . . . . 556, 557
P300176 . . . . . 556, 557
P300177 . . . . . 556, 557
P300178 . . . 171, 173, 566, 567
P300179 . . . . . 566, 567
P300180 . . . . . 566, 567
P300181 . . . . . 566, 567
P300182 . . . . . 490, 491
P300183 . . . . . 496, 497
P300184 . . . . . 496, 497
P300185 . . . . . 488, 489
P300186 . . . . . 488, 489
P300187 . . . . . 488, 489
P300188 . . . . . 488, 489
P300203 . . . . . .550, 551
P300205 503
P300206 503
P300207 503
P300208 504
P300209 504
P300210 504
P300211 505
P300212 505
P300213 505
P300215 462
P300216 . . . . . 534, 535
P300217 . . . . . 534, 535
P300218 . . . . . 534, 535
P300219 585
P300220 585
P300221 585
P300222 . 208, 209, 469, 585
P300223 502
P300224 502
P300225 502
P300226 . . . . . 552, 553
P300227 . . . . . 552, 553
P300228 . . . . . 552, 553
P300229 . . . . . 552, 553
P300230 . . . . . 546, 547
P300231 . . . . . 546, 547
P300232 . . . . . 546, 547
P300233 . . . . . .604, 605
P300234 . . . . . .604, 605
P300235 . . . . . .604, 605
P300236 . . . . . .604, 605
P300237 . . . . . .604, 605
P300238 . . . . . .604, 605
P300239 507
P300240 507
P300243 507
P300244 507
P300253 . . . . . .530, 531
P300254 . . . . . .530, 531
P300255 . . . . . .530, 531
P300256 . . . . . .530, 531
P300257 . . . . . 528, 529
P300258 . . . . . 528, 529
P300259 . . . . . 528, 529
P300261 . . . . . 572, 573
P300262 . . . . . 572, 573
P300263 . . . . . 572, 573
P300264 . . . . . 572, 573
P300265 . . . . . 538, 539
P300266 . . . . . 538, 539
P300267 . . . . . 538, 539
P300268 . . . . . 536, 537
P300269 . . . . . 536, 537
P300270 . . . . . 536, 537
P300271 . . . . . 536, 537
P300272 . . . . . 532, 533
P300273 . . . . . 532, 533
P300274 . . . . . 532, 533
P300275 . . . . . 532, 533
P300277 599
P300278 599
P300279 599
P300280 . . . . . 514, 515
P300281 . . . . . 514, 515
P300282 . . . . . 514, 515
P300283 . . . . . 514, 515
P300286 . . . . . 564, 565
P300287 . . . . . 564, 565
P300288 . . . . . 564, 565
P300289 . . . . . 564, 565
P300290 506
P300291 506
P300292 506
P3025 612
P3026 612
P3027 591
P3028 591
P3029 591
P3030 . . . . . .215, 574
P3038 612
P3041 591
P3051 608
P3052 608
P3053 608
P3054 608
P3055 608
P3056 608
P3057 574
P3058 574
P3076 513
P3077 513
P3078 513
P3110 609
P3111 609
P3114 613
P3115 613
P3116 613
P3117 613
P3118 613
P3161 . . . . . 250, 251, 593
P3162 593
P3163 593
P3164 593
P3184 423
P3190 . . . . . .239, 241, 592
P3191 592
P3192 592
P3193 592
P3203 437
P3266 590
P3267 590
P3268 590
P3269 590
P3287 . . . . . 610, 611
P3288 . . . . . 610, 611
P3289 . . . . . 610, 611
P3290 428
P3298 612
P3299 612
P3300 612
P3333 612
P3335 612
P3368 609
P3369 609
P3401 437
P3402 413
P3405 436
P3406 436
P3408 436
P3410 436
P3412 436
P3423 427
P3424 . . . . . 212, 213, 214, 427
P3434 412
P3447 443
P3448 443
P3449 443
P3450 . . . . . 212, 213, 214
P3452 416
P3460 431
P3473 . . . . . 238, 240, 424
P3474 . . . . . 238, 240
P3475 424
P3476 424
P3480 427
P3481 427
P3483 427
P3484 427
P3486 265
P3487 265
P3490 429
P3495 413
P350002 450
P350003 450
P350005 451
P350006 451
P350007 451
P350008 451
P350019 450
P350020 450
P350022 419
P350023 451
P350024 451
P350039 419
P350042 175
P350043 430
P350044 430
P350045 430
P350046 415
P350049 . . . . . .147, 149, 420
P350051 448
P350052 448
P350053 448
P350054 448
P350055 446
P350056 446
P350057 . . . . . 248, 249, 431
P350059 . . . . . 131, 413
P350060 . . . . . .210, 211, 415
P350061 415
P350063 . . . . . .220, 221
P350064 . . . . . .266, 267, 440
P350065 . . . . . .266, 267, 440
P350066 . . . . . .266, 267, 440
P350070 440
P350071 440
P350072 440
P350074 416
P350076 453
P350077 453
P350078 453
P350079 . . . . . 81, 83, 424
P350081 449
P350082 449
P350085 444
P350086 444
P350087 444
P350088 447
P350089 445
P350091 420
P350093 161
P350094 . . . . . 85, 87
P350096 412
P350098 . . . . . .95, 97, 414
P350100 448
P350101 448
P350103 424
P350107 . . . . . 228, 229
P350109 . . . . . 171, 173
P350110 . . . . . 189, 191
P350113 443
P350114 441
P350115 133
P350116 419
P350117 . . . . . 151, 153
P350122 . . . . . .71, 73
P350129 422
P350130 422
P350131 448
P350132 412
P350133 430
P350134 446
P350135 446
P350136 . . . . . 248, 249, 431
P350137 . . . . . .208, 209
P350144 416
P350145 418

Product Index

P4000

P350146 435
P350147 435
P350148 . . . . . 115, 117, 415
P350149 . . . . . 103, 105, 414
P350150 . . . . . 167, 169, 418
P350151 418
P350152 418
P350153 . . . . . 111, 113, 416
P350154 419
P350167 422
P350168 422
P350171 414
P350172 . . . . . 123, 125, 420
P3509 . . . . . 222, 223
P3511 429
P3516 439
P3518 439
P3520 439
P3549 429
P3551 429
P3561 427
P3563 427
P3567 427
P3569 427
P3573 265
P3575 265
P3577 121
P3587 . . . . . 244, 245
P3599 437

P3605 437
P3610 441
P3611 . . . . . 425, 441
P3612 . . . . . 425, 441
P3617 423
P3620 426
P3631 447
P3632 447
P3633 425
P3644 . . . . . 224, 225, 425
P3645 438
P3647 734
P3648 734
P3649 734
P3650 734
P3658 447
P3663 425
P3665 . . . . . 449, 743
P3673 . . . . . 449, 743
P3680 69
P3683 446
P3688 435
P3689 435
P3690 438
P3693 426
P3694 . . . . . 242, 243, 426
P3696 446
P3697 435

P3701 289
P3706 735
P3709 735
P3712 422
P3713 422
P3720 . . . . . 226, 227, 423
P3739 423
P3740 417
P3748 . . . . . 254, 255, 430
P3750 437
P3753 307
P3757 . . . . . 222, 223
P3786 261
P3787 261
P3788 . . . . . 257, 428
P3791 . . . . . 91, 93
P3792 . . . . . 250, 251
P3793 . . . . . 250, 251
P3799 . . . . . 236, 237

P3806 . . . . . 239, 241
P3807 . . . . . 239, 241
P3813 . . . . . 473, 609
P3816 434
P3817 434
P3818 434
P3821 . . . . . 218, 219
P3827 . . . . . 89, 91, 92, 93
P3836 428
P3841 . . . . . 89, 91, 92, 93
P3843 . . . . . 230, 232, 423
P3846 . . . . . 216, 217
P3847 . . . . . 230, 232
P3852 426
P3854 426
P3855 428
P3864 . . . . . 244, 245, 428
P3876 434
P3883 718
P3884 109
P3889 . . . . . 89, 91, 92, 93
P3898 264

P3905 . . . . . 226, 227
P3912 . . . . . 218, 219
P3914 . . . . . 254, 255
P3921 264
P3924 432
P3925 433
P3926 433
P3927 432
P3928 256
P3929 256
P3931 . . . . . 236, 237
P3942 414
P3946 77
P3951 . . . . . 244, 245
P3954 . . . . . 215, 413
P3955 . . . . . 252, 253
P3969 . . . . . 218, 219
P3977 . . . . . 216, 217
P3991 429
P3992 429

P400029 175
P400030 175
P400033 109
P400034 207
P400035 207
P400036 207
P400042 . . . . . 210, 211
P400043 . . . . . 210, 211
P400044 . . . . . 210, 211
P400047 . . . . . 139, 141
P400048 . . . . . 139, 141
P400052 . . . . . 220, 221
P400053 . . . . . 220, 221
P400054 . . . . . 220, 221
P400055 131
P400057 . . . . . 179, 181
P400058 . . . . . 179, 181
P400059 . . . . . 201, 203
P400060 . . . . . 201, 203
P400061 . . . . . 201, 203
P400062 . . . . . 248, 249
P400063 . . . . . 248, 249
P400064 . . . . . 248, 249
P400065 . . . . . 81, 83
P400066 . . . . . 81, 83
P400067 . . . . . 81, 83
P400073 . . . . . 157, 159
P400074 . . . . . 157, 159
P400087 . . . . . 85, 87
P400088 . . . . . 85, 87
P400095 . . . . . 95, 97
P400096 . . . . . 95, 97
P400097 . . . . . 147, 149
P400102 161
P400103 161
P400104 161
P400110 . . . . . 81, 83
P400115 . . . . . 53, 55
P400118 . . . . . 228, 229
P400119 . . . . . 228, 229
P400120 . . . . . 228, 229
P400132 . . . . . 163, 165
P400133 . . . . . 163, 165
P400134 . . . . . 171, 173
P400135 . . . . . 171, 173
P400136 . . . . . 171, 173
P400137 . . . . . 171, 173
P400141 67
P400142 67
P400146 185
P400147 185
P400148 205
P400149 205
P400150 67
P400151 133
P400152 133
P400153 177
P400154 177

P400158 . . . . . 151, 153
P400159 . . . . . 151, 153
P400167 . . . . . 71, 73
P400168 . . . . . 71, 73
P400175 . . . . . 53, 55
P400177 . . . . . 57, 59
P400178 . . . . . 57, 59
P400181 . . . . . 208, 209
P400182 . . . . . 208, 209
P400183 . . . . . 208, 209
P400187 . . . . . 53, 55
P400190 127
P400193 260
P400194 . . . . . 115, 117
P400195 . . . . . 115, 117
P400196 . . . . . 115, 117
P400197 . . . . . 103, 105
P400198 . . . . . 103, 105
P400199 . . . . . 167, 169
P400200 . . . . . 167, 169
P400204 137
P400205 137
P400206 . . . . . 111, 113
P400207 . . . . . 111, 113
P400208 . . . . . 111, 113
P400209 . . . . . 246, 247
P400210 . . . . . 246, 247
P400218 . . . . . 167, 169
P400225 . . . . . 99, 101
P400226 . . . . . 99, 101
P400229 . . . . . 123, 125
P4008 263
P4009 263
P4036 235
P4037 235

P4141 69
P4142 69

P4217 260
P4280 . . . . . 250, 251
P4281 . . . . . 250, 251
P4282 . . . . . 250, 251

P4318 . . . . . 212, 213, 214
P4319 . . . . . 212, 213, 214
P4324 . . . . . 239, 241
P4325 . . . . . 238, 240
P4326 . . . . . 238, 240
P4328 . . . . . 238, 240
P4329 . . . . . 239, 241
P4346 262
P4355 262
P4356 262
P4357 262
P4365 . . . . . 239, 241
P4390 257
P4391 257

P4401 317
P4402 317
P4403 317
P4405 . . . . . 230, 232
P4406 317
P4416 . . . . . 230, 232
P4417 . . . . . 230, 232
P4418 . . . . . 231, 233
P4419 . . . . . 231, 233
P4434 . . . . . 222, 223
P4435 . . . . . 222, 223
P4436 . . . . . 222, 223
P4439 . . . . . 222, 223
P4440 . . . . . 254, 255
P4441 . . . . . 254, 255
P4458 . . . . . 216, 217
P4459 . . . . . 216, 217
P4489 . . . . . 244, 245
P4490 . . . . . 244, 245
P4492 . . . . . 244, 245
P4497 . . . . . 244, 245

P45AT 793

P4609 437
P4610 437
P4612 . . . . . 224, 225
P4613 . . . . . 224, 225
P4614 . . . . . 224, 225
P4618 187
P4619 . . . . . 216, 217
P4621 . . . . . 218, 219
P4622 . . . . . 218, 219
P4623 . . . . . 218, 219
P4624 234
P4625 . . . . . 218, 219
P4626 . . . . . 216, 217
P4627 . . . . . 254, 255
P4632 . . . . . 236, 237
P4635 . . . . . 236, 237
P4638 . . . . . 236, 237
P4644 79
P4645 77
P4646 77
P4650 . . . . . 236, 237
P4659 215
P4663 215
P4664 . . . . . 252, 253
P4666 . . . . . 252, 253
P4668 . . . . . 252, 253
P4685 79
P4687 . . . . . 218, 219
P4695 . . . . . 242, 243
P4696 . . . . . 242, 243
P4697 . . . . . 242, 243
P4699 193

P4700 193
P4709 121
P4710 121
P4711 121
P4718 75
P4719 75

P5000

P4720 155
P4725 . . . . . 242, 243
P4726 . . . . . 212, 213, 214
P4732 259
P4734 . . . . . 254, 255
P4735 . . . . . 254, 255
P4739 . . . . . 236, 237
P4742 183
P4745 . . . . . 226, 227
P4746 . . . . . 226, 227
P4747 . . . . . 226, 227
P4748 . . . . . 226, 227
P4757 259
P4758 . . . . . 216, 217
P4762 258
P4770 258

P4961 439
P4962 439

P500002 280
P500018 312
P500019 312
P500021 294
P500022 . . . . . 147, 149
P500023 . . . . . 147, 149
P500029 . . . . . 210, 211
P500030 . . . . . 210, 211
P500034 293
P500041 . . . . . 139, 141
P500050 . . . . . 220, 221
P500051 300
P500052 300
P500053 300
P500054 . . . . . 220, 221
P500055 . . . . . 163, 165
P500056 131
P500061 . . . . . 179, 181
P500062 . . . . . 81, 83
P500065 310
P500066 310
P500068 . . . . . 63, 65
P500069 . . . . . 63, 65
P500071 . . . . . 248, 249
P500072 . . . . . 81, 83
P500078 . . . . . 157, 159
P500079 . . . . . 157, 159
P500090 . . . . . 147, 149
P500092 . . . . . 143, 145
P500093 . . . . . 143, 145
P500094 . . . . . 143, 145
P500099 . . . . . 85, 87
P500100 . . . . . 85, 87
P500103 . . . . . 95, 97
P500113 161
P500114 161
P500121 . . . . . 53, 55
P500122 . . . . . 53, 55
P500125 . . . . . 228, 229
P500126 . . . . . 228, 229
P500135 286
P500137 . . . . . 171, 173
P500138 . . . . . 189, 191
P500139 . . . . . 189, 191
P500140 199
P500141 67
P500147 304
P500148 304
P500149 314
P500152 . . . . . 163, 165
P500155 177
P500156 306
P500157 . . . . . 151, 153
P500158 . . . . . 151, 153
P500159 287
P500160 287
P500170 282
P500176 . . . . . 57, 59
P500177 . . . . . 57, 59
P500178 . . . . . 139, 141
P500180 . . . . . 208, 209
P500192 127

P500206 . . . . . 212, 213, 214
P500207 . . . . . 115, 117
P500208 . . . . . 103, 105
P500209 . . . . . 103, 105
P500210 . . . . . 167, 169
P500212 282
P500213 290
P500214 290
P500220 295
P500223 197
P500224 197
P500225 197
P500226 620
P500227 620
P500228 137
P500229 297
P500230 297
P500231 297
P500234 618
P500235 618
P500236 289
P500237 286
P500238 . . . . . 111, 113
P500239 . . . . . 111, 113
P500240 . . . . . 111, 113
P500241 308
P500242 308
P500243 . . . . . 246, 247
P500274 . . . . . 99, 101
P500276 280
P500277 . . . . . 123, 125
P500281 295
P500282 295
P500283 305
P500284 305
P500287 . . . . . 63, 65
P500288 259
P5003 311
P5010 235
P5011 311
P5012 311
P5013 316
P5023 294
P5024 294
P5026 234
P5031 69
P5036 312
P5037 312
P5038 195
P5044 . . . . . 79, 412
P5047 . . . . . 242, 243
P5050 285
P5061 75
P5065 . . . . . 236, 237
P5066 . . . . . 224, 225
P5067 292
P5068 315
P5070 292
P5072 310
P5078 . . . . . 250, 251
P5080 316
P5082 193

P5087 315
P5090 257
P5091 316
P5092 . . . . . 226, 227
P5094 315
P5095 . . . . . 238, 240
P5096 . . . . . 238, 240

P5103 316
P5108 . . . . . 222, 223
P5110 . . . . . 242, 243
P5112 . . . . . 222, 223
P5113 . . . . . 254, 255
P5114 215
P5131 . . . . . 252, 253
P5137 296
P5138 296
P5142 . . . . . 91, 93
P5143 307
P5147 . . . . . 216, 217
P5152 155
P5153 . . . . . 231, 233
P5156 195
P5158 314
P5161 293
P5167 . . . . . 222, 223
P5168 155
P5170 . . . . . 212, 213, 214
P5173 234
P5175 313
P5176 311
P5180 183
P5182 307
P5183 307
P5184 313
P5187 313
P5188 284
P5190 183
P5191 183
P5196 296
P5197 284
P5198 273
P5199 273

P5200 761
P5202 753
P5203 753
P5204 759
P5205 759
P5207 753
P5212 753
P5214 753
P5219 760
P5230 761
P5235 759
P5245 758
P5246 758
P5247 758
P5253 760
P5261 760
P5262 761
P5270 . . . . . 244, 245

P5271 760
P5272 760
P5275 760
P5276 760
P5295 758
P5296 758
P5297 758
P5298 758
P5299 758

P5300 . . . . . 218, 219
P5306 79
P5313 759
P5315 155
P5328 292
P5340 303
P5341 303
P5342 303
P5390 755
P5391 755
P5392 755
P5394 755

P5400 . . . . . 638, 639
P540005 755
P540007 708
P540010 683
P540011 . . . . . 636, 637
P540012 . . . . . 642, 643
P540014 684
P540015 684
P540019 . . . . . 716, 717
P540020 709
P540022 667
P540023 646
P540024 695
P540025 666
P540028 627
P540029 659
P540030 . . . . . 640, 641
P540031 . . . . . 660, 661
P540032 668
P540034 635
P540039 622
P540054 694
P540058 682
P540060 677
P540062 623
P540064 631
P540065 629
P540068 . . . . . 632, 633
P5401 712
P5402 699
P5404 621
P5413 696
P5414 732
P5420 653
P5426 733
P5428 681
P5429 710
P5430 726
P5432 726

Product Index

P5436 733
P5438 652
P5444 732
P5445 . . . . . 713, 719
P5450 654
P5456 729
P5458 718
P5459 678
P5468 645
P5474 650
P5475 725
P5478 733
P5479 674
P5482 722
P5483 722
P5484 644
P5487 656
P5493 732

P5500 . . . . . 638, 639
P550011 . . . . . 642, 643
P550012 . . . . . 642, 643
P550014 684
P550015 684
P550016 684
P550017 684
P550019 701
P550020 709
P550021 709
P550022 667
P550023 646
P550025 666
P550028 627
P550029 659
P550030 . . . . . 640, 641
P550031 . . . . . 660, 661
P550032 668
P550033 700
P550034 635
P550035 715
P550036 714
P550038 683
P550039 683
P550040 . . . . . 636, 637
P550042 . . . . . 716, 717
P550043 . . . . . 716, 717
P550047 695
P550054 694
P550055 680
P550057 682
P550058 682
P550059 677
P550060 677
P550061 626
P550062 623
P550064 631
P550065 629
P550068 . . . . . 632, 633
P550070 . . . . . 421, 664
P550071 . . . . . 453, 742
P5501 712
P5504 621
P5513 696
P5520 653
P5523 696
P5529 710
P5530 718
P5535 702
P5550 654
P5551 702
P5559 678
P5560 658
P5561 658
P5562 654
P5565 724
P5574 650
P5579 674
P5582 722
P5584 644
P5587 656
P5589 289

P560001 . . . . . 479, 742
P560024 704
P560029 738
P560030 739
P560034 704
P560035 707
P560036 . . . . . 642, 643
P560037 . . . . . 642, 643
P560038 . . . . . 642, 643
P560042 684
P560043 684
P560044 706
P560045 707
P560046 707
P560047 706
P560048 706
P560049 701
P560050 701
P560051 737
P560052 670
P560053 670
P560056 737
P560057 709
P560058 709
P560059 667
P560060 667
P560061 667
P560062 646
P560063 646
P560064 646
P560065 666
P560066 666
P560067 666
P560071 704
P560072 742
P560073 742
P560077 627
P560078 627
P560079 627
P560080 659
P560081 659
P560082 659
P560083 . . . . . 640, 641
P560084 . . . . . 640, 641
P560085 . . . . . 640, 641
P560087 625
P560088 625
P560089 704
P560090 736
P560091 665
P560092 708
P560093 739
P560094 . . . . . 660, 661
P560095 . . . . . 660, 661
P560096 . . . . . 660, 661
P560097 668
P560098 668
P560099 700
P560100 700
P560101 635
P560102 635
P560103 635
P560110 683
P560111 683
P560112 683
P560113 . . . . . 636, 637
P560114 . . . . . 636, 637
P560115 . . . . . 636, 637
P560119 . . . . . 716, 717
P560120 . . . . . 716, 717
P560121 . . . . . 716, 717
P560129 695
P560130 695
P560131 695
P560132 739
P560136 743
P560137 738
P560148 694
P560149 694
P560150 694
P560151 680
P560152 680
P560156 . . . . . 632, 633
P560157 . . . . . 632, 633
P560158 . . . . . 632, 633
P560159 682
P560160 682
P560162 677
P560163 624
P560164 624
P560166 622
P560167 622
P560168 626
P560171 623
P560172 623
P560173 623
P560174 631
P560175 631
P560176 631
P560177 629
P560178 629
P560185 629
P5602 730
P560208 741
P560209 741
P560210 741
P560211 741
P5603 730
P5604 730
P5605 . . . . . 638, 639
P5607 728
P5610 . . . . . 638, 639
P5611 . . . . . 638, 639
P5612 730
P5613 . . . . . 638, 639
P5622 . . . . . 702, 703
P5623 . . . . . 702, 703
P5624 696
P5625 696
P5626 733
P5627 657
P5628 681
P5629 681
P563000 744
P563001 744
P5634 736
P5635 736
P5641 . . . . . 746, 747
P5642 . . . . . 746, 747
P5643 748
P5644 748
P5645 732
P5649 654
P5650 654
P5651 654
P5652 654
P5656 729
P5665 696
P5670 650
P5671 650
P5672 650
P5673 650
P5674 . . . . . 745, 747
P5675 . . . . . 745, 747
P5676 705
P5681 723
P5682 723
P5683 723
P5684 723
P5686 651
P5687 657
P5688 656
P5689 657
P5690 723
P5692 621
P5693 621
P5699 621

P5700 712
P5701 712
P5702 735
P5703 735
P5704 735
P5705 735
P5706 735
P5710 733
P5711 733
P5712 749
P5713 749
P5715 645
P5716 645
P5717 645
P5721 688
P5722 688
P5723 . . . . . 688, 689
P5727 731
P5729 731
P5730 726
P5731 727
P5738 729
P5741 . . . . . 746, 747,
P5744 731
P5745 731
P5749 . . . . . 674, 675
P5750 . . . . . 674, 675
P5751 . . . . . 674, 675
P5753 649
P5754 649
P5755 649
P5756 727
P5758 727
P5762 725
P5763 686
P5764 686
P5765 725
P5767 725
P5770 724
P5773 724
P5774 . . . . . 745, 747
P5775 699
P5777 724
P5778 699
P5780 699
P5788 . . . . . 438, 728
P5789 . . . . . 438, 728

P5800 740
P5801 740
P5806 740
P5813 730
P5814 732
P5815 732
P5817 730
P5820 653
P5822 653
P5823 653
P5826 729
P5828 710
P5829 710
P5831 727
P5832 726

P5834 . . . . . 438, 726
P5835 652
P5836 652
P5837 652
P5844 730
P5846 727
P5862 . . . . . 713, 719
P5863 . . . . . 713, 719
P5864 . . . . . 713, 718
P5875 654
P5878 712
P5895 691
P5896 691
P5899 691

P5906 678
P5907 678
P5920 644
P5921 644
P5923 644
P5948 . . . . . 469, 705
P5949 705
P5968 754
P5969 754
P5970 754
P5980 687
P5981 687
P5982 687
P5985 724
P5986 724
P5987 647
P5988 647
P5989 647
P5999 678

P6000

P6000 679
P6001 679
P6002 679
P6017 674
P6019 725
P6023 678
P6030 634
P6031 634
P6032 634
P6038 698
P6039 698
P6043 658
P6050 658
P6052 676
P6053 676
P6054 676
P6055 676
P6056 628
P6057 628
P6058 628
P6059 708
P6060 708
P6062 697
P6063 697
P6064 697
P6067 690
P6068 690
P6069 690
P6070 711
P6071 711
P6072 711
P6073 720
P6074 720
P6075 720
P6076 690
P6077 721
P6078 721
P6079 721
P6084 . . . . . 672, 673
P6085 . . . . . 672, 673
P6086 708

P6112 806
P6115 806
P6117 806
P6144 803
P6147 803
P6149 803
P6155 803
P6160 802
P6162 802

P6280 808

P6325 806
P6326 806
P6327 806
P6328 807
P6329 807
P6369 806
P6397 803
P6400 679
P6404 647
P6414 794
P6416 794
P6417 725
P6420 698
P6424 . . . . . 672, 673
P6425 720
P6426 628
P6427 690
P6428 697
P6429 711
P6430 721
P6431 634
P6432 648
P6433 714
P6436 658
P6437 715
P645 792
P6452 676

P6500 679
P6504 647
P6520 698
P6524 673
P6525 720
P6527 690
P6529 711
P6531 634
P6532 648
P6533 714
P6537 715
P6552 676

P660003 821
P6603 . . . . . 469, 705
P6610 714
P6611 714
P6612 714
P6615 715
P6616 715
P6617 715
P6619 657
P6620 657
P6621 657
P6630 651
P6631 651
P6632 651
P6633 651
P6676 787

P6820 821
P6827 . . . . . 764, 820
P6828 . . . . . 764, 820
P6829 . . . . . 764, 820
P6832 . . . . . 764, 820

P6917 794
P6952 794

P7000

P700000 816
P700001 816
P700002 816
P700003 816
P700004 816
P700005 817
P700008 818
P700009 818
P700010 818
P700011 819
P700012 819
P700013 819
P700014 819
P700015 819
P700016 819
P700017 819
P700018 819
P700019 819
P700020 818
P700021 818
P700022 819
P700023 818
P7024 819
P7046 . . . . . 77, 460, 513
P7077 89
P7078 89
P7083 478
P7085 478
P7088 478
P7092 478
P7093 478

P710010 479
P710012 . 139, 141, 466, 546, 547
P710015 . . . . . 466, 534, 535
P710028 . . . . . 81, 83, 460
P710031 . 147, 149, 467, 544, 545
P710036 . . . . . 266, 267, 477
P710044 . . . . . 161, 468
P710045 . . . . . 189, 191, 468
P710046 . . . . . 67, 460, 508
P710047 . . . . . 476, 498, 499
P710049 . . . . . 476, 490, 491
P710050 . . . . . 476, 496, 497
P710051 492
P710052 492
P710054 475
P710056 . . . . . 71, 73, 461
P710058 475
P710061 486
P710062 485
P710071 477
P710072 473
P710073 . 103, 105, 463, 528, 529
P710074 . . . . . 167, 169, 466
P710079 479
P710080 474
P710081 474
P710082 . . 246, 247, 462, 599
P710084 470
P710085 470
P710086 468
P710087 464
P710088 464
P710089 . . . . . 99, 101, 463
P710090 477
P710093 . . . . . 123, 125, 467
P710094 471
P710095 471
P7103 473
P7105 478
P7112 473
P7149 . . . . . 193, 465
P7153 472
P7156 . . . . . 465, 561
P7158 . . . . . 121, 466
P7159 . . . . . 183, 465
P7170 472
P7172 . . . . . 187, 464
P7175 472
P7181 . . . . . 230, 232, 472
P7183 454
P7185 472
P7186 454
P7196 454

P7249 442
P7250 442
P7251 442
P7253 442
P7258 449
P7278 454
P7279 454

P730000 455
P730001 455
P730002 452
P730003 452
P730005 452
P730006 452
P730007 452
P730008 452
P730011 455
P730012 455

P745 792

P7801 . . . . . 761, 824

Product Index

P8000

P8000 793
P800004 770
P8001 793
P8004 792
P8007 . . . . . .785, 791
P8008 785
P8009 . . . . . .785, 791
P8011 . . . . . .785, 791
P8020 787
P8025 . . . . . .785, 791
P8036 778
P8037 778
P8039 778
P8041 . . . . . 779, 788
P8042 . . . . . 779, 788
P8044 . . . . . 779, 788
P8045 778
P8046 . . . . 773, 774, 779, 788
P8047 . . . . . 779, 788
P8052 . . . . . .785, 791
P8053 791
P8057 778
P8060 . . . . . .785, 791
P8061 . . 772, 775, 780, 782, 783
P8062 . . . . . .785, 791
P8063 787
P8065 . . . . . .785, 791
P8066 . . . . . .785, 791
P8068 . . . . . .785, 791
P8071. . . . . 772, 776, 784, 787
P8072 . . . . . .785, 791
P8073 787
P8074 . . . . . .785, 791
P8075 . . . . . .785, 791
P8076. . 773, 776, 784, 785, 787, 791
P8077 . . . . . .785, 791
P8079 . . . . . .785, 791
P8080 . . . . . 772, 774, 779
P8082 . . . . . .785, 791

P810012. 800
P810013. 800
P810014. 800
P810015. 798
P810016. 798
P810017. 798
P810018. 798
P810019. 797
P810020 797
P810021. 797
P810024 798
P810025 452
P810026 452
P810027 800
P8109 . . . . . 782, 789
P8147. 801
P816. 778
P8168. 789
P817. 778
P8172. 789
P8175. 789
P8176 . 773, 775, 780, 782, 783, 789
P818. 778

P821. 790
P8222 801
P8247 801
P8268 780
P8270 762

P830 . . . . . 774, 779
P831. . . . . 774, 779, 788
P832 . . . . . 774, 779
P8367 . . . . . 782, 789
P8368 782
P8375 782

P84 . . . . . 775, 782
P8400. 752
P8403 276
P8404 279
P8475 783

P85 789
P851. 780
P8511 795
P8517. 762
P8518. 762
P8519. 763
P8520 763
P8521. 763
P8522 763
P8523 763
P8524 763
P8525 763
P8526 763
P8531. 763
P8555 795
P8562 761
P8584 795
P8585 795
P8587 795
P8588 795
P8589 795
P8593 795
P8595 801
P8596 801

P86 787
P860004. 279
P860005. 279
P860006. 755
P860007. . . . . .85, 319
P860008. . . . . .87, 319
P860027 . . . . . 161, 319
P860028. 558
P860029. 817
P860030. 817
P860031 817
P860040. 771
P860041 . . . . . .151, 153, 319
P860042. . . . . .151, 153, 319
P860044. 771
P860045. 749
P860046. 749
P860047. 749
P860048. 799
P860049. 799
P860050. 799
P860051 799
P860052. 799
P860053. 797
P860054. 797
P860055. 797
P8601 318
P8602 318
P8607 795
P8618. 761
P8625 318
P8651. 761
P8666 761
P8667 761
P867 . . . . . 780, 783
P8671 761
P8672 761
P8678 318
P868 780
P8685 318

P87 . . . . . 776, 784
P8700 . . . . . 794, 795
P8704 319
P8708 761
P8709 752
P8710. 749
P8712. 749
P8715. 812
P8716. . . . . 794, 795
P8717. 811
P8718. 812
P8720 811
P8721. 811
P8722 811
P8723 811
P8725 795
P8726 752
P8727 812
P8728 812
P8730 810
P8734 812
P8736 811
P8739 795
P8740 817
P8741. 749
P8742 810
P8745 810
P8746 810
P8748 755
P8753 811
P8757 319
P8759 319
P876 . . . . . 780, 783
P8760 810
P8770 811
P8771. 811
P8773 795
P8788 262

P8822 . . . . . 272, 273
P8823 . . . . . 272, 273
P8824 . . . . . 272, 273
P8825 . . . . . 272, 273
P8828 . . . . . 272, 273
P8829 . . . . . 272, 273
P8830 . . . . . 272, 273
P8926 319

P9000

P900000 813
P900001. 813
P900002. 813
P900003. 813
P900011 804
P900012 804
P900013 805
P900014 805

P9103 810
P9104 810
P9105 810
P9106 810
P9107. 811
P9108 810
P9109 810
P9110. 810
P9113 812
P9115 811
P9116. 811
P9117 811
P9121 810
P9122. 811
P9123. 810

P9200 807
P9201 807
P9203 809
P9204 809
P9205 808
P9206 808
P9207 808
P9215. 809
P9216. 809
P9219. 809
P9220 809

PC - PT

PC001 754
PE2EU 823
PECUE. 822
PEOEU. 823
PETPE 822
PTORK3010. 754

Every effort has been made to ensure the accuracy of information in this catalog. Progress Lighting reserves the right to make product changes from time to time, without prior notification, which may change the information provided in this catalog. Errors brought to our attention will be corrected in subsequent issues.

UL, CSA, or ETL Listed or Classified unless otherwise noted. Bulbs not included with fixtures unless specified. Specifications subject to change without notice.

Metal finishes not specified as "solid" have quality plated or painted finishes.

Finish representations are high resolution digital reproductions, and, while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes, due to the nature of hand craftsmanship.

©Progress Lighting 2020
All rights reserved.
International copyright secured.



Featuring Jusdon



Where to Buy

To purchase Progress Lighting products from one of our authorized dealers visit **progresslighting.com/where-to-buy**

Customer Support

United States	Call Us 800-447-0573
Canada	Call Us 866-418-5542

Speak to a Customer Support Representative from 8:00 AM to 8:00 PM EST, Monday – Friday, or visit **progresslighting.com/contactus**



Be Inspired

@ProgressLtg
@ProgressLtg
@ProgressLighting
@ProgressLtg
Progress Lighting
Progress-Lighting
#ProgressLightingMoments

Equip. Educate. Excite.

These three words define the mission of Progress Lighting. Flip through our catalog, and you'll quickly see how we equip you with the education to make all your exciting design dreams come true. Whether you're looking for the latest and greatest trends or some tried-and-true pieces, you'll find the just-right lighting choices to illuminate the special moments in your life. Not sure where to start? Whether you're browsing our catalog or visiting our website, Progress is at your service to help you envision where and how to use our products.

Experience Progress

Learn how lighting can totally transform a space. Experience Progress features beautiful room images from our builder partners, design firms, social media fans and influencers bringing the Progress Lighting story to life. By working together, we're furthering a vision of providing whole home solutions to those who are seeking inspiration.
Visit **progresslighting.com/experienceprogress**

Our Blog

Explore our blog for even more design inspiration, product integration and trend guidance to make your home into a haven of livable luxury.
See **progresslighting.com/blog**

PROGRESS LIGHTING™

701 Millennium Boulevard
Greenville, SC 29607

See Yourself Here

Every home and every family has a story that's all their own. In this issue, we introduce you to the many ways Progress Lighting can bring that story to life.



PROGRESS LIGHTING

701 Millennium Boulevard
Greenville, SC 29607

progresslighting.com