

NOTE: FOR INSTRUCTION SHEET SCROLL DOWN TO NEXT SHEET

NOTES:
1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
2. BOX VOLUME: 42 IN³ [688.2 CM³]
3. ACCEPTS ALL 4-11/16" COVERS,707RAC & 709 PARTITIONS, ALL SOLD SEPARATELY
4. UL LISTED
5. KNOCKOUTS IN LOCATION "A" ARE ACCESSIBLE FOR 5-1/2"[140] & 6"[152.4] STUDS ONLY

KNOCKOUTS

TRADE SIZE	LOCATION	QTY.
(1/2"-3/4") TKO®	B, C, D, E	3
(1/2"-3/4") TKO®	A (SEE NOTE 5)	3
1/2" KO	A (SEE NOTE 5)	1

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
SPACER	STEEL	GALVANIZED
SIDE	STEEL	GALVANIZED
FASTENERS	STEEL	GALVANIZED
FARSIDE SUPPORT	STEEL	GALVANIZED
PIGTAIL	INSULATED SOLID COPPER	N/A
STUD BRACKET	STEEL	GALVANIZED

257M CUS

SYM.	REVISION DESCRIPTION	APP	DATE
	INITIAL RELEASE	K.K.	06/22/2015

257M

DIMENSION SHEET FOR CAT. NO.

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE: **4-11/16" SQUARE WELDED BOX 2-1/8" DEEP WITH RAISED GROUND, SOLID PIGTAIL, STUD BRACKETS & FARSIDE SUPPORT**

TOLERANCE UNLESS OTHERWISE SPECIFIED

.XX DECIMAL ±.015
.XXX DECIMAL ±.005
ANGLE ±2°

RACO
South Bend, Indiana

DRAWN BY:	K.K.	SCALE: 1:3
APP. BY:	N.S.	
DATE:	06/22/2015	

SIZE: A

Instructions for using the RACO® Universal Box Stabilizer

1-1/2” Deep Boxes

Bend center tab as shown

For 2-1/2” deep studs



Bend center tab as shown - 2 places

For 3-1/2” deep studs



Bend center tab as shown

For 3-5/8” deep studs



Bend center tab as shown

For 4” deep studs



Bend both tabs as shown

For 5-1/2” deep studs

Bend both tabs as shown

For 6” deep studs

2-1/8” Deep Boxes



Comes preset



Bend center tab as shown - 2 places



Bend center tab as shown



Bend center tab as shown



Bend both tabs as shown

Bend both tabs as shown

NOTICE: Bottom knockouts are NOT usable with the FS support.