

Bell & TayMac Hour

Topic: TayMac/Bell Adapter System

July 28, 2020

NOTE: For those who are unable to attend we will be recording this training session for future reference and review....

PLEASE MUTE YOUR PHONES....



COMMERCIAL CONSTRUCTION



Overview

- Allows for quick and easy adaptation of TayMac and Bell covers to accommodate the installation needs through including various adapter inserts
- Configurations are based on three main factors:
 - Pre-configured configuration (GFCI, Duplex)
 - Gang Size (Single Gang, Dual Gang)
 - Orientation (Vertical, Horizontal or both)
- The patented Universal Fit Adapter System Technology (U-Fast) comes pre-configured for GFCI
- Primarily the construction of the adapters are non-metallic however some models do offer metallic inserts
- The adapter inserts include the following types (depending upon specific model):
 - GFCI
 - Duplex
 - Round
 - Switch
 - 1-1/4"
 - 1-3/8"
 - 1-9/16" & 1-5/8"
 - 1-3/4"
 - 1-11/16"
 - 2-1/8"
 - 2-1/4"
 - 2-5/8"
 - 2-7/16"






COMMERCIAL CONSTRUCTION






TayMac Adapter Systems Overview



- 6in1
 - MR420 Series
- 8in1
 - MX Single Gang Series
- 16in1
 - ML & MM Single Gang Series
- 55in1
 - ML, MM and MX Dual Gang Series
- Other Notable:
 - 40in1 - Mainly MM7440 Series (Standard Duty, NOT Extra Duty)



- 3in1
 - Single Gang Device Cover
- 4in1
 - Locking Cover
- 12in1
 - Single Gang MX Flip Cover
- 14in1
 - MX Series Flip Cover
- 25in1
 - MX Series Dual Gang Flip Cover
- 125in1
 - MX Series 3-Gang Flip Cover



COMMERCIAL CONSTRUCTION



Configuration Summary


Allows for quick and easy adaptation of TayMac and Bell covers to accommodate the installation need through including various adapter inserts. The adapter inserts will range from

MR420 Series:


- Mounts horizontally or vertically
- Accommodates duplex, GFCI or round receptacle (not included)
- Patented Universal Fit Adapter System Technology (U-Fast) comes pre-configured for GFCI
- Electrical box and siding flange included
- For all common siding types and materials (vinyl, wood, stucco, brick or block)
- Installation instructions and mounting hardware included
- Available in Gray, White and Bronze

6ⁱⁿ1
CONFIGURATIONS

Adapters
Included:



Configurations:
Horizontal and Vertical



MR420CW



MR420CZ



Vinyl Siding

Brick

Stucco



COMMERCIAL CONSTRUCTION




Configuration Summary

MX Metal IU Series:


- Heavy duty die-cast metal construction
- Meets or exceeds Extra Duty® specifications
- Patented Quick-Fit keyhole mounting system allows cover installation in under a minute
- Includes gasket and mounting hardware
- Patented Universal Fit Adapter System Technology (U-Fast) comes pre-configured for GFCI
- Premium powder coat finish
- Lockable tab

8ⁱⁿ1
CONFIGURATIONS

Adapters
Included:



Configurations: Vertical



COMMERCIAL CONSTRUCTION



Configuration Summary


ML/MM IU Series Covers:

- High-impact polycarbonate construction provides maximum durability
- Patented Quick-Fit keyhole mounting system allows installation in under a minute
- Includes attached gasket and mounting hardware
- Patented Universal Fit Adapter System Technology (U-Fast) for 16-in-1 configurations, comes pre-configured for GFCI
- Lockable tab

16ⁱⁿ1

CONFIGURATIONS

Adapters Included:



Configurations:
Horizontal and Vertical



Additional 16in1 Configurations not listed:

ML450G	16-in-1 Flat Expandable Vertical/Horizontal
ML450W	16-in-1 Flat Expandable Vertical/Horizontal
ML450Z	16-in-1 Flat Expandable Vertical/Horizontal
MM110C	Horizontal/Vertical 16-in-1
MM110G	Horizontal/Vertical 16-in-1
MM110W	Horizontal/Vertical 16-in-1
MM410C	Horizontal/Vertical 16-in-1 Standard
MM410CA	Horizontal/Vertical 16-in-1 Standard w/Round Box Adaptor
MM410CW	Horizontal/Vertical 16-in-1 Standard
MM410G	Horizontal/Vertical 16-in-1 Standard
MM410W	Horizontal/Vertical 16-in-1 Standard
MM510C	Horizontal/Vertical 16-in-1 Deep
MM510G	Horizontal/Vertical 16-in-1 Deep
MM710C	Horizontal/Vertical 16-in-1 Jumbo
MM710G	Horizontal/Vertical 16-in-1 Jumbo



COMMERCIAL CONSTRUCTION



TayMac®

Configuration Summary


2-Gang Series Covers:

- High-impact polycarbonate construction provides maximum durability (ML/MM Series)
- Heavy duty die-cast metal construction (MX Series)
- Meets or exceeds Extra Duty® specifications
- Patented Quick-Fit keyhole mounting system allows installation in under a minute
- Includes attached gasket and mounting hardware
- Patented Universal Fit Adapter System Technology (U-Fast) comes pre-configured for GFCI
- Lockable tab

55ⁱⁿ1 CONFIGURATIONS

Adapters Included: 

Configurations:
Horizontal



Multiple combinations of duplex, GFCI, switch, and rounds: 1-1/4", 1-3/8", 1-9/16", 1-5/8", 1-11/16", 1-3/4", 2-1/8", 2-1/4", 2-7/16"



COMMERCIAL CONSTRUCTION



TayMac®

Configuration Summary

2-Gang Series Covers:

- High-impact polycarbonate construction provides maximum durability
- Patented Quick-Fit keyhole mounting system allows installation in under a minute
- Includes attached gasket and mounting hardware
- Patented Universal Fit Adapter System Technology (U-Fast) comes pre-configured for GFCI
- Lockable tab

40ⁱⁿ1
CONFIGURATIONS




MM7440C



MM7440G

Configurations:
Horizontal



Multiple combinations of duplex, GFCI, switch and rounds: 1-3/8", 1-5/8", 1-3/4", 2-1/4", 2-5/8"



COMMERCIAL CONSTRUCTION



TayMac®

Configuration Summary

Device Cover Series Covers:

- Heavy duty die-cast metal construction
- Patented Quick-Fit keyhole mounting system allows cover installation in under a minute
- Includes gasket and mounting hardware
- Patented Universal Fit Adapter System Technology (U-Fast) comes pre-configured for GFCI
- Premium powder coat finish
- Horizontal or vertical mount
- Lockable tab

3 IN 1
CONFIGURATIONS

**Adapters
Included:**



2 1/4"



Adapter (Included)



2 1/4"



Duplex



GFCI

**Configurations:
Horizontal or Vertical**



MX2150S



COMMERCIAL CONSTRUCTION




Configuration Summary

Locking Cover Series Covers:

- Heavy duty cast aluminum construction with durable enamel paint
- Cobra Cam lock, key removal in locked and unlocked positions
- 2 keys provided
- Patented Universal Fit Adapter System Technology (U-Fast) for 4-in-1 custom device configurations, comes pre-configured for GFCI
- Irradiation crosslinked polyethylene foam gasket
- Mounting hardware included
- Adapters included for various devices

4 IN 1
CONFIGURATIONS

**Adapters
Included:**



COMMERCIAL CONSTRUCTION




Configuration Summary

MX Flip Cover Series Covers:


- Heavy duty die-cast metal construction
- Patented quick-fit keyhole mounting system allows cover installation in under a minute
- Includes gasket and mounting hardware
- Patented Universal Fit Adapter System Technology (U-Fast) comes pre-configured for GFCI
- Premium powder coat finish
- Horizontal or vertical mount
- Lockable tab (fits up to 1/8" shackle)

12 IN 1
CONFIGURATIONS

Adapters Included:



Configurations:
Horizontal or Vertical



MX1050S



MX1050W



MX1050Z



MX1250S, W, Z



COMMERCIAL CONSTRUCTION




Configuration Summary

MX Flip Cover Series Covers:

- Heavy duty die-cast metal construction
- Patented quick-fit keyhole mounting system allows cover installation in under a minute
- Includes gasket and mounting hardware
- Patented Universal Fit Adapter System Technology (U-Fast) comes pre-configured for GFCI
- Premium powder coat finish
- Horizontal or vertical mount
- Lockable tab


14 IN 1
CONFIGURATIONS

**Adapters
Included:**



MX1550S

**Configurations:
Horizontal or Vertical**



COMMERCIAL CONSTRUCTION



Configuration Summary

MX Flip Cover Series Covers:

- Heavy duty die-cast metal construction
- Patented Quick-Fit keyhole mounting system allows cover installation in under a minute
- Includes gasket and mounting hardware
- Patented Universal Fit Adapter System Technology (U-Fast) comes pre-configured for GFCI
- Premium powder coat finish
- Horizontal or vertical mount
- Lockable tab

25 IN 1
CONFIGURATIONS

Adapters
Included:



MX2050S




MX2050WH



MX2050Z

Configurations:
Horizontal or Vertical



COMMERCIAL CONSTRUCTION




Configuration Summary

MX Flip Cover Series Covers:

- Heavy duty die-cast metal construction
- Patented Quick-Fit keyhole mounting system allows cover installation in under a minute
- Includes gasket and mounting hardware
- Patented Universal Fit Adapter System Technology (U-Fast) for 125-in-1 custom device configurations, comes pre-configured for GFCI
- Premium powder coat finish
- Horizontal or vertical mount
- Lockable tab (fits up to 3/16" shackle)

125 IN 1
CONFIGURATIONS

**Adapters
Included:**



GFCI



DUPLEX



SWITCH



3 ROUNDS



MX3050S



COMMERCIAL CONSTRUCTION





Q & A Session

Weatherproof Bell – TayMac Contact Information:

Agus The

WP Bell-TayMac Brand Manager



480.225.9033 (Mobile)



Athe@Hubbell.com

Eugene Hardin II

WP Bell-TayMac Product Manager



480.389.7309 (Mobile)



Ehardin@Hubbell.com




COMMERCIAL CONSTRUCTION



TayMac®

Configuration Summary

Single Gang



Multiple combinations of duplex, GFCI, switch and rounds: 1-3/8", 1-5/8", 1-3/4", 2-1/4", 2-5/8"



COMMERCIAL CONSTRUCTION






8 in 1 CONFIGURATIONS






33 in 1 CONFIGURATIONS



8 in 1 CONFIGURATIONS




16 in 1 CONFIGURATIONS




Multiple combinations of duplex, GFCI, switch, and rounds: 1-1/4", 1-3/8", 1-9/16", 1-5/8", 1-11/16", 1-3/4", 2-1/8", 2-1/4", 2-7/16"



40 in 1 CONFIGURATIONS




Multiple combinations of duplex, GFCI, switch and rounds: 1-3/8", 1-5/8", 1-3/4", 2-1/4", 2-5/8"



Multiple Combinations of GFCI, Duplex, Switch, and Rounds: 1-1/4", 1-3/8", 1-9/16" & 1-5/8", 1-11/16", 2-1/8", 2-1/4", 2-7/16"


8ⁱⁿ1

CONFIGURATIONS




16ⁱⁿ1

CONFIGURATIONS




6ⁱⁿ1

CONFIGURATIONS



55ⁱⁿ1


CONFIGURATIONS




Multiple Combinations of GFCI, Duplex, Switch, and Rounds:
1-1/4" 1-3/8" 1-9/16" & 1-5/8" 1-11/16" 2-1/8" 2-1/4" 2-7/16"

40ⁱⁿ1

CONFIGURATIONS



Multiple combinations of duplex, GFCI, switch and rounds: 1-3/8", 1-5/8", 1-3/4", 2-1/4", 2-5/8"



Multiple combinations of duplex, GFCI, switch, and rounds: 1-1/4", 1-3/8", 1-9/16", 1-5/8", 1-11/16", 1-3/4, 2-1/8", 2-1/4", 2-7/16"