PART#	OLD#	COLOR	"A" WIDTH	"B" LENGTH	"C" DEPTH	INSULATION THICKNESS	HEAT	WEIGHT
HQ010026022E	PHR1	BROWN	10 [254]	26 [660]	22 [559]	1 [25]	60W	25#
HQ010026022N	PHR1	GRANITE	10 [254]	26 [660]	22 [559]	1 [25]	60W	25#
HQ012043027E	PHR2	BROWN	12 [305]	43 [1092]	27 [686]	1 [25]	90W	50#
HQ012043027N	PHR2	GRANITE	12 [305]	43 [1092]	27 [686]	1 [25]	90W	50#





LOCKING DETAIL
2 PLACES



NOTES:

1. INSIDE LENGTH AND WIDTH ARE AT THE BFP CENTERLINE. ALL DIMENSIONS ARE APPROXIMATE.

2. FOR RECOMMENDED SLAB SIZE ADD 9" [229] TO THE ENCLOSURE EXTERIOR.

3. FOR UNHEATED VERSION REPLACE THE PREFIX "H" WITH AN "L". FOR NON-INSULATED VERSION REPLACE PREFIX "H" WITH A "V".

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.

	BY	DATE
DRN	KPC	10/1/09
CHK		
ENG		
APR		
APR		

WEIGHT

SCALE 1 1/2"=1'

SIZE B

HUBBELL®
3621 INDUSTRIAL PARK DR
LENOIR CITY, TN 37771
800-346-3062
www.hot-box.com

LOC LC S

DRAWING DESCRIPTION
HOT BOX®
POLY ROK ENCLOSURES

REV A 9/09

PROJECT NUMBER 091082

SHEET 1 OF 1

DRAWING NUMBER SEE TABLE