M-11866 2

GENERAL INFORMATION			
WIRE LOCATION	WIRE	WIRE COLOR	WIRE SIZE (AWG)
1	LINE (L3)	BLUE	#12
2	ISOLATED GROUND (IG)	GREEN/YELLOW	#12
3	GROUND (G)	GREEN	#12
4	NEUTRAL (N3)	GRAY	#12
5	NEUTRAL (N1)	WHITE	#12
6	LINE (L1)	BLACK	#12
7	LINE (L2)	RED	#12
8	NEUTRAL (N2)	WHITE/BLACK	#12

NOTES:
1. RATING: 20A 120/208 V.
2. ALL DIMENSIONS ARE IN INCHES [mm]
   EXCEPT THE FLEXIBLE METAL CONDUIT LENGTH IN FOOT.



CATALOG NUMBER	DESCRIPTION	"L" LENGTH
CEXT332MFL01	EXT CABLE. 3/3/2 (3 HOTS, 3 NEUTRALS, 2 GROUNDS), MALE TO FEMALE	1-FT.
CEXT332MFL05		5-FT.
CEXT332MFL10		10-FT.
CEXT332MFL15		15-FT.
CEXT332MFL20		20-FT.
CEXT332MFL25		25-FT.
CEXT332MFL30		30-FT.

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
MALE CONNECTOR	THERMOPLASTIC	BLACK
FEMALE CONNECTOR	THERMOPLASTIC	BLACK
CONDUIT	GALV. STEEL	
CLAMP	STEEL	ZINC PLATE
RIVET	STEEL	ZINC PLATE
INSULATOR	THERMOPLASTIC	
WIRE	COPPER	

SYM	REVISIONS	APP	DATE
2	UPDATE THE PRINT PER DCN #21027.		2/5/15
1	NEW RELEASE PER DCN #20674		5/8/14

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
MODULAR WIRING
EXTENDER CABLE 3/3/2
MALE TO FEMALE

TOLERANCES UNLESS OTHERWISE SPECIFIED
.XX = ±.01
.XXX = ±.005
ANGLES = ±2°

WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
SHELTON, CT

DR. BY DMP	APP. BY
TR. BY	SCALE NONE
CHK. BY	DATE 2/3/11

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE ☐ NON-REPAIRABLE ☒

B

M-11866 2

CODE 74545