



LiteBox® Edge-Lit Remote Mount, Switchable CCT

The LITEBOX® Edge-Lit low profile surface mount downlighting family affordably combines Edge-Lit technology and contemporary appearance with ease of installation and functional versatility. The Remote Mount, Switchable CCT models allow four CCT choices in one, 90+ CRI with a remote driver J-Box included.



Click RDC/QS Guide for full details.

LBSES-RM

STOCK

Part #	Catalog #	UPC Code	Description	CA 03	GA 27	IL 06	NJ 12	Lbs. each	Ctn. Qty.	ENERGY STAR®
BG1626000	LBSES-4RD-RM-CS9-WH	840141400907	LED, 4" Surface Downlight, Round, Remote Mt, 750 LMS, 90+ CRI, 27/30/35/40K, 0-10V/Triac/ELV Dimming Driver, 120-277V, White		●			0.62	12	●
BG1626100	LBSES-6RD-RM-CS9-WH	840141400914	LED, 6" Surface Downlight, Round, Remote Mt, 1100 LMS, 90+ CRI, 27/30/35/40K, 0-10V/Triac/ELV Dimming Driver, 120-277V, White		●			0.82	12	●
BG1626200	LBSES-8RD-RM-CS9-WH	840141400921	LED, 8" Surface Downlight, Round, Remote Mt, 1750 LMS, 90+ CRI, 27/30/35/40K, 0-10V/Triac/ELV Dimming Driver, 120-277V, White		●			1.10	12	●
BG1626900	LBSES-4SQD-RM-CS9-WH	840141400990	LED, 4" Surface Downlight, Square, Remote Mt, 750 LMS, 90+ CRI, 27/30/35/40K, 0-10V/Triac/ELV Dimming Driver, 120-277V, White		●			0.72	12	●
BG1627000	LBSES-6SQD-RM-CS9-WH	840141401003	LED, 6" Surface Downlight, Square, Remote Mt, 1100 LMS, 90+ CRI, 27/30/35/40K, 0-10V/Triac/ELV Dimming Driver, 120-277V, White		●			0.99	12	●
BG1627100	LBSES-8SQD-RM-CS9-WH	840141401010	LED, 8" Surface Downlight, Square, Remote Mt, 1750 LMS, 90+ CRI, 27/30/35/40K, 0-10V/Triac/ELV Dimming Driver, 120-277V, White		●			1.33	12	●



LiteBox® Edge-Lit Accessories, Decorative Color Trim Rings

The LITEBOX® Edge-Lit low profile surface mount downlighting family affordably combines Edge-Lit technology and contemporary appearance with ease of installation and functional versatility. Decorative color trim ring accessories are non-conductive and fit over standard model exterior.

Part #	Catalog #	UPC Code	Description	CA 03	GA 27	IL 06	NJ 12	Lbs. each	Ctn. Qty.	ENERGY STAR®
BG1628300	LBSE-4RD-T-WH	840141401089	Accessory, Decorative Color Trim, 4" Round, White		●			0.07	12	
BG1628900	LBSE-4RD-T-BL	840141401140	Accessory, Decorative Color Trim, 4" Round, Black		●			0.07	12	
BG1630100	LBSE-4RD-T-SVR	840141401263	Accessory, Decorative Color Trim, 4" Round, Silver		●			0.07	12	
BG1629500	LBSE-4RD-T-BBZ	840141401201	Accessory, Decorative Color Trim, 4" Round, Brushed Oil Rubbed Bronze		●			0.07	12	
BG1628400	LBSE-6RD-T-WH	840141401096	Accessory, Decorative Color Trim, 6" Round, White		●			0.11	12	
BG1629000	LBSE-6RD-T-BL	840141401157	Accessory, Decorative Color Trim, 6" Round, Black		●			0.11	12	
BG1630200	LBSE-6RD-T-SVR	840141401270	Accessory, Decorative Color Trim, 6" Round, Silver		●			0.11	12	
BG1629600	LBSE-6RD-T-BBZ	840141401218	Accessory, Decorative Color Trim, 6" Round, Brushed Oil Rubbed Bronze		●			0.11	12	
BG1628500	LBSE-8RD-T-WH	840141401102	Accessory, Decorative Color Trim, 8" Round, White		●			0.13	12	
BG1629100	LBSE-8RD-T-BL	840141401164	Accessory, Decorative Color Trim, 8" Round, Black		●			0.13	12	
BG1630300	LBSE-8RD-T-SVR	840141401287	Accessory, Decorative Color Trim, 8" Round, Silver		●			0.13	12	
BG1629700	LBSE-8RD-T-BBZ	840141401225	Accessory, Decorative Color Trim, 8" Round, Brushed Oil Rubbed Bronze		●			0.13	12	
BG1628600	LBSE-4SQD-T-WH	840141401119	Accessory, Decorative Color Trim, 4" Square, White		●			0.07	12	
BG1629200	LBSE-4SQD-T-BL	840141401171	Accessory, Decorative Color Trim, 4" Square, Black		●			0.07	12	
BG1630400	LBSE-4SQD-T-SVR	840141401294	Accessory, Decorative Color Trim, 4" Square, Silver		●			0.07	12	
BG1629800	LBSE-4SQD-T-BBZ	840141401232	Accessory, Decorative Color Trim, 4" Square, Brushed Oil Rubbed Bronze		●			0.07	12	
BG1628700	LBSE-6SQD-T-WH	840141401126	Accessory, Decorative Color Trim, 6" Square, White		●			0.11	12	
BG1629300	LBSE-6SQD-T-BL	840141401188	Accessory, Decorative Color Trim, 6" Square, Black		●			0.11	12	
BG1630500	LBSE-6SQD-T-SVR	840141401300	Accessory, Decorative Color Trim, 6" Square, Silver		●			0.11	12	
BG1629900	LBSE-6SQD-T-BBZ	840141401249	Accessory, Decorative Color Trim, 6" Square, Brushed Oil Rubbed Bronze		●			0.11	12	



(continued)

LiteBox® Edge-Lit Accessories, Decorative Color Trim Rings

Part #	Catalog #	UPC Code	Description	CA 03	GA 27	IL 06	NJ 12	Lbs. each	Ctn. Qty.	ENERGY STAR®
BG1628800	LBSE-8SQD-T-WH	840141401133	Accessory, Decorative Color Trim, 8" Square, White		●			0.13	12	
BG1629400	LBSE-8SQD-T-BL	840141401195	Accessory, Decorative Color Trim, 8" Square, Black		●			0.13	12	
BG1630600	LBSE-8SQD-T-SVR	840141401317	Accessory, Decorative Color Trim, 8" Square, Silver		●			0.13	12	
BG1630000	LBSE-8SQD-T-BBZ	840141401256	Accessory, Decorative Color Trim, 8" Square, Brushed Oil Rubbed Bronze		●			0.13	12	



LiteBox® Edge-Lit Accessories, EM Emergency Battery Pack

The LITEBOX® Edge-Lit low profile surface mount downlighting family affordably combines Edge-Lit technology and contemporary appearance with ease of installation and functional versatility. EM accessories are UL 924 compliant and provide 90 minutes of emergency lighting and can be field installed onto Remote Mount models.

Part #	Catalog #	UPC Code	Description	CA 03	GA 27	IL 06	NJ 12	Lbs. each	Ctn. Qty.	ENERGY STAR®
BG1627200	LBSE-4RD-EM-WH	840141401027	Accessory, 4" Round, EM Emergency Battery Pack with integral test switch and indicator light, White		●			0.95	12	
BG1627300	LBSE-6RD-EM-WH	840141401034	Accessory, 6" Round, EM Emergency Battery Pack with integral test switch and indicator light, White		●			1.01	12	
BG1627400	LBSE-8RD-EM-WH	840141401041	Accessory, 8" Round, EM Emergency Battery Pack with integral test switch and indicator light, White		●			1.10	12	
BG1627600	LBSE-4SQD-EM-WH	840141401058	Accessory, 4" Square, EM Emergency Battery Pack with integral test switch and indicator light, White		●			0.95	12	
BG1627700	LBSE-6SQD-EM-WH	840141401065	Accessory, 6" Square, EM Emergency Battery Pack with integral test switch and indicator light, White		●			1.01	12	
BG1627800	LBSE-8SQD-EM-WH	840141401072	Accessory, 8" Square, EM Emergency Battery Pack with integral test switch and indicator light, White		●			1.10	12	
BG1632200	LBSE-4RD-EM-BL	840141401621	Accessory, 4" Round, EM Emergency Battery Pack with integral test switch and indicator light, Black		●			0.95	12	
BG1632300	LBSE-6RD-EM-BL	840141401638	Accessory, 6" Round, EM Emergency Battery Pack with integral test switch and indicator light, Black		●			1.01	12	
BG1632400	LBSE-8RD-EM-BL	840141401645	Accessory, 8" Round, EM Emergency Battery Pack with integral test switch and indicator light, Black		●			1.10	12	
BG1632600	LBSE-4SQD-EM-BL	840141401669	Accessory, 4" Square, EM Emergency Battery Pack with integral test switch and indicator light, Black		●			0.95	12	
BG1632700	LBSE-6SQD-EM-BL	840141401676	Accessory, 6" Square, EM Emergency Battery Pack with integral test switch and indicator light, Black		●			1.01	12	
BG1632800	LBSE-8SQD-EM-BL	840141401683	Accessory, 8" Square, EM Emergency Battery Pack with integral test switch and indicator light, Black		●			1.10	12	



LiteBox® Edge-Lit Accessories, Extension Cables

The LITEBOX® Edge-Lit low profile surface mount downlighting family affordably combines Edge-Lit technology and contemporary appearance with ease of installation and functional versatility. EM accessories are UL 924 compliant and provide 90 minutes of emergency lighting and can be field installed onto Remote Mount models.

Part #	Catalog #	UPC Code	Description	CA 03	GA 27	IL 06	NJ 12	Lbs. each	Ctn. Qty.	ENERGY STAR®
BG1630800	LBSES-C-12	840141401348	Accessory, Extension Cable for LBSE/LBSES Remote Mount, 12"		●			0.07	12	
BG1631000	LBSES-C-24	840141401362	Accessory, Extension Cable for LBSE/LBSES Remote Mount, 24"		●			0.09	12	
BG1632900	LBSES-C-24-EM	840141401690	Accessory, Extension Cable for EM, 24"		●			0.09	12	