M-10106 | 1





NOTES:

PRODUCT SPECIFICATIONS:

QUICKWIRE TERMINALS NO 18 WIRE
FOR HIGH OUTPUT LAMPS
660W-1000V
SLIDE ON BASE
UL LISTED

CODE 74545

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
CONTACTS	BRASS	
HOUSING	PLASTIC	

SYM	REVISIONS	APP	DATE
1	RELEASED TO PRODUCTION PER DCN #13353 AMZ	RDK	08/18/06

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
PEDESTAL TYPE HIGH OUTPUT LAMP, RECESSED DOUBLE CONTACT PLUNGER/SLIDE BASE

TOLERANCES UNLESS OTHERWISE SPECIFIED
FRACTIONS ±1/84
DECIMALS ±.005
ANGLES ±2°

HUBBELL WIRING SYSTEMS
BRIDGEPORT, CT

DR. BY AMZ | APP. BY RDK
TR. BY | SCALE NONE
CHK'D BY RDK | DATE 05/01/06

DIMENSION SHEET FOR CAT. NO. RL305

REPAIRABLE ☐ NON-REPAIRABLE ☒

B

M-10106

1