



LiteFrame® 2.0 4" Round Fixture Modules, Trims and Optional Housings

The LiteFrame® 2.0 family provides a balance between product solutions and performance while keeping it simple to select and use.



Click RDC/QS Guide for full details.

LFR-4R

STOCK

Fixture Module		
Part #	Catalog #	Description
BG1647200	LFR-4RD-M-10L30K8-MD-DM1	LED, 4" Downlight Module, Direct Install, Round, 1000lm, 80+ CRI, 3000K, Medium, 0-10V 1% Dimming, 120-277V
BG1647300	LFR-4RD-M-15L30K8-MD-DM1	LED, 4" Downlight Module, Direct Install, Round, 1500lm, 80+ CRI, 3000K, Medium, 0-10V 1% Dimming, 120-277V
BG1647400	LFR-4RD-M-20L30K8-MD-DM1	LED, 4" Downlight Module, Direct Install, Round, 2000lm, 80+ CRI, 3000K, Medium, 0-10V 1% Dimming, 120-277V
BG1647500	LFR-4RD-M-10L35K8-MD-DM1	LED, 4" Downlight Module, Direct Install, Round, 1000lm, 80+ CRI, 3500K, Medium, 0-10V 1% Dimming, 120-277V
BG1647600	LFR-4RD-M-15L35K8-MD-DM1	LED, 4" Downlight Module, Direct Install, Round, 1500lm, 80+ CRI, 3500K, Medium, 0-10V 1% Dimming, 120-277V
BG1647700	LFR-4RD-M-20L35K8-MD-DM1	LED, 4" Downlight Module, Direct Install, Round, 2000lm, 80+ CRI, 3500K, Medium, 0-10V 1% Dimming, 120-277V
BG1647800	LFR-4RD-M-10L40K8-MD-DM1	LED, 4" Downlight Module, Direct Install, Round, 1000lm, 80+ CRI, 4000K, Medium, 0-10V 1% Dimming, 120-277V
BG1647900	LFR-4RD-M-15L40K8-MD-DM1	LED, 4" Downlight Module, Direct Install, Round, 1500lm, 80+ CRI, 4000K, Medium, 0-10V 1% Dimming, 120-277V
BG1648000	LFR-4RD-M-20L40K8-MD-DM1	LED, 4" Downlight Module, Direct Install, Round, 2000lm, 80+ CRI, 4000K, Medium, 0-10V 1% Dimming, 120-277V
BG1648100	LFR-4RD-M-10L30K8-XW-DM1	LED, 4" Downlight Module, Direct Install, Round, 1000lm, 80+ CRI, 3000K, Extra Wide, 0-10V 1% Dimming, 120-277V
BG1648200	LFR-4RD-M-15L30K8-XW-DM1	LED, 4" Downlight Module, Direct Install, Round, 1500lm, 80+ CRI, 3000K, Extra Wide, 0-10V 1% Dimming, 120-277V
BG1648300	LFR-4RD-M-20L30K8-XW-DM1	LED, 4" Downlight Module, Direct Install, Round, 2000lm, 80+ CRI, 3000K, Extra Wide, 0-10V 1% Dimming, 120-277V
BG1648400	LFR-4RD-M-10L35K8-XW-DM1	LED, 4" Downlight Module, Direct Install, Round, 1000lm, 80+ CRI, 3500K, Extra Wide, 0-10V 1% Dimming, 120-277V
BG1648500	LFR-4RD-M-15L35K8-XW-DM1	LED, 4" Downlight Module, Direct Install, Round, 1500lm, 80+ CRI, 3500K, Extra Wide, 0-10V 1% Dimming, 120-277V
BG1648600	LFR-4RD-M-20L35K8-XW-DM1	LED, 4" Downlight Module, Direct Install, Round, 2000lm, 80+ CRI, 3500K, Extra Wide, 0-10V 1% Dimming, 120-277V
BG1648700	LFR-4RD-M-10L40K8-XW-DM1	LED, 4" Downlight Module, Direct Install, Round, 1000lm, 80+ CRI, 4000K, Extra Wide, 0-10V 1% Dimming, 120-277V
BG1648800	LFR-4RD-M-15L40K8-XW-DM1	LED, 4" Downlight Module, Direct Install, Round, 1000lm, 80+ CRI, 4000K, Extra Wide, 0-10V 1% Dimming, 120-277V
BG1648900	LFR-4RD-M-20L40K8-XW-DM1	LED, 4" Downlight Module, Direct Install, Round, 2000lm, 80+ CRI, 4000K, Extra Wide, 0-10V 1% Dimming, 120-277V

Trims		
Part #	Catalog #	Description
BG1650800	LFR-4RD-T-S	LED, 4" Downlight Trim, Round, NR/MD/WD/XW, Specular Clear Reflector
BG1650900	LFR-4RD-T-SS	LED, 4" Downlight Trim, Round, NR/MD/WD/XW Semi-Specular Clear Reflector
BG1651200	LFR-4RD-T-S-CL	LED, 4" Downlight Trim, Round, NR/MD/WD/XW, Specular Clear Reflector, Clear Lens
BG1651300	LFR-4RD-T-SS-CL	LED, 4" Downlight Trim, Round, NR/MD/WD/XW Semi-Specular Clear Reflector, Clear Lens
BG1651000	LFR-4RD-T-VNR-S	LED, 4" Downlight Trim, Round, Very Narrow, Specular Clear Reflector
BG1651100	LFR-4RD-T-VNR-SS	LED, 4" Downlight Trim, Round, Very Narrow, Semi-Specular Clear Reflector
BG1651400	LFR-4RD-T-VNR-S-CL	LED, 4" Downlight Trim, Round, Very Narrow, Specular Clear Reflector, Clear Lens
BG1651500	LFR-4RD-T-VNR-SS-CL	LED, 4" Downlight Trim, Round, Very Narrow, Semi-Specular Clear Reflector, Clear Lens
BG1652400	LFR-4RDS-T-S	LED, 4" Shallow Downlight Trim, Round, Specular Clear Reflector
BG1652500	LFR-4RDS-T-SS	LED, 4" Shallow Downlight Trim, Round, Semi-Specular Clear Reflector
BG1652800	LFR-4RW-T-LWW-S	LED, 4" Lensed Wall Wash Trim, Round, Specular Clear Reflector
BG1652900	LFR-4RW-T-LWW-SS	LED, 4" Lensed Wall Wash Trim, Round, Semi-Specular Clear Reflector
BG1653200	LFR-4RA-T-S	LED, 4" Adjustable Trim, Round, Cut Cone, Specular Clear Reflector
BG1653300	LFR-4RA-T-SS	LED, 4" Adjustable Trim, Round, Cut Cone, Specular Clear Reflector

Optional Housings		
Part #	Catalog #	Description
BG1647000	LFR-4RD-H	Accessory, 4" Housing Frame, New Construction, Round, Non-IC