Medium Voltage Transformer - Three Phase, 2400Δ - 600ΔV, 112.5kVA

By Acme Electric
Catalog # WI112K14

*Representative Image

Medium Voltage Transformer - Three Phase, 2400Δ - 600ΔV, 112.5kVA

General

Catalog Number	WI112K14
Construction	Ventilated
Mounting Type	Floor
Primary Voltage	2400Δ
Product Category	Medium Voltage Transformer
Secondary Voltage	600D V
UPC	047503098264
Winding Material	AL
kVA	112.5

Dimensions

Depth	21.8 in
Height	40.5 in
Weight	940 lb
Width	36.5 in

Electrical Ratings

Efficiency	98.52%
Frequency Rating	60 Hz
Primary Voltage	2400D V

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

Product Assets

Brochures - Medium voltage dry-type transformers
Catalogs - Acme Electric Catalog - Section 2 - Medium Voltage Transformers
Customer Notices - Prop65_Cancer
SDS - HCC SDS
Specifications - WI112K14
Terms and Conditions - HCC Terms & Conditions

©2024 Hubbell Incorporated. All rights reserved