HUBBELL
Power Systems

Deadend, Straight line, Spring Loaded, Side Opening, #4 (7 STR) - 350 (19 STR) AL, #4 (6/1) - 336.4 (18/1) ACSR

By ANDERSON
Catalog # ADEZ70N



*Representative Image

Deadend, Straight line, Spring Loaded, Side Opening, #4 (7 STR) - 350 (19 STR) AL, #4 (6/1) - 336.4 (18/1) ACSR, Conductor Range 0.31 - 0.70 in, Fitting: None.

Features

Captive hardware to prevent disassemblyPivoting spring loaded keeper for easy conductor insertionAdd "S" for Socket or "C" for Clevis Fitting Options

General

Catalog Number	ADEZ70N
Fitting Type	None
Material	Aluminum Alloy
Material - Body	356 T6 Aluminum Alloy
Material - Hardware	Galvanized Steel
Material - Keeper	356 T6 Aluminum Alloy
Material - Pin (Cotter)	Stainless Steel
Material - Socket and Clevis	Ductle Iron, Galvinized
Material - Spring (on Eyestem)	Stainless Steel
Product Category	Straight Line
Strength Rating - Ultimate	9000 lb
Body	
Style	ADEZ
Type	Bolted
U-Bolts	2 in
UPC	096359612612

Dimensions

Diameter - Bolt	0.375 in
Diameter - Pin	0.625 in
Length	8.25 in
Weight	1.6 lb
Width	0.937 in

Conductor Related

Conductor Diameter - Maximum	0.7
Conductor Diameter - Minimum	0.31
Conductor Diameter Range	0.31 - 0.7
Conductor Type	• AAC • ACSR • AAAC

Logistics

Pallet Quantity	800

Product Assets

Catalogs - Distribution Connectors
Installation Manuals - ADEZ Series Aluminum Deadend
Recommended Installation Instructions
Literature - Ropes Course Industry Letter (April 2021)
Literature - Deadends For Overhead Connections
Sales Drawings - AL, DE Easy On Clamp FF # Adez-See Table
Specifications - ADEZ70N

©2024 Hubbell Incorporated. All rights reserved