1PLD7503HD, UV Rated Black, 2-sided, 3-port, #2 AWG-750 kcmil

By Burndy
Catalog # 1PLD7503HD

750-2 TWO-SIDED 3 PORT HD BLK.

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

General

Catalog Number	1PLD7503HD
Connector Type	Multi Tap
Hex Key	3/8 in
Installation Torque Recommended in-lb	500 in-lb
Material	Aluminum
Number Of Ports	3
Temperature Rating	-40°C to 135°C
Trade Name	UNITAP™
UPC	621945480735

Dimensions

Dimension - L Length Overall mm	101.6
Dimension - Length Overall inch	4

Electrical Ratings

Voltage - Maximum	600 V

Conductor Related

Conductor Size	2 AWG-750 KCMIL

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1

Product Assets

Catalogs - BURNDY Master Catalog - Section A - Mechanical
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog
Sales Drawings - 50079815
Specifications - 1PLD7503HD

©2024 Hubbell Incorporated. All rights reserved