BB067L17G9 Flexible Copper Braid

By Burndy
Catalog # BB067L17G9

Tinned copper braid 17″x0.83″x0.17.

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	BB067L17G9
Connector Type	Braid
Material	Copper
Material - Ferrules	Copper
UPC	781810566824
UPC 12 Digit	7818105668244

Dimensions

Dimension - L Length Overall mm	432
Dimension - Length Overall inch	17
Dimension - Width inch	0.83
Dimension - Width mm	21 mm
Length	17 in

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1

Product Assets

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Interactive Catalog - BURNDY Full-Line Digital Catalog
Specifications - BB067L17G9

©2024 Hubbell Incorporated. All rights reserved