BB100L26D59G21TN Flexible Copper Braid

By Burndy
Catalog # BB100L26D59G21TN

Tin Plated Copper Braid 25.59 inches long.

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	BB100L26D59G21TN
Connector Type	Braid
Material	Copper
UPC	621945443563
UPC 12 Digit	6219454435633

Dimensions

Dimension - L Length Overall mm	650 mm
Dimension - Length Overall inch	25.59 in
Length	26.59 in

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	2625

Product Assets

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog
Sales Drawings - 50002016
Specifications - BB100L26D59G21TN

©2024 Hubbell Incorporated. All rights reserved