BB100L7D08G26 Flexible Copper Braid

By Burndy
Catalog # BB100L7D08G26

Tin Plated Copper Braid 7.08 inches long.

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	BB100L7D08G26
Connector Type	Braid
Material	Copper
Plated	Y
UPC	781810649732
UPC 12 Digit	7818106497322

Dimensions

Dimension - L Length Overall mm	180 mm
Dimension - Length Overall inch	7.08 in
Dimension - Pad Width inch	1.3 in
Length	7.08 in

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1

Product Assets

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Interactive Catalog - BURNDY Full-Line Digital Catalog
Sales Drawings - 50026140
Specifications - BB100L7D08G26

©2024 Hubbell Incorporated. All rights reserved