CT18075FLC, Cable Tie, .75″ Max Bundle, 18 Lb Tensile, Natural, Identification

By Burndy
Catalog # CT18075FLC



Nylon cable ties, Tensile strength-18 Lbs, Color- Natural, 04.10″L, 0.10″W, 0.75″ Bundle Dia.

Features

Identification

General

Catalog Number	CT18075FLC
Color	Natural
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	18 lb
Trade Name	UNIRAP™
UPC	781810335376

Dimensions

Dimension - Bundle Diameter Max inch	0.75
Dimension - L Length Overall mm	104 mm
Dimension - Length Overall inch	4.10 in
Dimension - Marking Pad Size inch	0.36 X 0.81
Dimension - Width inch	0.10 in
Dimension - Width mm	2.5 mm

Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - UV Rated	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	20000
Minimum Pack Quantity	1000

Product Assets

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Catalogs - BURNDY Master Catalog - Section G - Wire Management
Interactive Catalog - BURNDY Full-Line Digital Catalog
Product Cross Section Image(s) - BUR_CT_ID_UNIRAP_CABLE_TIE_LineArt
Sales Drawings - 50004698
Specifications - CT18075FLC

©2024 Hubbell Incorporated. All rights reserved