GAR3908, Mechanical Grounding Connector, Conductor to Water Pipe

By Burndy
Catalog # GAR3908

Mechanical Grounding Connector, Conductor to Water Pipe, 4-4/0 AWG, 10" Pipe, 3/8" Stud. Galvanized Steel Hardware.

Features

- Cable clamp swivels at 90°, permits parallel grounding of one pipe on a 90° cable run for grounding several parallel pipes
- One-wrench installation for simplified installation
- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- Provides quality assurance to recognized industry NEC standards from an independent part

Application

For Connecting A Small To Medium Range Copper Ground Conductor To Water Pipe As Well As Structural And Reinforcing Rod Shapes, Direct Burial Cables

General

Catalog Number	GAR3908
EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	200 lb-in
Material	Copper Alloy
Material - Hardware	Galvanized Steel
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GAR3902
U Bolt Type	1029G
UPC	781810234075
UPC 12 Digit	7818102340755

Dimensions

Dimension - B Length inch	1.75 in
Dimension - Height inch	12.00 in
Dimension - Height mm	304.8 mm
Dimension - Length Overall inch	1.75 in
Dimension - Outside Diameter inch	10.75 in
Dimension - Width inch	12.75 in
Dimension - Width mm	324 mm

Conductor Related

Conductor - Copper Solid Size Range	4 AWG - 4/0 AWG
Conductor - Copper Str Size	4;3;2;1;1/0;2/0;3/0;4/0
Conductor - Copper Str Size Range	4 AWG - 4/0 AWG
Conductor - Copper Tube Std Size	10
Conductor - Copper Tube Std Size Range	10
Conductor - Pipe or Round Tube Size	10 in

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1

Product Assets

3D Models - GAR3908_MODEL-STEP
3D Models - GAR3908_MODEL-PDF
3D Models - GAR3908_MODEL-IGES
Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog
Product Cross Section Image(s) - BUR_GAR3900_Lineart
Sales Drawings - SD206499-01
Specifications - GAR3908

©2024 Hubbell Incorporated. All rights reserved