GB39, Mechanical Grounding Connector, Cable to Bar

By Burndy
Catalog # GB39

Mechanical Grounding Connector, Cable to 1/4" Thick Bar, 550 kcmil - 750 kcmil, 5/8" Stud, 2-3/4 IN Width.

General

Catalog Number	GB39
Installation Torque Recommended in-lb	660 lb-in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Oval Shank Bolt
Plated	N
Plating Type	Unplated
UPC	781810231357
UPC 12 Digit	7818102313577

Dimensions

Dimension - B Length inch	1.75 in
Dimension - Height inch	3.28 in
Dimension - Height mm	83.3 mm
Dimension - L Length Overall mm	45 mm
Dimension - Length Overall inch	1.75 in
Dimension - Width fraction	2-3/4 in
Dimension - Width inch	2.75 in

Conductor Related

Conductor - Copper Solid Size Range	550 KCMIL - 750 KCMIL
Conductor - Copper Str Size	550 kcmil;600 kcmil;700 kcmil;750 kcmil
Conductor - Copper Str Size Range	550 kcmil - 750 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1

Product Assets

3D Models - GB39_MODEL-STEP
3D Models - GB39_MODEL-IGES
3D Models - GB39_MODEL-PDF
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog
Product Cross Section Image(s) - BUR_GB_Lineart
Sales Drawings - sc091657-01
Specifications - GB39

©2024 Hubbell Incorporated. All rights reserved