



Power and  
Style  
Where You  
Need It

Stylish Solutions  
for Ceiling to  
Floor Delivery



### Typical Applications

- Retail Checkouts
- Open Offices
- Laboratories
- Workshops



- ✓ Power and data communication delivery from the ceiling to the floor
- ✓ Sturdy lightweight extruded aluminum construction
- ✓ Varied configurations for a range of applications

Bryant's family of multi-service service pole products provide electrical and telecommunications wiring needs wherever they are needed. Designed for ease of installation, Bryant service poles come factory wired with Bryant decorator receptacles in a variety of device configurations. All Bryant service poles are fitted with an internal divider to separate power and low voltage wiring.

Service poles are used in many commercial applications as an alternative to floor boxes. These products are designed for permanent or semi-permanent installation and are built to last. They are made from tough and attractive aluminum and are equipped with a scuff boot to prevent damage. Bryant service poles can deliver standard electrical needs as well as provide surge suppression and isolated ground solutions. A blank pole is offered which does not have devices or wiring to meet custom configuration needs.

## Ordering Information



### Standard Duplex

- Multi-service, two 20A 125V decorator duplex receptacles, one circuit

Color	10' 2" (3.10m)	12' 2" (3.71m)	15' 2" (4.62m)
Gray	<b>BRYPP10A</b>	<b>BRYPP12A</b>	<b>BRYPP15A</b>
Ivory	<b>BRYPP10AI</b>	<b>BRYPP12AI</b>	<b>BRYPP15AI</b>
Clear Anodized Aluminum	<b>BRYPP10AAL</b>	<b>BRYPP12AAL</b>	<b>BRYPP15AAL</b>

### Isolated Ground

- Multi-service, one orange isolated ground 20A 125V decorator duplex receptacle, one 20A 125V decorator duplex receptacle, two circuits

Color	10' 2" (3.10m)
Gray	<b>BRYPP10IGA</b>
Ivory	<b>BRYPP10IGAI</b>
Clear Anodized Aluminum	<b>BRYPP10IGAL</b>

### Isolated Ground and Surge Suppression

- Multi-service, two orange isolated ground 20A 125V decorator duplex receptacles, one isolated ground surge suppression 20A 125V duplex receptacle, one circuit

Description	10' 2" (3.10m)
Gray	<b>BRYPP10SA</b>
Ivory	<b>BRYPP10SAI</b>

### Blank

- Multi-service, blank pole, divider, four decorator device knockouts

Description	10' 2" (3.10m)	12' 2" (3.71m)	15' 2" (4.62m)
Gray	<b>BRYPP0A</b>	<b>BRYPP012A</b>	<b>BRYPP015A</b>
Ivory	<b>BRYPP0AI</b>	<b>BRYPP012AI</b>	<b>BRYPP015AI</b>
Clear Anodized Aluminum	<b>BRYPP0AAL</b>	<b>BRYPP012AAL</b>	<b>BRYPP015AAL</b>

### Accessories

Description	15' 2" (4.62m)
Adjustable T-bar assembly for mounting poles in the middle of ceiling tile.	<b>BRYATB*</b>
Replacement service pole trim kit (office white).	<b>BRYPPTRIM1*</b>

Note: \*Not UL listed.



**BRYPP10A**



**BRYPP10IGA**



**BRYPP10SA**




**BRYPP0A**




**BRYATB**




**BRYPPTRIM1**



**BRYPP10, BRYPP12, BRYPP15, BRYPP10IG**



**BRYPP10S**



**BRYPP0, BRYPP012, BRYPP015**