

Hubbell Industrial Controls, Inc.

Jockey Pump Controllers

For Electric Pressure Maintenance Pumps

Price List 6420P • July 2010, New

LX-600
Version "C"

Replacement Parts List				
Description	Voltage	Size	Part No.	List Price
Control Transformer	208-230 380-460	50 VA	HC57511-354	\$60
Control Transformer	380-575	50 VA	HC57511-404	\$195
Control Transformer Fuse Primary	1/2 amp 60 v TD		HCFU2696	\$16
Control Transformer Fuse Secondary	1 amp 250 v MDL-1		HC57361-726	\$4

Pressure Switch	15-290 psi	HC57501-050	\$150
Pressure Switch	12-464 psi	HC57501-007	\$195
Toggle Switch MAN/OFF/AUTO	DPDT	HCSW3531	\$10
Run Period Timer		HC31658-111	\$129
Pilot Light Red	125 vac	HC57470-155	\$12
Pilot Light Red	208-240 vac	HC57470-160	\$12
Pilot Light Green	125 vac	HC57740-158	\$12
Pilot Light Green	208-240 vac	HC57470-163	\$12

Description	Voltage	HP	Size	Coil Voltage	Part No.	List Price
Contactor	200-240	1/3-2	9 A	240 v	HC57300-872	\$40
	380-415	13-3	9 A	120 v	HC57300-871	\$40
	440-480	1/3-5				
	575-600	1/3-7-1/2				
	200-208	3-5	23 A	240 v	HC5730-712	\$60
	220-240	3-7 1/2				
	380-415	5-10	23 A	120 v	HC57300-711	\$65
	440-480	7 1/2-15				
	575-600	5-15				
	200-208	7-1/2-10	43 A	240 v	HC57300-722	\$135
	220-240	10-15				
	380-415	15-20	43 A	120 v	HC57300-721	\$125
	440-480	20-25				
	575-600	20-25				

Prices subject to change without notice.



Motor Protection Circuit Breaker w/ Overload Adjust							
Horse Power @					Adjust Range (Amp)	Part No.	List Price
200/208 V	220/240 V	380/415 V	440/480 V	575/600 V			
				1/3	0.40 - 0.63	HC57504-785	\$135
		1/3	1/3	1/2	0.63 - 1.0	HC57504-786	\$135
1/3	1/3	1/2	1/2	3/4 - 1	1.0 - 1.6	HC57504-787	\$135
		3/4	3/4 - 1	1 1/2	1.6 - 2.5	HC57504-788	\$135
1/2 - 3/4	1/2 - 3/4	1 - 1 1/2	1 1/2 - 2	2	2.5 - 4.0	HC57504-789	\$135
1	1	2	3	3	4.0 - 6.3	HC57504-790	\$135
1 1/2 - 2	1 1/2 - 2	3	5	5 - 7 1/2	6.3 - 10.0	HC57504-791	\$150
3	3	5	7 1/2 - 10	10	10.0 - 16.0	HC57504-792	\$150
5	5	7 1/2		15	14.5 - 20.0	HC57504-793	\$170
	7 1/2	10	15	20	18.0 - 25.0	HC57504-794	\$170
7 1/2	10	15	20	25	23.0 - 32.0	HC57504-795	\$290
10	15	20	25		32.0 - 45.0	HC57504-796	\$335

Prices subject to change without notice.



Hubbell Industrial Controls, Inc.
a subsidiary of Hubbell Incorporated
 4301 Cheyenne Drive, Archdale, NC 27263
 Phone (336) 434-2800 | Fax (336) 434-2803
www.hubbell-icd.com
sales@hubbell-icd.com