

B-91125-004

VOLTAGE	HORSEPOWER	LX-450 ATS CONTIN. RATING	GE CAT. NUMBER	SIEMENS CAT. NUMBER	SHORT CIRCUIT RATING (KA)
200-208	15	100A	SELA36A10100	HHED63B125	42
	20	100A	SELA36A10100	HHED63B125	42
	25	100A	SELA36A10100	HHED63B125	42
	30	200A	SELA36A10150	HFD63B250	50
	40	200A	SELA36A10150	HFD63B250	50
	50	200A	SFLA36A10250	HFD63B250	50
	60	200A	SFLA36A10250	HFD63B250	50
	75	260A	SGLA36A10400	HJD63B400	65
	100	400A	SGLA36A10400	HJD63B400	65
	125	400A	SGLA36A10400	HJD63B400	65
	150	600A	SGLA36A10600	HLD63B600	100
200	600A	SGLA36A10600	HLD63B600	100	
220-240	15	100A	SELA36A10100	HHED63B125	42
	20	100A	SELA36A10100	HHED63B125	42
	25	100A	SELA36A10100	HHED63B125	42
	30	100A	SELA36A10100	HHED63B125	42
	40	200A	SELA36A10150	HFD63B250	50
	50	200A	SELA36A10150	HFD63B250	50
	60	200A	SFLA36A10250	HFD63B250	50
	75	260A	SFLA36A10250	HFD63B250	65
	100	400A	SGLA36A10400	HJD63B400	65
	125	400A	SGLA36A10400	HJD63B400	65
	150	600A	SGLA36A10600	HLD63B600	100
200	600A	SGLA36A10600	HLD63B600	100	
380-416	15	100A	SELA36A10100	HHED63B125	42
	20	100A	SELA36A10100	HHED63B125	42
	25	100A	SELA36A10100	HHED63B125	42
	30	100A	SELA36A10100	HHED63B125	42
	40	100A	SELA36A10100	HHED63B125	42
	50	100A	SELA36A10100	HHED63B125	42
	60	200A	SELA36A10150	HFD63B250	50
	75	200A	SELA36A10150	HFD63B250	50
	100	200A	SFLA36A10250	HFD63B250	50
	125	260A	SFLA36A10250	HFD63B250	65
	150	400A	SGLA36A10400	HJD63B400	65
	200	400A	SGLA36A10400	HJD63B400	65
	250	600A	SGLA36A10400	HJD63B400	100
	300	600A	SGLA36A10600	HLD63B600	100
350	600A	SGLA36A10600	HLD63B600	100	
440-480	15	100A	SELA36A10100	HHED63B125	42
	20	100A	SELA36A10100	HHED63B125	42
	25	100A	SELA36A10100	HHED63B125	42
	30	100A	SELA36A10100	HHED63B125	42
	40	100A	SELA36A10100	HHED63B125	42
	50	100A	SELA36A10100	HHED63B125	42
	60	100A	SELA36A10150	HFD63B250	42
	75	200A	SELA36A10150	HFD63B250	50
	100	200A	SELA36A10150	HFD63B250	50
	125	200A	SFLA36A10250	HFD63B250	50
	150	260A	SFLA36A10250	HFD63B250	65
	200	400A	SGLA36A10400	HJD63B400	65
	250	400A	SGLA36A10400	HJD63B400	65
	300	600A	SGLA36A10600	HLD63B600	100
350	600A	SGLA36A10600	HLD63B600	100	
400	600A	SGLA36A10600	HLD63B600	100	

NOTE: THESE RATINGS APPLY TO THE EMERGENCY SIDE IN APPLICATIONS UTILIZING A SINGLE ISOLATING CIRCUIT BREAKER.

Controlled Document
Notify Factory Mutual of all
revisions to this drawing

NOTE: DRAWING NUMBERS 91125-001 THROUGH 91125-003 ARE A SIZE
DRAWING NUMBERS 91125-004 THROUGH 91125-007 ARE B SIZE

PLOT SCALE 1=1

TABLE 4-AUTOMATIC TRANSFER SWITCH RATINGS
EMERGENCY POWER ISOLATING SWITCH (FOR GEN-
SET) & SHORT CIRCUIT RATINGS MODELS: LX2100
2200, 2300, 2400, 2600, 2700, 2800, 2900

ANGLES	HOLE	DATE 7-10-01	DR.	CK.	REF.
LINEAR	PUNCH	UNDIM			
0 X ±.050	±.002	90° ±2'			
0 XX ±.020	±.001				
0 XXX ±.005	±.000				
	REAL SPECIFIED				
	CADD NO. 91125124				
	R.M.S.				
	Hubbell Industrial Controls, Inc.				
	50 Edwards Street Madison, OH 44057				
	DRG. NO. B-91125-004				
	3 OF 3				

Rev	DATE	BY	DESCRIPTION
A	111901	LMH	CORRECT 208V RATINGS FOR 60 & 125 HP