HSTPYG01256IPK25, Thin Wall Polyolefin Heat Shrink Tubing, Yellow/Green, 25-Pack, 6″ Lengths, 1/8″ ID

By Burndy
Catalog # HSTPYG01256IPK25

1/8 I.D., 1 Unit = 1 Pk Of 25, Color = Yellow/Green, 3:1 Shrink Ratio, Thin Wall Polyolefin Heat Shrink, 600V Max, Shrink Temp 90°C Min, -55°C To 135°C Continuous Operating Temp, Store At 21°C.

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 3:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

General

Catalog Number	HSTPYG01256IPK25
Color	Yellow/Green
UPC	621945692510

Logistics

Carton Quantity	80

Product Assets

Brochures - Polyolefin Thin Wall Heat Shrink Brochure
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing
Interactive Catalog - BURNDY Full-Line Digital Catalog
Literature - Distributor Promotion: HS-TP Thin Wall Polyolefin Heat Shrink Expires 12-31-2024
Specifications - HSTPYG01256IPK25

©2024 Hubbell Incorporated. All rights reserved