




PRO READY™

PRODUCT GUIDE

Ultimate G Series Mounting Brackets





Ultimate G Series Brackets


The Ultimate G series mounting brackets from RACO maximize flexibility and productivity in electrical prefab installations. The brackets' gangable design allows for hands-free installation, saving time and effort on the jobsite. Snap the brackets onto any stud or the new open center bracket.

Features and Benefits


- Saves time and increases productivity
- Mounts to either side of the stud
- Gangable design makes it easy to add boxes on either side
- Positive posting tabs ensure consistent alignment on the stud
- Center window for accurate positioning
- Available with integrated Hinged Adjustable Mud Rings

Applications

Ideal for prefab applications, the Ultimate G Series brackets work with both 4" boxes and mud rings or 4-11/16" boxes and mud rings. Mount the brackets to studs or an open center bracket.




Ultimate G Series Brackets with RACO Stab-iT® boxes



Ultimate Mounting Bracket
9030GP



Ultimate Mounting Bracket
with 4" STAB-iT Box
232GSCM




Ultimate Mounting Bracket
with 4 11/16" STAB-iT II Box
252GSCM

Features and Benefits


- Works with any depth 4" and 4-11/16" boxes
- Compatible with any 4" or 4-11/16" mud ring
- Built-in Stab-iT connectors are the fastest way to terminate MC cable
- Part of the ProReady suite of solutions, offering installation flexibility and labor and time savings
- Clips to stud or 9030G open center bracket for hands-free installation
- Gangable, making it easy to add more boxes
- Contractor can decide how to use it at the jobsite



Ultimate Mounting Brackets for EMT/Rigid Conduit



Ultimate Mounting Bracket
with 4" Box
232GHF




Ultimate Mounting Bracket
with 4 11/16" Box
257GHF

Features and Benefits


- Works with EMT and Rigid conduit
- Clips to stud or 9030G open center bracket for hands-free installation
- Gangable design makes it easy to add more boxes
- Contractor can decide how to use it at the jobsite




Ultimate G Series Brackets with Hinge Adjustable Mud Rings



Ultimate Mounting Bracket Single Device
Horizontal with Hinged Adjustable Mud Ring
768HAMRGH



Ultimate Mounting Bracket Single Device
with Hinged Adjustable Mud Ring
768HAMRG



Ultimate Mounting Bracket Two Device
with Hinged Adjustable Mud Ring
769HAMRG

Features and Benefits

- Works with any depth 4" and 4-11/16" boxes
- Includes RACO's exclusive Hinged Adjustable Mud Ring—adjusts from 1/2" to 1-3/8" for when you don't know what the finished wall depth will be
- Hinged design allows easy access for conduit and wiring installation or inspection
- Mounts to stud or 9030G open center bracket for hands-free installation
- Gangable design makes it easy to add boxes on either side
- Contractor can decide how to use it at the job site



Floor Mounted Box Supports



18 in. Floor Mounted
Box Support
GKS18



Adjustable Floor Mounted
Box Support
GKSADJ

Features and Benefits

- Supports electrical boxes with Ultimate G Series Brackets from floor or concrete forms
- GKS18 is designed for mounting square boxes 18" above floor
- GKSADJ, Adjustable Box Support can be adjusted in 1" intervals from 12" to 18"
- Ideal for prefab assemblies



Open Center Bracket



*Open Center
Bracket for G & S Series
9030G*

Features and Benefits

- Taller open center design, exclusive to Ultimate G Series and Universal Stud Mount Brackets
- Large opening allows for mounting multiple boxes anywhere on the bracket
- Adjustable to 16" to 24" studs
- Rigid design eliminates the need for box support in most cases
- For use on wood or metal studs



Box Support Bracket



*Box Support
Bracket - Ultimate G Series
995*

Features and Benefits

- Keeps bracket and box from moving during installation
- Ensures stability when installing on stud
- Exclusive design for the Ultimate G Series
- Accommodates stud depth from 3.5" to 6"
- Required in Canada



Product Information

Catalog No.	Description	Ctn. Qty.	Carton Dimensions Weight x H x W x D (in.)	Carton 12of5
9030GP	Ultimate G Series mounting bracket	25	9.740 x 6.500 x 9.000 x 13.250	50050169985491
232GSCM	Ultimate G Series mounting bracket with 4" STAB-iT box	12	16.320 x 8.000 x 13.000 x 13.750	50050169985507
252GSCM	Ultimate G Series mounting bracket 4-11/16" STAB-iT II box	12	19.900 x 8.000 x 13.000 x15.125	50050169985514
232GHF	4" Square Box with G Series bracket	12	13.75 x 13.00 x 8.00	50050169549136
257GHF	4-11/16" Square Box w/G Series bracket	12	15.125 x 13.00 x 8.00	50050169549143
768HAMRGH	Ultimate G Series mounting bracket single device horizontal with HAMR	20	21.200 x 7.500 x 13.000 x 16x000	50050169985521
768HAMRG	Ultimate G Series mounting bracket single device with HAMR	20	21.200 x 7.500 x 13.000 x 16x000	50050169985538
769HAMRG	Ultimate G Series mounting bracket two device with HAMR	20	21.240 x 7.500 x 13.000 x 16x000	50050169985545
GKS18	Box Support Floor Mount for G Series	25	21.00 x 4.25 x 5.00	50050169549167
GKSADJ	Box Support Floor Mount Adj for G Series	25	15.00 x 4.25 x 5.00	50050169549174
9030G	Open center bracket for G & S Series	25	20.850 x 12.870 x 7.750 x 15.250	50050169985484
995	Box support bracket - Ultimate G Series	50	5.470 x 4.875 x 4.750 x 7.750	50050169985552



RACO strives to provide efficiency and consistency to electrical contractors. Save time, labor, cost, and waste with products designed to streamline installation. Whether contractors need flexibility on site or prefab assembly in the shop, ProReady solutions are perfect for commercial projects with repetitive wiring installs.

GET IN TOUCH:

racocustomerservice@hubbell.com

[\(800\) 992-7030](tel:(800)992-7030)

www.hubbell.com/raco

Raco
3902 W. Sample St.
South Bend, IN 46619

©2025 Raco. All rights reserved.

Hubbell and the Hubbell logo are registered trademarks or trademarks of Hubbell Incorporated. All other trademarks are the property of their respective owners.

EP-RACO-BR-EN-2023-01529 | 08/2025

A Hubbell brand

