



COMPONENTS



RAIL LENGTH	MODEL NUMBER
ft. (m)	
3.0 (0.9)	WS50-T03
4.0 (1.2)	WS50-T04
5.0 (1.5)	WS50-T05
6.0 (1.8)	WS50-T06
7.0 (2.1)	WS50-T07
8.0 (2.4)	WS50-T08
9.0 (2.7)	WS50-T09
10.0 (3.0)	WS50-T10
12.0 (3.6)	WS50-T12

STEEL TRACK, 50 lb.

For loads up to 50 lbs. (22.5 kg)



WS50 TRACK

Beige polyester finish.

USE: Heavy duty tool rail for horizontal supports and vertical columns; up to 50 lbs.(22.5 kg) maximum load.

NOTE: Horizontal track must have a support hanger every 6.0 ft.(1.8m) to maintain maximum rated capacity. Multiple spans of rail must be joined using a COUPLER/HANGER.

Consult factory for lengths not shown above.

Separate TOOL RAIL COMPONENTS allow you to quickly and inexpensively build your own work stations, retrofit existing stations or customize a kit. Finished as shown, all parts are the same high quality included with kits and guaranteed to be interchangeable. All mounting hardware is included.

All components below fit WS50 track. Items outside blue box may also be used with WA50 Extruded Aluminum Track.

WS50-HG HANGER
Black polyester finish.
USE: Hangs single spans of WS50 track from WS50 or WA50 rail and other suitable supports. **Cannot be used to hang WA50 track.**

WS50-CH COUPLER/HANGER
Black polyester finish.
USE: Connects and hangs multiple spans of WS50 track from WS50 or WA50 rail and other suitable supports. **Cannot be used to hang WA50 track.**

WS50-MP UNIVERSAL BASE
Zinc plated steel
USE: Weld or bolt to new or existing benches or conveyors. Provides pocket for mounting WS50 column. Cannot be used with WA50 rail.

WS50-BTL BALANCER TROLLEY
Black polyester finish.
USE: Moving support for tool balancers, etc. Runs in WS50 or WA50 tool rail.

WS50-BTS SINGLE ROLLER BALANCER TROLLEY
Black polyester finish.
USE: Tool balancer trolley. Runs in WS50 or WA50 tool rail.

WS00-CH 90° CONNECTOR
Brass. For 3/8"(9mm) hose.
USE: Attach hose to balancer trolley or various brackets.

WS-AB ANGLE BRACKET
Black polyester finish.
USE: Mounts horizontal tool rail to vertical column.

WS50-TN TRACK NUT
Zinc plated steel.
USE: Attaches fixed components to rail. Slides in from rail end.

WS50-EZTN E-Z NUT
Zinc plated steel.
USE: Attaches fixed components to rail, from front.

WS50-ES END STOP
Zinc plated steel.
USE: Keeps balancer trolley movement within preselected limits.

WS50-ESH END STOP HOOK
Zinc plated steel.
USE: Supports tool balancer. Adjustable location. Also acts as end stop.

WS-EC01
0.31 - 0.59 O.D. (08 - 15mm)
WS-EC02
0.60 - 0.94 O.D. (15 - 24mm)
END CLAMP ASSY
USE: Supports hose/cable and prevents trolley overtravel.

WS50-EP END CAP
Black molded vinyl.
USE: Caps off ends of rail.

WS50-10HR ROLLING HANGER
Black polyester finish.
USE: Supports tool rail beneath track to provide six way tool positioning. Runs in WS50 steel or WA50 aluminum rail. **Hanger will support WS50 track only.**

WS50-06TP
A=6.25 (158)
WS50-10TP
A=10.0 (254)
PLAIN TROLLEY
Black polyester finish.
USE: Utility trolley. Runs in WS50 OR WA50 rail.

WS50-HT01
0.31 - 0.59 O.D. hose (08 - 15mm)
WS50-HT02*
0.60 - 0.94 O.D. hose (15 - 24mm)
HOSE/CABLE TROLLEY
Black polyester finish.
USE: Moving cable/hose clip. Runs in WS50 or WA50 tool rail.

WS50-SPT SWING PLATE TROLLEY
Black polyester finish.
USE: Designed for use with Hose-Hider but also works extremely well alone. Swinging tool hook aids lateral movement. Runs in WS50 OR WA50 tool rail.

WS50-HBS HOOK BRACKET SET (2)
Black polyester finish.
USE: Hang rod to hold rolls of wrap, wire, etc.

WS50-HR03 (04) (05) (06) HANGER ROD
5/8" O.D. X 3/8" I.D. unfinished steel tube in length (ft.) shown

WS-UH UNIVERSAL BRACKET
Black polyester finish.
USE: Supports hose or cable, peg board, etc.

WS50-TB BENCH MOUNT
Beige polyester finish.

WS50-TBS Backing Plate
(Same size as Mounting Base)
Optional

WS50-MB FLOOR MOUNT
Black polyester finish.

WS50-MBS Backing Plate
(Same size as Mounting Base)
Optional

MOUNTING BASE DIMENSIONS

MOUNTING BASE DIMENSIONS