

Hubbell Industrial Controls, Inc.

HMTS 3 Pole Manual Transfer Switches

Selection Table, 3 Pole, *August 2011* New

Discount Schedule. T-1010-CO

Non-Fused, NEMA 1 Enclosure, 3 Pole, with Neutral & Ground Bar		
Ampere Rating	208-240 Volt Part Number	380-480 Volt Part Number
30	HCMTNF30131AB00	HCMTNF30132AB00
60	HCMTNF60131AB00	HCMTNF60132AB00
100	HCMTNF100131AB00	HCMTNF100132AB00
125	HCMTNF125131AB00	HCMTNF125132AB00
200	HCMTNF200131AB00	HCMTNF200132AB00
400	HCMTNF400131AB00	HCMTNF400132AB00
600	HCMTNF600131AB00	HCMTNF600132AB00
800	HCMTNF800131AB00	HCMTNF800132AB00
1200	HCMTNF1200131AB00	HCMTNF1200132AB00

Non-Fused, NEMA 3R Enclosure, 3 Pole, with Neutral & Ground Bar		
Ampere Rating	208-240 Volt Part Number	380-480 Volt Part Number
30	HCMTNF303R31AB00	HCMTNF303R32AB00
60	HCMTNF603R31AB00	HCMTNF603R32AB00
100	HCMTNF1003R31AB00	HCMTNF1003R32AB00
125	HCMTNF1253R31AB00	HCMTNF1253R32AB00
200	HCMTNF2003R31AB00	HCMTNF2003R32AB00
400	HCMTNF4003R31AB00	HCMTNF4003R32AB00
600	HCMTNF6003R31AB00	HCMTNF6003R32AB00
800	HCMTNF8003R31AB00	HCMTNF8003R32AB00
1200	HCMTNF12003R31AB00	HCMTNF12003R32AB00

Non-Fused, NEMA 4X Enclosure, 3 Pole, with Neutral & Ground Bar		
Ampere Rating	208-240 Volt Part Number	380-480 Volt Part Number
30	HCMTNF30X31AB00	HCMTNF30X32AB00
60	HCMTNF60X31AB00	HCMTNF60X32AB00
100	HCMTNF100X31AB00	HCMTNF100X32AB00
125	HCMTNF125X31AB00	HCMTNF125X32AB00
200	HCMTNF200X31AB00	HCMTNF200X32AB00
400	HCMTNF400X31AB00	HCMTNF400X32AB00
600	HCMTNF600X31AB00	HCMTNF600X32AB00
800	HCMTNF800X31AB00	HCMTNF800X32AB00
1200	HCMTNF1200X31AB00	HCMTNF1200X32AB00

Prices subject to change without notice

Consult factory for sizes larger than 1200 amps

Service Entrance Rated, Fused, NEMA 1 Enclosure, 3 Pole		
Ampere Rating	208-240 Volt Part Number	380-480 Volt Part Number
30	HCMTFJ30131AB00	HCMTFJ30132AB00
60	HCMTFJ60131AB00	HCMTFJ60132AB00
100	HCMTFJ100131AB00	HCMTFJ100132AB00
200	HCMTFJ200131AB00	HCMTFJ200132AB00
400	HCMTFJ400131AB00	HCMTFJ400132AB00
600	HCMTFJ600131AB00	HCMTFJ600132AB00
800	HCMTFL800131AB00	HCMTFL800132AB00
1200	HCMTFL1200131AB00	HCMTFL1200132AB00
Service Entrance Rated, Fused, NEMA 3R Enclosure, 3 Pole		
Ampere Rating	208-240 Volt Part Number	380-480 Volt Part Number
30	HCMTFJ303R31AB00	HCMTFJ303R32AB00
60	HCMTFJ603R31AB00	HCMTFJ603R32AB00
100	HCMTFJ1003R31AB00	HCMTFJ1003R32AB00
200	HCMTFJ2003R31AB00	HCMTFJ2003R32AB00
400	HCMTFJ4003R31AB00	HCMTFJ4003R32AB00
600	HCMTFJ6003R31AB00	HCMTFJ6003R32AB00
800	HCMTFL8003R31AB00	HCMTFL8003R32AB00
1200	HCMTFL12003R31AB00	HCMTFL12003R32AB00
Service Entrance Rated, Fused, NEMA 4X Enclosure, 3 Pole		
Ampere Rating	208-240 Volt Part Number	380-480 Volt Part Number
30	HCMTFJ30X31AB00	HCMTFJ30X32AB00
60	HCMTFJ60X31AB00	HCMTFJ60X32AB00
100	HCMTFJ100X31AB00	HCMTFJ100X32AB00
200	HCMTFJ200X31AB00	HCMTFJ200X32AB00
400	HCMTFJ400X31AB00	HCMTFJ400X32AB00
600	HCMTFJ600X31AB00	HCMTFJ600X32AB00
800	HCMTFL800X31AB00	HCMTFL800X32AB00
1200	HCMTFL1200X31AB00	HCMTFL1200X32AB00

Prices subject to change without notice
Consult factory for sizes larger than 1200 amps
Fuses not included
Neutral bar & ground bar included

Hubbell Industrial Controls, Inc.

a subsidiary of Hubbell Incorporated

4301 Cheyenne Dr.
Archdale, NC 27263



Ph. (336) 434-2800
Fax (336) 434-2803
Website <http://www.hubbell-icd.com>
Email: sales@hubbell-icd.com