

Hubbell Industrial Controls, Inc.

HMTS 4 Pole Manual Transfer Switches

Selection Table, 4 Pole, *August 2011* New

Discount Schedule. T-1010-CO

Non-Fused, NEMA 1 Enclosure, 4 Pole, with Neutral & Ground Bar		
Ampere Rating	208-240 Volt Part Number	380-480 Volt Part Number
30	HCMTNF30141AB00	HCMTNF30142AB00
60	HCMTNF60141AB00	HCMTNF60142AB00
100	HCMTNF100141AB00	HCMTNF100142AB00
125	HCMTNF125141AB00	HCMTNF125142AB00
200	HCMTNF200141AB00	HCMTNF200142AB00
400	HCMTNF400141AB00	HCMTNF400142AB00
600	HCMTNF600141AB00	HCMTNF600142AB00
800	HCMTNF800141AB00	HCMTNF800142AB00
1200	HCMTNF1200141AB00	HCMTNF1200142AB00
Non-Fused, NEMA 3R Enclosure, 4 Pole, with Neutral & Ground Bar		
Ampere Rating	208-240 Volt Part Number	380-480 Volt Part Number
30	HCMTNF303R41AB00	HCMTNF303R42AB00
60	HCMTNF603R41AB00	HCMTNF603R42AB00
100	HCMTNF1003R41AB00	HCMTNF1003R42AB00
125	HCMTNF1253R41AB00	HCMTNF1253R42AB00
200	HCMTNF2003R41AB00	HCMTNF2003R42AB00
400	HCMTNF4003R41AB00	HCMTNF4003R42AB00
600	HCMTNF6003R41AB00	HCMTNF6003R42AB00
800	HCMTNF8003R41AB00	HCMTNF8003R42AB00
1200	HCMTNF12003R41AB00	HCMTNF12003R42AB00
Non-Fused, NEMA 4X Enclosure, 4 Pole, with Neutral & Ground Bar		
Ampere Rating	208-240 Volt Part Number	380-480 Volt Part Number
30	HCMTNF30X41AB00	HCMTNF30X42AB00
60	HCMTNF60X41AB00	HCMTNF60X42AB00
100	HCMTNF100X41AB00	HCMTNF100X42AB00
125	HCMTNF125X41AB00	HCMTNF125X42AB00
200	HCMTNF200X41AB00	HCMTNF200X42AB00
400	HCMTNF400X41AB00	HCMTNF400X42AB00
600	HCMTNF600X41AB00	HCMTNF600X42AB00
800	HCMTNF800X41AB00	HCMTNF800X42AB00
1200	HCMTNF1200X41AB00	HCMTNF1200X42AB00

Prices subject to change without notice
 Consult factory for sizes larger than 1200 amps

Service Entrance Rated, Fused, NEMA 1 Enclosure, 4 Pole		
Ampere Rating	208-240 Volt Part Number	380-480 Volt Part Number
30	HCMTFJ30141AB00	HCMTFJ30142AB00
60	HCMTFJ60141AB00	HCMTFJ60142AB00
100	HCMTFJ100141AB00	HCMTFJ100142AB00
200	HCMTFJ200141AB00	HCMTFJ200142AB00
400	HCMTFJ400141AB00	HCMTFJ400142AB00
600	HCMTFJ600141AB00	HCMTFJ600142AB00
800	HCMTFL800141AB00	HCMTFL800142AB00
1200	HCMTFL1200141AB00	HCMTFL1200142AB00
Service Entrance Rated, Fused, NEMA 3R Enclosure, 4 Pole		
Ampere Rating	208-240 Volt Part Number	380-480 Volt Part Number
30	HCMTFJ303R41AB00	HCMTFJ303R42AB00
60	HCMTFJ603R41AB00	HCMTFJ603R42AB00
100	HCMTFJ1003R41AB00	HCMTFJ1003R42AB00
200	HCMTFJ2003R41AB00	HCMTFJ2003R42AB00
400	HCMTFJ4003R41AB00	HCMTFJ4003R42AB00
600	HCMTFJ6003R41AB00	HCMTFJ6003R42AB00
800	HCMTFL8003R41AB00	HCMTFL8003R42AB00
1200	HCMTFL12003R41AB00	HCMTFL12003R42AB00
Service Entrance Rated, Fused, NEMA 4X Enclosure, 4 Pole		
Ampere Rating	208-240 Volt Part Number	380-480 Volt Part Number
30	HCMTFJ30X41AB00	HCMTFJ30X42AB00
60	HCMTFJ60X41AB00	HCMTFJ60X42AB00
100	HCMTFJ100X41AB00	HCMTFJ100X42AB00
200	HCMTFJ200X41AB00	HCMTFJ200X42AB00
400	HCMTFJ400X41AB00	HCMTFJ400X42AB00
600	HCMTFJ600X41AB00	HCMTFJ600X42AB00
800	HCMTFL800X41AB00	HCMTFL800X42AB00
1200	HCMTFL1200X41AB00	HCMTFL1200X42AB00

Prices subject to change without notice
Consult factory for sizes larger than 1200 amps
Fuses not included

Hubbell Industrial Controls, Inc.

a subsidiary of Hubbell Incorporated

4301 Cheyenne Dr.
Archdale, NC 27263



Ph. (336) 434-2800
Fax (336) 434-2803
Website <http://www.hubbell-icd.com>
Email: sales@hubbell-icd.com