



QUALITY PRODUCTS SINCE 1940



QUALITY PRODUCTS SINCE 1940

VERSATILE

- Emergency lamp heads with full vertical and horizontal rotation allow precise aiming
- Heads are reconfigurable from one on each side to two on a single side
- Low profile housing allows for mounting over doorways with low ceiling heights; fits nicely in tight areas.
- Shipped standard with all components for universal single/double face installation
- Universal wall/ceiling/end mounting. Mounting canopy included standard



BRIGHT

- Diffuser is spectrally matched to the LED wavelength for uniform and enhanced EXIT letter color
- MR16 halogen lamps provide a 33% improvement over comparable wattage incandescent lamps

EFFICIENT

- Advanced LED technology ensures economical operation while maintaining bright even illumination
- Remote capacity models coupled with remote heads offer an extended illumination path powered from a single centralized source
- Maintenance-free battery provides 90-minute emergency operation and never needs water

DURABLE

- Sturdy thermoplastic housing is impact-resistant, UV stable and flame-rated for safety
- Lifetime warranty on LED strip
- Unit components warranty: five full years (excluding battery)
- Battery warranty: 1 year full, 5 years pro-rata

COMPLIANT

- Unit is listed to UL standard 924 (emergency lighting)
- NFPA 101 (Life Safety Code) compliant
- NFPA 70 (National Electrical Code) compliant
- International Building Code (IBC) compliant
- EPACT 2005 compliant
- OCR outdoor remote heads are UL listed for wet location installation



EPACT 2005



Hubbell Lighting, Inc. Life Safety Products • www.dual-lite.com
701 Millennium Boulevard • Greenville, SC 29607

A Hubbell Lighting, Inc. brand with representatives' offices in principal cities throughout North America.
Copyright Hubbell Lighting, Inc., All Rights Reserved. Specifications subject to change without notice.

Printed in U.S.A.

060313 Rev B 4/08

HGX SYSTEM

Emergency Lighting Unit and Remote Combinations

LED Emergency Exit Sign
with Side-Mounted Lighting Heads
for Low Profile Installation



HUBBELL LIGHTING, INC.




QUALITY PRODUCTS SINCE 1940

THE HCX SYSTEM

The HCX is a system of options to provide the best possible solution to emergency lighting situations. With a variety of products controlled from one central source, you can design an effective emergency system that is easy to install and maintain.

- HCXURWRC12**
23 watts remote capacity with integral heads removed
- CPRSW0605**
2 single matching 5 watt indoor remote heads
- OCRSZ0605**
2 single 5 watt outdoor remote heads

Mounted at 7'-6" high, a single unit produces 1 FC average with a 3' wide path 24' long. Meets NFPA Life Safety Code illuminance. Assumes open space with 80/50/20 reflectance values. Actual results may vary.



- HCXURWRC12**
12 watts remote capacity
- CPRSW0605**
2 matching 5 watt indoor remote heads

- HCXURWRC12**
23 watts remote capacity with integral heads removed
- CPRSW0605**
2 single matching 5 watt indoor remote heads

- OCRDZ0605**
1 twin 10 watt outdoor remote head

- LXURW-DC**
1 exit sign with -DC option (3 watt input)

